

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Bandpass Filter

ZX75BP-1250-S+

50Ω 1215 to 1285 MHz



Generic photo used for illustration purposes only

CASE STYLE: HY1238

Connectors	Model
SMA-MF	ZX75BP-1250-S+

Features

- Low Insertion loss
- High selectivity
- Good VSWR
- Connectorized package

Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1250	-	MHz
	Insertion Loss	F1-F2	1215-1285	-	1.0	dB
	VSWR	F1-F2	1215-1285	-	1.2	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 1055	20	35	dB
	VSWR	DC-F3	DC - 1055	-	20	:1
Stop Band, Upper	Insertion Loss	F4-F5	1510-2500	20	30	dB
	VSWR	F4-F5	1510-2500	-	20	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	5 W max.

* Passband rating, derate linearly to 3.5W at 85°C ambient. Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	106.01	23622.22	1215	6.02
500	69.45	275.31	1217	5.95
750	59.09	142.31	1220	5.85
1055	39.67	62.52	1225	5.70
1085	30.69	51.63	1230	5.57
1118	20.44	35.09	1235	5.46
1150	9.50	12.31	1240	5.38
1170	3.72	3.79	1245	5.31
1215	1.04	1.10	1250	5.26
1250	0.95	1.05	1255	5.21
1285	0.97	1.08	1260	5.18
1300	1.04	1.20	1262	5.18
1340	3.15	3.52	1265	5.17
1380	10.54	17.14	1268	5.16
1435	20.65	45.88	1270	5.16
1510	30.99	63.20	1275	5.18
1750	57.79	73.96	1278	5.19
2000	43.42	81.65	1280	5.20
2250	40.12	93.49	1282	5.22
2500	38.65	101.11	1285	5.25

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

INPUT	SMA-MALE
OUTPUT	SMA-FEMALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
H	J	K	L	M	N	Wt.
.50	.35	.18	.21	2.05	.106	grams
12.70	8.89	4.57	5.28	52.07	2.69	35.0

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	108.02	106.01	104.74	0.00	0.00	0.00	0.00	0.00	0.00
10	98.96	105.31	101.68	0.00	0.00	0.00	0.00	0.00	0.00
50	104.27	98.08	96.44	0.00	0.00	0.01	0.01	0.01	0.01
100	107.12	109.26	106.63	0.00	0.01	0.01	0.01	0.02	0.02
150	98.07	102.98	99.16	0.00	0.01	0.02	0.02	0.04	0.04
200	91.84	91.11	89.16	0.00	0.02	0.02	0.03	0.06	0.07
300	80.16	82.46	82.84	0.00	0.03	0.04	0.09	0.12	0.14
400	74.45	74.59	74.83	0.01	0.04	0.05	0.16	0.20	0.23
500	69.00	69.45	69.52	0.02	0.06	0.08	0.24	0.30	0.33
600	64.02	64.66	64.85	0.03	0.09	0.11	0.33	0.40	0.44
700	60.35	60.59	61.14	0.04	0.11	0.13	0.42	0.51	0.55
800	57.03	57.46	57.79	0.06	0.13	0.16	0.50	0.60	0.66
900	55.34	55.91	56.32	0.09	0.17	0.20	0.57	0.69	0.77
1000	68.43	64.16	61.72	0.14	0.22	0.26	0.61	0.76	0.86
1050	41.87	41.21	40.61	0.18	0.27	0.31	0.63	0.80	0.90
1055	40.30	39.67	39.07	0.19	0.28	0.32	0.63	0.80	0.91
1087	30.60	30.08	29.58	0.24	0.34	0.40	0.65	0.83	0.94
1095	28.18	27.68	27.17	0.25	0.37	0.43	0.66	0.85	0.96
1100	26.65	26.15	25.64	0.27	0.39	0.45	0.67	0.86	0.98
1118	20.96	20.44	19.94	0.35	0.50	0.58	0.73	0.94	1.07
1140	13.49	12.97	12.50	0.67	0.90	1.06	1.02	1.31	1.49
1150	9.97	9.50	9.09	1.08	1.41	1.65	1.43	1.82	2.07
1170	3.85	3.72	3.60	3.87	4.69	5.28	4.32	5.20	5.77
1185	1.57	1.74	1.81	9.44	10.63	11.48	10.28	11.57	12.40
1200	0.94	1.19	1.31	17.30	18.52	19.59	19.62	21.13	22.41
1215	0.79	1.04	1.17	24.60	26.38	27.79	29.23	32.11	35.63
1230	0.74	0.98	1.11	33.09	36.21	36.86	37.75	47.62	52.02
1250	0.71	0.95	1.08	36.48	33.01	34.55	40.76	38.74	47.40
1270	0.71	0.95	1.08	30.20	30.41	32.39	34.39	38.18	44.12
1285	0.72	0.97	1.11	27.30	27.90	28.25	29.63	30.79	29.48
1300	0.78	1.04	1.19	20.93	20.82	20.24	21.20	20.89	19.94
1310	0.89	1.18	1.36	15.99	15.72	15.16	16.07	15.64	14.93
1320	1.15	1.49	1.71	11.57	11.29	10.85	11.70	11.31	10.80
1325	1.38	1.75	2.00	9.64	9.39	9.03	9.82	9.48	9.06
1330	1.70	2.10	2.39	7.93	7.72	7.43	8.16	7.87	7.54
1340	2.66	3.15	3.50	5.16	5.07	4.91	5.48	5.33	5.15
1370	7.86	8.49	8.89	1.30	1.43	1.48	1.78	1.91	1.98
1380	9.93	10.54	10.93	0.87	1.01	1.08	1.37	1.54	1.64
1400	13.96	14.52	14.87	0.45	0.61	0.69	0.99	1.19	1.31
1435	20.18	20.65	20.93	0.24	0.38	0.45	0.80	1.01	1.14
1475	26.11	26.51	26.75	0.17	0.30	0.37	0.74	0.96	1.09
1500	29.39	29.76	29.98	0.16	0.28	0.34	0.72	0.94	1.08
1510	30.63	30.99	31.21	0.16	0.27	0.33	0.72	0.94	1.07
1550	35.40	35.73	35.93	0.15	0.26	0.31	0.70	0.92	1.06
1600	41.35	41.63	41.82	0.14	0.25	0.30	0.69	0.91	1.04
1650	48.48	48.69	48.87	0.14	0.24	0.29	0.68	0.91	1.03
1700	62.48	62.50	62.55	0.14	0.24	0.29	0.68	0.90	1.01
1725	67.98	68.59	69.55	0.14	0.24	0.28	0.68	0.89	1.01
1750	57.30	57.79	58.08	0.14	0.23	0.28	0.69	0.90	1.00
1775	53.14	53.50	53.89	0.14	0.23	0.28	0.70	0.90	1.00
1800	50.60	51.03	51.34	0.13	0.23	0.28	0.71	0.90	1.00
1825	48.82	49.23	49.58	0.13	0.23	0.27	0.72	0.91	1.00
1850	47.48	47.88	48.24	0.13	0.23	0.27	0.74	0.92	1.01
1900	45.56	45.94	46.25	0.12	0.22	0.27	0.77	0.94	1.03
1950	44.11	44.53	44.78	0.12	0.22	0.26	0.81	0.97	1.06
2000	43.03	43.42	43.67	0.11	0.21	0.26	0.86	1.02	1.11
2100	41.41	41.77	41.99	0.09	0.20	0.25	0.97	1.14	1.25
2300	39.39	39.72	39.96	0.07	0.18	0.24	1.19	1.45	1.63
2400	38.74	39.13	39.40	0.05	0.18	0.24	1.27	1.58	1.79
2500	38.22	38.65	38.98	0.04	0.17	0.25	1.34	1.68	1.89



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com







IF/RF MICROWAVE COMPONENTS

REV. A
ZX75BP-1250-S+
181218


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1215	6.12	6.02	5.96
1216	6.08	5.99	5.92
1217	6.04	5.95	5.89
1218	5.99	5.91	5.86
1219	5.96	5.88	5.82
1220	5.92	5.85	5.79
1221	5.88	5.81	5.76
1222	5.85	5.79	5.73
1223	5.82	5.75	5.70
1224	5.79	5.73	5.68
1225	5.76	5.70	5.65
1226	5.73	5.67	5.62
1227	5.70	5.64	5.60
1228	5.67	5.62	5.57
1229	5.65	5.60	5.55
1230	5.63	5.57	5.53
1231	5.60	5.55	5.51
1232	5.58	5.52	5.49
1233	5.56	5.51	5.47
1234	5.53	5.49	5.45
1235	5.51	5.46	5.43
1236	5.50	5.45	5.42
1237	5.48	5.43	5.40
1238	5.46	5.41	5.38
1239	5.44	5.40	5.37
1240	5.42	5.38	5.35
1241	5.41	5.36	5.34
1242	5.39	5.35	5.33
1243	5.38	5.34	5.31
1244	5.36	5.32	5.30
1245	5.34	5.31	5.28
1246	5.34	5.30	5.28
1247	5.32	5.29	5.26
1248	5.31	5.28	5.26
1249	5.30	5.27	5.24
1250	5.29	5.26	5.24
1251	5.27	5.24	5.23
1252	5.26	5.23	5.22
1253	5.25	5.23	5.21
1254	5.24	5.22	5.20
1255	5.24	5.21	5.20
1256	5.23	5.21	5.19
1257	5.22	5.20	5.19
1258	5.22	5.19	5.19
1259	5.21	5.19	5.18
1260	5.20	5.18	5.17
1261	5.19	5.18	5.17
1262	5.19	5.18	5.17
1263	5.18	5.17	5.16
1264	5.18	5.17	5.16
1265	5.18	5.17	5.16
1266	5.18	5.17	5.16
1267	5.18	5.16	5.15
1268	5.17	5.16	5.16
1269	5.17	5.16	5.16
1270	5.17	5.16	5.16
1275	5.18	5.18	5.18
1280	5.20	5.20	5.21
1283	5.22	5.23	5.24
1285	5.24	5.25	5.26

Typical Performance Curves



Typical Performance Curves




Case Style

HY

Outline Dimensions

HY1238



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1238	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	2.05 (52.07)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
 Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A