

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Bandpass Filter

ZX75BP-1260-S+

50Ω 1200 to 1320 MHz



Generic photo used for illustration purposes only

CASE STYLE: HY1238

Connectors	Model
SMA-MF	ZX75BP-1260-S+

Features

- Low Insertion loss
- High selectivity
- Good VSWR
- Connectorized package

Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1260	-	MHz
	Insertion Loss	F1-F2	1200 - 1320	1.2	2	dB
	VSWR	F1-F2	1200 - 1320	1.4	-	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 1025	20	35	dB
	VSWR	DC-F3	DC - 1025	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	1640 - 2500	20	30	dB
	VSWR	F4-F5	1640 - 2500	20	-	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	5 W max.

* Passband rating, derate linearly to 3.5W at 85°C ambient. Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	99.26	5132.29	1200	5.18
500	70.47	398.12	1210	4.93
750	61.36	219.58	1220	4.74
1025	39.74	98.13	1230	4.58
1060	30.47	77.83	1240	4.41
1095	20.40	47.51	1245	4.34
1145	4.05	4.23	1250	4.27
1155	2.20	2.22	1255	4.22
1200	1.12	1.34	1260	4.17
1260	1.03	1.33	1265	4.14
1320	1.04	1.28	1270	4.11
1390	2.34	2.67	1275	4.07
1400	3.03	3.43	1280	4.07
1450	9.07	14.51	1285	4.06
1535	20.12	57.89	1290	4.05
1640	30.43	92.69	1295	4.05
1800	44.68	103.60	1300	4.03
2000	55.80	111.64	1310	4.05
2250	59.78	112.53	1315	4.07
2500	60.21	104.12	1320	4.10

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

INPUT	SMA-MALE
OUTPUT	SMA-FEMALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
H	J	K	L	M	N	Wt.
.50	.35	.18	.21	2.05	.106	grams
12.70	8.89	4.57	5.28	52.07	2.69	35.0

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	103.80	99.26	102.19	0.00	0.00	0.00	0.01	0.00	0.00
10	101.59	101.08	97.81	0.00	0.00	0.00	0.00	0.00	0.01
50	96.90	94.77	105.11	0.01	0.01	0.01	0.01	0.02	0.03
100	105.71	103.90	110.67	0.01	0.01	0.01	0.01	0.03	0.04
150	107.11	98.09	98.55	0.00	0.01	0.01	0.02	0.05	0.06
200	94.76	93.92	93.26	0.00	0.02	0.02	0.04	0.07	0.09
300	82.59	84.14	82.63	0.00	0.02	0.03	0.11	0.16	0.18
400	75.54	75.81	76.33	0.00	0.03	0.04	0.21	0.26	0.30
500	70.57	70.47	70.80	0.01	0.04	0.06	0.29	0.37	0.41
600	66.17	66.67	66.13	0.01	0.06	0.07	0.38	0.47	0.53
700	62.72	62.80	62.92	0.02	0.07	0.09	0.46	0.57	0.64
800	60.17	60.29	60.53	0.04	0.09	0.11	0.51	0.64	0.73
900	62.53	62.89	62.89	0.06	0.12	0.14	0.58	0.73	0.83
1000	46.88	46.54	46.25	0.10	0.16	0.18	0.65	0.82	0.94
1025	40.07	39.74	39.47	0.11	0.18	0.20	0.67	0.86	0.97
1040	36.14	35.79	35.51	0.13	0.20	0.22	0.69	0.88	0.99
1060	30.85	30.47	30.19	0.15	0.22	0.25	0.72	0.92	1.04
1095	20.86	20.40	20.06	0.27	0.37	0.42	0.85	1.08	1.21
1120	12.66	12.14	11.76	0.64	0.84	0.97	1.27	1.59	1.79
1130	9.15	8.67	8.30	1.15	1.47	1.70	1.81	2.27	2.56
1148	3.55	3.37	3.21	4.27	5.21	5.99	5.16	6.30	7.20
1150	3.09	2.97	2.85	4.96	6.01	6.89	5.91	7.19	8.21
1175	1.01	1.24	1.38	17.24	17.29	17.35	21.98	22.90	22.52
1200	0.89	1.12	1.24	16.95	16.86	17.06	18.11	18.19	18.38
1225	0.79	1.02	1.14	20.80	20.19	20.53	22.47	22.46	23.62
1250	0.80	1.02	1.15	18.22	17.70	17.58	19.83	20.15	20.54
1260	0.81	1.03	1.16	17.46	17.02	16.89	19.02	19.34	19.58
1275	0.80	1.03	1.16	17.41	16.97	16.84	18.99	19.17	19.25
1300	0.78	1.01	1.14	18.99	18.30	18.23	20.73	20.27	20.22
1320	0.80	1.04	1.17	18.80	18.14	18.28	19.89	19.25	19.44
1360	1.07	1.34	1.48	12.61	12.50	12.70	12.79	12.71	12.97
1390	1.99	2.34	2.57	6.88	6.84	6.79	7.31	7.33	7.39
1410	3.49	3.93	4.26	3.87	3.89	3.84	4.50	4.63	4.68
1425	5.16	5.66	6.05	2.40	2.46	2.45	3.14	3.33	3.43
1450	8.52	9.07	9.52	1.09	1.20	1.23	1.95	2.22	2.37
1460	9.93	10.49	10.95	0.82	0.94	0.98	1.72	2.00	2.15
1500	15.34	15.90	16.34	0.32	0.44	0.50	1.32	1.61	1.78
1540	20.13	20.68	21.07	0.18	0.29	0.34	1.24	1.51	1.66
1600	26.34	26.84	27.14	0.12	0.22	0.26	1.23	1.47	1.62
1640	29.99	30.43	30.65	0.10	0.19	0.23	1.26	1.50	1.66
1650	30.86	31.28	31.49	0.11	0.19	0.23	1.27	1.51	1.69
1675	32.94	33.31	33.49	0.10	0.18	0.22	1.33	1.59	1.80
1700	34.93	35.28	35.41	0.09	0.17	0.21	1.44	1.75	2.00
1725	36.86	37.18	37.29	0.09	0.17	0.20	1.66	2.06	2.41
1750	38.85	39.14	39.26	0.10	0.17	0.20	2.10	2.67	3.20
1775	41.02	41.40	41.66	0.09	0.17	0.20	2.98	3.93	4.83
1800	44.01	44.68	45.23	0.09	0.17	0.20	4.80	6.43	7.93
1825	49.20	50.48	51.57	0.09	0.16	0.19	7.27	8.75	9.41
1850	60.72	62.94	64.45	0.09	0.16	0.19	6.38	6.39	6.21
1875	60.97	60.65	60.51	0.09	0.16	0.19	4.01	3.98	3.93
1900	56.06	56.46	56.80	0.10	0.17	0.19	2.64	2.71	2.75
1925	54.90	55.45	55.69	0.09	0.17	0.19	1.91	2.03	2.11
1950	54.65	55.25	55.48	0.09	0.16	0.18	1.49	1.63	1.73
1975	55.00	55.42	55.68	0.08	0.16	0.18	1.23	1.38	1.48
2000	55.46	55.80	56.13	0.08	0.16	0.18	1.06	1.21	1.31
2100	57.48	57.62	57.80	0.08	0.15	0.18	0.71	0.87	0.98
2200	58.94	59.23	59.39	0.08	0.16	0.19	0.57	0.74	0.84
2300	60.16	60.51	60.67	0.08	0.16	0.19	0.49	0.66	0.76
2400	62.67	63.05	63.42	0.08	0.17	0.21	0.43	0.61	0.72
2500	59.85	60.21	60.42	0.07	0.17	0.22	0.40	0.59	0.70



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com







IF/RF MICROWAVE COMPONENTS

REV. A
ZX75BP-1260-S+
181218


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1200	5.25	5.18	5.13
1202	5.19	5.12	5.08
1204	5.11	5.06	5.03
1206	5.06	5.00	4.97
1208	5.04	4.97	4.94
1210	4.98	4.93	4.90
1212	4.94	4.89	4.86
1214	4.90	4.86	4.82
1216	4.86	4.82	4.78
1218	4.83	4.78	4.76
1220	4.79	4.74	4.73
1222	4.75	4.71	4.68
1224	4.71	4.67	4.64
1226	4.69	4.65	4.63
1228	4.66	4.62	4.59
1230	4.61	4.58	4.55
1232	4.56	4.53	4.51
1234	4.54	4.51	4.48
1236	4.52	4.47	4.45
1238	4.47	4.44	4.42
1240	4.44	4.41	4.38
1242	4.41	4.38	4.35
1244	4.39	4.36	4.33
1246	4.36	4.34	4.32
1248	4.33	4.29	4.29
1250	4.30	4.27	4.26
1252	4.28	4.27	4.24
1254	4.26	4.25	4.22
1256	4.24	4.22	4.21
1258	4.20	4.19	4.17
1260	4.18	4.17	4.16
1262	4.18	4.16	4.14
1264	4.17	4.14	4.13
1266	4.15	4.13	4.11
1268	4.13	4.12	4.09
1270	4.13	4.11	4.09
1272	4.11	4.09	4.09
1274	4.11	4.08	4.09
1276	4.09	4.07	4.06
1278	4.08	4.08	4.06
1280	4.08	4.07	4.05
1282	4.08	4.07	4.06
1284	4.07	4.07	4.06
1286	4.04	4.04	4.03
1288	4.05	4.04	4.03
1290	4.07	4.05	4.04
1292	4.05	4.04	4.03
1294	4.04	4.04	4.02
1296	4.05	4.04	4.02
1298	4.05	4.04	4.04
1300	4.05	4.03	4.04
1302	4.06	4.04	4.04
1304	4.05	4.04	4.04
1306	4.05	4.04	4.05
1308	4.06	4.04	4.05
1310	4.07	4.05	4.05
1312	4.07	4.07	4.06
1314	4.06	4.06	4.05
1316	4.07	4.08	4.06
1320	4.08	4.10	4.09

Typical Performance Curves



Typical Performance Curves




Case Style

HY

Outline Dimensions

HY1238



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1238	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	2.05 (52.07)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
 Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A