

Coaxial Bandpass Filter

ZX75BP-1940-S+

50Ω 1710 to 2170 MHz

The Big Deal

- Fast roll-off on the upper sideband
- Good Matching and low loss in the pass band
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: KE1467

Product Overview

ZX75BP-1940-S+ is a wideband bandpass filter in a rugged connectorized package covering 1710 to 2170 MHz. This is designed for asymmetric rejection applications such as super-heterodyne receivers. By having asymmetric band, faster roll-off at upper side band is achieved in a comparatively smaller package and lower pass band insertion loss. It has repeatable performance across lots and consistent performance across temperature

Key Features

Feature	Advantages
Fast roll-off on the upper side band	Wide bandwidth filter with fast-roll off on the upper side band, which increases selectivity on the adjacent channel.
Good matching and low loss in pass band	This filter has good matching and low loss in the pass band
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.
High power handling	This model uses high Q capacitors and high current handling inductors which is well suited for high power applications.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Bandpass Filter

50Ω 1710 to 2170 MHz

ZX75BP-1940-S+



Generic photo used for illustration purposes only

CASE STYLE: KE1467	
Connectors	Model
SMA-MF	ZX75BP-1940-S+


Features

- Fast roll-off on the upper side band
- Good matching in the pass band
- Connectorized package


Applications

- Defense systems
- Cable TV relay
- DECT, GSM and IMT
- Mobile satellite
- Private and public land mobile
- PCS Broadband

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1940	-	MHz
	Insertion Loss	F1-F2	1710-2170	0.7	2.0	dB
	VSWR	F1-F2	1710-2170	-	1.2	1.78
Stop Band, Lower	Insertion Loss	DC-F3	DC - 150	20	30	dB
	VSWR	DC-F3	DC - 150	-	20	-
Stop Band, Upper	Insertion Loss	F4-F5	2800-4000	20	31	dB
	VSWR	F4-F5	2800-4000	-	20	-

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	8 W max.





Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
5	59.48	1737.18	1710	1.06
40	41.47	1737.18	1730	1.05
150	30.00	579.06	1750	1.04
400	21.49	133.63	1780	1.03
750	15.61	49.64	1800	1.02
1250	7.24	13.70	1830	1.02
1450	3.00	4.78	1850	1.02
1530	1.63	2.89	1870	1.03
1710	0.40	1.14	1890	1.03
1940	0.45	1.15	1900	1.04
2170	0.60	1.08	1920	1.05
2280	1.52	2.08	1940	1.06
2340	3.67	4.36	1960	1.07
2400	7.26	9.43	1980	1.08
2500	14.13	22.87	2000	1.10
2600	20.58	34.75	2030	1.13
2800	31.78	46.96	2050	1.15
3000	41.55	51.10	2100	1.21
3500	58.35	56.04	2140	1.29
4000	60.06	56.04	2170	1.37

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

INPUT	SMA-MALE
OUTPUT	SMA-FEMALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G
.74	.75	.46	1.18	.04	.362	.21
18.80	19.05	11.68	29.97	1.02	9.19	5.33
H	J	K	L	M	Wt.	
.362	1.00	.37	.18	.11	grams	
9.19	25.40	9.40	4.57	2.79	24.4	

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
5	59.57	59.48	59.49	0.00	0.00	0.00	0.00	0.00	0.00
10	53.58	53.53	53.54	0.00	0.00	0.00	0.00	0.00	0.00
20	47.50	47.51	47.47	0.00	0.00	0.00	0.00	0.00	0.00
45	40.47	40.47	40.42	0.00	0.01	0.00	0.00	0.00	0.00
90	34.52	34.43	34.37	0.00	0.01	0.01	0.00	0.01	0.01
150	30.14	30.00	29.89	0.01	0.03	0.03	0.00	0.01	0.01
260	25.24	25.24	25.16	0.04	0.06	0.07	0.02	0.03	0.04
470	19.98	20.07	20.15	0.13	0.16	0.17	0.05	0.07	0.08
510	19.26	19.35	19.42	0.16	0.19	0.19	0.06	0.09	0.09
590	17.93	18.01	18.07	0.20	0.24	0.24	0.09	0.11	0.12
720	15.98	16.04	16.10	0.28	0.33	0.33	0.14	0.17	0.18
850	14.10	14.15	14.21	0.38	0.43	0.43	0.22	0.25	0.26
990	11.93	12.00	12.03	0.53	0.58	0.58	0.35	0.39	0.40
1090	10.24	10.32	10.32	0.69	0.74	0.75	0.52	0.56	0.57
1210	7.98	8.06	8.02	1.02	1.08	1.12	0.88	0.93	0.95
1300	6.14	6.19	6.14	1.51	1.59	1.65	1.40	1.45	1.50
1400	4.01	4.03	3.98	2.59	2.71	2.82	2.51	2.61	2.70
1450	2.98	3.00	2.96	3.52	3.69	3.83	3.47	3.61	3.73
1500	2.06	2.09	2.07	4.90	5.11	5.31	4.88	5.06	5.22
1580	0.97	1.02	1.04	8.46	8.84	9.12	8.50	8.84	9.09
1610	0.71	0.77	0.79	10.42	10.90	11.23	10.50	10.94	11.23
1710	0.31	0.40	0.45	22.81	23.93	24.40	22.83	23.96	24.70
1740	0.29	0.39	0.44	33.55	36.34	36.35	31.09	33.37	36.47
1770	0.30	0.39	0.44	32.70	32.83	32.73	29.66	30.46	31.38
1800	0.31	0.41	0.46	25.38	25.84	26.24	24.61	25.24	25.75
1840	0.33	0.43	0.48	21.96	22.61	23.19	21.78	22.49	23.00
1890	0.35	0.44	0.49	20.95	21.77	22.56	21.10	21.98	22.65
1910	0.35	0.44	0.50	21.13	22.06	22.97	21.42	22.41	23.21
1940	0.35	0.45	0.51	21.84	23.03	24.15	22.45	23.76	24.86
1980	0.36	0.46	0.52	23.50	25.22	26.80	24.45	26.59	28.49
2020	0.36	0.47	0.53	25.48	27.77	29.47	26.53	29.51	32.11
2060	0.38	0.49	0.56	26.49	28.26	28.81	26.62	28.34	29.01
2090	0.39	0.52	0.59	26.56	27.65	27.61	25.80	26.62	26.63
2130	0.42	0.55	0.63	27.33	28.08	27.53	25.55	25.88	25.37
2170	0.46	0.60	0.69	28.32	28.05	26.73	25.92	25.26	24.00
2210	0.54	0.71	0.82	20.84	20.08	19.33	20.36	19.31	18.38
2230	0.64	0.83	0.95	16.86	16.26	15.73	16.65	15.82	15.15
2280	1.25	1.52	1.70	9.40	9.08	8.82	9.23	8.81	8.51
2300	1.74	2.05	2.27	7.25	7.02	6.83	7.06	6.77	6.55
2330	2.82	3.20	3.46	4.79	4.67	4.57	4.58	4.43	4.31
2350	3.77	4.19	4.49	3.60	3.54	3.49	3.39	3.30	3.23
2390	6.11	6.60	6.93	2.06	2.09	2.10	1.85	1.85	1.85
2410	7.42	7.93	8.26	1.59	1.64	1.67	1.38	1.41	1.43
2470	11.55	12.08	12.42	0.83	0.93	0.98	0.63	0.71	0.74
2530	15.61	16.13	16.48	0.54	0.64	0.71	0.34	0.42	0.47
2590	19.45	19.97	20.31	0.41	0.52	0.58	0.22	0.30	0.34
2600	20.07	20.58	20.92	0.40	0.50	0.56	0.21	0.29	0.33
2670	24.23	24.72	25.07	0.33	0.43	0.50	0.15	0.23	0.27
2770	29.75	30.22	30.56	0.28	0.38	0.45	0.11	0.19	0.22
2800	31.32	31.78	32.13	0.27	0.37	0.44	0.11	0.19	0.22
2960	39.22	39.67	40.02	0.24	0.35	0.40	0.09	0.16	0.19
3080	44.75	45.12	45.48	0.22	0.33	0.39	0.08	0.15	0.18
3220	50.63	50.90	51.14	0.21	0.32	0.38	0.07	0.15	0.17
3400	56.52	56.56	56.66	0.20	0.32	0.37	0.08	0.15	0.18
3605	59.69	59.63	59.48	0.20	0.31	0.37	0.08	0.15	0.19
3705	60.16	60.12	59.73	0.20	0.31	0.37	0.08	0.16	0.19
3785	60.27	59.95	59.60	0.19	0.31	0.37	0.09	0.16	0.19
3805	60.29	60.02	59.69	0.19	0.31	0.37	0.09	0.16	0.19
3965	60.12	59.76	59.54	0.19	0.31	0.37	0.09	0.17	0.20
4000	60.20	60.06	59.68	0.19	0.31	0.38	0.09	0.17	0.21


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1710	1.07	1.06	1.05
1720	1.06	1.05	1.04
1730	1.06	1.05	1.04
1740	1.06	1.04	1.04
1750	1.05	1.04	1.03
1760	1.05	1.04	1.03
1770	1.04	1.03	1.03
1780	1.04	1.03	1.02
1790	1.04	1.03	1.02
1800	1.03	1.02	1.02
1810	1.03	1.02	1.02
1820	1.03	1.02	1.02
1830	1.03	1.02	1.02
1840	1.03	1.02	1.02
1850	1.03	1.02	1.02
1860	1.03	1.02	1.02
1870	1.03	1.03	1.02
1880	1.04	1.03	1.03
1890	1.04	1.03	1.03
1900	1.04	1.04	1.03
1910	1.05	1.04	1.04
1920	1.05	1.05	1.04
1930	1.06	1.05	1.05
1940	1.06	1.06	1.05
1950	1.07	1.06	1.06
1960	1.08	1.07	1.07
1970	1.08	1.08	1.08
1980	1.09	1.08	1.08
1990	1.10	1.09	1.09
2000	1.11	1.10	1.10
2010	1.11	1.11	1.11
2020	1.12	1.12	1.12
2030	1.13	1.13	1.13
2040	1.14	1.14	1.14
2050	1.15	1.15	1.15
2060	1.16	1.16	1.16
2070	1.18	1.17	1.17
2080	1.19	1.19	1.18
2090	1.20	1.20	1.20
2100	1.22	1.21	1.21
2110	1.23	1.23	1.23
2120	1.25	1.25	1.25
2130	1.27	1.27	1.27
2140	1.29	1.29	1.29
2150	1.31	1.32	1.32
2160	1.34	1.34	1.35
2170	1.37	1.37	1.38


Typical Performance Curves



Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A