

# Coaxial Bandpass Filter

## ZX75BP-2150-S+

50Ω 2050 to 2250 MHz

### The Big Deal

- Fast roll-off on the upper sideband
- Good Matching and low loss in the pass band
- Connectorized package



Generic photo used for illustration purposes only  
CASE STYLE: KE1467

### Product Overview

ZX75BP-2150-S+ is a wideband bandpass filter in a rugged connectorized package covering 2050 to 2250 MHz. This is designed for asymmetric rejection applications such as super-heterodyne receivers. By having asymmetric band, faster roll-off at upper side band is achieved in a comparatively smaller package and lower pass band insertion loss. It has repeatable performance across lots and consistent performance across temperature

### Key Features

Feature	Advantages
Fast roll-off on the upper side band	Wide bandwidth filter with fast-roll off on the upper side band, which increases selectivity on the adjacent channel.
Good matching and low loss in pass band	This filter has good matching and low loss in the pass band
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.
High power handling	This model uses high Q capacitors and high current handling inductors which is well suited for high power applications.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial Bandpass Filter

50Ω 2050 to 2250 MHz

## ZX75BP-2150-S+



Generic photo used for illustration purposes only

CASE STYLE: KE1467

Connectors	Model
SMA-MF	ZX75BP-2150-S+


### Features

- Fast roll-off on the upper side band
- Good matching in the pass band
- Connectorized package


### Applications

- Defense systems
- Fixed microwave
- IMT
- Auxiliary broadcasting
- Private and public land mobile

### Functional Schematic



### Typical Frequency Response



### Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	2150	-	MHz
	Insertion Loss	F1-F2	2050-2250	0.8	2.0	dB
	VSWR	F1-F2	2050-2250	1.3	1.78	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 600	20	-	dB
	VSWR	DC-F3	DC - 600	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	2720-4500	20	-	dB
	VSWR	F4-F5	2720-4500	20	-	:1

### Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	6.3 W max.





Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	85.06	1737.18	2050	1.43
50	51.32	1737.18	2060	1.43
525	31.10	347.44	2070	1.43
600	29.95	289.53	2080	1.43
1250	20.93	86.86	2090	1.43
1500	15.46	52.65	2100	1.44
1725	7.90	15.39	2110	1.44
1850	3.09	4.62	2120	1.45
1900	1.73	2.79	2130	1.46
2050	0.55	1.15	2140	1.48
2150	0.58	1.08	2150	1.49
2250	0.76	1.14	2160	1.51
2310	1.57	1.98	2170	1.53
2350	3.30	3.70	2180	1.55
2400	7.07	8.77	2200	1.61
2500	16.02	28.03	2210	1.64
2560	20.97	39.49	2220	1.69
2720	32.37	59.91	2230	1.73
3500	60.08	124.09	2240	1.78
4500	55.33	133.63	2250	1.84

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

INPUT	SMA-MALE
OUTPUT	SMA-FEMALE

## Outline Drawing



## Outline Dimensions ( $\frac{\text{inch}}{\text{mm}}$ )

A	B	C	D	E	F	G
.74	.75	.46	1.18	.04	.362	.21
18.80	19.05	11.68	29.97	1.02	9.19	5.33
H	J	K	L	M	Wt.	
.362	1.00	.37	.18	.11	grams	
9.19	25.40	9.40	4.57	2.79	24.4	

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)









*Typical Performance Data*

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	84.54	85.06	85.41	0.00	0.00	0.00	0.00	0.00	0.00
2	78.43	79.18	79.95	0.00	0.00	0.00	0.00	0.00	0.00
4	73.31	73.25	73.07	0.00	0.00	0.00	0.00	0.00	0.00
10	65.44	65.37	65.02	0.00	0.00	0.00	0.00	0.00	0.00
20	59.23	59.33	59.23	0.00	0.00	0.00	0.00	0.00	0.00
35	54.38	54.36	54.39	0.00	0.00	0.00	0.00	0.00	0.00
55	50.52	50.51	50.41	0.00	0.00	0.00	0.00	0.00	0.00
95	45.85	45.74	45.67	0.00	0.00	0.01	0.00	0.00	0.00
185	40.11	39.98	39.87	0.01	0.01	0.01	0.01	0.00	0.01
265	36.93	36.90	36.82	0.01	0.01	0.02	0.01	0.01	0.01
590	30.02	30.09	30.14	0.02	0.06	0.06	0.00	0.02	0.04
600	29.88	29.95	29.99	0.02	0.06	0.07	0.00	0.02	0.04
970	25.06	25.12	25.17	0.08	0.13	0.14	0.03	0.07	0.08
1295	20.03	20.10	20.08	0.15	0.21	0.24	0.09	0.14	0.15
1465	16.36	16.38	16.31	0.23	0.30	0.34	0.18	0.23	0.26
1605	12.35	12.30	12.21	0.42	0.51	0.56	0.39	0.46	0.50
1645	10.99	10.93	10.83	0.53	0.64	0.70	0.51	0.59	0.64
1720	8.17	8.10	8.00	0.94	1.08	1.17	0.95	1.06	1.14
1770	6.15	6.09	6.00	1.50	1.68	1.81	1.52	1.67	1.79
1820	4.18	4.14	4.08	2.53	2.78	2.96	2.58	2.80	2.98
1850	3.11	3.09	3.05	3.53	3.82	4.05	3.59	3.87	4.10
1885	2.06	2.08	2.08	5.20	5.56	5.84	5.30	5.65	5.95
1920	1.28	1.35	1.39	7.57	7.99	8.30	7.72	8.14	8.50
1965	0.71	0.82	0.88	11.84	12.22	12.51	12.09	12.50	12.90
2030	0.43	0.57	0.65	20.58	20.33	20.24	20.87	20.78	20.96
2050	0.41	0.55	0.63	23.67	23.01	22.67	23.79	23.39	23.34
2080	0.41	0.54	0.63	27.65	26.49	25.81	27.07	26.39	25.92
2110	0.41	0.55	0.64	28.88	28.21	27.46	27.83	27.49	26.91
2150	0.44	0.58	0.67	27.23	27.85	27.43	26.22	26.78	26.39
2180	0.47	0.61	0.71	27.00	28.22	28.12	25.67	26.62	26.43
2210	0.50	0.65	0.76	29.76	31.71	31.53	26.90	27.76	27.13
2250	0.57	0.76	0.89	25.88	23.96	22.65	24.18	22.32	20.97
2290	0.88	1.14	1.33	13.98	13.23	12.58	13.79	12.87	12.15
2325	1.69	2.07	2.36	7.89	7.50	7.14	7.78	7.28	6.89
2345	2.56	3.02	3.38	5.51	5.27	5.03	5.39	5.07	4.82
2355	3.11	3.61	4.00	4.58	4.39	4.22	4.46	4.21	4.01
2395	6.02	6.63	7.10	2.17	2.16	2.14	2.04	1.99	1.95
2430	9.12	9.76	10.24	1.21	1.27	1.30	1.07	1.10	1.12
2460	11.85	12.49	12.96	0.80	0.89	0.94	0.67	0.73	0.76
2485	14.10	14.72	15.17	0.60	0.70	0.76	0.48	0.55	0.59
2500	15.41	16.02	16.47	0.52	0.62	0.69	0.40	0.47	0.51
2555	20.01	20.58	21.00	0.35	0.45	0.52	0.24	0.32	0.36
2620	24.98	25.52	25.91	0.26	0.36	0.42	0.16	0.24	0.27
2695	30.21	30.72	31.10	0.20	0.30	0.36	0.13	0.19	0.23
2720	31.84	32.37	32.74	0.19	0.29	0.35	0.11	0.18	0.21
2845	39.53	40.02	40.37	0.14	0.24	0.30	0.09	0.16	0.18
2950	45.38	45.81	46.12	0.11	0.21	0.27	0.08	0.14	0.16
3035	49.63	50.10	50.39	0.09	0.20	0.25	0.07	0.14	0.16
3120	53.50	53.73	54.05	0.07	0.18	0.24	0.07	0.13	0.16
3230	57.12	57.40	57.53	0.05	0.17	0.23	0.07	0.13	0.16
3390	60.00	59.99	59.80	0.03	0.15	0.21	0.06	0.13	0.15
3440	59.99	60.04	60.10	0.03	0.15	0.21	0.06	0.13	0.16
3515	60.11	60.04	59.85	0.02	0.14	0.20	0.06	0.13	0.16
3600	59.60	59.52	59.30	0.02	0.14	0.20	0.06	0.13	0.16
3700	58.98	58.86	58.79	0.01	0.13	0.19	0.06	0.13	0.16
3925	57.52	57.32	57.07	0.01	0.12	0.19	0.06	0.13	0.18
4175	56.26	55.97	55.79	0.00	0.12	0.20	0.05	0.13	0.19
4350	55.70	55.51	55.30	0.00	0.13	0.21	0.04	0.14	0.20
4450	55.37	55.31	55.20	0.00	0.13	0.22	0.03	0.14	0.20
4500	55.35	55.33	55.32	0.00	0.13	0.23	0.03	0.14	0.20


*Typical Performance Data*

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
2050	1.44	1.43	1.43
2055	1.43	1.43	1.42
2060	1.44	1.43	1.42
2065	1.43	1.43	1.42
2070	1.43	1.43	1.42
2075	1.43	1.43	1.42
2080	1.44	1.43	1.43
2085	1.43	1.43	1.43
2090	1.44	1.43	1.43
2095	1.43	1.43	1.43
2100	1.44	1.44	1.44
2105	1.44	1.44	1.44
2110	1.44	1.44	1.44
2115	1.46	1.45	1.45
2120	1.45	1.45	1.45
2125	1.46	1.46	1.46
2130	1.46	1.46	1.46
2135	1.46	1.47	1.47
2140	1.47	1.48	1.48
2145	1.48	1.48	1.48
2150	1.48	1.49	1.49
2155	1.50	1.50	1.50
2160	1.50	1.51	1.51
2165	1.51	1.52	1.52
2170	1.51	1.53	1.53
2175	1.54	1.54	1.54
2180	1.53	1.55	1.56
2185	1.54	1.56	1.57
2190	1.56	1.58	1.59
2195	1.58	1.59	1.60
2200	1.59	1.61	1.62
2205	1.61	1.63	1.64
2210	1.62	1.64	1.66
2215	1.63	1.66	1.68
2220	1.67	1.69	1.70
2225	1.68	1.71	1.72
2230	1.70	1.73	1.75
2235	1.74	1.76	1.77
2240	1.75	1.78	1.80
2245	1.78	1.81	1.83
2250	1.81	1.84	1.86


## Typical Performance Curves



## Typical Performance Curves



### Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

Tolerance on hole size and interaxes dimensions to be  $\pm .005$ .

#### Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A