



LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-98-S+

50Ω 75 to 131 MHz SMA-Male to SMA-Female

KEY FEATURES

- Good Insertion Loss, 3dB Max.
- Stop Band Return Loss, 12dB Min.
- Stop Band Rejection, 30dB Typ.

APPLICATIONS

- FM Communication
- Aircraft Communication


PRODUCT OVERVIEW

ZX75BP-98-S+ is a 50Ω bandpass filter in a connectorized package covering 75 to 131MHz. This offers good matching within the passband and high rejection in stopband.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	Fc	—	103	—	MHz
	Insertion Loss	F1-F2	75 - 131	—	3	dB
	Return Loss	F1-F2	75 - 131	11.8	—	dB
Stop Band, Lower	Rejection	DC-F3	DC - 45	35	—	dB
		F3-F4	45 - 55	20	—	dB
Stop Band, Upper	Rejection	F5-F6	170 - 210	20	—	dB
		F6-F7	210 - 2000	35	—	dB
		F7-F8	2000 - 3500	—	30	—


1. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

ABSOLUTE MAXIMUM RATINGS²

Parameter	Ratings
Operating Temperature	-40°C to + 85°C
Storage Temperature	-55°C to + 100°C
Input Power ³	0.5W at 25°C

2. Permanent damage may occur if any of these limits are exceeded.
 3. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE AT +25°C





LUMPED LC COAXIAL





Bandpass Filter

ZX75BP-98-S+

Mini-Circuits

50Ω 75 to 131 MHz SMA-Male to SMA-Female

TYPICAL PERFORMANCE GRAPHS





LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-98-S+


Mini-Circuits

50Ω 75 to 131 MHz SMA-Male to SMA-Female

CONNECTOR DESCRIPTION

Function	Marking on Unit	Connector
RF1 ¹	1	SMA Male
RF2 ¹	2	SMA Female

CASE STYLE DRAWING



Weight: 24.4 gram

Dimensions are in inches (mm). Tolerances: 2PI. ± .03; 3PI. ± .015

Tolerance on hole size and interaxes dimensions to be ± .005.

PRODUCT MARKING*: ZX75BP-98-S+

*Marking may contain other features or characters for internal lot control.



LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-98-S+

Mini-Circuits

50Ω 75 to 131 MHz SMA-Male to SMA-Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	<p>Data</p> <p>Graphs</p> <p>S-Parameter (S2P Files) Data Set (.zip file)</p>
Case Style	KE1467
RoHS Status	Compliant
Environmental Ratings	ENV46

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial Band Pass Filter

ZX75BP-98-S+

Typical Performance Data


FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	113.61	96.47	107.18	0.00	0.00	0.00	0.00	0.00	0.00
12	94.05	117.09	107.96	0.00	0.01	0.01	0.00	0.00	0.01
14	96.75	109.90	95.52	0.01	0.01	0.01	0.00	0.01	0.01
16	104.53	97.40	107.24	0.01	0.01	0.01	0.01	0.01	0.01
20	92.51	95.24	90.22	0.01	0.02	0.02	0.01	0.01	0.01
22	86.36	85.39	89.28	0.02	0.02	0.02	0.02	0.02	0.02
25	80.42	80.59	80.16	0.02	0.03	0.03	0.02	0.02	0.03
30	70.11	70.15	69.39	0.03	0.04	0.05	0.03	0.04	0.05
35	61.03	60.69	60.90	0.06	0.07	0.07	0.05	0.06	0.07
40	52.68	52.47	52.32	0.09	0.11	0.12	0.09	0.10	0.11
45	44.57	44.38	44.18	0.15	0.17	0.19	0.14	0.16	0.18
50	36.45	36.20	35.98	0.25	0.29	0.31	0.24	0.28	0.31
55	27.93	27.66	27.42	0.44	0.51	0.56	0.43	0.50	0.56
60	18.69	18.44	18.20	0.97	1.12	1.23	0.95	1.10	1.23
65	8.99	8.92	8.84	3.30	3.73	4.09	3.29	3.73	4.11
70	3.21	3.46	3.65	16.07	16.61	16.97	16.24	16.81	17.21
75	2.17	2.40	2.57	19.36	19.74	20.06	19.22	19.57	19.95
80	1.82	2.03	2.19	25.66	24.96	24.38	25.06	24.51	24.20
85	1.67	1.86	2.01	19.62	19.58	19.60	19.53	19.59	19.65
90	1.57	1.75	1.89	18.52	18.94	19.37	18.65	19.18	19.70
98	1.46	1.64	1.78	26.98	26.99	27.01	33.41	36.69	41.48
103	1.47	1.65	1.79	24.49	24.11	23.78	26.58	26.21	25.62
122	1.72	1.95	2.14	25.42	24.81	24.12	23.30	23.05	22.74
131	2.26	2.59	2.88	17.85	17.09	16.44	25.77	23.94	22.45
150	14.23	14.74	15.19	1.42	1.52	1.57	1.46	1.55	1.61
170	28.29	28.55	28.80	0.53	0.59	0.64	0.51	0.58	0.63
200	41.71	41.79	41.90	0.28	0.33	0.36	0.27	0.32	0.35
210	45.00	45.05	45.12	0.24	0.29	0.31	0.23	0.28	0.31
400	70.30	70.68	70.52	0.08	0.12	0.14	0.08	0.12	0.15
500	77.76	77.57	78.00	0.07	0.12	0.14	0.07	0.12	0.14
600	87.49	88.39	89.26	0.07	0.12	0.15	0.07	0.12	0.15
700	99.27	93.44	86.99	0.08	0.13	0.17	0.07	0.13	0.17
800	85.65	91.60	89.27	0.08	0.14	0.19	0.08	0.14	0.18
900	89.90	91.05	92.20	0.08	0.16	0.20	0.08	0.15	0.20
1000	95.46	106.60	95.61	0.09	0.17	0.23	0.09	0.17	0.22
1100	86.42	86.58	86.20	0.11	0.19	0.25	0.10	0.18	0.23
1200	77.67	76.49	76.45	0.12	0.21	0.27	0.11	0.20	0.25
1300	72.76	71.95	71.14	0.13	0.22	0.29	0.12	0.21	0.27
1400	68.50	68.00	67.54	0.15	0.24	0.31	0.13	0.22	0.28
1500	65.29	64.55	64.27	0.16	0.25	0.33	0.13	0.24	0.30
1600	62.47	61.98	61.59	0.17	0.27	0.34	0.15	0.25	0.32
1700	59.99	59.62	59.49	0.18	0.28	0.36	0.15	0.27	0.33
1800	57.94	57.50	57.45	0.20	0.30	0.37	0.17	0.28	0.35
1900	56.03	55.74	55.60	0.20	0.30	0.39	0.17	0.29	0.36
2000	54.32	54.04	53.84	0.21	0.32	0.40	0.18	0.30	0.37
2100	52.59	52.38	52.22	0.22	0.33	0.41	0.20	0.31	0.39
2200	51.03	50.84	50.72	0.23	0.34	0.42	0.20	0.32	0.39
2300	49.58	49.40	49.31	0.24	0.35	0.43	0.21	0.33	0.40
2400	48.15	47.98	47.92	0.25	0.36	0.44	0.22	0.34	0.41
2500	46.72	46.59	46.56	0.26	0.37	0.45	0.23	0.36	0.43
2600	45.94	45.73	45.66	0.26	0.38	0.46	0.23	0.35	0.43
2700	44.56	44.41	44.36	0.27	0.39	0.47	0.24	0.36	0.44
2800	43.32	43.22	43.17	0.29	0.40	0.48	0.26	0.38	0.45
2900	42.13	42.00	41.97	0.28	0.40	0.48	0.23	0.36	0.44
3000	40.95	40.82	40.77	0.29	0.40	0.49	0.24	0.37	0.44
3100	39.77	39.62	39.58	0.30	0.42	0.50	0.24	0.37	0.44
3200	38.61	38.46	38.39	0.31	0.43	0.52	0.24	0.37	0.45
3300	37.38	37.22	37.15	0.32	0.45	0.55	0.24	0.37	0.45
3400	36.13	35.97	35.87	0.35	0.49	0.60	0.24	0.38	0.46
3500	34.85	34.69	34.52	0.42	0.59	0.71	0.25	0.38	0.46

Typical Performance Data


FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
75	30.84	30.37	30.00
76	29.67	29.21	28.85
77	28.36	27.94	27.60
78	27.02	26.65	26.36
79	25.74	25.44	25.20
80	24.60	24.36	24.17
81	23.61	23.42	23.26
82	22.76	22.60	22.47
83	22.03	21.89	21.78
84	21.38	21.26	21.17
85	20.81	20.71	20.63
86	20.30	20.21	20.14
87	19.84	19.76	19.70
88	19.42	19.35	19.29
89	19.04	18.98	18.93
90	18.69	18.64	18.59
91	18.37	18.33	18.29
92	18.08	18.05	18.02
93	17.83	17.79	17.77
94	17.59	17.56	17.54
95	17.38	17.35	17.34
96	17.18	17.16	17.15
97	17.01	16.99	16.98
98	16.85	16.83	16.82
99	16.70	16.68	16.68
100	16.57	16.55	16.55
102	16.34	16.33	16.33
103	16.24	16.23	16.23
106	16.01	16.02	16.03
108	15.92	15.94	15.96
110	15.89	15.92	15.95
112	15.92	15.95	15.99
114	16.00	16.04	16.09
116	16.15	16.20	16.26
118	16.37	16.43	16.50
120	16.68	16.76	16.84
122	17.10	17.20	17.29
124	17.66	17.76	17.86
126	18.34	18.44	18.53
128	19.09	19.16	19.22
131	20.13	20.08	20.05

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm




INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A