

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

ZX75BP-B1280-S+

50Ω 1160 to 1400 MHz



Generic photo used for illustration purposes only
CASE STYLE: HY1238

Connectors SMA-MF Model ZX75BP-B1280-S+

Features

- Low insertion loss
- High selectivity
- High rejection > 60dB
- Connectorized package

Applications

- Aviation
- Research testing & Development
- Earth Exploration-satellite (Active) service
- Fixed wireless transmitters and receivers

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	-	-	1280	-	MHz	
	Insertion Loss	F1-F2	1160 - 1400	-	1.0	-	dB
	VSWR	F1-F2	1160 - 1400	-	1.5	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 800	60	68	-	dB
		F3-F4	800 - 955	40	47	-	dB
	VSWR	DC-F4	DC - 955	-	20	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	1570 - 1700	20	28	-	dB
		F6-F7	1700 - 1850	40	47	-	dB
		F7-F8	1850 - 2200	60	68	-	dB
	VSWR	F5-F8	1570 - 2220	-	20	-	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W max.

Permanent damage may occur if any of these limits are exceeded.


Functional Schematic



Typical Performance Data at 25°C





Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	117.93	17216.83	1160	5.30
10	104.10	48228.15	1170	5.02
100	99.38	3597.16	1180	4.79
800	102.21	75.16	1190	4.60
955	48.04	47.90	1200	4.45
1015	29.43	31.59	1210	4.33
1040	20.88	22.86	1220	4.23
1070	10.48	10.39	1230	4.16
1100	3.11	2.81	1240	4.09
1160	0.95	1.12	1250	4.03
1280	0.73	1.09	1260	3.97
1400	0.84	1.19	1270	3.92
1450	3.20	3.55	1280	3.88
1480	9.69	14.33	1290	3.85
1530	20.85	40.44	1300	3.83
1570	28.26	50.59	1320	3.83
1585	30.79	52.97	1340	3.90
1700	48.25	62.85	1360	4.01
1850	77.62	70.91	1380	4.17
2200	79.09	78.19	1400	4.54

Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
H	J	K	L	M	N	Wt.
.50	.35	.18	.21	2.05	.106	grams
12.70	8.89	4.57	5.28	52.07	2.69	35.0

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	100.30	117.93	98.42	0.01	0.00	0.00	0.00	0.00	0.00
5	97.75	97.41	100.02	0.01	0.00	0.00	0.01	0.00	0.00
10	99.75	104.10	94.67	0.00	0.00	0.00	0.01	0.00	0.00
50	96.72	99.95	100.71	0.00	0.00	0.00	0.01	0.00	0.00
100	98.55	99.38	100.30	0.01	0.00	0.01	0.01	0.00	0.01
150	102.21	99.55	107.27	0.01	0.01	0.02	0.01	0.01	0.01
200	113.47	103.06	116.54	0.00	0.02	0.03	0.02	0.01	0.01
250	102.08	121.93	107.30	0.00	0.03	0.04	0.01	0.02	0.03
300	100.19	117.60	121.01	0.01	0.04	0.05	0.01	0.02	0.03
350	105.52	96.12	102.06	0.02	0.05	0.07	0.00	0.03	0.04
400	105.07	98.75	97.29	0.03	0.07	0.09	0.00	0.04	0.04
450	103.04	105.07	105.90	0.04	0.09	0.11	0.01	0.05	0.06
500	96.94	96.82	102.47	0.06	0.11	0.13	0.02	0.07	0.07
550	95.64	92.33	102.91	0.07	0.12	0.15	0.03	0.08	0.08
600	95.82	98.50	96.51	0.09	0.14	0.18	0.05	0.10	0.11
650	106.21	93.85	99.25	0.11	0.16	0.20	0.06	0.11	0.12
700	100.08	110.35	92.41	0.13	0.19	0.23	0.08	0.14	0.15
750	95.37	103.11	105.49	0.15	0.21	0.25	0.10	0.16	0.17
800	92.84	102.21	95.14	0.17	0.23	0.28	0.13	0.19	0.20
850	77.16	77.28	76.33	0.19	0.26	0.31	0.17	0.23	0.25
900	63.61	63.49	62.94	0.22	0.30	0.36	0.21	0.28	0.30
950	49.79	49.48	49.20	0.26	0.36	0.43	0.28	0.37	0.40
955	48.32	48.04	47.71	0.27	0.36	0.44	0.29	0.38	0.42
1000	34.68	34.32	33.98	0.35	0.48	0.57	0.40	0.52	0.59
1015	29.80	29.43	29.09	0.40	0.55	0.66	0.45	0.60	0.68
1040	21.25	20.88	20.59	0.57	0.76	0.90	0.62	0.82	0.93
1070	10.72	10.48	10.37	1.36	1.68	1.94	1.38	1.71	1.94
1100	3.01	3.11	3.30	5.85	6.46	6.94	5.82	6.41	6.74
1126	1.07	1.28	1.50	16.43	17.19	18.01	16.30	17.00	17.28
1150	0.77	0.98	1.17	35.68	33.39	28.46	38.07	35.05	34.25
1160	0.74	0.95	1.13	25.54	24.84	23.19	25.61	24.91	24.77
1200	0.68	0.88	1.03	19.36	19.07	19.04	19.05	18.79	19.16
1280	0.54	0.73	0.86	27.99	27.08	26.54	27.25	26.71	25.58
1300	0.54	0.73	0.86	24.92	24.14	24.35	24.03	23.54	23.27
1350	0.52	0.73	0.86	33.51	33.28	29.35	32.22	32.41	29.95
1400	0.60	0.84	1.00	21.07	21.09	20.71	20.89	21.06	21.03
1450	2.55	3.20	3.66	5.34	5.02	4.75	5.37	5.05	4.76
1500	13.65	14.41	14.92	0.55	0.67	0.74	0.46	0.60	0.65
1530	20.20	20.85	21.26	0.31	0.43	0.50	0.22	0.34	0.39
1570	27.73	28.26	28.59	0.23	0.34	0.41	0.14	0.25	0.29
1585	30.30	30.79	31.10	0.22	0.33	0.40	0.13	0.23	0.27
1600	32.76	33.23	33.52	0.21	0.32	0.39	0.12	0.22	0.25
1650	40.50	40.88	41.10	0.20	0.29	0.36	0.12	0.21	0.23
1700	47.86	48.25	48.39	0.18	0.28	0.35	0.12	0.20	0.22
1750	55.53	55.84	55.92	0.17	0.27	0.33	0.12	0.21	0.22
1800	64.44	64.55	64.80	0.16	0.26	0.32	0.13	0.20	0.22
1850	76.92	77.62	77.56	0.15	0.25	0.32	0.13	0.21	0.22
1900	83.50	86.13	85.24	0.14	0.24	0.31	0.14	0.21	0.22
1950	78.92	79.99	79.51	0.12	0.23	0.30	0.14	0.21	0.23
2000	78.42	80.53	80.73	0.11	0.22	0.30	0.14	0.22	0.23
2020	80.07	81.50	82.44	0.11	0.22	0.29	0.15	0.22	0.23
2040	82.11	83.99	82.87	0.11	0.22	0.29	0.14	0.22	0.24
2060	81.11	82.02	83.63	0.10	0.22	0.29	0.15	0.23	0.24
2080	85.56	84.72	83.78	0.10	0.22	0.29	0.15	0.23	0.25
2100	83.42	83.89	84.80	0.10	0.21	0.29	0.15	0.23	0.25
2120	85.55	86.48	83.56	0.10	0.21	0.29	0.15	0.23	0.25
2140	81.92	81.36	84.76	0.10	0.21	0.29	0.16	0.24	0.26
2160	80.26	81.76	83.99	0.09	0.21	0.29	0.17	0.25	0.27
2180	81.32	81.32	81.30	0.10	0.22	0.30	0.17	0.26	0.28
2200	80.09	79.09	80.14	0.10	0.22	0.30	0.17	0.26	0.29

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(ns)		
	@-40°C	@+25°C	@+85°C
1160	5.35	5.30	5.26
1166	5.17	5.12	5.09
1172	5.01	4.97	4.94
1178	4.87	4.83	4.80
1184	4.74	4.71	4.69
1190	4.63	4.60	4.58
1196	4.54	4.51	4.49
1202	4.45	4.43	4.41
1208	4.38	4.35	4.34
1214	4.31	4.29	4.28
1220	4.25	4.23	4.22
1226	4.20	4.18	4.18
1232	4.16	4.14	4.14
1238	4.12	4.10	4.10
1244	4.08	4.06	4.06
1250	4.04	4.03	4.02
1254	4.02	4.00	4.00
1258	4.00	3.98	3.98
1262	3.97	3.96	3.96
1266	3.95	3.94	3.94
1270	3.93	3.92	3.92
1274	3.91	3.90	3.90
1278	3.90	3.89	3.88
1280	3.89	3.88	3.87
1286	3.87	3.86	3.85
1290	3.85	3.85	3.84
1294	3.84	3.83	3.83
1298	3.84	3.83	3.83
1302	3.83	3.82	3.82
1306	3.82	3.82	3.82
1310	3.82	3.82	3.82
1314	3.83	3.82	3.83
1318	3.83	3.83	3.83
1322	3.84	3.84	3.84
1326	3.85	3.85	3.85
1330	3.86	3.86	3.86
1334	3.87	3.87	3.88
1338	3.88	3.89	3.90
1342	3.91	3.91	3.92
1346	3.92	3.93	3.94
1350	3.94	3.95	3.96
1356	3.97	3.98	3.99
1362	4.01	4.02	4.03
1368	4.05	4.06	4.07
1374	4.10	4.11	4.12
1380	4.15	4.17	4.19
1386	4.23	4.25	4.27
1392	4.32	4.35	4.38
1394	4.36	4.39	4.42
1396	4.40	4.44	4.47
1400	4.49	4.54	4.58

Typical Performance Curves




Case Style

HY

Outline Dimensions

HY1238



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1238	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	2.05 (52.07)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
 Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A