

## Voltage Controlled Oscillator

ZX95-3800AR-S+

50Ω 1900 to 3700 MHz

### The Big Deal:

- Wide Band
- Low Phase Noise
- Robust design and construction
- Rigid unibody construction



*Generic photo used for illustration purposes only*

CASE STYLE: GB956

### Product Overview:

The ZX95-3800AR-S+ is a Voltage Controlled Oscillator, designed to operate from 1900 to 3700 MHz for point-to-point system applications. The ZX95-3800AR-S+ is built using Mini-Circuits proven unibody construction (size of 1.20" x .75" x .46") which integrates the RF connectors with the case body to shield against unwanted signals and noise.

### Key Features

Feature	Advantages
Wide Band: from 1900 to 3700 MHz	The model's wide bandwidth makes it suitable for a wide variety of applications, such as: CATV, military, test equipment etc...
Low Phase Noise: -88 dBc/Hz typ at 10 kHz offset	Low phase noise improves system EVM (Error Vector Magnitude).
High Power Output, +6 dBm typ.	Reduces amplification requirements and improves immunity to external noise sources.
Good Pulling, 2 MHz typ.	Improves immunity against changes in output load.

Coaxial

## Voltage Controlled Oscillator

### ZX95-3800AR-S+

Wide Band 1900 to 3700 MHz

#### Features

- low phase noise, -88 dBc/Hz typ. @ 10kHz offset
- high power output, +6 dBm typ.
- low pulling, 2 MHz typ.
- wide band
- protected by US patent 6,790,049

#### Applications

- wireless communications
- point-to-point systems
- r & d
- instrumentation



Generic photo used for illustration purposes only

CASE STYLE: GB956

Connectors Model

SMA ZX95-3800AR-S+

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)		HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER			
	Min.	Max.		Typ.	Typ.				VOLTAGE RANGE (V)	SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.	Typ.	Typ.	Max.			Typ.	Max.	Vcc	Current (mA)
					1	10	100	1000														
ZX95-3800AR-S+	1900	3700	+6	-61	-88	-110	-130	0.5	20	60	-150	50	10	-90	-22	-10	2	6	6	55		

#### Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	21V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).

#### Outline Drawing









#### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.08	1.00	.50	.35	.18	.106	grams
30.48	19.15	11.61	30.07	1.02	9.53	9.53	14.43	4.62	8.31	5.28	5.59	2.03	25.40	12.70	8.89	4.57	2.69	35.0

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			I <sub>cc</sub> (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 2800 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	214.35	1770.9	1722.4	1681.7	6.58	6.57	6.40	44.58	-16.1	-25.8	-35.5	1.03	1.09	-59.59	-84.5	-105.1	-124.9	1.0	-63.74
1.00	173.25	1964.8	1924.9	1889.5	6.40	6.35	5.85	44.93	-16.8	-25.5	-50.4	0.32	0.90	-59.69	-85.4	-106.4	-126.3	2.0	-71.82
2.00	153.28	2128.6	2092.6	2063.7	6.04	5.75	5.64	45.25	-17.9	-25.9	-68.7	0.68	0.74	-63.81	-87.3	-107.7	-127.6	3.5	-77.09
3.00	139.98	2276.7	2242.3	2216.1	5.91	5.53	5.25	45.47	-22.7	-23.8	-52.1	1.07	0.67	-64.23	-88.6	-108.8	-128.7	6.0	-82.63
4.00	144.47	2414.1	2381.0	2356.6	5.60	5.25	4.86	45.46	-24.0	-27.4	-54.5	1.98	0.36	-64.38	-88.3	-109.1	-129.0	8.5	-86.31
5.00	138.71	2558.4	2524.6	2499.0	6.49	5.40	4.84	45.55	-25.0	-38.6	-42.3	3.18	0.48	-64.51	-87.5	-108.5	-128.7	10.0	-87.49
6.00	132.90	2693.5	2661.5	2636.1	6.52	5.83	4.93	45.70	-24.7	-36.2	-44.9	2.95	0.24	-66.54	-88.0	-108.9	-129.2	20.8	-94.58
7.00	129.47	2824.7	2793.4	2768.9	6.60	5.89	5.17	45.77	-23.9	-36.6	-39.3	3.09	0.16	-63.87	-87.7	-109.0	-129.4	35.5	-99.44
8.00	126.13	2952.6	2922.6	2898.9	6.67	6.23	5.54	46.04	-22.4	-38.9	-40.0	3.64	0.22	-63.06	-87.8	-109.3	-129.7	60.7	-105.00
9.00	122.90	3077.6	3047.8	3025.5	6.93	6.52	6.10	46.50	-19.9	-41.4	-40.4	4.70	0.32	-61.04	-87.5	-109.6	-130.3	86.7	-107.74
10.00	114.85	3196.8	3168.0	3146.7	7.22	6.79	6.39	46.93	-19.2	-47.8	-42.4	6.46	0.45	-60.43	-85.8	-109.4	-130.5	100.0	-109.05
11.00	104.10	3307.1	3280.6	3260.9	7.37	6.90	6.57	47.25	-20.1	-46.8	-43.3	8.40	0.86	-58.60	-86.9	-109.7	-131.3	148.1	-112.88
12.00	91.57	3406.8	3382.8	3364.6	7.27	6.88	6.60	47.20	-21.8	-32.1	-42.3	9.99	1.54	-59.97	-86.5	-109.9	-131.7	177.0	-113.88
13.00	79.70	3496.0	3473.1	3456.8	7.25	6.88	6.48	46.90	-25.3	-35.6	-40.7	9.06	1.90	-59.90	-87.8	-111.3	-133.3	211.6	-115.99
14.00	69.71	3573.7	3551.4	3537.3	7.08	6.73	6.39	46.58	-30.1	-38.0	-42.1	7.39	1.53	-59.49	-88.0	-112.6	-134.4	302.4	-118.97
15.50	57.83	3668.7	3650.6	3638.4	7.01	6.54	6.14	46.35	-36.7	-38.1	-44.8	3.27	1.81	-59.85	-89.3	-113.9	-134.7	355.1	-120.24
17.00	47.01	3752.9	3731.6	3716.7	6.48	6.07	5.79	46.14	-31.1	-36.5	-51.2	1.88	3.91	-62.66	-88.9	-113.1	-134.4	498.5	-123.17
17.50	40.29	3777.1	3755.1	3738.5	6.34	5.97	5.64	46.07	-30.8	-35.9	-53.3	1.77	0.93	-64.56	-89.7	-114.4	-135.4	595.9	-124.64
19.00	32.78	3836.4	3809.8	3792.1	5.96	5.71	5.47	45.81	-28.7	-36.3	-63.1	1.64	3.80	-61.26	-88.7	-113.5	-134.8	982.3	-129.13
20.00	26.49	3867.4	3840.1	3820.8	5.72	5.59	5.33	45.66	-29.1	-34.7	-62.9	1.49	0.95	-60.48	-89.0	-113.9	-135.5	1000.0	-129.28

\*at 25°C unless mentioned otherwise



### Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Voltage Controlled Oscillator

# ZX95-3800AR+

## Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (kHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.00	214.3	1770.9	1722.4	1681.7	6.6	6.6	6.4	-16.1	-25.8	-35.5	1.0	1	-61
0.50	190.6	1875.1	1829.6	1789.4	6.7	6.6	6.0	-16.1	-25.0	-41.5	0.5	10	-88
1.00	173.3	1964.8	1924.9	1889.5	6.4	6.4	5.9	-16.8	-25.5	-50.4	0.3	100	-110
1.50	162.2	2049.2	2011.5	1980.3	6.2	6.1	5.8	-18.2	-26.6	-54.5	0.5	1000	-130
2.00	153.3	2128.6	2092.6	2063.7	6.0	5.8	5.6	-17.9	-25.9	-68.7	0.7		
2.50	146.1	2204.3	2169.3	2141.7	5.9	5.7	5.5	-21.2	-25.1	-59.2	0.9		
3.00	140.0	2276.7	2242.3	2216.1	5.9	5.5	5.3	-22.7	-23.8	-52.1	1.1		
3.50	137.3	2345.3	2312.3	2287.4	5.7	5.4	5.1	-24.2	-23.8	-51.0	1.2		
4.00	144.5	2414.1	2381.0	2356.6	5.6	5.3	4.9	-24.0	-27.4	-54.5	2.0		
4.50	142.7	2487.3	2453.2	2428.0	6.2	5.2	4.7	-26.1	-39.7	-47.2	3.1		
5.00	138.7	2558.4	2524.6	2499.0	6.5	5.4	4.8	-25.0	-38.6	-42.3	3.2		
5.50	135.2	2626.8	2593.9	2568.2	6.5	5.7	4.9	-24.9	-35.8	-40.7	3.1		
6.00	132.9	2693.5	2661.5	2636.1	6.5	5.8	4.9	-24.7	-36.2	-44.9	3.0		
6.50	130.8	2759.3	2728.0	2702.9	6.4	5.9	5.1	-24.3	-35.5	-41.5	3.0		
7.00	129.5	2824.7	2793.4	2768.9	6.6	5.9	5.2	-23.9	-36.6	-39.3	3.1		
7.50	128.9	2888.8	2858.1	2834.5	6.5	6.0	5.5	-22.5	-38.6	-41.5	3.3		
8.00	126.1	2952.6	2922.6	2898.9	6.7	6.2	5.5	-22.4	-38.9	-40.0	3.6		
8.50	124.3	3016.0	2985.7	2962.4	6.9	6.3	5.8	-21.0	-40.1	-37.8	4.1		
9.00	122.9	3077.6	3047.8	3025.5	6.9	6.5	6.1	-19.9	-41.4	-40.4	4.7		
9.50	117.5	3137.9	3109.3	3086.8	7.2	6.6	6.2	-19.9	-42.8	-39.1	5.4		
10.00	114.9	3196.8	3168.0	3146.7	7.2	6.8	6.4	-19.2	-47.8	-42.4	6.5		
10.50	110.3	3253.0	3225.5	3205.3	7.3	6.8	6.4	-20.0	-53.5	-44.0	7.3		
11.00	104.1	3307.1	3280.6	3260.9	7.4	6.9	6.6	-20.1	-46.8	-43.3	8.4		
11.50	100.3	3358.3	3332.7	3314.5	7.4	7.0	6.6	-20.9	-38.8	-46.6	9.0		
12.00	91.6	3406.8	3382.8	3364.6	7.3	6.9	6.6	-21.8	-32.1	-42.3	10.0		
12.50	89.1	3453.7	3428.6	3412.0	7.2	6.9	6.6	-23.9	-33.0	-42.9	9.7		
13.00	79.7	3496.0	3473.1	3456.8	7.3	6.9	6.5	-25.3	-35.6	-40.7	9.1		
13.50	76.8	3537.0	3513.0	3497.9	7.1	6.8	6.5	-28.2	-38.1	-41.7	8.8		
14.00	69.7	3573.7	3551.4	3537.3	7.1	6.7	6.4	-30.1	-38.0	-42.1	7.4		
14.5	66.3	3607.8	3586.3	3573.5	7.1	6.7	6.3	-32.7	-37.7	-44.8	5.9		
15.5	57.8	3668.7	3650.6	3638.4	7.0	6.5	6.1	-36.7	-38.1	-44.8	3.3		
16.0	53.9	3697.5	3679.5	3667.9	6.8	6.4	6.0	-35.4	-37.0	-46.5	2.5		
17.0	47.0	3752.9	3731.6	3716.7	6.5	6.1	5.8	-31.1	-36.5	-51.2	1.9		
17.5	40.3	3777.1	3755.1	3738.5	6.3	6.0	5.6	-30.8	-35.9	-53.3	1.8		
18.5	33.5	3819.1	3793.1	3776.2	6.0	5.8	5.5	-29.2	-35.0	-61.2	1.6		
19.0	32.8	3836.4	3809.8	3792.1	6.0	5.7	5.5	-28.7	-36.3	-63.1	1.6		
20.0	26.5	3867.4	3840.1	3820.8	5.7	5.6	5.3	-29.1	-34.7	-62.9	1.5		
20.5	25.1	3881.1	3853.4	3834.3	5.7	5.5	5.3	-28.7	-35.6	-61.7	1.5		
21.5	21.8	3904.5	3877.4	3857.2	5.6	5.3	5.2	-28.4	-36.2	-60.9	1.4		
22.0	21.8	3915.0	3888.3	3868.1	5.5	5.3	5.1	-28.8	-34.0	-55.9	1.4		

**Notes**






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCULStoreTerms.jsp](http://www.minicircuits.com/MCULStoreTerms.jsp)



# Voltage Controlled Oscillator

# ZX95-3800AR+

## Typical Performance Data



**Notes**


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)

# Case Style

# GB

## Outline Dimensions

## GB956



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GB956	1.20 (30.48)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.38 (9.53)	.38 (9.53)	.57 (14.43)	.18 (4.62)	.33 (8.31)	.21 (5.28)	.22 (5.59)	.08 (2.03)

CASE #.	P	Q	R	S	T	WT GRAMS
GB956	1.00 (25.4)	.50 (12.7)	.35 (8.89)	.18 (4.57)	.106 (2.69)	35

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$   
Tolerance on hole size and interaxes dimensions to be  $\pm .005$ .

### Note:

1. Case material: Brass
2. Case finish: Nickel plate

**Mini-Circuits®**

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I