


## Outline Dimensions

## TT3651



**Weight: .1 grams.**

**Dimensions are in inches (mm).**

**Tolerances: 2Pl.  $\pm$  .01 (.254); 3Pl.  $\pm$  .005 (.127)**

### Notes:

1. Open style, Base material: Printed wiring laminate.
2. Termination finish: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate  
All models, (+) suffix.
3. Orientation dot on top hat & orientation feature on substrate correspondence to pin #1
4. Top-Hat total thickness: .013 inches MAX.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS