


Outline Dimensions

VU3196



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
VU3196	8.486 (215.54)	7.969 (202.40)	7.027 (178.49)	4.660 (118.36)	4.528 (115.00)	1.110 (28.19)	0.310 (7.87)	0.280 (7.11)	.560 (14.24)	3.708 (94.18)	2.724 (69.18)	1.936 (49.18)

CASE #	N	P	Q	R	S	T	U	V	W	Y	WEIGHT (GRAMS)
VU3196	.952 (24.18)	2.151 (54.63)	2.330 (59.18)	.586 (14.89)	4.070 (103.38)	3.330 (84.58)	.534 (13.56)	1.924 (48.87)	2.212 (56.18)	.560 (14.24)	608

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01(0.254)$; 3Pl. $\pm .005(0.127)$

Notes:

1. Base plate: Aluminum 6061 T6; Shield: Tin plated steel
2. Finish: PCB: ENIG; Baseplate: Clear Chemical conversion coating, non-chrome or trivalent chrome based.
3. Recommended screws for mounting model with heat sink: Use M4 SHCS.
4. Remove shield lid to expose mounting holes as noted in the drawing.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS