

Cable SMA-Male to Right-Angle MCX-Male

086-12SMMCR+

Typical Performance Data (+25°C)

FREQ.	INSERTION LOSS	SMA-MALE RETURN LOSS	RIGHT-ANGLE MCX-MALE RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
10	0.05	48.77	47.21
200	0.13	40.59	39.39
400.0	0.18	54.49	42.01
600.0	0.21	37.31	38.49
800.0	0.24	41.01	35.27
1000.0	0.27	34.70	34.80
1200.0	0.30	35.29	33.91
1400.0	0.32	32.45	31.10
1600.0	0.34	33.47	33.27
1800.0	0.36	31.26	29.04
2000.0	0.38	30.15	29.87
2200.0	0.40	31.33	28.76
2400.0	0.42	27.93	26.76
2600.0	0.43	31.09	30.07
2800.0	0.45	27.86	25.63
3000.0	0.46	28.58	28.06
3200.0	0.48	27.83	25.70
3400.0	0.50	26.60	25.17
3600.0	0.51	27.83	26.42
3800.0	0.53	25.23	23.52
4000.0	0.54	26.86	26.02
4200.0	0.56	24.77	23.06
4400.0	0.57	25.70	24.94
4600.0	0.58	25.46	23.86
4800.0	0.60	24.34	22.93
5000.0	0.60	25.98	25.01
5200.0	0.62	23.81	22.21
5400.0	0.62	25.87	25.03
5600.0	0.64	23.93	22.39
5800.0	0.64	25.90	24.45
6000.0	0.65	24.91	23.82



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS