

**Adapter 2.4mm-Male to 2.92mm-Female****24MR-KF+***Typical Performance Data*

| FREQ. | INSERTION LOSS | 2.4mm-MALE<br>VSWR | 2.92mm-FEMALE<br>VSWR |
|-------|----------------|--------------------|-----------------------|
| (GHz) | (dB)           | (:1)               | (:1)                  |
| 0.01  | 0.01           | 1.01               | 1.01                  |
| 0.05  | 0.01           | 1.01               | 1.01                  |
| 0.10  | 0.01           | 1.01               | 1.01                  |
| 1.00  | 0.05           | 1.03               | 1.02                  |
| 2.00  | 0.06           | 1.05               | 1.02                  |
| 3.00  | 0.07           | 1.04               | 1.03                  |
| 4.00  | 0.08           | 1.02               | 1.02                  |
| 5.00  | 0.08           | 1.01               | 1.01                  |
| 6.00  | 0.09           | 1.01               | 1.03                  |
| 7.00  | 0.10           | 1.04               | 1.06                  |
| 8.00  | 0.11           | 1.09               | 1.10                  |
| 9.00  | 0.12           | 1.15               | 1.14                  |
| 10.00 | 0.13           | 1.18               | 1.16                  |
| 11.00 | 0.14           | 1.17               | 1.16                  |
| 12.00 | 0.14           | 1.13               | 1.14                  |
| 13.00 | 0.13           | 1.07               | 1.08                  |
| 14.00 | 0.13           | 1.07               | 1.01                  |
| 15.00 | 0.14           | 1.11               | 1.07                  |
| 16.00 | 0.14           | 1.12               | 1.16                  |
| 17.00 | 0.13           | 1.10               | 1.23                  |
| 18.00 | 0.13           | 1.09               | 1.27                  |
| 19.00 | 0.15           | 1.13               | 1.27                  |
| 20.00 | 0.18           | 1.17               | 1.22                  |
| 21.00 | 0.19           | 1.16               | 1.14                  |
| 22.00 | 0.17           | 1.09               | 1.07                  |
| 23.00 | 0.17           | 1.08               | 1.12                  |
| 24.00 | 0.20           | 1.18               | 1.20                  |
| 25.00 | 0.24           | 1.27               | 1.27                  |
| 26.00 | 0.25           | 1.29               | 1.29                  |
| 27.00 | 0.23           | 1.24               | 1.26                  |
| 28.00 | 0.20           | 1.14               | 1.18                  |
| 29.00 | 0.20           | 1.05               | 1.09                  |
| 30.00 | 0.21           | 1.03               | 1.02                  |
| 31.00 | 0.22           | 1.03               | 1.09                  |
| 32.00 | 0.22           | 1.03               | 1.14                  |
| 33.00 | 0.23           | 1.06               | 1.15                  |
| 34.00 | 0.25           | 1.11               | 1.12                  |
| 35.00 | 0.25           | 1.10               | 1.06                  |
| 36.00 | 0.25           | 1.09               | 1.07                  |
| 37.00 | 0.27           | 1.16               | 1.16                  |
| 38.00 | 0.32           | 1.26               | 1.24                  |
| 39.00 | 0.35           | 1.27               | 1.28                  |
| 40.00 | 0.33           | 1.22               | 1.26                  |

