

Flexible Cable SMA-M to RA MCX-M

FL086-12SMMCR+

Typical Performance Data

FREQ.	INSERTION LOSS	SMA-MALE RETURN LOSS	RIGHT-ANGLE MCX-MALE RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
10	0.04	51.00	50.10
200	0.14	34.89	36.28
400.0	0.20	38.84	39.21
600.0	0.24	40.80	43.17
800.0	0.28	36.32	35.27
1000.0	0.31	39.91	42.49
1200.0	0.34	35.10	34.14
1400.0	0.36	35.48	34.59
1600.0	0.39	30.81	32.41
1800.0	0.41	30.55	29.17
2000.0	0.43	30.10	29.83
2200.0	0.45	27.74	26.41
2400.0	0.47	28.34	27.40
2600.0	0.49	25.85	25.60
2800.0	0.51	27.11	25.46
3000.0	0.53	24.89	24.62
3200.0	0.54	26.28	25.49
3400.0	0.57	23.56	23.67
3600.0	0.58	26.84	25.08
3800.0	0.59	24.47	24.16
4000.0	0.61	25.28	24.32
4200.0	0.62	26.46	26.06
4400.0	0.63	23.77	24.68
4600.0	0.64	29.21	27.35
4800.0	0.66	25.08	25.16
5000.0	0.66	28.81	28.59
5200.0	0.68	27.60	26.49
5400.0	0.68	28.95	29.54
5600.0	0.70	31.31	28.89
5800.0	0.71	30.20	28.54
6000.0	0.71	34.76	34.42



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS