

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10	0.06	41.22	41.44
20	0.06	38.24	38.37
30	0.08	37.01	37.02
40	0.10	36.99	36.70
50	0.10	37.64	37.55
60	0.12	39.32	39.06
70	0.13	42.43	42.26
80	0.14	46.58	44.85
90	0.15	44.81	42.55
100	0.16	41.47	39.54
200	0.23	49.66	48.74
300	0.27	41.27	40.41
400	0.31	43.47	43.47
500	0.35	38.88	41.08
600	0.38	40.78	45.18
700	0.42	44.36	43.12
800	0.44	48.70	56.02
900	0.47	47.28	46.03
1000	0.50	36.26	35.99
1100	0.53	34.96	34.94
1200	0.55	31.52	32.22
1300	0.58	32.30	33.33
1400	0.60	36.75	38.75
1500	0.62	45.98	42.96
1600	0.63	35.50	36.38
1700	0.66	32.64	34.27
1800	0.68	32.38	33.76
1900	0.70	31.65	31.59
2000	0.72	30.30	29.50
2100	0.73	31.95	30.49
2200	0.74	35.16	33.77
2300	0.76	50.10	31.81
2400	0.77	32.84	28.83
2500	0.80	28.96	27.02
2600	0.82	27.57	27.26
2700	0.85	29.24	30.38
2800	0.84	31.07	31.96
2900	0.84	34.04	28.77
3000	0.84	30.02	26.89