

Directional Coupler

DBTC-20-4-75L+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
5.0	0.44	20.42	20.24	26.11	28.25	23.98
6.0	0.44	20.40	20.33	26.58	28.87	24.43
7.0	0.43	20.39	20.42	26.91	29.38	24.75
8.0	0.43	20.39	20.46	27.15	29.76	24.97
9.0	0.43	20.38	20.51	27.33	30.04	25.13
10.0	0.43	20.38	20.56	27.46	30.29	25.25
20.0	0.43	20.38	20.59	27.88	31.06	25.45
30.0	0.44	20.39	20.53	27.87	31.02	25.13
40.0	0.45	20.40	20.54	27.76	30.84	24.70
50.0	0.46	20.42	20.53	27.64	30.64	24.22
60.0	0.47	20.43	20.55	27.42	30.32	23.71
70.0	0.48	20.44	20.55	27.21	29.96	23.19
80.0	0.48	20.45	20.55	26.95	29.59	22.66
90.0	0.49	20.46	20.57	26.68	29.13	22.11
100.0	0.50	20.46	20.53	26.35	28.66	21.57
200.0	0.59	20.52	20.46	22.18	23.83	17.06
300.0	0.68	20.49	20.72	19.56	20.35	14.02
400.0	0.73	20.50	19.56	17.67	18.14	12.05
500.0	0.80	20.41	18.87	15.49	16.59	10.50
550.0	0.82	20.37	16.66	15.04	15.77	9.94
600.0	0.84	20.43	15.53	14.67	15.25	9.44
625.0	0.84	20.43	15.34	14.79	15.32	9.23
650.0	0.83	20.46	15.00	14.91	15.32	9.04
675.0	0.82	20.48	14.67	14.89	15.16	8.86
700.0	0.83	20.50	14.16	14.72	14.97	8.63
750.0	0.85	20.50	13.95	14.28	14.72	8.14
800.0	0.86	20.52	13.50	14.24	14.46	7.88
825.0	0.86	20.54	13.11	14.31	14.28	7.74
850.0	0.87	20.56	12.88	14.32	14.18	7.57
860.0	0.88	20.56	12.83	14.31	14.16	7.51
870.0	0.88	20.56	12.75	14.29	14.15	7.45
880.0	0.88	20.57	12.65	14.28	14.12	7.39
890.0	0.88	20.59	12.55	14.28	14.07	7.34
900.0	0.88	20.61	12.45	14.28	13.99	7.29
1000.0	0.92	20.81	11.42	13.78	13.57	6.83
1050.0	0.93	20.92	10.89	14.07	13.44	6.61
1100.0	0.96	21.04	10.64	14.20	13.38	6.37
1150.0	1.02	21.22	10.21	13.82	13.18	6.33
1200.0	1.05	21.41	9.67	13.80	12.74	6.09
1250.0	1.11	21.63	9.29	13.44	12.33	6.01



ISO 9001 ISO 14001 AS 9100 CERTIFIED

For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

RF/MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MC3.0308/terms.jsp.

REV. OR
DBTC-20-4-75L+

060718

Page 1 of 1