




Signal Generator

SSG-5N9G-RC


Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.




Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.




Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.



Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.



Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.

