







Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 0°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 25°C.






Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.



Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.



Typical Performance Graphs

Test Conditions: @ Temperature = 50°C.

