


# Solid State USB / I<sup>2</sup>C RF SP4T Switch Typical Performance Curves


## U2C-1SP4T-63H

TEST CONDITIONS: @Temperature = 0°C, Pin=8dBm


Insertion Loss




Isolation




VSWR (COM)



VSWR, Internally Terminated Ports



VSWR, Active Ports



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




# Solid State USB / I<sup>2</sup>C RF SP4T Switch Typical Performance Curves


## U2C-1SP4T-63H

TEST CONDITIONS: @Temperature = +25°C, Pin=8dBm


Insertion Loss




Isolation




VSWR (COM)



VSWR, Internally Terminated Ports



VSWR, Active Ports



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Solid State


## USB / I<sup>2</sup>C RF SP4T Switch

### Typical Performance Curves


# U2C-1SP4T-63H

TEST CONDITIONS: @Temperature = +50°C, Pin=8dBm


**Insertion Loss**




**Isolation**




**VSWR (COM)**



**VSWR, Internally Terminated Ports**



**VSWR, Active Ports**



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

