

4 Way-0° Power Splitter/Combiner

WP4M+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
500	11.84	12.01	11.97	11.82	0.19	2.00	14.17	13.88	14.36	6.89	1.67	1.67	1.67	1.68
550	10.28	10.44	10.39	10.26	0.18	1.66	15.37	15.02	15.59	4.92	1.66	1.65	1.65	1.66
600	9.04	9.19	9.15	9.02	0.17	1.33	17.02	16.59	17.29	3.56	1.62	1.63	1.62	1.62
620	8.63	8.78	8.73	8.61	0.17	1.22	17.83	17.35	18.12	3.14	1.61	1.61	1.61	1.60
640	8.26	8.41	8.37	8.24	0.17	1.10	18.72	18.19	19.04	2.78	1.59	1.59	1.59	1.58
660	7.95	8.09	8.05	7.93	0.16	0.99	19.69	19.11	20.06	2.48	1.57	1.58	1.57	1.56
680	7.68	7.82	7.77	7.66	0.16	0.88	20.75	20.12	21.17	2.23	1.55	1.56	1.55	1.54
700	7.44	7.58	7.54	7.43	0.16	0.79	21.89	21.18	22.35	2.01	1.53	1.54	1.53	1.52
720	7.25	7.39	7.34	7.23	0.16	0.68	23.06	22.29	23.56	1.82	1.51	1.52	1.51	1.50
740	7.09	7.22	7.17	7.07	0.15	0.58	24.15	23.35	24.72	1.66	1.49	1.49	1.49	1.48
760	6.96	7.09	7.04	6.93	0.15	0.50	25.06	24.26	25.69	1.53	1.47	1.48	1.47	1.46
780	6.85	6.98	6.93	6.83	0.15	0.39	25.70	24.95	26.30	1.42	1.45	1.46	1.45	1.45
800	6.77	6.89	6.84	6.74	0.15	0.32	25.90	25.30	26.41	1.33	1.44	1.45	1.43	1.43
820	6.70	6.82	6.78	6.69	0.14	0.23	25.67	25.22	26.08	1.26	1.42	1.43	1.42	1.42
840	6.66	6.78	6.73	6.64	0.14	0.14	25.09	24.78	25.44	1.22	1.41	1.41	1.41	1.41
860	6.63	6.74	6.70	6.61	0.13	0.12	24.38	24.17	24.67	1.22	1.40	1.40	1.39	1.40
880	6.61	6.72	6.68	6.59	0.13	0.21	23.65	23.49	23.88	1.23	1.39	1.39	1.38	1.39
900	6.60	6.72	6.67	6.58	0.13	0.28	22.95	22.82	23.11	1.27	1.38	1.39	1.38	1.38
920	6.60	6.71	6.67	6.59	0.13	0.36	22.26	22.14	22.39	1.31	1.38	1.38	1.37	1.38
940	6.61	6.72	6.67	6.60	0.12	0.42	21.61	21.48	21.75	1.37	1.37	1.37	1.36	1.37
960	6.63	6.73	6.69	6.61	0.12	0.51	21.03	20.88	21.16	1.43	1.37	1.37	1.36	1.37
980	6.65	6.75	6.70	6.63	0.12	0.58	20.52	20.34	20.62	1.49	1.37	1.36	1.35	1.37
1000	6.67	6.77	6.72	6.65	0.12	0.66	20.07	19.88	20.15	1.54	1.37	1.36	1.35	1.36
1020	6.70	6.79	6.74	6.68	0.11	0.72	19.66	19.44	19.72	1.60	1.37	1.36	1.35	1.37
1040	6.73	6.82	6.76	6.71	0.11	0.79	19.26	19.01	19.33	1.66	1.37	1.36	1.35	1.37
1060	6.77	6.85	6.80	6.74	0.10	0.87	18.89	18.61	18.97	1.73	1.37	1.36	1.35	1.37
1080	6.80	6.88	6.83	6.78	0.10	0.97	18.56	18.27	18.65	1.79	1.38	1.36	1.35	1.37
1100	6.83	6.91	6.86	6.81	0.10	1.02	18.29	17.96	18.35	1.84	1.38	1.36	1.35	1.37
1125	6.87	6.94	6.89	6.85	0.10	1.09	17.99	17.62	18.01	1.90	1.38	1.37	1.35	1.38
1150	6.91	6.98	6.93	6.89	0.09	1.16	17.69	17.28	17.71	1.97	1.39	1.38	1.36	1.38
1175	6.96	7.02	6.97	6.94	0.08	1.24	17.40	16.97	17.44	2.04	1.40	1.38	1.36	1.39
1200	7.01	7.06	7.01	6.98	0.08	1.37	17.16	16.68	17.18	2.11	1.40	1.38	1.37	1.39
1250	7.08	7.14	7.08	7.06	0.08	1.50	16.77	16.21	16.75	2.22	1.42	1.40	1.38	1.41
1300	7.18	7.21	7.16	7.15	0.06	1.68	16.40	15.75	16.38	2.35	1.44	1.41	1.40	1.42
1350	7.25	7.28	7.22	7.22	0.06	1.88	16.13	15.40	16.06	2.44	1.46	1.43	1.41	1.44
1400	7.34	7.35	7.29	7.31	0.06	1.99	15.85	15.03	15.79	2.55	1.47	1.45	1.43	1.46
1450	7.41	7.41	7.35	7.37	0.06	2.21	15.65	14.74	15.55	2.63	1.49	1.46	1.45	1.47
1500	7.47	7.47	7.41	7.44	0.07	2.32	15.45	14.45	15.35	2.72	1.51	1.49	1.46	1.49
1550	7.54	7.52	7.47	7.51	0.08	2.52	15.28	14.17	15.15	2.81	1.53	1.50	1.48	1.51
1600	7.59	7.56	7.50	7.55	0.09	2.67	15.15	13.94	14.99	2.86	1.55	1.52	1.50	1.53
1650	7.67	7.61	7.56	7.63	0.10	2.81	14.99	13.68	14.83	2.95	1.57	1.53	1.52	1.54
1700	7.70	7.65	7.59	7.66	0.12	3.01	14.90	13.48	14.69	2.99	1.59	1.56	1.53	1.55
1750	7.77	7.69	7.64	7.73	0.13	3.09	14.76	13.24	14.57	3.07	1.61	1.57	1.55	1.58
1800	7.80	7.72	7.66	7.76	0.14	3.31	14.69	13.05	14.45	3.11	1.63	1.59	1.57	1.58
1850	7.85	7.75	7.70	7.81	0.15	3.39	14.58	12.83	14.35	3.16	1.64	1.61	1.59	1.61
1900	7.90	7.78	7.73	7.85	0.17	3.59	14.51	12.63	14.24	3.21	1.66	1.62	1.60	1.62
1950	7.93	7.80	7.75	7.88	0.18	3.71	14.44	12.44	14.15	3.24	1.68	1.64	1.62	1.63
2000	7.98	7.83	7.79	7.93	0.18	3.83	14.35	12.23	14.06	3.31	1.70	1.65	1.63	1.65
2100	8.05	7.88	7.84	8.00	0.20	4.08	14.21	11.85	13.91	3.38	1.72	1.68	1.66	1.68
2200	8.10	7.92	7.88	8.05	0.22	4.37	14.08	11.49	13.76	3.45	1.75	1.70	1.68	1.70
2300	8.15	7.95	7.90	8.10	0.25	4.67	13.97	11.15	13.63	3.50	1.77	1.73	1.70	1.72
2400	8.19	7.98	7.92	8.13	0.27	5.02	13.86	10.82	13.50	3.54	1.80	1.76	1.73	1.74
2500	8.25	8.02	7.95	8.18	0.30	5.40	13.73	10.49	13.35	3.59	1.82	1.78	1.75	1.76

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4M+

100627

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4M+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
500	11.85	12.01	11.97	11.84	0.17	2.42	13.99	13.72	14.21	7.53	1.67	1.65	1.66	1.67
550	10.26	10.42	10.38	10.26	0.16	2.06	15.16	14.82	15.43	5.30	1.65	1.64	1.65	1.66
600	9.00	9.14	9.11	8.98	0.16	1.75	16.79	16.37	17.09	3.77	1.62	1.62	1.62	1.62
620	8.57	8.72	8.68	8.56	0.16	1.65	17.59	17.13	17.92	3.31	1.60	1.60	1.61	1.60
640	8.21	8.35	8.31	8.19	0.16	1.55	18.49	17.96	18.83	2.92	1.59	1.59	1.59	1.58
660	7.88	8.03	7.98	7.86	0.16	1.45	19.45	18.88	19.84	2.60	1.57	1.58	1.57	1.56
680	7.61	7.75	7.70	7.58	0.17	1.36	20.52	19.89	20.95	2.33	1.55	1.56	1.55	1.54
700	7.37	7.51	7.46	7.34	0.17	1.27	21.68	20.98	22.13	2.09	1.53	1.54	1.53	1.52
720	7.17	7.30	7.25	7.14	0.16	1.21	22.88	22.11	23.36	1.89	1.52	1.52	1.51	1.50
740	7.00	7.13	7.09	6.97	0.16	1.16	24.04	23.23	24.56	1.72	1.50	1.50	1.49	1.48
760	6.87	6.99	6.95	6.84	0.15	1.08	25.04	24.21	25.59	1.58	1.48	1.49	1.47	1.46
780	6.76	6.88	6.84	6.73	0.15	1.01	25.76	25.00	26.27	1.46	1.46	1.47	1.45	1.45
800	6.67	6.79	6.75	6.65	0.15	0.95	26.05	25.42	26.48	1.36	1.44	1.45	1.43	1.43
820	6.61	6.72	6.68	6.58	0.14	0.85	25.84	25.39	26.19	1.28	1.43	1.43	1.41	1.42
840	6.56	6.68	6.63	6.54	0.14	0.78	25.25	24.95	25.59	1.24	1.41	1.42	1.40	1.41
860	6.53	6.64	6.60	6.51	0.14	0.72	24.50	24.32	24.80	1.22	1.40	1.40	1.39	1.39
880	6.51	6.62	6.58	6.49	0.13	0.66	23.75	23.63	23.98	1.23	1.39	1.39	1.38	1.39
900	6.50	6.61	6.56	6.48	0.13	0.59	23.03	22.92	23.20	1.26	1.38	1.39	1.37	1.38
920	6.50	6.61	6.57	6.48	0.13	0.54	22.32	22.23	22.47	1.30	1.37	1.38	1.36	1.37
940	6.51	6.61	6.57	6.49	0.12	0.49	21.65	21.55	21.80	1.36	1.37	1.37	1.35	1.37
960	6.53	6.63	6.59	6.51	0.12	0.57	21.06	20.94	21.19	1.42	1.36	1.36	1.35	1.36
980	6.55	6.64	6.60	6.53	0.11	0.64	20.53	20.38	20.64	1.48	1.36	1.36	1.34	1.36
1000	6.57	6.66	6.62	6.55	0.11	0.71	20.07	19.90	20.15	1.53	1.36	1.35	1.34	1.36
1020	6.60	6.69	6.64	6.58	0.11	0.78	19.63	19.45	19.71	1.59	1.36	1.35	1.34	1.36
1040	6.63	6.71	6.67	6.61	0.10	0.86	19.22	19.01	19.31	1.65	1.36	1.35	1.34	1.36
1060	6.66	6.74	6.70	6.65	0.10	0.94	18.84	18.60	18.95	1.72	1.36	1.35	1.34	1.36
1080	6.70	6.78	6.73	6.68	0.10	1.03	18.51	18.24	18.62	1.78	1.36	1.35	1.34	1.36
1100	6.73	6.81	6.76	6.71	0.10	1.09	18.23	17.94	18.31	1.83	1.37	1.35	1.34	1.36
1125	6.77	6.84	6.79	6.75	0.10	1.18	17.93	17.59	17.98	1.90	1.37	1.36	1.34	1.36
1150	6.81	6.88	6.83	6.79	0.09	1.24	17.62	17.25	17.67	1.96	1.37	1.36	1.34	1.37
1175	6.86	6.92	6.87	6.84	0.08	1.33	17.33	16.93	17.39	2.04	1.38	1.37	1.35	1.37
1200	6.90	6.96	6.91	6.88	0.08	1.45	17.09	16.65	17.13	2.11	1.39	1.37	1.35	1.38
1250	6.98	7.03	6.98	6.96	0.07	1.58	16.69	16.17	16.69	2.22	1.40	1.39	1.36	1.39
1300	7.07	7.11	7.07	7.06	0.05	1.76	16.30	15.70	16.32	2.35	1.42	1.39	1.38	1.40
1350	7.14	7.17	7.12	7.12	0.05	1.94	16.02	15.33	16.00	2.44	1.43	1.41	1.39	1.42
1400	7.23	7.25	7.20	7.21	0.05	2.06	15.73	14.95	15.72	2.56	1.45	1.43	1.41	1.44
1450	7.30	7.31	7.26	7.27	0.05	2.27	15.52	14.66	15.47	2.64	1.47	1.45	1.43	1.46
1500	7.37	7.37	7.32	7.34	0.06	2.37	15.31	14.35	15.27	2.74	1.49	1.47	1.45	1.49
1550	7.44	7.42	7.38	7.41	0.07	2.58	15.15	14.09	15.07	2.83	1.52	1.49	1.47	1.50
1600	7.49	7.47	7.42	7.46	0.08	2.71	15.02	13.86	14.91	2.89	1.54	1.51	1.49	1.52
1650	7.57	7.52	7.47	7.54	0.09	2.85	14.86	13.60	14.74	2.98	1.56	1.53	1.51	1.53
1700	7.60	7.55	7.50	7.57	0.10	3.05	14.77	13.40	14.60	3.02	1.58	1.55	1.53	1.54
1750	7.67	7.59	7.56	7.64	0.12	3.12	14.64	13.16	14.47	3.12	1.60	1.56	1.54	1.56
1800	7.71	7.62	7.58	7.67	0.13	3.34	14.56	12.96	14.35	3.16	1.62	1.58	1.56	1.57
1850	7.76	7.65	7.62	7.72	0.14	3.43	14.45	12.75	14.26	3.22	1.64	1.60	1.58	1.59
1900	7.80	7.67	7.65	7.75	0.15	3.65	14.38	12.56	14.15	3.26	1.66	1.61	1.60	1.60
1950	7.82	7.69	7.66	7.79	0.16	3.79	14.31	12.36	14.06	3.30	1.67	1.63	1.61	1.62
2000	7.86	7.71	7.70	7.83	0.16	3.94	14.22	12.16	13.97	3.35	1.69	1.63	1.63	1.64
2100	7.94	7.77	7.76	7.91	0.18	4.18	14.07	11.77	13.81	3.46	1.71	1.66	1.66	1.67
2200	8.00	7.81	7.79	7.96	0.21	4.49	13.95	11.40	13.68	3.53	1.75	1.70	1.69	1.71
2300	8.04	7.83	7.80	7.99	0.24	4.79	13.86	11.07	13.56	3.58	1.78	1.74	1.71	1.75
2400	8.08	7.86	7.81	8.03	0.27	5.11	13.77	10.75	13.43	3.62	1.81	1.77	1.74	1.77
2500	8.12	7.89	7.83	8.07	0.29	5.49	13.65	10.42	13.29	3.68	1.84	1.80	1.76	1.78

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4M+

100627

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4M+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
500	11.84	12.01	11.96	11.82	0.19	2.45	14.32	14.04	14.52	6.46	1.68	1.68	1.69	1.70
550	10.29	10.45	10.41	10.27	0.18	2.10	15.56	15.20	15.77	4.64	1.67	1.67	1.67	1.67
600	9.07	9.23	9.18	9.05	0.17	1.84	17.24	16.80	17.49	3.38	1.64	1.64	1.64	1.63
620	8.67	8.82	8.77	8.65	0.17	1.75	18.06	17.57	18.33	3.00	1.62	1.63	1.62	1.61
640	8.32	8.47	8.42	8.29	0.18	1.66	18.94	18.41	19.25	2.67	1.60	1.61	1.60	1.59
660	8.01	8.16	8.11	7.98	0.17	1.56	19.90	19.32	20.27	2.39	1.58	1.59	1.58	1.58
680	7.75	7.89	7.84	7.72	0.17	1.51	20.95	20.30	21.39	2.16	1.56	1.57	1.56	1.56
700	7.52	7.66	7.61	7.49	0.17	1.43	22.05	21.34	22.55	1.95	1.54	1.55	1.54	1.54
720	7.32	7.46	7.41	7.30	0.16	1.35	23.17	22.41	23.73	1.77	1.52	1.53	1.52	1.52
740	7.17	7.30	7.25	7.14	0.16	1.30	24.19	23.41	24.84	1.62	1.50	1.51	1.50	1.50
760	7.04	7.17	7.12	7.01	0.15	1.22	25.02	24.24	25.73	1.50	1.48	1.49	1.48	1.48
780	6.93	7.06	7.01	6.91	0.15	1.16	25.56	24.85	26.24	1.40	1.46	1.47	1.46	1.46
800	6.85	6.97	6.92	6.82	0.15	1.10	25.73	25.13	26.29	1.32	1.45	1.45	1.44	1.45
820	6.79	6.91	6.86	6.77	0.14	1.02	25.47	25.02	25.93	1.26	1.43	1.44	1.43	1.44
840	6.74	6.86	6.81	6.72	0.14	0.99	24.90	24.59	25.28	1.23	1.42	1.42	1.41	1.42
860	6.71	6.83	6.78	6.69	0.13	1.04	24.20	23.98	24.53	1.23	1.41	1.41	1.40	1.41
880	6.70	6.81	6.76	6.67	0.13	1.05	23.50	23.34	23.75	1.25	1.40	1.40	1.39	1.40
900	6.69	6.80	6.75	6.66	0.13	1.06	22.84	22.69	23.02	1.29	1.39	1.40	1.39	1.39
920	6.69	6.80	6.75	6.67	0.13	1.09	22.20	22.05	22.33	1.33	1.39	1.39	1.38	1.39
940	6.70	6.80	6.75	6.68	0.12	1.13	21.59	21.43	21.70	1.39	1.38	1.38	1.37	1.39
960	6.71	6.81	6.77	6.70	0.11	1.21	21.03	20.85	21.12	1.45	1.38	1.38	1.37	1.38
980	6.74	6.83	6.78	6.71	0.11	1.28	20.54	20.34	20.60	1.51	1.38	1.37	1.37	1.38
1000	6.75	6.85	6.80	6.73	0.11	1.37	20.11	19.89	20.14	1.56	1.38	1.37	1.36	1.38
1020	6.78	6.87	6.82	6.76	0.11	1.45	19.71	19.47	19.73	1.62	1.38	1.38	1.36	1.38
1040	6.81	6.89	6.84	6.79	0.10	1.53	19.32	19.05	19.34	1.68	1.38	1.37	1.36	1.38
1060	6.84	6.92	6.87	6.82	0.10	1.65	18.96	18.67	18.99	1.74	1.38	1.37	1.36	1.38
1080	6.88	6.95	6.90	6.86	0.09	1.72	18.64	18.33	18.68	1.80	1.39	1.37	1.36	1.39
1100	6.91	6.98	6.93	6.89	0.09	1.81	18.37	18.03	18.39	1.86	1.39	1.37	1.36	1.39
1125	6.94	7.01	6.96	6.92	0.09	1.90	18.07	17.69	18.06	1.92	1.39	1.38	1.37	1.39
1150	6.98	7.05	7.00	6.96	0.09	2.00	17.78	17.36	17.76	1.98	1.39	1.38	1.37	1.40
1175	7.03	7.09	7.04	7.01	0.08	2.08	17.49	17.04	17.49	2.05	1.40	1.39	1.37	1.41
1200	7.08	7.13	7.08	7.06	0.07	2.19	17.26	16.76	17.25	2.12	1.41	1.39	1.38	1.41
1250	7.15	7.20	7.15	7.13	0.07	2.38	16.87	16.30	16.82	2.23	1.42	1.41	1.39	1.42
1300	7.24	7.27	7.22	7.22	0.06	2.56	16.50	15.84	16.45	2.35	1.44	1.41	1.40	1.44
1350	7.31	7.34	7.28	7.28	0.06	2.78	16.23	15.48	16.14	2.44	1.46	1.43	1.42	1.45
1400	7.40	7.41	7.35	7.37	0.05	2.94	15.95	15.11	15.87	2.55	1.47	1.44	1.43	1.47
1450	7.47	7.46	7.41	7.43	0.06	3.14	15.74	14.81	15.62	2.62	1.49	1.46	1.45	1.48
1500	7.53	7.52	7.46	7.50	0.07	3.30	15.55	14.52	15.43	2.70	1.51	1.48	1.46	1.50
1550	7.60	7.57	7.52	7.56	0.08	3.50	15.37	14.24	15.22	2.79	1.53	1.49	1.48	1.51
1600	7.65	7.61	7.55	7.61	0.10	3.68	15.23	14.00	15.06	2.84	1.54	1.51	1.49	1.53
1650	7.73	7.67	7.62	7.68	0.11	3.85	15.06	13.73	14.91	2.93	1.56	1.52	1.51	1.54
1700	7.77	7.70	7.64	7.72	0.13	4.06	14.96	13.52	14.76	2.96	1.58	1.54	1.53	1.56
1750	7.83	7.74	7.69	7.78	0.14	4.21	14.83	13.27	14.64	3.04	1.60	1.56	1.54	1.58
1800	7.87	7.77	7.71	7.81	0.16	4.43	14.74	13.07	14.51	3.08	1.62	1.57	1.56	1.58
1850	7.92	7.81	7.75	7.86	0.17	4.61	14.64	12.86	14.41	3.13	1.63	1.59	1.57	1.60
1900	7.96	7.84	7.78	7.91	0.18	4.82	14.55	12.64	14.30	3.18	1.65	1.60	1.59	1.61
1950	8.00	7.86	7.80	7.93	0.20	5.04	14.47	12.45	14.21	3.20	1.67	1.63	1.60	1.63
2000	8.05	7.90	7.85	7.99	0.21	5.21	14.38	12.24	14.12	3.27	1.69	1.63	1.61	1.64
2100	8.13	7.96	7.90	8.06	0.22	5.58	14.23	11.85	13.96	3.35	1.72	1.66	1.64	1.67
2200	8.19	8.00	7.94	8.12	0.25	6.03	14.10	11.49	13.81	3.40	1.75	1.70	1.67	1.69
2300	8.23	8.04	7.96	8.16	0.27	6.45	14.00	11.16	13.68	3.44	1.77	1.73	1.69	1.71
2400	8.28	8.07	7.99	8.20	0.29	6.90	13.89	10.84	13.54	3.47	1.80	1.76	1.71	1.73
2500	8.33	8.11	8.02	8.25	0.31	7.35	13.75	10.53	13.39	3.52	1.82	1.78	1.74	1.75

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4M+

100627

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

