

Waveguide WR10 UG387/U to 1.0mm-F**WR10-10R+***Typical Performance Data (+25°C)*

FREQ.	INSERTION LOSS	1.0mm-FEMALE VSWR
(GHz)	(dB)	(:1)
75	-0.72	1.29
78	-0.73	1.11
81	-0.78	1.09
84	-0.63	1.16
87	-0.58	1.22
90	-0.55	1.11
94	-0.58	1.09
95	-0.60	1.11
95	-0.61	1.14
96	-0.61	1.13
96	-0.62	1.11
97	-0.61	1.11
98	-0.62	1.14
98	-0.64	1.19
99	-0.68	1.25
99	-0.72	1.31
100	-0.72	1.34
100	-0.78	1.34
101	-0.70	1.29
102	-0.65	1.21
103	-0.66	1.25
105	-0.73	1.30
106	-0.75	1.24
107	-0.73	1.15
108	-0.73	1.11
109	-0.80	1.08
110	-0.74	1.10



P.O. Box 350166, Brooklyn, New York 11235-0003 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS