

Waveguide WR12 UG387/U to 1.0mm-F

WR12-10R+

Typical Performance Data (+25 °C)

FREQ.	INSERTION LOSS	1.0mm-FEMALE VSWR
(GHz)	(dB)	(:1)
60	-0.67	1.25
61	-0.64	1.23
62	-0.61	1.20
63	-0.59	1.18
64	-0.58	1.16
65	-0.57	1.14
66	-0.57	1.13
67	-0.57	1.13
68	-0.57	1.14
69	-0.58	1.15
70	-0.58	1.19
71	-0.59	1.19
72	-0.59	1.20
73	-0.61	1.20
74	-0.60	1.23
75	-0.61	1.25
76	-0.61	1.22
77	-0.60	1.19
78	-0.61	1.20
79	-0.59	1.20
80	-0.59	1.17
81	-0.59	1.11
82	-0.58	1.07
83	-0.58	1.08
84	-0.59	1.08
85	-0.60	1.08
86	-0.61	1.13
87	-0.64	1.20
88	-0.64	1.20
89	-0.64	1.18
90	-0.64	1.16



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS