

Waveguide WR15 UG385/U to 1.85mm-F

WR15-185R+

Typical Performance Data (+25 °C)

FREQ.	INSERTION LOSS	1.0mm-FEMALE VSWR
(GHz)	(dB)	(:1)
50	-0.34	1.17
51	-0.33	1.16
51	-0.32	1.15
52	-0.30	1.14
52	-0.31	1.11
53	-0.33	1.12
53	-0.35	1.14
54	-0.36	1.11
54	-0.35	1.10
55	-0.38	1.12
55	-0.39	1.12
56	-0.41	1.08
56	-0.42	1.06
57	-0.42	1.06
57	-0.42	1.06
58	-0.42	1.06
58	-0.43	1.06
59	-0.44	1.06
59	-0.45	1.05
60	-0.44	1.06
60	-0.43	1.08
61	-0.44	1.12
61	-0.46	1.14
62	-0.45	1.14
62	-0.45	1.14
63	-0.44	1.15
63	-0.42	1.14
64	-0.40	1.11
64	-0.41	1.11
65	-0.41	1.13
65	-0.40	1.16
66	-0.41	1.16
66	-0.40	1.17
67	-0.41	1.16
67	-0.42	1.16
68	-0.41	1.12
68	-0.45	1.14
69	-0.40	1.14
69	-0.41	1.16
70	-0.43	1.17
70	-0.43	1.19



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
 WR15-185R+
 11/21/2024
 Page 1 of 1