

Attenuator/Switch

TFAS-1SM+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB) at 20mA Control Current	AMP. UNBAL. (dB) at ± 20mA Control Current	PHASE UNBAL. (deg.) at ± 20mA Control Current	ISOLATION at 0 mA Control Current (dB)		RETURN LOSS (dB) Input
				In-Out	In-Con	
2.0	1.67	0.01	179.9	78	54	18.1
7.0	1.16	0.00	180.0	68	43	15.4
10.0	1.16	0.00	180.0	66	40	27.6
21.9	1.16	0.00	180.0	58	33	31.0
39.8	1.19	0.00	180.1	53	28	31.9
59.7	1.23	0.00	180.1	50	25	32.1
61.7	1.23	0.00	180.1	50	25	32.1
81.6	1.24	0.00	180.2	47	22	32.2
99.5	1.27	0.00	180.2	46	21	32.3
121.4	1.31	0.01	180.3	44	19	32.4
141.3	1.32	0.01	180.4	42	18	32.4
181.1	1.37	0.01	180.6	39	16	32.2
200.0	1.40	0.01	180.6	39	15	32.0
220.9	1.39	0.01	180.8	38	15	31.6
240.8	1.39	0.01	180.9	36	14	30.3
280.6	1.52	0.05	181.1	35	13	26.6
300.5	1.52	0.04	181.1	35	14	24.8
340.3	1.56	0.03	181.4	33	13	21.4
360.2	1.64	0.06	181.6	32	13	19.8
400.0	1.78	0.09	181.7	31	14	17.1

CONTROL CURRENT (mA)	ATTENUATION (dB)			PHASE UNBALANCE REF AT 15 mA CONTROL (deg.)			INPUT VSWR (:1)		
	2 MHz	200 MHz	400 MHz	2 MHz	200 MHz	400 MHz	2 MHz	200 MHz	400 MHz
0.0000	72.7	39.0	30.6	27.2	-87.7	-95.3	7.7	7.2	4.4
0.0003	64.4	39.2	30.7	22.2	-86.0	-94.6	7.7	7.2	4.4
0.0005	56.5	39.0	30.8	28.6	-84.3	-93.7	7.6	7.2	4.4
0.0012	50.4	39.0	30.7	17.6	-80.5	-92.0	7.6	7.2	4.4
0.0019	47.8	39.0	30.7	14.1	-77.4	-90.3	7.5	7.2	4.4
0.0054	42.5	37.9	30.6	8.2	-56.2	-79.9	7.4	7.0	4.3
0.0100	38.4	35.8	30.1	7.6	-37.3	-67.6	7.2	6.9	4.3
0.0157	35.1	33.1	29.0	8.8	-25.3	-55.1	7.1	6.7	4.2
0.0284	30.6	28.7	26.3	8.8	-12.8	-37.6	6.7	6.3	4.0
0.0433	27.3	25.3	23.7	9.2	-7.2	-26.9	6.3	5.9	3.8
0.0722	23.2	21.2	20.0	9.3	-3.1	-17.7	5.6	5.3	3.5
0.1012	20.7	18.6	17.6	9.0	-1.4	-13.2	5.2	4.9	3.3
0.1898	16.1	14.1	13.3	8.2	0.4	-8.0	4.1	3.9	2.8
0.3008	13.1	11.2	10.6	7.4	0.9	-5.5	3.4	3.2	2.4
0.4259	10.9	9.2	8.8	6.7	1.1	-4.2	2.9	2.7	2.1
0.7017	8.3	6.9	6.6	5.4	1.1	-2.8	2.2	2.1	1.7
0.9968	6.8	5.6	5.4	4.4	0.9	-2.1	1.9	1.8	1.5
1.7486	4.8	3.9	4.0	3.0	0.7	-1.3	1.5	1.5	1.3
5.6920	2.5	2.1	2.3	0.9	0.2	-0.3	1.2	1.1	1.2
15.1258	1.8	1.5	1.8	0.0	0.0	0.1	1.3	1.1	1.3

REV. X1
TFAS-1SM+
061204
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

