



THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-023000	NEW RELEASE	09/16/24	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR TT1491-8 CASE STYLE




NOTES:

1. LINE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: $.030 \pm .002$ ";
COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS LINE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	09/10/24
TOLERANCES ON:	CHECKED	GF	09/10/24
2 PL DECIMALS \pm	APPROVED	IL	09/10/24
3 PL DECIMALS \pm .005			
ANGLES \pm			
FRACTIONS \pm			



Mini-Circuits[®]

13 Neptune Avenue
Brooklyn NY 11235

PL, TT1491-8, TB-RBDC918275X+

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-795	REV: OR
FILE: 98PL795	SCALE: 8:1	SHEET: 1 OF 1	