



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0°C to +65°C	----
Storage Temperature	-20°C to +85°C	----
Stabilization Bake	125°C, 24 hours (Non-operating)	----
Thermal Shock	-20°C to +85°C 30 min dwell at extreme temperatures, 1 min transfer 250 cycles	MIL-STD-202, Method 107
ESD Gun Contact	Contact: ±2.0 kV, ±4.0 kV, ±6.0 kV, ±8.0 kV. Non-operating Condition 10 positive & 10 negative charges at each location.	IEC 61000-4-2
ESD HBM Test	Tested up to ± 1000V	JS-001
FedEx Transit Test (Packaging)	Test performed on packaged unit. Pre-conditioning + Shock (20 drops, 30 inches) + Compression + Vibration (90 min random Vibration)	ISTA 6-FEDEX-A TEST