

Engineering Development Model

Band Pass Filter

Surface Mount

BFCN-EDR9964/11

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FV1206

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 6dB)	6090		6250	MHz
Center Frequency		6170		MHz
Stopband Low Band (Loss > 20 dB)	2600		4600	MHz
Low Band (Loss > 40 dB)	DC		2600	MHz
High Band (Loss > 10 dB)	12600		15000	MHz
High Band (Loss > 15 dB)	6900		12600	MHz
Passband VSWR		2.2		(:1)
Stopband VSWR		18		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	1.5W at 25°C

Functional Schematic

