



Mini-Circuits®

CERAMIC


High Pass Filter

HFCN-7150AT+

50Ω 7900 to 11000 MHz

FEATURES

- Small size
- 5 sections
- Temperature stable
- Excellent power handling, 6 W
- Hermetically sealed
- LTCC construction
- Low cost
- Protected by US Patent 7,760,485
- AEC-Q200 qualified component family



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Automotive

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Stop Band	Rejection Loss	5100	—	30	dB
		6150	20	—	
	Freq. Cut-Off	7150	—	3.0	dB
	VSWR	5100-6150	—	20	
Pass Band	Insertion Loss	7900-11000	—	2.0	dB
		8500-10500	—	1.5	
	VSWR	7250-11000	—	1.5	:1

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required.


2. Measured on Mini-Circuits Characterization Test Board TB-285 using HFCN-7150+.

ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-40°C to +105°C
Storage temperature	-40°C to +105°C
RF Power Input ³	6 W max. at +25°C

3. Passband rating, derate linearly to 3 W at +105°C ambient.
Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



REV. OR
NPO-005331
HFCN-7150AT+
MCL NY
250610





Mini-Circuits®

CERAMIC

High Pass Filter

HFCN-7150AT+


50Ω 7900 to 11000 MHz

PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4,5,6

PRODUCT MARKING: ZR


DEMO BOARD MCL P/N: TB-285
SUGGESTED PCB LAYOUT (PL-158)




- NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350 WITH DIELECTRIC THICKNESS: .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

	DENOTES PCB COPPER LAYOUT
	DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F
.126	.063	.035	.024	.022	.011
3.20	1.60	0.89	0.61	0.56	0.28
G	H	J	K		wt
.039	.024	.042	.123		grams
0.99	0.61	1.07	3.12		.020

TAPE & REEL INFORMATION: F75



Mini-Circuits

CERAMIC


High Pass Filter

HFCN-7150AT+

50Ω 7900 to 11000 MHz

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	59.58	1737.18
1000	35.04	217.15
2800	28.81	86.86
4540	38.96	37.77
5100	29.87	32.18
6150	23.72	23.81
6650	18.85	15.26
7020	4.74	3.34
7150	2.97	2.01
7250	2.31	1.56
7900	1.46	1.23
8500	1.24	1.14
10500	0.92	1.29
11000	0.82	1.05
12000	1.37	1.87
15000	3.95	3.19
18000	5.64	2.95



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

