LTCC SURFACE MOUNT

High Pass Filter

HFHK-1320+

50Ω 1500 to 8500 MHz

THE BIG DEAL

- Insertion Loss, Typ. 0.7 dB
- Stopband Rejection, Typ. 78 dB
- Passband Return Loss, Typ. 17 dB
- 1008 Surface Mount Footprint
- Power Handling: 6 W
- Shielded Construction: Prevents De-Tuning & EMI
- Protected by US Patents 11,638,370 and 11,744,057




Generic photo used for illustration purposes only

APPLICATIONS

- Radar, EW, ECM Defense Systems
- Test and Measurement Equipment
- Telecommunications and Broadband Wireless Systems
- 5G Sub-6 GHz
- WiFi 6E

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

The HFHK-1320+ is a passive RF component designed for signal conditioning in high-frequency circuits. It utilizes ceramic-based construction to achieve stable electrical behaviour across a broad operating range. The device supports bidirectional signal flow and is optimized for integration into compact layouts, making it suitable for dense PCB designs. It's surface-mount format aligns with standard automated assembly processes, and the internal structure is engineered to minimize parasitic effects that could impact performance at microwave frequencies. The component is built to maintain consistent characteristics under varying environmental conditions, contributing to overall system reliability.

ELECTRICAL SPECIFICATIONS[1,2,3] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F4-F5	1500 - 3500	—	1.5	2.5	dB
		F5-F6	3500 - 6500	—	0.7	1.5	
		F6-F7	6500 - 8500	—	0.8	2.5	
	Freq. Cut-Off[4]	Fc	1350	—	3	—	dB
	Return Loss	F4-F5	1500 - 3500	—	15	—	
		F5-F6	3500 - 6500	8	17	—	
		F6-F7	6500 - 8500	—	16	—	
Stopband	Rejection	DC-F1	DC - 350	67	78	—	dB
		F1-F2	350 - 700	40	49	—	
		F2-F3	700 - 975	20	28	—	


1. Tested in Evaluation Board P/N TB-HFHK-1320+.
2. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.
3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ± 5%

ABSOLUTE MAXIMUM RATINGS[5]

Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power[6]	6 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1 W at +125°C.

TYPICAL FREQUENCY RESPONSE





High Pass Filter


HFHK-1320+


50Ω 1500 to 8500 MHz


TYPICAL PERFORMANCE GRAPHS











High Pass Filter

HFHK-1320+

50Ω 1500 to 8500 MHz

FUNCTIONAL DIAGRAM





Figure 1. HFHK-1320+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	1	Connects to RF Input Port
RF2[2]	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-798)

CASE STYLE DRAWING



Weight: .019 grams.
Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

PRODUCT MARKING*: Y1

*Marking may contain other features or characters for internal lot control.

High Pass Filter

HFHK-1320+

50Ω 1500 to 8500 MHz

SUGGESTED PCB LAYOUT




Figure 2. Suggested PCB Layout

LTCC SURFACE MOUNT

High Pass Filter

HFHK-1320+

50Ω 1500 to 8500 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NL1008C-10 Lead Finish: Tin Over Nickel Plating
RoHS/REACH Status	Compliant
Tape and Reel	F75
Suggested Layout for PCB Design	PL-798
Evaluation Board	TB-HFHK-1320+ Gerber File
Environmental Rating	ENV06T10

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html