


THE BIG DEAL

- High Gain, Typ. 30.3 dB
- High P_{SAT} , Typ. +39.1 dBm
- Excellent PAE, Typ. 28.3%
- High Linearity Design Optimized for High PAR Communication Signals
- 6x6 mm 28-Lead QFN-Style Package




Generic photo used for illustration purposes only

APPLICATIONS

- Back Haul Radio Systems
- Radar Systems

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' PMA6-123-10W+ is a GaAs MMIC Power Amplifier operating from 10.0 to 11.7 GHz. This internally matched 50Ω amplifier provides 30.3 dB of gain, +39.1 dBm saturated output power, and +46.1 dBm output IP3, while operating from a +8 V power supply and consuming 1.5 A of bias current. This amplifier is fully matched at the input and output, allowing for seamless implementation, and it is assembled in a 6x6 mm 28-Lead QFN-style package. These characteristics make it ideally suited for back haul radio systems and radar systems that require high operating output power, while maintaining very low distortion characteristics.

KEY FEATURES

Feature	Advantages
High P _{SAT} Typ. +39.1 dBm	With a high saturated output power, this device can be used as the power amplifier for Back Haul Radio and/or Radar Systems.
High Gain Typ. 30.3 dB	Reduces the number of amplification stages at the system level.
6x6 mm 28-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.



MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_{DD} = +8 V, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		10.0		11.7	GHz
Gain	10.0	27.4	29.0		dB
	10.5	27.8	29.4		
	10.9	28.9	30.3		
	11.3	29.4	30.7		
	11.7	29.3	30.7		
Output Power at 1 dB Compression (P _{1dB})	10.0		+38.4		dBm
	10.5		+38.4		
	10.9		+38.6		
	11.3		+38.7		
	11.7		+38.4		
Output Power at Saturation (P _{SAT}) ²	10.0		+39.0		dBm
	10.5		+39.0		
	10.9		+39.1		
	11.3		+39.2		
	11.7		+38.9		
Power Added Efficiency (PAE) at P _{SAT}			28.3		%
Output Third-Order Intercept (P _{OUT} = +31 dBm/Tone)	10.0		+45.9		dBm
	10.5		+45.6		
	10.9		+45.3		
	11.3		+45.0		
	11.7		+44.2		
Input Return Loss	10.0		10		dB
	10.5		11		
	10.9		12		
	11.3		16		
	11.7		16		
Output Return Loss	10.0		17		dB
	10.5		13		
	10.9		13		
	11.3		14		
	11.7		13		
Isolation	10.0		69		dB
	10.5		67		
	10.9		63		
	11.3		64		
	11.7		61		
Noise Figure	10.0		4.9		dB
	10.5		4.9		
	10.9		5.0		
	11.3		5.1		
	11.7		5.2		
Device Operating Voltage (V _{DD}) ³		+6	+8	+8	V
Device Operating Current (I _{DD}) ^{4, 5}			1.5		A
Gate Voltage (V _{G12})			-0.85		V
Gate Voltage (V _{G3})			-0.81		V
Gate Voltage (V _{G4})			-1.2		V
Device Gate Current (I _{GG}) ⁶				29	mA
DC Current Variation vs. Temperature ⁷			-0.34		mA/°C
DC Current Variation vs. Voltage ⁸			-0.44		μA/mV

1. Tested on Mini-Circuits Characterization Test Board TB-PMA612310WC+. See Figure 2. Loss de-embedded to the RF input and output pins of the device.

2. P_{SAT} is defined as when the Output Power changes 0.1 dB per 1 dB change in Input Power.3. V_{DD} = V_{D1} = V_{D2} = V_{D3} = V_{D4} = V_{D3B} = V_{D4B}4. Current at P_{IN} = -20 dBm. Current at saturation reaches 4.7 A.5. I_{DD} = I_{DD1} + I_{DD2} + I_{DD3} + I_{DD4}; I_{DD12} = I_{DD1} + I_{DD2} = 310 mA; I_{DD3} = 840 mA; I_{DD4} = 350 mA.

6. At saturation.

7. (Current at +95°C - Current at -40°C)/(+135°C)

8. (Current at +8 V - Current at +6 V)/(+2 V)





MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+


Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS


GAIN vs. TEMPERATURE

$P_{IN} = -15$ dBm, $V_{DD} = +8$ V




GAIN vs. DEVICE VOLTAGE

$P_{IN} = -15$ dBm, TEMPERATURE = +25°C




INPUT RETURN LOSS vs. TEMPERATURE

$P_{IN} = -15$ dBm, $V_{DD} = +8$ V




INPUT RETURN LOSS vs. DEVICE VOLTAGE

$P_{IN} = -15$ dBm, TEMPERATURE = +25°C




OUTPUT RETURN LOSS vs. TEMPERATURE

$P_{IN} = -15$ dBm, $V_{DD} = +8$ V



OUTPUT RETURN LOSS vs. DEVICE VOLTAGE

$P_{IN} = -15$ dBm, TEMPERATURE = +25°C





MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+


Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS


ISOLATION vs. TEMPERATURE

$P_{IN} = -15$ dBm, $V_{DD} = +8$ V




ISOLATION vs. DEVICE VOLTAGE

$P_{IN} = -15$ dBm, TEMPERATURE = +25°C




P1dB vs. TEMPERATURE

$V_{DD} = +8$ V




P1dB vs. DEVICE VOLTAGE

TEMPERATURE = +25°C




P_{SAT} vs. TEMPERATURE

$V_{DD} = +8$ V



P_{SAT} vs. DEVICE VOLTAGE

TEMPERATURE = +25°C





MMIC SURFACE MOUNT

Power Amplifier


PMA6-123-10W+

Mini-Circuits


50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS


OUTPUT IP3 vs. TEMPERATURE
 $P_{OUT} = +31$ dBm/TONE, TONE SPACING = 5 MHz, $V_{DD} = +8$ V




OUTPUT IP3 vs. DEVICE VOLTAGE
 $P_{OUT} = +31$ dBm/TONE, TONE SPACING = 5 MHz
TEMPERATURE = +25°C




IM3 vs. TEMPERATURE
 $P_{OUT} = +31$ dBm/TONE, TONE SPACING = 5 MHz, $V_{DD} = +8$ V




IM3 vs. DEVICE VOLTAGE
 $P_{OUT} = +31$ dBm/TONE, TONE SPACING = 5 MHz
TEMPERATURE = +25°C



NOISE FIGURE vs. TEMPERATURE
 $V_{DD} = +8$ V



NOISE FIGURE vs. DEVICE VOLTAGE
TEMPERATURE = +25°C



Mini-Circuits



MMIC SURFACE MOUNT







Power Amplifier

PMA6-123-10W+

Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS



Mini-Circuits









MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS





MMIC SURFACE MOUNT






Power Amplifier

PMA6-123-10W+

Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS





MMIC SURFACE MOUNT

Power Amplifier


PMA6-123-10W+

Mini-Circuits


50 Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS


2nd HARMONIC vs. P_{OUT}
V_{DD} = +8 V, TEMPERATURE = +25°C




2nd HARMONIC vs. DEVICE VOLTAGE
P_{OUT} = +39 dBm, TEMPERATURE = +25°C



3rd HARMONIC vs. P_{OUT}
V_{DD} = +8 V, TEMPERATURE = +25°C



3rd HARMONIC vs. DEVICE VOLTAGE
P_{OUT} = +39 dBm, TEMPERATURE = +25°C





MMIC SURFACE MOUNT




Power Amplifier

PMA6-123-10W+

Mini-Circuits

50 Ω 10 to 11.7 GHz +39 dBm P_{SAT}

TYPICAL PERFORMANCE GRAPHS





MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

ABSOLUTE MAXIMUM RATINGS⁹

Parameter	Ratings
Operating Temperature ¹⁰	-40°C to +95°C
Storage Temperature	-65°C to +150°C
Junction Temperature ¹¹	+175°C
Total Power Dissipation	24 W
Input Power (CW), V _{DD} = +8 V	+34 dBm
DC Drain Voltage at V _{DD} ¹²	+9 V
DC Gate Voltage at V _{G12} , V _{G3} , V _{G4}	-3 V ≤ V _{G12} , V _{G3} , V _{G4} ≤ -0.4 V
DC Drain Current I _{DD}	5 A
DC Gate Current I _{GG}	29 mA

9. Permanent damage may occur if these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

10. Bottom of Die.

11. Peak temperature on top of Die.

12. V_{DD} = V_{D1} = V_{D2} = V_{D3} = V_{D4} = V_{D3B} = V_{D4B}

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ _{JC}) ¹³	4.8°C/W

13. Θ_{JC} = (Hot Spot Temperature on Die - Temperature at Ground Lead) / Dissipated Power

ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1C	1000 to < 2000	ANSI/ESDA/JEDEC JS-001-2023
CDM	C2A	500 to < 750	ANSI/ESDA/JEDEC JS-002-2022



ESD HANDLING PRECAUTION: This device is designed to be Class 1C for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C





MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

FUNCTIONAL DIAGRAM




Figure 1. PMA6-123-10W+ Functional Diagram

PIN DESCRIPTION

Function	Pin Number	Description (Refer to Figure 1)
RF-IN	4	RF-IN pin connects to RF Input port.
RF-OUT	18	RF-OUT pin connects to RF Output port.
V _{D1}	27	DC Input pin connects to First Stage Drain Voltage port.
V _{G12}	9	DC Input pin connects to First/Second Stage Gate Voltage port.
V _{D2}	26	DC Input pin connects to Drain Voltage port of 2 nd stage top half.
V _{D3}	24	DC Input pin connects to Drain Voltage port of 3 rd stage top half.
V _{G3}	10	DC Input pin connects to 3 rd Stage Gate Voltage port.
V _{D4}	23	DC Input pin connects to 4 th Stage Drain Voltage port.
V _{G4}	11	DC Input pin connects to 4 th Stage Gate Voltage port.
V _{D3B}	12	DC Input pin connects to Drain Voltage port of 3 rd stage bottom half.
V _{D4B} ¹⁴	13	DC Input pin connects to 4 th Stage Drain Voltage Alternate port.
NC	3, 5, 17, 19, 25	Not connected on test board. May be connected to ground or left open.
NC	2, 6, 16, 20	Connected to ground on test board. May be connected to ground or left open.
GND	1, 7, 8, 14, 15, 21, 22, 28 PADDLE	Connect to ground.

14. V_{D4B} can be used as an alternate to V_{D4}. V_{D4B} and V_{D4} are connected internally. For optimal performance, voltage should be applied to both ports. During characterization, V_{D4} and V_{D4B} were connected via a jumper on TB-PMA612310WC+.



MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

CHARACTERIZATION BOARD




Figure 2. PMA6-123-10W+ Characterization Circuit

Component	Value	Size	Part Number	Manufacturer
C1 – C9	0.001 µF	0402	GRM1555C1H102JA01D	MURATA
C10 – C18	0.1 µF	0402	GRM155R71E104KE14D	MURATA
C19 – C27	1 µF	0603	06035C105KAT2A	KYOCERA AVX
L1, L2	33 nH	0603	0603AF-33NXJRW	COILCRAFT
L3, L4	56 nH	0402	0402DF-560XJRW	COILCRAFT
R1	24Ω	0402	RK73H1ETTP24R0F	KOA SPEER
R2	12Ω	0402	RK73H1ETTP12R0F	KOA SPEER
R3	0Ω	0402	RK73Z1ETTP	KOA SPEER



MMIC SURFACE MOUNT


Power Amplifier

PMA6-123-10W+

Mini-Circuits

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}


CASE STYLE DRAWING



Weight: 0.11 grams

Dimensions are in mm [inches]. Tolerances: 3 Pl. ±.050 [.002] mm [Inches]

PRODUCT MARKING



Marking may contain other features or characters for internal lot control.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 14 OF 15



MMIC SURFACE MOUNT

Power Amplifier

PMA6-123-10W+

50Ω 10 to 11.7 GHz +39 dBm P_{SAT}

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	WQ3359 Plastic package, exposed paddle, Lead Finish: Matte-Tin
RoHs Status	Compliant
Tape & Reel	F68
Standard Quantities Available on Reel	7" reels with 20, 50, 100, 200, 500, or 1K 13" reels with 2K, 3K, or 4K
Suggested Layout for PCB Design	PL-824
Evaluation Board	TB-PMA612310WC+
	Gerber File
Environmental Ratings	ENV08T1

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

