

# N-Type Adapter Panel

ZT-240

50Ω DC-11 GHz



## Overview

Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

## Mechanical Configuration

Parameter	Details
Configuration	24 x connector adapters: N-type female to N-type female
Finish	Clear or black anodized panel
Dimensions	19" width, 3U height

## Electrical Specifications at 25°C, per Adapter

Parameter	Conditions	Min	Typical	Max	Units
Frequency		DC		11	GHz
Insertion Loss			0.1		dB
Return Loss	DC - 6 GHz		35		dB
	6 - 11 GHz		30		

## Typical Performance

