



USB & ETHERNET & DAISY-CHAIN Solid-State Switch

ZTS-1SP80T-852

Mini-Circuits

50Ω

10 – 8500 MHz

SP80T

N-type & SMA

THE BIG DEAL

- Solid-state, high-performance switch
- High port count (1 to 80)
- Convenient rack-mountable chassis
- SSH secure Ethernet communication
- Daisy-chain control stacking of multiple switch racks

APPLICATIONS

- RF test automation & signal routing
- 5G FR1, Bluetooth & WiFi signal distribution
- MIMO antenna testing
- C-band radar & satcom

PRODUCT OVERVIEW

Mini-Circuits' ZTS series platform allows multiple solid-state switch types to be combined and integrated into a single rack-mount package with software control via USB and Ethernet. ZTS-1SP80T-852 integrates a combination of Mini-Circuits' USB-1SP16T-83H (SP16T) and USB-1SP8T-63H (SP8T) models into a single SP80T (1 x 80) switch configuration, operating from 10 MHz to 8.5 GHz with fast switching and high isolation.

The system is housed in a compact, 2U height, 19-inch rack chassis, with all RF connectors (N-type for the Common port and SMA for the input / output ports) on the front panel and power and control connections out of the way on the rear panel.

The switch is controlled via USB or Ethernet (supporting SSH, HTTP & Telnet protocols). Full software support is provided, including our user-friendly GUI application for Windows, flexible API, and programming instructions for Windows and Linux environments.

The daisy-chain control interface further simplifies control integration by allowing multiple switch racks to be interconnected via their respective serial in and out connections. The complete set of daisy-chained switches can then be independently controlled through a single USB / Ethernet connection.

KEY FEATURES

Feature	Advantages
High port count	Single SP80T (1 x 80) configuration with high isolation is well suited to automated test setups with large numbers of devices or channels under test
Wide bandwidth	Operation from 10 MHz to 8.5 GHz incorporates most of the key commercial wireless mesh network applications, including WiFi 6E, 5G FR1 and Zigbee.
Rack-mount chassis	Compact, 2U height 19" rack-chassis minimizes the rack space required in crowded production test environments.
Secure Ethernet communication	Support for SSH (Secure Shell protocol) provides a means for secure communication over Ethernet networks with strict security policies. HTTP & Telnet communication via Ethernet are also supported.



Generic photo used for illustration purposes only



ELECTRICAL SPECIFICATIONS @ 25°C

Parameter	Conditions	Min	Typ	Max	Units
Frequency		10		8500	MHz
Insertion Loss	10 - 3000 MHz		10	14	dB
	3000 - 6000 MHz		14	17	
	6000 - 8500 MHz		19	21	
Isolation (Between Outputs) ¹	10 - 3000 MHz	85	90		dB
	3000 - 6000 MHz	75	85		
	6000 - 8500 MHz	65	75		
Isolation (Inactive Paths) ²	10 - 3000 MHz	80	90		dB
	3000 - 6000 MHz	65	75		
	6000 - 8500 MHz	55	65		
Return Loss (COM Port) ³	10 - 3000 MHz		18		dB
	3000 - 6000 MHz		15		
	6000 - 8500 MHz		10		
Return Loss (Active Ports) ⁴	10 - 3000 MHz		19		dB
	3000 - 6000 MHz		15		
	6000 - 8500 MHz		13		
Return Loss (Terminated Ports) ⁵	10 - 3000 MHz		20		dB
	3000 - 6000 MHz		17		
	6000 - 8500 MHz		15		
Input Power	Thru Path, Cold Switching			+29	dBm
	Hot Switching			+20	
	Into Termination			+24	

1. Isolation measured between any pair of ports J1 to J80

2. Isolation measured between COM and any disconnected port. Example: Isolation for COM to J1 is the leakage measured at port J1 from a signal input at COM when the active switch path is set COM to J2.




3. Return loss into COM port for any active switch path (eg. COM to J1). COM is reflective when disconnected.



4. Return loss into any of ports J1-J80 when connected to COM

5. Return loss into any of ports J1-J80 when internally terminated



TYPICAL PERFORMANCE DATA







CONTROL INTERFACES

Ethernet Control	Supported Protocols	TCP / IP, SSH, HTTP, Telnet, DHCP, UDP
	Max Data Rate	100 Mbps (100Base-T Full Duplex)
USB Control	Supported Protocols	HID - High Speed
	Min Communication Time	400 μ s typ ¹

1. Based on the polling interval of the USB HID protocol (125 μ s with 64 bytes per packet) and no other significant CPU or USB activity

SOFTWARE & DOCUMENTATION

Mini-Circuits' full software and support package including user guide, Windows GUI, API, programming manual and examples can be downloaded free of charge (refer to the last page for the download path).

A comprehensive set of software control options is provided:

- GUI for Windows – Simple software interface for control via Ethernet and USB
- Programming / automation via Ethernet
 - Complete set of control commands which can be sent via any supported protocol – simple to implement in the majority of modern programming environments
- Programming / automation via USB
 - DLL files provide a full API for Windows with a set of intuitive functions which can be implemented in any programming environment supporting .Net Framework or ActiveX
 - Direct USB programming is possible in any other environment (not supporting .Net or ActiveX)

Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS

Hardware	Intel i3 (or equivalent) or later
GUI (USB or Ethernet Control)	Windows 7 or later
USB API DLL	Windows 7 or later with support for Microsoft .Net Framework or ActiveX
USB Direct Programming	Windows 7 or later; Linux
Ethernet	Windows, Linux or macOS with Ethernet TCP / IP support

PROGRAMMING COMMANDS

The key ASCII / SCPI commands for control of the system for control via the Ethernet or USB API are summarized below (refer to the programming manual for full details):

Command / Query	Description
:MN?	Read model name
:SN?	Read serial number
:FIRMWARE?	Read firmware version
:SP80T:STATE:port	Set the switch path: port = the switch port to connect Example. :SP80T:STATE:48 (set switch to state 48)
:SP80T:STATE?	Get the state of the SP80T



GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS

Mini-Circuits Multi Switch Controller (Ver. C3X6)

Mini-Circuits Main Control

Block Diagram Help

User Profile: Admin

Model Name: ZTS-1SP80T-852

Serial Number: 02306060127

Protocol: USB

IP:

Connection Status: Connected

Connection Options

Ethernet Config

Firmware Upgrade

Change User Profile

GUI Configuration

Switch Sequence

#	Name	State
01	USB-1SP8T-852H	3
02	USB-1SP16T-83H	13
03	USB-1SP16T-83H	1
04	USB-1SP16T-83H	7
05	USB-1SP16T-83H	3
06	USB-1SP16T-83H	8

01: USB-1SP8T-852H 02: USB-1SP16T-83H 03: USB-1SP16T-83H 04: USB-1SP16T-83H 05: USB-1SP16T-83H 06: USB-1SP16T-83H

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

No Switch No Switch No Switch No Switch No Switch No Switch

Switch Commands: :02:SP16T:STATE:13

Switch State Queries: :01:SP8T:STATE?

System Queries: :NumberOfSlaves?

Command History

```
[2/8/2024 9:28:51 AM] [Other Settings] SCPI: :01:SP8T:STATE? Result: :01:3 Return: 1
[2/8/2024 9:28:54 AM] [Other Settings] SCPI: :MN? Result: ZTS-1SP80T-852 Return: 1
[2/8/2024 9:28:57 AM] [Other Settings] SCPI: :SN? Result: 02306060127 Return: 1
[2/8/2024 9:29:01 AM] [Other Settings] SCPI: :FIRMWARE? Result: B1-ID92 Return: 1
[2/8/2024 9:29:04 AM] [Other Settings] SCPI: :NUMBEROFSLAVES? Result: 6 Return: 1
```

- Connect via USB or Ethernet
- Run GUI in demo mode to evaluate the software without a hardware connection
- View and set all switch states at the click of a button
- Configure automated switch sequences
- Update Ethernet settings and firmware



ABSOLUTE MAXIMUM RATINGS

Parameter	Conditions	Limits	Units
Temperature	Operating	0 to +50	°C
	Storage	-20 to +60	
Input Power (No Damage)	Cold switching	+30	dBm
	Into internal termination	+24	

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

POWER SUPPLY

Power Supply	AC mains input: 100-240 V, 50 / 60 Hz
Fuse	2A, 250V rating
Power Consumption	150W maximum

SWITCH STATE TABLE


Command	Switch Path
:SP80T:STATE:0	All ports disconnected
:SP80T:STATE:1	Com to port J1
:SP80T:STATE:2	Com to port J2
:SP80T:STATE:3	Com to port J3
:SP80T:STATE:4	Com to port J4
:SP80T:STATE:5	Com to port J5
:SP80T:STATE:6	Com to port J6
:SP80T:STATE:7	Com to port J7
:SP80T:STATE:8	Com to port J8
...	...
:SP80T:STATE:80	Com to port J80

CONNECTIONS

Port	Connector
COM	N-type female
J1-J80	SMA female
USB	USB type B
Ethernet / LAN	RJ45
Serial In & Out	D-Sub 9-pin
AC Input	IEC C14 inlet

FUNCTIONAL BLOCK DIAGRAM

- Absorptive SP80T (single-pole, eighty throw) switch
- Ports J1 to J80 are internally terminated in 50Ω when disconnected
- COM is reflective in the disconnected state (connected internally to S1 - open circuit)






USB & ETHERNET & DAISY-CHAIN Solid-State Switch

ZTS-1SP80T-852

Mini-Circuits

OUTLINE DRAWING



DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ± .03

3 PL DECIMALS ± .015

PRODUCT MARKING*

Product Marking: ZTS-1SP80T-852

Product Description: Solid-State SP80T

Product Frequency: 10-8500 MHz

Unit ID Label: Serial number and other identification marks

*Marking may contain other features or characters for internal lot control





USB & ETHERNET & DAISY-CHAIN Solid-State Switch




ZTS-1SP80T-852






Mini-Circuits

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE

Case Style	99-01-3086
Software, User Guide & Programming Manual	www.minicircuits.com/softwaredownload/multissw.html
Environmental Rating	ENV55
Regulatory Compliance	<div style="display: flex; align-items: center;"> <div style="border: 1px solid black; padding: 2px; font-size: 8px; margin-right: 10px;"> Refer to our website for compliance methodologies and qualifications </div> www.minicircuits.com/quality/environmental_introduction.html </div>

Contact Us: testsolutions@minicircuits.com

Included Accessories	Part Number	Description
	CBL-3W-xx	AC power cord (IEC C13 connector to local plug) Select one option from the list below. Please contact testsolutions@minicircuits.com if your regions is not listed.
	USB-CBL-AB-7+	USB cable (6.8ft) type A to type B
	CBL-RJ45-MM-5+	Ethernet cable (5 ft)
	HT-4-SMA	SMA connector wrench (4" length)
	D-SUB9-MF-6+	D-Sub (9-pin) serial cable (6 ft)

AC Power Cord Options	Part Number	Description
	CBL-3W-US	USA NEMA 5-15 plug (type B) to IEC C13 connector
	CBL-3W-EU	Europe CEE 7/7 plug (type E/F) to IEC C13 connector
	CBL-3W-UK	UK BS-1363 plug (type G) to IEC C13 connector
	CBL-3W-AU	Australia & China AS/NZS 3112 plug (type I) to IEC C13 connector
	CBL-3W-IL	Israel SI-32 plug (type H) to IEC C13 connector

Revision	Updates	Date	Creator	Reviewer
1	Original web publication	2-Nov-21	LW	N/A
2	Updated format; added block diagram; added max ratings	10-Feb-23	LW	SO
3	Extended frequency range	28-Aug-24	LW	WT

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

