



COAXIAL

# Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

## KEY FEATURES

- Wideband Coverage, 6 to 18 GHz
- Ultra-Low Phase Noise, -169 dBc/Hz Typ. at 10 kHz Offset
- High Output P1dB, +18 dBm Typ.
- High Output IP3, +28 dBm Typ.
- Voltage-Regulated Internally and Reverse Voltage-Protected
- Ideal evaluation module for LVA-6183PN+ MMIC




Generic photo used for illustration purposes only

## APPLICATIONS

- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems
- 5G MIMO and Back Haul Radio Systems
- Signal Distribution Networks

## FUNCTIONAL DIAGRAM



## PRODUCT OVERVIEW

Mini-Circuits' ZX60-06183LPN+ is an ultra-low phase noise amplifier utilizing MCL's own GaAs HBT-based amplifier, the LVA-6183PN+, offering industry-leading performance over its full frequency range from 6 to 18 GHz. This design operates on a single +8 V supply @ 146 mA and comes in a rugged, compact unibody case (0.74" x 0.75" x 0.46") with integrated SMA female connectors, making it an excellent candidate for demanding operating conditions and use in crowded system layouts. A compatible heat sink is provided (not installed) for convenient setup and standalone operation.

## ELECTRICAL SPECIFICATIONS AT +25°C BASEPLATE AND $V_s = +8V$ , UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range	-	6	-	18	GHz
Gain	6	16.8	18.6	-	dB
	9	17.2	19.0	-	
	12	17.1	19.1	-	
	15	15.9	17.8	-	
	18	13.4	15.6	-	
Input Return Loss	6	-	13	-	dB
	9	-	12	-	
	12	-	13	-	
	15	-	12	-	
	18	-	11	-	
Output Return Loss	6	-	15	-	dB
	9	-	12	-	
	12	-	12	-	
	15	-	10	-	
	18	-	10	-	

REV. OR  
ECO-027533  
ZX60-06183LPN+  
MCL NY  
251126

**Mini-Circuits**



COAXIAL

Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

**ELECTRICAL SPECIFICATIONS AT +25°C BASEPLATE AND  $V_s = +8V$ , UNLESS NOTED OTHERWISE**

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Output Power at 1 dB Compression (P <sub>1dB</sub> )	6	-	+20.0	-	dBm
	9	-	+20.0	-	
	12	-	+19.0	-	
	15	-	+16.5	-	
	18	-	+14.5	-	
Saturated Output Power (P <sub>SAT</sub> ) <sup>1</sup>	6	-	+25	-	dBm
	9	-	+24	-	
	12	-	+22	-	
	15	-	+20	-	
	18	-	+19	-	
Output Third Order Intercept Point (Output Power = +0 dBm/Tone)	6	-	+29.5	-	dBm
	9	-	+29.5	-	
	12	-	+28.5	-	
	15	-	+25.5	-	
	18	-	+23.0	-	
Directivity	6	-	34	-	dB
	9	-	23	-	
	12	-	20	-	
	15	-	18	-	
	18	-	19	-	
Noise Figure	6	-	4.7	-	dB
	9	-	4.8	-	
	12	-	4.6	-	
	15	-	5.5	-	
	18	-	7.1	-	
Additive Phase Noise <sup>2</sup>	-	-	-169	-	dBc/Hz
DC Supply Voltage (V <sub>s</sub> )	-	+6.5	+8	+9	V
DC Current <sup>3</sup>	-	-	146	215	mA

1. At P<sub>SAT</sub>, P<sub>OUT</sub> changes less than 0.1 dB for a 1 dB change in P<sub>IN</sub>.

2. Measured at an input power of -1.3 dBm, 6 GHz, and at 10 KHz offset.

3. Typical current measured under small signal conditions. Max DC current measured at P<sub>SAT</sub>. DC current increases as amplifier is driven into compression.







**COAXIAL**

# Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

**Mini-Circuits**

## TYPICAL PERFORMANCE GRAPHS

**GAIN****DIRECTIVITY****RETURN LOSS****OUTPUT POWER****NOISE FIGURE****OUTPUT IP3****Mini-Circuits**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 7



COAXIAL

Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

**ABSOLUTE MAXIMUM RATINGS<sup>4,5</sup>**

Parameter	Ratings
Operating Temperature (Case)	-40°C to +85°C Baseplate -40°C to +65 °C Ambient <sup>6</sup>
Storage Temperature	-55°C to +100°C
Total Power Dissipation <sup>6,7</sup>	1.72 W
RF Input Power (CW)	+15 dBm
DC Operating Voltage	+9.5 V

4. Specified under matched load to 50 ohms.

5. Continuous operation is not recommended at these extremes. Permanent damage may occur if any of these limits are exceeded.

6. Operation is recommended using the supplied heatsink or an alternative heatsink with a thermal resistance  $\leq 11.5 \text{ }^{\circ}\text{C/W}$ .7. Total power dissipation determined at  $V_s = +9.5 \text{ V}$  with the amplifier in saturation.**DETERMINING MAXIMUM THERMAL RESISTANCE OF USERS' EXTERNAL HEAT SINK**

MAXIMUM THERMAL RESISTANCE	$= \frac{\text{MAXIMUM OPERATING CASE TEMP} - \text{MAXIMUM USER AMBIENT TEMP}}{\text{POWER DISSIPATION}}$
<b>Example:</b>	MAXIMUM OPERATING CASE TEMP = +50°C (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) MAXIMUM USER AMBIENT TEMP = +30°C (USER DEFINED) POWER DISSIPATION = 10 WATTS (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) THEN MAXIMUM ALLOWABLE THERMAL RESISTANCE = 2°C/W




COAXIAL

Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

## ADDITIVE PHASE NOISE VS. OFFSET FREQUENCY



Measured at 6 GHz with an input power of -1.3 dBm.




COAXIAL


Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

## CASE STYLE DRAWING



## MOUNTING INFORMATION OF MODEL WITHOUT HEATSINK



Weight: 43 grams; without heatsink 23 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03; 3 Pl. ±.015 inches



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminal. See Application Note AN-40-010



COAXIAL

# Low Phase Noise Amplifier **ZX60-06183LPN+**

50Ω 6 to 18 GHz SMA Female

**ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD.**

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
RoHS Status	Compliant
Environmental Ratings	ENV23T10
Export Information	ECCN# EAR99

**ORDERING INFORMATION**

Model No. Link	<a href="#">ZX60-06183LPN+</a>
Case Style	GC957-3
Connector	IN: SMA Female OUT: SMA Female

## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)

