

Frequency Mixer

ADE-201FMH+

Level 13 (LO Power +13 dBm) 90 to 200 MHz



CASE STYLE: CD636

The Big Deal

- High IP3: +30 dBm
- Low conversion loss, 6.4 dB
- Excellent P1dB compression, +16 dBm at input
- High L-R isolation, 42 dB typ.
- High L-I isolation, 35 dB typ.

Product Overview

Mini-Circuits' ADE-201FMH+ is a surface mount frequency mixer providing high IP3 performance, ideal for minimizing 3rd order intermodulation distortion in multiple carrier environments and other systems where unwanted signals may be present. It also provides high isolation, high P1dB compression point, and low conversion loss. The mixer comes in a compact, six-lead plastic case measuring 0.27 x 0.31 x 0.22", saving space in dense board layouts.

Feature	Advantages
High IP3, +30 dBm	Minimizes third order intermodulation distortion and enables high-dynamic range.
Low conversion loss, 6.4 dB	Enables lower NF front ends, improving system sensitivity.
Excellent P1dB compression, +16 dBm at input	Provides linear performance for a wide range of RF input power levels.
High L-R isolation, • L-R, 42 dB • L-I, 35 dB	Preserves signal integrity from input to output and reduces undesired signal responses that can interfere with system performance.
Small size (0.27 x 0.31 x 0.22")	Saves board space and accommodates tight layouts

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High IP3

Frequency Mixer

ADE-201FMH+

Level 13 (LO Power +13 dBm) 90 to 200 MHz



Generic photo used for illustration purposes only

CASE STYLE: CD636

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	20 dBm
LO Power	17 dBm
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	4
IF	3
GROUND	1,2,5

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.162	.055	.100
6.91	7.87	5.59	2.54	4.11	1.40	2.54
H	J	K	L			wt
.030	.026	.065	.300			grams
0.76	0.66	1.65	7.62			0.25

Demo Board MCL P/N: TB-02 Suggested PCB Layout (PL-051)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- excellent IP3, 30 dBm typ.
- excellent P1dB compression, +16 dBm at input
- good L-R isolation, 42 dB typ.
- good L-I isolation, 35 dB typ.
- aqueous washable
- protected by U.S. patent 6,133,525

Applications

- amateur radio
- mobil radio
- radar
- vehicle recovery system
- locator transmitters


Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Frequency Range, RF	90	—	200	MHz
Frequency Range, LO	154	—	264	MHz
Frequency Range, IF	10	—	150	MHz
Conversion Loss	—	6.4	8.2	dB
LO to RF Isolation	34	42	—	dB
LO to IF Isolation	26	35	—	dB
IP3	—	30	—	dBm
RF Input Power at 1 dB Compression	—	+16	—	dBm

Typical Performance Data

Frequency (MHz)	Conversion Loss (dB)		Isolation L-R (dB)		Isolation L-I (dB)		VSWR RF Port (:1)		VSWR LO Port (:1)		IP3 (dBm)
	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	LO	+13 dBm	
90.10	154.10	6.87	52.67	42.88	1.88	5.24	28.50				
100.10	164.10	6.79	50.96	40.90	1.92	5.03	29.99				
106.10	170.10	6.67	49.81	39.71	1.96	4.86	30.79				
110.10	174.10	6.57	48.93	38.94	1.98	4.70	31.12				
112.10	176.10	6.46	48.50	38.56	1.96	4.63	31.01				
114.10	178.10	6.41	48.14	38.20	1.96	4.55	31.67				
116.10	180.10	6.41	47.76	37.83	1.95	4.46	32.52				
118.10	182.10	6.39	47.29	37.44	1.94	4.35	32.32				
120.10	184.10	6.36	46.83	37.08	1.94	4.23	32.40				
130.10	194.10	6.23	45.00	35.42	1.97	3.55	33.15				
136.10	200.10	6.29	44.04	34.47	1.95	3.06	33.70				
138.10	202.10	6.26	43.81	34.16	1.94	2.89	32.69				
140.10	204.10	6.24	43.55	33.85	1.93	2.72	33.30				
142.10	206.10	6.26	43.25	33.58	1.92	2.56	32.81				
150.10	214.10	6.20	42.42	32.67	1.98	1.98	33.46				
160.10	224.10	6.28	41.79	32.22	1.94	1.61	34.49				
170.10	234.10	6.33	42.09	32.64	1.81	1.77	34.58				
180.10	244.10	6.43	43.19	33.44	1.82	2.17	34.26				
190.10	254.10	6.52	44.37	34.27	1.82	2.58	29.36				
200.10	264.10	6.55	45.33	35.02	1.69	2.94	27.92				








Electrical Schematic



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ADE-201FMH+
ED-16303/1
WL/CP/AM
200421
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

ADE-201FMH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=64MHz (dB)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	7.29	7.10	6.94
50.1	114.1	7.25	6.98	6.87
60.1	124.1	7.18	6.95	6.83
72.1	136.1	7.21	7.01	6.88
82.1	146.1	7.10	6.96	6.83
92.1	156.1	7.00	6.88	6.76
106.1	170.1	6.80	6.67	6.55
114.1	178.1	6.54	6.41	6.33
126.1	190.1	6.38	6.28	6.18
136.1	200.1	6.38	6.29	6.17
146.1	210.1	6.27	6.18	6.11
158.1	222.1	6.37	6.27	6.20
168.1	232.1	6.46	6.35	6.24
180.1	244.1	6.54	6.43	6.33
190.1	254.1	6.65	6.52	6.43
200.1	264.1	6.72	6.55	6.43
212.1	276.1	6.80	6.61	6.45
222.1	286.1	6.84	6.62	6.44
232.1	296.1	6.91	6.66	6.45
244.1	308.1	7.13	6.84	6.61
254.1	318.1	7.31	6.99	6.76
266.1	330.1	7.49	7.15	6.88
276.1	340.1	7.64	7.25	6.98
286.1	350.1	7.86	7.44	7.15
298.1	362.1	8.03	7.59	7.25
308.1	372.1	8.17	7.68	7.32
320.1	384.1	8.30	7.77	7.37
330.1	394.1	8.48	7.90	7.47
340.1	404.1	8.69	8.06	7.60
352.1	416.1	8.91	8.25	7.76
362.1	426.1	9.12	8.42	7.92
372.1	436.1	9.32	8.58	8.08
384.1	448.1	9.52	8.77	8.23
394.1	458.1	9.67	8.89	8.35
406.1	470.1	9.83	9.00	8.42
416.1	480.1	9.97	9.10	8.51
426.1	490.1	10.13	9.22	8.59
438.1	502.1	10.37	9.41	8.75
448.1	512.1	10.53	9.54	8.85
460.1	524.1	10.73	9.70	8.97

RF (IN) (MHz)	LO (MHz)	IP-3 INPUT (dBm)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	25.42	23.71	23.20
50.1	114.1	20.94	22.27	24.69
60.1	124.1	20.46	22.94	26.22
72.1	136.1	22.40	25.40	28.60
82.1	146.1	24.09	26.84	27.84
92.1	156.1	25.84	29.06	29.44
106.1	170.1	27.88	31.09	32.83
114.1	178.1	28.68	31.26	34.86
126.1	190.1	31.30	34.27	34.33
136.1	200.1	31.62	34.21	36.94
146.1	210.1	31.86	33.45	34.20
158.1	222.1	32.85	33.81	36.44
168.1	232.1	32.67	34.21	36.82
180.1	244.1	29.89	33.03	37.79
190.1	254.1	27.86	29.46	34.32
200.1	264.1	26.37	28.24	29.36
212.1	276.1	24.62	26.97	28.19
222.1	286.1	22.97	25.76	27.56
232.1	296.1	21.31	24.05	26.12
244.1	308.1	19.78	22.68	25.13
254.1	318.1	18.86	21.74	24.32
266.1	330.1	17.69	20.71	23.27
276.1	340.1	16.83	19.71	22.33
286.1	350.1	16.09	18.76	21.67
298.1	362.1	15.54	18.18	20.72
308.1	372.1	15.14	17.66	20.14
320.1	384.1	14.34	16.79	19.18
330.1	394.1	13.58	16.08	18.56
340.1	404.1	13.15	15.67	18.10
352.1	416.1	12.84	15.45	17.84
362.1	426.1	12.40	14.94	17.40
372.1	436.1	11.98	14.49	16.95
384.1	448.1	11.81	14.23	16.57
394.1	458.1	11.78	14.25	16.58
406.1	470.1	11.65	13.99	16.20
416.1	480.1	11.42	13.73	15.93
426.1	490.1	11.17	13.43	15.64
438.1	502.1	11.04	13.35	15.52
448.1	512.1	10.89	13.13	15.22
460.1	524.1	10.72	12.92	14.90

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+16dBm (dB)		
		@LO (dBm)		
		+10	+13	+16
40.1	104.1	1.77	0.85	0.39
50.1	114.1	1.85	1.03	0.55
60.1	124.1	1.82	1.03	0.62
72.1	136.1	1.48	0.83	0.50
82.1	146.1	1.22	0.69	0.43
92.1	156.1	0.99	0.56	0.35
106.1	170.1	0.69	0.39	0.28
114.1	178.1	0.60	0.37	0.26
126.1	190.1	0.46	0.28	0.23
136.1	200.1	0.40	0.23	0.23
146.1	210.1	0.36	0.27	0.21
158.1	222.1	0.33	0.25	0.19
168.1	232.1	0.38	0.24	0.22
180.1	244.1	0.57	0.34	0.26
190.1	254.1	0.78	0.42	0.27
200.1	264.1	1.10	0.57	0.35
212.1	276.1	1.63	0.75	0.42
222.1	286.1	2.26	1.05	0.55
232.1	296.1	2.93	1.47	0.71
244.1	308.1	3.75	1.98	0.94
254.1	318.1	4.33	2.46	1.15
266.1	330.1	4.97	3.01	1.47
276.1	340.1	5.31	3.36	1.72
286.1	350.1	5.58	3.65	2.00
298.1	362.1	5.91	3.99	2.28
308.1	372.1	6.21	4.31	2.55
320.1	384.1	6.74	4.83	2.99
330.1	394.1	7.16	5.28	3.40
340.1	404.1	7.52	5.63	3.73
352.1	416.1	7.94	6.08	4.14
362.1	426.1	8.22	6.33	4.41
372.1	436.1	8.35	6.52	4.59
384.1	448.1	8.41	6.60	4.66
394.1	458.1	8.50	6.72	4.80
406.1	470.1	8.72	6.94	5.04
416.1	480.1	8.88	7.17	5.27
426.1	490.1	9.09	7.41	5.49
438.1	502.1	9.31	7.64	5.76
448.1	512.1	9.49	7.84	5.95
460.1	524.1	9.57	7.92	6.08

Frequency Mixer

ADE-201FMH+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=146.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=106.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=186.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+13			+13			+13
136.0	10.1	11.76	10.0	116.1	7.77	176.0	10.1	12.02
130.0	16.1	10.28	20.0	126.1	7.54	172.0	14.1	11.13
124.0	22.1	9.46	30.0	136.1	7.38	168.0	18.1	10.43
118.0	28.1	8.90	40.0	146.1	7.14	164.0	22.1	9.95
112.0	34.1	8.55	50.0	156.1	7.06	160.0	26.1	9.56
104.0	42.1	8.22	62.0	168.1	6.94	156.0	30.1	9.29
98.0	48.1	7.95	72.0	178.1	6.83	152.0	34.1	9.08
92.0	54.1	7.73	82.0	188.1	6.76	148.0	38.1	8.97
86.0	60.1	7.63	92.0	198.1	6.72	144.0	42.1	8.80
78.0	68.1	7.45	104.0	210.1	6.59	140.0	46.1	8.64
72.0	74.1	7.31	114.0	220.1	6.73	136.0	50.1	8.45
66.0	80.1	7.27	124.0	230.1	6.73	132.0	54.1	8.33
60.0	86.1	7.23	134.0	240.1	6.72	128.0	58.1	8.24
52.0	94.1	7.19	146.0	252.1	6.76	124.0	62.1	8.15
46.0	100.1	7.14	156.0	262.1	6.79	120.0	66.1	8.03
40.0	106.1	7.09	166.0	272.1	6.83	116.0	70.1	7.92
34.0	112.1	7.06	176.0	282.1	6.93	112.0	74.1	7.86
28.0	118.1	6.95	186.0	292.1	7.01	108.0	78.1	7.84
20.0	126.1	6.92	198.0	304.1	7.10	104.0	82.1	7.82
14.0	132.1	7.00	208.0	314.1	7.21	100.0	86.1	7.77
10.0	156.1	6.69	218.0	324.1	7.30	96.0	90.1	7.74
28.0	174.1	6.47	228.0	334.1	7.44	92.0	94.1	7.55
46.0	192.1	6.35	240.0	346.1	7.58	88.0	98.1	7.57
66.0	212.1	6.33	250.0	356.1	7.68	84.0	102.1	7.59
84.0	230.1	6.25	260.0	366.1	7.74	80.0	106.1	7.57
104.0	250.1	6.31	270.0	376.1	7.87	76.0	110.1	7.64
122.0	268.1	6.37	282.0	388.1	7.97	72.0	114.1	7.58
142.0	288.1	6.47	292.0	398.1	8.10	68.0	118.1	7.50
160.0	306.1	6.70	302.0	408.1	8.12	64.0	122.1	7.46
178.0	324.1	6.79	312.0	418.1	8.27	60.0	126.1	7.45
198.0	344.1	6.87	322.0	428.1	8.42	56.0	130.1	7.38
216.0	362.1	6.89	334.0	440.1	8.52	52.0	134.1	7.32
236.0	382.1	6.99	344.0	450.1	8.62	48.0	138.1	7.27
254.0	400.1	7.16	354.0	460.1	8.71	44.0	142.1	7.27
274.0	420.1	7.32	364.0	470.1	8.83	40.0	146.1	7.16
292.0	438.1	7.40	376.0	482.1	8.96	36.0	150.1	7.18
310.0	456.1	7.52	386.0	492.1	9.09	32.0	154.1	7.11
330.0	476.1	7.65	396.0	502.1	9.21	28.0	158.1	7.03
348.0	494.1	7.82	406.0	512.1	9.37	24.0	162.1	7.11
368.0	514.1	7.98	418.0	524.1	9.50	20.0	166.1	7.01

Frequency Mixer

ADE-201FMH+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)					@LO (dBm)		
	+10	+13	+16	+10	+13	+16			+10	+13	+16
104.1	59.34	59.12	59.35	49.17	49.03	48.98	40.1	104.1	22.32	21.53	20.61
114.1	57.58	57.59	57.74	48.21	48.04	47.93	50.1	114.1	21.17	20.61	20.11
124.1	56.61	56.82	56.96	47.32	47.13	47.00	60.1	124.1	24.33	23.84	23.52
136.1	55.39	55.36	55.19	45.90	45.81	45.67	72.1	136.1	27.85	27.27	26.94
146.1	54.04	53.80	53.70	44.43	44.28	44.15	82.1	146.1	30.37	29.99	29.90
156.1	52.54	52.42	52.12	42.67	42.52	42.36	92.1	156.1	33.69	33.38	33.46
170.1	50.12	49.81	49.62	39.91	39.71	39.50	106.1	170.1	35.95	35.82	35.80
178.1	48.39	48.14	47.93	38.42	38.20	38.01	114.1	178.1	38.53	38.24	38.15
190.1	45.95	45.71	45.58	36.29	36.05	35.86	126.1	190.1	40.42	40.53	40.89
200.1	44.26	44.04	43.90	34.71	34.47	34.27	136.1	200.1	42.57	42.70	42.77
210.1	42.90	42.80	42.64	33.28	33.08	32.89	146.1	210.1	42.15	42.16	42.16
222.1	41.97	41.86	41.99	32.37	32.24	32.37	158.1	222.1	41.05	40.96	41.17
232.1	42.06	42.00	41.99	32.60	32.51	32.51	168.1	232.1	38.65	38.90	39.25
244.1	43.25	43.19	43.12	33.51	33.44	33.37	180.1	244.1	37.46	37.74	37.80
254.1	44.51	44.37	44.34	34.33	34.27	34.22	190.1	254.1	35.86	35.97	36.14
264.1	45.50	45.33	45.25	35.09	35.02	34.96	200.1	264.1	35.55	35.43	35.63
276.1	46.12	45.87	45.74	35.91	35.83	35.77	212.1	276.1	33.92	33.55	33.39
286.1	46.69	46.43	46.24	36.57	36.47	36.40	222.1	286.1	33.78	33.54	33.09
296.1	47.85	47.59	47.34	37.25	37.16	37.09	232.1	296.1	33.56	33.20	32.91
308.1	49.58	49.22	49.01	38.03	37.96	37.89	244.1	308.1	33.24	33.24	32.79
318.1	50.56	50.06	49.72	38.60	38.51	38.46	254.1	318.1	32.71	32.75	32.27
330.1	51.43	50.86	50.49	39.04	38.99	38.93	266.1	330.1	31.73	31.63	31.33
340.1	52.41	51.86	51.35	39.26	39.20	39.16	276.1	340.1	32.13	31.92	31.74
350.1	53.39	52.80	52.30	39.37	39.35	39.32	286.1	350.1	31.08	30.89	30.57
362.1	53.99	53.24	52.74	39.45	39.44	39.42	298.1	362.1	31.96	31.51	31.04
372.1	54.30	53.63	52.98	39.58	39.58	39.59	308.1	372.1	30.86	30.32	29.78
384.1	55.17	54.23	53.50	39.69	39.73	39.76	320.1	384.1	31.79	31.30	30.83
394.1	56.07	55.23	54.46	39.96	40.04	40.08	330.1	394.1	31.22	30.31	29.84
404.1	56.83	55.80	54.93	40.16	40.24	40.30	340.1	404.1	32.54	31.65	30.91
416.1	58.21	56.98	56.00	40.39	40.50	40.59	352.1	416.1	32.40	31.22	30.54
426.1	59.99	58.58	57.45	40.38	40.50	40.60	362.1	426.1	33.38	31.83	31.11
436.1	61.33	60.02	58.70	40.39	40.54	40.67	372.1	436.1	33.93	31.97	31.15
448.1	61.00	60.05	58.93	40.30	40.43	40.57	384.1	448.1	34.83	32.46	31.44
458.1	60.72	59.72	58.58	40.21	40.36	40.53	394.1	458.1	36.10	33.29	32.10
470.1	61.17	60.72	59.72	40.07	40.22	40.37	406.1	470.1	36.80	33.34	31.96
480.1	62.33	62.80	61.90	40.24	40.41	40.55	416.1	480.1	38.64	34.25	32.50
490.1	62.08	63.09	63.17	40.34	40.52	40.73	426.1	490.1	39.87	34.25	32.05
502.1	59.55	60.84	61.21	40.56	40.74	40.98	438.1	502.1	45.69	36.81	33.86
512.1	60.05	61.16	60.77	40.57	40.79	41.02	448.1	512.1	48.76	36.97	33.49
524.1	59.75	62.58	64.88	40.42	40.65	40.87	460.1	524.1	49.76	40.36	35.20

Frequency Mixer

ADE-201FMH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=250.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+10	+13	+16		+10	+13	+16		+10	+13	+16
40.1	104.1	1.65	1.76	1.85	104.1	5.55	5.55	5.54	10.1	1.34	1.29	1.30
50.1	114.1	1.68	1.78	1.88	114.1	5.57	5.57	5.56	14.1	1.36	1.27	1.23
60.1	124.1	1.74	1.85	1.95	124.1	5.50	5.49	5.49	20.1	1.32	1.29	1.25
72.1	136.1	1.74	1.85	1.95	136.1	5.42	5.42	5.42	26.1	1.33	1.30	1.25
82.1	146.1	1.76	1.87	1.99	146.1	5.35	5.35	5.35	32.1	1.41	1.34	1.29
92.1	156.1	1.78	1.89	2.00	156.1	5.21	5.20	5.20	38.1	1.45	1.38	1.34
106.1	170.1	1.85	1.96	2.07	170.1	4.87	4.86	4.84	44.1	1.47	1.42	1.36
114.1	178.1	1.85	1.96	2.07	178.1	4.57	4.55	4.52	50.1	1.47	1.41	1.35
126.1	190.1	1.85	1.95	2.05	190.1	3.90	3.86	3.82	56.1	1.44	1.37	1.32
136.1	200.1	1.86	1.95	2.04	200.1	3.11	3.06	3.01	62.1	1.39	1.33	1.28
146.1	210.1	1.85	1.93	2.02	210.1	2.30	2.25	2.20	68.1	1.37	1.32	1.26
158.1	222.1	1.87	1.96	2.04	222.1	1.66	1.64	1.62	74.1	1.38	1.33	1.28
168.1	232.1	1.74	1.83	1.90	232.1	1.70	1.71	1.73	80.1	1.39	1.34	1.29
180.1	244.1	1.73	1.82	1.90	244.1	2.14	2.17	2.19	86.1	1.41	1.35	1.31
190.1	254.1	1.72	1.82	1.91	254.1	2.55	2.58	2.61	92.1	1.41	1.35	1.30
200.1	264.1	1.60	1.69	1.78	264.1	2.92	2.94	2.97	98.1	1.38	1.32	1.27
212.1	276.1	1.59	1.67	1.76	276.1	3.29	3.30	3.33	104.1	1.34	1.28	1.23
222.1	286.1	1.58	1.66	1.75	286.1	3.53	3.54	3.56	110.1	1.30	1.25	1.20
232.1	296.1	1.56	1.63	1.71	296.1	3.72	3.73	3.74	116.1	1.30	1.25	1.20
244.1	308.1	1.52	1.58	1.65	308.1	3.92	3.92	3.93	122.1	1.34	1.28	1.24
254.1	318.1	1.54	1.60	1.66	318.1	4.04	4.04	4.05	126.1	1.37	1.31	1.27
266.1	330.1	1.55	1.61	1.67	330.1	4.15	4.16	4.17	132.1	1.40	1.35	1.30
276.1	340.1	1.54	1.59	1.65	340.1	4.24	4.25	4.26	138.1	1.41	1.35	1.30
286.1	350.1	1.58	1.63	1.68	350.1	4.32	4.33	4.33	144.1	1.39	1.33	1.28
298.1	362.1	1.63	1.68	1.73	362.1	4.39	4.40	4.40	150.1	1.35	1.29	1.24
308.1	372.1	1.66	1.70	1.76	372.1	4.44	4.45	4.45	156.1	1.30	1.25	1.20
320.1	384.1	1.67	1.71	1.76	384.1	4.50	4.51	4.51	162.1	1.28	1.23	1.18
330.1	394.1	1.75	1.79	1.84	394.1	4.55	4.55	4.55	168.1	1.29	1.24	1.19
340.1	404.1	1.77	1.82	1.87	404.1	4.57	4.58	4.58	174.1	1.31	1.25	1.20
352.1	416.1	1.78	1.82	1.87	416.1	4.60	4.60	4.61	180.1	1.31	1.25	1.21
362.1	426.1	1.82	1.87	1.91	426.1	4.62	4.63	4.63	186.1	1.29	1.24	1.19
372.1	436.1	1.86	1.91	1.96	436.1	4.64	4.65	4.64	192.1	1.25	1.20	1.15
384.1	448.1	1.89	1.95	2.00	448.1	4.69	4.69	4.69	198.1	1.21	1.16	1.12
394.1	458.1	1.91	1.96	2.01	458.1	4.71	4.71	4.71	204.1	1.20	1.15	1.11
406.1	470.1	1.97	2.02	2.07	470.1	4.74	4.74	4.74	210.1	1.22	1.17	1.13
416.1	480.1	2.00	2.07	2.13	480.1	4.76	4.76	4.77	216.1	1.25	1.20	1.16
426.1	490.1	1.99	2.05	2.11	490.1	4.77	4.77	4.77	222.1	1.27	1.22	1.17
438.1	502.1	2.03	2.09	2.15	502.1	4.80	4.80	4.80	228.1	1.27	1.21	1.17
448.1	512.1	2.04	2.10	2.16	512.1	4.80	4.81	4.81	234.1	1.24	1.19	1.14
460.1	524.1	2.06	2.12	2.18	524.1	4.83	4.83	4.83	240.1	1.20	1.15	1.10

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	-0.56	15.44	25.44	22.46	26.51	16.80	25.27	24.48	27.68	41.40
1	---	29.50	---	33.94	10.35	34.92	20.12	40.95	32.03	41.97	61.77	45.11
2	122.38	73.83	77.02	80.07	80.85	84.28	102.54	87.76	98.97	87.53	91.67	85.95
3	129.28	101.47	88.51	102.27	90.56	101.07	98.81	105.04	103.22	101.72	103.50	102.59
4	129.21	101.52	99.64	93.39	102.29	95.25	101.82	101.45	103.45	102.84	104.04	101.07
5	129.13	102.56	101.71	96.86	99.05	96.32	98.74	100.06	102.92	103.38	103.27	103.42
6	129.61	103.72	101.64	102.31	88.73	102.95	84.74	103.89	99.97	100.64	101.55	103.10
7	129.81	103.98	102.68	99.91	101.18	91.76	103.46	92.11	102.81	99.32	103.55	104.45
8	129.53	103.60	103.29	105.19	101.08	98.77	96.82	96.43	96.03	102.43	103.09	104.49
9	126.01	100.62	101.90	100.44	103.30	99.21	94.74	98.12	93.37	95.09	100.99	102.18
10	129.74	95.80	98.56	86.14	100.88	77.53	98.80	66.30	93.20	64.90	101.57	77.15
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -15 dBm.
 LO IN: 210 MHz; +13.00 dBm
 IF OUT: 64 MHz; -21.71 dBm

RF HARMONICS ORDER








	(-dBm)	(-dBc)										
0	---	---	9.65	25.63	35.61	32.61	36.74	26.85	35.38	33.86	36.57	53.80
1	---	29.41	---	33.93	10.34	34.94	20.04	41.00	31.73	42.05	61.21	45.18
2	111.01	63.41	67.22	69.71	71.31	73.97	96.73	77.59	87.80	77.53	81.22	75.05
3	122.59	95.34	91.54	95.00	80.38	92.75	78.34	93.60	82.03	94.92	90.20	100.03
4	125.15	101.02	108.99	92.56	104.39	96.53	103.76	107.64	105.41	114.11	108.52	108.88
5	124.02	111.63	96.65	108.83	96.73	106.54	99.77	113.37	99.81	112.48	102.15	109.09
6	120.28	110.67	104.98	110.18	92.27	109.36	88.46	109.82	98.71	111.76	105.73	111.79
7	123.18	113.06	112.84	111.38	112.78	102.21	113.83	102.45	113.89	109.52	111.81	112.78
8	123.09	113.65	112.84	114.47	110.92	107.63	107.31	108.41	107.11	112.79	113.21	114.38
9	120.32	113.98	113.11	104.92	111.26	101.54	101.42	99.67	103.60	93.51	110.38	102.18
10	123.80	109.34	110.26	102.60	113.06	90.80	111.72	80.99	110.65	80.44	111.87	91.16
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER







Test conditions: RF IN: 146 MHz; -5 dBm.
 LO IN: 210 MHz; +13.00 dBm
 IF OUT: 64 MHz; -11.54 dBm

- Notes:
1. All Harmonics are in (dBc) relative to IF OUTPUT
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT
 3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

Typical Performance Curves



Typical Performance Curves



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	-0.56	15.44	25.44	22.46	26.51	16.80	25.27	24.48	27.68	41.40
1	---	29.50	---	33.94	10.35	34.92	20.12	40.95	32.03	41.97	61.77	45.11
2	122.38	73.83	77.02	80.07	80.85	84.28	102.54	87.76	98.97	87.53	91.67	85.95
3	129.28	101.47	88.51	102.27	90.56	101.07	98.81	105.04	103.22	101.72	103.50	102.59
4	129.21	101.52	99.64	93.39	102.29	95.25	101.82	101.45	103.45	102.84	104.04	101.07
5	129.13	102.56	101.71	96.86	99.05	96.32	98.74	100.06	102.92	103.38	103.27	103.42
6	129.61	103.72	101.64	102.31	88.73	102.95	84.74	103.89	99.97	100.64	101.55	103.10
7	129.81	103.98	102.68	99.91	101.18	91.76	103.46	92.11	102.81	99.32	103.55	104.45
8	129.53	103.60	103.29	105.19	101.08	98.77	96.82	96.43	96.03	102.43	103.09	104.49
9	126.01	100.62	101.90	100.44	103.30	99.21	94.74	98.12	93.37	95.09	100.99	102.18
10	129.74	95.80	98.56	86.14	100.88	77.53	98.80	66.30	93.20	64.90	101.57	77.15
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -15 dBm.
 LO IN: 210 MHz; +13.00 dBm
 IF OUT: 64 MHz; -21.71 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	---	---	9.65	25.63	35.61	32.61	36.74	26.85	35.38	33.86	36.57	53.80
1	---	29.41	---	33.93	10.34	34.94	20.04	41.00	31.73	42.05	61.21	45.18
2	111.01	63.41	67.22	69.71	71.31	73.97	96.73	77.59	87.80	77.53	81.22	75.05
3	122.59	95.34	91.54	95.00	80.38	92.75	78.34	93.60	82.03	94.92	90.20	100.03
4	125.15	101.02	108.99	92.56	104.39	96.53	103.76	107.64	105.41	114.11	108.52	108.88
5	124.02	111.63	96.65	108.83	96.73	106.54	99.77	113.37	99.81	112.48	102.15	109.09
6	120.28	110.67	104.98	110.18	92.27	109.36	88.46	109.82	98.71	111.76	105.73	111.79
7	123.18	113.06	112.84	111.38	112.78	102.21	113.83	102.45	113.89	109.52	111.81	112.78
8	123.09	113.65	112.84	114.47	110.92	107.63	107.31	108.41	107.11	112.79	113.21	114.38
9	120.32	113.98	113.11	104.92	111.26	101.54	101.42	99.67	103.60	93.51	110.38	102.18
10	123.80	109.34	110.26	102.60	113.06	90.80	111.72	80.99	110.65	80.44	111.87	91.16
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 146 MHz; -5 dBm.
 LO IN: 210 MHz; +13.00 dBm
 IF OUT: 64 MHz; -11.54 dBm

- Notes:
1. All Harmonics are in (dBc) relative to IF OUTPUT
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT
 3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

Case Style

CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
			100	
			200	
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	MMG	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR CD541/542/636/637 CASE STYLES,
"jv", "ju", "jw" PIN CONNECTIONS**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±

	INITIALS	DATE
DRAWN	MMG	07/17/02
CHECKED	WL	08/02/02
APPROVED	DJ	08/05/02



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, jv/ju/jw, CD541/542/636/637, ADE, TB-02



Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-051	A
FILE:	98PL051	SCALE: 8:1	SHEET: 1 OF 1

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215