



Mini-Circuits

MMIC SURFACE MOUNT


Medium Power Amplifier

AVA-17303+

50 Ω 17 to 31.5 GHz High Linearity Driver

THE BIG DEAL

- High P1dB, Typ. +22.9 dBm
- High OIP3, Typ. +33 dBm
- Supply Voltage, +6 V at 160 mA
- 4x4 mm 20-Lead QFN-Style Package




Generic photo used for illustration purposes only

APPLICATIONS

- Test and Measurement Equipment
- Satellite Communications
- Radar, EW, and ECM Defense Systems
- 5G mmWave, MIMO Wireless Infrastructure Systems
- Microwave Radio & VSAT

FUNCTIONAL DIAGRAM (Top View)



PRODUCT OVERVIEW

The AVA-17303+ is a GaAs MMIC Medium Power Amplifier operating from 17 to 31.5 GHz. This amplifier provides typical 20.5 dB of gain, +22.9 dBm P1dB, and +33 dBm OIP3 while operating from a +6 V power supply at 160 mA. Additionally, it is internally matched to 50 Ω and comes in a 4x4 mm 20-Lead QFN-Style package. These characteristics make it ideally suited as a driver amplifier in point-to-point radios and communications systems requiring high operating output power while maintaining low distortion characteristics.

KEY FEATURES

Features	Advantages
High Gain, Typ. 20.5 dB High P1dB, Typ. +22.9 dBm	High gain and output power make this device excellent for wideband systems from 17 to 31.5 GHz that require at least 0.2 W of operating output power over the full band.
High OIP3, Typ. +33 dBm	High operating OIP3 provides very low in-band distortion products, enabling minimal signal degradation in high fidelity measurement systems and demanding communication systems.
4x4 mm 20-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.



MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

ELECTRICAL SPECIFICATIONS¹ AT +25°C, $V_{DD} = +6$ V, AND $Z_0 = 50\Omega$ UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		17		31.5	GHz
Gain	17	18.4	21.0		dB
	20	17.7	20.4		
	24	16.8	20.5		
	27	18.7	21.9		
	30	16.0	23.7		
	31.5	13.7	20.1		
Input Return Loss	17		11		dB
	20		17		
	24		12		
	27		8		
	30		10		
	31.5		7		
Output Return Loss	17		19		dB
	20		13		
	24		12		
	27		10		
	30		17		
	31.5		20		
Isolation	17 - 31.5		56		dB
Output Power at 1 dB Compression (P_{1dB})	17		+23.3		dBm
	20		+22.6		
	24		+22.9		
	27		+23.7		
	30		+23.2		
	31.5		+21.8		
Output Power at Saturation (P_{SAT}) ²	17		+25.2		dBm
	20		+23.7		
	24		+23.6		
	27		+23.8		
	30		+23.5		
	31.5		+21.9		
Output Third-Order Intercept (OIP3) ($P_{OUT} = +6$ dBm/Tone)	17		+31		dBm
	20		+31		
	24		+33		
	27		+33		
	30		+34		
	31.5		+31		
Noise Figure	17		5.7		dB
	20		4.9		
	24		4.1		
	27		3.7		
	30		3.4		
	31.5		3.5		
Device Operating Voltage (V_{DD}) ³		+5	+6	+7	V
Device Operating Current (I_{DD}) ⁴			160		mA
Gate Voltage (V_G)			-0.54		V
Gate Current (I_G) ⁵			57		μA
Device Current Variation vs. Temperature ⁶			-3.6		μA/°C

1. Tested on Mini-Circuits Evaluation Test Board TB-AVA-17303C+. See Figure 2. Board loss de-embedded.

2. Defined as output power at which change is 0.1 per 1 dB change in input power.

3. $V_{DD} = V_{DD1} = V_{DD2} = V_{DD3}$ 4. Current at $P_{IN} = -25$ dBm. Increases to 250 mA at P1dB. $I_{DD} = I_{DD1} + I_{DD2} + I_{DD3}$.5. Current at $P_{IN} = -25$ dBm. Increases to 300 μA at P1dB.6. (Current at +85°C - Current at -55°C)/(140°C). V_G held constant over temperature.









MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

TYPICAL PERFORMANCE GRAPHS











MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**







50Ω 17 to 31.5 GHz High Linearity Driver

TYPICAL PERFORMANCE GRAPHS





TYPICAL PERFORMANCE GRAPHS










MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

TYPICAL PERFORMANCE GRAPHS





MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

ABSOLUTE MAXIMUM RATINGS⁷

Parameter	Ratings
Operating Temperature (ground lead)	-55°C to +85°C
Storage Temperature	-65°C to +150°C
Junction Temperature ⁸	+175°C
Total Power Dissipation	1.8 W
Input Power (CW), $V_{DD} = +6$ V	+25 dBm
DC Drain Voltage on V_{DD} ⁹	+9 V
DC Drain Current I_{DD} ¹⁰	500 mA
DC Voltage at RF-IN	+9 V
DC Voltage at RF-OUT	+9 V
DC Gate Voltage on V_G	-6 V to +1 V
DC Gate Current I_G	8 mA

7. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

8. Peak Temperature on top of Die.

9. $V_{DD} = V_{DD1} = V_{DD2} = V_{DD3}$.

10. $I_{DD} = I_{DD1} + I_{DD2} + I_{DD3}$.

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC}) ¹¹	46.9°C/W

11. $\Theta_{JC} = (\text{Hot Spot Temperature on Die} - \text{Temperature at Ground Lead}) / \text{Dissipated Power}$

ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1A	250 V to < 500 V	ANSI/ESDA/JEDEC JS-001-2023
CDM	C2A	500 V to < 750 V	ANSI/ESDA/JEDEC JS-002-2022



ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL3 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C





MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

FUNCTIONAL DIAGRAM (Top View)




Figure 1. AVA-17303+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description (Refer to Fig 2)
RF-IN	9	RF-IN Pad connects to RF Input port.
RF-OUT	17	RF-OUT Pad connects to RF Output port.
V _{DD1}	5	DC input pad connects to Drain voltage 1.
V _{DD2}	3	DC input pad connects to Drain voltage 2.
V _{DD3}	1	DC input pad connects to Drain voltage 3.
V _G	13	DC input pad connects to Gate control voltage.
NC	2, 4, 6, 7, 11, 12, 14, 15, 19, 20	Not used internally. Connected to ground on test board.
GND	8, 10, 16, 18, Paddle	Connects to ground.

EVALUATION TEST BOARD




Figure 2. AVA-17303+ Evaluation and Application Circuit

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1 dB Compression (P_{1dB}), Output IP₃ (OIP₃), and Noise Figure measured using N5245B PNA-X Microwave Network Analyzer.

Conditions:

- Gain and Return Loss: P_{IN} = -25 dBm
- Output IP₃ (OIP₃): Two tones, spaced 1 MHz apart, +6 dBm/Tone at output.

Power ON/Power OFF Sequence

Caution: Permanent damage to the device will occur if the Power ON and Power OFF sequences are not followed.

POWER ON:

- Set V_G = -1.2 V and Turn ON.
- Set V_{DD} = +6 V and Turn ON.
- Increase V_G to desired nominal I_{DD} = 160 mA.
- Turn ON RF signal.

POWER OFF:

- Turn OFF RF signal.
- Decrease V_G to -1.2 V.
- Turn OFF V_{DD}.
- Turn OFF V_G.

Component	Value	Size	Part Number	Manufacturer
C1, C3, C5, C9	10 μF	1206	CL31B106KBHNNNE	SAMSUNG
C2, C4, C6, C8	0.1 μF	0603	06035C104KAT2A	AVX CORPORATION
C7	100 pF	0603	GRM1885C1H101GA01D	MURATA






MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**


Mini-Circuits

50Ω 17 to 31.5 GHz High Linearity Driver

CASE STYLE DRAWING



PCB Land Pattern




Suggested Layout,
Tolerance to be within ± 0.050 [0.002]

 DENOTES METALLIZATION

Weight: .042 Grams

Dimensions are in mm [Inches]. Tolerances: 2 Pl. ± 0.254 [0.01]; 3 Pl. ± 0.127 [0.005] mm [inches]

PRODUCT MARKING



Marking may contain other features or characters for internal lot control





Mini-Circuits

MMIC SURFACE MOUNT

Medium Power Amplifier **AVA-17303+**

50Ω 17 to 31.5 GHz High Linearity Driver

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DG983-4 Plastic package, exposed paddle, Lead Finish: Nickel-Palladium-Gold
RoHS Status	Compliant
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500, or 1000 devices 13" reels with 2000, 3000, or 4000 devices
Suggested Layout for PCB Design	PL-811
Evaluation Board	TB-AVA-17303C+
	Gerber File
Environmental Ratings	ENV08T1
Product Handling	The use of no-clean solder is recommended. This package cannot be subjected to aqueous wash.

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +5\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Psat Output	IP-3 Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
16.0	20.70	54.34	5.99	15.63	23.01	1.21	21.93	24.43	30.39	6.49
16.5	21.25	53.28	7.91	15.98	22.61	1.13	21.65	24.19	31.19	5.95
17.0	21.51	52.76	9.92	15.48	20.19	1.07	21.41	23.61	30.31	5.54
17.2	21.55	52.52	10.33	15.17	19.46	1.05	21.43	23.52	30.13	5.43
17.4	21.55	52.40	10.75	14.50	19.85	1.04	21.25	23.31	30.32	5.23
17.6	21.55	51.73	11.45	14.11	19.13	1.03	21.18	23.06	30.81	5.15
17.8	21.54	52.05	12.01	13.85	20.76	1.02	21.09	22.87	29.79	5.07
18.0	21.52	51.59	12.33	13.24	20.69	1.02	21.15	22.83	30.12	5.07
18.2	21.51	51.38	12.78	13.08	20.48	1.01	20.99	22.56	30.53	5.08
18.4	21.48	51.22	13.06	12.78	19.37	1.01	20.78	22.34	30.81	4.98
18.6	21.45	51.11	13.51	12.41	20.27	1.00	21.01	22.52	30.39	5.03
18.8	21.39	51.19	14.00	12.44	19.52	1.00	21.03	22.43	29.97	5.01
19.0	21.36	51.50	14.39	12.28	19.51	0.99	20.69	22.09	30.35	4.92
19.2	21.32	51.04	14.77	12.27	19.22	0.98	21.01	22.37	30.42	4.89
19.4	21.27	51.43	15.35	12.39	21.63	0.98	21.04	22.32	29.64	4.87
19.6	21.25	52.11	15.98	12.21	22.09	0.97	20.64	21.96	30.10	4.84
19.8	21.24	52.47	16.49	12.09	23.17	0.97	21.04	22.40	30.05	4.79
20.0	21.24	51.66	17.28	11.99	24.03	0.97	20.86	22.22	29.16	4.74
20.2	21.25	52.49	17.64	11.86	23.75	0.97	20.61	21.98	30.43	4.65
20.4	21.26	52.53	17.85	11.94	25.16	0.97	20.97	22.32	30.39	4.56
20.6	21.30	53.42	17.86	11.87	23.99	0.97	20.95	22.21	30.38	4.50
20.8	21.34	53.52	17.74	11.82	24.93	0.97	20.68	22.04	32.10	4.41
21.0	21.39	53.67	17.80	11.89	27.04	0.97	21.02	22.42	30.93	4.39
21.2	21.42	54.20	17.79	11.82	27.48	0.97	20.92	22.23	32.22	4.26
21.4	21.42	54.69	17.67	12.02	29.54	0.97	21.02	22.27	31.33	4.28
21.6	21.43	54.24	17.45	12.18	28.48	0.97	21.27	22.56	31.04	4.24
21.8	21.43	53.94	17.20	12.08	25.61	0.97	21.12	22.40	32.11	4.24
22.0	21.46	54.37	16.76	12.15	26.18	0.97	21.02	22.29	31.02	4.20
22.2	21.46	54.69	16.56	12.08	27.23	0.98	21.47	22.76	31.45	4.17
22.4	21.45	54.85	16.33	12.08	30.19	0.98	21.14	22.40	31.56	4.16
22.6	21.47	54.97	16.00	12.16	31.14	0.98	20.84	22.22	31.08	4.11
22.8	21.49	56.40	15.60	12.11	33.50	0.98	20.88	22.16	31.92	4.11
23.0	21.50	57.48	15.03	11.83	38.82	0.98	20.87	22.13	32.04	4.08
23.2	21.55	59.43	14.49	11.81	44.90	0.98	20.76	21.96	30.93	4.03
23.4	21.58	60.63	14.01	11.81	51.98	0.98	20.98	22.18	32.42	3.99
23.5	21.60	60.69	13.71	11.84	54.54	0.99	20.99	22.14	32.13	3.98
23.6	21.63	60.13	13.49	11.96	55.08	0.99	21.00	22.12	30.76	3.96
23.8	21.69	61.12	13.10	12.17	63.02	0.99	21.11	22.24	31.46	3.91
24.0	21.75	61.27	12.96	12.18	55.75	0.99	21.32	22.50	32.19	3.81
24.2	21.81	61.85	12.72	12.11	55.64	1.00	21.17	22.30	31.97	3.85
24.4	21.86	61.70	12.52	11.95	61.98	1.00	20.98	22.15	32.43	3.87
24.6	21.90	60.63	12.23	11.76	55.26	1.00	21.45	22.53	32.07	3.88
24.8	21.97	60.87	11.82	11.60	51.72	1.01	21.51	22.52	31.46	3.80
25.0	22.04	60.56	11.49	11.42	47.30	1.01	21.40	22.41	32.42	3.80
25.2	22.10	61.10	11.11	11.14	53.01	1.01	21.68	22.69	31.61	3.71
25.4	22.17	59.85	10.74	10.98	49.35	1.01	21.42	22.38	31.47	3.69
25.6	22.25	59.50	10.44	10.53	49.74	1.01	21.28	22.27	32.16	3.69
25.8	22.31	60.64	10.19	10.35	50.81	1.01	21.70	22.67	31.97	3.62
26.0	22.39	60.38	9.89	10.13	42.29	1.01	21.49	22.40	31.86	3.61
26.2	22.48	59.32	9.60	10.01	36.32	1.00	21.82	22.65	32.19	3.56
26.4	22.55	60.50	9.32	10.03	42.70	1.01	21.84	22.66	31.45	3.54
26.6	22.67	60.94	9.06	10.00	38.87	1.01	22.20	22.86	32.33	3.54
26.8	22.76	60.90	8.85	10.09	36.67	1.02	21.94	22.58	31.54	3.53
27.0	22.86	60.98	8.66	10.40	37.27	1.03	22.34	22.96	32.03	3.40
27.5	23.14	61.16	8.35	11.15	32.05	1.05	22.77	23.20	32.65	3.33
28.0	23.48	58.69	8.66	12.92	33.38	1.07	22.67	23.11	32.36	3.17
28.5	24.02	60.15	9.76	15.45	39.93	1.08	22.44	23.05	32.31	3.19
29.0	24.50	58.16	10.61	19.17	28.51	1.08	22.31	22.81	32.62	3.09
29.5	24.52	57.26	10.93	19.34	24.07	1.07	21.64	22.20	31.89	3.11
30.0	24.06	55.41	9.74	19.67	24.42	1.09	21.46	21.91	31.89	3.07
30.5	22.99	53.84	8.91	20.92	18.93	1.12	21.13	21.54	31.93	3.08
31.0	21.75	51.95	7.73	23.13	15.57	1.16	20.07	20.34	32.31	3.10
31.5	20.17	50.19	7.13	29.87	14.83	1.19	20.01	20.22	30.48	3.16
32.0	18.29	49.27	7.48	24.63	16.05	1.18	18.92	19.31	28.18	3.28
32.5	16.43	48.46	8.09	14.90	23.07	1.14				
33.0	14.58	48.71	9.06	10.93	28.28	1.07				
33.5	12.88	49.01	11.01	8.57	36.76	0.96				
34.0	10.94	49.46	13.19	7.17	42.47	0.87				

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions**Definitions:**

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Psat Output	IP-3 Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
16.0	20.25	55.11	6.38	18.69	22.37	1.21	23.79	25.60	32.35	6.65
16.5	20.74	53.47	8.46	19.35	19.76	1.12	23.19	25.17	32.34	6.07
17.0	20.95	52.71	10.63	18.57	19.59	1.07	23.06	25.10	31.97	5.70
17.2	20.97	52.72	11.11	18.10	20.25	1.05	22.86	24.82	31.79	5.58
17.4	20.96	52.39	11.59	17.18	19.06	1.04	22.72	24.59	32.16	5.44
17.6	20.94	52.12	12.36	16.58	17.61	1.03	22.70	24.35	32.22	5.32
17.8	20.92	52.21	13.00	16.25	18.51	1.02	22.64	24.30	30.85	5.26
18.0	20.89	52.36	13.38	15.47	18.98	1.02	22.48	24.02	31.43	5.20
18.2	20.86	52.01	13.92	15.25	19.22	1.01	22.31	23.87	31.82	5.21
18.4	20.82	51.39	14.22	14.83	17.87	1.01	22.51	24.07	32.11	5.17
18.6	20.77	51.68	14.71	14.33	18.31	1.00	22.53	23.94	31.59	5.19
18.8	20.70	51.31	15.33	14.32	17.90	0.99	22.19	23.68	31.57	5.17
19.0	20.65	51.36	15.66	14.05	19.59	0.99	22.49	23.95	31.63	5.08
19.2	20.60	51.54	15.96	13.90	18.91	0.98	22.54	23.84	31.82	5.12
19.4	20.54	52.10	16.33	13.83	19.37	0.98	22.11	23.46	30.84	5.04
19.6	20.50	52.16	16.81	13.54	20.92	0.97	22.44	23.77	31.32	5.06
19.8	20.48	52.25	17.13	13.39	22.06	0.97	22.31	23.54	31.16	4.97
20.0	20.46	52.72	17.41	13.17	20.17	0.97	22.03	23.36	30.34	4.86
20.2	20.46	52.56	17.42	12.95	21.88	0.97	22.30	23.61	31.70	4.80
20.4	20.45	53.02	17.23	12.96	21.14	0.97	22.27	23.46	31.29	4.71
20.6	20.47	52.71	17.09	12.73	22.19	0.97	22.04	23.35	31.29	4.63
20.8	20.49	53.26	16.73	12.66	24.06	0.97	22.42	23.82	32.90	4.59
21.0	20.51	53.86	16.51	12.69	25.03	0.97	22.42	23.62	32.09	4.56
21.2	20.51	54.40	16.33	12.54	25.04	0.97	22.40	23.70	33.18	4.51
21.4	20.49	54.45	16.23	12.71	27.42	0.97	22.65	23.96	32.59	4.44
21.6	20.47	54.26	16.07	12.79	26.25	0.98	22.52	23.55	32.04	4.43
21.8	20.45	53.54	15.86	12.63	23.94	0.97	22.42	23.46	33.04	4.35
22.0	20.44	54.26	15.45	12.69	26.73	0.97	22.91	23.99	32.09	4.35
22.2	20.42	55.05	15.30	12.74	29.30	0.97	22.75	23.59	32.53	4.32
22.4	20.39	55.04	15.11	12.62	27.43	0.97	22.50	23.36	32.50	4.29
22.6	20.38	55.74	14.83	12.66	29.93	0.98	22.43	23.41	32.14	4.35
22.8	20.35	55.66	14.54	12.68	30.54	0.98	22.53	23.36	32.99	4.29
23.0	20.33	57.38	14.03	12.51	39.18	0.98	22.34	23.25	32.72	4.28
23.2	20.37	58.51	13.61	12.41	46.26	0.98	22.45	23.36	32.03	4.21
23.4	20.39	60.19	13.16	12.09	52.16	0.98	22.43	23.23	33.62	4.19
23.5	20.41	60.45	12.91	12.12	49.53	0.98	22.44	23.16	32.92	4.18
23.6	20.42	60.89	12.72	12.22	52.66	0.98	22.62	23.25	31.72	4.14
23.8	20.48	61.34	12.35	12.38	59.33	0.99	22.81	23.66	32.51	4.10
24.0	20.55	61.36	12.24	12.37	58.66	0.99	22.64	23.36	32.89	4.11
24.2	20.63	61.31	12.04	12.25	57.68	1.00	22.56	23.20	32.89	4.05
24.4	20.69	61.38	11.88	12.05	55.34	1.01	22.97	23.58	33.87	4.02
24.6	20.74	60.88	11.61	11.82	49.58	1.01	23.04	23.47	32.82	4.05
24.8	20.82	60.81	11.23	11.62	50.52	1.01	22.94	23.39	32.87	3.99
25.0	20.88	60.47	10.93	11.37	45.09	1.00	23.18	23.66	33.08	4.02
25.2	20.94	61.02	10.61	11.29	52.04	1.00	22.94	23.35	32.38	3.97
25.4	21.03	60.89	10.30	11.07	50.24	1.01	22.80	23.26	32.70	3.93
25.6	21.11	60.03	10.03	10.57	49.09	1.00	23.13	23.57	33.05	3.88
25.8	21.20	61.00	9.81	10.25	44.89	1.00	22.93	23.22	33.37	3.88
26.0	21.28	60.49	9.55	9.95	41.32	1.00	23.21	23.48	33.25	3.81
26.2	21.39	60.24	9.28	9.71	36.45	1.00	23.22	23.50	33.37	3.78
26.4	21.49	59.53	9.03	9.64	38.56	1.01	23.46	23.63	32.39	3.75
26.6	21.62	59.61	8.79	9.54	44.60	1.00	23.24	23.45	33.22	3.78
26.8	21.75	61.77	8.57	9.59	49.84	1.01	23.64	23.82	32.31	3.74
27.0	21.88	59.70	8.41	9.77	36.02	1.03	24.11	24.07	32.95	3.71
27.5	22.18	58.61	8.14	10.36	36.85	1.04	24.06	24.00	33.31	3.55
28.0	22.63	58.58	8.49	11.52	28.94	1.06	23.96	24.01	33.34	3.45
28.5	23.33	61.09	9.48	13.28	33.95	1.07	23.79	24.02	33.17	3.41
29.0	23.94	59.73	10.33	15.61	34.82	1.07	23.39	23.64	33.78	3.37
29.5	24.10	57.22	10.59	17.32	26.22	1.07	23.09	23.46	33.57	3.43
30.0	23.79	55.26	9.46	16.75	21.57	1.09	22.97	23.10	33.75	3.39
30.5	22.84	53.03	8.66	16.47	20.10	1.12	21.90	21.94	33.17	3.44
31.0	21.67	51.53	7.54	17.40	17.10	1.15	21.88	21.95	34.33	3.48
31.5	20.12	49.22	7.06	21.04	16.22	1.17	20.90	21.03	33.41	3.54
32.0	18.27	48.70	7.47	33.11	18.58	1.16	21.11	20.37	30.99	3.52
32.5	16.44	49.15	8.12	18.53	22.14	1.14				
33.0	14.62	48.73	9.14	12.63	27.97	1.05				
33.5	12.93	49.64	11.11	9.69	34.29	0.96				
34.0	10.94	50.06	13.20	7.89	43.64	0.86				

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +7\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = $+25^\circ\text{C}$

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Psat Output	IP-3 Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
16.0	19.74	54.31	6.68	21.94	26.11	1.24	26.18	26.72	32.31	6.78
16.5	20.17	53.55	8.91	23.15	25.98	1.16	25.52	26.42	32.92	6.25
17.0	20.37	52.42	11.25	21.70	22.46	1.09	24.62	25.86	32.67	6.08
17.2	20.39	52.76	11.78	21.00	25.63	1.07	24.44	25.76	32.47	5.75
17.4	20.38	52.99	12.28	19.87	24.31	1.05	24.13	25.51	33.27	5.64
17.6	20.36	52.14	13.13	19.03	23.10	1.03	23.94	25.29	33.17	5.58
17.8	20.34	52.44	13.85	18.53	21.91	1.02	23.90	25.15	31.48	5.38
18.0	20.30	52.41	14.26	17.54	21.40	1.02	23.91	25.19	32.16	5.43
18.2	20.28	51.91	14.84	17.33	21.59	1.01	23.74	24.88	32.44	5.34
18.4	20.23	52.25	15.15	16.81	23.30	1.01	23.47	24.70	32.78	5.37
18.6	20.17	51.89	15.66	16.18	21.89	1.00	23.62	24.88	32.44	5.31
18.8	20.10	51.65	16.27	16.16	21.15	1.00	23.67	24.74	32.09	5.31
19.0	20.03	51.71	16.69	15.72	22.39	0.99	23.25	24.59	32.95	5.27
19.2	19.95	51.76	16.77	15.50	22.52	0.99	23.53	24.85	32.94	5.29
19.4	19.88	51.90	16.92	15.24	22.46	0.99	23.63	24.77	31.95	5.18
19.6	19.82	52.49	17.15	14.76	25.53	0.98	23.19	24.55	32.44	5.14
19.8	19.79	52.97	17.05	14.62	25.56	0.98	23.56	24.81	32.12	5.08
20.0	19.75	53.08	16.97	14.22	25.19	0.98	23.43	24.47	31.07	5.00
20.2	19.73	52.94	16.69	13.84	23.11	0.98	23.08	24.27	32.69	4.94
20.4	19.72	52.96	16.54	13.78	25.56	0.98	23.29	24.53	32.49	4.88
20.6	19.71	53.43	16.30	13.41	25.69	0.98	23.30	24.27	31.91	4.83
20.8	19.70	53.96	15.95	13.40	25.52	0.98	22.99	24.22	33.94	4.81
21.0	19.69	53.62	15.66	13.38	26.33	0.98	23.26	24.60	32.43	4.78
21.2	19.66	54.29	15.36	13.02	28.91	0.98	23.20	24.30	34.15	4.78
21.4	19.62	54.49	15.24	13.14	26.76	0.99	23.24	24.51	32.60	4.72
21.6	19.58	54.07	15.17	13.11	28.18	0.99	23.39	24.75	32.84	4.68
21.8	19.53	53.71	14.98	12.96	26.51	1.00	23.40	24.44	33.68	4.74
22.0	19.51	53.84	14.63	12.92	30.68	1.00	23.34	24.43	32.77	4.68
22.2	19.45	54.22	14.50	12.90	31.36	1.00	23.75	24.89	33.01	4.51
22.4	19.40	55.04	14.31	12.86	32.49	1.00	23.55	24.42	33.11	4.62
22.6	19.38	55.20	14.04	13.00	33.49	1.01	23.28	24.23	32.49	4.68
22.8	19.33	56.01	13.81	12.78	41.15	1.00	23.10	24.25	33.25	4.54
23.0	19.29	57.62	13.37	12.75	40.91	1.00	23.14	24.05	33.17	4.47
23.2	19.32	58.87	12.95	12.60	46.54	1.00	23.00	23.90	32.06	4.38
23.4	19.33	60.53	12.57	12.18	66.78	1.00	22.94	23.93	33.22	4.36
23.5	19.33	60.50	12.34	12.05	60.34	1.00	22.94	23.73	32.93	4.33
23.6	19.35	61.01	12.16	12.15	64.99	1.00	22.95	23.68	31.98	4.31
23.8	19.39	61.20	11.85	12.26	57.64	1.00	23.21	23.94	32.80	4.33
24.0	19.46	60.13	11.75	12.22	71.56	1.01	23.38	24.10	33.32	4.22
24.2	19.54	60.69	11.57	12.09	59.92	1.01	23.25	23.68	33.19	4.23
24.4	19.59	60.98	11.42	11.87	57.24	1.01	23.18	23.59	33.64	4.25
24.6	19.65	59.77	11.16	11.62	61.41	1.01	23.59	23.98	33.24	4.18
24.8	19.75	60.98	10.81	11.38	61.50	1.01	23.57	23.86	32.41	4.15
25.0	19.82	60.49	10.54	11.10	54.98	1.01	23.49	23.81	33.06	4.19
25.2	19.89	60.88	10.26	11.05	58.88	1.00	23.67	24.00	32.67	4.15
25.4	19.98	59.55	9.95	10.93	51.52	1.00	23.32	23.67	32.32	4.13
25.6	20.06	59.89	9.71	10.39	48.56	1.00	23.35	23.65	32.51	4.07
25.8	20.14	60.23	9.51	10.05	57.75	1.00	23.61	23.96	33.36	4.06
26.0	20.23	60.62	9.27	9.72	50.46	1.00	23.33	23.56	32.59	3.99
26.2	20.32	61.87	9.02	9.33	58.56	1.00	23.68	23.86	32.80	4.00
26.4	20.42	60.22	8.80	9.22	41.13	1.00	23.63	23.83	32.02	4.02
26.6	20.53	62.12	8.56	9.06	37.64	1.00	23.52	23.81	32.50	3.96
26.8	20.62	61.46	8.38	9.04	54.88	1.01	23.54	23.72	31.99	4.05
27.0	20.74	59.64	8.20	9.10	43.19	1.03	23.73	24.01	32.21	3.89
27.5	21.15	59.67	7.95	9.65	51.58	1.05	24.38	24.46	32.70	3.77
28.0	21.70	59.59	8.27	10.49	39.16	1.08	24.34	24.26	32.68	3.77
28.5	22.48	61.66	9.24	11.79	46.93	1.09	24.32	24.37	32.19	3.67
29.0	23.17	58.66	10.08	13.37	32.31	1.08	24.41	24.37	32.08	3.65
29.5	23.37	57.28	10.35	14.54	33.49	1.08	24.12	24.16	31.73	3.67
30.0	23.06	56.11	9.27	15.11	29.34	1.10	24.02	24.11	31.08	3.70
30.5	22.30	53.42	8.50	13.83	18.52	1.14	23.87	23.96	31.06	3.67
31.0	21.18	50.73	7.44	14.28	20.64	1.17	22.81	22.84	31.46	3.70
31.5	19.72	48.98	7.05	16.57	19.16	1.19	22.82	22.84	31.11	3.69
32.0	18.01	48.49	7.54	22.61	19.15	1.18	21.89	21.87	30.25	4.00
32.5	16.22	49.01	8.18	23.61	24.37	1.14				
33.0	14.41	49.00	9.24	14.48	31.47	1.09				
33.5	12.68	49.33	11.16	10.75	39.79	0.99				
34.0	10.64	49.76	13.26	8.58	56.06	0.89				

Typical Performance Data

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Psat Output	IP-3 Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
16.0	21.14	54.34	5.65	21.83	18.37	1.26	25.11	26.33	32.41	5.54
16.5	21.65	53.34	7.73	22.77	17.70	1.16	23.70	25.78	31.94	4.81
17.0	21.83	52.76	10.13	21.42	17.59	1.09	23.61	25.48	31.47	4.40
17.2	21.84	52.82	11.20	20.93	18.12	1.07	23.62	25.42	31.31	4.31
17.4	21.83	51.95	12.07	20.11	16.64	1.05	23.33	25.24	32.20	4.34
17.6	21.78	51.68	12.66	19.58	16.36	1.04	23.20	25.02	30.49	4.24
17.8	21.73	52.27	13.06	19.42	17.73	1.04	23.01	24.75	31.03	4.14
18.0	21.66	51.19	13.43	18.66	15.83	1.03	22.93	24.72	31.10	4.15
18.2	21.59	51.31	13.76	18.11	16.23	1.02	22.84	24.42	31.05	4.11
18.4	21.51	52.16	13.92	17.59	18.06	1.02	22.42	23.98	31.10	3.98
18.6	21.43	51.04	14.08	16.83	16.01	1.02	22.62	24.23	30.46	3.97
18.8	21.32	51.06	14.61	16.40	16.31	1.01	22.63	24.10	30.13	3.90
19.0	21.20	50.97	15.03	15.54	16.35	1.00	22.16	23.67	31.32	3.86
19.2	21.11	50.95	15.26	14.81	16.43	0.99	22.59	24.11	30.15	3.79
19.4	20.98	51.12	15.68	14.21	16.98	0.99	22.80	24.15	30.28	3.87
19.6	20.89	51.75	16.09	13.41	18.36	0.98	22.48	23.85	30.18	3.91
19.8	20.82	52.95	15.99	12.85	21.11	0.97	22.98	24.36	30.03	3.84
20.0	20.76	52.46	16.06	12.51	19.98	0.97	23.04	24.17	30.21	3.83
20.2	20.71	52.22	15.76	12.16	19.41	0.96	22.82	23.99	30.29	3.74
20.4	20.69	52.26	15.39	12.15	19.53	0.97	23.04	24.32	29.83	3.71
20.6	20.70	53.20	15.08	11.93	21.63	0.97	23.24	24.15	30.95	3.61
20.8	20.74	53.37	14.92	12.12	22.04	0.97	22.81	23.87	30.52	3.47
21.0	20.78	53.42	15.03	12.46	22.20	0.97	23.04	24.19	31.23	3.41
21.2	20.83	53.53	15.11	12.66	22.44	0.98	23.04	23.87	32.14	3.30
21.4	20.88	54.10	15.07	13.02	23.96	0.98	22.66	23.60	30.75	3.30
21.6	20.92	53.45	15.19	13.59	22.26	0.99	22.84	23.82	31.46	3.15
21.8	20.95	53.44	15.33	13.64	22.26	0.99	22.75	23.51	32.21	3.21
22.0	20.97	54.21	15.08	13.60	24.22	0.99	22.44	23.41	30.70	3.20
22.2	20.97	54.69	14.66	13.29	25.48	0.99	23.03	24.08	31.99	3.19
22.4	20.96	53.69	14.42	12.79	22.58	0.98	22.89	23.76	31.93	3.14
22.6	20.94	54.50	13.79	12.56	24.67	0.99	22.72	23.63	31.49	3.30
22.8	20.88	55.96	13.05	12.25	29.02	0.99	22.70	23.75	31.97	3.28
23.0	20.82	56.24	12.44	11.92	29.81	0.99	22.96	23.76	30.83	3.23
23.2	20.79	59.29	11.98	11.91	42.24	1.00	22.84	23.65	31.78	3.25
23.4	20.77	59.74	11.57	11.75	44.23	1.00	22.97	23.91	32.14	3.20
23.5	20.75	58.19	11.40	11.76	37.00	1.00	23.13	23.81	31.04	3.22
23.6	20.75	58.87	11.16	11.87	39.87	1.01	23.15	23.76	31.01	3.14
23.8	20.76	60.55	10.77	12.03	48.18	1.02	23.08	23.75	32.42	3.05
24.0	20.81	60.66	10.69	12.08	48.52	1.02	23.17	23.94	32.98	3.14
24.2	20.87	61.82	10.70	12.22	55.35	1.02	23.16	23.61	31.28	2.95
24.4	20.91	60.08	10.44	12.16	44.86	1.02	22.73	23.41	32.75	2.92
24.6	20.98	59.12	10.36	11.84	39.62	1.02	23.19	23.84	31.76	3.02
24.8	21.07	60.37	10.37	11.77	45.33	1.02	23.32	23.76	32.04	2.94
25.0	21.11	59.27	10.08	11.13	39.04	1.01	22.95	23.57	32.56	2.94
25.2	21.17	60.31	9.82	10.46	42.86	1.01	23.38	24.00	31.87	3.01
25.4	21.22	59.15	9.51	10.12	36.69	1.00	23.24	23.70	32.04	3.03
25.6	21.27	60.51	9.16	9.54	41.55	1.00	23.18	23.58	32.77	2.96
25.8	21.34	59.71	8.91	9.09	36.85	0.99	23.70	24.12	31.94	2.98
26.0	21.43	59.65	8.52	8.82	35.39	0.99	23.70	23.91	33.43	2.88
26.2	21.52	59.58	8.15	8.54	34.00	0.99	24.07	24.16	32.97	2.82
26.4	21.65	59.47	8.09	8.48	32.92	0.99	24.02	24.23	32.41	2.79
26.6	21.79	60.11	7.98	8.41	34.72	0.99	24.51	24.44	33.35	2.72
26.8	21.94	64.40	7.67	8.44	55.22	1.00	24.06	24.01	32.34	2.69
27.0	22.10	60.94	7.56	8.77	36.77	1.02	24.46	24.43	32.79	2.62
27.5	22.55	57.18	7.58	9.35	23.21	1.03	24.72	24.54	32.25	2.62
28.0	23.00	57.90	7.76	10.37	24.80	1.06	24.77	24.45	32.41	2.61
28.5	23.79	59.42	8.26	11.85	28.37	1.07	24.39	24.59	33.61	2.63
29.0	24.62	59.61	9.13	13.19	27.66	1.07	24.21	24.77	33.20	2.46
29.5	25.35	58.67	9.85	15.20	23.82	1.07	23.48	24.17	33.82	2.50
30.0	25.79	56.80	9.51	16.86	18.41	1.09	23.22	23.82	34.50	2.41
30.5	25.66	56.59	7.98	16.14	17.24	1.13	23.07	23.49	34.38	2.44
31.0	24.80	52.43	6.11	13.85	10.39	1.20	22.43	22.52	32.79	2.65
31.5	23.36	49.37	4.99	13.25	7.68	1.26	22.50	22.62	34.67	2.69
32.0	21.81	48.12	5.22	16.86	8.46	1.28	21.26	21.54	33.46	2.55
32.5	19.98	48.76	6.32	21.80	12.62	1.22				
33.0	18.08	48.65	8.08	14.84	16.65	1.12				
33.5	16.22	48.99	9.74	10.84	21.51	1.01				
34.0	14.30	49.00	10.84	9.08	26.41	0.95				

Typical Performance Data

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		1dB Comp. Output	Psat Output	IP-3 Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
16.0	18.36	54.51	5.85	16.01	25.45	1.23	21.30	23.94	30.63	7.60
16.5	18.90	53.16	7.44	16.18	22.64	1.15	21.04	23.55	30.55	6.92
17.0	19.19	52.42	9.15	16.11	21.50	1.09	20.67	22.85	30.15	6.52
17.2	19.26	52.68	9.80	15.74	22.32	1.07	20.70	22.79	30.42	6.40
17.4	19.30	51.86	10.35	15.55	20.48	1.06	20.48	22.54	30.70	6.30
17.6	19.30	51.70	10.70	15.08	20.20	1.05	20.46	22.36	29.95	6.19
17.8	19.29	51.94	10.83	14.67	20.77	1.04	20.49	22.32	30.18	6.16
18.0	19.27	51.96	11.01	14.23	20.85	1.04	20.60	22.43	30.34	6.08
18.2	19.25	51.20	11.14	13.64	19.07	1.03	20.51	22.23	30.28	6.09
18.4	19.25	51.36	11.34	13.46	19.48	1.02	20.35	22.10	30.74	6.01
18.6	19.22	50.59	11.64	13.19	17.92	1.01	20.56	22.32	30.17	6.01
18.8	19.17	51.69	11.95	12.88	20.42	1.01	20.61	22.24	29.77	5.95
19.0	19.14	51.25	12.49	12.74	19.59	1.00	20.27	21.98	30.94	5.92
19.2	19.11	50.79	13.15	12.61	18.71	0.99	20.62	22.27	30.22	5.88
19.4	19.07	51.48	13.62	12.48	20.38	0.98	20.65	22.21	29.79	5.84
19.6	19.06	51.95	14.27	12.38	21.62	0.98	20.26	21.86	29.81	5.71
19.8	19.06	51.84	14.97	12.25	21.37	0.97	20.65	22.20	30.25	5.72
20.0	19.05	51.84	15.68	12.24	21.45	0.96	20.47	21.97	30.56	5.60
20.2	19.06	52.04	16.47	12.20	21.98	0.96	20.17	21.70	30.57	5.57
20.4	19.07	52.19	16.96	12.10	22.29	0.96	20.49	22.02	30.64	5.45
20.6	19.09	52.63	17.63	12.08	23.42	0.95	20.47	21.92	31.12	5.36
20.8	19.11	52.96	18.25	11.99	24.25	0.95	20.26	21.74	30.57	5.33
21.0	19.12	53.72	18.33	11.81	26.30	0.95	20.64	22.14	30.88	5.28
21.2	19.12	53.05	18.64	11.86	24.33	0.95	20.57	22.01	31.47	5.21
21.4	19.12	54.13	18.91	11.79	27.53	0.95	20.56	22.01	30.86	5.15
21.6	19.12	53.88	18.61	11.77	26.68	0.95	20.83	22.30	31.20	5.18
21.8	19.13	54.22	18.26	11.82	27.66	0.95	20.68	22.10	31.21	5.22
22.0	19.11	54.01	18.17	11.70	26.95	0.95	20.58	21.99	30.20	5.13
22.2	19.11	54.38	17.70	11.72	28.08	0.95	21.08	22.51	31.07	5.13
22.4	19.09	54.37	17.01	11.76	27.98	0.95	20.83	22.22	30.85	5.06
22.6	19.07	54.74	16.57	11.75	29.13	0.95	20.59	21.95	31.60	5.13
22.8	19.05	55.68	16.02	11.91	32.49	0.96	20.52	21.90	32.15	5.06
23.0	19.04	58.41	15.62	11.96	44.41	0.96	20.62	21.96	30.39	4.96
23.2	19.04	58.86	15.17	11.93	46.56	0.96	20.48	21.76	31.47	4.98
23.4	19.04	60.02	14.44	12.13	53.05	0.97	20.63	21.92	31.37	4.92
23.5	19.05	60.36	14.27	12.16	55.10	0.97	20.62	21.88	30.12	4.95
23.6	19.06	59.64	14.14	12.14	50.59	0.98	20.68	21.94	30.64	4.91
23.8	19.11	60.97	13.82	12.06	58.52	0.98	20.86	22.09	32.14	4.83
24.0	19.16	62.03	13.38	12.11	65.54	0.98	21.14	22.38	32.20	4.87
24.2	19.21	61.80	13.18	11.98	63.42	0.98	21.02	22.20	31.57	4.82
24.4	19.27	60.73	13.03	11.84	55.54	0.98	20.94	22.12	32.33	4.71
24.6	19.35	60.80	12.79	11.66	55.26	0.98	21.40	22.57	31.16	4.82
24.8	19.44	60.77	12.55	11.30	54.20	0.98	21.44	22.55	32.47	4.70
25.0	19.52	61.16	12.30	11.12	55.94	0.98	21.31	22.43	32.46	4.66
25.2	19.60	60.47	12.13	10.80	50.83	0.97	21.53	22.65	32.49	4.70
25.4	19.67	61.49	11.85	10.37	56.06	0.97	21.26	22.31	32.88	4.63
25.6	19.76	61.94	11.48	10.10	57.84	0.97	21.10	22.12	32.89	4.55
25.8	19.85	58.71	11.03	9.75	38.90	0.96	21.40	22.41	32.32	4.56
26.0	19.95	59.79	10.74	9.42	43.02	0.96	21.22	22.13	33.85	4.51
26.2	20.06	59.42	10.40	9.27	40.43	0.96	21.53	22.38	32.45	4.50
26.4	20.17	60.64	10.00	9.04	45.43	0.96	21.56	22.39	32.71	4.49
26.6	20.29	61.20	9.72	9.04	47.70	0.97	21.88	22.59	33.84	4.42
26.8	20.44	64.63	9.42	9.06	69.58	0.97	21.66	22.33	32.04	4.45
27.0	20.57	57.86	9.30	9.07	31.50	0.98	22.04	22.68	33.69	4.36
27.5	21.00	56.60	9.33	9.95	27.09	1.00	22.52	22.97	32.67	4.20
28.0	21.50	60.77	9.95	11.74	44.30	1.03	22.36	22.86	32.92	4.18
28.5	22.24	60.50	11.57	14.53	42.79	1.03	22.01	22.62	33.73	4.19
29.0	22.76	59.91	13.06	18.21	40.07	1.03	21.84	22.38	33.12	3.89
29.5	22.86	57.43	13.52	20.06	30.65	1.03	21.29	21.77	33.67	4.16
30.0	22.32	56.99	12.36	19.12	30.97	1.04	21.09	21.55	35.46	4.09
30.5	21.26	54.74	10.34	19.41	26.28	1.08	20.66	21.10	34.84	4.17
31.0	19.82	53.46	8.76	21.93	25.91	1.13	19.50	19.87	35.33	4.17
31.5	18.23	50.89	7.89	37.18	22.63	1.16	19.32	19.74	33.18	4.37
32.0	16.46	49.11	7.98	20.45	22.72	1.15	18.40	18.85	31.52	4.49
32.5	14.64	49.97	9.04	13.45	31.41	1.07				
33.0	12.77	48.36	10.59	9.85	31.84	0.97				
33.5	10.89	49.67	12.94	7.79	44.45	0.88				
34.0	8.92	50.82	16.14	6.78	61.70	0.81				

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = $+25^{\circ}\text{C}$

Power	P_{OUT} (@17 GHz)	P_{OUT} (@24 GHz)	P_{OUT} (@30 GHz)	P_{OUT} (@32 GHz)	I_{DD} (@17 GHz)	I_{DD} (@24 GHz)	I_{DD} (@30 GHz)	I_{DD} (@32 GHz)	Gain (@17 GHz)	Gain (@24 GHz)	Gain (@30 GHz)	Gain (@32 GHz)
(dBm)	(dBm)	(dBm)	(dBm)	(dBm)	(mA)	(mA)	(mA)	(mA)	(dBm)	(dBm)	(dBm)	(dBm)
-10	8.6	8.91	10.76	5.68	162.54	162.46	162.67	160.74	20.92	20.80	23.82	18.25
-9	9.62	9.92	11.78	6.65	163.1	163.04	163.47	160.91	20.92	20.79	23.83	18.23
-8	10.61	10.93	12.79	7.63	163.82	163.75	164.49	161.18	20.91	20.80	23.84	18.22
-7	11.61	11.94	13.8	8.61	164.72	164.64	165.83	161.54	20.91	20.80	23.86	18.21
-6	12.61	12.93	14.83	9.61	165.91	165.81	167.56	162	20.90	20.79	23.88	18.21
-5	13.62	13.92	15.86	10.6	167.42	167.28	169.78	162.62	20.90	20.78	23.91	18.21
-4	14.61	14.91	16.91	11.59	169.36	169.16	172.6	163.56	20.89	20.78	23.94	18.20
-3	15.6	15.91	18	12.58	171.8	171.5	176.11	164.87	20.88	20.78	24.02	18.19
-2	16.59	16.92	19.13	13.59	174.9	174.39	180.58	166.71	20.88	20.80	24.13	18.17
-1	17.6	17.95	20.29	14.57	178.77	177.93	186.19	168.98	20.89	20.85	24.24	18.15
0	18.63	19	21.4	15.54	183.48	182.17	193.31	171.92	20.92	20.91	24.33	18.12
1	19.67	20.16	22.34	16.5	189.13	187.75	203.02	175.82	20.95	20.98	24.23	18.09
1.2	19.88	20.38	22.49	16.69	190.39	188.87	205.35	176.78	20.95	20.99	24.17	18.09
1.4	20.08	20.58	22.62	16.88	191.68	190.01	207.77	177.79	20.94	20.99	24.10	18.08
1.6	20.28	20.78	22.74	17.08	193.01	191.17	210.3	178.85	20.93	20.99	24.02	18.08
1.8	20.53	20.97	22.84	17.27	194.72	192.36	212.9	179.97	20.91	20.98	23.92	18.07
2	20.73	21.16	22.93	17.47	196.11	193.6	215.61	181.18	20.89	20.96	23.81	18.07
2.2	20.91	21.33	23.01	17.67	197.54	194.86	218.37	182.44	20.85	20.93	23.69	18.07
2.4	21.09	21.5	23.08	17.87	198.94	196.16	221.19	183.75	20.81	20.90	23.56	18.07
2.6	21.27	21.66	23.14	18.08	200.35	197.5	224.06	185.11	20.77	20.86	23.42	18.08
2.8	21.44	21.81	23.19	18.28	201.7	198.87	226.99	186.55	20.72	20.80	23.27	18.08
3	21.59	21.95	23.24	18.48	203.04	200.29	229.92	188.1	20.66	20.74	23.11	18.09
3.2	21.74	22.08	23.28	18.69	204.31	201.79	232.78	189.75	20.60	20.66	22.96	18.10
3.4	21.89	22.2	23.31	18.9	205.6	203.34	235.5	191.49	20.52	20.59	22.79	18.11
3.6	22.03	22.31	23.35	19.11	206.89	204.98	238.06	193.36	20.44	20.50	22.55	18.12
3.8	22.16	22.42	23.38	19.31	208.25	206.71	240.43	195.37	20.36	20.40	22.32	18.12
4	22.29	22.51	23.41	19.51	209.67	208.53	242.6	197.48	20.27	20.29	21.77	18.12
4.2	22.41	22.61		19.7	211.17	210.47		199.7	20.18	20.17		18.11
4.4	22.53	22.69		19.88	212.81	212.51		201.97	20.10	20.05		18.09
4.6	22.64	22.77		20.04	214.58	214.69		203.89	20.01	19.93		18.05
4.8	22.75	22.85		20.17	216.45	216.97		205.61	19.92	19.80		17.99
5	22.86	22.92		20.29	218.44	219.39		207.3	19.83	19.67		17.91
5.2	22.97	22.99		20.38	220.52	221.93		208.96	19.73	19.54		17.81
5.4	23.07	23.05		20.46	222.69	224.63		210.58	19.63	19.47		17.69
5.6	23.17	23.11		20.53	224.95	227.47		212.13	19.53	19.22		17.56
5.8	23.26			20.66	227.29			213.67	19.42			17.48
6	23.35			20.70	229.69			215.32	19.31			17.32
6.2				20.73				216.91				17.15
6.4				20.69				217.86				16.93
6.6				20.91				219.35				17.01
6.8				20.71				221.31				16.59
7												16.41
7.2												16.08

Typical Performance Data

TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$ @ Temperature = $+25^{\circ}\text{C}$







FREQ	OIP3 @ 0 dBm/Tone	OIP3 @ +3 dBm/Tone	OIP3 @ +6 dBm/Tone	OIP3 @ +9 dBm/Tone	OIP3 @ +12 dBm/Tone
(GHz)	(dBm)	(dBm)	(dBm)	(dBm)	(dBm)
16.0	30.77	31.92	32.35	32.35	31.61
17.0	30.68	31.62	31.97	32.01	31.40
18.0	30.81	31.27	31.43	31.33	30.75
19.0	30.79	31.41	31.63	31.59	30.92
20.0	29.90	30.09	30.34	29.68	28.74
21.0	31.17	32.08	32.09	31.41	30.27
22.0	31.30	32.26	32.09	31.60	30.18
23.0	32.34	33.20	32.72	32.21	30.88
24.0	33.07	32.94	32.89	32.71	31.51
25.0	32.10	32.80	33.08	32.22	30.66
26.0	32.51	33.34	33.25	32.04	29.89
27.0	31.02	32.37	32.95	32.04	30.07
28.0	31.86	32.52	33.34	32.56	30.68
29.0	32.43	34.98	33.78	32.64	30.50
30.0	31.28	33.37	33.75	32.23	30.11
31.0	31.57	34.08	34.33	33.87	31.98
32.0	30.74	30.88	30.99	33.81	30.79
P _{OUT} /Tone (dBm)	@17 GHz	@20 GHz	@24 GHz	@27 GHz	@30 GHz
0	30.68	29.90	33.07	31.02	31.28
3	31.62	30.09	32.94	32.37	33.37
6	31.97	30.34	32.89	32.95	33.75
9	32.01	29.68	32.71	32.04	32.23
12	31.40	28.74	31.51	30.07	30.11

Typical Performance Data







TEST CONDITIONS: $V_{DD} = +6\text{ V}$, $I_{DD} = 160\text{ mA}$, 200 mA , 250 mA @ Temperature = $+25^\circ\text{C}$

FREQ	Gain @ 160 mA	Gain @ 200 mA	Gain @ 250 mA	1dB Comp. Output @ 160 mA	1dB Comp. Output @ 200 mA	1dB Comp. Output @ 250 mA	OIP3 @ 160 mA	OIP3 @ 200 mA	OIP3 @ 250 mA	Noise Figure @ 160 mA	Noise Figure @ 200 mA	Noise Figure @ 250 mA
(GHz)	(dB)	(dB)	(dB)	(dBm)	(dBm)	(dBm)	(dBm)	(dBm)	(dBm)	(dB)	(dB)	(dB)
16.0	20.25	21.09	21.64	25.44	25.00	24.65	32.35	30.77	28.41	6.65	6.77	6.97
16.5	20.74	21.53	22.07	23.79	24.36	24.12	32.34	31.16	28.83	6.07	6.21	6.41
17.0	20.95	21.70	22.22	23.19	23.70	23.53	31.97	30.65	28.20	5.70	5.78	6.04
17.2	20.97	21.70	22.22	23.06	23.55	23.46	31.79	30.44	28.15	5.58	5.60	5.89
17.4	20.96	21.67	22.18	22.86	23.43	23.20	32.16	30.78	28.43	5.44	5.51	5.77
17.6	20.94	21.64	22.14	22.72	23.22	23.04	32.22	31.10	28.56	5.32	5.38	5.67
17.8	20.92	21.60	22.09	22.70	23.07	22.99	30.85	29.86	27.44	5.26	5.34	5.57
18.0	20.89	21.56	22.04	22.64	23.13	23.23	31.43	30.20	27.63	5.20	5.32	5.55
18.2	20.86	21.52	21.99	22.48	22.90	22.99	31.82	30.45	28.02	5.21	5.27	5.54
18.4	20.82	21.46	21.92	22.31	22.77	22.88	32.11	30.64	28.01	5.17	5.26	5.49
18.6	20.77	21.39	21.84	22.51	23.05	23.26	31.59	29.92	27.33	5.19	5.29	5.51
18.8	20.70	21.30	21.74	22.53	23.00	23.17	31.57	30.16	27.52	5.17	5.27	5.45
19.0	20.65	21.24	21.66	22.19	22.76	22.96	31.63	30.52	27.88	5.08	5.23	5.45
19.2	20.60	21.16	21.58	22.49	23.12	23.34	31.82	30.19	27.50	5.12	5.20	5.44
19.4	20.54	21.07	21.48	22.54	23.15	23.29	30.84	29.70	27.02	5.04	5.19	5.42
19.6	20.50	21.01	21.41	22.11	22.76	22.90	31.32	29.70	26.92	5.06	5.20	5.36
19.8	20.48	20.98	21.36	22.44	23.12	23.38	31.16	29.61	26.90	4.97	5.06	5.31
20.0	20.46	20.94	21.31	22.31	22.87	23.10	30.34	28.97	26.24	4.86	5.02	5.20
20.2	20.46	20.93	21.29	22.03	22.58	22.79	31.70	29.84	27.10	4.80	4.92	5.14
20.4	20.45	20.90	21.26	22.30	22.86	23.09	31.29	29.96	27.05	4.71	4.86	5.09
20.6	20.47	20.92	21.27	22.27	22.72	22.86	31.29	29.43	26.78	4.63	4.81	4.96
20.8	20.49	20.93	21.26	22.04	22.58	22.76	32.90	31.08	28.15	4.59	4.73	4.98
21.0	20.51	20.93	21.26	22.42	23.00	23.16	32.09	30.11	27.07	4.56	4.66	4.95
21.2	20.51	20.92	21.24	22.42	22.85	22.94	33.18	31.47	28.54	4.51	4.61	4.85
21.4	20.49	20.88	21.19	22.40	22.93	23.13	32.59	30.18	27.13	4.44	4.65	4.83
21.6	20.47	20.86	21.16	22.65	23.16	23.34	32.04	30.28	27.32	4.43	4.57	4.80
21.8	20.45	20.82	21.12	22.52	22.89	23.07	33.04	31.30	28.32	4.35	4.60	4.86
22.0	20.44	20.80	21.09	22.42	22.74	22.86	32.09	30.02	26.97	4.35	4.53	4.75
22.2	20.42	20.76	21.04	22.91	23.25	23.40	32.53	30.57	27.36	4.32	4.52	4.66
22.4	20.39	20.72	20.99	22.75	22.99	23.14	32.50	30.65	27.62	4.29	4.47	4.72
22.6	20.38	20.71	20.97	22.50	22.83	22.91	32.14	29.95	26.66	4.35	4.52	4.70
22.8	20.35	20.67	20.94	22.43	22.78	22.92	32.99	30.90	27.66	4.29	4.45	4.73
23.0	20.33	20.65	20.92	22.53	22.67	22.83	32.72	30.71	27.33	4.28	4.41	4.67
23.2	20.37	20.67	20.93	22.34	22.54	22.70	32.03	29.59	26.54	4.21	4.39	4.66
23.4	20.39	20.69	20.94	22.45	22.63	22.80	33.62	31.01	27.66	4.19	4.35	4.61
23.5	20.41	20.70	20.96	22.43	22.57	22.71	32.92	30.61	27.26	4.18	4.36	4.61
23.6	20.42	20.72	20.97	22.44	22.52	22.66	31.72	29.06	25.79	4.14	4.35	4.59
23.8	20.48	20.77	21.02	22.62	22.80	22.88	32.51	30.15	27.00	4.10	4.27	4.59
24.0	20.55	20.84	21.07	22.81	22.98	23.07	32.89	31.06	27.71	4.11	4.25	4.51
24.2	20.63	20.92	21.15	22.64	22.81	22.88	32.89	30.33	26.86	4.05	4.22	4.51
24.4	20.69	20.97	21.20	22.56	22.74	22.77	33.87	31.29	27.95	4.02	4.23	4.53
24.6	20.74	21.03	21.27	22.97	23.15	23.26	32.82	31.01	27.54	4.05	4.23	4.52
24.8	20.82	21.13	21.36	23.04	23.19	23.23	32.87	30.25	26.69	3.99	4.19	4.48
25.0	20.88	21.19	21.43	22.94	23.11	23.05	33.08	30.92	27.37	4.02	4.15	4.54
25.2	20.94	21.26	21.51	23.18	23.37	23.26	32.38	29.96	26.62	3.97	4.15	4.44
25.4	21.03	21.35	21.61	22.94	23.09	22.92	32.70	29.90	26.60	3.93	4.10	4.38
25.6	21.11	21.43	21.68	22.80	22.93	22.86	33.05	30.96	27.36	3.88	4.10	4.36
25.8	21.20	21.51	21.78	23.13	23.27	23.30	33.37	30.57	26.95	3.88	4.07	4.38
26.0	21.28	21.61	21.90	22.93	22.98	23.07	33.25	30.29	26.84	3.81	4.00	4.35
26.2	21.39	21.72	22.02	23.21	23.32	23.41	33.37	30.90	27.25	3.78	3.97	4.31
26.4	21.49	21.84	22.15	23.22	23.30	23.35	32.39	29.47	26.01	3.75	4.02	4.33
26.6	21.62	21.98	22.29	23.46	23.53	23.56	33.22	30.83	27.02	3.78	3.96	4.21
26.8	21.75	22.12	22.46	23.24	23.35	23.36	32.31	30.11	26.48	3.74	4.02	4.27
27.0	21.88	22.26	22.61	23.64	23.74	23.68	32.95	30.30	26.64	3.71	3.88	4.24
27.5	22.18	22.61	23.02	24.11	24.21	24.05	33.31	30.71	27.31	3.55	3.85	4.10
28.0	22.63	23.13	23.60	24.06	24.07	24.04	33.34	30.66	27.02	3.45	3.73	4.06
28.5	23.33	23.94	24.52	23.96	23.81	23.80	33.17	30.31	26.56	3.41	3.71	4.03
29.0	23.94	24.69	25.39	23.79	23.72	23.75	33.78	30.44	26.39	3.37	3.68	3.95
29.5	24.10	25.07	26.03	23.39	23.21	23.22	33.57	29.81	25.90	3.43	3.66	4.00
30.0	23.79	24.96	26.17	23.09	23.16	23.16	33.75	29.31	25.44	3.39	3.68	4.01
30.5	22.84	24.13	25.52	22.97	22.90	22.85	33.17	29.11	24.79	3.44	3.71	4.08
31.0	21.67	23.02	24.49	21.90	21.81	21.79	34.33	30.07	25.40	3.48	3.79	4.12
31.5	20.12	21.45	22.91	21.88	21.83	21.85	33.41	29.99	25.29	3.54	3.79	4.20
32.0	18.27	19.52	20.89	20.90	20.85	20.94	30.99	29.31	24.75	3.52	3.79	4.26
32.5	16.44	17.61	18.90									
33.0	14.62	15.74	16.95									
33.5	12.93	14.00	15.14									
34.0	10.94	11.94	12.99									







Typical Performance Curves








Typical Performance Curves






Typical Performance Curves





Typical Performance Curves




Typical Performance Curves





Suggested Layout,
Tolerance to be within ± 0.050 [0.002]



BOTTOM VIEW

NOTES:

1.  DENOTES METALLIZATION

Weight: .042 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl. ± 0.254 [0.01]; 3 Pl. ± 0.127 [0.005] mm [Inches]

Notes:

1. Case material: Plastic.
2. Termination finish: PPF (NiPdAu Plating 0.5 μm /0.02 μm /0.05 μm)




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F68



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-024214	NEW RELEASE	01/22/25	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR DG983-4 CASE STYLE

COMPONENT	SIZE
C2,C4,C6,C7,C8	0603
C1,C3,C5,C9	1206

63X ϕ .012 PTH,
PLUGGED WITH NON-CONDUCTIVE
EPOXY & CAPPED WITH COPPER

COPLANAR WAVEGUIDE:
.0195 $\pm$.002 TRACE WIDTH &
.0227 $\pm$.002 GAP, 2 PL.
(SEE NOTE 1)




NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010".
COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-AVA-17303+.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN ITG	01/16/25
TOLERANCES ON:	CHECKED GF	01/16/25
2 PL DECIMALS $\pm$	APPROVED IL	01/16/25
3 PL DECIMALS $\pm$.005		
ANGLES $\pm$		
FRACTIONS $\pm$		

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



Mini-Circuits®



13 Neptune Avenue
Brooklyn NY 11235

PL, DG983-4, TB-AVA-17303(C)+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-811	OR
FILE:	98PL811	SCALE: 5:1	SHEET: 1 OF 1

Evaluation Board and Circuit

SEE DETAIL "A"



DETAIL "A"
LOCATION OF INTERCONNECTOR
AND UNITS COMPONENTS
(SCALE 3:1)



SCHEMATIC DIAGRAM

Component	Size	Value	Part Number	Manufacturer
C1,C3,C5,C9	1206	10uF	B55-109-106K+	Samsung
C2,C4,C6,C8	0603	0.1uF	B55-18-104+	AVX
C7	0603	100pF	B55-19-101G+	Murata

Notes:

1. 2.4mm Female Connectors.
2. PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.010 inch



Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215