



SUPER WIDEBAND, LOW NOISE

Monolithic Amplifier Die **AVA-0233LN-D+**

50Ω 2 to 30 GHz

THE BIG DEAL

- Super Wideband & Flat Gain, 16.8±0.3 dB @ 2 to 30 GHz
- Outstanding Match for Signal Chain Integration, >15 dB
- Low Noise Figure (NF<2 dB), and High OIP3 (OIP3 > +26 dBm at Mid Band)

APPLICATIONS

- Test & Instrument
- Military & Space
- Fixed Satellite
- Mobile



+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

SEE ORDERING INFORMATION ON THE LAST PAGE

PRODUCT OVERVIEW

AVA-0233LN-D+ is a GaAs, pHEMT, MMIC Distributed Amplifier Die that operates from 2 to 30GHz. The amplifier typically provides 16.8 dB Gain and 2.0 dB Noise Figure, +14 dBm Output Power at 1 dB Gain Compression, +25.7 dBm OIP3. The amplifier is well-matched to 50 Ohm at both input and output. AVA-0223LN-D+ is a self-biased single positive supply device with $V_{DD} = +5 V$ and $I_{DD} = 65.2 mA$ Typical.

KEY FEATURES

Feature	Advantages
Super-Wide Bandwidth with Flat Gain • 16.8 ±0.3 dB over 3 - 20 GHz	General Purpose Wideband Amplifier with adjustable gain vs. control voltage is suitable for wide variety of applications.
Low Noise Figure Typical: • <3 dB from 3.5 to 27.5 GHz • <2 dB from 5 to 20 GHz	Enables lower system noise figure performance.
High Output IP3 • +27 dBm from 2 to 20 GHz • +25 dBm from 20 to 30 GHz	Easy to integrate into signal chain.
Excellent Wideband In/Out Return Loss • >15 dB from 2 to 30 GHz	
Unpackaged Die	Enables user to integrate it directly into hybrids

REV. A
 ECO-021862
 AVA-0233LN-D+
 MCLNY
 240529





SUPER WIDEBAND, LOW NOISE

Monolithic Amplifier Die **AVA-0233LN-D+**

50Ω 2 to 30 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	V _{DD} = +5 V & V _C = Open			Units
		Min.	Typ.	Max.	
Frequency range		2000		30000	MHz
Gain	2000		16.8		dB
	10000		16.8		
	20000		17.0		
	30000		16.7		
Input Return loss	2000		26.0		dB
	10000		16.0		
	20000		17.8		
	30000		22.7		
Output Return loss	2000		13.3		dB
	10000		23.5		
	20000		20.1		
	30000		26.8		
P1dB	2000		+16.5		dBm
	10000		+15.0		
	20000		+13.5		
	30000		+12.3		
OIP3 (P _{OUT} = 0 dBm/Tone)	2000		+28.3		dBm
	10000		+26.8		
	20000		+25.7		
	30000		+22.0		
Noise Figure	2000		4.1		dB
	10000		1.4		
	20000		2.2		
	30000		3.9		
Device operating voltage (V _{DD})		+4.75	+5	+5.25	V
Device operating current (I _{DD})			65.2	92	mA
Device current variation vs. temperature ²			-10		μA/°C
Device current variation vs voltage ³			0.0128		mA/mV
Thermal resistance, junction-to-ground Lead			14.7		°C/W

1. Measured on Mini-Circuits Characterization Test Board MB-089. See Characterization Test & Application Circuit (Fig. 2)
2. Device Current Variation vs. Temperature = (Current in mA at 85°C - Current in mA at -45°C)/130°C
3. Device Current Variation vs. Voltage = (Current in mA at 5.25V - Current in mA at 4.75V) / (5.25V-4.75V)*1000 mA/mV

ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating temperature (ground lead)	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Junction Temperature	150°C ⁵
Total power dissipation	1.55 W
Input power (CW)	+20 dBm
DC voltage at VC	-2.5 V to 3.0 V
DC voltage at V _{DD}	+8 V

4. Permanent damage may occur if any of those limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.
5. T_j = 85°C + (V_{DD})*(I_{DD})*θ(JC) = 90°C
Nominal Operating Condition with T_j = 90°C will ensure MTTF > 428Years

FIG 1. GAIN VS. CONTROL VOLTAGE (VC)




FIG 1. When VC = Open, the measured VC = 2.2V typical. For RF Performance at different VC, please see View Data and Graph.






SUPER WIDEBAND, LOW NOISE

Monolithic Amplifier Die **AVA-0233LN-D+**


50Ω 2 to 30 GHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Pad Number	Description
1	RF IN
4	RF OUT
7	V _{DD}
8	V _C
2, 3, 5, 6, 9 & Bottom of Die	GROUND

BONDING PAD POSITION



Dimension in μm

L1	L2	L3	L4	L5	H1	H2
102	300	500	3021	3120	246	396

H3	H4	H5	H6	H7	H8
546	732	882	1032	1398	1500

Thickness	Die size	Pad size 1,4	Pad size 2, 3, 5, 6, 7, 8 & 9
100	3120 x 1500	93 x 113	93 x 93

CHARACTERIZATION, APPLICATION CIRCUIT & ASSEMBLY DRAWING




Fig 2. Characterization, Application Circuit & Assembly Drawing
 Note: This block diagram is used for characterization. (DUT was soldered on test board of Mini-Circuits Characterization Test Board MB-089). Gain, Return Loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:
 1. V_{DD} = +5 V, V_C = Open
 2. Gain and Return Loss: P_{IN} = -25dBm
 3. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Component#	Size	Value	Manufacturer	P/N
C1, C2	22x22mil	100pF	Macon Inc	MA4M3100
C3, C4	0402	0.1uF	Murata	GRM155R71C04KA88D

ASSEMBLY PROCEDURE

- Storage**
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
- ESD**
MMIC PHEMT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
- Die Handling and Attachment**
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
- Wire Bonding**
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.





SUPER WIDEBAND, LOW NOISE

Monolithic Amplifier Die **AVA-0233LN-D+**

50Ω 2 to 30 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.

Performance Data	Data Table								
	Swept Graphs								
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)								
Case Style	Die								
Die Ordering and packaging information	<table border="0"> <tr> <td>Quantity, Package</td> <td>Model No.</td> </tr> <tr> <td>Small, Gel - Pak: 5,10,50,100 KGD*</td> <td>AVA-0233LN-DG+</td> </tr> <tr> <td>Medium†, Partial wafer: KGD*<464</td> <td>AVA-0233LN-DP+</td> </tr> <tr> <td>Full Wafer</td> <td>AVA-0233LN-DF+</td> </tr> </table>	Quantity, Package	Model No.	Small, Gel - Pak: 5,10,50,100 KGD*	AVA-0233LN-DG+	Medium†, Partial wafer: KGD*<464	AVA-0233LN-DP+	Full Wafer	AVA-0233LN-DF+
	Quantity, Package	Model No.							
Small, Gel - Pak: 5,10,50,100 KGD*	AVA-0233LN-DG+								
Medium†, Partial wafer: KGD*<464	AVA-0233LN-DP+								
Full Wafer	AVA-0233LN-DF+								
	†Available upon request contact sales representative Refer to AN-60-067								
Environmental Ratings	ENV80								

*Known Good Die ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ADDITIONAL NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, VC=Open, Id = 66mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.77	48.36	24.88	13.39	18.78	0.96	29.03	16.49	3.78
2500	16.73	49.80	26.08	14.23	22.69	0.96	28.00	16.04	3.49
3000	16.65	50.74	27.93	14.53	25.88	0.97	28.26	15.74	3.17
3500	16.61	49.30	26.92	14.31	22.14	0.96	26.83	15.57	2.96
4000	16.84	48.28	25.83	14.39	19.33	0.97	26.87	15.58	2.81
4500	16.90	47.41	26.66	14.36	17.50	0.96	27.20	15.57	2.56
5000	16.97	47.50	26.33	14.50	17.70	0.97	27.43	15.66	2.22
5500	16.97	46.98	26.20	14.51	16.79	0.97	26.19	15.67	1.87
6000	17.03	46.64	23.97	14.49	16.15	0.97	27.55	15.55	1.88
6500	17.03	46.67	23.16	14.45	16.32	0.97	27.54	15.63	1.72
7000	17.05	46.74	23.11	14.70	16.57	0.97	27.22	15.61	1.63
7500	17.07	47.11	23.54	15.61	17.48	0.98	27.33	15.53	1.54
8000	17.07	47.18	23.41	17.42	17.90	0.99	26.81	15.48	1.46
8500	17.05	47.13	21.99	20.85	18.09	1.00	26.75	15.55	1.34
9000	17.00	46.62	19.98	28.70	17.29	1.01	27.67	15.54	1.37
9500	16.92	46.16	18.20	34.54	16.59	1.01	26.90	15.29	1.29
10000	16.83	45.08	17.08	23.63	14.77	1.01	26.72	14.98	1.27
10500	16.74	44.79	16.59	20.13	14.42	1.01	27.27	15.00	1.31
11000	16.68	43.82	16.63	18.95	13.02	1.01	26.66	14.91	1.29
11500	16.62	42.89	17.08	19.22	11.86	1.01	26.00	14.81	1.40
12000	16.60	42.00	17.82	20.49	10.84	1.01	26.53	14.72	1.42
12500	16.58	41.51	18.60	21.42	10.35	1.01	26.23	14.76	1.52
13000	16.56	40.72	19.14	20.38	9.52	1.00	26.47	14.67	1.55
13500	16.53	39.91	19.40	18.30	8.70	0.99	25.64	14.54	1.64
14000	16.52	39.67	19.88	16.67	8.47	0.99	26.44	14.45	1.71
14500	16.52	39.34	20.30	15.86	8.15	0.98	26.60	14.47	1.71
15000	16.54	38.93	20.50	15.82	7.78	0.98	26.37	14.49	1.79
15500	16.61	38.53	20.14	16.68	7.45	0.99	26.74	14.39	1.81
16000	16.67	38.04	19.28	18.30	7.06	0.99	25.74	14.38	1.85
16500	16.74	37.62	18.32	20.65	6.72	1.00	25.70	14.29	1.80
17000	16.79	37.20	17.61	23.52	6.42	1.01	26.19	14.28	1.80
17500	16.81	36.80	17.21	23.07	6.13	1.01	25.79	13.96	1.85
18000	16.81	36.35	17.19	20.75	5.82	1.00	25.92	13.89	1.93
18500	16.83	35.77	17.46	18.85	5.45	1.00	26.17	13.82	2.02
19000	16.85	35.21	18.03	18.21	5.11	0.99	25.91	13.86	1.98
19500	16.90	34.63	18.29	18.73	4.79	0.99	25.86	13.79	2.02
20000	16.95	34.06	17.87	20.80	4.51	1.00	25.87	13.54	1.96
20500	16.96	33.57	16.91	23.62	4.28	1.00	24.75	13.38	2.02
21000	16.93	33.15	15.98	23.60	4.09	1.01	24.76	13.32	2.07
21500	16.89	32.96	15.70	20.94	4.01	1.01	25.36	13.31	2.17
22000	16.90	32.60	16.11	19.11	3.85	1.00	24.86	13.21	2.23
22500	16.94	32.22	17.12	18.45	3.70	0.99	24.59	13.20	2.36
23000	17.00	31.84	18.47	18.96	3.57	0.98	24.65	13.12	2.36
23500	17.05	31.44	19.60	21.14	3.45	0.98	24.61	13.09	2.45
24000	17.09	31.18	20.52	25.79	3.37	0.98	24.64	13.04	2.54
24500	17.09	30.84	21.40	25.39	3.26	0.98	23.84	12.79	2.55
25000	17.04	30.56	21.69	20.46	3.17	0.97	24.22	12.71	2.68
25500	16.98	30.28	21.56	17.46	3.07	0.96	24.02	12.64	2.78
26000	16.92	30.00	21.04	16.01	2.99	0.95	24.14	12.47	2.84
26500	16.90	29.61	20.01	15.82	2.87	0.95	24.07	12.44	2.91
27000	16.89	29.12	18.72	16.03	2.73	0.96	22.90	12.35	2.92
27500	16.86	28.90	17.88	16.61	2.68	0.96	23.07	12.01	3.05
28000	16.84	28.39	17.38	17.54	2.56	0.96	22.69	12.08	3.30
28500	16.81	28.22	17.75	18.49	2.54	0.96	23.72	12.15	3.33
29000	16.77	27.87	18.39	20.68	2.49	0.96	21.50	12.13	3.40
29500	16.66	27.57	19.77	24.15	2.47	0.96	22.67	12.28	3.57
30000	16.59	27.56	22.43	31.48	2.52	0.96	21.92	12.37	3.71

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, VC=Open, Id = 64mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.75	48.67	25.01	13.43	19.52	0.96	29.21	16.23	3.88
2500	16.71	49.59	26.22	14.30	22.19	0.97	27.81	15.79	3.47
3000	16.63	49.55	28.08	14.59	22.62	0.97	27.39	15.56	3.20
3500	16.60	49.12	26.98	14.37	21.73	0.96	26.73	15.35	3.05
4000	16.82	48.19	25.93	14.46	19.17	0.97	27.09	15.36	2.81
4500	16.89	47.76	26.71	14.45	18.26	0.97	26.88	15.35	2.59
5000	16.95	47.05	26.42	14.58	16.85	0.97	27.29	15.44	2.24
5500	16.96	47.23	26.27	14.59	17.32	0.97	25.97	15.41	1.92
6000	17.02	46.33	24.07	14.58	15.61	0.97	27.36	15.24	1.87
6500	17.02	46.58	23.26	14.54	16.19	0.97	27.27	15.37	1.74
7000	17.04	46.81	23.19	14.81	16.74	0.97	27.33	15.35	1.67
7500	17.06	46.55	23.63	15.72	16.43	0.98	27.36	15.28	1.51
8000	17.06	46.98	23.48	17.54	17.52	0.99	26.51	15.22	1.40
8500	17.04	46.89	22.10	21.02	17.62	1.00	26.44	15.32	1.34
9000	16.99	46.56	20.06	28.89	17.19	1.01	26.66	15.28	1.31
9500	16.91	45.82	18.25	34.11	15.98	1.01	26.89	15.03	1.26
10000	16.83	45.29	17.13	23.59	15.14	1.01	26.14	14.76	1.29
10500	16.73	44.77	16.65	20.15	14.41	1.01	26.92	14.75	1.32
11000	16.67	43.84	16.66	19.00	13.07	1.01	26.63	14.67	1.27
11500	16.62	42.77	17.11	19.29	11.71	1.01	25.69	14.56	1.35
12000	16.59	41.90	17.85	20.60	10.72	1.01	26.58	14.47	1.40
12500	16.57	41.26	18.65	21.56	10.07	1.01	26.24	14.55	1.52
13000	16.56	40.71	19.16	20.53	9.51	1.00	26.53	14.42	1.52
13500	16.53	40.25	19.43	18.41	9.04	0.99	25.60	14.30	1.63
14000	16.52	39.77	19.91	16.78	8.57	0.99	26.41	14.23	1.67
14500	16.52	39.20	20.33	15.94	8.03	0.98	26.51	14.22	1.69
15000	16.55	38.88	20.56	15.94	7.75	0.98	25.93	14.24	1.76
15500	16.62	38.58	20.24	16.81	7.50	0.99	26.89	14.10	1.81
16000	16.68	38.10	19.36	18.47	7.11	0.99	25.85	14.09	1.79
16500	16.75	37.69	18.44	20.86	6.78	1.00	25.66	13.99	1.81
17000	16.80	37.16	17.73	23.84	6.39	1.01	26.45	13.99	1.86
17500	16.81	36.66	17.31	23.36	6.03	1.01	25.38	13.66	1.85
18000	16.82	36.22	17.24	20.94	5.73	1.00	25.51	13.60	2.01
18500	16.84	35.71	17.55	19.00	5.41	1.00	25.96	13.53	1.92
19000	16.86	35.23	18.09	18.33	5.12	0.99	25.48	13.58	1.98
19500	16.92	34.56	18.36	18.86	4.75	0.99	25.64	13.48	2.02
20000	16.96	34.08	17.91	21.04	4.52	1.00	25.08	13.26	1.94
20500	16.98	33.55	16.96	23.85	4.27	1.00	24.92	13.11	1.99
21000	16.94	33.22	16.01	23.84	4.12	1.01	24.50	13.09	1.94
21500	16.91	32.86	15.71	21.10	3.96	1.01	24.86	13.07	2.19
22000	16.92	32.45	16.09	19.24	3.78	1.00	24.24	12.97	2.24
22500	16.96	32.05	17.10	18.58	3.62	0.99	24.48	12.93	2.31
23000	17.02	31.73	18.49	19.09	3.52	0.98	24.72	12.85	2.38
23500	17.08	31.30	19.64	21.26	3.38	0.98	24.26	12.82	2.42
24000	17.13	31.01	20.64	26.08	3.30	0.98	24.29	12.74	2.51
24500	17.12	30.68	21.66	25.71	3.19	0.98	23.54	12.52	2.52
25000	17.08	30.42	21.89	20.63	3.11	0.97	23.74	12.41	2.62
25500	17.02	30.10	21.73	17.57	3.00	0.96	23.95	12.37	2.75
26000	16.96	29.74	21.11	16.10	2.89	0.95	23.93	12.21	2.78
26500	16.94	29.51	20.07	15.92	2.83	0.95	23.70	12.14	2.92
27000	16.93	29.11	18.83	16.11	2.72	0.96	22.55	12.05	2.97
27500	16.90	28.74	17.91	16.68	2.62	0.96	22.83	11.75	3.05
28000	16.90	28.37	17.33	17.54	2.54	0.96	21.96	11.75	3.13
28500	16.87	28.06	17.58	18.46	2.48	0.96	23.23	11.85	3.30
29000	16.83	27.72	18.30	20.53	2.43	0.96	21.54	11.80	3.43
29500	16.74	27.46	19.53	23.74	2.42	0.96	22.22	11.89	3.55
30000	16.68	27.44	22.07	31.32	2.46	0.96	21.56	11.98	3.61

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, VC=Open, Id = 66mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.79	48.64	24.80	13.33	19.34	0.96	29.00	16.68	3.85
2500	16.75	50.75	25.90	14.19	25.23	0.96	28.25	16.26	3.48
3000	16.66	50.29	27.78	14.46	24.50	0.97	27.67	15.95	3.24
3500	16.63	48.97	26.84	14.24	21.26	0.96	27.06	15.71	3.03
4000	16.85	48.76	25.84	14.32	20.39	0.96	27.43	15.76	2.78
4500	16.91	47.78	26.62	14.28	18.21	0.96	27.27	15.75	2.59
5000	16.98	47.90	26.21	14.39	18.50	0.97	27.73	15.87	2.16
5500	16.98	47.22	26.08	14.40	17.23	0.97	26.37	15.85	1.91
6000	17.04	46.73	23.86	14.38	16.27	0.97	27.76	15.77	1.80
6500	17.04	47.19	23.06	14.34	17.28	0.97	27.31	15.84	1.74
7000	17.06	47.18	23.04	14.60	17.38	0.97	27.42	15.82	1.63
7500	17.08	47.41	23.43	15.49	18.06	0.98	27.94	15.75	1.54
8000	17.08	47.57	23.29	17.28	18.68	0.99	26.83	15.71	1.41
8500	17.06	47.15	21.91	20.69	18.09	1.00	26.56	15.76	1.34
9000	17.01	47.00	19.90	28.47	18.02	1.01	27.41	15.75	1.30
9500	16.93	46.13	18.12	34.90	16.51	1.01	27.15	15.50	1.24
10000	16.84	45.34	17.03	23.61	15.20	1.01	26.69	15.24	1.29
10500	16.74	44.48	16.54	20.06	13.90	1.01	27.28	15.21	1.32
11000	16.68	43.71	16.60	18.86	12.86	1.01	26.92	15.12	1.28
11500	16.62	42.88	17.04	19.13	11.84	1.01	25.81	15.05	1.37
12000	16.60	42.03	17.81	20.37	10.88	1.01	26.95	14.92	1.41
12500	16.58	41.27	18.58	21.29	10.06	1.00	26.75	15.00	1.49
13000	16.56	40.75	19.12	20.28	9.54	1.00	27.02	14.87	1.52
13500	16.53	39.91	19.40	18.21	8.69	0.99	25.91	14.75	1.60
14000	16.51	39.76	19.86	16.58	8.56	0.99	26.32	14.69	1.63
14500	16.51	39.39	20.28	15.73	8.20	0.98	26.73	14.71	1.64
15000	16.54	38.94	20.46	15.70	7.79	0.98	26.53	14.73	1.77
15500	16.61	38.65	20.08	16.54	7.56	0.98	27.11	14.64	1.85
16000	16.66	38.15	19.17	18.15	7.14	0.99	26.12	14.67	1.84
16500	16.73	37.90	18.22	20.44	6.94	1.00	26.93	14.57	1.80
17000	16.79	37.28	17.50	23.23	6.48	1.01	26.64	14.56	1.86
17500	16.80	36.71	17.11	22.82	6.07	1.01	25.77	14.25	1.90
18000	16.81	36.37	17.08	20.54	5.83	1.00	25.95	14.15	1.98
18500	16.82	35.98	17.39	18.70	5.58	1.00	26.48	14.07	2.00
19000	16.84	35.30	17.97	18.04	5.16	0.99	26.24	14.06	2.02
19500	16.89	34.78	18.22	18.57	4.88	0.99	26.06	13.99	1.97
20000	16.94	34.12	17.79	20.68	4.54	1.00	26.13	13.77	2.02
20500	16.95	33.73	16.86	23.42	4.36	1.01	25.39	13.62	1.98
21000	16.92	33.26	15.96	23.40	4.15	1.01	24.96	13.55	2.12
21500	16.87	32.96	15.71	20.81	4.01	1.01	25.53	13.54	2.17
22000	16.88	32.60	16.12	18.97	3.85	1.00	24.71	13.44	2.21
22500	16.91	32.26	17.17	18.31	3.72	0.99	24.92	13.42	2.35
23000	16.97	31.94	18.52	18.85	3.62	0.98	24.89	13.35	2.35
23500	17.02	31.59	19.54	21.03	3.51	0.98	25.09	13.35	2.46
24000	17.06	31.33	20.32	25.56	3.44	0.98	25.13	13.27	2.53
24500	17.05	30.99	21.17	25.03	3.32	0.98	24.28	13.09	2.57
25000	17.01	30.65	21.44	20.28	3.21	0.97	24.53	12.98	2.74
25500	16.94	30.46	21.40	17.32	3.15	0.96	23.83	12.94	2.77
26000	16.88	30.11	20.90	15.90	3.03	0.96	24.13	12.77	2.87
26500	16.86	29.78	19.90	15.74	2.93	0.96	23.95	12.66	2.92
27000	16.84	29.43	18.68	15.97	2.83	0.96	22.83	12.60	2.90
27500	16.81	28.97	17.89	16.58	2.71	0.96	23.13	12.26	3.10
28000	16.79	28.64	17.41	17.52	2.64	0.97	23.00	12.37	3.20
28500	16.75	28.31	17.77	18.50	2.58	0.96	23.31	12.43	3.35
29000	16.71	28.13	18.62	20.71	2.58	0.97	21.57	12.41	3.40
29500	16.59	27.83	19.95	24.34	2.56	0.97	22.97	12.57	3.54
30000	16.51	27.74	22.76	32.15	2.59	0.96	22.10	12.76	3.67

MMIC Amplifier Die

AVA-0233LN-D+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, VC=Open, Id = 66mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	17.44	48.78	24.72	13.32	18.23	0.96	29.26	16.56	3.14
2500	17.41	50.74	25.60	14.20	23.35	0.96	28.35	16.08	2.54
3000	17.32	51.64	27.87	14.48	26.53	0.97	27.80	15.72	2.59
3500	17.29	49.65	27.58	14.27	21.32	0.96	27.01	15.50	2.39
4000	17.54	49.76	26.82	14.55	21.18	0.97	26.80	15.55	2.17
4500	17.61	48.45	27.95	14.62	18.22	0.97	27.01	15.55	1.95
5000	17.67	48.13	26.46	14.76	17.57	0.97	27.58	15.67	1.62
5500	17.68	47.91	25.76	14.67	17.24	0.97	26.21	15.64	1.33
6000	17.75	47.20	23.52	14.52	15.84	0.97	27.55	15.57	1.29
6500	17.75	47.52	22.73	14.36	16.54	0.97	27.60	15.57	1.20
7000	17.79	47.58	22.67	14.56	16.73	0.97	27.55	15.60	1.11
7500	17.82	47.93	23.21	15.29	17.60	0.97	28.20	15.54	0.94
8000	17.83	47.88	23.52	16.83	17.73	0.98	27.33	15.46	0.91
8500	17.83	47.75	22.53	19.74	17.72	0.99	26.56	15.57	0.81
9000	17.80	46.93	20.37	26.33	16.35	1.01	27.32	15.58	0.75
9500	17.73	46.50	18.19	36.33	15.70	1.01	27.12	15.30	0.71
10000	17.65	45.56	16.78	23.38	14.19	1.02	27.22	15.00	0.73
10500	17.55	44.81	16.02	19.47	13.10	1.01	27.11	15.02	0.76
11000	17.49	44.03	15.85	18.23	12.06	1.01	27.05	14.90	0.79
11500	17.44	42.93	16.29	18.48	10.78	1.01	26.05	14.81	0.72
12000	17.44	42.26	17.14	20.29	10.11	1.01	27.21	14.70	0.79
12500	17.43	41.42	18.14	22.03	9.28	1.01	26.74	14.79	0.89
13000	17.42	40.80	18.84	20.76	8.70	1.00	26.90	14.66	0.93
13500	17.38	40.18	19.10	18.04	8.12	0.99	26.34	14.56	0.94
14000	17.36	40.05	19.31	16.18	8.01	0.98	26.75	14.49	0.99
14500	17.36	39.58	19.60	15.45	7.58	0.98	26.86	14.50	1.03
15000	17.39	39.20	19.84	15.40	7.25	0.98	26.60	14.52	1.04
15500	17.47	38.75	19.96	16.19	6.90	0.98	27.10	14.47	1.06
16000	17.54	38.29	19.35	17.45	6.56	0.99	26.44	14.49	1.10
16500	17.62	37.93	18.68	19.03	6.29	1.00	26.86	14.42	1.12
17000	17.69	37.48	18.10	21.90	5.98	1.00	27.40	14.41	1.15
17500	17.73	37.07	17.14	23.68	5.70	1.01	26.28	14.11	1.19
18000	17.74	36.52	16.67	21.70	5.34	1.01	25.99	14.04	1.23
18500	17.75	36.10	16.47	18.95	5.07	1.00	26.30	13.96	1.21
19000	17.76	35.40	16.67	17.06	4.66	0.99	26.16	13.93	1.25
19500	17.81	35.03	17.37	16.21	4.46	0.98	26.60	13.85	1.25
20000	17.91	34.13	17.86	17.99	4.05	0.99	26.55	13.63	1.25
20500	17.98	33.78	17.20	22.79	3.91	1.00	25.31	13.51	1.22
21000	17.94	33.40	15.30	24.19	3.75	1.01	25.74	13.44	1.27
21500	17.86	33.17	14.47	19.49	3.63	1.01	25.80	13.43	1.32
22000	17.84	32.80	14.60	17.28	3.48	1.00	25.17	13.29	1.37
22500	17.90	32.40	15.87	16.66	3.34	0.99	25.35	13.30	1.48
23000	18.00	32.00	17.54	17.95	3.23	0.98	25.30	13.26	1.53
23500	18.09	31.74	19.89	20.60	3.18	0.98	25.27	13.29	1.60
24000	18.15	31.40	22.24	23.66	3.08	0.97	25.05	13.22	1.56
24500	18.14	31.10	23.18	21.45	2.98	0.97	24.48	13.00	1.70
25000	18.13	30.84	21.98	21.18	2.91	0.97	24.65	12.98	1.77
25500	18.10	30.48	20.75	19.21	2.80	0.96	24.68	12.91	1.85
26000	18.02	30.26	19.44	15.96	2.71	0.95	24.89	12.72	1.89
26500	17.99	29.93	18.66	14.38	2.61	0.94	24.76	12.60	1.93
27000	18.00	29.48	18.42	13.89	2.48	0.93	23.18	12.57	2.00
27500	18.04	29.02	18.05	15.06	2.37	0.94	23.50	12.25	2.05
28000	18.07	28.57	16.17	17.76	2.27	0.96	23.20	12.33	2.10
28500	18.02	28.24	15.91	17.86	2.21	0.96	23.53	12.36	2.16
29000	17.98	28.00	17.00	17.31	2.18	0.95	22.12	12.23	2.29
29500	17.91	27.88	19.09	18.21	2.21	0.94	23.66	12.29	2.43
30000	17.89	27.67	22.86	25.53	2.22	0.95	22.41	12.59	2.51



MMIC Amplifier Die

AVA-0233LN-D+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, VC=Open, Id = 64mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	17.42	48.73	24.87	13.34	18.16	0.96	29.00	16.29	3.09
2500	17.40	50.45	25.75	14.23	22.64	0.96	28.27	15.85	2.77
3000	17.31	51.02	28.04	14.50	24.75	0.97	27.37	15.50	2.57
3500	17.27	49.29	27.71	14.30	20.51	0.96	26.80	15.24	2.34
4000	17.53	49.26	26.88	14.59	20.02	0.97	27.20	15.33	2.13
4500	17.60	48.51	28.05	14.67	18.36	0.97	26.89	15.29	1.96
5000	17.66	47.88	26.67	14.80	17.11	0.97	27.52	15.37	1.70
5500	17.67	47.89	25.91	14.72	17.22	0.97	26.10	15.38	1.31
6000	17.74	46.98	23.61	14.56	15.47	0.97	27.19	15.23	1.26
6500	17.75	47.51	22.85	14.41	16.53	0.97	27.24	15.31	1.19
7000	17.78	47.53	22.75	14.62	16.66	0.97	26.90	15.31	1.10
7500	17.81	47.62	23.30	15.35	17.00	0.97	27.56	15.24	0.96
8000	17.83	47.87	23.62	16.88	17.72	0.98	26.77	15.16	0.88
8500	17.83	47.57	22.66	19.80	17.36	0.99	26.53	15.28	0.81
9000	17.80	46.91	20.44	26.35	16.31	1.01	27.54	15.28	0.76
9500	17.73	46.22	18.25	35.80	15.22	1.01	26.92	15.01	0.70
10000	17.65	45.73	16.79	23.32	14.46	1.02	26.82	14.74	0.71
10500	17.55	44.98	16.06	19.49	13.36	1.01	27.00	14.74	0.72
11000	17.50	44.12	15.85	18.27	12.19	1.01	26.86	14.61	0.75
11500	17.45	43.03	16.30	18.53	10.90	1.01	26.05	14.53	0.72
12000	17.44	42.21	17.14	20.38	10.04	1.01	26.93	14.46	0.79
12500	17.44	41.34	18.17	22.14	9.20	1.01	26.62	14.54	0.90
13000	17.42	40.98	18.84	20.85	8.89	1.00	26.48	14.41	0.90
13500	17.39	40.16	19.09	18.09	8.10	0.99	25.56	14.31	0.95
14000	17.37	39.90	19.28	16.21	7.86	0.99	26.91	14.24	1.01
14500	17.37	39.50	19.60	15.50	7.51	0.98	26.66	14.24	1.05
15000	17.40	39.19	19.85	15.46	7.24	0.98	26.23	14.24	1.11
15500	17.48	38.70	20.05	16.27	6.86	0.98	27.20	14.13	1.04
16000	17.55	38.40	19.49	17.54	6.63	0.99	25.73	14.15	1.09
16500	17.63	37.93	18.85	19.11	6.29	1.00	26.23	14.08	1.11
17000	17.71	37.24	18.24	22.02	5.81	1.00	25.95	14.07	1.09
17500	17.74	36.97	17.26	23.88	5.63	1.01	25.63	13.71	1.16
18000	17.76	36.47	16.76	21.88	5.30	1.01	26.09	13.70	1.17
18500	17.77	35.99	16.49	19.02	5.00	1.00	26.10	13.63	1.20
19000	17.78	35.57	16.68	17.09	4.74	0.99	25.77	13.64	1.23
19500	17.83	34.93	17.39	16.23	4.40	0.98	26.32	13.57	1.22
20000	17.93	34.23	17.96	17.99	4.09	0.99	26.17	13.34	1.22
20500	18.00	33.85	17.26	22.94	3.93	1.00	25.17	13.18	1.23
21000	17.96	33.30	15.30	24.34	3.70	1.01	25.10	13.12	1.27
21500	17.89	33.02	14.43	19.56	3.56	1.01	26.05	13.11	1.33
22000	17.87	32.75	14.55	17.33	3.44	1.00	24.42	13.01	1.38
22500	17.93	32.40	15.80	16.70	3.33	0.99	25.50	12.98	1.46
23000	18.03	31.98	17.49	17.98	3.21	0.98	24.95	12.95	1.52
23500	18.13	31.64	19.97	20.67	3.13	0.98	25.24	12.97	1.53
24000	18.19	31.35	22.57	23.76	3.05	0.97	24.87	12.87	1.59
24500	18.19	31.01	23.66	21.54	2.94	0.97	24.16	12.65	1.62
25000	18.18	30.71	22.34	21.39	2.86	0.97	24.30	12.63	1.71
25500	18.15	30.45	21.01	19.44	2.77	0.96	24.22	12.56	1.81
26000	18.07	30.14	19.57	16.03	2.67	0.95	24.23	12.34	1.88
26500	18.04	29.82	18.71	14.41	2.56	0.94	24.05	12.25	1.90
27000	18.05	29.41	18.42	13.87	2.45	0.93	22.89	12.23	1.94
27500	18.10	28.95	18.11	15.12	2.34	0.94	23.10	11.90	2.01
28000	18.13	28.56	16.24	17.86	2.26	0.96	23.06	11.95	2.00
28500	18.09	28.03	15.78	17.82	2.14	0.96	22.93	11.98	2.18
29000	18.06	27.83	16.80	17.17	2.13	0.95	21.55	11.82	2.29
29500	17.99	27.59	18.83	17.95	2.12	0.94	22.55	11.92	2.42
30000	18.00	27.57	22.29	24.95	2.17	0.94	21.89	12.11	2.47



MMIC Amplifier Die

AVA-0233LN-D+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, VC=Open, Id = 66mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	17.46	48.97	24.58	13.30	18.61	0.96	29.88	16.86	3.13
2500	17.43	50.80	25.45	14.18	23.48	0.96	28.13	16.37	2.82
3000	17.34	50.10	27.61	14.45	22.17	0.97	28.39	15.97	2.63
3500	17.30	49.60	27.50	14.25	21.17	0.96	27.15	15.75	2.41
4000	17.55	49.17	26.70	14.51	19.76	0.97	27.39	15.83	2.17
4500	17.62	48.68	27.83	14.58	18.67	0.97	27.82	15.84	1.97
5000	17.68	47.85	26.33	14.71	17.00	0.97	28.30	15.95	1.61
5500	17.68	48.10	25.58	14.63	17.61	0.97	26.63	15.93	1.32
6000	17.75	47.44	23.40	14.46	16.26	0.97	28.12	15.86	1.27
6500	17.75	48.01	22.66	14.31	17.47	0.97	27.93	15.89	1.19
7000	17.79	47.84	22.60	14.51	17.23	0.97	27.45	15.85	1.11
7500	17.82	47.98	23.13	15.25	17.70	0.97	28.40	15.82	1.03
8000	17.83	48.43	23.44	16.79	18.88	0.98	27.43	15.80	0.95
8500	17.82	47.84	22.40	19.70	17.92	0.99	27.23	15.87	0.83
9000	17.80	47.66	20.27	26.32	17.78	1.01	28.00	15.87	0.82
9500	17.73	46.66	18.14	36.83	16.01	1.01	27.90	15.63	0.79
10000	17.64	45.75	16.74	23.44	14.51	1.02	27.04	15.33	0.77
10500	17.55	45.01	16.01	19.48	13.42	1.01	27.77	15.31	0.77
11000	17.48	43.95	15.84	18.19	11.96	1.01	27.21	15.22	0.78
11500	17.44	43.13	16.29	18.43	11.03	1.01	26.49	15.09	0.84
12000	17.42	42.11	17.12	20.22	9.95	1.01	27.18	14.99	0.85
12500	17.42	41.48	18.11	21.92	9.35	1.01	27.50	15.07	0.91
13000	17.41	40.98	18.79	20.71	8.90	1.00	26.99	14.94	0.95
13500	17.37	40.28	19.10	18.01	8.23	0.99	26.19	14.88	0.99
14000	17.35	39.97	19.33	16.14	7.94	0.98	27.17	14.79	1.09
14500	17.35	39.71	19.63	15.38	7.70	0.98	27.56	14.83	1.04
15000	17.38	39.27	19.83	15.31	7.33	0.98	26.76	14.82	1.10
15500	17.45	38.77	19.85	16.08	6.93	0.98	27.45	14.78	1.12
16000	17.52	38.45	19.22	17.37	6.69	0.99	26.79	14.83	1.19
16500	17.60	37.90	18.53	19.00	6.28	1.00	27.14	14.76	1.15
17000	17.67	37.55	17.91	21.82	6.04	1.00	27.43	14.75	1.19
17500	17.70	37.16	17.00	23.39	5.77	1.01	26.49	14.46	1.24
18000	17.72	36.63	16.59	21.49	5.41	1.01	26.81	14.42	1.26
18500	17.72	36.07	16.43	18.84	5.06	1.00	27.49	14.30	1.28
19000	17.74	35.50	16.68	17.02	4.73	0.99	26.50	14.27	1.34
19500	17.79	35.11	17.34	16.28	4.51	0.99	27.15	14.15	1.32
20000	17.89	34.42	17.77	18.04	4.19	0.99	26.19	13.96	1.30
20500	17.95	33.78	17.08	22.58	3.92	1.00	25.91	13.81	1.27
21000	17.91	33.46	15.32	23.99	3.78	1.01	25.60	13.74	1.29
21500	17.83	33.14	14.53	19.58	3.64	1.01	26.36	13.77	1.39
22000	17.81	32.89	14.73	17.30	3.52	1.00	25.25	13.66	1.45
22500	17.86	32.50	15.99	16.67	3.39	0.99	25.48	13.67	1.56
23000	17.95	32.17	17.64	17.86	3.31	0.98	26.01	13.60	1.61
23500	18.04	31.82	19.78	20.43	3.22	0.98	25.49	13.66	1.68
24000	18.10	31.53	21.84	23.54	3.14	0.98	25.27	13.55	1.68
24500	18.09	31.24	22.70	21.55	3.04	0.97	25.03	13.36	1.75
25000	18.08	30.99	21.65	20.96	2.97	0.97	24.84	13.34	1.84
25500	18.04	30.70	20.55	18.96	2.88	0.97	24.94	13.27	1.92
26000	17.96	30.34	19.34	15.91	2.75	0.95	25.04	13.09	1.97
26500	17.93	29.99	18.62	14.42	2.64	0.94	24.66	12.93	2.03
27000	17.94	29.58	18.31	13.92	2.52	0.94	23.50	12.97	2.08
27500	17.97	29.10	17.97	15.09	2.41	0.94	23.90	12.61	2.16
28000	18.00	28.83	16.26	17.63	2.35	0.96	23.82	12.70	2.12
28500	17.95	28.49	16.05	17.83	2.29	0.96	23.46	12.76	2.24
29000	17.90	28.24	17.21	17.55	2.26	0.95	22.41	12.63	2.41
29500	17.81	27.99	19.47	18.73	2.26	0.95	23.61	12.75	2.53
30000	17.78	27.87	23.49	26.34	2.30	0.95	22.44	13.06	2.57



MMIC Amplifier Die

AVA-0233LN-D+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, VC=Open, Id = 64mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.17	48.57	25.20	13.53	20.65	0.96	28.79	16.08	4.43
2500	16.12	50.02	26.71	14.37	25.00	0.97	27.63	15.68	4.05
3000	16.04	49.88	28.47	14.66	25.16	0.97	27.28	15.46	3.78
3500	16.01	48.54	26.81	14.41	21.75	0.97	26.77	15.29	3.55
4000	16.21	48.21	25.45	14.39	20.59	0.97	26.55	15.29	3.29
4500	16.28	47.54	25.93	14.25	19.05	0.96	26.62	15.23	3.04
5000	16.34	47.09	25.93	14.32	18.11	0.96	27.13	15.32	2.71
5500	16.35	46.49	26.11	14.33	17.02	0.96	25.69	15.33	2.36
6000	16.39	46.13	24.13	14.43	16.37	0.97	27.18	15.11	2.33
6500	16.40	46.58	23.34	14.53	17.38	0.97	26.79	15.24	2.22
7000	16.41	46.21	23.23	14.95	16.80	0.97	26.71	15.25	2.06
7500	16.42	46.75	23.66	15.97	18.11	0.98	27.46	15.16	1.97
8000	16.42	46.58	23.43	17.88	18.05	0.99	26.55	15.06	1.88
8500	16.38	46.59	21.83	21.56	18.37	1.00	26.41	15.18	1.78
9000	16.32	46.41	19.75	30.58	18.26	1.01	26.95	15.08	1.76
9500	16.22	45.54	18.08	32.27	16.72	1.01	26.32	14.86	1.68
10000	16.13	44.84	17.16	23.03	15.57	1.01	26.38	14.59	1.74
10500	16.03	43.78	16.90	20.01	13.95	1.01	26.64	14.62	1.77
11000	15.97	43.55	17.16	19.29	13.74	1.01	26.27	14.52	1.78
11500	15.91	42.57	17.84	20.04	12.48	1.01	25.56	14.42	1.89
12000	15.88	41.83	18.61	21.46	11.59	1.01	26.16	14.31	1.95
12500	15.85	41.20	19.16	21.25	10.88	1.00	26.12	14.38	2.00
13000	15.82	40.55	19.30	19.40	10.15	1.00	25.96	14.24	2.11
13500	15.78	40.00	19.20	17.78	9.54	0.99	25.18	14.07	2.17
14000	15.78	39.50	19.51	16.90	9.04	0.99	26.12	14.02	2.21
14500	15.79	39.16	19.82	16.67	8.71	0.99	26.37	14.00	2.30
15000	15.82	38.71	19.98	16.97	8.29	0.99	25.70	14.02	2.35
15500	15.88	38.27	19.76	17.83	7.90	0.99	26.58	13.83	2.35
16000	15.92	37.84	19.17	19.14	7.53	1.00	25.17	13.85	2.38
16500	15.98	37.62	18.56	21.13	7.35	1.00	25.63	13.73	2.42
17000	16.02	37.05	18.21	23.64	6.91	1.01	25.59	13.72	2.46
17500	16.02	36.59	18.08	22.72	6.57	1.01	25.45	13.42	2.47
18000	16.02	36.05	18.16	20.49	6.17	1.00	24.86	13.33	2.53
18500	16.03	35.63	18.54	19.12	5.90	1.00	25.50	13.33	2.56
19000	16.05	35.00	18.96	19.19	5.50	0.99	25.39	13.32	2.59
19500	16.09	34.48	18.75	20.36	5.20	1.00	25.78	13.20	2.58
20000	16.10	34.09	17.77	22.93	4.99	1.00	24.97	13.02	2.61
20500	16.08	33.49	16.62	24.22	4.68	1.01	24.28	12.86	2.69
21000	16.03	33.16	15.80	22.78	4.52	1.01	24.59	12.79	2.69
21500	16.01	32.84	15.77	20.88	4.37	1.01	24.47	12.77	2.84
22000	16.03	32.47	16.38	19.83	4.20	1.00	24.06	12.64	2.94
22500	16.08	32.10	17.60	19.65	4.04	0.99	24.47	12.66	3.02
23000	16.13	31.67	19.23	21.01	3.89	0.99	24.29	12.59	3.07
23500	16.17	31.27	20.89	24.51	3.75	0.99	23.97	12.50	3.14
24000	16.19	31.03	22.44	28.25	3.68	0.99	23.84	12.41	3.20
24500	16.15	30.67	23.77	23.00	3.55	0.98	23.12	12.17	3.27
25000	16.10	30.38	23.92	19.74	3.45	0.97	23.46	12.10	3.36
25500	16.03	30.07	23.27	18.14	3.35	0.97	23.36	12.03	3.50
26000	15.96	29.82	21.66	17.50	3.28	0.97	23.74	11.88	3.54
26500	15.92	29.50	19.90	17.41	3.18	0.97	23.36	11.81	3.66
27000	15.87	29.10	18.56	17.00	3.06	0.97	21.64	11.76	3.80
27500	15.81	28.84	17.91	16.93	2.99	0.97	22.16	11.45	3.83
28000	15.78	28.36	17.87	17.79	2.87	0.97	21.76	11.53	3.98
28500	15.75	28.08	18.80	19.15	2.82	0.97	22.54	11.57	4.12
29000	15.70	27.95	20.17	21.80	2.84	0.97	21.01	11.44	4.25
29500	15.57	27.65	21.31	25.04	2.80	0.97	22.76	11.58	4.43
30000	15.48	27.52	22.99	27.59	2.82	0.97	21.77	11.65	4.56



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, VC=Open, Id = 66mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.18	48.77	25.12	13.47	21.09	0.96	29.10	16.32	4.47
2500	16.13	49.89	26.61	14.31	24.60	0.97	27.54	15.91	4.08
3000	16.05	50.94	28.42	14.61	28.40	0.97	27.04	15.65	3.74
3500	16.02	48.97	26.75	14.34	22.82	0.96	26.66	15.49	3.56
4000	16.22	48.22	25.42	14.31	20.56	0.97	26.89	15.48	3.35
4500	16.28	47.64	25.89	14.17	19.23	0.96	26.98	15.46	3.04
5000	16.35	46.96	25.88	14.23	17.80	0.96	27.52	15.55	2.72
5500	16.36	47.17	26.02	14.23	18.37	0.96	26.12	15.52	2.38
6000	16.40	46.26	24.05	14.34	16.58	0.97	27.23	15.39	2.36
6500	16.41	46.97	23.28	14.43	18.15	0.97	27.41	15.47	2.24
7000	16.42	46.56	23.12	14.84	17.46	0.97	27.11	15.44	2.15
7500	16.43	46.68	23.53	15.84	17.95	0.98	27.71	15.39	2.05
8000	16.42	46.97	23.31	17.74	18.83	0.99	26.51	15.30	1.90
8500	16.39	46.61	21.78	21.40	18.39	1.00	26.42	15.38	1.79
9000	16.32	46.36	19.70	30.27	18.14	1.01	27.14	15.35	1.78
9500	16.22	45.72	18.05	32.49	17.07	1.01	26.94	15.09	1.71
10000	16.13	45.24	17.11	23.04	16.31	1.01	26.31	14.82	1.77
10500	16.03	44.16	16.85	19.98	14.55	1.01	27.14	14.84	1.81
11000	15.97	43.58	17.12	19.23	13.78	1.01	26.58	14.71	1.87
11500	15.92	42.73	17.80	19.95	12.69	1.01	25.69	14.63	1.91
12000	15.88	41.96	18.60	21.35	11.77	1.01	26.56	14.50	1.98
12500	15.85	41.30	19.17	21.14	11.01	1.00	26.54	14.56	2.07
13000	15.81	40.53	19.28	19.29	10.12	1.00	26.45	14.46	2.14
13500	15.78	40.21	19.20	17.68	9.78	0.99	25.42	14.33	2.20
14000	15.78	39.71	19.47	16.77	9.26	0.99	26.40	14.26	2.29
14500	15.79	39.30	19.78	16.57	8.86	0.99	26.30	14.25	2.33
15000	15.81	38.91	19.93	16.84	8.48	0.99	25.88	14.27	2.34
15500	15.87	38.49	19.71	17.69	8.11	0.99	26.48	14.13	2.38
16000	15.91	37.80	19.09	18.97	7.49	1.00	25.58	14.14	2.42
16500	15.97	37.66	18.49	20.89	7.39	1.00	26.20	14.03	2.47
17000	16.01	37.11	18.10	23.30	6.96	1.01	25.91	14.01	2.50
17500	16.01	36.80	17.99	22.49	6.73	1.01	25.38	13.72	2.53
18000	16.02	36.07	18.09	20.37	6.19	1.00	25.46	13.66	2.59
18500	16.02	35.64	18.49	18.98	5.91	1.00	25.73	13.58	2.62
19000	16.04	35.21	18.90	19.05	5.63	0.99	25.22	13.57	2.69
19500	16.08	34.53	18.69	20.21	5.23	1.00	25.60	13.48	2.67
20000	16.09	34.07	17.72	22.72	4.99	1.00	25.71	13.22	2.67
20500	16.06	33.57	16.58	24.01	4.73	1.01	24.41	13.10	2.75
21000	16.02	33.21	15.80	22.62	4.55	1.01	24.68	13.03	2.77
21500	15.99	32.79	15.77	20.73	4.35	1.01	24.86	13.01	2.89
22000	16.01	32.52	16.42	19.67	4.23	1.00	24.19	12.88	2.95
22500	16.05	32.15	17.61	19.55	4.08	0.99	24.42	12.91	3.03
23000	16.10	31.77	19.22	20.92	3.95	0.99	24.35	12.83	3.08
23500	16.13	31.45	20.82	24.40	3.84	0.99	24.73	12.78	3.17
24000	16.15	31.13	22.28	27.72	3.73	0.99	24.33	12.69	3.24
24500	16.12	30.79	23.53	22.72	3.61	0.98	23.49	12.41	3.39
25000	16.06	30.44	23.66	19.60	3.49	0.97	23.53	12.42	3.46
25500	15.99	30.26	23.10	18.04	3.43	0.97	24.01	12.34	3.57
26000	15.92	29.91	21.49	17.40	3.32	0.97	23.85	12.20	3.62
26500	15.87	29.64	19.84	17.31	3.24	0.97	23.38	12.08	3.71
27000	15.83	29.18	18.48	16.90	3.10	0.97	22.36	12.06	3.82
27500	15.77	28.98	17.96	16.86	3.05	0.97	22.78	11.69	3.97
28000	15.73	28.67	17.90	17.76	2.98	0.97	22.06	11.88	4.06
28500	15.69	28.24	18.93	19.17	2.89	0.97	23.11	11.89	4.18
29000	15.64	28.16	20.31	21.85	2.92	0.97	21.57	11.82	4.35
29500	15.50	27.79	21.65	25.21	2.87	0.97	22.62	11.92	4.53
30000	15.40	27.68	23.31	27.44	2.90	0.97	22.26	11.99	4.61

MMIC Amplifier Die

AVA-0233LN-D+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)









Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, VC=Open, Id = 66mA @ Temperature = +85°C








FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
2000	16.20	48.36	25.05	13.42	20.06	0.96	28.99	16.53	4.45
2500	16.15	50.10	26.47	14.26	25.14	0.96	28.44	16.12	4.15
3000	16.06	50.16	28.20	14.54	25.90	0.97	27.47	15.84	3.80
3500	16.03	49.23	26.74	14.27	23.47	0.96	26.97	15.64	3.58
4000	16.23	48.46	25.40	14.23	21.11	0.96	27.13	15.67	3.33
4500	16.30	47.65	25.84	14.09	19.22	0.96	27.19	15.66	3.08
5000	16.36	47.39	25.80	14.14	18.68	0.96	28.01	15.75	2.70
5500	16.36	47.05	25.97	14.14	18.08	0.96	26.01	15.72	2.41
6000	16.41	46.47	24.01	14.25	16.95	0.97	27.29	15.60	2.37
6500	16.41	46.77	23.18	14.33	17.71	0.97	27.22	15.67	2.26
7000	16.43	46.78	23.05	14.76	17.88	0.97	27.08	15.64	2.11
7500	16.44	47.00	23.42	15.73	18.59	0.98	27.56	15.59	2.02
8000	16.43	46.85	23.26	17.59	18.57	0.99	27.28	15.54	1.90
8500	16.39	46.87	21.68	21.23	18.93	1.00	26.42	15.62	1.84
9000	16.33	46.28	19.65	29.94	17.96	1.01	27.09	15.56	1.75
9500	16.23	45.72	17.97	32.81	17.05	1.01	26.79	15.33	1.78
10000	16.13	45.12	17.05	23.06	16.07	1.01	26.99	15.02	1.80
10500	16.03	44.48	16.80	19.94	15.09	1.01	27.29	15.04	1.86
11000	15.97	43.73	17.09	19.16	14.02	1.01	26.63	14.94	1.86
11500	15.91	42.57	17.78	19.83	12.45	1.01	25.95	14.83	1.95
12000	15.88	41.89	18.58	21.24	11.66	1.01	26.83	14.73	1.95
12500	15.85	41.30	19.15	21.02	11.00	1.00	26.43	14.79	2.06
13000	15.81	40.66	19.27	19.20	10.28	1.00	26.36	14.62	2.14
13500	15.77	40.11	19.19	17.56	9.67	0.99	25.68	14.56	2.27
14000	15.77	39.77	19.46	16.68	9.32	0.99	26.39	14.50	2.29
14500	15.78	39.45	19.78	16.46	9.01	0.99	26.46	14.53	2.32
15000	15.81	38.95	19.88	16.72	8.52	0.99	26.36	14.51	2.37
15500	15.86	38.32	19.63	17.58	7.95	0.99	26.96	14.41	2.43
16000	15.90	37.94	18.99	18.80	7.62	1.00	25.81	14.39	2.42
16500	15.96	37.61	18.39	20.66	7.35	1.00	26.80	14.32	2.51
17000	16.00	37.17	18.02	23.01	7.01	1.01	26.05	14.26	2.49
17500	16.00	36.65	17.91	22.30	6.62	1.01	25.33	13.97	2.55
18000	16.00	36.09	18.00	20.20	6.21	1.00	25.38	13.94	2.62
18500	16.01	35.69	18.41	18.86	5.94	1.00	26.14	13.86	2.68
19000	16.03	35.24	18.84	18.87	5.66	0.99	25.58	13.77	2.69
19500	16.06	34.65	18.61	20.05	5.31	1.00	25.73	13.68	2.67
20000	16.07	34.25	17.67	22.56	5.10	1.00	25.34	13.46	2.66
20500	16.05	33.68	16.54	23.83	4.79	1.01	24.59	13.33	2.71
21000	16.00	33.30	15.77	22.40	4.61	1.01	24.97	13.26	2.78
21500	15.96	32.95	15.76	20.56	4.44	1.01	25.26	13.24	2.91
22000	15.98	32.56	16.42	19.55	4.26	1.00	24.32	13.14	2.94
22500	16.02	32.18	17.62	19.42	4.10	0.99	24.55	13.13	3.09
23000	16.07	31.93	19.23	20.84	4.03	0.99	24.71	13.09	3.17
23500	16.10	31.58	20.77	24.25	3.91	0.99	24.54	13.04	3.22
24000	16.12	31.20	22.07	27.30	3.77	0.99	24.52	12.91	3.30
24500	16.08	30.94	23.26	22.50	3.68	0.98	24.02	12.68	3.37
25000	16.02	30.62	23.43	19.48	3.57	0.97	23.95	12.65	3.46
25500	15.95	30.28	22.89	17.95	3.46	0.97	24.03	12.61	3.58
26000	15.88	30.05	21.38	17.32	3.39	0.97	23.90	12.46	3.65
26500	15.83	29.75	19.73	17.23	3.29	0.97	23.80	12.34	3.76
27000	15.78	29.46	18.50	16.83	3.21	0.97	22.67	12.29	3.78
27500	15.72	29.10	17.95	16.79	3.11	0.97	23.04	11.98	3.96
28000	15.68	28.73	17.93	17.78	3.02	0.97	22.48	12.14	4.06
28500	15.63	28.52	19.05	19.21	3.00	0.97	23.28	12.22	4.20
29000	15.57	28.13	20.44	22.00	2.94	0.97	21.82	12.12	4.34
29500	15.42	28.11	21.89	25.30	3.00	0.97	22.97	12.20	4.51
30000	15.32	27.97	23.66	27.35	3.02	0.97	22.07	12.30	4.60










Typical Performance Curves



Typical Performance Curves



Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	