
MMIC SURFACE MOUNT

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier

THE BIG DEAL

- Wide Bandwidth, 100 kHz to 22 GHz
- High Saturated Output Power, Typ. +27.2 dBm
- High OIP3, Typ. +38.2 dBm
- Low Noise Figure, Typ. 3 dB
- Positive Gain Slope from 4 to 22 GHz




Generic photo used for illustration purposes only

APPLICATIONS

- Test and Measurement Equipment
- 5G MIMO and Back Haul Radio
- Satellite Communication
- Radar, EW, and ECM Defense Systems

FUNCTIONAL DIAGRAM (Top View)



PRODUCT OVERVIEW

Mini-Circuits' AVA-223MP+ is a wideband, high dynamic range, MMIC amplifier fabricated on a GaAs pHEMT process with high output power and broadband gain. Operating from 100 kHz to 22 GHz, this amplifier features typical +26 dBm P1dB, +27.2 dBm P_{SAT}, 3 dB NF, and +38.2 dBm OIP3. The AVA-223MP+ comes in an industry standard 5×5 mm 32-Lead QFN-style package for ease of integration into dense circuit board layouts.

KEY FEATURES

Features	Advantages
Wide Bandwidth: 100 kHz to 22 GHz	Supports a variety of broadband and narrowband applications without the need to reconfigure circuitry.
High Dynamic Range - Noise Figure: 3 dB - Output IP3: +38.2 dBm - Output P1dB: +26 dBm	Low noise figure, high IP3, and high P1dB make this ideal for use in high dynamic range receivers.
Positive Gain Slope from 4 to 22 GHz	Positive gain slope acts as equalization to counteract loss from other components in the signal chain as frequency increases.
5×5 mm 32-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier

ELECTRICAL SPECIFICATIONS[1] AT +25°C, V_{DD} = +10 V, V_{GG2} = +3.5 V, AND Z_O = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		0.0001		22	GHz
Gain	0.1[2]		14.3		dB
	5	10.8	13.5		
	10	11.1	13.9		
	15	12.3	14.8		
	22	11.8	14.9		
Input Return Loss	0.1[2]		20		dB
	5		18		
	10		18		
	15		20		
	22		12		
Output Return Loss	0.1[2]		20		dB
	5		20		
	10		18		
	15		20		
	22		14		
Isolation	0.1-22		43.7		dB
Output Power at 1 dB Compression (P1dB)	0.1[2]		+24.2		dBm
	5		+27.1		
	10		+26.0		
	15		+25.5		
	22		+23.6		
Output Power at Saturation (P_{SAT})[3]	0.1[2]		+27.2		dBm
	5		+29.3		
	10		+27.2		
	15		+27.8		
	22		+25.2		
Output Third-Order Intercept (OIP3) (P_{OUT} = +16 dBm/Tone)	0.1[2]		+39.7		dBm
	5		+41.1		
	10		+38.2		
	15		+37.1		
	22		+29.7		
Noise Figure	2		5.2		dB
	5		3.1		
	10		3.0		
	15		3.3		
	22		4.4		
Device Operating Voltage (V_{DD})		+9	+10	+11	V
Gate Voltage (V_{GG1})		-2.0	-0.8	-0.6	V
Gate Voltage (V_{GG2})[4]		+3.25	+3.5	+3.75	V
Device Operating Current (I_{DD})[5]		250	300		mA
Gate Current (I_{GG1})			0.2		mA
Gate Current (I_{GG2})			1.4		mA
Device Current Variation vs. Temperature[6]			-157.7		µA/°C
Device Current Variation vs. Voltage[7]			+0.8		µA/mV

1. Tested on Mini-Circuits Characterization Test Board TB-AVA-223MPC+. See Figure 2. Board loss de-embedded to the device reference plane.
2. Tested on AVA-223MP+ Modified Application Circuit. See Figure 3. Board loss de-embedded to the device reference plane.
3. Defined as output power at which change is 0.1 dB per 1 dB change in input power.
4. V_{GG2} should be set to +3.5 V for optimal performance. It is not recommended to operate V_{GG2} outside of the specified range.
5. Current at P_{IN} = -25 dBm. Increases to 380 mA at P_{SAT}.
6. (Current at +85°C - Current at -45°C)/(+85°C - -45°C)
7. (Current at +11 V - Current at +9 V)/(+11 V - +9 V)


Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier


TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.


GAIN vs. TEMPERATURE
P_{IN} = -25 dBm




GAIN vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



INPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm



INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier


TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.


OUTPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm




OUTPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




P1dB vs. TEMPERATURE




P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



P_{SAT} vs. TEMPERATURE



P_{SAT} vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C




Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier


TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.


OUTPUT IP3 vs. TEMPERATURE
P_{OUT} = +16 dBm/TONE




OUTPUT IP3 vs. DEVICE VOLTAGE (V_{DD})
P_{OUT} = +16 dBm/TONE, TEMPERATURE = +25°C




OIP3 vs. P_{OUT}
TEMPERATURE = +25°C




NOISE FIGURE vs. TEMPERATURE



NOISE FIGURE vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C





GAIN VARIATION vs. TEMPERATURE
P_{IN} = -25 dBm



TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.






Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier


TYPICAL PERFORMANCE GRAPHS

Note: Data was taken at V_{DD} = +10 V and V_{GG2} = +3.5 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. Data was taken on a modified TB-AVA-223MPC+ test board using an external bias tee. See Figure 3.


GAIN vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




ISOLATION vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




INPUT RETURN LOSS vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




OUTPUT RETURN LOSS vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C



P1dB vs. FREQUENCY
TEMPERATURE = +25°C



OUTPUT IP3 vs. FREQUENCY
P_{OUT} = +16 dBm/TONE, TEMPERATURE = +25°C



ABSOLUTE MAXIMUM RATINGS[8]

Parameter	Ratings
Operating Temperature	-45°C to +85°C
Storage Temperature	-65°C to +150°C
Total Power Dissipation	6.38 W
Junction Temperature[9]	+175°C
Input Power (CW), V_{DD} = +10 V	+22 dBm
DC Voltage on RF-OUT & V_{DD}	+14 V
DC Voltage on RF-IN	+6 V
DC Gate Voltage on V_{GG1}	-3 V < V_{GG1} < 0 V
DC Gate Voltage on V_{GG2}	+5 V
DC Drain Current I_{DD}	500 mA
DC Gate Current I_{GG1}	1 mA
DC Gate Current I_{GG2}	10 mA

8. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.
9. Peak Temperature on top of Die.

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC})[10]	14.1°C/W

10. Θ_{JC}= (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

	Class	Voltage Range	Reference Standard
HBM	1B	500 V < 1000 V	ANSI/ESDA/JEDEC JS-001-2023
CDM	C3	> 1000 V	ANSI/ESDA/JEDEC JS-002-2022

ESD HANDLING PRECAUTION: This device is designed to be Class 1B for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL3 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier

FUNCTIONAL DIAGRAM (Top View)




Figure 1. AVA-223MP+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description (Refer to Fig 2)
RF-IN	5	RF-IN pad connects to RF Input port.
RF-OUT & V_{DD}	21	RF-OUT & V_{DD} pad connects to RF-Output port and voltage input port, V_{DD}.
V_{GG1}	13	DC Input pad connects to voltage input port, V_{GG1}.
V_{GG2}	2	DC Input pad connects to voltage input port, V_{GG2}.
ACG1	30	ACG1 pad connects to AC ground port 1.
ACG2	29	ACG2 pad connects to AC ground port 2.
ACG3	15	ACG3 pad connects to AC ground port 3.
GND	1, 4, 6, 8, 9, 16, 17, 20, 22, 24, 25, 32, & Paddle	Connects to ground.
NC	3, 7, 10-12, 14, 18, 19, 23, 26-28, 31	Not used internally. Connected to ground on test board.

EVALUATION BOARD




Figure 2. AVA-223MP+ Evaluation and Application Circuit

Electrical Parameters and Conditions
Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output Power at Saturation (P_{SAT}), Output IP3 (OIP3), and Noise Figure measured using PNA-X N5245B Microwave Network Analyzer.

Conditions:
1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +16 dBm/Tone at output.

Power ON/Power OFF Sequence[11]
Caution: Permanent damage to the device will occur if the Power ON and Power OFF sequences are not followed.

POWER ON:
1) Set V_{GG1} = -2 V. Apply V_{GG1}.
2) Set V_{GG2} = +3.5 V. Apply V_{GG2}.
3) Set V_{DD} = +10 V. Apply V_{DD}.
4) Increase V_{GG1} to obtain the desired I_{DD} as shown in specification table.
5) Apply RF Signal.

POWER OFF:
1) Turn off RF Signal.
2) Adjust V_{GG1} to -2 V.
3) Turn off V_{DD}.
4) Turn off V_{GG2}.
5) Turn off V_{GG1}.

11. V_{GG2} may be derived from V_{DD} using a resistive divider, zener diode, or equivalent circuit. If V_{GG2} is derived from V_{DD}, it may be applied simultaneously with V_{DD}.

Component	Value	Size	Part Number	Manufacturer
C5, C9	100 pF	0603	GRM1885C1H101GA01D	Murata
C2, C4, C6, C8, C11	0.01 µF	0402	GRM155R71E103KA01D	Murata
C12, C13	30 pF	0201	P21BN300M5S	DLI
C1, C3, C7, C10	4.7 µF	1812	C4532X7S2A475K230KB	TDK Corp
L1	0.22 µH	0.2 x 0.15 in	CCM19T40-002	Piconics

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier

EVALUATION AND APPLICATION CIRCUIT




Figure 3. AVA-223MP+ Low Frequency Evaluation and Application Circuit

Electrical Parameters and Conditions
Gain and Return Loss measured using P5022A Vector Network Analyzer.
Output Power at 1 dB Compression (P1dB) measured using Mini-Circuits' PWR-4GHS Power Sensor.


Output IP3 (OIP3) measured using MXA N9020A Signal Analyzer.
1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +16 dBm/tone at output.

Component	Value	Size	Part Number	Manufacturer
C2, C4, C6, C8	0.01 µF	0402	GRM155R71E103KA01D	Murata
C1, C5, C7	4.7 µF	1812	C4532X7S2A475K230KB	TDK Corp
C3	100 pF	0603	GRM1885C1H101GA01D	Murata

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier


CASE STYLE DRAWING



Weight: .056 Grams

Dimensions are in mm [Inches]. Tolerances: 2 Pl. ± 0.254 [0.01]; 3 Pl. ± 0.127 [0.005] mm [inches]

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Medium Power Amplifier AVA-223MP+

50Ω 100 kHz to 22 GHz Wideband Amplifier

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DG1677-8 Plastic package, exposed paddle, Lead Finish: Nickle Palladium Gold
RoHS Status	Compliant
Tape & Reel **Standard quantities available on reel**	F102 7″ reels with 20, 50, 100, 200, 500 devices 13" reels with 1000 devices
Suggested Layout for PCB Design	PL-804
Evaluation Board	TB-AVA-223MPC+ Gerber File
Environmental Ratings	ENV08T10
Product Handling	The use of no-clean solder is recommended. This package cannot be subjected to aqueous wash.

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +9 V, I_{DD} = 304 mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	16.2	-63.4	-6.0	-6.4	136.0	1.0	37.7	26.7	22.3	26.0	20.9
0.2	17.2	-52.7	-9.3	-10.9	37.5	1.0	38.0	30.6	24.1	27.4	17.7
0.3	17.6	-61.6	-10.7	-10.7	91.3	1.0	36.6	33.3	24.7	28.1	15.1
0.4	15.9	-53.6	-11.7	-11.9	43.2	1.0	36.5	34.9	25.1	28.0	13.5
0.5	15.7	-53.7	-13.4	-13.5	45.4	1.0	36.6	35.8	25.3	28.1	12.1
0.6	15.6	-57.5	-14.2	-14.8	71.3	1.0	36.3	36.6	25.4	28.2	11.0
0.7	15.6	-59.9	-14.8	-15.8	93.4	1.0	36.6	37.9	25.9	28.6	9.9
0.8	15.6	-60.3	-15.2	-16.5	97.8	1.0	36.1	38.7	26.0	28.6	9.2
0.9	15.5	-75.0	-15.7	-17.1	532.2	1.0	36.1	39.7	26.1	28.7	8.6
1.0	15.5	-60.7	-16.1	-17.7	102.8	1.0	35.7	40.3	26.2	28.7	8.0
1.5	15.1	-62.2	-17.8	-20.7	127.4	1.0	35.9	42.1	26.9	29.3	6.2
2.0	14.7	-56.0	-20.8	-23.9	64.7	1.0	35.7	42.2	26.7	29.1	5.1
2.5	14.9	-58.9	-25.1	-24.1	88.6	1.0	35.8	41.8	26.7	29.2	4.5
3.0	14.6	-63.4	-25.3	-20.6	154.6	1.0	35.6	40.7	26.4	28.8	4.2
3.5	14.1	-54.5	-24.0	-18.6	58.1	1.0	35.5	41.2	26.4	28.8	3.6
4.0	14.1	-54.3	-24.1	-18.9	57.7	1.0	35.6	41.1	26.6	28.9	3.3
4.5	13.9	-52.2	-22.5	-21.1	46.2	1.0	35.4	40.6	26.6	28.9	3.1
5.0	13.6	-48.0	-18.7	-21.3	29.5	1.0	35.7	40.2	26.5	28.8	2.9
5.5	13.7	-49.3	-17.0	-18.5	33.8	1.0	35.4	40.0	26.4	28.7	2.7
6.0	13.8	-47.9	-17.8	-17.5	28.5	1.0	35.2	40.2	26.3	28.6	2.6
6.5	14.0	-47.3	-20.9	-19.0	26.6	1.0	35.2	39.6	26.4	28.7	2.6
7.0	14.2	-45.7	-23.3	-23.7	22.0	1.0	35.1	39.6	26.5	28.7	2.5
7.5	14.2	-44.9	-21.7	-30.5	20.1	1.0	34.7	39.0	26.3	28.5	2.6
8.0	14.3	-44.8	-22.2	-32.6	19.8	1.0	34.7	38.7	26.2	28.2	2.9
8.5	14.4	-44.0	-26.6	-40.8	18.1	1.0	34.1	39.0	26.2	28.1	2.9
9.0	14.3	-43.0	-24.8	-31.5	16.3	1.0	34.0	38.6	25.7	27.5	2.9
9.5	14.3	-42.5	-19.9	-22.5	15.6	1.0	34.1	38.2	25.7	27.2	2.9
10.0	14.1	-43.5	-18.4	-18.5	17.6	1.0	33.6	37.6	25.4	26.9	2.8
10.5	14.0	-42.7	-18.5	-17.0	16.3	1.0	33.7	37.8	25.2	26.8	2.8
11.0	13.9	-41.8	-17.9	-16.7	14.8	1.0	33.5	36.5	25.1	26.8	2.8
11.5	13.8	-41.2	-16.0	-16.7	13.9	1.0	33.7	36.8	25.2	26.9	2.9
12.0	13.8	-41.0	-14.7	-16.6	13.6	1.0	33.7	36.5	25.4	27.1	2.9
12.5	14.0	-40.1	-14.6	-16.3	12.1	1.0	33.7	36.0	25.3	27.1	2.9
13.0	14.2	-39.7	-16.2	-16.6	11.4	1.0	33.0	35.6	25.3	27.2	2.9
13.5	14.5	-38.7	-19.6	-18.0	10.1	1.0	32.5	36.1	25.3	27.4	3.0
14.0	14.8	-37.4	-25.3	-21.0	8.6	1.0	32.6	35.1	25.0	27.2	3.1
14.5	15.0	-37.7	-32.8	-27.3	8.9	1.0	32.0	35.3	24.8	27.2	3.3
15.0	15.1	-36.8	-41.7	-28.9	8.0	1.0	31.9	35.1	25.0	27.4	3.4
15.5	15.0	-36.8	-23.9	-23.5	8.1	1.0	31.0	35.0	24.5	27.0	3.4
16.0	14.8	-36.6	-17.6	-19.1	8.0	1.0	31.5	34.0	24.5	27.0	3.6
16.5	14.6	-35.8	-15.0	-16.5	7.4	1.0	31.7	33.6	24.4	26.8	3.4
17.0	14.4	-36.0	-14.2	-14.9	7.6	1.0	30.6	34.7	24.6	26.7	3.6
17.5	14.4	-35.9	-14.1	-13.6	7.5	1.0	31.5	33.6	24.7	26.7	3.6
18.0	14.5	-35.2	-14.5	-12.9	6.8	1.0	31.2	32.9	24.5	26.4	3.5
18.5	14.8	-34.4	-15.3	-13.0	6.1	1.0	31.0	32.2	24.4	26.2	3.6
19.0	15.3	-33.2	-17.4	-15.0	5.3	1.0	30.9	30.9	24.2	26.1	3.8
19.5	15.7	-32.9	-22.0	-19.2	5.0	1.0	30.8	31.0	23.8	25.7	3.8
20.0	15.9	-32.4	-25.8	-18.7	4.7	1.0	30.7	31.2	23.9	25.9	4.2
20.5	15.8	-32.2	-19.8	-16.0	4.6	1.0	29.8	29.8	23.7	25.6	4.3
21.0	15.8	-32.1	-14.8	-16.7	4.5	1.0	29.7	27.9	23.3	25.3	4.4
21.5	15.5	-32.2	-12.2	-17.7	4.6	1.0	30.0	28.0	23.1	25.0	4.5
22.0	15.3	-31.5	-11.8	-14.2	4.4	1.0	31.1	27.7	23.1	24.7	4.2
22.5	15.3	-31.3	-13.8	-12.8	4.4	1.0	30.2	26.8	22.6	24.3	4.3
23.0	15.5	-30.5	-16.5	-14.7	4.1	1.0	29.3	25.8	22.0	23.8	4.4
23.5	16.1	-29.8	-19.3	-16.8	3.7	1.0	29.7	24.6	21.8	23.7	4.8
24.0	16.5	-29.5	-18.7	-13.8	3.4	0.9	29.2	23.6	21.6	23.4	5.3

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +10 V, I_{DD} = 303 mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	16.1	-64.3	-6.0	-6.4	151.4	1.0	37.4	27.9	23.2	26.5	20.9
0.2	17.1	-64.8	-9.3	-11.0	151.1	1.0	38.4	33.8	25.1	28.0	17.6
0.3	17.5	-52.1	-10.7	-10.7	31.0	1.0	37.2	37.4	25.9	28.7	15.2
0.4	15.9	-59.8	-11.6	-12.0	89.5	1.0	36.4	38.3	26.1	28.6	13.5
0.5	15.7	-63.9	-13.3	-13.5	148.0	1.0	36.6	38.8	26.2	28.6	12.2
0.6	15.6	-63.9	-14.2	-14.8	148.6	1.0	36.8	39.7	26.4	28.8	10.9
0.7	15.6	-58.1	-14.8	-15.8	76.3	1.0	36.5	40.1	26.8	29.1	10.0
0.8	15.6	-63.3	-15.3	-16.5	138.9	1.0	36.3	40.6	26.8	29.1	9.2
0.9	15.5	-63.9	-15.7	-17.1	149.1	1.0	36.0	41.4	27.0	29.3	9.2
1.0	15.4	-62.6	-16.0	-17.7	128.5	1.0	36.1	41.7	27.0	29.3	7.9
1.5	15.0	-62.4	-17.7	-20.9	131.4	1.0	36.1	42.4	27.4	29.7	6.2
2.0	14.7	-64.0	-20.7	-24.3	163.7	1.0	35.6	42.8	27.3	29.5	5.1
2.5	14.8	-63.7	-25.0	-24.4	155.5	1.0	36.5	42.5	27.3	29.6	4.5
3.0	14.5	-61.3	-25.3	-20.6	121.8	1.0	35.9	42.3	27.0	29.2	4.1
3.5	14.1	-56.1	-24.0	-18.6	69.9	1.0	35.7	42.2	26.9	29.1	3.6
4.0	14.0	-51.4	-24.2	-19.0	41.5	1.0	35.7	41.8	27.0	29.2	3.2
4.5	13.8	-51.8	-22.4	-21.1	44.7	1.0	35.7	41.3	26.9	29.1	3.0
5.0	13.6	-49.6	-18.7	-21.3	35.7	1.0	35.6	41.1	26.8	29.0	2.9
5.5	13.6	-48.5	-17.1	-18.5	31.1	1.0	35.6	41.4	26.7	28.9	2.7
6.0	13.8	-46.8	-17.8	-17.5	25.4	1.0	35.3	40.7	26.7	28.9	2.6
6.5	14.0	-44.8	-21.0	-19.1	20.1	1.0	35.3	40.4	26.8	28.9	2.6
7.0	14.1	-45.7	-23.5	-23.7	22.3	1.0	35.1	40.2	26.8	29.0	2.6
7.5	14.2	-46.0	-21.7	-30.4	22.9	1.0	34.8	39.7	26.7	28.7	2.5
8.0	14.3	-44.2	-22.3	-32.0	18.6	1.0	34.5	39.3	26.7	28.5	2.8
8.5	14.3	-44.0	-26.7	-40.3	18.2	1.0	33.4	39.4	26.6	28.3	2.9
9.0	14.2	-44.0	-24.8	-31.8	18.5	1.0	33.7	38.5	26.2	27.7	2.8
9.5	14.2	-43.8	-19.9	-22.5	18.2	1.0	33.7	38.6	26.1	27.3	3.0
10.0	14.0	-43.3	-18.3	-18.5	17.3	1.0	33.7	38.2	25.8	27.1	2.9
10.5	13.9	-41.7	-18.4	-17.0	14.6	1.0	33.4	37.9	25.6	26.9	2.8
11.0	13.8	-41.5	-17.8	-16.6	14.5	1.0	33.6	37.5	25.5	26.9	2.8
11.5	13.7	-41.6	-16.0	-16.6	14.8	1.0	33.6	37.7	25.6	27.0	2.9
12.0	13.7	-41.3	-14.7	-16.5	14.1	1.0	33.2	37.2	25.6	27.2	2.9
12.5	13.9	-39.7	-14.6	-16.3	11.6	1.0	33.1	37.3	25.7	27.3	2.9
13.0	14.1	-39.1	-16.3	-16.5	10.8	1.0	32.5	37.6	25.6	27.4	2.9
13.5	14.5	-38.3	-19.8	-17.9	9.7	1.0	32.3	37.8	25.7	27.6	3.0
14.0	14.7	-38.2	-25.4	-21.1	9.6	1.0	32.0	37.9	25.4	27.4	3.1
14.5	14.9	-37.4	-32.8	-27.0	8.7	1.0	31.6	37.7	25.3	27.5	3.2
15.0	15.0	-37.3	-39.7	-27.9	8.5	1.0	31.1	37.1	25.5	27.7	3.4
15.5	14.9	-36.8	-23.6	-22.7	8.2	1.0	30.6	37.2	25.0	27.3	3.5
16.0	14.7	-36.4	-17.5	-18.8	7.9	1.0	31.3	36.6	25.0	27.3	3.5
16.5	14.4	-36.0	-14.9	-16.2	7.6	1.0	30.6	36.1	24.9	27.2	3.5
17.0	14.3	-36.0	-14.1	-14.6	7.7	1.0	29.9	37.0	25.0	26.8	3.7
17.5	14.3	-35.5	-14.1	-13.4	7.2	1.0	31.2	36.1	25.1	27.0	3.5
18.0	14.4	-35.0	-14.5	-12.8	6.8	1.0	30.5	35.4	24.9	26.8	3.7
18.5	14.7	-34.0	-15.4	-12.9	5.9	1.0	30.4	34.9	24.8	26.5	3.7
19.0	15.1	-33.5	-17.7	-15.1	5.5	1.0	30.0	33.2	24.6	26.5	3.7
19.5	15.6	-32.7	-22.3	-19.4	5.0	1.0	29.9	33.1	24.2	26.1	4.0
20.0	15.7	-32.2	-25.9	-18.4	4.7	1.0	29.3	33.4	24.4	26.3	4.3
20.5	15.7	-32.0	-19.6	-15.8	4.5	1.0	29.2	32.2	24.2	26.1	4.4
21.0	15.6	-32.2	-14.7	-16.4	4.6	1.0	28.5	30.5	23.9	25.7	4.5
21.5	15.3	-31.6	-12.1	-17.2	4.4	1.0	29.1	30.4	23.8	25.4	4.4
22.0	15.1	-31.6	-11.8	-13.8	4.5	1.0	29.3	29.7	23.6	25.1	4.2
22.5	15.1	-31.2	-14.0	-12.7	4.4	1.0	29.0	28.3	23.1	24.7	4.4
23.0	15.4	-30.6	-16.9	-14.8	4.2	1.0	28.4	27.2	22.4	24.2	4.6
23.5	15.9	-29.6	-20.1	-17.0	3.7	1.0	28.4	25.9	22.2	24.1	5.0
24.0	16.3	-29.2	-18.3	-14.0	3.3	1.0	27.4	25.0	21.9	23.9	5.4

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +11 V, I_{DD} = 303 mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	16.1	-59.9	-6.0	-6.3	91.4	1.0	35.6	28.5	23.4	26.9	20.9
0.2	17.1	-58.6	-9.3	-11.0	74.5	1.0	37.5	35.2	25.6	28.5	17.7
0.3	17.5	-62.8	-10.7	-10.8	105.8	1.0	37.6	36.7	26.5	29.2	15.2
0.4	15.9	-60.5	-11.7	-11.9	96.9	1.0	37.6	37.8	26.5	29.0	13.4
0.5	15.6	-56.6	-13.3	-13.6	64.2	1.0	37.5	38.2	26.6	29.0	12.3
0.6	15.5	-61.8	-14.2	-14.9	117.5	1.0	36.9	38.7	26.7	29.2	11.0
0.7	15.5	-69.9	-14.8	-15.9	298.6	1.0	37.2	39.2	27.0	29.5	10.0
0.8	15.5	-68.8	-15.2	-16.7	261.0	1.0	36.7	39.8	27.0	29.5	9.3
0.9	15.5	-66.4	-15.6	-17.2	200.3	1.0	37.1	40.3	27.2	29.6	8.6
1.0	15.4	-65.7	-16.0	-17.9	184.8	1.0	36.4	40.6	27.2	29.6	8.0
1.5	15.0	-66.0	-17.7	-21.1	200.4	1.0	36.5	41.4	27.4	29.8	6.3
2.0	14.6	-65.0	-20.7	-24.6	184.4	1.0	36.5	41.7	27.2	29.7	5.2
2.5	14.8	-57.3	-25.0	-24.6	74.9	1.0	37.2	42.0	27.2	29.8	4.6
3.0	14.4	-55.2	-25.3	-20.8	60.8	1.0	36.6	41.2	26.9	29.4	4.1
3.5	14.0	-55.0	-24.0	-18.7	62.6	1.0	36.1	41.1	26.8	29.2	3.7
4.0	13.9	-51.9	-24.2	-19.1	44.5	1.0	36.2	40.9	26.9	29.3	3.3
4.5	13.8	-51.1	-22.5	-21.2	41.4	1.0	36.2	40.0	26.8	29.2	3.0
5.0	13.5	-50.2	-18.7	-21.4	38.3	1.0	36.5	40.0	26.6	29.0	3.0
5.5	13.5	-48.5	-17.1	-18.5	31.4	1.0	36.0	39.8	26.5	28.9	2.7
6.0	13.7	-47.9	-17.9	-17.5	28.7	1.0	36.1	39.7	26.6	28.9	2.7
6.5	13.9	-46.3	-21.0	-19.1	24.1	1.0	36.3	39.2	26.6	29.0	2.6
7.0	14.0	-45.8	-23.4	-23.7	22.6	1.0	35.7	39.3	26.7	28.9	2.7
7.5	14.1	-44.4	-21.8	-30.1	19.2	1.0	35.9	39.1	26.6	28.7	2.5
8.0	14.2	-43.8	-22.4	-31.6	17.9	1.0	35.3	38.7	26.6	28.5	2.9
8.5	14.3	-43.9	-26.7	-39.1	18.2	1.0	34.7	38.6	26.5	28.2	3.0
9.0	14.2	-43.5	-24.7	-32.2	17.5	1.0	34.5	37.8	26.1	27.6	3.1
9.5	14.1	-44.2	-19.8	-22.5	19.3	1.0	34.7	38.2	25.9	27.3	3.0
10.0	14.0	-41.7	-18.3	-18.5	14.5	1.0	34.2	37.7	25.6	27.0	2.9
10.5	13.8	-42.5	-18.4	-16.9	16.2	1.0	34.3	37.3	25.5	26.9	2.9
11.0	13.8	-42.5	-17.8	-16.6	16.5	1.0	34.5	36.9	25.4	26.8	2.8
11.5	13.7	-40.8	-15.9	-16.5	13.6	1.0	34.0	36.7	25.4	26.9	2.9
12.0	13.6	-40.1	-14.7	-16.5	12.4	1.0	33.9	36.5	25.5	27.1	2.9
12.5	13.8	-39.4	-14.7	-16.2	11.4	1.0	34.1	36.6	25.6	27.3	2.9
13.0	14.1	-39.2	-16.3	-16.5	11.0	1.0	33.5	37.1	25.5	27.4	3.0
13.5	14.4	-38.4	-19.8	-17.9	10.0	1.0	32.7	37.1	25.6	27.6	3.1
14.0	14.7	-37.9	-25.7	-21.1	9.3	1.0	32.5	37.4	25.4	27.5	3.1
14.5	14.8	-37.4	-33.5	-26.7	8.8	1.0	32.7	36.8	25.3	27.6	3.3
15.0	14.9	-36.5	-40.3	-27.1	7.9	1.0	31.7	36.4	25.4	27.8	3.4
15.5	14.8	-36.4	-23.4	-22.2	7.9	1.0	31.4	36.8	25.0	27.5	3.5
16.0	14.6	-36.2	-17.4	-18.4	7.8	1.0	31.8	36.0	24.9	27.4	3.6
16.5	14.3	-35.8	-14.9	-15.9	7.5	1.0	31.5	35.5	24.8	27.2	3.6
17.0	14.2	-35.7	-14.1	-14.4	7.4	1.0	30.8	36.1	24.9	26.8	3.7
17.5	14.2	-35.2	-14.1	-13.2	7.0	1.0	31.6	35.1	25.0	27.1	3.6
18.0	14.3	-34.2	-14.6	-12.6	6.2	1.0	31.7	34.6	24.7	26.8	3.8
18.5	14.6	-33.7	-15.4	-12.9	5.8	1.0	30.8	33.7	24.6	26.5	3.8
19.0	15.1	-33.4	-17.8	-15.1	5.5	1.0	30.3	32.4	24.4	26.6	3.9
19.5	15.5	-32.5	-22.7	-19.2	5.0	1.0	30.3	32.0	24.0	26.2	4.0
20.0	15.6	-32.0	-25.9	-18.0	4.6	1.0	29.8	32.2	24.1	26.3	4.3
20.5	15.6	-31.6	-19.4	-15.5	4.4	1.0	29.9	31.1	23.9	26.1	4.5
21.0	15.5	-31.7	-14.6	-16.2	4.5	1.0	28.9	29.8	23.7	25.8	4.5
21.5	15.2	-31.9	-12.0	-16.8	4.6	1.0	29.4	29.8	23.6	25.5	4.4
22.0	14.9	-31.7	-11.8	-13.6	4.6	1.0	30.0	28.9	23.4	25.1	4.3
22.5	14.9	-31.1	-14.1	-12.7	4.4	1.0	29.8	27.6	22.8	24.7	4.4
23.0	15.2	-30.7	-17.4	-14.8	4.3	1.0	29.1	26.3	22.0	24.2	4.7
23.5	15.7	-30.0	-20.5	-17.1	3.9	1.0	28.3	25.2	21.7	24.2	5.0
24.0	16.0	-29.2	-17.9	-14.2	3.4	1.0	27.6	24.1	21.4	23.9	5.3

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +9 V, I_{DD} = 327 mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	17.1	-70.5	-5.5	-5.6	273.2	0.9	32.4	27.1	23.3	26.7	19.3
0.2	18.0	-67.5	-8.8	-9.9	192.2	1.0	39.0	30.3	24.6	27.7	16.7
0.3	18.4	-73.0	-10.2	-9.9	316.2	1.0	37.9	32.1	25.2	28.1	14.2
0.4	16.8	-58.5	-11.2	-11.3	72.0	1.0	36.4	33.1	25.5	28.1	12.7
0.5	16.6	-64.0	-12.8	-12.9	140.4	1.0	36.3	33.8	25.6	28.0	11.4
0.6	16.4	-70.8	-13.7	-14.3	312.9	1.0	35.7	34.4	25.7	28.2	10.3
0.7	16.4	-63.3	-14.4	-15.3	130.2	1.0	35.7	35.5	26.2	28.5	9.3
0.8	16.4	-78.4	-14.8	-16.1	742.3	1.0	35.7	36.9	26.2	28.4	8.5
0.9	16.3	-63.6	-15.2	-16.8	135.2	1.0	35.6	38.2	26.3	28.6	7.8
1.0	16.3	-63.4	-15.6	-17.6	133.0	1.0	35.4	39.0	26.4	28.6	7.2
1.5	15.9	-64.0	-17.5	-21.7	149.8	1.0	35.3	43.3	27.0	29.2	5.5
2.0	15.5	-60.9	-20.7	-26.1	107.9	1.0	35.0	43.6	26.8	29.1	4.5
2.5	15.7	-76.1	-27.0	-25.6	606.3	1.0	35.7	43.2	26.9	29.4	3.9
3.0	15.4	-60.3	-26.5	-20.8	100.2	1.0	35.4	42.5	26.6	29.0	3.6
3.5	14.9	-55.5	-24.3	-18.9	60.9	1.0	35.1	42.5	26.7	29.0	3.2
4.0	14.9	-49.4	-24.0	-18.6	30.3	1.0	35.2	43.0	26.9	29.2	2.9
4.5	14.8	-51.4	-20.9	-20.0	38.8	1.0	34.7	42.1	26.9	29.2	2.6
5.0	14.4	-49.6	-17.6	-19.8	32.4	1.0	34.8	42.8	26.8	29.1	2.3
5.5	14.4	-47.8	-16.1	-17.6	26.1	1.0	35.0	42.4	26.6	28.8	2.2
6.0	14.6	-48.5	-16.9	-16.7	27.7	1.0	35.1	41.5	26.7	28.8	2.1
6.5	14.8	-46.8	-19.9	-18.1	22.8	1.0	35.3	41.0	26.8	29.0	1.9
7.0	14.9	-45.5	-23.2	-22.5	19.8	1.0	34.8	41.5	26.9	29.0	2.0
7.5	15.0	-44.8	-21.9	-30.1	18.3	1.0	34.2	40.9	26.8	28.8	2.1
8.0	15.1	-45.7	-22.0	-34.5	20.1	1.0	33.9	39.6	26.7	28.6	2.0
8.5	15.2	-44.1	-25.3	-40.3	16.7	1.0	34.0	40.3	26.7	28.5	2.1
9.0	15.2	-43.9	-23.1	-29.5	16.5	1.0	33.5	39.7	26.3	27.9	2.3
9.5	15.1	-43.6	-18.7	-21.8	16.1	1.0	33.3	39.1	26.2	27.6	2.4
10.0	14.9	-42.5	-17.6	-18.1	14.2	1.0	33.4	38.2	25.9	27.5	2.2
10.5	14.8	-41.7	-18.1	-16.9	13.2	1.0	33.1	38.8	25.7	27.4	2.2
11.0	14.7	-41.6	-17.5	-17.2	13.2	1.0	33.6	37.1	25.7	27.4	2.1
11.5	14.6	-42.0	-15.6	-17.1	13.9	1.0	33.3	37.5	25.7	27.4	2.2
12.0	14.6	-41.9	-14.4	-16.7	13.7	1.0	32.8	37.6	25.8	27.6	2.2
12.5	14.7	-40.4	-14.4	-16.2	11.3	1.0	32.7	36.0	25.8	27.6	2.3
13.0	15.0	-39.3	-16.1	-16.7	9.9	1.0	32.8	36.0	25.8	27.7	2.1
13.5	15.3	-37.9	-19.7	-18.1	8.4	1.0	32.3	36.0	25.7	27.8	2.2
14.0	15.6	-37.8	-24.8	-20.7	8.2	1.0	32.1	35.5	25.4	27.6	2.2
14.5	15.8	-37.9	-29.7	-24.1	8.1	1.0	31.6	35.7	25.2	27.7	2.3
15.0	15.9	-37.1	-48.2	-28.3	7.4	1.0	31.1	35.7	25.3	27.9	2.5
15.5	15.8	-36.9	-24.7	-25.8	7.3	1.0	30.7	35.1	24.8	27.5	2.5
16.0	15.7	-36.7	-18.2	-20.6	7.1	1.0	31.3	34.3	24.8	27.4	2.6
16.5	15.5	-36.1	-15.2	-17.7	6.8	1.0	30.7	34.3	24.7	27.2	2.6
17.0	15.3	-35.9	-14.1	-15.4	6.6	1.0	30.8	35.8	24.9	27.0	2.8
17.5	15.2	-34.9	-14.0	-13.6	5.9	1.0	31.2	34.8	25.0	27.0	2.8
18.0	15.3	-34.6	-14.3	-12.9	5.7	1.0	31.1	34.6	24.8	26.8	2.7
18.5	15.6	-34.3	-14.4	-12.8	5.4	1.0	30.9	34.1	24.7	26.5	2.7
19.0	16.0	-33.9	-15.6	-13.6	5.0	1.0	30.8	31.6	24.5	26.4	2.8
19.5	16.4	-33.4	-20.0	-16.4	4.7	1.0	30.0	31.2	24.0	25.9	2.9
20.0	16.8	-32.1	-28.1	-20.3	4.0	1.0	29.9	31.7	24.1	26.1	2.9
20.5	16.8	-32.0	-23.1	-16.4	4.0	1.0	29.4	30.2	24.0	25.9	3.1
21.0	16.7	-31.9	-15.8	-15.2	3.9	1.0	28.6	28.3	23.6	25.6	3.4
21.5	16.5	-32.3	-12.0	-18.9	4.1	1.0	29.2	28.1	23.2	25.3	3.5
22.0	16.2	-32.0	-10.9	-14.7	4.0	1.0	29.9	28.0	23.2	25.0	3.5
22.5	16.2	-31.4	-12.7	-12.0	3.8	1.0	29.4	27.2	22.8	24.5	3.2
23.0	16.4	-30.8	-15.5	-13.7	3.7	1.0	28.8	26.3	22.3	24.1	3.1
23.5	16.9	-30.0	-15.9	-16.7	3.3	1.0	29.1	25.2	22.2	24.0	3.4
24.0	17.5	-29.4	-17.6	-12.8	2.9	0.9	28.5	23.9	22.1	23.8	3.7

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +10 V, I_{DD} = 327 mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	17.0	-66.7	-5.5	-5.5	180.6	0.9	35.3	28.4	24.3	27.4	19.3
0.2	17.9	-58.1	-8.8	-9.8	65.8	1.0	38.8	33.7	25.8	28.5	16.6
0.3	18.3	-54.8	-10.2	-9.9	39.8	1.0	37.1	37.8	26.5	28.9	14.2
0.4	16.7	-69.3	-11.3	-11.3	253.6	1.0	36.4	39.4	26.7	28.8	12.7
0.5	16.4	-62.5	-12.9	-12.9	120.6	1.0	35.8	40.2	26.8	28.8	11.5
0.6	16.3	-78.1	-13.8	-14.2	731.6	1.0	35.6	40.9	27.0	28.9	10.2
0.7	16.3	-75.5	-14.4	-15.3	543.5	1.0	36.0	41.3	27.4	29.2	9.3
0.8	16.3	-62.4	-14.8	-16.2	119.2	1.0	35.3	41.5	27.4	29.2	8.5
0.9	16.2	-68.9	-15.2	-16.8	253.2	1.0	35.7	41.6	27.5	29.3	8.6
1.0	16.1	-68.2	-15.6	-17.6	235.8	1.0	35.3	41.8	27.6	29.3	7.2
1.5	15.7	-67.1	-17.4	-21.9	218.0	1.0	35.5	41.2	28.0	29.8	5.4
2.0	15.4	-60.0	-20.7	-26.5	98.8	1.0	35.3	41.4	27.9	29.8	4.4
2.5	15.5	-60.4	-26.8	-25.9	100.7	1.0	35.5	41.4	27.9	30.0	3.8
3.0	15.2	-55.5	-26.7	-20.9	58.9	1.0	35.4	41.8	27.6	29.6	3.7
3.5	14.8	-52.8	-24.3	-18.9	45.2	1.0	35.2	41.5	27.5	29.5	3.2
4.0	14.7	-50.9	-24.0	-18.7	36.7	1.0	34.9	41.5	27.7	29.7	2.8
4.5	14.6	-48.7	-20.9	-20.0	29.0	1.0	35.2	41.3	27.6	29.7	2.5
5.0	14.3	-49.4	-17.6	-19.8	32.3	1.0	34.8	40.8	27.5	29.6	2.4
5.5	14.3	-47.2	-16.2	-17.5	24.7	1.0	35.1	41.2	27.4	29.3	2.2
6.0	14.5	-47.3	-16.9	-16.7	24.6	1.0	34.6	41.0	27.5	29.3	2.1
6.5	14.6	-47.0	-19.9	-18.1	23.8	1.0	34.8	40.9	27.5	29.4	2.1
7.0	14.8	-45.5	-23.3	-22.5	20.2	1.0	34.8	39.9	27.6	29.5	2.0
7.5	14.8	-45.6	-22.0	-30.3	20.4	1.0	34.2	39.5	27.5	29.2	1.9
8.0	15.0	-45.1	-22.2	-34.2	19.1	1.0	33.9	39.6	27.4	29.0	2.0
8.5	15.0	-44.1	-25.4	-40.9	16.9	1.0	33.1	38.9	27.4	28.8	2.1
9.0	15.0	-43.8	-22.9	-29.8	16.5	1.0	33.0	38.6	26.9	28.2	2.3
9.5	14.9	-43.9	-18.7	-21.7	16.9	1.0	33.4	38.6	26.9	27.9	2.3
10.0	14.7	-43.8	-17.6	-18.0	16.8	1.0	33.2	38.5	26.6	27.8	2.3
10.5	14.6	-42.8	-18.0	-16.9	15.1	1.0	33.1	38.0	26.5	27.7	2.2
11.0	14.5	-42.3	-17.5	-17.1	14.5	1.0	33.0	38.3	26.4	27.7	2.2
11.5	14.4	-40.9	-15.7	-17.0	12.5	1.0	32.8	38.3	26.4	27.7	2.1
12.0	14.4	-41.0	-14.4	-16.6	12.6	1.0	32.8	37.7	26.5	27.9	2.1
12.5	14.6	-40.0	-14.5	-16.1	11.1	1.0	33.0	38.0	26.5	27.9	2.2
13.0	14.8	-38.9	-16.2	-16.7	9.7	1.0	32.1	38.1	26.5	28.1	2.1
13.5	15.2	-38.3	-19.9	-18.2	8.9	1.0	31.9	37.6	26.5	28.2	2.2
14.0	15.4	-37.9	-25.1	-20.6	8.4	1.0	31.8	38.2	26.2	28.1	2.2
14.5	15.6	-37.8	-30.5	-24.2	8.2	1.0	31.4	37.5	26.1	28.1	2.4
15.0	15.7	-36.9	-43.1	-27.8	7.4	1.0	30.7	37.0	26.3	28.3	2.5
15.5	15.6	-36.5	-24.3	-24.9	7.1	1.0	30.3	37.0	25.8	27.9	2.5
16.0	15.5	-36.8	-18.1	-20.1	7.4	1.0	30.9	37.7	25.8	28.0	2.6
16.5	15.3	-36.3	-15.1	-17.4	7.0	1.0	30.9	37.5	25.7	27.8	2.8
17.0	15.1	-35.7	-14.1	-15.1	6.6	1.0	30.3	37.8	25.9	27.6	2.7
17.5	15.0	-35.3	-14.0	-13.4	6.3	1.0	31.1	37.7	25.9	27.7	2.6
18.0	15.2	-34.8	-14.4	-12.9	5.9	1.0	30.7	38.4	25.8	27.4	2.8
18.5	15.4	-33.7	-14.5	-12.7	5.1	1.0	30.2	38.4	25.6	27.1	2.7
19.0	15.8	-33.5	-15.9	-13.6	4.9	1.0	30.0	38.5	25.4	27.0	2.8
19.5	16.3	-33.0	-20.4	-16.4	4.6	1.0	29.4	37.7	25.0	26.6	2.8
20.0	16.6	-32.6	-29.5	-20.3	4.3	1.0	29.2	36.9	25.2	26.8	3.0
20.5	16.6	-31.9	-22.8	-16.1	4.0	1.0	28.7	37.0	25.1	26.7	3.3
21.0	16.5	-31.8	-15.5	-15.0	3.9	1.0	28.3	34.5	24.8	26.4	3.4
21.5	16.3	-31.6	-11.7	-18.6	3.8	1.0	28.4	34.0	24.6	26.1	3.6
22.0	16.0	-31.6	-10.9	-14.2	3.9	1.0	28.6	33.2	24.4	25.8	3.5
22.5	15.9	-31.2	-12.9	-11.9	3.8	1.0	28.6	31.8	24.0	25.3	3.3
23.0	16.2	-30.5	-15.9	-13.8	3.6	1.0	28.3	30.4	23.4	24.9	3.2
23.5	16.7	-30.0	-16.5	-16.8	3.4	1.0	28.2	29.0	23.2	24.8	3.5
24.0	17.2	-29.3	-17.7	-12.9	2.9	0.9	27.2	27.6	23.0	24.6	3.8

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +11 V, I_{DD} = 327 mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	16.9	-61.8	-5.5	-5.5	103.3	0.9	34.0	29.4	24.7	28.0	19.4
0.2	17.9	-58.3	-8.8	-9.9	68.0	1.0	38.0	36.3	26.3	29.1	16.6
0.3	18.3	-60.3	-10.2	-10.0	74.9	1.0	36.3	37.7	27.1	29.6	14.4
0.4	16.6	-56.0	-11.2	-11.3	55.0	1.0	36.2	39.3	27.4	29.5	12.7
0.5	16.4	-75.0	-12.8	-12.9	509.7	1.0	36.0	39.6	27.5	29.4	11.4
0.6	16.3	-69.7	-13.7	-14.3	280.3	1.0	36.2	40.2	27.6	29.5	10.3
0.7	16.3	-64.4	-14.3	-15.4	151.5	1.0	36.3	40.5	27.9	29.8	9.3
0.8	16.2	-64.4	-14.8	-16.3	151.8	1.0	36.2	40.6	27.9	29.7	8.4
0.9	16.2	-74.4	-15.3	-17.0	480.3	1.0	36.2	40.8	28.1	29.9	7.9
1.0	16.1	-74.1	-15.6	-17.7	468.9	1.0	36.0	40.7	28.1	29.8	7.2
1.5	15.7	-60.5	-17.4	-22.0	102.1	1.0	36.0	41.0	28.3	30.2	5.4
2.0	15.3	-62.1	-20.7	-27.0	127.0	1.0	36.2	41.2	28.2	30.1	4.4
2.5	15.5	-57.8	-26.9	-26.3	75.6	1.0	36.2	41.3	28.2	30.3	4.0
3.0	15.2	-55.4	-26.5	-21.2	58.4	1.0	36.1	41.3	27.9	30.0	3.6
3.5	14.7	-56.6	-24.3	-19.1	70.3	1.0	36.0	41.3	27.7	29.9	3.3
4.0	14.7	-51.6	-24.0	-18.8	40.2	1.0	35.9	41.1	27.9	30.0	2.8
4.5	14.5	-49.8	-21.0	-20.1	33.1	1.0	36.0	41.1	27.8	29.9	2.6
5.0	14.2	-49.8	-17.7	-19.8	34.0	1.0	35.7	41.7	27.7	29.7	2.4
5.5	14.2	-48.1	-16.2	-17.6	27.8	1.0	35.9	41.1	27.6	29.6	2.1
6.0	14.4	-47.3	-16.9	-16.6	25.0	1.0	36.3	40.9	27.7	29.5	2.0
6.5	14.6	-46.4	-20.0	-18.1	22.4	1.0	35.7	40.7	27.7	29.6	2.0
7.0	14.7	-46.0	-23.4	-22.5	21.5	1.0	34.9	39.9	27.8	29.6	2.0
7.5	14.8	-45.5	-22.0	-30.1	20.2	1.0	35.2	39.3	27.7	29.4	2.1
8.0	14.9	-44.8	-22.2	-33.6	18.7	1.0	34.6	39.0	27.6	29.2	2.0
8.5	15.0	-43.7	-25.4	-41.2	16.5	1.0	34.3	38.2	27.5	28.9	2.1
9.0	14.9	-45.1	-23.0	-30.3	19.4	1.0	34.2	38.5	27.1	28.3	2.3
9.5	14.8	-43.3	-18.6	-21.9	15.9	1.0	34.2	38.2	26.9	28.0	2.3
10.0	14.7	-43.7	-17.5	-18.1	16.7	1.0	33.8	37.9	26.7	27.8	2.4
10.5	14.6	-43.2	-18.0	-16.8	16.0	1.0	33.8	37.8	26.6	27.8	2.2
11.0	14.5	-41.4	-17.5	-17.1	13.2	1.0	33.8	37.6	26.5	27.7	2.2
11.5	14.4	-41.5	-15.6	-16.9	13.5	1.0	34.1	37.6	26.5	27.8	2.3
12.0	14.3	-40.7	-14.4	-16.5	12.3	1.0	33.5	37.1	26.6	28.0	2.2
12.5	14.5	-39.8	-14.5	-16.0	10.9	1.0	33.7	36.8	26.6	28.1	2.2
13.0	14.8	-38.9	-16.2	-16.6	9.7	1.0	33.3	36.7	26.7	28.2	2.2
13.5	15.1	-38.3	-20.0	-18.1	9.0	1.0	32.6	36.2	26.7	28.4	2.3
14.0	15.4	-37.7	-25.2	-20.6	8.2	1.0	32.6	36.5	26.5	28.3	2.3
14.5	15.5	-37.1	-31.0	-23.9	7.6	1.0	32.3	36.1	26.4	28.4	2.5
15.0	15.6	-36.6	-40.6	-27.3	7.2	1.0	31.8	35.9	26.5	28.6	2.5
15.5	15.6	-36.2	-24.1	-24.3	6.9	1.0	31.4	36.0	26.1	28.2	2.7
16.0	15.4	-36.1	-17.9	-19.7	6.9	1.0	31.6	36.1	26.1	28.3	2.7
16.5	15.2	-35.6	-14.9	-17.1	6.5	1.0	31.2	36.1	26.0	28.2	2.8
17.0	15.0	-35.3	-14.0	-14.9	6.4	1.0	30.8	36.4	26.1	27.7	2.8
17.5	15.0	-35.3	-14.0	-13.2	6.4	1.0	32.1	37.0	26.2	28.0	2.8
18.0	15.1	-34.2	-14.4	-12.7	5.6	1.0	31.7	36.7	26.0	27.8	2.7
18.5	15.3	-34.2	-14.6	-12.6	5.4	1.0	31.5	37.0	25.8	27.5	2.7
19.0	15.7	-33.7	-15.9	-13.5	5.0	1.0	30.8	37.6	25.7	27.4	2.8
19.5	16.2	-32.5	-20.9	-16.5	4.3	1.0	30.1	36.1	25.3	27.0	2.9
20.0	16.5	-32.4	-29.8	-20.0	4.3	1.0	30.3	35.6	25.4	27.2	3.0
20.5	16.5	-31.9	-22.7	-15.8	4.0	1.0	29.6	35.8	25.3	27.1	3.2
21.0	16.4	-31.8	-15.4	-14.8	4.0	1.0	28.8	35.6	25.1	26.8	3.5
21.5	16.1	-31.5	-11.7	-18.3	3.8	1.0	29.3	35.6	24.9	26.5	3.5
22.0	15.9	-31.2	-10.8	-13.9	3.8	1.0	29.8	35.1	24.7	26.1	3.5
22.5	15.8	-31.1	-13.0	-11.7	3.8	1.0	29.4	33.3	24.2	25.6	3.3
23.0	16.1	-30.5	-16.3	-13.8	3.7	1.0	28.9	31.3	23.6	25.2	3.3
23.5	16.6	-29.5	-16.9	-16.7	3.3	1.0	28.4	29.8	23.3	25.2	3.6
24.0	17.1	-29.0	-17.6	-12.8	2.9	0.9	27.6	28.3	23.0	24.9	3.9

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +9 V, I_{DD} = 302 mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	15.2	-56.0	-5.5	-5.6	63.1	0.9	33.8	27.1	22.7	26.3	22.0
0.2	16.5	-59.9	-8.8	-10.0	92.9	1.0	38.0	31.3	24.4	27.8	18.4
0.3	16.9	-66.1	-10.1	-10.0	166.2	1.0	38.3	33.9	25.1	28.4	15.6
0.4	15.3	-51.8	-11.2	-11.3	38.4	1.0	37.4	35.2	25.2	28.1	14.0
0.5	15.0	-62.4	-12.8	-12.8	134.3	1.0	37.1	35.9	25.2	28.0	12.7
0.6	14.9	-69.4	-13.7	-14.2	303.4	1.0	38.0	36.5	25.4	28.1	11.4
0.7	15.0	-62.2	-14.3	-15.2	131.8	1.0	37.4	37.2	25.8	28.4	10.4
0.8	14.9	-58.5	-14.7	-15.9	85.8	1.0	37.2	37.9	25.8	28.3	9.7
0.9	14.9	-63.5	-15.1	-16.6	153.0	1.0	37.2	38.4	25.9	28.5	10.1
1.0	14.8	-64.7	-15.5	-17.1	176.5	1.0	37.3	38.8	26.0	28.4	8.5
1.5	14.4	-61.7	-17.3	-20.5	130.3	1.0	37.3	40.1	26.4	28.7	6.7
2.0	14.1	-66.2	-20.0	-24.7	224.8	1.0	36.9	40.2	26.3	28.6	5.8
2.5	14.2	-57.4	-23.9	-24.7	80.3	1.0	37.3	39.6	26.3	28.6	5.2
3.0	13.8	-57.9	-25.6	-21.3	88.8	1.0	37.4	39.1	26.0	28.2	4.9
3.5	13.4	-53.3	-25.1	-19.1	54.7	1.0	36.9	39.1	25.9	28.1	4.3
4.0	13.3	-51.2	-25.2	-19.3	43.5	1.0	37.0	38.9	26.1	28.2	3.9
4.5	13.2	-52.7	-23.6	-21.8	53.2	1.0	36.5	38.3	26.0	28.1	3.8
5.0	12.9	-50.0	-19.7	-22.1	40.1	1.0	37.2	38.5	25.9	28.1	3.4
5.5	13.0	-50.1	-17.7	-19.1	40.2	1.0	37.0	38.3	25.8	28.0	3.4
6.0	13.1	-47.0	-18.3	-18.0	28.1	1.0	36.5	38.0	25.8	28.0	3.3
6.5	13.3	-46.5	-21.4	-19.5	26.4	1.0	36.3	37.9	25.8	28.0	3.3
7.0	13.4	-46.3	-23.6	-24.3	25.7	1.0	36.0	38.2	25.8	28.0	3.3
7.5	13.5	-45.4	-21.8	-30.6	23.1	1.0	35.7	37.8	25.7	27.8	3.3
8.0	13.6	-44.3	-22.2	-31.2	20.4	1.0	35.5	37.6	25.6	27.6	3.5
8.5	13.7	-44.7	-26.7	-38.5	21.5	1.0	34.9	37.8	25.6	27.4	3.6
9.0	13.6	-43.5	-25.4	-30.7	19.0	1.0	34.7	36.9	25.1	26.8	3.7
9.5	13.5	-43.4	-20.5	-22.4	18.8	1.0	35.1	36.9	25.0	26.5	3.7
10.0	13.3	-42.5	-18.9	-18.6	17.3	1.0	35.2	36.3	24.7	26.2	3.7
10.5	13.2	-42.5	-18.8	-16.8	17.5	1.0	34.5	36.4	24.4	26.0	3.6
11.0	13.1	-42.2	-18.1	-16.3	17.0	1.0	34.2	35.1	24.3	26.0	3.7
11.5	13.1	-42.0	-16.4	-16.4	16.7	1.0	34.2	35.3	24.4	26.0	3.6
12.0	13.1	-40.0	-15.2	-16.7	13.3	1.0	34.2	35.3	24.5	26.3	3.7
12.5	13.2	-40.4	-15.1	-16.7	13.7	1.0	34.0	34.5	24.5	26.3	3.7
13.0	13.5	-39.2	-16.3	-17.0	11.8	1.0	33.7	34.5	24.4	26.4	3.8
13.5	13.8	-38.2	-19.5	-18.2	10.4	1.0	33.1	34.6	24.4	26.5	3.9
14.0	14.1	-37.9	-26.3	-21.4	10.0	1.0	32.9	33.9	24.1	26.4	3.9
14.5	14.2	-37.3	-37.6	-30.4	9.4	1.0	32.4	33.7	23.9	26.4	4.0
15.0	14.3	-36.5	-37.9	-25.9	8.6	1.0	32.2	33.5	24.1	26.5	4.2
15.5	14.1	-36.4	-25.0	-20.2	8.5	1.0	31.6	33.2	23.5	26.2	4.4
16.0	14.0	-36.9	-18.1	-18.0	9.2	1.0	32.2	32.6	23.6	26.1	4.5
16.5	13.7	-36.6	-15.0	-16.5	9.0	1.0	31.3	32.5	23.5	26.0	4.6
17.0	13.6	-35.9	-14.3	-14.6	8.3	1.0	30.6	32.8	23.6	25.8	4.6
17.5	13.6	-35.0	-14.6	-13.1	7.6	1.0	31.9	32.0	23.7	25.8	4.5
18.0	13.8	-35.6	-15.4	-12.9	7.9	1.0	31.7	31.5	23.4	25.6	4.6
18.5	14.1	-34.2	-16.6	-13.6	6.7	1.0	31.1	31.1	23.3	25.4	4.6
19.0	14.5	-33.4	-18.9	-16.6	6.0	1.0	31.3	30.0	22.9	25.2	4.8
19.5	14.9	-32.5	-23.3	-20.7	5.4	1.0	32.2	30.1	22.5	24.8	5.0
20.0	15.0	-32.6	-24.9	-17.0	5.3	1.0	30.7	30.1	22.8	25.0	5.3
20.5	15.0	-31.9	-18.9	-15.0	4.9	1.0	30.9	28.8	22.4	24.7	5.4
21.0	14.9	-31.8	-14.1	-17.1	4.9	1.0	29.6	27.2	22.1	24.4	5.5
21.5	14.6	-31.9	-12.0	-16.4	5.0	1.0	31.2	27.2	21.8	24.1	5.2
22.0	14.3	-31.8	-12.7	-12.9	5.1	1.0	32.4	26.7	21.7	23.7	5.2
22.5	14.4	-31.2	-15.8	-13.1	4.9	1.0	30.9	25.9	21.2	23.3	5.3
23.0	14.8	-30.4	-17.9	-16.7	4.5	1.0	29.9	24.9	20.7	22.9	5.7
23.5	15.2	-29.8	-19.6	-16.1	4.1	1.0	30.1	23.9	20.4	22.7	6.1
24.0	15.4	-29.4	-16.7	-13.8	3.8	1.0	29.2	23.2	20.0	22.4	6.4

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +10 V, I_{DD} = 302 mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	15.1	-57.7	-5.6	-5.6	77.8	0.9	34.3	28.2	23.5	26.9	21.9
0.2	16.3	-59.0	-8.9	-10.0	85.2	1.0	37.5	34.3	25.4	28.4	18.4
0.3	16.8	-63.9	-10.2	-10.0	131.2	1.0	37.5	36.8	26.1	29.0	15.7
0.4	15.1	-75.0	-11.3	-11.3	564.2	1.0	37.3	37.1	26.0	28.7	14.1
0.5	14.9	-60.5	-12.9	-12.8	109.5	1.0	37.7	37.5	26.0	28.5	12.8
0.6	14.8	-58.6	-13.7	-14.2	88.9	1.0	38.5	38.0	26.1	28.6	11.4
0.7	14.8	-65.6	-14.3	-15.2	197.1	1.0	37.8	38.2	26.3	28.8	10.4
0.8	14.8	-63.9	-14.7	-15.9	161.6	1.0	37.6	38.9	26.3	28.8	9.7
0.9	14.8	-63.3	-15.1	-16.6	151.8	1.0	37.9	39.3	26.5	28.9	8.3
1.0	14.6	-64.2	-15.6	-17.1	168.9	1.0	37.6	39.4	26.4	28.8	8.4
1.5	14.2	-67.6	-17.3	-20.5	260.8	1.0	37.9	40.4	26.7	29.0	6.8
2.0	13.9	-58.0	-20.0	-24.7	89.5	1.0	37.8	40.5	26.5	28.8	5.9
2.5	14.0	-67.5	-23.9	-24.7	262.6	1.0	37.9	40.1	26.5	28.8	5.1
3.0	13.7	-54.3	-25.8	-21.3	59.7	1.0	37.8	39.6	26.2	28.5	4.8
3.5	13.3	-56.2	-25.3	-19.1	77.6	1.0	37.1	39.4	26.1	28.3	4.3
4.0	13.2	-51.6	-25.4	-19.3	46.5	1.0	37.3	39.3	26.2	28.4	3.9
4.5	13.0	-49.6	-23.8	-21.8	38.0	1.0	37.8	38.7	26.1	28.3	3.7
5.0	12.8	-49.6	-19.6	-22.1	38.9	1.0	37.8	38.8	25.9	28.2	3.5
5.5	12.8	-48.9	-17.7	-19.1	35.8	1.0	37.0	38.5	25.8	28.1	3.3
6.0	13.0	-47.7	-18.4	-18.0	30.9	1.0	37.1	38.3	25.9	28.1	3.2
6.5	13.1	-45.6	-21.4	-19.5	24.1	1.0	37.4	38.1	25.9	28.1	3.3
7.0	13.3	-45.5	-23.8	-24.3	24.0	1.0	37.0	38.3	26.0	28.2	3.3
7.5	13.4	-45.1	-21.9	-30.6	22.7	1.0	36.3	38.1	25.9	28.0	3.4
8.0	13.5	-45.0	-22.3	-31.2	22.5	1.0	35.3	37.6	25.8	27.7	3.5
8.5	13.5	-44.6	-26.6	-38.5	21.6	1.0	35.2	37.8	25.7	27.5	3.8
9.0	13.5	-43.5	-25.5	-30.7	19.2	1.0	35.3	37.3	25.3	26.9	3.7
9.5	13.4	-43.9	-20.6	-22.4	20.3	1.0	35.3	37.3	25.2	26.6	3.6
10.0	13.2	-42.8	-18.9	-18.6	18.0	1.0	35.4	36.4	24.8	26.3	3.8
10.5	13.1	-42.3	-18.7	-16.8	17.4	1.0	34.7	36.7	24.6	26.1	3.7
11.0	13.0	-42.0	-18.2	-16.3	17.0	1.0	34.6	36.0	24.5	26.0	3.7
11.5	12.9	-40.9	-16.4	-16.4	15.2	1.0	35.1	35.8	24.6	26.1	3.7
12.0	12.9	-40.6	-15.2	-16.7	14.6	1.0	34.2	35.7	24.6	26.3	3.7
12.5	13.1	-40.0	-15.1	-16.7	13.3	1.0	34.6	35.4	24.6	26.4	3.8
13.0	13.3	-39.1	-16.3	-17.0	11.9	1.0	33.7	35.7	24.6	26.5	3.8
13.5	13.7	-38.4	-19.7	-18.2	10.9	1.0	33.5	35.8	24.6	26.7	3.9
14.0	13.9	-37.8	-26.7	-21.4	10.1	1.0	33.3	35.4	24.4	26.6	4.0
14.5	14.1	-37.6	-38.1	-30.4	9.9	1.0	33.1	35.2	24.2	26.6	4.1
15.0	14.1	-36.8	-36.3	-25.9	9.1	1.0	32.4	34.7	24.3	26.8	4.3
15.5	14.0	-36.4	-24.8	-20.2	8.7	1.0	31.7	34.6	23.9	26.4	4.3
16.0	13.8	-36.5	-18.0	-18.0	8.9	1.0	32.1	33.7	23.9	26.4	4.5
16.5	13.5	-36.2	-15.0	-16.5	8.7	1.0	32.3	33.5	23.8	26.2	4.5
17.0	13.4	-36.0	-14.3	-14.6	8.6	1.0	30.8	33.8	23.8	25.8	4.6
17.5	13.4	-35.6	-14.6	-13.1	8.2	1.0	31.4	32.9	23.9	26.0	4.5
18.0	13.6	-34.8	-15.4	-12.9	7.4	1.0	31.7	32.3	23.7	25.8	4.6
18.5	13.9	-33.5	-16.8	-13.6	6.3	1.0	31.7	31.8	23.5	25.6	4.8
19.0	14.4	-33.1	-19.2	-16.6	5.9	1.0	31.6	30.8	23.2	25.5	4.8
19.5	14.7	-32.9	-23.6	-20.7	5.7	1.0	31.3	30.7	22.8	25.1	5.0
20.0	14.8	-32.6	-25.0	-17.0	5.4	1.0	31.0	30.7	23.0	25.3	5.2
20.5	14.7	-32.1	-18.7	-15.0	5.1	1.0	30.7	29.6	22.7	25.0	5.4
21.0	14.6	-31.6	-14.0	-17.1	4.9	1.0	29.8	28.4	22.4	24.7	5.6
21.5	14.3	-31.9	-11.9	-16.4	5.1	1.0	30.9	28.2	22.3	24.4	5.4
22.0	14.0	-31.3	-12.8	-12.9	5.0	1.0	31.8	27.3	22.0	24.0	5.3
22.5	14.1	-31.0	-16.0	-13.1	4.9	1.0	30.9	26.4	21.5	23.5	5.4
23.0	14.5	-30.4	-18.3	-16.7	4.7	1.0	30.0	25.3	20.9	23.1	5.7
23.5	14.9	-29.6	-20.1	-16.1	4.2	1.0	29.4	24.3	20.6	23.0	6.2
24.0	15.1	-29.5	-16.2	-13.8	4.0	1.0	28.6	23.5	20.1	22.7	6.5

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)


TEST CONDITIONS: V_{GG1} = -0.77 V, I_{GG1} = 0.22 mA , V_{GG2} = +3.5 V, I_{GG2} = 1.42 mA, V_{DD} = +11 V, I_{DD} = 302 mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +10 dBm	IP-3 Output P_{OUT} = +16 dBm	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
0.1	15.2	-62.6	-5.5	-5.6	135.8	0.9	33.4	29.7	23.8	27.3	22.0
0.2	16.4	-84.7	-8.8	-10.1	1636.7	1.0	36.6	35.4	25.9	28.9	18.4
0.3	16.8	-58.4	-10.1	-10.0	69.5	1.0	37.1	36.7	26.7	29.5	15.8
0.4	15.2	-55.1	-11.2	-11.3	56.6	1.0	38.8	37.4	26.3	29.1	14.1
0.5	14.9	-69.0	-12.7	-12.9	289.5	1.0	37.8	37.7	26.3	28.9	12.7
0.6	14.9	-65.6	-13.6	-14.3	197.5	1.0	38.9	38.0	26.3	28.9	11.5
0.7	14.9	-64.8	-14.2	-15.3	178.5	1.0	38.3	38.4	26.5	29.1	10.5
0.8	14.8	-71.3	-14.7	-16.0	379.6	1.0	38.3	38.9	26.6	29.0	9.7
0.9	14.8	-67.0	-15.1	-16.7	230.7	1.0	38.5	39.3	26.6	29.1	8.9
1.0	14.7	-64.2	-15.5	-17.3	167.6	1.0	38.1	39.6	26.6	29.1	8.5
1.5	14.3	-57.3	-17.2	-20.6	79.7	1.0	38.4	40.3	26.7	29.1	6.9
2.0	13.9	-58.5	-19.8	-25.0	94.0	1.0	38.4	40.6	26.5	28.9	5.8
2.5	14.1	-65.4	-23.8	-25.2	205.4	1.0	38.3	40.1	26.5	28.9	5.3
3.0	13.7	-60.3	-25.6	-21.5	118.8	1.0	38.8	39.6	26.2	28.6	4.8
3.5	13.3	-57.5	-25.0	-19.2	90.0	1.0	38.3	39.4	26.1	28.3	4.4
4.0	13.2	-51.7	-25.3	-19.4	47.0	1.0	38.4	39.3	26.1	28.4	4.0
4.5	13.0	-51.7	-23.7	-22.0	48.5	1.0	38.4	38.5	26.0	28.3	3.8
5.0	12.8	-50.9	-19.6	-22.2	45.4	1.0	37.9	38.7	25.9	28.1	3.7
5.5	12.8	-48.2	-17.6	-19.2	33.1	1.0	38.4	38.6	25.8	28.0	3.4
6.0	13.0	-47.2	-18.2	-18.0	29.0	1.0	38.4	38.4	25.8	28.1	3.4
6.5	13.1	-46.6	-21.4	-19.5	27.0	1.0	38.3	38.0	25.9	28.1	3.3
7.0	13.3	-45.3	-23.7	-24.3	23.5	1.0	37.7	38.1	25.9	28.1	3.4
7.5	13.4	-45.1	-21.8	-30.3	22.8	1.0	37.0	37.9	25.9	27.9	3.5
8.0	13.5	-44.7	-22.3	-30.6	21.6	1.0	37.1	37.8	25.8	27.7	3.6
8.5	13.5	-43.9	-26.8	-36.7	20.0	1.0	35.5	38.1	25.7	27.4	3.7
9.0	13.4	-44.0	-25.5	-30.7	20.4	1.0	36.5	37.3	25.3	26.9	3.8
9.5	13.3	-42.9	-20.4	-22.3	18.1	1.0	36.2	37.2	25.2	26.5	3.8
10.0	13.2	-42.6	-18.8	-18.4	17.7	1.0	35.6	36.4	24.8	26.2	3.7
10.5	13.0	-41.7	-18.6	-16.6	16.3	1.0	36.0	36.3	24.6	26.0	3.6
11.0	12.9	-41.7	-18.0	-16.1	16.5	1.0	36.1	35.9	24.5	26.0	3.7
11.5	12.9	-40.8	-16.4	-16.1	14.9	1.0	35.3	36.0	24.5	26.0	3.7
12.0	12.9	-40.5	-15.2	-16.4	14.5	1.0	35.4	35.6	24.6	26.3	3.8
12.5	13.0	-39.8	-15.1	-16.5	13.2	1.0	35.0	35.5	24.7	26.4	3.8
13.0	13.3	-38.8	-16.4	-16.9	11.6	1.0	35.0	35.9	24.6	26.5	3.8
13.5	13.6	-37.9	-19.8	-18.1	10.3	1.0	34.4	36.2	24.7	26.7	4.0
14.0	13.9	-37.5	-26.7	-21.5	9.9	1.0	34.0	35.8	24.4	26.6	4.0
14.5	14.0	-37.7	-40.4	-29.5	10.1	1.0	34.0	35.6	24.3	26.7	4.2
15.0	14.1	-36.8	-35.9	-24.6	9.1	1.0	33.4	35.1	24.4	26.8	4.4
15.5	13.9	-36.5	-24.4	-19.3	8.8	1.0	32.6	35.0	24.0	26.5	4.4
16.0	13.7	-36.1	-17.8	-17.3	8.6	1.0	33.3	34.0	23.9	26.5	4.6
16.5	13.5	-35.9	-14.9	-15.8	8.6	1.0	32.5	33.5	23.8	26.3	4.6
17.0	13.3	-35.4	-14.3	-14.2	8.1	1.0	30.9	34.1	23.8	25.8	4.7
17.5	13.3	-35.5	-14.5	-12.9	8.2	1.0	31.8	33.2	23.9	26.1	4.7
18.0	13.5	-34.7	-15.4	-12.7	7.4	1.0	32.8	32.4	23.6	25.8	4.6
18.5	13.8	-34.3	-16.8	-13.5	7.0	1.0	31.5	31.8	23.5	25.6	4.7
19.0	14.3	-33.4	-19.4	-16.8	6.2	1.0	32.1	30.8	23.1	25.6	4.8
19.5	14.6	-32.3	-24.3	-20.8	5.4	1.0	32.7	30.6	22.7	25.2	5.1
20.0	14.7	-31.8	-24.9	-16.4	5.0	1.0	32.3	30.6	22.9	25.3	5.4
20.5	14.6	-31.8	-18.4	-14.9	5.0	1.0	32.0	29.5	22.6	25.0	5.7
21.0	14.5	-31.6	-13.8	-16.9	5.0	1.0	30.6	28.4	22.4	24.7	5.8
21.5	14.1	-31.6	-11.8	-15.5	5.1	1.0	31.9	28.2	22.3	24.4	5.5
22.0	13.8	-31.4	-12.8	-12.6	5.1	1.0	33.3	27.1	22.0	24.0	5.4
22.5	13.9	-30.8	-16.3	-13.2	4.9	1.0	31.1	26.3	21.4	23.5	5.7
23.0	14.3	-30.5	-18.8	-17.3	4.8	1.0	30.8	25.2	20.7	23.1	5.9
23.5	14.7	-29.7	-20.3	-16.5	4.3	1.0	29.6	24.2	20.4	23.0	6.3
24.0	14.7	-29.2	-15.7	-14.7	4.0	1.0	28.6	23.4	19.9	22.6	6.7


Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.


GAIN vs. TEMPERATURE
P_{IN} = -25 dBm




GAIN vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



INPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm





INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C





Typical Performance Curves


Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.
















Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.


OUTPUT IP3 vs. TEMPERATURE
P_{OUT} = +16 dBm/TONE




OUTPUT IP3 vs. DEVICE VOLTAGE (V_{DD})
P_{OUT} = +16 dBm/TONE, TEMPERATURE = +25°C




OIP3 vs. P_{OUT}
TEMPERATURE = +25°C




NOISE FIGURE vs. TEMPERATURE



NOISE FIGURE vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C





GAIN VARIATION vs. TEMPERATURE
P_{IN} = -25 dBm



Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +10 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. V_{GG1} was not adjusted at -45°C or +85°C. For over voltage data, V_{GG1} was adjusted until I_{DD} = 300 mA at all V_{DD} levels specified. All data taken with V_{GG2} = +3.5 V.







Typical Performance Curves

Note: Data was taken at V_{DD} = +10 V and V_{GG2} = +3.5 V. At +25°C, V_{GG1} has been adjusted to achieve I_{DD} = 300 mA. Data was taken on a modified TB-AVA-223MPC+ test board using an external bias tee. See Figure 3.


GAIN vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




ISOLATION vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




INPUT RETURN LOSS vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C




OUTPUT RETURN LOSS vs. FREQUENCY
P_{IN} = -25 dBm, TEMPERATURE = +25°C



P1dB vs. FREQUENCY
TEMPERATURE = +25°C




OUTPUT IP3 vs. FREQUENCY
P_{OUT} = +16 dBm/TONE, TEMPERATURE = +25°C




Case Style DG

Outline Dimensions


DG1677-8



TOP VIEW




SIDE VIEW



BOTTOM VIEW

PCB Land Pattern



Suggested Layout,
Tolerance to be within ±0.050[0.002]

NOTES:

1. ▨ DENOTES METALLIZATION

Weight: .056 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl.±0.254[0.01]; 3 Pl.±.0.127[0.005] mm[Inches]

Notes:


1. Case material: Plastic.
2. Termination finish: PPF (NiPdAu Plating 0.5 µm/0.02µm/0.05µm)

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F102

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-023653	NEW RELEASE	11/19/24	ITG	IL
A	ECO-030460	L1 INFO UPDATED TABLE	JUL 26	SK	YP

SUGGESTED MOUNTING CONFIGURATION FOR DG1677-8 CASE STYLE

COMPONENT	SIZE
C1,C13	0603
C2-C6	0402
C7-C10	1812
C11,C12	0201
L1	1105



NOTES:

1. LINE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4003C WITH DIELECTRIC THICKNESS .008"; COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS LINE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-AVA-223MP+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	11/18/24
TOLERANCES ON:	CHECKED	GF	11/18/24
2 PL DECIMALS ±	APPROVED	IL	11/18/24
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits®
13 Neptune Avenue
Brooklyn NY 11235


PL, DG1677-8, TB-AVA-223MP(C)+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-804	A


FILE:	SCALE:	SHEET:
98PL804	5:1	1 OF 1

Evaluation Board and Circuit





DETAIL "A"
LOCATION OF
UNITS COMPONENTS
(SCALE 2:1)



SCHEMATIC DIAGRAM

Components	Size	Value	Part Numbers	Manufacturer
C1,C13	0603	100pF	GRM1885C1H101GA01D	Murata
C2,C3,C4,C5,C6	0402	0.01uF	GRM155R71E103KA01D	Murata
C7,C8,C9,C10	1812	4.7uF	C4532X7S2A475K230KB	TDK Corp
C11,C12,C14,C15	0201	30pF	P21BN300M5S	Knowles
L1	1105	0.22uH	CC19T40K240G5-C	Piconics

Notes:

1. 2.4mm Female Connectors.
2. PCB Material: Roger RO4003C or equivalent, Dielectric constant=3.5, Thickness=0.008 inch

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications **ENV08T10**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to +85° C, -55° to +95°C	Individual Model Data Sheet
Storage Temperature	-65° to 150°C	Individual Model Data Sheet
Moisture Sensitivity: Level 3	Bake at 125°C for 24 hours. Soak at 30°C/60%RH for 192 hours, Reflow 3 cycles at 260°C peak	J-STD-020D
Unbiased HAST	Temperature: 130°C, RH: 85%, Pressure: 33.3 psia Duration: 96 hours	JESD22-A118A, Test Condition A
Temperature Cycling	-65°C to +150°C, Dwell Time: 15 mins 500 cycles	JESD22-A104E, Condition C
HTSL	Temperature: 150°C Duration: 1000 hours	JESD22-A103E, Test Condition B
HTOL	1000 Hours at 125°C	JESD22-A108
ESD HBM	Refer datasheet for classification	JS-001
ESD CDM	Refer datasheet for classification	JESD22-C101
Vibration (Variable Frequency)	Sinusoidal vibration, 20 - 2000 Hz, 4 min sweeps, 16 min along each of 3 axis, amplitude limits of 20g and 0.06 in	MIL-STD-883, Method 2007, Condition A
Drop Test	1m drops onto concrete in final packed box in 6 orientations	--

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Bend Test	1mm deflection for 5 seconds. Board thickness: 0.024", Span: 2.75"	--
Solderability	10x magnification	J-STD-002 Method B, B1
Resistance to Soldering Heat	Sn-Pb Eutectic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020

This document and its contents are the property of Mini-Circuits.