
MMIC SURFACE MOUNT

Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased


THE BIG DEAL

- High Saturated Output Power, Typ. +28.5 dBm
- High Gain, Typ. 20.9 dB
- Single Supply Voltage +6 V at 663 mA
- 5x5 mm 32-Lead QFN-Style Package



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM (Top View)



APPLICATIONS

- 5G MIMO and Backhaul Radio
- Radar, EW, and ECM Defense Systems
- Satellite Communication
- Test and Measurement Equipment

PRODUCT OVERVIEW

Mini-Circuits' AVA-6183MPS+ is a wideband, medium power MMIC amplifier fabricated on a GaAs pHEMT process with high output power and broadband gain. Operating from 6 to 18 GHz, this amplifier features typical +26 dBm P1dB, +28.5 dBm P_{SAT}, and 20.9 dB Gain while operating from a single +6 V power supply. AVA-6183MPS+ is internally matched to 50 Ohms and comes in a 5x5 mm 32-Lead industry standard QFN-style package. These characteristics make it the ideal driver amplifier for a wide range of applications including back haul radio, radar and satellite communications.

KEY FEATURES

Features	Advantages
Self Biased	Simplifies circuit design by eliminating the need for external biasing components, reducing PCB footprint and lowering the cost of integration.
High Gain, Typ. 20.9 dB	The MMIC amplifier's high gain enables fewer system components in receiver signal chains.
High Saturated Output Power, Typ. +28.5 dBm	High saturated output power and high gain make this amplifier ideal as a driver amplifier in 5G MIMO, backhaul radio, satellite communication, and EW applications.
5x5 mm 32-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.

REV. A
ECO-031325
AVA-6183MPS+
MCL NY
261008

Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased

ELECTRICAL SPECIFICATIONS[1] AT +25°C, V_{DD} = +6 V, AND Zo = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		6		18	GHz
Gain	6	19.2	22.3		dB
	9	18.4	21.8		
	12	17.0	20.9		
	15	16.9	20.7		
	18	18.8	23.1		
Input Return Loss	6		15		dB
	9		15		
	12		12		
	15		20		
	18		14		
Output Return Loss	6		14		dB
	9		13		
	12		15		
	15		17		
	18		16		
Isolation	6-18		60.7		dB
Output Power at 1 dB Compression (P1dB)	6		+25.0		dBm
	9		+26.6		
	12		+26.0		
	15		+26.1		
	18		+25.7		
Output Power at Saturation (P_{SAT})[2]	6		+27.9		dBm
	9		+29.4		
	12		+28.5		
	15		+28.8		
	18		+28.7		
Output Third-Order Intercept (OIP3) (P_{OUT} = +12 dBm/Tone)	6		+33.6		dBm
	9		+32.7		
	12		+32.6		
	15		+32.3		
	18		+31.1		
Noise Figure	6		9.0		dB
	9		6.3		
	12		5.6		
	15		5.1		
	18		5.6		
Device Operating Voltage (V_{DD})[3,4]		+5	+6	+7	V
Device Operating Current (I_{DD})[5, 6]			663		mA
Device Current Variation Vs. Temperature[7]			-0.325		mA/°C
Device Current Variation Vs. Voltage[8]			+10.3		µA/mV


1. Tested on Mini-Circuits Characterization Test Board TB-AVA6183MPSC+. See Figure 2. Loss de-embedded to the device reference plane.
2. Defined as output power at which change is 0.1 dB per 1 dB change in input power.
3. $V_{DD} = V_{D1} = V_{D2}$
4. Voltage must be applied to all V_{D1} and V_{D2} pins for standard operation.
5. Current at P_{IN} = -25 dBm. Increases to 810 mA at P_{SAT}.
6. $I_{DD} = I_{D1} + I_{D2}$
7. (Current at +85°C - Current at -55°C)/(+85°C - -55°C).
8. (Current at +7 V – Current at +5 V)/(+7 V - +5 V).


Medium Power Amplifier AVA-6183MPS+


50Ω 6 to 18 GHz Self Biased


TYPICAL PERFORMANCE GRAPHS


Note: All data taken at V_{DD} = +6 V unless noted otherwise.















Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased


TYPICAL PERFORMANCE GRAPHS

Note: All data taken at V_{DD} = +6 V unless noted otherwise.


ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




P1dB vs. TEMPERATURE




P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



P_{SAT} vs. TEMPERATURE



P_{SAT} vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C




Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased


TYPICAL PERFORMANCE GRAPHS

Note: All data taken at V_{DD} = +6 V unless noted otherwise.


OUTPUT IP3 vs. TEMPERATURE
P_{OUT} = +12 dBm/TONE




OUTPUT IP3 vs. DEVICE VOLTAGE (V_{DD})
P_{OUT} = +12 dBm/TONE, TEMPERATURE = +25°C




OUTPUT IP3 vs. P_{OUT}
TEMPERATURE = +25°C




GAIN VARIATION vs. TEMPERATURE
P_{IN} = -25 dBm



NOISE FIGURE vs. TEMPERATURE



NOISE FIGURE vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased

ABSOLUTE MAXIMUM RATINGS[9]

Parameter	Ratings
Operating Temperature	-55°C to +85°C
Storage Temperature	-65°C to +150°C
Total Power Dissipation	4.8 W
Junction Temperature[10]	+175°C
Input Power (CW), V_{DD}[11] = +6 V	+26 dBm
DC Voltage on RF-OUT	+10 V
DC Voltage on RF-IN	+10 V
DC Drain Voltage on V_{DD}	+10 V
DC Drain Current I_{DD}[12]	900 mA

9. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.
10. Peak temperature on top of die.
11. $V_{DD} = V_{D1} = V_{D2}$
12. $I_{DD} = I_{D1} + I_{D2}$

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC})[13]	18.6°C/W

13. Θ_{JC}= (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

	Class	Voltage Range	Reference Standard
Human Body Model (HBM)	1A	250 V < 500 V	ANSI/ESDA/JEDEC JS-001-2023
Charged Device Model (CDM)	C3	> 1000 V	ANSI/ESDA/JEDEC JS-002-2022

ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL3 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C

Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased

FUNCTIONAL DIAGRAM (TOP VIEW)




Figure 1. AVA-6183MPS+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	(Refer to Figure 2)
RF-IN	3	RF-IN pad connects to RF-Input port.
RF-OUT	18	RF-OUT pad connects to RF-Output port.
V_{D1}	12, 29	DC Input pads connects to voltage input ports, V_{D1}.
V_{D2}	15, 26	DC Input pads connects to voltage input ports, V_{D2}.
GND	1, 2, 4, 8, 9, 16, 17, 19, 24, 25, 32, & Paddle	Connects to ground.
NC	5-7, 10, 11, 13, 14, 20-23, 27, 28, 30, 31	Not used internally. Connected to ground on test board.

EVALUATION BOARD




Figure 2. AVA-6183MPS+ Evaluation and Application Circuit

Electrical Parameters and Conditions
Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output Power at Saturation (P_{SAT}), Output IP3 (OIP3), and Noise Figure measured using N52425B PNA-X Microwave Network Analyzer.

Conditions:
1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +12 dBm/tone at output.


Power ON/Power OFF Sequence:
AVA-6183MPS+ is not sensitive to power ON/OFF sequence. V_{D1} and V_{D2} can be applied in any order. All voltage lines may be tied together and applied simultaneously.


Component	Value	Size	Part Number	Manufacturer
C3, C5, C6, C8	100 pF	0603	GRM1885C1H101GA01D	Murata
C2, C4, C7, C9	0.01 µF	0402	GRM155R71E103KA01D	Murata
C1, C10	10 µF	1206	CL31B106KBHNNNE	Samsung
C11, C12	30 pF	0201	P21BNL300M5ST	DLI

Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased

CASE STYLE DRAWING






Weight: .056 Grams

Dimensions are in mm [Inches]. Tolerances: 2 Pl. ± 0.254 [0.01]; 3 Pl. ± 0.127 [0.005] mm [inches]

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Medium Power Amplifier AVA-6183MPS+

50Ω 6 to 18 GHz Self Biased

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DG1677-8. QFN-style package, exposed paddle, Lead Finish: Nickle Palladium Gold
RoHs Status	Compliant
Tape & Reel **Standard quantities available on reel**	F102 7″ reels with 20, 50, 100, 200, or 500 devices 13″ 1,000 devices
Suggested Layout for PCB Design	PL-808
Evaluation Board	TB-AVA6183MPSC+ Gerber File
Environmental Ratings	ENV08T10
Product Handling	The use of no-clean solder is recommended. This package cannot be subjected to aqueous wash.

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 677 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	11.9	-65.3	-7.3	-22.4	216.2	1.2	37.3	21.3	25.0	17.0
4.50	15.8	-64.5	-9.1	-24.2	136.2	1.1	35.7	22.0	25.5	14.2
5.00	19.1	-62.7	-10.8	-17.1	78.6	1.1	34.9	22.7	26.0	12.1
5.50	21.2	-64.0	-12.8	-14.7	73.6	1.0	33.8	23.1	26.1	10.3
6.00	22.5	-62.3	-14.9	-15.0	53.5	1.0	33.4	23.5	26.0	8.9
6.50	23.2	-60.0	-16.4	-17.3	39.3	1.0	33.0	23.9	26.3	7.9
7.00	23.2	-57.3	-17.2	-17.5	29.0	1.0	32.8	24.3	26.6	7.2
7.50	23.0	-59.8	-18.0	-17.0	40.0	1.0	32.9	24.5	26.9	6.8
8.00	22.7	-60.6	-18.0	-15.9	45.1	1.0	32.9	24.6	27.2	6.5
8.50	22.4	-58.7	-16.5	-14.1	36.9	1.0	32.7	24.8	27.5	6.4
9.00	22.3	-64.0	-15.2	-13.2	68.2	1.0	32.6	25.0	27.9	6.2
9.50	22.3	-72.6	-14.8	-13.2	185.8	1.0	32.7	25.0	27.9	5.9
10.00	22.3	-75.1	-15.4	-13.6	247.3	1.0	32.6	24.8	27.7	5.8
10.25	22.3	-72.2	-15.8	-13.8	178.2	1.0	32.7	24.6	27.5	5.7
10.50	22.4	-68.5	-16.2	-14.4	116.8	1.0	32.8	24.6	27.6	5.6
10.75	22.4	-67.3	-16.2	-14.8	102.4	1.0	32.8	24.7	27.7	5.6
11.00	22.3	-61.3	-15.8	-15.7	52.1	1.0	32.9	24.6	27.5	5.5
11.25	22.3	-60.3	-15.1	-16.1	46.6	1.0	32.9	24.7	27.5	5.5
11.50	22.1	-59.9	-13.7	-16.2	45.0	1.0	32.8	24.5	27.4	5.4
11.75	22.0	-60.7	-12.8	-16.0	49.5	1.0	32.8	24.4	27.3	5.4
12.00	21.8	-59.0	-11.8	-15.3	41.4	1.0	32.8	24.5	27.3	5.4
12.25	21.7	-59.6	-11.5	-15.0	44.3	1.0	32.9	24.5	27.3	5.4
12.50	21.5	-58.6	-11.6	-15.1	40.4	1.0	32.8	24.6	27.5	5.3
12.75	21.5	-57.9	-12.0	-15.3	37.9	1.0	32.8	24.6	27.5	5.3
13.00	21.4	-60.5	-13.0	-16.3	52.5	1.0	32.7	24.7	27.5	5.2
13.25	21.4	-61.2	-13.9	-17.2	58.1	1.0	32.7	24.7	27.5	5.2
13.50	21.4	-59.1	-15.4	-18.1	47.1	1.0	32.7	24.8	27.5	5.1
13.75	21.3	-58.4	-16.5	-18.4	43.8	1.0	32.8	24.9	27.6	5.0
14.00	21.3	-61.8	-18.5	-18.2	66.0	1.0	32.8	25.0	27.6	4.9
14.25	21.2	-63.4	-19.9	-17.7	80.2	1.0	32.9	25.0	27.6	4.9
14.50	21.2	-63.0	-22.2	-17.0	76.6	1.0	32.8	24.9	27.5	4.8
14.75	21.2	-63.0	-22.4	-16.9	76.9	1.0	32.7	24.9	27.5	4.8
15.00	21.2	-60.2	-21.7	-17.1	55.9	1.0	32.9	24.9	27.4	4.8
15.25	21.2	-59.1	-20.6	-17.6	49.2	1.0	32.9	24.8	27.4	4.7
15.50	21.3	-60.9	-18.5	-18.8	60.2	1.0	32.9	24.9	27.5	4.7
15.75	21.4	-57.3	-17.1	-19.0	39.1	1.0	33.0	24.8	27.3	4.7
16.00	21.6	-58.4	-15.0	-17.4	43.2	1.0	33.0	24.6	27.2	4.8
16.25	21.7	-55.7	-13.8	-16.3	30.7	1.0	32.9	24.5	27.2	4.8
16.50	22.0	-54.9	-12.7	-14.9	26.4	1.0	32.8	24.3	27.0	4.8
16.75	22.2	-53.2	-12.5	-14.3	21.2	1.0	32.5	24.4	27.1	4.8
17.00	22.6	-53.2	-12.4	-13.8	20.1	1.0	32.2	24.4	27.1	4.8
17.25	22.9	-51.8	-12.7	-13.7	16.7	1.0	31.9	24.4	27.1	4.9
17.50	23.2	-53.0	-13.2	-13.9	18.8	1.0	31.4	24.4	27.1	4.9
17.75	23.3	-50.8	-13.4	-14.3	14.6	1.0	31.6	24.4	27.1	5.0
18.00	23.4	-50.1	-13.7	-14.7	13.4	1.0	31.4	24.4	27.2	5.0
18.25	23.3	-50.7	-13.6	-15.0	14.5	1.0	31.4	24.4	27.7	5.1
18.50	23.1	-51.2	-13.2	-14.8	15.8	1.0	31.0	24.2	27.6	5.3
18.75	22.8	-50.2	-12.8	-14.4	14.4	1.0	30.9	23.8	26.9	5.3
19.00	22.2	-51.5	-12.3	-13.7	17.9	1.0	30.6	23.6	26.5	5.6
19.25	21.6	-52.6	-11.8	-12.8	21.4	1.0	30.6	23.4	26.1	5.8
19.50	20.3	-54.7	-11.9	-12.6	31.5	1.0	31.1	23.1	25.8	6.1
19.75	19.2	-56.5	-12.4	-12.6	45.1	1.0	30.6	22.6	25.0	6.5
20.00	16.7	-61.0	-12.8	-12.4	100.8	1.0	30.7	22.3	24.7	7.2

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 687 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	11.5	-64.2	-7.3	-22.2	199.3	1.2	36.4	22.9	26.4	17.1
4.50	15.5	-69.3	-9.1	-26.2	248.0	1.1	35.0	23.6	27.1	14.4
5.00	18.7	-63.5	-10.8	-17.2	90.1	1.1	34.7	24.4	27.8	12.4
5.50	20.8	-71.4	-12.8	-14.4	181.2	1.0	33.8	24.9	28.1	10.5
6.00	22.1	-59.6	-14.9	-14.7	41.0	1.0	33.4	25.3	28.0	9.1
6.50	22.6	-58.1	-16.3	-17.0	33.3	1.0	33.0	25.7	28.3	8.1
7.00	22.6	-58.3	-17.2	-17.5	34.6	1.0	32.9	26.1	28.4	7.4
7.50	22.4	-58.2	-18.0	-17.2	35.7	1.0	32.9	26.5	28.6	7.0
8.00	22.1	-62.6	-17.9	-16.1	60.8	1.0	32.9	26.6	28.8	6.7
8.50	21.7	-61.6	-16.5	-14.2	55.5	1.0	32.4	26.9	29.2	6.5
9.00	21.5	-64.1	-15.2	-13.2	75.4	1.0	32.4	26.9	29.4	6.3
9.50	21.5	-72.4	-14.8	-13.1	199.2	1.0	32.5	26.8	29.2	6.1
10.00	21.4	-71.4	-15.2	-13.5	179.5	1.0	32.3	26.4	28.8	5.9
10.25	21.4	-81.6	-15.6	-13.6	581.2	1.0	32.4	26.2	28.6	5.9
10.50	21.4	-71.1	-16.0	-14.2	176.0	1.0	32.4	26.2	28.6	5.8
10.75	21.4	-70.2	-16.1	-14.5	158.9	1.0	32.4	26.3	28.8	5.7
11.00	21.3	-64.4	-15.7	-15.3	83.1	1.0	32.6	26.2	28.7	5.6
11.25	21.2	-62.4	-15.0	-15.7	66.6	1.0	32.4	26.3	28.7	5.6
11.50	21.0	-61.1	-13.7	-15.8	58.5	1.0	32.4	26.1	28.5	5.5
11.75	20.9	-62.3	-12.8	-15.6	67.5	1.0	32.4	26.0	28.4	5.5
12.00	20.7	-61.3	-12.0	-15.0	61.0	1.0	32.4	26.1	28.4	5.6
12.25	20.6	-58.7	-11.7	-14.7	45.6	1.0	32.4	26.1	28.5	5.5
12.50	20.5	-59.1	-11.8	-14.8	48.6	1.0	32.2	26.2	28.7	5.5
12.75	20.4	-59.1	-12.3	-15.1	49.2	1.0	32.3	26.1	28.7	5.4
13.00	20.4	-59.8	-13.3	-16.1	54.9	1.0	32.2	26.2	28.7	5.3
13.25	20.4	-59.7	-14.2	-17.0	55.4	1.0	32.3	26.2	28.7	5.2
13.50	20.3	-60.2	-15.7	-18.1	59.7	1.0	32.3	26.2	28.7	5.2
13.75	20.3	-61.1	-16.7	-18.4	67.2	1.0	32.3	26.4	28.8	5.1
14.00	20.3	-66.3	-18.6	-18.3	123.6	1.0	32.4	26.5	28.9	5.1
14.25	20.3	-61.0	-20.0	-17.9	67.3	1.0	32.4	26.5	29.0	5.1
14.50	20.3	-58.9	-21.9	-17.2	53.1	1.0	32.5	26.4	29.0	5.0
14.75	20.3	-62.4	-22.0	-17.2	79.9	1.0	32.2	26.4	28.9	5.0
15.00	20.4	-63.5	-21.5	-17.4	89.9	1.0	32.4	26.3	28.9	4.9
15.25	20.5	-61.3	-20.5	-17.8	69.3	1.0	32.4	26.3	28.9	4.9
15.50	20.6	-59.8	-18.5	-18.9	57.5	1.0	32.3	26.3	28.9	4.9
15.75	20.7	-57.2	-17.1	-19.1	41.9	1.0	32.5	26.2	28.8	4.9
16.00	20.9	-59.9	-15.0	-17.5	54.9	1.0	32.4	26.1	28.7	4.9
16.25	21.1	-56.3	-13.9	-16.4	35.4	1.0	32.3	26.0	28.6	5.0
16.50	21.4	-55.6	-12.8	-14.9	30.7	1.0	32.2	25.7	28.3	5.0
16.75	21.7	-55.1	-12.6	-14.3	28.1	1.0	31.9	25.8	28.4	5.0
17.00	22.1	-52.2	-12.4	-13.9	19.2	1.0	31.6	25.8	28.4	5.0
17.25	22.4	-52.0	-12.8	-13.8	18.2	1.0	31.5	25.9	28.5	5.1
17.50	22.6	-53.0	-13.3	-14.0	20.0	1.0	31.0	25.9	28.5	5.1
17.75	22.8	-50.8	-13.4	-14.5	15.5	1.0	31.1	26.0	28.6	5.1
18.00	22.8	-51.1	-13.7	-14.9	16.4	1.0	31.0	26.0	28.8	5.2
18.25	22.6	-50.6	-13.6	-15.1	15.5	1.0	30.8	26.2	29.4	5.2
18.50	22.3	-51.2	-13.2	-14.8	17.3	1.0	30.7	26.1	29.3	5.4
18.75	22.0	-51.0	-12.7	-14.4	17.4	1.0	30.3	25.7	28.5	5.5
19.00	21.3	-52.6	-12.2	-13.6	22.4	1.0	30.2	25.5	28.2	5.8
19.25	20.6	-52.5	-11.8	-12.8	23.7	1.0	30.1	25.4	27.9	6.0
19.50	19.3	-56.4	-11.9	-12.7	43.4	1.0	30.0	25.2	27.6	6.3
19.75	18.1	-57.0	-12.5	-12.8	54.1	1.0	29.7	24.7	26.9	6.7
20.00	15.8	-63.9	-12.8	-12.5	156.8	1.0	29.6	24.5	26.5	7.4

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 697 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	11.06	-65.8	-7.3	-21.8	250.8	1.2	36.1	24.0	27.4	17.3
4.50	15.05	-67.9	-9.1	-28.0	221.9	1.1	35.3	24.8	28.3	14.6
5.00	18.31	-61.9	-10.8	-17.2	78.8	1.1	34.8	25.7	29.0	12.5
5.50	20.33	-70.2	-12.8	-14.2	164.6	1.0	33.9	26.2	29.4	10.7
6.00	21.56	-62.1	-14.8	-14.3	57.8	1.0	33.5	26.7	29.4	9.3
6.50	22.07	-58.2	-16.3	-16.7	36.0	1.0	33.2	27.2	29.6	8.3
7.00	21.98	-58.6	-17.1	-17.6	38.5	1.0	33.1	27.7	29.7	7.6
7.50	21.75	-57.9	-17.9	-17.4	37.1	1.0	33.1	28.2	29.8	7.2
8.00	21.39	-61.0	-17.9	-16.2	54.6	1.0	33.1	28.3	30.0	6.9
8.50	21.06	-61.8	-16.4	-14.3	61.8	1.0	32.7	28.3	30.3	6.7
9.00	20.80	-63.7	-15.2	-13.2	78.3	1.0	32.5	28.3	30.4	6.4
9.50	20.67	-65.0	-14.7	-13.0	92.7	1.0	32.6	28.1	30.0	6.3
10.00	20.59	-69.3	-15.2	-13.3	154.3	1.0	32.4	27.7	29.4	6.1
10.25	20.56	-70.9	-15.5	-13.4	187.2	1.0	32.5	27.4	29.2	6.0
10.50	20.53	-69.0	-15.9	-13.9	153.0	1.0	32.4	27.4	29.2	6.0
10.75	20.49	-64.5	-16.0	-14.3	92.0	1.0	32.5	27.5	29.3	5.9
11.00	20.39	-64.6	-15.6	-15.0	94.6	1.0	32.6	27.3	29.2	5.8
11.25	20.28	-65.5	-15.0	-15.4	106.4	1.0	32.5	27.3	29.2	5.8
11.50	20.07	-61.0	-13.7	-15.5	64.6	1.0	32.4	27.2	29.1	5.8
11.75	19.91	-62.1	-12.9	-15.3	73.3	1.0	32.4	27.1	29.1	5.7
12.00	19.69	-60.4	-12.1	-14.7	61.5	1.0	32.4	27.2	29.1	5.7
12.25	19.59	-60.6	-11.8	-14.5	63.7	1.0	32.4	27.1	29.1	5.7
12.50	19.49	-62.7	-12.0	-14.6	82.3	1.0	32.2	27.2	29.3	5.7
12.75	19.45	-60.2	-12.5	-14.8	62.7	1.0	32.3	27.2	29.3	5.6
13.00	19.44	-60.4	-13.5	-15.9	65.7	1.0	32.2	27.3	29.4	5.5
13.25	19.41	-63.0	-14.4	-16.8	90.2	1.0	32.2	27.2	29.4	5.5
13.50	19.42	-62.2	-15.9	-18.0	83.5	1.0	32.4	27.2	29.3	5.4
13.75	19.42	-60.6	-16.9	-18.4	70.4	1.0	32.4	27.4	29.6	5.3
14.00	19.41	-60.0	-18.7	-18.4	66.0	1.0	32.4	27.5	29.7	5.3
14.25	19.42	-60.1	-19.9	-18.0	67.4	1.0	32.4	27.5	29.8	5.3
14.50	19.48	-60.8	-21.7	-17.4	72.6	1.0	32.4	27.5	29.8	5.2
14.75	19.52	-63.0	-21.8	-17.4	93.9	1.0	32.4	27.5	29.9	5.2
15.00	19.62	-60.1	-21.3	-17.5	66.6	1.0	32.4	27.4	29.8	5.1
15.25	19.72	-61.2	-20.4	-18.0	74.7	1.0	32.4	27.4	29.9	5.2
15.50	19.90	-61.6	-18.5	-19.1	76.7	1.0	32.3	27.4	30.0	5.1
15.75	20.04	-58.9	-17.1	-19.2	55.2	1.0	32.4	27.3	29.9	5.2
16.00	20.28	-56.1	-15.0	-17.6	38.5	1.0	32.2	27.2	29.7	5.1
16.25	20.47	-56.0	-13.9	-16.4	36.8	1.0	32.1	27.2	29.6	5.2
16.50	20.81	-53.4	-12.8	-14.9	25.5	1.0	32.2	27.0	29.3	5.3
16.75	21.08	-56.1	-12.6	-14.3	33.9	1.0	31.8	27.1	29.4	5.2
17.00	21.50	-53.5	-12.4	-14.0	23.8	1.0	31.3	27.0	29.4	5.3
17.25	21.75	-53.8	-12.8	-13.9	24.1	1.0	31.2	27.2	29.5	5.3
17.50	22.00	-52.8	-13.3	-14.2	21.1	1.0	30.9	27.4	29.6	5.3
17.75	22.10	-52.8	-13.4	-14.6	21.2	1.0	30.9	27.7	29.8	5.4
18.00	22.05	-50.4	-13.7	-15.1	16.2	1.0	30.8	27.8	29.9	5.4
18.25	21.90	-50.8	-13.6	-15.3	17.4	1.0	30.6	28.2	30.5	5.5
18.50	21.52	-51.2	-13.1	-14.9	18.9	1.0	30.7	28.1	30.7	5.7
18.75	21.14	-51.9	-12.6	-14.3	21.3	1.0	30.5	27.7	30.1	5.7
19.00	20.36	-52.8	-12.2	-13.6	25.4	1.0	30.5	27.6	29.7	6.0
19.25	19.68	-53.7	-11.8	-12.8	30.3	1.0	30.4	27.4	29.3	6.2
19.50	18.32	-56.5	-12.0	-12.8	49.6	1.0	30.2	27.3	29.0	6.6
19.75	17.14	-61.2	-12.5	-12.9	98.5	1.0	30.1	26.7	28.3	6.9
20.00	14.85	-58.0	-12.7	-12.7	88.5	1.0	30.2	26.4	27.8	7.7

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 695 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	13.42	-66.9	-7.6	-20.3	224.5	1.2	35.2	20.4	24.8	15.6
4.50	17.50	-71.0	-9.3	-21.7	243.8	1.1	35.2	21.1	24.9	12.9
5.00	20.79	-64.3	-10.4	-16.0	78.1	1.1	34.9	22.0	25.3	10.8
5.50	23.06	-60.4	-12.2	-14.1	39.2	1.0	35.2	22.7	25.4	9.0
6.00	24.55	-58.7	-14.2	-14.4	27.9	1.0	35.0	23.1	25.3	7.5
6.50	25.31	-60.2	-15.6	-16.0	31.1	1.0	35.0	23.6	25.7	6.5
7.00	25.37	-59.0	-16.4	-15.9	27.3	1.0	35.0	23.7	25.9	5.9
7.50	25.24	-58.4	-17.2	-16.1	26.0	1.0	35.1	23.8	26.4	5.4
8.00	24.99	-59.5	-17.4	-16.1	30.5	1.0	35.2	23.9	26.7	5.2
8.50	24.68	-60.1	-15.7	-13.6	32.9	1.0	34.9	23.9	26.8	5.0
9.00	24.50	-61.7	-14.1	-11.8	39.4	1.0	34.8	24.0	27.3	4.8
9.50	24.55	-73.3	-13.7	-12.3	151.2	1.0	35.0	24.1	27.6	4.6
10.00	24.72	-64.3	-14.7	-14.2	54.2	1.0	35.4	23.9	27.4	4.5
10.25	24.79	-66.0	-15.2	-14.7	66.0	1.0	35.9	23.8	27.2	4.4
10.50	24.88	-77.1	-16.1	-15.1	237.5	1.0	35.8	23.9	27.4	4.3
10.75	24.91	-67.2	-16.4	-14.9	75.8	1.0	35.9	24.1	27.5	4.2
11.00	24.91	-62.6	-16.0	-14.7	44.2	1.0	35.9	24.0	27.3	4.2
11.25	24.85	-65.1	-15.0	-14.8	59.3	1.0	35.6	24.0	27.0	4.1
11.50	24.75	-58.6	-13.4	-15.6	28.3	1.0	35.5	23.8	27.1	4.2
11.75	24.65	-61.0	-12.4	-16.3	37.4	1.0	35.5	23.7	27.0	4.1
12.00	24.48	-60.4	-11.3	-16.8	35.0	1.1	35.3	23.6	26.9	4.1
12.25	24.40	-60.3	-10.8	-16.6	34.8	1.1	35.3	23.7	26.8	4.1
12.50	24.28	-59.2	-10.8	-15.7	30.9	1.1	34.8	23.8	27.0	4.0
12.75	24.21	-59.3	-11.0	-15.1	31.8	1.0	34.9	23.8	26.9	4.0
13.00	24.15	-58.9	-11.9	-14.8	30.8	1.0	34.8	23.9	27.0	3.9
13.25	24.12	-58.4	-12.9	-15.2	29.8	1.0	34.8	23.9	26.9	3.8
13.50	24.11	-60.3	-14.6	-16.5	38.5	1.0	34.8	23.9	26.8	3.8
13.75	24.10	-59.3	-15.9	-18.0	34.6	1.0	34.9	24.1	26.7	3.7
14.00	24.07	-62.5	-18.2	-20.8	51.3	1.0	34.9	24.1	26.7	3.7
14.25	24.04	-60.3	-20.0	-22.1	40.5	1.0	34.9	24.1	26.7	3.6
14.50	23.99	-62.1	-23.2	-19.8	50.1	1.0	35.0	24.0	26.6	3.5
14.75	23.93	-61.9	-24.4	-17.7	49.0	1.0	34.8	24.0	26.6	3.5
15.00	23.87	-60.6	-23.6	-15.4	42.1	1.0	34.7	23.9	26.5	3.4
15.25	23.85	-61.7	-21.7	-14.6	47.7	1.0	34.4	23.8	26.5	3.4
15.50	23.90	-59.7	-18.7	-15.0	37.3	1.0	34.6	23.8	26.6	3.4
15.75	23.99	-58.1	-17.1	-16.0	30.9	1.0	35.0	23.7	26.4	3.4
16.00	24.23	-57.3	-15.2	-18.7	27.4	1.0	34.8	23.5	26.3	3.4
16.25	24.42	-57.1	-14.1	-20.6	26.2	1.0	34.9	23.4	26.2	3.4
16.50	24.75	-56.8	-12.9	-17.6	23.9	1.0	34.2	23.2	26.0	3.4
16.75	24.98	-53.7	-12.5	-15.2	16.0	1.0	34.1	23.3	26.1	3.4
17.00	25.38	-54.8	-12.1	-12.8	16.8	1.0	34.0	23.3	25.7	3.4
17.25	25.66	-53.4	-12.2	-12.0	13.8	1.0	34.1	23.4	25.5	3.5
17.50	26.03	-51.5	-12.6	-11.2	10.6	1.0	33.7	23.4	25.4	3.5
17.75	26.28	-52.6	-12.6	-11.4	11.8	1.0	33.8	23.5	25.5	3.5
18.00	26.57	-50.3	-13.3	-13.0	9.1	1.0	34.0	23.5	25.6	3.5
18.25	26.70	-49.5	-13.6	-15.6	8.4	1.0	34.1	23.6	25.8	3.6
18.50	26.70	-50.4	-13.5	-19.1	9.5	1.0	33.8	23.6	26.0	3.6
18.75	26.56	-50.4	-13.1	-17.7	9.5	1.0	34.2	23.3	25.5	3.8
19.00	26.11	-50.8	-12.5	-14.5	10.2	1.0	34.9	23.0	25.1	3.8
19.25	25.62	-50.8	-11.5	-11.7	10.4	1.0	35.9	22.9	24.8	4.0
19.50	24.45	-52.3	-10.4	-9.6	13.2	1.0	38.6	22.7	24.7	4.3
19.75	23.36	-55.5	-10.5	-9.1	21.4	0.9	39.0	22.2	24.2	4.6
20.00	21.15	-58.8	-11.8	-9.9	42.4	1.0	38.5	21.9	24.0	5.2

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 714 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	12.81	-64.0	-7.6	-20.2	174.0	1.2	37.2	22.5	26.6	15.8
4.50	16.89	-68.9	-9.3	-22.7	204.6	1.1	35.1	23.1	27.2	13.0
5.00	20.18	-62.4	-10.4	-16.1	67.5	1.1	34.6	24.0	27.8	11.0
5.50	22.40	-68.2	-12.1	-14.0	103.4	1.0	33.7	24.5	28.1	9.1
6.00	23.81	-60.6	-14.1	-14.3	37.9	1.0	33.3	24.9	28.0	7.7
6.50	24.48	-57.4	-15.5	-15.9	24.9	1.0	32.8	25.3	28.4	6.7
7.00	24.48	-59.8	-16.3	-15.9	33.1	1.0	32.6	25.6	28.5	6.1
7.50	24.30	-58.9	-17.1	-16.2	30.6	1.0	32.6	25.8	28.7	5.6
8.00	24.02	-63.0	-17.3	-16.3	50.9	1.0	32.7	26.0	29.0	5.4
8.50	23.68	-61.2	-15.7	-13.7	42.0	1.0	32.5	26.1	29.3	5.2
9.00	23.46	-61.6	-14.1	-11.9	43.8	1.0	32.4	26.2	29.7	5.0
9.50	23.46	-66.7	-13.6	-12.2	79.9	1.0	32.3	26.2	29.5	4.8
10.00	23.56	-90.3	-14.4	-14.0	1229.1	1.0	32.2	25.9	29.1	4.6
10.25	23.59	-69.4	-15.0	-14.5	112.3	1.0	32.3	25.8	28.8	4.5
10.50	23.63	-72.9	-15.7	-14.9	168.1	1.0	32.4	25.9	28.9	4.5
10.75	23.61	-63.7	-16.0	-14.6	58.8	1.0	32.4	26.0	29.1	4.4
11.00	23.54	-67.5	-15.5	-14.4	90.8	1.0	32.5	26.0	29.0	4.3
11.25	23.44	-65.6	-14.6	-14.5	73.1	1.0	32.4	26.0	29.1	4.3
11.50	23.28	-60.1	-13.1	-15.2	39.6	1.0	32.3	25.9	29.0	4.3
11.75	23.16	-60.2	-12.2	-16.0	40.2	1.0	32.3	25.9	28.9	4.3
12.00	22.97	-58.8	-11.3	-16.6	34.7	1.0	32.3	25.9	28.9	4.3
12.25	22.88	-60.1	-11.0	-16.4	40.6	1.1	32.3	25.9	28.8	4.2
12.50	22.75	-61.1	-11.1	-15.5	46.0	1.0	32.1	26.1	29.1	4.2
12.75	22.68	-59.3	-11.5	-14.8	37.8	1.0	32.0	26.0	29.1	4.1
13.00	22.62	-60.1	-12.4	-14.5	42.7	1.0	32.0	26.0	29.1	4.1
13.25	22.58	-60.7	-13.4	-15.0	46.6	1.0	32.0	26.0	29.0	4.0
13.50	22.58	-60.8	-15.3	-16.3	48.8	1.0	32.1	26.0	28.8	3.9
13.75	22.59	-60.0	-16.6	-17.9	45.2	1.0	32.1	26.1	28.9	3.9
14.00	22.58	-63.1	-18.9	-21.1	65.8	1.0	32.1	26.1	28.9	3.8
14.25	22.57	-61.3	-20.7	-22.5	53.7	1.0	32.1	26.1	29.1	3.7
14.50	22.56	-62.8	-23.5	-20.0	64.2	1.0	32.1	26.0	29.0	3.7
14.75	22.53	-63.0	-24.0	-17.8	65.1	1.0	32.1	25.9	28.9	3.7
15.00	22.50	-62.5	-22.7	-15.4	61.2	1.0	32.1	25.8	28.8	3.7
15.25	22.51	-63.3	-21.1	-14.6	66.5	1.0	32.1	25.7	28.8	3.6
15.50	22.62	-60.7	-18.4	-15.0	48.8	1.0	32.1	25.8	28.9	3.6
15.75	22.73	-58.5	-16.9	-16.0	37.3	1.0	32.2	25.6	28.6	3.6
16.00	23.02	-58.8	-15.2	-18.9	37.5	1.0	32.3	25.4	28.5	3.6
16.25	23.24	-56.5	-14.1	-21.1	28.2	1.0	32.1	25.3	28.3	3.6
16.50	23.60	-56.0	-13.0	-17.8	25.1	1.0	32.2	25.0	28.1	3.6
16.75	23.85	-56.8	-12.7	-15.2	26.1	1.0	31.9	25.1	28.1	3.6
17.00	24.24	-54.4	-12.2	-12.7	18.4	1.0	31.6	25.0	28.0	3.6
17.25	24.51	-51.7	-12.3	-11.8	12.9	1.0	31.4	25.1	27.9	3.6
17.50	24.84	-51.8	-12.6	-11.1	12.6	1.0	30.9	25.1	27.9	3.7
17.75	25.05	-52.4	-12.7	-11.4	13.3	1.0	31.0	25.2	28.2	3.7
18.00	25.29	-50.6	-13.3	-13.1	10.9	1.0	30.8	25.2	28.4	3.8
18.25	25.38	-50.7	-13.7	-16.0	11.2	1.0	30.8	25.4	29.1	3.8
18.50	25.30	-49.6	-13.5	-19.8	10.2	1.0	30.7	25.4	29.2	3.8
18.75	25.09	-50.7	-12.9	-17.9	11.7	1.0	30.6	25.1	28.3	3.9
19.00	24.49	-52.5	-12.2	-14.1	14.9	1.0	30.4	25.0	28.1	4.1
19.25	23.86	-51.5	-11.3	-11.4	13.5	1.0	30.7	24.9	27.9	4.3
19.50	22.52	-53.2	-10.5	-9.4	18.2	1.0	31.7	24.8	27.7	4.6
19.75	21.35	-54.4	-10.7	-9.1	23.8	0.9	31.2	24.4	27.0	4.9
20.00	19.14	-60.3	-11.9	-10.0	64.0	1.0	31.3	24.3	26.7	5.5

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 732 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	12.35	-67.5	-7.6	-20.0	272.1	1.2	35.3	24.1	27.7	15.9
4.50	16.45	-70.3	-9.3	-24.2	252.5	1.1	34.4	24.9	28.5	13.2
5.00	19.75	-60.0	-10.4	-16.2	53.6	1.1	34.2	25.8	29.2	11.2
5.50	21.92	-64.4	-12.1	-13.9	70.2	1.0	33.3	26.3	29.6	9.3
6.00	23.26	-62.1	-14.0	-14.2	47.7	1.0	32.8	26.8	29.6	7.9
6.50	23.86	-59.0	-15.5	-15.7	31.9	1.0	32.5	27.3	29.9	6.9
7.00	23.80	-58.3	-16.3	-15.9	30.0	1.0	32.3	27.7	29.9	6.2
7.50	23.59	-57.3	-17.1	-16.3	27.9	1.0	32.2	28.2	30.0	5.8
8.00	23.29	-57.4	-17.3	-16.5	29.0	1.0	32.3	28.4	30.3	5.5
8.50	22.92	-60.5	-15.7	-13.8	42.5	1.0	31.9	28.6	30.5	5.4
9.00	22.65	-63.9	-14.0	-11.8	63.0	1.0	31.6	28.7	30.6	5.2
9.50	22.60	-75.9	-13.6	-12.1	254.6	1.0	31.7	28.5	30.3	5.0
10.00	22.64	-76.0	-14.3	-13.9	265.2	1.0	31.4	28.2	29.8	4.8
10.25	22.65	-65.2	-14.8	-14.4	76.6	1.0	31.5	28.0	29.5	4.7
10.50	22.65	-75.3	-15.5	-14.7	248.7	1.0	31.5	28.0	29.6	4.7
10.75	22.60	-65.7	-15.7	-14.4	82.7	1.0	31.6	28.2	29.8	4.6
11.00	22.48	-63.2	-15.3	-14.1	62.5	1.0	31.6	28.1	29.8	4.5
11.25	22.36	-61.6	-14.4	-14.1	52.3	1.0	31.5	28.1	29.9	4.5
11.50	22.17	-63.1	-13.0	-14.9	63.3	1.0	31.4	28.0	29.7	4.4
11.75	22.04	-60.9	-12.2	-15.7	49.8	1.0	31.4	27.9	29.7	4.5
12.00	21.85	-59.5	-11.4	-16.4	42.7	1.0	31.4	28.0	29.8	4.5
12.25	21.75	-60.4	-11.2	-16.2	48.1	1.0	31.4	27.9	29.7	4.4
12.50	21.62	-59.7	-11.3	-15.2	44.6	1.0	31.0	28.0	30.0	4.3
12.75	21.55	-59.7	-11.7	-14.6	45.5	1.0	31.0	28.0	30.1	4.4
13.00	21.48	-61.9	-12.7	-14.2	59.6	1.0	31.2	28.1	30.1	4.3
13.25	21.46	-59.9	-13.8	-14.7	48.6	1.0	31.0	28.0	30.0	4.2
13.50	21.48	-59.9	-15.6	-16.1	49.5	1.0	31.4	27.9	29.9	4.1
13.75	21.50	-60.0	-17.0	-17.9	50.9	1.0	31.4	28.0	30.1	4.0
14.00	21.51	-60.0	-19.3	-21.4	51.7	1.0	31.3	28.1	30.2	4.0
14.25	21.52	-60.4	-20.9	-23.0	54.7	1.0	31.3	28.1	30.5	3.9
14.50	21.54	-64.8	-23.4	-20.2	91.1	1.0	31.4	28.0	30.4	3.9
14.75	21.53	-63.1	-23.6	-17.9	74.1	1.0	31.4	28.0	30.4	3.9
15.00	21.54	-59.9	-22.4	-15.5	50.8	1.0	31.4	27.9	30.3	3.8
15.25	21.58	-59.5	-20.8	-14.6	47.8	1.0	31.4	27.8	30.4	3.8
15.50	21.71	-62.7	-18.2	-15.0	68.0	1.0	31.3	27.8	30.5	3.8
15.75	21.86	-59.5	-16.8	-16.0	46.4	1.0	31.4	27.7	30.3	3.8
16.00	22.18	-58.0	-15.1	-19.1	37.9	1.0	31.3	27.5	30.1	3.8
16.25	22.42	-58.4	-14.1	-21.5	38.4	1.0	31.1	27.4	30.0	3.8
16.50	22.81	-55.0	-13.0	-18.0	24.5	1.0	31.3	27.1	29.6	3.8
16.75	23.07	-56.3	-12.7	-15.2	27.0	1.0	31.0	27.1	29.6	3.8
17.00	23.45	-54.2	-12.3	-12.7	19.6	1.0	30.6	27.0	29.5	3.8
17.25	23.71	-54.5	-12.4	-11.8	19.5	1.0	30.5	27.1	29.5	3.9
17.50	24.00	-54.3	-12.5	-11.0	18.4	1.0	30.1	27.2	29.6	3.9
17.75	24.18	-51.0	-12.6	-11.4	12.5	1.0	30.0	27.5	29.8	4.0
18.00	24.37	-50.8	-13.4	-13.2	12.4	1.0	29.8	27.6	30.0	4.0
18.25	24.42	-50.5	-13.7	-16.1	12.2	1.0	29.6	28.0	30.6	4.0
18.50	24.27	-50.6	-13.4	-20.1	12.8	1.0	29.9	28.1	31.0	4.0
18.75	24.00	-50.9	-12.8	-18.0	13.6	1.0	29.6	27.7	30.3	4.1
19.00	23.29	-52.5	-12.0	-13.8	16.9	1.0	29.6	27.6	29.8	4.3
19.25	22.59	-53.4	-11.2	-11.1	19.3	1.0	29.6	27.6	29.4	4.5
19.50	21.16	-55.2	-10.5	-9.3	26.8	1.0	29.5	27.5	29.2	4.8
19.75	19.97	-56.4	-10.9	-9.1	35.5	0.9	29.5	27.1	28.6	5.1
20.00	17.80	-62.9	-11.9	-10.1	100.7	1.0	29.5	26.9	28.2	5.8

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 662 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	11.17	-65.0	-7.3	-23.5	224.7	1.2	35.1	21.4	24.8	17.9
4.50	15.07	-63.3	-9.2	-25.6	128.4	1.1	35.2	22.1	25.4	15.2
5.00	18.28	-64.8	-11.1	-17.2	109.3	1.1	34.7	22.8	26.0	13.2
5.50	20.31	-61.0	-13.3	-14.6	57.3	1.0	34.9	23.2	26.2	11.3
6.00	21.58	-60.0	-15.3	-14.8	45.3	1.0	34.7	23.5	26.0	9.8
6.50	22.13	-55.9	-16.7	-17.4	27.2	1.0	34.4	23.9	26.3	8.9
7.00	22.10	-58.7	-17.5	-18.1	38.3	1.0	34.5	24.3	26.5	8.2
7.50	21.92	-61.0	-18.3	-17.7	51.3	1.0	34.6	24.6	26.8	7.8
8.00	21.62	-60.9	-18.3	-16.2	52.7	1.0	34.7	24.7	27.0	7.5
8.50	21.35	-62.3	-16.8	-14.4	63.0	1.0	34.6	24.8	27.3	7.3
9.00	21.19	-64.4	-15.6	-13.7	80.8	1.0	34.7	24.9	27.6	7.1
9.50	21.13	-72.7	-15.1	-13.5	212.6	1.0	34.6	24.8	27.5	7.0
10.00	21.14	-67.3	-15.5	-13.6	115.1	1.0	34.8	24.4	27.3	6.7
10.25	21.14	-70.2	-15.8	-13.5	160.4	1.0	35.1	24.2	27.1	6.7
10.50	21.18	-69.0	-16.2	-14.0	141.3	1.0	35.1	24.1	27.1	6.6
10.75	21.19	-65.1	-16.4	-14.5	90.9	1.0	35.1	24.2	27.1	6.5
11.00	21.18	-61.5	-16.1	-15.6	60.3	1.0	35.3	24.1	27.0	6.4
11.25	21.11	-61.4	-15.5	-16.2	60.2	1.0	35.1	24.1	27.0	6.4
11.50	20.97	-59.1	-14.2	-16.3	46.8	1.0	35.2	23.9	26.9	6.3
11.75	20.85	-58.5	-13.3	-15.9	43.8	1.0	35.1	23.8	26.8	6.3
12.00	20.64	-59.5	-12.3	-15.0	49.8	1.0	35.1	23.9	26.8	6.3
12.25	20.55	-59.2	-11.9	-14.7	48.2	1.0	35.0	23.8	26.8	6.3
12.50	20.45	-58.7	-11.9	-14.9	46.4	1.0	34.5	23.9	27.0	6.3
12.75	20.42	-58.2	-12.3	-15.3	44.6	1.0	34.8	23.9	27.0	6.2
13.00	20.39	-59.0	-13.3	-16.6	50.0	1.0	34.6	24.0	27.0	6.2
13.25	20.36	-57.5	-14.1	-17.6	42.9	1.0	34.7	24.1	27.1	6.1
13.50	20.33	-61.1	-15.6	-18.5	66.3	1.0	34.7	24.2	27.1	6.0
13.75	20.30	-55.3	-16.5	-18.5	34.4	1.0	34.7	24.3	27.2	6.0
14.00	20.25	-60.1	-18.5	-17.8	60.5	1.0	34.5	24.4	27.2	6.0
14.25	20.22	-59.3	-19.9	-17.1	56.1	1.0	34.6	24.5	27.2	6.0
14.50	20.21	-60.2	-22.0	-16.4	62.6	1.0	34.4	24.5	27.1	5.9
14.75	20.21	-59.1	-22.2	-16.5	55.0	1.0	34.5	24.5	27.1	5.9
15.00	20.26	-59.2	-21.9	-17.2	55.6	1.0	34.6	24.5	27.0	5.8
15.25	20.32	-58.7	-21.1	-18.2	52.5	1.0	34.4	24.5	27.1	5.8
15.50	20.45	-60.9	-19.2	-20.1	67.4	1.0	34.4	24.5	27.1	5.8
15.75	20.54	-57.0	-17.6	-20.1	42.1	1.0	34.6	24.5	27.0	5.8
16.00	20.70	-55.2	-15.3	-17.4	33.4	1.0	34.3	24.3	26.9	5.9
16.25	20.84	-56.3	-14.0	-15.9	36.5	1.0	34.2	24.2	26.9	5.9
16.50	21.10	-55.9	-12.8	-14.5	33.2	1.0	34.0	24.0	26.7	6.0
16.75	21.33	-53.7	-12.6	-14.0	25.0	1.0	33.8	24.1	26.9	6.0
17.00	21.71	-52.7	-12.5	-13.8	21.4	1.0	33.6	24.1	27.0	6.0
17.25	21.94	-51.5	-12.8	-13.9	18.4	1.0	33.3	24.2	27.0	6.0
17.50	22.17	-50.6	-13.3	-14.4	16.3	1.0	33.2	24.2	27.0	6.1
17.75	22.26	-51.9	-13.5	-15.0	19.0	1.0	33.2	24.2	27.0	6.1
18.00	22.23	-49.9	-13.9	-15.3	15.4	1.0	33.0	24.2	27.1	6.2
18.25	22.11	-49.7	-13.9	-15.3	15.1	1.0	33.1	24.2	27.4	6.3
18.50	21.79	-50.4	-13.7	-14.8	17.0	1.0	32.9	24.0	27.2	6.4
18.75	21.47	-50.0	-13.4	-14.3	16.8	1.0	32.9	23.6	26.7	6.5
19.00	20.79	-52.1	-12.9	-13.8	22.8	1.0	33.0	23.4	26.3	6.8
19.25	20.15	-52.2	-12.6	-13.2	24.9	1.0	32.8	23.1	25.9	7.0
19.50	18.83	-56.6	-12.6	-13.6	48.4	1.0	33.5	22.9	25.5	7.5
19.75	17.62	-55.8	-13.0	-13.8	50.9	1.0	32.6	22.3	24.8	7.9
20.00	15.13	-61.2	-12.8	-12.9	126.3	1.0	32.7	22.0	24.4	8.7

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 668 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	10.45	-79.6	-7.3	-22.7	1315.5	1.2	36.3	22.8	26.1	18.1
4.50	14.37	-67.6	-9.2	-26.9	227.3	1.1	35.4	23.6	26.9	15.5
5.00	17.58	-63.9	-11.1	-17.2	106.5	1.1	35.0	24.4	27.6	13.3
5.50	19.55	-59.5	-13.2	-14.5	52.4	1.0	34.1	24.8	27.9	11.5
6.00	20.76	-59.6	-15.2	-14.6	47.3	1.0	33.8	25.2	27.8	10.2
6.50	21.25	-58.8	-16.6	-17.2	42.2	1.0	33.5	25.6	28.1	9.1
7.00	21.19	-57.0	-17.5	-18.1	34.9	1.0	33.4	26.0	28.2	8.5
7.50	20.97	-57.3	-18.2	-17.9	37.7	1.0	33.6	26.4	28.4	8.0
8.00	20.63	-59.2	-18.2	-16.4	48.4	1.0	33.7	26.5	28.6	7.7
8.50	20.32	-60.6	-16.8	-14.5	58.1	1.0	33.5	26.5	28.9	7.5
9.00	20.10	-60.5	-15.5	-13.7	58.7	1.0	33.3	26.5	29.0	7.3
9.50	19.98	-69.6	-15.1	-13.4	170.4	1.0	33.4	26.3	28.7	7.2
10.00	19.90	-81.5	-15.3	-13.4	674.3	1.0	33.3	25.8	28.3	6.9
10.25	19.87	-84.3	-15.7	-13.3	942.4	1.0	33.4	25.6	28.0	6.8
10.50	19.86	-64.3	-16.0	-13.7	94.8	1.0	33.6	25.5	28.0	6.7
10.75	19.84	-62.6	-16.2	-14.2	79.2	1.0	33.6	25.6	28.1	6.7
11.00	19.79	-66.6	-16.0	-15.2	127.3	1.0	33.7	25.5	28.0	6.6
11.25	19.70	-62.2	-15.4	-15.8	78.2	1.0	33.6	25.4	28.0	6.6
11.50	19.52	-61.2	-14.2	-15.9	70.2	1.0	33.6	25.3	27.8	6.4
11.75	19.38	-61.8	-13.3	-15.6	75.6	1.0	33.6	25.2	27.7	6.5
12.00	19.16	-57.4	-12.4	-14.7	46.4	1.0	33.6	25.2	27.8	6.5
12.25	19.07	-59.7	-12.1	-14.4	61.1	1.0	33.7	25.2	27.8	6.5
12.50	18.97	-58.9	-12.2	-14.6	56.2	1.0	33.5	25.3	27.9	6.5
12.75	18.94	-59.4	-12.6	-15.0	60.3	1.0	33.5	25.3	27.9	6.4
13.00	18.93	-61.0	-13.6	-16.4	75.0	1.0	33.3	25.3	28.0	6.3
13.25	18.91	-59.8	-14.5	-17.4	66.1	1.0	33.4	25.4	28.0	6.3
13.50	18.90	-59.1	-15.9	-18.5	62.6	1.0	33.4	25.5	28.0	6.2
13.75	18.89	-59.4	-16.8	-18.5	65.3	1.0	33.3	25.6	28.2	6.2
14.00	18.88	-60.9	-18.6	-17.9	78.4	1.0	33.3	25.7	28.3	6.2
14.25	18.88	-59.2	-19.8	-17.3	64.8	1.0	33.3	25.8	28.3	6.2
14.50	18.92	-61.1	-21.6	-16.7	80.0	1.0	33.4	25.7	28.3	6.1
14.75	18.95	-64.0	-21.8	-16.8	112.1	1.0	33.1	25.8	28.3	6.1
15.00	19.05	-59.3	-21.6	-17.5	64.8	1.0	33.3	25.7	28.3	6.0
15.25	19.15	-59.1	-20.8	-18.5	62.8	1.0	33.3	25.7	28.3	6.0
15.50	19.33	-59.9	-19.1	-20.4	67.9	1.0	33.2	25.8	28.3	6.0
15.75	19.46	-57.0	-17.6	-20.3	47.8	1.0	33.1	25.7	28.3	6.1
16.00	19.66	-55.9	-15.3	-17.5	40.7	1.0	33.0	25.6	28.2	6.1
16.25	19.83	-55.8	-14.0	-15.9	38.9	1.0	32.7	25.6	28.1	6.2
16.50	20.12	-55.2	-12.9	-14.5	34.2	1.0	33.0	25.3	27.9	6.2
16.75	20.36	-53.9	-12.7	-14.0	28.7	1.0	32.5	25.5	28.1	6.2
17.00	20.75	-55.0	-12.5	-13.9	31.1	1.0	32.2	25.5	28.1	6.2
17.25	20.98	-52.0	-12.8	-14.0	21.6	1.0	32.0	25.6	28.2	6.3
17.50	21.18	-52.1	-13.3	-14.6	21.8	1.0	31.9	25.6	28.3	6.3
17.75	21.25	-50.8	-13.5	-15.2	18.9	1.0	31.6	25.8	28.4	6.3
18.00	21.16	-50.8	-14.0	-15.5	19.2	1.0	31.7	25.8	28.5	6.4
18.25	20.99	-50.4	-13.9	-15.4	18.7	1.0	31.5	26.0	28.9	6.4
18.50	20.58	-50.7	-13.6	-14.7	20.2	1.0	31.5	25.9	28.8	6.6
18.75	20.19	-52.2	-13.2	-14.2	24.8	1.0	31.4	25.5	28.2	6.8
19.00	19.41	-52.7	-12.9	-13.7	28.9	1.0	31.3	25.3	27.9	7.0
19.25	18.72	-52.0	-12.6	-13.2	28.6	1.0	31.1	25.1	27.6	7.3
19.50	17.36	-54.7	-12.8	-13.8	46.1	1.0	31.1	24.9	27.3	7.7
19.75	16.15	-56.6	-13.1	-14.0	66.6	1.0	30.6	24.3	26.5	8.2
20.00	13.76	-59.2	-12.7	-13.2	117.5	1.0	30.6	24.1	26.2	9.0

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)


TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 675 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +12 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	9.76	-65.1	-7.3	-21.9	267.4	1.2	35.5	23.7	27.0	18.2
4.50	13.68	-64.5	-9.2	-27.9	172.3	1.1	35.1	24.6	28.0	15.6
5.00	16.89	-67.9	-11.1	-17.3	182.3	1.1	34.8	25.5	28.8	13.5
5.50	18.82	-61.2	-13.2	-14.4	69.4	1.0	34.1	26.1	29.2	11.7
6.00	19.98	-62.9	-15.2	-14.4	75.6	1.0	33.7	26.6	29.1	10.4
6.50	20.44	-58.8	-16.6	-16.9	46.0	1.0	33.5	27.0	29.4	9.3
7.00	20.35	-60.2	-17.4	-18.1	55.5	1.0	33.4	27.5	29.4	8.6
7.50	20.10	-56.6	-18.2	-18.0	38.1	1.0	33.6	27.8	29.6	8.2
8.00	19.74	-62.0	-18.2	-16.5	73.9	1.0	33.6	27.8	29.7	7.9
8.50	19.40	-61.1	-16.7	-14.5	68.4	1.0	33.4	27.7	29.9	7.7
9.00	19.13	-69.1	-15.5	-13.7	176.3	1.0	33.1	27.6	30.0	7.5
9.50	18.95	-70.7	-14.9	-13.4	217.5	1.0	33.2	27.2	29.5	7.3
10.00	18.82	-74.4	-15.2	-13.2	339.5	1.0	33.0	26.9	28.9	7.1
10.25	18.77	-62.2	-15.5	-13.2	83.9	1.0	33.1	26.6	28.5	7.0
10.50	18.72	-65.5	-15.9	-13.6	123.8	1.0	33.2	26.5	28.5	7.0
10.75	18.68	-64.8	-16.1	-14.0	115.6	1.0	33.3	26.6	28.6	6.9
11.00	18.59	-61.3	-15.9	-15.0	79.8	1.0	33.4	26.4	28.5	6.8
11.25	18.49	-63.8	-15.4	-15.5	106.9	1.0	33.2	26.4	28.5	6.8
11.50	18.30	-62.2	-14.2	-15.6	90.9	1.0	33.3	26.2	28.3	6.8
11.75	18.15	-61.0	-13.4	-15.3	80.1	1.0	33.2	26.1	28.3	6.7
12.00	17.92	-61.2	-12.5	-14.4	82.6	1.0	33.3	26.2	28.3	6.7
12.25	17.82	-60.0	-12.2	-14.2	72.3	1.0	33.3	26.1	28.3	6.7
12.50	17.73	-61.8	-12.3	-14.4	91.3	1.0	33.1	26.3	28.5	6.7
12.75	17.71	-62.5	-12.8	-14.9	99.5	1.0	33.1	26.3	28.5	6.6
13.00	17.71	-59.2	-13.8	-16.3	69.7	1.0	33.1	26.3	28.6	6.5
13.25	17.70	-61.0	-14.7	-17.3	87.5	1.0	33.1	26.4	28.6	6.5
13.50	17.71	-60.6	-16.0	-18.4	85.1	1.0	33.1	26.4	28.6	6.5
13.75	17.71	-59.4	-16.9	-18.5	75.0	1.0	33.1	26.6	28.8	6.5
14.00	17.72	-60.1	-18.6	-18.0	81.3	1.0	33.1	26.6	28.9	6.4
14.25	17.74	-60.8	-19.7	-17.4	88.4	1.0	33.1	26.7	29.1	6.4
14.50	17.81	-61.3	-21.3	-16.9	93.4	1.0	33.1	26.7	29.0	6.4
14.75	17.87	-59.4	-21.4	-17.0	74.6	1.0	33.0	26.7	29.1	6.4
15.00	18.01	-60.7	-21.3	-17.7	86.0	1.0	33.2	26.6	29.1	6.3
15.25	18.13	-58.7	-20.7	-18.7	67.5	1.0	33.0	26.7	29.2	6.3
15.50	18.35	-58.8	-19.0	-20.6	67.5	1.0	32.8	26.7	29.3	6.3
15.75	18.50	-58.7	-17.6	-20.4	65.1	1.0	32.9	26.7	29.2	6.3
16.00	18.74	-58.4	-15.3	-17.6	60.0	1.0	32.8	26.6	29.1	6.3
16.25	18.92	-55.6	-14.1	-16.0	42.3	1.0	32.6	26.6	29.1	6.4
16.50	19.24	-53.7	-12.9	-14.6	31.9	1.0	32.3	26.4	28.9	6.4
16.75	19.48	-54.1	-12.7	-14.0	32.3	1.0	32.1	26.6	29.1	6.4
17.00	19.87	-54.4	-12.5	-13.9	32.2	1.0	31.7	26.6	29.1	6.5
17.25	20.09	-52.7	-12.8	-14.1	26.0	1.0	31.6	26.9	29.3	6.5
17.50	20.27	-51.9	-13.3	-14.7	23.7	1.0	31.4	27.1	29.4	6.6
17.75	20.31	-51.8	-13.5	-15.3	23.4	1.0	31.4	27.4	29.6	6.6
18.00	20.17	-51.0	-14.0	-15.6	22.0	1.0	31.3	27.6	29.7	6.6
18.25	19.97	-50.7	-13.8	-15.5	21.7	1.0	31.2	27.8	30.2	6.7
18.50	19.50	-50.8	-13.5	-14.7	23.2	1.0	31.0	27.7	30.3	6.9
18.75	19.07	-50.0	-13.0	-14.1	21.9	1.0	31.0	27.4	29.7	7.0
19.00	18.24	-51.9	-12.8	-13.6	29.9	1.0	31.0	27.3	29.4	7.2
19.25	17.52	-52.4	-12.6	-13.3	34.5	1.0	30.9	27.1	29.0	7.5
19.50	16.14	-54.9	-12.8	-14.0	54.3	1.0	30.6	26.9	28.7	8.0
19.75	14.95	-58.3	-13.1	-14.2	93.7	1.0	30.5	26.2	27.9	8.5
20.00	12.65	-64.4	-12.7	-13.4	244.1	1.0	30.5	25.9	27.5	9.3


Typical Performance Curves

Note: All data taken at V_{DD} = +6 V unless noted otherwise.


GAIN vs. TEMPERATURE
P_{IN} = -25 dBm




GAIN vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




INPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm




INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



OUTPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm




OUTPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




Typical Performance Curves

Note: All data taken at V_{DD} = +6 V unless noted otherwise.


ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm




ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C




P1dB vs. TEMPERATURE




P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



P_{SAT} vs. TEMPERATURE




P_{SAT} vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C




Typical Performance Curves

Note: All data taken at V_{DD} = +6 V unless noted otherwise.


OUTPUT IP3 vs. TEMPERATURE
P_{OUT} = +12 dBm/TONE




OUTPUT IP3 vs. DEVICE VOLTAGE (V_{DD})
P_{OUT} = +12 dBm/TONE, TEMPERATURE = +25°C




OUTPUT IP3 vs. P_{OUT}
TEMPERATURE = +25°C




GAIN VARIATION vs. TEMPERATURE
P_{IN} = -25 dBm



NOISE FIGURE vs. TEMPERATURE




NOISE FIGURE vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C




Case Style DG

Outline Dimensions


DG1677-8



TOP VIEW




SIDE VIEW



BOTTOM VIEW

PCB Land Pattern



Suggested Layout,
Tolerance to be within ±0.050[0.002]

NOTES:

1. ▨ DENOTES METALLIZATION

Weight: .056 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl.±0.254[0.01]; 3 Pl.±.0.127[0.005] mm[Inches]

Notes:


1. Case material: Plastic.
2. Termination finish: PPF (NiPdAu Plating 0.5 µm/0.02µm/0.05µm)

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F102

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-023879	NEW RELEASE	12/09/24	ITG	IL
A	ECO-026250	CHANGED AS PER TB-AVA-6183MPS+	07/21/25	ITG	CT

SUGGESTED MOUNTING CONFIGURATION FOR DG1677-8 CASE STYLE



COMPONENT	SIZE
C1,C10	1206
C2,C4,C7,C9	0402
C3,C5,C6,C8	0603
C11,C12	0201

NOTES:

1. LINE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"; COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS LINE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-AVA-6183MPS+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	12/09/24
TOLERANCES ON:	CHECKED	GF	12/09/24
2 PL DECIMALS ±	APPROVED	IL	12/09/24
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®


13 Neptune Avenue
Brooklyn NY 11235


PL,DG1677-8,TB-AVA-6183MPS(C)+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-808	A

FILE:	SCALE:	SHEET:
98PL808	4:1	1 OF 1

Evaluation Board and Circuit







DETAIL "A" ROTATED
LOCATION OF
UNITS COMPONENTS
(SCALE 2:1)

Components	Size	Value	Part Numbers	Manufacturer
C3,C5,C6,C8	0603	100pF	B55-19-101G+	Murata
C2,C4,C7,C9	0402	0.01uF	B55-33-103K+	Murata
C1,C10	1206	10uF	B55-109-106K+	Samsung
C11,C12,C13,C14	0201	30pF	B55-104-300M+	DLI

Notes:

1. 2.4mm Female Connectors.
2. PCB Material: Roger RO4350B or equivalent, Dielectric constant=3.5, Thickness=0.010 inch

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications **ENV08T10**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to +85° C, -55° to +95°C	Individual Model Data Sheet
Storage Temperature	-65° to 150°C	Individual Model Data Sheet
Moisture Sensitivity: Level 3	Bake at 125°C for 24 hours. Soak at 30°C/60%RH for 192 hours, Reflow 3 cycles at 260°C peak	J-STD-020D
Unbiased HAST	Temperature: 130°C, RH: 85%, Pressure: 33.3 psia Duration: 96 hours	JESD22-A118A, Test Condition A
Temperature Cycling	-65°C to +150°C, Dwell Time: 15 mins 500 cycles	JESD22-A104E, Condition C
HTSL	Temperature: 150°C Duration: 1000 hours	JESD22-A103E, Test Condition B
HTOL	1000 Hours at 125°C	JESD22-A108
ESD HBM	Refer datasheet for classification	JS-001
ESD CDM	Refer datasheet for classification	JESD22-C101
Vibration (Variable Frequency)	Sinusoidal vibration, 20 - 2000 Hz, 4 min sweeps, 16 min along each of 3 axis, amplitude limits of 20g and 0.06 in	MIL-STD-883, Method 2007, Condition A
Drop Test	1m drops onto concrete in final packed box in 6 orientations	--

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Bend Test	1mm deflection for 5 seconds. Board thickness: 0.024", Span: 2.75"	--
Solderability	10x magnification	J-STD-002 Method B, B1
Resistance to Soldering Heat	Sn-Pb Eutectic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020

This document and its contents are the property of Mini-Circuits.