MMIC SURFACE MOUNT

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

THE BIG DEAL

- High Saturated Output Power, Typ. +30.9 dBm
- High Gain, Typ. 19.3 dB
- High OIP3, Typ. +35.5 dBm
- Supply Voltage +6 V
- 5x5 mm 32-Lead QFN-Style Package



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM (Top View)



APPLICATIONS

- Microwave Radio Backhaul Systems
- Radar, EW, and ECM Defense Systems
- Satellite Communications
- Test and Measurement Equipment

PRODUCT OVERVIEW

Mini-Circuits' AVA-6183MP+ is a wideband, medium power MMIC amplifier fabricated on a GaAs pHEMT process with high output power and broadband gain. Operating from 6 to 18 GHz, this amplifier features typical +27.9 dBm P1dB, +30.9 dBm P_{SAT}, and 19.3 dB gain while operating from a +6 V power supply. AVA-6183MP+ is internally matched to 50 Ohms and comes in a 5x5 mm 32-Lead QFN-style package. These characteristics make it the ideal driver amplifier for a wide range of applications.

KEY FEATURES

Features	Advantages
High Gain, Typ. 19.3 dB	The MMIC amplifier's high gain enables fewer system components in transmit and receive signal chains.
High Saturated Output Power, Typ. +30.9 dBm	High saturated output power makes this amplifier ideal as a driver amplifier in 5G MIMO, backhaul radio, satellite communication, and Electronic Warfare applications.
Dual bias offering gate and drain supply voltage control	Offers control over operating point for improved linearity and higher power-added efficiency. Gate bias may be used to support power control or shutdown functionality.
5x5 mm 32-Lead QFN-Style Package	Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. Industry standard packaging allows for ease of assembly in high volume manufacturing processes.

REV. OR
ECO-027042
AVA-6183MP+
MCL NY
250919

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

ELECTRICAL SPECIFICATIONS[1] AT +25°C, V_{DD} = +6 V, I_{DD} = 550 mA, AND Z_O = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		6		18	GHz
Gain	6	16.7	19.9		dB
	9	16.2	20.0		
	12	14.9	19.3		
	15	15.1	19.8		
	18	14.5	20.1		
Input Return Loss	6		18		dB
	9		16		
	12		12		
	15		20		
	18		14		
Output Return Loss	6		17		dB
	9		15		
	12		16		
	15		19		
	18		15		
Isolation	6-18		60.6		dB
Output Power at 1 dB Compression (P1dB)	6		+26.5		dBm
	9		+28.8		
	12		+27.9		
	15		+28.1		
	18		+29.0		
Output Power at Saturation (P_{SAT})[2]	6		+29.4		dBm
	9		+31.0		
	12		+30.9		
	15		+31.1		
	18		+29.8		
Output Third-Order Intercept (OIP3) (P_{OUT} = +16 dBm/Tone)	6		+32.8		dBm
	9		+34.1		
	12		+35.5		
	15		+35.3		
	18		+33.8		
Noise Figure	6		7.7		dB
	9		5.1		
	12		4.8		
	15		4.8		
	18		5.1		
Device Operating Voltage (V_{DD})[3,4]		+5	+6	+7	V
Device Operating Current (I_{DD})[5,6]		220	550	600	mA
Device Operating Gate Voltage (V_{GG})[7,8]			-0.78		V
Device Operating Gate Current (I_{GG})[9]			0.79		mA
Device Current Variation Vs. Temperature[10]			-0.435		mA/°C
Device Current Variation Vs. Voltage[11]			+0.094		mA/mV

1. Tested on Mini-Circuits Characterization Test Board TB-AVA-6183MPC+. See Figure 2. De-embedded to the device reference plane.
2. Defined as output power at which change is 0.1 dB per 1 dB change in input power.
3. $V_{DD} = V_{DD1} = V_{DD2}$
4. Voltage must be applied to all V_{DD1} and V_{DD2} pins for standard operation.
5. Current at P_{IN} = -25 dBm. Increases to 1250 mA at P_{SAT}.
6. $I_{DD} = I_{DD1} + I_{DD2}$
7. $V_{GG} = V_{GG1} = V_{GG2}$
8. Voltage must be applied to both V_{GG1} and V_{GG2} pins for standard operation.
9. $I_{GG} = I_{GG1} + I_{GG2}$
10. (Current at +85°C - Current at -55°C)/(+85°C - -55°C)
11. (Current at +7 V - Current at +5 V)/(+7 V - +5 V)

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.













Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.

ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm



ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



P1dB vs. TEMPERATURE



P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



P_{SAT} vs. TEMPERATURE



P_{SAT} vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.













Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

TYPICAL PERFORMANCE GRAPHS

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.







ABSOLUTE MAXIMUM RATINGS[12]

Parameter	Ratings
Operating Temperature	-55°C to +85°C
Storage Temperature	-65°C to +150°C
Total Power Dissipation	6.5 W
Junction Temperature[13]	+175°C
Input Power (CW), V_{DD}[14] = +6 V	+26 dBm
DC Voltage on RF-OUT	+10 V
DC Voltage on RF-IN	+10 V
DC Drain Voltage on V_{DD}	+7.5 V
DC Drain Current I_{DD}[15]	1400 mA
DC Gate Voltage on V_{GG}[16]	-3 V < V_{GG} < 0 V
DC Gate Current I_{GG}[17]	5 mA

12. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.
13. Peak temperature on top of die.
14. $V_{DD} = V_{DD1} = V_{DD2}$
15. $I_{DD} = I_{DD1} + I_{DD2}$
16. $V_{GG} = V_{GG1} = V_{GG2}$
17. $I_{GG} = I_{GG1} + I_{GG2}$

THERMAL RESISTANCE

Parameter	Ratings
Thermal Resistance (Θ_{JC})[18]	18.3°C/W

18. Θ_{JC}= (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

	Class	Voltage Range	Reference Standard
Human Body Model (HBM)	1A	250 V < 500 V	ANSI/ESDA/JEDEC JS-001-2023
Charged Device Model (CDM)	C3	> 1000 V	ANSI/ESDA/JEDEC JS-002-2022

ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL3 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

FUNCTIONAL DIAGRAM (TOP VIEW)



Figure 1. AVA-6183MP+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description (Refer to Figure 2)
RF-IN	3	RF-IN pad connects to RF-Input port.
RF-OUT	18	RF-OUT pad connects to RF-Output port.
V_{DD1}	12, 29	DC Input pads connects to voltage input ports, V_{DD1}.
V_{DD2}	15, 26	DC Input pads connects to voltage input ports, V_{DD2}.
V_{GG1}	10	DC Input pads connects to voltage input ports, V_{GG1}.
V_{GG2}	31	DC Input pads connects to voltage input ports, V_{GG2}.
GND	1, 2, 4, 8, 9, 16, 17, 19, 24, 25, 32, & Paddle	Connects to ground.
NC	5-7, 11, 13, 14, 20-23, 27, 28, 30	Not used internally. Connected to ground on test board.

EVALUATION BOARD



Figure 2. AVA-6183MP+ Evaluation and Application Circuit

Electrical Parameters and Conditions
Gain, Return Loss, Output Power at 1 dB Compression (P1dB), Output Power at Saturation (P_{SAT}), Output IP3 (OIP3), and Noise Figure measured using N52425B PNA-X Microwave Network Analyzer.

Conditions:
1. Gain and Return Loss: P_{IN} = -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +16 dBm/tone at output.

Power ON/Power OFF Sequence:
Caution: Permanent damage to the device will occur if the Power ON and Power OFF sequences are not followed.

Power ON:
1) Set V_{GG} = -2 V. Apply V_{GG}.
2) Set V_{DD} = +6 V. Apply V_{DD}.
3) Increase V_{GG} to obtain the desired I_{DD} as shown in specification table.
4) Apply RF Signal.

Power OFF:
1) Turn off RF Signal.
2) Adjust V_{GG} to -2 V.
3) Turn off V_{DD}.
4) Turn off V_{GG}.

Component	Value	Size	Part Number	Manufacturer
C3, C5, C6, C8, C11, & C16	100 pF	0603	GRM1885C1H101GA01D	Murata
C2, C4, C7, C9, C12, &C15	0.01 µF	0402	GRM155R71E103KA01D	Murata
C1, C10, C13, & C14	10 µF	1206	CL31B106KBHNNNE	Samsung
C17 & C18	30 pF	0201	P21BNL300M5ST	KDL

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

CASE STYLE DRAWING





Weight: .056 Grams

Dimensions are in mm [Inches]. Tolerances: 2 Pl. ± 0.254 [0.01]; 3 Pl. ± 0.127 [0.005] mm [inches]

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Medium Power Amplifier AVA-6183MP+

50Ω 6 to 18 GHz Dual Biased

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DG1677-8. QFN-style package, exposed paddle, Lead Finish: Nickel Palladium Gold
RoHs Status	Compliant
Tape & Reel **Standard quantities available on reel**	F102 7″ reels with 20, 50, 100, 200, or 500 devices 13″ 1,000 devices
Suggested Layout for PCB Design	PL-833
Evaluation Board	TB-AVA-6183MPC+ Gerber File
Environmental Ratings	ENV08T10
Product Handling	The use of no-clean solder is recommended. This package cannot be subjected to aqueous wash.

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 550 mA, V_{GG} = -0.77 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.6	-68.4	-8.1	-20.4	743.4	1.1	29.5	22.4	25.3	17.3
4.50	11.8	-68.9	-11.3	-30.9	378.0	1.1	30.9	23.8	26.7	13.0
5.00	16.5	-64.0	-15.6	-24.2	132.2	1.0	32.5	25.3	28.2	10.5
5.50	18.8	-66.5	-18.3	-18.9	135.9	1.0	33.3	26.5	29.3	8.8
6.00	20.0	-67.0	-18.4	-16.8	126.9	1.0	33.5	27.3	29.9	7.7
6.50	20.5	-65.0	-17.7	-17.2	94.9	1.0	33.7	27.7	30.3	6.9
7.00	20.6	-61.9	-17.9	-18.0	66.1	1.0	33.4	27.9	30.4	6.4
7.50	20.6	-57.6	-18.7	-18.0	40.8	1.0	34.4	28.0	30.2	5.9
8.00	20.4	-57.2	-19.5	-17.1	40.1	1.0	33.8	28.5	30.4	5.6
8.50	20.2	-63.6	-18.7	-15.8	86.0	1.0	34.2	29.1	31.0	5.3
9.00	20.0	-63.1	-17.3	-14.6	81.5	1.0	34.3	29.1	31.1	5.1
9.50	19.9	-66.6	-16.8	-14.0	122.8	1.0	36.1	28.7	30.6	5.0
10.00	19.9	-68.4	-17.4	-14.0	153.8	1.0	36.3	28.9	30.4	4.8
10.25	19.9	-75.8	-17.5	-14.2	360.9	1.0	36.7	29.5	30.9	4.7
10.50	19.9	-70.1	-17.5	-14.3	188.2	1.0	37.5	29.8	31.2	4.7
10.75	19.9	-64.8	-16.9	-14.7	102.8	1.0	36.7	29.9	31.4	4.7
11.00	19.8	-66.5	-16.4	-15.0	125.9	1.0	37.1	29.8	31.4	4.7
11.25	19.7	-63.4	-15.6	-15.3	88.9	1.0	37.3	29.0	31.5	4.7
11.50	19.6	-64.0	-15.0	-15.5	96.5	1.0	36.8	28.5	31.5	4.6
11.75	19.5	-58.9	-13.8	-15.5	54.4	1.0	36.9	27.9	31.2	4.7
12.00	19.3	-63.4	-13.0	-15.5	91.4	1.0	36.8	27.9	31.0	4.8
12.25	19.2	-59.4	-12.0	-15.3	58.5	1.0	36.5	28.0	31.1	4.9
12.50	19.1	-60.2	-11.5	-15.1	64.0	1.0	37.0	28.2	31.3	5.0
12.75	19.0	-58.9	-11.1	-15.0	55.7	1.0	36.2	28.1	31.1	5.0
13.00	19.0	-58.0	-11.2	-15.1	50.3	1.0	36.6	28.1	31.2	4.9
13.25	19.1	-58.4	-11.9	-15.5	53.4	1.0	36.5	27.8	30.5	5.0
13.50	19.1	-59.4	-12.7	-15.9	59.9	1.0	36.2	28.1	31.0	4.9
13.75	19.3	-62.2	-14.6	-16.7	84.4	1.0	36.3	27.9	30.8	4.9
14.00	19.4	-59.4	-16.2	-17.3	61.1	1.0	36.0	28.0	30.9	4.9
14.25	19.5	-59.5	-19.3	-18.3	62.2	1.0	36.3	28.0	31.1	4.8
14.50	19.6	-61.3	-21.4	-19.1	76.1	1.0	36.1	28.1	31.1	4.7
14.75	19.8	-61.7	-23.8	-20.0	78.8	1.0	36.0	28.2	31.1	4.7
15.00	19.9	-59.3	-24.1	-20.4	59.6	1.0	36.6	28.4	31.1	4.7
15.25	20.0	-60.5	-22.1	-20.0	67.8	1.0	36.3	28.4	30.9	4.8
15.50	20.1	-58.6	-20.1	-19.1	53.7	1.0	35.8	28.5	31.0	4.7
15.75	20.2	-57.6	-17.3	-17.8	46.5	1.0	35.7	28.4	30.8	4.8
16.00	20.2	-56.9	-15.9	-16.9	42.2	1.0	35.2	28.4	30.8	4.7
16.25	20.3	-55.8	-14.4	-16.1	36.7	1.0	35.3	28.0	30.4	4.8
16.50	20.3	-55.3	-13.8	-15.7	34.3	1.0	35.8	28.1	30.4	4.8
16.75	20.4	-53.6	-13.2	-15.0	27.8	1.0	35.3	28.4	30.2	4.9
17.00	20.4	-52.7	-12.9	-14.6	25.0	1.0	35.6	28.6	30.0	4.8
17.25	20.3	-53.0	-12.9	-14.3	26.0	1.0	35.2	28.9	29.8	4.8
17.50	20.2	-53.6	-13.0	-14.3	28.3	1.0	34.4	29.1	29.9	4.9
17.75	20.1	-54.5	-13.2	-14.5	32.1	1.0	34.4	29.4	29.8	4.9
18.00	20.0	-52.6	-13.6	-15.0	26.6	1.0	34.3	29.3	29.8	5.0
18.25	19.7	-51.3	-14.0	-16.1	23.8	1.0	33.8	29.3	30.2	5.2
18.50	19.3	-52.9	-13.8	-16.6	30.0	1.0	33.8	28.8	30.0	5.3
18.75	18.3	-54.2	-12.9	-16.6	39.2	1.0	31.6	28.5	29.6	5.6
19.00	17.2	-57.0	-12.3	-16.2	61.3	1.0	31.7	28.0	29.0	5.7
19.25	15.1	-64.3	-12.0	-15.3	178.4	1.0	30.4	27.6	28.6	6.1
19.50	13.4	-63.5	-12.4	-14.4	197.6	1.0	30.3	27.0	28.2	6.5
19.75	10.5	-64.2	-13.1	-13.3	300.7	1.0	30.2	26.1	26.8	7.2
20.00	8.5	-70.3	-13.1	-12.4	763.2	1.0	31.0	25.6	26.0	7.8

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 220 mA, V_{GG} = -1.01 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	2.0	-66.0	-8.1	-20.8	763.2	1.1	25.3	24.8	25.8	17.7
4.50	9.3	-62.1	-11.2	-31.7	230.8	1.1	27.2	26.7	27.9	13.0
5.00	13.9	-70.6	-15.4	-23.5	380.8	1.0	30.6	27.6	29.3	10.4
5.50	16.2	-74.0	-18.2	-18.3	438.5	1.0	31.9	28.2	29.6	8.7
6.00	17.3	-64.4	-18.4	-16.6	127.4	1.0	32.4	28.4	29.4	7.6
6.50	17.8	-56.8	-17.8	-17.2	50.6	1.0	33.0	28.6	29.2	6.8
7.00	18.0	-57.1	-18.1	-18.2	51.7	1.0	32.7	28.9	29.1	6.2
7.50	18.0	-57.5	-19.0	-18.0	54.6	1.0	33.5	29.3	29.5	5.7
8.00	17.8	-56.0	-19.8	-17.1	47.0	1.0	32.3	29.6	29.9	5.4
8.50	17.6	-57.7	-18.9	-15.7	58.1	1.0	32.5	30.0	30.3	5.1
9.00	17.5	-58.5	-17.3	-14.5	64.7	1.0	31.8	30.4	30.1	4.9
9.50	17.4	-57.5	-16.7	-13.8	57.5	1.0	33.3	30.4	29.1	4.7
10.00	17.5	-63.1	-17.3	-13.9	110.4	1.0	29.5	30.7	30.1	4.6
10.25	17.5	-64.3	-17.7	-14.1	126.4	1.0	29.0	30.6	30.6	4.5
10.50	17.5	-66.4	-17.9	-14.3	161.3	1.0	29.7	30.6	30.9	4.4
10.75	17.5	-60.3	-17.5	-14.7	80.1	1.0	28.7	18.6	31.1	4.4
11.00	17.5	-60.0	-17.1	-15.0	78.1	1.0	28.8	18.7	31.0	4.4
11.25	17.5	-58.6	-16.3	-15.3	66.2	1.0	29.0	18.5	30.9	4.4
11.50	17.4	-58.0	-15.5	-15.4	62.6	1.0	28.6	18.3	30.9	4.4
11.75	17.3	-57.2	-14.3	-15.5	57.4	1.0	28.7	18.5	30.3	4.4
12.00	17.2	-55.2	-13.3	-15.5	46.0	1.0	28.5	18.8	30.1	4.4
12.25	17.1	-56.9	-12.1	-15.3	55.8	1.0	28.4	18.8	30.3	4.5
12.50	17.0	-55.3	-11.5	-15.1	46.5	1.0	28.9	18.7	30.1	4.6
12.75	16.9	-56.0	-11.0	-15.1	50.6	1.0	28.3	19.1	30.1	4.6
13.00	16.9	-54.6	-11.0	-15.2	43.1	1.0	28.7	19.6	30.3	4.6
13.25	17.0	-53.2	-11.5	-15.7	36.9	1.0	28.7	19.9	30.1	4.6
13.50	17.1	-53.9	-12.2	-16.1	40.2	1.0	28.7	20.3	30.5	4.5
13.75	17.2	-54.7	-13.9	-17.0	44.4	1.0	28.9	20.1	31.0	4.5
14.00	17.3	-56.2	-15.5	-17.6	53.2	1.0	28.9	20.7	31.2	4.4
14.25	17.5	-56.1	-18.4	-18.7	52.9	1.0	29.3	21.8	31.3	4.3
14.50	17.6	-54.4	-20.6	-19.4	43.7	1.0	29.4	22.4	31.5	4.3
14.75	17.7	-53.6	-23.1	-20.2	39.5	1.0	29.3	22.3	31.4	4.2
15.00	17.8	-52.0	-23.7	-20.5	32.4	1.0	29.7	22.4	31.3	4.2
15.25	18.0	-51.3	-22.2	-20.0	29.6	1.0	29.7	23.4	31.4	4.2
15.50	18.0	-52.4	-20.2	-19.2	33.1	1.0	29.7	24.2	31.6	4.2
15.75	18.2	-51.0	-17.5	-17.8	27.6	1.0	29.4	25.2	31.5	4.2
16.00	18.2	-50.7	-16.0	-17.0	26.1	1.0	28.6	25.6	31.2	4.1
16.25	18.4	-50.0	-14.5	-16.2	23.4	1.0	28.3	25.6	30.7	4.2
16.50	18.4	-49.4	-14.0	-15.9	21.6	1.0	27.8	26.3	30.8	4.2
16.75	18.5	-49.6	-13.3	-15.3	21.8	1.0	28.1	28.1	31.0	4.2
17.00	18.6	-49.0	-13.0	-14.8	20.3	1.0	29.9	29.0	30.9	4.3
17.25	18.5	-47.0	-12.8	-14.2	16.0	1.0	30.3	29.7	30.7	4.4
17.50	18.5	-48.1	-12.8	-14.0	18.3	1.0	30.3	29.8	30.6	4.3
17.75	18.4	-47.2	-13.0	-14.1	16.8	1.0	30.9	29.6	30.3	4.3
18.00	18.3	-47.7	-13.4	-14.6	18.2	1.0	31.4	29.7	30.0	4.5
18.25	18.2	-47.6	-14.1	-15.9	18.6	1.0	31.3	29.5	30.2	4.6
18.50	17.9	-48.1	-14.1	-16.7	20.3	1.0	32.2	29.2	30.1	4.6
18.75	17.1	-48.8	-13.2	-16.9	24.2	1.0	31.1	28.0	29.7	4.9
19.00	16.1	-50.2	-12.4	-16.4	31.5	1.0	31.3	27.8	29.3	5.0
19.25	14.0	-51.3	-11.9	-15.2	45.4	1.0	31.0	27.6	28.8	5.4
19.50	12.2	-55.7	-12.1	-14.4	91.9	1.0	31.6	27.0	28.0	5.7
19.75	9.3	-55.4	-13.0	-13.2	125.9	1.0	32.9	26.7	27.2	6.2
20.00	7.1	-61.9	-13.1	-12.3	340.3	1.0	32.7	26.1	26.5	6.8

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 300 mA, V_{GG} = -0.95 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	3.0	-65.3	-8.1	-20.4	624.0	1.1	26.0	22.7	25.4	17.4
4.50	10.3	-72.3	-11.3	-30.0	672.9	1.1	28.5	25.6	27.7	12.9
5.00	14.9	-67.3	-15.5	-23.7	232.6	1.0	31.1	27.0	28.7	10.3
5.50	17.2	-67.8	-18.2	-18.7	191.5	1.0	32.2	27.5	29.3	8.6
6.00	18.3	-66.1	-18.4	-16.8	137.3	1.0	32.6	27.8	29.4	7.5
6.50	18.9	-58.9	-17.8	-17.3	56.6	1.0	33.0	28.1	29.4	6.8
7.00	19.0	-58.4	-18.0	-18.1	53.3	1.0	32.8	28.4	29.3	6.1
7.50	19.0	-57.5	-18.8	-18.0	48.6	1.0	33.8	28.8	29.6	5.7
8.00	18.9	-55.3	-19.7	-17.0	38.5	1.0	32.9	29.0	29.9	5.3
8.50	18.7	-59.5	-18.8	-15.8	63.3	1.0	33.2	29.3	30.3	5.1
9.00	18.5	-60.5	-17.3	-14.5	71.7	1.0	33.0	29.5	30.2	4.9
9.50	18.5	-60.8	-16.7	-13.9	74.6	1.0	37.2	29.6	29.6	4.6
10.00	18.5	-64.1	-17.3	-14.0	110.0	1.0	35.0	30.0	30.5	4.5
10.25	18.5	-67.7	-17.6	-14.2	165.5	1.0	33.6	29.9	30.8	4.4
10.50	18.5	-64.2	-17.7	-14.4	112.0	1.0	34.2	30.0	30.9	4.4
10.75	18.5	-64.8	-17.2	-14.8	119.4	1.0	32.3	22.9	31.1	4.3
11.00	18.5	-61.9	-16.8	-15.1	85.9	1.0	32.3	23.3	31.0	4.3
11.25	18.5	-59.6	-15.9	-15.4	67.1	1.0	32.5	22.9	30.9	4.3
11.50	18.4	-61.2	-15.2	-15.5	80.5	1.0	31.6	22.6	30.9	4.4
11.75	18.2	-57.9	-14.0	-15.7	56.0	1.0	31.6	22.5	30.5	4.4
12.00	18.1	-57.2	-13.1	-15.6	51.9	1.0	31.4	22.3	30.3	4.5
12.25	18.0	-57.6	-12.0	-15.4	54.5	1.0	30.8	22.5	30.3	4.5
12.50	17.9	-56.8	-11.4	-15.2	50.1	1.0	31.7	22.2	30.1	4.6
12.75	17.8	-56.6	-11.0	-15.2	48.6	1.0	30.8	22.5	30.2	4.6
13.00	17.8	-57.9	-11.1	-15.3	57.2	1.0	31.3	23.0	30.3	4.6
13.25	17.9	-56.7	-11.6	-15.7	50.4	1.0	31.1	22.9	30.2	4.6
13.50	17.9	-57.4	-12.4	-16.1	54.7	1.0	30.9	23.2	30.6	4.5
13.75	18.1	-55.9	-14.2	-16.9	46.8	1.0	31.0	24.1	31.0	4.5
14.00	18.2	-56.9	-15.9	-17.5	52.9	1.0	30.9	24.3	31.2	4.4
14.25	18.3	-58.4	-18.9	-18.5	63.1	1.0	31.2	24.3	31.2	4.4
14.50	18.4	-56.0	-21.0	-19.2	47.3	1.0	31.2	24.5	31.5	4.3
14.75	18.5	-56.7	-23.5	-20.0	51.2	1.0	31.0	24.7	31.4	4.3
15.00	18.6	-55.3	-24.0	-20.3	43.5	1.0	31.9	25.0	31.2	4.3
15.25	18.7	-55.7	-22.2	-20.0	44.9	1.0	31.5	25.8	31.4	4.3
15.50	18.8	-55.3	-20.2	-19.1	42.1	1.0	31.5	26.3	31.5	4.2
15.75	18.9	-53.9	-17.4	-17.8	35.0	1.0	30.9	26.9	31.5	4.3
16.00	19.0	-53.5	-15.9	-17.0	33.1	1.0	31.2	27.0	31.2	4.2
16.25	19.1	-54.0	-14.5	-16.2	34.0	1.0	31.1	26.6	30.7	4.3
16.50	19.2	-51.2	-13.9	-15.8	24.5	1.0	31.3	27.2	30.8	4.3
16.75	19.2	-50.9	-13.3	-15.1	23.2	1.0	31.2	28.6	31.0	4.3
17.00	19.2	-51.5	-13.0	-14.7	24.7	1.0	32.1	29.1	30.9	4.3
17.25	19.2	-49.4	-12.9	-14.2	19.6	1.0	32.5	29.4	30.6	4.3
17.50	19.1	-50.3	-12.9	-14.1	22.0	1.0	31.8	29.3	30.6	4.3
17.75	19.1	-50.9	-13.1	-14.3	23.9	1.0	32.4	29.2	30.2	4.5
18.00	19.0	-49.4	-13.5	-14.8	20.5	1.0	33.0	29.3	30.0	4.5
18.25	18.8	-49.5	-14.1	-15.9	21.6	1.0	33.2	29.1	30.2	4.7
18.50	18.5	-50.3	-14.0	-16.6	24.7	1.0	34.1	29.0	30.1	4.8
18.75	17.5	-50.9	-13.0	-16.7	29.6	1.0	32.2	28.0	29.7	5.0
19.00	16.4	-52.6	-12.3	-16.3	40.4	1.0	32.3	27.8	29.3	5.1
19.25	14.3	-54.0	-11.9	-15.2	59.8	1.0	31.4	27.7	28.8	5.5
19.50	12.5	-57.9	-12.2	-14.4	114.5	1.0	31.6	27.1	28.1	5.8
19.75	9.6	-63.5	-13.1	-13.2	307.3	1.0	32.9	26.6	27.1	6.4
20.00	7.4	-63.6	-13.1	-12.3	397.4	1.0	33.8	26.0	26.4	6.9

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 600 mA, V_{GG} = -0.74 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.7	-63.0	-8.1	-20.5	393.3	1.1	29.4	20.0	23.9	17.3
4.50	12.0	-69.6	-11.3	-31.4	404.7	1.1	31.1	20.6	25.7	13.1
5.00	16.7	-64.6	-15.6	-24.3	138.1	1.0	32.9	22.9	27.4	10.6
5.50	19.0	-63.5	-18.3	-18.8	94.9	1.0	33.5	25.2	28.5	8.9
6.00	20.1	-65.2	-18.4	-16.8	101.4	1.0	33.6	25.1	29.0	7.8
6.50	20.6	-61.5	-17.7	-17.1	62.8	1.0	33.9	24.6	29.4	7.0
7.00	20.8	-59.5	-17.9	-18.0	49.4	1.0	33.6	26.6	29.6	6.5
7.50	20.7	-58.5	-18.8	-18.0	44.5	1.0	34.4	27.3	29.7	6.1
8.00	20.5	-59.3	-19.6	-17.2	50.5	1.0	34.0	26.9	29.8	5.7
8.50	20.3	-61.1	-18.7	-15.9	63.5	1.0	34.4	27.0	31.0	5.4
9.00	20.1	-62.4	-17.3	-14.6	74.1	1.0	34.4	27.9	30.6	5.2
9.50	20.1	-68.9	-16.8	-14.0	157.8	1.0	36.1	28.3	30.4	5.1
10.00	20.0	-68.6	-17.4	-13.9	154.0	1.0	36.3	28.2	30.2	4.9
10.25	20.0	-74.5	-17.5	-14.2	308.4	1.0	36.7	28.3	30.6	4.8
10.50	20.0	-66.0	-17.5	-14.3	115.5	1.0	37.4	28.5	30.8	4.8
10.75	20.0	-64.8	-16.9	-14.7	101.0	1.0	36.9	28.6	31.0	4.8
11.00	19.9	-66.4	-16.4	-14.9	122.6	1.0	37.2	28.5	31.0	4.8
11.25	19.8	-61.5	-15.6	-15.3	71.3	1.0	37.5	28.2	31.0	4.8
11.50	19.7	-61.9	-15.0	-15.4	74.7	1.0	37.0	28.4	31.0	4.8
11.75	19.5	-60.3	-13.8	-15.5	63.0	1.0	37.1	28.3	30.9	4.8
12.00	19.4	-61.2	-13.1	-15.4	70.9	1.0	37.2	28.2	30.9	4.9
12.25	19.2	-61.1	-12.0	-15.2	70.6	1.0	36.7	27.8	31.0	5.0
12.50	19.2	-58.8	-11.5	-15.1	54.3	1.0	37.3	27.8	31.0	5.0
12.75	19.1	-58.7	-11.2	-15.0	54.0	1.0	36.5	27.5	30.8	5.0
13.00	19.1	-59.9	-11.2	-15.1	62.0	1.0	36.9	27.6	30.7	5.1
13.25	19.2	-61.7	-11.9	-15.5	76.9	1.0	36.8	27.8	30.6	5.1
13.50	19.2	-61.5	-12.7	-15.8	76.1	1.0	36.5	28.2	30.6	5.1
13.75	19.4	-62.7	-14.6	-16.6	87.6	1.0	36.5	28.3	30.6	5.1
14.00	19.5	-60.8	-16.2	-17.3	70.9	1.0	36.3	28.3	30.8	5.0
14.25	19.6	-63.5	-19.3	-18.3	96.6	1.0	36.7	28.1	31.0	4.9
14.50	19.7	-63.9	-21.4	-19.1	100.9	1.0	36.3	28.2	31.1	4.9
14.75	19.9	-62.6	-23.7	-20.0	86.7	1.0	36.2	28.2	31.1	4.8
15.00	20.0	-59.4	-24.1	-20.4	59.5	1.0	36.8	28.4	31.1	4.9
15.25	20.1	-59.9	-22.1	-20.0	62.5	1.0	36.5	28.4	30.9	4.9
15.50	20.2	-58.4	-20.1	-19.2	51.9	1.0	36.0	28.6	30.9	4.9
15.75	20.3	-56.9	-17.3	-17.8	42.4	1.0	35.8	28.5	30.7	4.9
16.00	20.4	-56.0	-15.9	-17.0	37.8	1.0	35.4	28.5	30.7	4.9
16.25	20.4	-57.3	-14.4	-16.1	42.9	1.0	35.4	28.3	30.2	5.0
16.50	20.5	-54.5	-13.8	-15.7	30.9	1.0	35.9	28.4	30.2	5.0
16.75	20.5	-53.9	-13.2	-15.0	28.3	1.0	35.4	28.7	30.1	5.0
17.00	20.5	-53.2	-12.9	-14.7	26.0	1.0	35.6	28.7	30.0	5.0
17.25	20.4	-53.4	-12.9	-14.4	27.0	1.0	35.2	28.8	29.8	5.0
17.50	20.3	-52.7	-13.0	-14.3	25.2	1.0	34.5	28.9	29.8	5.0
17.75	20.2	-53.3	-13.2	-14.6	27.7	1.0	34.3	29.1	29.7	5.0
18.00	20.1	-53.2	-13.6	-15.1	27.9	1.0	34.3	29.2	29.7	5.2
18.25	19.8	-53.9	-14.0	-16.0	31.9	1.0	33.6	29.1	30.1	5.3
18.50	19.4	-51.9	-13.8	-16.5	26.5	1.0	33.6	28.6	29.8	5.5
18.75	18.4	-56.1	-12.9	-16.7	48.4	1.0	31.6	28.5	29.5	5.7
19.00	17.3	-56.7	-12.3	-16.3	58.5	1.0	31.8	27.9	28.9	5.8
19.25	15.2	-57.1	-12.0	-15.3	76.8	1.0	30.5	27.4	28.4	6.3
19.50	13.5	-61.5	-12.3	-14.4	155.7	1.0	30.3	26.8	27.8	6.6
19.75	10.7	-83.9	-13.1	-13.2	2853.2	1.0	29.8	25.9	26.6	7.3
20.00	8.6	-63.7	-13.1	-12.4	348.8	1.0	30.3	25.4	25.8	7.9

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 500 mA, V_{GG} = -0.81 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.4	-68.7	-8.1	-20.3	785.5	1.1	29.7	21.3	23.2	17.2
4.50	11.6	-67.4	-11.3	-30.4	324.6	1.1	30.7	22.9	25.6	12.9
5.00	16.3	-78.3	-15.6	-24.1	700.2	1.0	32.2	24.7	27.8	10.3
5.50	18.6	-73.8	-18.3	-18.9	325.7	1.0	33.1	26.0	28.5	8.7
6.00	19.8	-66.5	-18.4	-16.9	122.4	1.0	33.3	27.2	29.2	7.6
6.50	20.3	-62.1	-17.7	-17.2	69.7	1.0	33.6	27.1	29.7	6.8
7.00	20.4	-60.1	-17.9	-18.0	54.6	1.0	33.3	27.7	29.9	6.3
7.50	20.4	-57.2	-18.7	-18.0	39.9	1.0	34.3	28.1	30.0	5.8
8.00	20.2	-58.0	-19.6	-17.1	45.1	1.0	33.7	28.3	30.3	5.5
8.50	20.0	-60.4	-18.7	-15.8	60.3	1.0	34.1	28.8	31.0	5.2
9.00	19.8	-62.0	-17.2	-14.6	73.4	1.0	34.0	28.9	31.0	5.0
9.50	19.8	-66.4	-16.8	-14.0	123.0	1.0	36.2	28.9	30.3	4.8
10.00	19.8	-81.3	-17.4	-14.0	684.2	1.0	36.4	29.0	30.3	4.7
10.25	19.8	-70.4	-17.5	-14.2	197.7	1.0	36.6	29.4	30.8	4.6
10.50	19.8	-68.3	-17.5	-14.4	155.5	1.0	37.6	29.6	31.1	4.6
10.75	19.7	-66.5	-16.9	-14.7	127.4	1.0	36.7	29.5	31.4	4.6
11.00	19.7	-63.9	-16.4	-15.0	95.1	1.0	36.9	29.3	31.4	4.5
11.25	19.6	-63.1	-15.6	-15.4	87.4	1.0	37.1	28.6	31.3	4.6
11.50	19.5	-61.4	-15.0	-15.5	72.6	1.0	36.5	28.4	31.3	4.6
11.75	19.3	-60.7	-13.8	-15.6	67.6	1.0	36.5	27.8	31.0	4.6
12.00	19.2	-60.2	-13.0	-15.5	64.8	1.0	36.4	27.7	30.9	4.7
12.25	19.0	-60.4	-12.0	-15.3	66.2	1.0	35.9	27.5	31.0	4.8
12.50	18.9	-60.3	-11.5	-15.2	65.7	1.0	36.6	27.5	31.1	4.9
12.75	18.9	-58.1	-11.1	-15.1	51.2	1.0	35.8	27.3	30.9	4.9
13.00	18.9	-59.0	-11.2	-15.2	57.3	1.0	36.2	27.4	30.9	4.9
13.25	18.9	-59.6	-11.9	-15.5	61.9	1.0	36.0	27.4	30.7	4.9
13.50	19.0	-60.9	-12.7	-15.9	73.0	1.0	35.7	27.7	30.7	4.9
13.75	19.2	-57.0	-14.6	-16.7	46.8	1.0	35.9	27.7	30.6	4.8
14.00	19.2	-60.0	-16.2	-17.3	66.6	1.0	35.5	27.9	30.8	4.8
14.25	19.4	-60.5	-19.3	-18.3	70.6	1.0	35.8	27.9	31.0	4.7
14.50	19.5	-57.9	-21.4	-19.1	52.5	1.0	35.7	28.0	31.2	4.7
14.75	19.6	-59.4	-23.7	-20.0	62.1	1.0	35.6	28.0	31.3	4.6
15.00	19.7	-59.7	-24.1	-20.3	63.6	1.0	36.2	28.1	31.3	4.6
15.25	19.8	-58.7	-22.1	-20.0	56.1	1.0	36.0	28.1	31.2	4.6
15.50	19.9	-59.5	-20.1	-19.1	60.8	1.0	35.6	28.3	31.2	4.6
15.75	20.0	-57.6	-17.3	-17.8	47.8	1.0	35.3	28.3	31.0	4.6
16.00	20.1	-55.4	-15.9	-17.0	36.5	1.0	34.9	28.3	30.8	4.6
16.25	20.1	-55.4	-14.4	-16.1	35.7	1.0	35.0	28.0	30.4	4.7
16.50	20.2	-54.9	-13.8	-15.7	33.2	1.0	35.6	28.1	30.3	4.7
16.75	20.2	-53.6	-13.2	-15.0	28.2	1.0	35.0	28.3	30.2	4.7
17.00	20.2	-53.6	-12.9	-14.6	28.0	1.0	35.6	28.5	30.0	4.7
17.25	20.2	-52.2	-12.9	-14.3	24.1	1.0	35.0	28.7	29.8	4.8
17.50	20.1	-51.8	-13.0	-14.3	23.5	1.0	34.3	29.1	29.9	4.7
17.75	20.0	-54.4	-13.2	-14.5	32.4	1.0	34.3	29.2	29.8	4.8
18.00	19.9	-51.4	-13.6	-15.0	23.3	1.0	34.3	29.2	29.8	4.9
18.25	19.6	-52.8	-14.0	-16.0	28.9	1.0	33.9	29.4	30.2	5.1
18.50	19.2	-51.8	-13.8	-16.6	27.0	1.0	34.0	28.8	30.0	5.1
18.75	18.1	-53.3	-12.9	-16.7	35.9	1.0	31.7	28.4	29.6	5.4
19.00	17.0	-56.2	-12.3	-16.3	56.4	1.0	31.8	27.9	29.0	5.6
19.25	14.9	-57.7	-12.0	-15.3	84.9	1.0	30.5	27.5	28.6	6.0
19.50	13.2	-61.1	-12.3	-14.4	153.4	1.0	30.1	27.1	28.0	6.3
19.75	10.4	-69.9	-13.1	-13.2	591.8	1.0	30.8	26.3	26.9	7.0
20.00	8.3	-66.0	-13.1	-12.4	475.4	1.0	32.0	25.8	26.0	7.6

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 550 mA, V_{GG} = -0.74 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.8	-66.8	-8.1	-19.9	606.8	1.1	30.9	24.2	25.9	17.1
4.50	11.9	-70.2	-11.3	-27.9	433.7	1.1	33.1	25.2	28.1	12.9
5.00	16.6	-67.3	-15.5	-23.8	192.1	1.0	36.7	25.8	28.4	10.3
5.50	18.9	-67.0	-18.3	-19.1	142.4	1.0	37.5	26.1	28.1	8.6
6.00	20.1	-61.6	-18.4	-17.2	67.2	1.0	37.4	26.7	28.4	7.5
6.50	20.7	-61.8	-17.7	-17.4	63.9	1.0	37.3	26.7	28.4	6.8
7.00	20.9	-59.6	-17.9	-18.1	49.0	1.0	37.0	27.1	28.5	6.2
7.50	20.9	-56.9	-18.8	-17.9	36.0	1.0	37.4	27.2	28.4	5.8
8.00	20.8	-59.7	-19.6	-17.1	50.9	1.0	37.0	27.7	28.8	5.4
8.50	20.6	-58.6	-18.8	-15.8	45.8	1.0	37.3	28.3	29.5	5.2
9.00	20.5	-62.5	-17.3	-14.6	72.7	1.0	37.4	28.3	29.6	5.0
9.50	20.5	-64.7	-16.8	-14.0	93.2	1.0	38.3	27.8	28.9	4.8
10.00	20.5	-71.7	-17.4	-14.1	210.2	1.0	37.0	27.3	28.5	4.6
10.25	20.5	-69.0	-17.6	-14.4	154.4	1.0	36.4	27.5	29.1	4.5
10.50	20.5	-65.9	-17.6	-14.6	108.5	1.0	37.0	27.5	29.4	4.6
10.75	20.5	-64.8	-17.0	-15.0	95.0	1.0	35.7	27.5	29.7	4.5
11.00	20.5	-65.2	-16.6	-15.3	100.6	1.0	36.0	27.4	29.8	4.6
11.25	20.4	-64.2	-15.8	-15.7	90.0	1.0	36.2	27.1	29.8	4.5
11.50	20.3	-63.7	-15.0	-15.8	85.7	1.0	35.5	27.1	29.9	4.6
11.75	20.2	-62.5	-13.9	-15.9	75.8	1.0	35.5	26.8	29.7	4.6
12.00	20.1	-60.1	-13.0	-15.8	57.7	1.0	35.3	26.8	29.7	4.6
12.25	19.9	-58.2	-12.0	-15.6	46.9	1.0	34.9	26.7	29.8	4.7
12.50	19.8	-59.2	-11.4	-15.5	52.4	1.0	35.7	26.9	30.0	4.8
12.75	19.7	-60.3	-11.0	-15.3	59.8	1.0	34.7	26.8	29.9	4.8
13.00	19.7	-59.1	-11.1	-15.4	52.8	1.0	35.2	26.9	29.9	4.8
13.25	19.8	-59.0	-11.7	-15.8	52.7	1.0	35.0	26.8	29.7	4.8
13.50	19.8	-58.6	-12.6	-16.1	50.7	1.0	34.7	27.0	29.7	4.8
13.75	20.0	-57.2	-14.4	-16.8	43.7	1.0	34.8	26.9	29.4	4.8
14.00	20.0	-61.2	-16.1	-17.4	70.1	1.0	34.6	27.0	29.5	4.7
14.25	20.2	-60.8	-19.1	-18.3	67.1	1.0	35.0	27.0	29.6	4.6
14.50	20.2	-60.2	-21.3	-18.9	62.9	1.0	34.8	27.1	29.8	4.6
14.75	20.3	-61.2	-23.7	-19.8	69.9	1.0	34.6	27.2	29.8	4.5
15.00	20.4	-62.1	-24.2	-20.1	77.1	1.0	35.4	27.3	29.9	4.6
15.25	20.5	-56.8	-22.3	-19.7	41.7	1.0	35.2	27.2	29.6	4.5
15.50	20.6	-59.3	-20.2	-19.0	54.8	1.0	34.8	27.3	29.6	4.6
15.75	20.7	-57.8	-17.4	-17.7	45.1	1.0	34.6	27.2	29.3	4.6
16.00	20.7	-56.3	-15.9	-16.8	37.1	1.0	34.5	27.2	29.2	4.6
16.25	20.8	-54.6	-14.5	-16.0	29.9	1.0	34.7	26.9	28.7	4.6
16.50	20.9	-54.6	-13.8	-15.6	29.6	1.0	35.6	27.0	28.7	4.7
16.75	20.9	-54.4	-13.2	-14.9	28.6	1.0	35.2	27.2	28.6	4.6
17.00	21.0	-52.5	-12.9	-14.5	22.8	1.0	35.5	27.2	28.6	4.7
17.25	20.9	-52.3	-12.9	-14.2	22.3	1.0	35.9	27.4	28.7	4.7
17.50	20.9	-52.6	-12.9	-14.1	23.2	1.0	35.1	27.6	28.9	4.7
17.75	20.8	-52.4	-13.2	-14.4	23.2	1.0	36.0	27.6	28.8	4.8
18.00	20.8	-51.9	-13.6	-14.9	22.2	1.0	35.6	27.5	28.6	4.8
18.25	20.5	-51.7	-14.1	-16.1	22.7	1.0	35.7	27.5	28.7	4.9
18.50	20.2	-53.1	-14.0	-16.7	27.9	1.0	36.0	27.3	28.4	5.1
18.75	19.1	-55.1	-12.9	-16.8	39.5	1.0	36.1	27.1	28.0	5.4
19.00	18.0	-55.7	-12.2	-16.3	47.5	1.0	36.2	26.5	27.5	5.5
19.25	15.8	-60.7	-11.9	-15.3	109.3	1.0	36.3	26.2	27.3	5.9
19.50	14.0	-59.7	-12.3	-14.4	119.9	1.0	36.3	25.8	26.9	6.2
19.75	11.0	-66.2	-13.1	-13.2	359.0	1.0	34.0	25.1	26.0	6.9
20.00	8.8	-65.3	-13.2	-12.3	409.5	1.0	34.8	24.6	25.3	7.5

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 550 mA, V_{GG} = -0.84 V, I_{GG} = 0.81 mA, Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.3	-67.2	-8.1	-20.6	667.0	1.1	25.8	19.7	21.3	17.6
4.50	11.6	-67.7	-11.3	-34.6	338.6	1.1	28.2	21.8	23.8	13.3
5.00	16.3	-69.6	-15.6	-24.5	257.2	1.0	29.2	23.3	25.7	10.7
5.50	18.6	-70.5	-18.3	-18.7	221.2	1.0	29.9	24.1	26.4	9.0
6.00	19.7	-63.0	-18.3	-16.6	82.9	1.0	30.1	24.7	28.8	7.9
6.50	20.1	-60.4	-17.7	-17.0	58.1	1.0	30.4	25.0	29.5	7.2
7.00	20.3	-58.7	-17.9	-18.0	47.7	1.0	30.3	25.3	30.3	6.6
7.50	20.2	-59.1	-18.7	-18.1	51.2	1.0	31.1	25.7	30.7	6.1
8.00	19.9	-58.2	-19.5	-17.3	47.1	1.0	30.6	25.9	31.3	5.8
8.50	19.7	-62.3	-18.7	-15.9	77.6	1.0	30.9	26.1	31.7	5.5
9.00	19.5	-61.3	-17.3	-14.6	70.7	1.0	30.9	26.2	31.9	5.3
9.50	19.4	-62.8	-16.8	-13.9	84.6	1.0	32.2	26.2	31.4	5.1
10.00	19.3	-78.1	-17.3	-13.8	498.8	1.0	32.0	26.5	31.4	5.0
10.25	19.3	-72.2	-17.4	-14.0	253.9	1.0	32.6	26.7	31.5	4.9
10.50	19.3	-80.0	-17.3	-14.2	633.9	1.0	33.6	26.8	31.6	4.9
10.75	19.2	-67.8	-16.7	-14.5	157.0	1.0	33.3	27.0	31.5	4.8
11.00	19.1	-65.6	-16.3	-14.7	122.9	1.0	33.9	27.0	31.4	4.8
11.25	19.0	-65.1	-15.5	-15.0	118.0	1.0	34.8	27.0	31.3	4.9
11.50	18.9	-62.6	-14.9	-15.2	88.8	1.0	34.5	27.1	31.4	4.9
11.75	18.7	-60.9	-13.8	-15.2	74.1	1.0	35.0	27.1	31.3	4.9
12.00	18.6	-61.8	-13.1	-15.2	83.1	1.0	35.2	27.0	31.4	4.9
12.25	18.4	-60.6	-12.1	-15.0	73.2	1.0	34.9	26.9	31.3	5.1
12.50	18.3	-61.9	-11.6	-14.8	85.0	1.0	35.8	26.8	31.4	5.1
12.75	18.3	-62.4	-11.3	-14.7	90.9	1.0	35.2	26.9	31.2	5.2
13.00	18.2	-58.6	-11.4	-14.9	59.0	1.0	35.8	27.1	31.2	5.1
13.25	18.3	-60.6	-12.0	-15.3	74.3	1.0	35.8	27.2	31.1	5.2
13.50	18.4	-62.8	-12.9	-15.6	96.3	1.0	36.0	27.3	31.2	5.1
13.75	18.6	-63.3	-14.7	-16.5	103.1	1.0	35.7	27.7	31.3	5.1
14.00	18.7	-61.9	-16.4	-17.2	88.1	1.0	35.7	28.2	31.4	5.0
14.25	18.9	-60.2	-19.4	-18.4	72.2	1.0	35.6	28.3	31.5	4.9
14.50	19.0	-59.2	-21.5	-19.2	64.4	1.0	35.2	28.7	31.6	4.9
14.75	19.1	-60.4	-23.7	-20.2	73.3	1.0	35.3	29.0	31.7	4.9
15.00	19.2	-61.5	-24.0	-20.6	82.8	1.0	35.8	29.2	31.7	4.9
15.25	19.4	-60.9	-22.0	-20.2	75.7	1.0	35.4	29.2	31.5	4.9
15.50	19.5	-60.6	-20.0	-19.3	72.2	1.0	34.7	29.3	31.7	4.9
15.75	19.6	-58.7	-17.3	-17.9	56.5	1.0	34.4	29.6	31.6	5.0
16.00	19.6	-57.9	-15.8	-17.1	51.0	1.0	33.4	28.9	31.6	4.9
16.25	19.7	-56.0	-14.4	-16.2	40.2	1.0	33.9	28.7	31.2	5.0
16.50	19.7	-55.0	-13.8	-15.8	35.7	1.0	34.0	28.5	31.3	5.0
16.75	19.7	-54.1	-13.2	-15.1	31.7	1.0	33.1	28.5	31.2	5.0
17.00	19.7	-53.9	-12.9	-14.7	31.0	1.0	33.4	28.7	31.1	5.0
17.25	19.6	-52.9	-12.9	-14.5	28.1	1.0	32.6	28.8	30.8	5.0
17.50	19.5	-54.2	-13.0	-14.5	33.0	1.0	31.4	28.5	30.9	5.1
17.75	19.4	-52.7	-13.3	-14.7	28.6	1.0	31.2	28.2	30.9	5.1
18.00	19.2	-52.8	-13.6	-15.1	29.7	1.0	31.1	28.0	30.9	5.2
18.25	18.9	-53.3	-13.9	-16.0	32.9	1.0	30.4	27.7	31.2	5.3
18.50	18.5	-52.7	-13.7	-16.5	32.5	1.0	30.5	27.5	31.1	5.5
18.75	17.4	-55.9	-12.8	-16.6	52.8	1.0	28.1	27.3	30.9	5.7
19.00	16.3	-57.3	-12.3	-16.3	69.4	1.0	27.0	27.1	30.4	5.9
19.25	14.3	-59.0	-12.1	-15.3	107.0	1.0	27.0	26.7	29.9	6.3
19.50	12.7	-63.6	-12.4	-14.5	218.0	1.0	26.9	26.2	29.2	6.7
19.75	10.0	-68.6	-13.1	-13.3	530.6	1.0	26.0	25.6	26.7	7.4
20.00	8.0	-72.3	-13.1	-12.5	1014.1	1.0	26.9	25.1	25.2	8.0

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 550 mA, V_{GG} = -0.74 V, I_{GG} = 0.81 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	5.3	-66.6	-8.3	-18.0	567.6	1.1	32.0	22.5	24.1	15.9
4.50	12.6	-65.4	-11.1	-24.4	231.7	1.1	34.5	22.7	26.9	11.7
5.00	17.5	-70.0	-14.6	-22.5	237.0	1.0	37.6	24.2	26.9	9.2
5.50	20.0	-61.5	-17.2	-18.2	67.1	1.0	38.2	25.4	27.4	7.3
6.00	21.3	-64.5	-17.6	-16.5	81.7	1.0	38.0	25.6	28.1	6.3
6.50	22.0	-60.1	-17.1	-16.5	45.1	1.0	37.7	25.0	27.8	5.9
7.00	22.3	-59.3	-17.4	-16.7	40.0	1.0	37.3	25.9	28.1	5.6
7.50	22.4	-58.8	-18.0	-17.0	38.0	1.0	37.6	26.5	28.2	5.1
8.00	22.2	-57.1	-18.5	-16.3	31.8	1.0	37.2	26.6	28.5	4.6
8.50	22.0	-59.8	-17.5	-15.0	43.6	1.0	37.1	26.6	29.0	4.4
9.00	21.9	-61.4	-16.2	-13.9	53.3	1.0	37.2	27.1	29.4	4.2
9.50	21.9	-67.7	-15.9	-13.2	110.0	1.0	38.1	27.3	29.1	3.9
10.00	22.0	-66.1	-16.9	-13.8	91.9	1.0	37.9	26.6	28.6	3.8
10.25	22.0	-70.6	-17.5	-14.5	155.7	1.0	37.4	26.6	29.0	3.6
10.50	22.0	-72.3	-17.6	-14.7	187.6	1.0	37.9	26.6	29.3	3.5
10.75	22.0	-65.6	-17.0	-14.8	87.5	1.0	36.9	26.4	29.7	3.5
11.00	22.0	-66.1	-16.3	-14.9	92.7	1.0	36.9	26.5	30.0	3.5
11.25	21.9	-66.7	-15.1	-15.2	99.4	1.0	37.1	26.3	29.9	3.5
11.50	21.8	-64.7	-14.4	-15.4	80.0	1.0	36.5	26.4	29.9	3.6
11.75	21.6	-59.9	-13.2	-15.6	46.3	1.0	36.4	26.1	29.7	3.5
12.00	21.5	-63.0	-12.4	-15.6	66.7	1.0	36.1	26.0	29.7	3.7
12.25	21.4	-58.6	-11.4	-15.6	40.4	1.0	35.9	25.7	30.0	3.7
12.50	21.3	-60.1	-11.0	-15.7	48.1	1.0	36.5	25.6	30.1	3.7
12.75	21.2	-60.8	-10.8	-15.9	52.8	1.1	35.7	25.3	29.8	3.8
13.00	21.2	-60.2	-10.9	-16.0	49.4	1.1	36.0	25.4	29.6	3.9
13.25	21.2	-61.9	-11.6	-16.1	60.7	1.0	36.0	25.6	29.3	3.8
13.50	21.3	-58.7	-12.4	-16.2	42.4	1.0	35.6	25.8	29.2	3.9
13.75	21.4	-59.1	-14.1	-16.8	45.2	1.0	35.8	25.8	29.0	3.8
14.00	21.5	-61.0	-15.5	-17.4	56.3	1.0	35.6	25.8	29.0	3.8
14.25	21.6	-58.6	-18.1	-18.5	42.9	1.0	36.0	25.7	29.2	3.7
14.50	21.7	-60.8	-20.0	-19.1	55.0	1.0	35.8	25.7	29.4	3.7
14.75	21.8	-63.1	-22.6	-19.6	71.5	1.0	35.6	25.7	29.3	3.6
15.00	21.9	-60.7	-23.8	-19.7	54.0	1.0	36.3	25.8	29.1	3.6
15.25	22.0	-59.5	-23.1	-19.6	46.4	1.0	36.1	25.7	28.8	3.6
15.50	22.1	-59.1	-21.3	-19.2	44.0	1.0	35.8	25.7	28.7	3.6
15.75	22.2	-59.0	-18.5	-18.0	42.3	1.0	35.7	25.6	28.4	3.6
16.00	22.3	-56.9	-16.9	-17.0	32.3	1.0	35.3	25.6	28.4	3.6
16.25	22.5	-56.6	-15.0	-16.0	30.4	1.0	35.6	25.3	28.1	3.7
16.50	22.6	-54.9	-14.2	-15.6	24.6	1.0	36.0	25.4	28.0	3.6
16.75	22.7	-54.5	-13.4	-15.2	22.9	1.0	35.5	25.6	27.8	3.6
17.00	22.8	-53.1	-13.0	-14.8	19.1	1.0	35.8	25.7	27.7	3.7
17.25	22.9	-51.4	-12.9	-14.3	15.6	1.0	36.1	26.1	27.5	3.6
17.50	22.9	-50.3	-13.0	-14.0	13.8	1.0	35.8	26.4	27.8	3.6
17.75	22.9	-52.2	-13.0	-13.9	17.0	1.0	36.4	26.5	28.1	3.6
18.00	22.9	-52.7	-13.4	-14.3	18.3	1.0	36.2	26.6	28.1	3.6
18.25	22.8	-52.7	-13.9	-15.8	18.7	1.0	36.0	27.0	28.6	3.7
18.50	22.6	-51.8	-13.8	-16.5	17.3	1.0	35.8	26.7	28.4	3.7
18.75	21.8	-53.2	-12.3	-16.4	22.1	1.0	35.6	26.8	27.5	3.9
19.00	20.7	-54.1	-11.1	-15.5	26.9	1.0	36.1	26.6	27.2	4.1
19.25	18.5	-57.1	-10.4	-14.3	48.1	1.1	35.6	26.5	27.4	4.4
19.50	16.7	-59.6	-10.9	-13.7	80.1	1.0	36.5	26.1	27.2	4.7
19.75	13.7	-61.3	-12.6	-12.9	140.9	1.0	36.2	25.4	26.3	5.0
20.00	11.5	-60.8	-13.4	-12.3	171.8	1.0	35.4	24.9	25.7	5.6

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 550 mA, V_{GG} = -0.77 V, I_{GG} = 0.81 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	5.3	-62.0	-8.3	-18.3	332.4	1.1	27.7	19.9	23.8	16.0
4.50	12.7	-70.7	-11.2	-25.4	427.4	1.1	28.4	21.1	25.8	11.8
5.00	17.6	-64.7	-14.6	-22.7	126.7	1.0	32.3	22.2	27.5	9.3
5.50	20.0	-73.2	-17.2	-18.0	256.9	1.0	33.5	26.2	28.5	7.4
6.00	21.3	-63.2	-17.5	-16.3	69.9	1.0	33.8	26.8	29.1	6.3
6.50	21.9	-61.8	-17.1	-16.4	55.4	1.0	34.0	27.8	29.5	5.7
7.00	22.2	-58.5	-17.3	-16.7	37.3	1.0	33.6	28.0	30.0	5.2
7.50	22.2	-61.0	-17.9	-17.1	50.2	1.0	34.4	27.9	30.0	4.8
8.00	22.0	-58.8	-18.5	-16.4	39.7	1.0	33.5	28.1	30.3	4.5
8.50	21.7	-61.8	-17.5	-15.0	56.9	1.0	33.7	28.3	30.7	4.3
9.00	21.6	-61.7	-16.1	-13.9	56.9	1.0	33.4	28.2	30.9	4.0
9.50	21.5	-64.4	-15.9	-13.1	77.7	1.0	35.4	28.9	30.8	3.9
10.00	21.6	-66.8	-16.9	-13.7	104.1	1.0	35.3	29.2	30.6	3.7
10.25	21.6	-90.4	-17.4	-14.3	1587.9	1.0	35.8	29.6	30.9	3.7
10.50	21.6	-68.7	-17.4	-14.5	129.9	1.0	36.8	29.8	31.1	3.6
10.75	21.6	-77.9	-16.8	-14.6	375.2	1.0	36.3	30.0	31.3	3.6
11.00	21.5	-71.9	-16.0	-14.7	190.4	1.0	36.6	30.1	31.4	3.6
11.25	21.4	-68.0	-14.9	-15.0	122.3	1.0	37.2	29.8	31.5	3.6
11.50	21.3	-65.2	-14.2	-15.2	89.4	1.0	36.9	29.4	31.6	3.6
11.75	21.1	-61.3	-13.1	-15.3	57.9	1.0	37.2	28.9	31.5	3.7
12.00	21.0	-59.7	-12.4	-15.3	48.4	1.0	37.3	28.8	31.6	3.8
12.25	20.8	-64.5	-11.5	-15.4	84.6	1.0	37.0	28.9	31.7	3.9
12.50	20.8	-60.6	-11.1	-15.5	54.3	1.0	37.5	29.0	31.8	4.0
12.75	20.7	-60.0	-10.9	-15.7	50.7	1.1	37.0	28.3	31.5	4.0
13.00	20.7	-59.5	-11.0	-15.8	48.4	1.0	37.3	28.2	31.3	4.0
13.25	20.7	-60.0	-11.8	-15.9	51.7	1.0	37.2	27.9	30.9	4.0
13.50	20.8	-61.1	-12.6	-16.0	59.5	1.0	37.1	28.3	30.8	3.9
13.75	20.9	-61.3	-14.3	-16.7	61.5	1.0	37.2	28.0	30.7	3.9
14.00	21.0	-61.9	-15.7	-17.4	66.0	1.0	37.0	27.9	30.8	3.8
14.25	21.2	-60.3	-18.3	-18.5	54.8	1.0	37.0	27.6	31.2	3.7
14.50	21.3	-65.1	-20.3	-19.2	94.9	1.0	36.8	27.6	31.5	3.7
14.75	21.4	-59.7	-22.7	-19.8	50.5	1.0	36.7	27.6	31.6	3.7
15.00	21.5	-60.3	-23.9	-19.9	53.6	1.0	37.0	27.8	31.6	3.7
15.25	21.6	-60.6	-22.9	-19.8	55.0	1.0	36.9	27.7	31.3	3.7
15.50	21.7	-60.9	-21.1	-19.4	55.9	1.0	36.4	27.8	31.3	3.7
15.75	21.9	-57.8	-18.4	-18.1	38.2	1.0	36.3	27.6	31.1	3.7
16.00	22.0	-56.8	-16.8	-17.1	33.5	1.0	35.6	27.6	31.1	3.7
16.25	22.1	-57.2	-14.9	-16.0	34.1	1.0	35.7	27.2	30.5	3.8
16.50	22.2	-55.7	-14.2	-15.7	28.0	1.0	35.8	27.3	30.5	3.8
16.75	22.3	-55.1	-13.3	-15.2	25.6	1.0	35.6	27.8	30.3	3.8
17.00	22.4	-53.1	-13.0	-14.9	20.2	1.0	35.5	28.1	30.1	3.7
17.25	22.4	-54.1	-12.8	-14.4	22.5	1.0	35.1	28.9	29.9	3.7
17.50	22.3	-51.4	-13.0	-14.1	16.6	1.0	34.2	29.0	30.0	3.7
17.75	22.3	-53.1	-13.2	-13.9	20.2	1.0	34.0	29.1	29.9	3.8
18.00	22.3	-52.3	-13.5	-14.4	18.8	1.0	34.0	29.3	29.9	3.8
18.25	22.1	-50.9	-13.9	-15.8	16.5	1.0	33.7	29.7	30.6	3.9
18.50	21.9	-52.5	-13.6	-16.4	20.5	1.0	33.7	28.6	30.4	4.1
18.75	20.9	-51.8	-12.1	-16.2	20.6	1.0	31.6	28.3	30.0	4.3
19.00	19.9	-54.5	-11.0	-15.4	31.0	1.0	31.1	27.8	29.3	4.5
19.25	17.7	-57.1	-10.4	-14.3	52.7	1.0	30.1	27.9	28.8	4.9
19.50	16.0	-61.1	-11.0	-13.7	102.9	1.0	29.6	27.3	28.3	5.1
19.75	13.1	-77.2	-12.7	-12.9	935.9	1.0	29.4	26.5	27.5	5.8
20.00	11.0	-71.8	-13.5	-12.3	640.6	1.0	29.0	26.0	26.6	6.4

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 550 mA, V_{GG} = -0.84 V, I_{GG} = 0.81 mA, Temperature = -55°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	5.1	-65.7	-8.3	-18.4	524.5	1.1	26.4	17.4	21.8	16.2
4.50	12.5	-68.6	-11.2	-26.5	341.5	1.1	27.6	19.2	23.7	12.0
5.00	17.4	-64.4	-14.7	-23.1	124.8	1.0	27.8	21.1	25.1	9.4
5.50	19.8	-71.4	-17.2	-17.9	212.8	1.0	27.8	22.7	26.0	7.5
6.00	21.1	-62.7	-17.5	-16.1	68.0	1.0	27.5	24.1	27.0	6.5
6.50	21.6	-62.1	-17.1	-16.2	59.4	1.0	27.5	24.5	28.3	6.1
7.00	21.8	-57.5	-17.3	-16.7	34.6	1.0	27.4	25.1	30.3	5.8
7.50	21.8	-59.6	-17.9	-17.2	44.5	1.0	28.5	25.4	31.0	5.3
8.00	21.6	-62.8	-18.4	-16.4	65.7	1.0	27.8	25.9	31.6	4.8
8.50	21.3	-60.4	-17.4	-15.0	51.1	1.0	28.5	26.4	32.5	4.6
9.00	21.1	-64.7	-16.1	-13.9	84.4	1.0	28.3	26.5	32.5	4.3
9.50	21.1	-63.5	-15.9	-13.1	74.0	1.0	30.3	26.2	32.4	4.1
10.00	21.1	-73.1	-16.9	-13.6	226.9	1.0	30.1	26.5	31.7	3.9
10.25	21.1	-70.7	-17.3	-14.2	173.5	1.0	30.7	27.1	32.3	3.8
10.50	21.1	-73.1	-17.3	-14.4	230.8	1.0	31.9	27.5	32.5	3.7
10.75	21.0	-74.2	-16.6	-14.4	261.5	1.0	31.5	27.9	32.7	3.7
11.00	20.9	-67.4	-15.8	-14.5	120.6	1.0	32.2	28.1	32.7	3.7
11.25	20.8	-66.8	-14.8	-14.8	113.8	1.0	33.2	28.2	32.6	3.7
11.50	20.7	-63.8	-14.1	-15.0	81.2	1.0	32.7	28.3	32.4	3.7
11.75	20.5	-66.1	-13.1	-15.1	108.2	1.0	33.3	28.2	32.3	3.8
12.00	20.3	-60.8	-12.3	-15.1	58.9	1.0	33.6	27.9	32.3	3.8
12.25	20.2	-59.7	-11.5	-15.1	52.3	1.0	33.2	27.8	32.3	3.8
12.50	20.1	-60.0	-11.1	-15.3	54.6	1.0	34.4	27.7	32.6	4.0
12.75	20.0	-61.0	-11.0	-15.5	61.8	1.0	33.8	27.9	32.6	4.0
13.00	20.0	-58.0	-11.2	-15.6	44.0	1.0	34.6	27.9	32.5	4.1
13.25	20.1	-58.9	-11.9	-15.6	49.2	1.0	34.7	27.8	32.5	4.0
13.50	20.1	-59.5	-12.8	-15.8	52.9	1.0	35.3	27.8	32.5	4.0
13.75	20.3	-63.1	-14.6	-16.5	80.7	1.0	35.0	27.7	32.2	4.0
14.00	20.4	-60.8	-15.9	-17.2	61.9	1.0	35.1	28.0	32.3	3.8
14.25	20.6	-60.8	-18.5	-18.5	62.4	1.0	35.0	28.5	32.4	3.8
14.50	20.7	-63.7	-20.4	-19.3	86.1	1.0	34.8	29.0	32.6	3.8
14.75	20.8	-60.5	-22.8	-19.9	59.3	1.0	34.8	29.8	32.8	3.8
15.00	21.0	-61.0	-23.8	-20.0	62.1	1.0	35.2	30.0	32.9	3.7
15.25	21.1	-62.8	-22.7	-19.9	75.2	1.0	35.0	30.4	32.8	3.8
15.50	21.2	-60.2	-21.0	-19.5	54.9	1.0	34.2	30.7	32.8	3.8
15.75	21.4	-59.6	-18.4	-18.2	49.7	1.0	34.1	30.9	32.7	3.7
16.00	21.5	-57.3	-16.8	-17.1	37.3	1.0	32.6	29.9	32.7	3.8
16.25	21.6	-56.0	-14.9	-16.1	31.4	1.0	33.3	28.9	32.2	3.7
16.50	21.7	-56.3	-14.1	-15.8	31.8	1.0	33.0	28.7	32.2	3.7
16.75	21.7	-55.7	-13.3	-15.3	29.1	1.0	32.5	28.7	32.0	3.8
17.00	21.8	-53.8	-13.0	-15.0	23.1	1.0	32.6	28.9	31.9	3.8
17.25	21.7	-52.0	-12.8	-14.5	18.9	1.0	31.5	29.2	31.6	3.8
17.50	21.7	-52.8	-13.0	-14.2	21.0	1.0	29.9	29.5	31.7	3.7
17.75	21.6	-51.4	-13.2	-14.0	18.0	1.0	29.6	29.7	31.8	3.8
18.00	21.5	-53.9	-13.6	-14.5	24.6	1.0	29.5	29.2	31.6	3.8
18.25	21.3	-53.5	-13.9	-15.9	24.4	1.0	29.5	28.4	31.8	3.9
18.50	21.0	-53.2	-13.5	-16.4	24.3	1.0	29.5	28.1	31.6	4.0
18.75	20.0	-53.1	-12.0	-16.0	26.5	1.0	25.7	28.0	31.5	4.1
19.00	19.0	-56.0	-10.9	-15.3	40.9	1.0	25.2	27.5	30.9	4.4
19.25	16.9	-58.1	-10.5	-14.3	65.6	1.0	24.9	27.0	30.5	4.6
19.50	15.3	-66.5	-11.0	-13.6	207.6	1.0	24.7	26.2	30.1	4.9
19.75	12.5	-61.3	-12.8	-13.0	161.9	1.0	24.1	24.9	28.4	5.3
20.00	10.5	-71.7	-13.5	-12.4	680.7	1.0	22.3	24.0	26.9	5.9

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +5 V, I_{DD} = 550 mA, V_{GG} = -0.74 V, I_{GG} = 0.81 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	4.1	-67.5	-8.1	-20.9	698.8	1.1	30.8	22.8	24.9	18.2
4.50	11.2	-65.7	-11.5	-32.0	278.4	1.1	33.4	23.0	27.2	14.0
5.00	15.8	-64.3	-16.1	-24.6	148.3	1.0	36.5	24.2	27.5	11.4
5.50	18.0	-68.3	-19.1	-19.1	183.7	1.0	37.1	25.3	27.5	9.5
6.00	19.1	-65.4	-19.1	-17.3	116.4	1.0	37.2	25.4	27.8	8.5
6.50	19.6	-63.2	-18.1	-17.6	85.8	1.0	37.1	25.2	27.7	8.2
7.00	19.7	-58.8	-18.2	-18.1	51.1	1.0	37.0	26.3	28.0	7.8
7.50	19.7	-58.1	-19.2	-18.3	48.1	1.0	37.6	26.6	28.1	7.3
8.00	19.5	-58.9	-20.3	-17.4	54.1	1.0	37.2	26.6	28.4	6.9
8.50	19.3	-58.9	-19.4	-16.0	55.2	1.0	37.3	26.9	29.0	6.5
9.00	19.2	-63.3	-17.8	-14.9	92.8	1.0	37.2	27.3	29.2	6.3
9.50	19.1	-67.5	-17.3	-14.1	150.2	1.0	37.6	26.8	28.8	6.0
10.00	19.1	-79.1	-17.9	-14.2	577.5	1.0	35.9	26.3	28.5	5.9
10.25	19.1	-63.0	-18.1	-14.5	90.5	1.0	35.4	26.1	28.8	5.7
10.50	19.1	-63.3	-17.9	-14.6	94.7	1.0	36.1	26.0	28.9	5.6
10.75	19.1	-68.9	-17.3	-14.8	181.2	1.0	34.8	25.7	29.0	5.7
11.00	19.1	-64.1	-16.7	-15.0	105.3	1.0	35.1	25.6	29.0	5.7
11.25	19.0	-60.4	-16.0	-15.5	69.4	1.0	35.4	25.5	29.0	5.6
11.50	18.9	-62.5	-15.4	-15.9	89.4	1.0	34.7	25.6	29.1	5.7
11.75	18.8	-60.2	-14.3	-16.1	69.2	1.0	34.7	25.4	29.1	5.7
12.00	18.7	-58.6	-13.5	-16.0	58.1	1.0	34.6	25.4	29.2	5.7
12.25	18.5	-58.1	-12.5	-15.7	55.1	1.0	34.2	25.1	29.1	5.8
12.50	18.4	-59.3	-11.9	-15.5	63.1	1.0	35.1	25.2	29.1	5.9
12.75	18.3	-57.7	-11.4	-15.4	53.2	1.0	34.2	25.0	28.9	6.0
13.00	18.3	-60.4	-11.4	-15.4	72.3	1.0	34.6	25.2	29.0	6.0
13.25	18.4	-58.6	-12.0	-15.5	59.4	1.0	34.5	25.3	29.0	6.1
13.50	18.5	-61.1	-12.9	-15.8	79.5	1.0	34.1	25.6	29.2	6.0
13.75	18.6	-61.4	-14.8	-16.5	83.9	1.0	34.3	25.6	29.3	6.0
14.00	18.7	-59.4	-16.5	-17.3	67.0	1.0	34.0	25.7	29.4	6.0
14.25	18.8	-60.4	-19.6	-18.6	75.5	1.0	34.4	25.7	29.5	5.9
14.50	18.9	-60.9	-22.0	-19.6	80.0	1.0	34.4	25.8	29.6	5.8
14.75	19.0	-59.9	-24.3	-20.7	70.7	1.0	34.2	25.9	29.6	5.8
15.00	19.1	-58.4	-24.6	-21.0	59.2	1.0	35.0	26.0	29.7	5.8
15.25	19.2	-59.2	-22.3	-20.6	64.3	1.0	34.7	26.0	29.5	5.8
15.50	19.3	-57.1	-20.2	-19.7	50.3	1.0	34.7	26.1	29.5	5.9
15.75	19.4	-55.6	-17.4	-17.9	41.6	1.0	34.3	26.1	29.2	5.9
16.00	19.4	-54.1	-15.9	-16.8	34.4	1.0	34.3	26.2	29.2	5.9
16.25	19.4	-54.9	-14.5	-15.8	37.1	1.0	34.3	26.0	28.8	5.9
16.50	19.5	-55.7	-13.9	-15.5	40.5	1.0	35.6	26.1	29.0	6.0
16.75	19.5	-52.9	-13.2	-15.0	29.1	1.0	35.4	26.3	28.8	6.0
17.00	19.5	-52.5	-13.0	-14.7	27.6	1.0	35.8	26.3	28.7	6.1
17.25	19.4	-51.8	-13.0	-14.5	25.8	1.0	35.8	26.4	28.6	6.0
17.50	19.3	-52.8	-13.3	-14.5	29.4	1.0	35.1	26.6	28.7	6.1
17.75	19.2	-52.5	-13.7	-14.9	29.3	1.0	36.1	26.7	28.7	6.1
18.00	19.1	-51.8	-14.2	-15.6	27.6	1.0	35.7	26.7	28.7	6.2
18.25	18.8	-51.5	-14.7	-17.0	28.2	1.0	35.9	26.7	28.8	6.2
18.50	18.4	-53.4	-14.4	-17.5	36.6	1.0	36.5	26.4	28.4	6.4
18.75	17.2	-55.1	-13.5	-17.2	50.5	1.0	36.7	26.3	28.1	6.5
19.00	16.1	-55.5	-12.9	-16.6	60.3	1.0	36.9	25.8	27.5	6.9
19.25	13.9	-58.5	-12.7	-15.5	108.7	1.0	35.0	25.4	26.9	7.1
19.50	12.1	-61.7	-13.0	-14.5	191.4	1.0	35.1	24.8	26.2	7.6
19.75	9.2	-66.5	-13.7	-13.4	465.8	1.0	33.6	24.1	25.1	8.1
20.00	7.1	-61.1	-13.4	-12.5	317.0	1.0	35.6	23.6	24.4	9.1

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +6 V, I_{DD} = 550 mA, V_{GG} = -0.77 V, I_{GG} = 0.81 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	3.9	-64.9	-8.1	-21.4	533.3	1.1	32.5	21.0	24.0	18.3
4.50	11.1	-64.0	-11.5	-37.2	233.3	1.1	33.7	21.9	26.6	14.1
5.00	15.6	-74.2	-16.1	-24.8	470.6	1.0	34.2	23.9	27.7	11.5
5.50	17.8	-67.1	-19.1	-18.8	163.4	1.0	34.5	25.4	27.9	9.6
6.00	18.8	-59.6	-19.0	-16.9	61.6	1.0	34.5	25.5	28.3	8.6
6.50	19.2	-59.7	-18.1	-17.4	59.8	1.0	34.6	25.2	28.7	8.0
7.00	19.3	-56.8	-18.1	-18.1	42.4	1.0	34.5	26.7	29.3	7.4
7.50	19.2	-59.3	-19.1	-18.3	58.0	1.0	35.3	27.0	29.5	7.0
8.00	19.0	-56.1	-20.2	-17.6	41.4	1.0	35.0	26.8	29.9	6.7
8.50	18.8	-56.9	-19.3	-16.0	46.5	1.0	35.4	26.9	30.4	6.4
9.00	18.6	-61.5	-17.8	-15.0	80.3	1.0	35.5	27.3	30.7	6.1
9.50	18.5	-66.5	-17.3	-14.1	144.7	1.0	36.9	27.4	30.5	6.0
10.00	18.5	-68.1	-17.9	-14.0	176.0	1.0	36.7	27.3	30.3	5.8
10.25	18.4	-69.3	-17.9	-14.2	203.8	1.0	36.5	27.4	30.4	5.7
10.50	18.4	-67.4	-17.7	-14.3	164.2	1.0	37.1	27.4	30.5	5.7
10.75	18.3	-70.2	-17.1	-14.5	227.3	1.0	36.1	27.2	30.5	5.7
11.00	18.3	-63.6	-16.6	-14.7	108.0	1.0	36.3	26.8	30.4	5.7
11.25	18.2	-64.4	-15.9	-15.2	119.6	1.0	36.5	26.6	30.3	5.7
11.50	18.1	-63.6	-15.3	-15.5	110.8	1.0	35.9	26.7	30.4	5.8
11.75	17.9	-58.4	-14.3	-15.8	61.9	1.0	36.0	26.5	30.4	5.8
12.00	17.8	-58.2	-13.6	-15.7	60.7	1.0	35.8	26.4	30.4	5.9
12.25	17.6	-59.3	-12.5	-15.3	69.4	1.0	35.5	26.1	30.3	6.0
12.50	17.6	-59.3	-12.0	-15.1	69.6	1.0	36.1	26.1	30.3	6.1
12.75	17.5	-60.1	-11.5	-15.0	77.0	1.0	35.2	25.9	30.1	6.1
13.00	17.5	-59.1	-11.6	-15.1	68.6	1.0	35.6	26.1	30.1	6.2
13.25	17.6	-59.2	-12.1	-15.3	70.2	1.0	35.5	26.3	30.1	6.2
13.50	17.7	-59.3	-13.0	-15.6	70.8	1.0	35.2	26.7	30.4	6.1
13.75	17.8	-60.1	-14.9	-16.4	78.5	1.0	35.3	26.7	30.5	6.1
14.00	17.9	-61.1	-16.6	-17.2	88.5	1.0	34.9	26.7	30.5	6.0
14.25	18.1	-59.6	-19.8	-18.7	75.1	1.0	35.3	26.7	30.6	5.9
14.50	18.2	-58.8	-22.1	-19.8	68.3	1.0	35.2	26.7	30.7	5.9
14.75	18.4	-59.1	-24.3	-21.1	69.7	1.0	35.1	26.9	30.7	5.9
15.00	18.4	-59.5	-24.5	-21.4	73.0	1.0	35.7	27.1	30.8	5.9
15.25	18.6	-58.3	-22.1	-20.8	62.8	1.0	35.2	27.2	30.7	5.9
15.50	18.6	-60.2	-19.9	-19.8	76.7	1.0	35.2	27.4	30.8	6.0
15.75	18.7	-55.2	-17.2	-18.1	42.6	1.0	34.6	27.4	30.6	6.0
16.00	18.8	-56.2	-15.8	-17.1	47.2	1.0	35.1	27.5	30.5	6.0
16.25	18.8	-54.3	-14.4	-16.0	37.2	1.0	34.4	27.5	30.2	6.1
16.50	18.8	-54.5	-13.9	-15.6	38.0	1.0	35.0	27.7	30.3	6.0
16.75	18.8	-54.8	-13.3	-15.0	39.3	1.0	34.7	27.9	30.1	6.1
17.00	18.7	-53.1	-13.1	-14.8	32.4	1.0	36.0	27.9	30.0	6.1
17.25	18.6	-52.2	-13.0	-14.6	29.7	1.0	35.0	27.8	29.8	6.2
17.50	18.5	-51.9	-13.3	-14.7	29.2	1.0	34.9	28.0	29.9	6.2
17.75	18.4	-51.4	-13.7	-15.0	28.3	1.0	34.3	28.3	30.0	6.3
18.00	18.2	-51.5	-14.1	-15.6	29.5	1.0	35.0	28.2	30.0	6.4
18.25	17.8	-52.9	-14.4	-16.7	36.6	1.0	33.8	28.0	30.2	6.5
18.50	17.4	-53.9	-14.2	-17.2	43.4	1.0	34.6	27.7	29.9	6.6
18.75	16.3	-54.1	-13.5	-17.3	50.2	1.0	31.6	27.4	29.6	6.9
19.00	15.2	-57.3	-13.1	-16.9	81.8	1.0	30.8	26.9	29.0	7.2
19.25	13.1	-60.3	-12.9	-15.7	147.0	1.0	31.4	26.4	28.2	7.8
19.50	11.5	-60.6	-13.1	-14.7	182.0	1.0	31.0	25.9	27.2	8.2
19.75	8.7	-63.6	-13.6	-13.5	354.5	1.0	30.8	25.1	25.8	9.1
20.00	6.7	-67.2	-13.2	-12.6	671.1	1.0	31.2	24.6	25.1	9.9

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:
Input Return Loss = S11 (dB)
Gain(Power Gain) = S21 (dB)
Isolation = S12 (dB)
Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{DD} = +7 V, I_{DD} = 550 mA, V_{GG} = -0.84 V, I_{GG} = 0.81 mA, Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output P_{OUT} = +16 dBm/Tone	1dB Comp. Output	P_{SAT} Output	Noise Figure
(GHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dBm)	(dB)
4.00	3.5	-65.2	-8.1	-21.5	581.6	1.1	27.8	18.3	22.2	18.6
4.50	10.8	-63.6	-11.5	-44.6	231.4	1.1	29.5	19.4	24.9	14.3
5.00	15.4	-72.3	-16.1	-24.8	389.5	1.0	32.0	21.2	26.6	11.7
5.50	17.5	-82.6	-19.1	-18.6	1004.4	1.0	32.5	22.7	26.9	9.7
6.00	18.5	-66.9	-18.9	-16.6	147.9	1.0	32.5	22.9	27.8	8.8
6.50	18.9	-59.9	-18.1	-17.2	63.6	1.0	32.6	22.8	28.4	8.4
7.00	18.9	-59.1	-18.1	-18.1	58.0	1.0	32.6	24.0	29.5	8.0
7.50	18.8	-59.5	-19.0	-18.4	62.9	1.0	33.0	24.4	29.7	7.5
8.00	18.5	-60.3	-20.2	-17.7	71.1	1.0	32.9	24.2	30.0	7.1
8.50	18.2	-59.9	-19.3	-16.1	69.7	1.0	33.1	24.2	30.3	6.8
9.00	18.0	-65.4	-17.8	-15.0	133.8	1.0	33.3	24.4	30.6	6.5
9.50	17.9	-65.0	-17.4	-14.0	130.2	1.0	33.9	24.6	30.6	6.2
10.00	17.8	-66.3	-17.8	-13.8	154.6	1.0	33.8	24.6	30.4	6.0
10.25	17.7	-69.9	-17.8	-14.0	234.0	1.0	34.1	24.8	30.4	5.9
10.50	17.7	-65.5	-17.6	-14.1	142.9	1.0	34.8	24.9	30.4	5.8
10.75	17.6	-60.1	-16.9	-14.3	77.8	1.0	34.5	25.0	30.3	5.8
11.00	17.5	-64.6	-16.5	-14.4	131.9	1.0	34.8	25.0	30.2	5.8
11.25	17.4	-60.1	-15.8	-14.9	80.2	1.0	35.5	24.9	30.2	5.8
11.50	17.3	-62.1	-15.3	-15.2	102.4	1.0	35.2	25.0	30.3	5.9
11.75	17.1	-58.9	-14.3	-15.5	71.5	1.0	35.5	25.1	30.3	5.9
12.00	17.0	-60.1	-13.6	-15.4	82.8	1.0	35.6	25.3	30.3	5.9
12.25	16.8	-60.7	-12.6	-15.0	89.6	1.0	35.3	25.4	30.2	6.0
12.50	16.7	-60.2	-12.1	-14.8	84.7	1.0	35.9	25.4	30.4	6.1
12.75	16.7	-58.4	-11.7	-14.7	69.0	1.0	35.3	25.3	30.2	6.2
13.00	16.7	-60.7	-11.7	-14.8	91.1	1.0	35.6	25.3	30.4	6.3
13.25	16.8	-59.7	-12.3	-15.1	81.3	1.0	35.6	25.4	30.4	6.2
13.50	16.9	-60.7	-13.1	-15.4	91.3	1.0	35.5	25.7	30.6	6.2
13.75	17.1	-62.0	-15.0	-16.3	106.6	1.0	35.3	26.0	30.7	6.2
14.00	17.2	-60.4	-16.7	-17.1	88.9	1.0	34.9	26.4	30.8	6.1
14.25	17.4	-62.3	-19.9	-18.8	110.9	1.0	35.0	26.8	30.9	6.1
14.50	17.5	-59.6	-22.1	-20.0	81.6	1.0	34.6	27.1	31.0	6.0
14.75	17.7	-60.0	-24.3	-21.3	84.3	1.0	34.6	27.3	31.1	6.0
15.00	17.8	-59.1	-24.3	-21.6	75.5	1.0	34.8	27.5	31.2	6.0
15.25	17.9	-58.4	-22.0	-21.0	68.9	1.0	34.5	27.4	31.1	5.9
15.50	18.0	-59.5	-19.8	-20.0	76.5	1.0	34.1	27.6	31.3	6.0
15.75	18.1	-55.8	-17.1	-18.3	49.3	1.0	33.6	27.5	31.1	6.0
16.00	18.1	-55.6	-15.7	-17.2	47.7	1.0	33.2	27.5	31.1	6.0
16.25	18.1	-57.1	-14.4	-16.1	55.5	1.0	32.7	27.3	30.8	6.1
16.50	18.1	-53.3	-13.9	-15.7	35.7	1.0	32.8	27.4	30.9	6.0
16.75	18.0	-53.9	-13.3	-15.1	38.6	1.0	32.3	27.3	30.8	6.2
17.00	18.0	-52.6	-13.1	-14.9	33.3	1.0	34.2	27.2	30.7	6.1
17.25	17.8	-51.9	-13.1	-14.8	31.4	1.0	32.7	27.1	30.6	6.2
17.50	17.7	-52.2	-13.3	-14.9	33.2	1.0	32.7	27.1	30.7	6.2
17.75	17.5	-52.3	-13.6	-15.2	34.5	1.0	31.5	26.8	30.6	6.3
18.00	17.4	-52.6	-14.0	-15.7	36.9	1.0	32.0	26.4	30.6	6.4
18.25	16.9	-52.9	-14.3	-16.6	40.4	1.0	31.0	26.3	30.7	6.5
18.50	16.5	-54.6	-14.1	-17.1	52.4	1.0	31.0	26.0	30.4	6.5
18.75	15.4	-55.6	-13.5	-17.3	66.2	1.0	27.6	25.9	30.0	6.7
19.00	14.3	-56.1	-13.2	-16.9	78.7	1.0	26.2	25.5	29.3	7.1
19.25	12.4	-58.8	-13.0	-15.8	134.3	1.0	27.8	25.0	28.3	7.3
19.50	10.8	-67.5	-13.2	-14.8	437.3	1.0	27.6	24.4	27.1	7.9
19.75	8.2	-65.4	-13.5	-13.6	464.4	1.0	27.1	23.3	25.4	8.4
20.00	6.2	-63.1	-13.2	-12.7	443.0	1.0	27.1	22.6	24.1	9.2

Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.

GAIN vs. TEMPERATURE
P_{IN} = -25 dBm



GAIN vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



INPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm



INPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



OUTPUT RETURN LOSS vs. TEMPERATURE
P_{IN} = -25 dBm



OUTPUT RETURN LOSS vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.

ISOLATION vs. TEMPERATURE
P_{IN} = -25 dBm



ISOLATION vs. DEVICE VOLTAGE (V_{DD})
P_{IN} = -25 dBm, TEMPERATURE = +25°C



P1dB vs. TEMPERATURE



P1dB vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



P_{SAT} vs. TEMPERATURE



P_{SAT} vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.

OUTPUT IP3 vs. TEMPERATURE
P_{OUT} = +16 dBm/TONE



OUTPUT IP3 vs. DEVICE VOLTAGE (V_{DD})
P_{OUT} = +16 dBm/TONE, TEMPERATURE = +25°C



OUTPUT IP3 vs. P_{OUT}
TEMPERATURE = +25°C



GAIN VARIATION vs. TEMPERATURE
P_{IN} = -25 dBm



NOISE FIGURE vs. TEMPERATURE



NOISE FIGURE vs. DEVICE VOLTAGE (V_{DD})
TEMPERATURE = +25°C



Typical Performance Curves

Note: Data over temperature was taken at V_{DD} = +6 V. For over temperature data, V_{GG} was adjusted until I_{DD} = 550 mA at all temperatures specified. For over voltage data, V_{GG} was adjusted until I_{DD} = 550 mA at all V_{DD} levels specified. For additional data over additional current levels at specified voltages, see the View Data page of the model dashboard.







Case Style DG

Outline Dimensions

DG1677-8



TOP VIEW



SIDE VIEW



BOTTOM VIEW

PCB Land Pattern



Suggested Layout,
Tolerance to be within ±0.050[0.002]

NOTES:

1. ▨ DENOTES METALLIZATION

Weight: .056 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl.±0.254[0.01]; 3 Pl.±.0.127[0.005] mm[Inches]

Notes:

1. Case material: Plastic.
2. Termination finish: PPF (NiPdAu Plating 0.5 µm/0.02µm/0.05µm)

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F102

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-026829	NEW RELEASE	09/03/25	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR DG1677-8 CASE STYLE



COMPONENT	SIZE
C1,C10,C13,C14	1206
C2,C4,C7,C9,C12,C15	0402
C3,C5,C6,C8,C11,C16	0603
C17,C18	0201

NOTES:

1. LINE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"; COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS LINE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-AVA-6183MPC+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	09/03/25
TOLERANCES ON:	CHECKED	GF	09/03/25
2 PL DECIMALS ±	APPROVED	IL	09/03/25
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, DG1677-8, TB-AVA-6183MPC+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-833	OR

FILE:	SCALE:	SHEET:
98PL833	4:1	1 OF 1

Evaluation Board and Circuit





DETAIL "A" ROTATED
LOCATION OF
UNITS COMPONENTS
(SCALE 2:1)



Schematic Diagram

Components	Size	Value	Part Numbers	Manufacturer
C3,C5,C6,C8,C11,C16	0603	100pF	B55-19-101G-1+	AVX
C2,C4,C7,C9,C12,C15	0402	0.01uF	B55-33-103K+	Murata
C1,C10,C13,C14	1206	10uF	B55-109-106K+	Samsung
C17,C18,C19,C20	0201	30pF	B55-104-300M+	DLI
J1,J2,J3,J4	N/A	N/A	B20-123-F1+	Southwest

NOTES:

1. 2.4 mm Female Connectors.
2. PCB Material: Roger RO4350B or equivalent, Dielectric constant=3.5, Thickness=0.010 inch

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications **ENV08T10**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to +85° C, -55° to +95°C	Individual Model Data Sheet
Storage Temperature	-65° to 150°C	Individual Model Data Sheet
Moisture Sensitivity: Level 3	Bake at 125°C for 24 hours. Soak at 30°C/60%RH for 192 hours, Reflow 3 cycles at 260°C peak	J-STD-020D
Unbiased HAST	Temperature: 130°C, RH: 85%, Pressure: 33.3 psia Duration: 96 hours	JESD22-A118A, Test Condition A
Temperature Cycling	-65°C to +150°C, Dwell Time: 15 mins 500 cycles	JESD22-A104E, Condition C
HTSL	Temperature: 150°C Duration: 1000 hours	JESD22-A103E, Test Condition B
HTOL	1000 Hours at 125°C	JESD22-A108
ESD HBM	Refer datasheet for classification	JS-001
ESD CDM	Refer datasheet for classification	JESD22-C101
Vibration (Variable Frequency)	Sinusoidal vibration, 20 - 2000 Hz, 4 min sweeps, 16 min along each of 3 axis, amplitude limits of 20g and 0.06 in	MIL-STD-883, Method 2007, Condition A
Drop Test	1m drops onto concrete in final packed box in 6 orientations	--

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Bend Test	1mm deflection for 5 seconds. Board thickness: 0.024", Span: 2.75"	--
Solderability	10x magnification	J-STD-002 Method B, B1
Resistance to Soldering Heat	Sn-Pb Eutectic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020

This document and its contents are the property of Mini-Circuits.