

Flat Gain, High IP3

# Monolithic Amplifier

CMA-62+

50Ω      0.01 to 6 GHz

## The Big Deal

- Ceramic, Hermetically Sealed, Nitrogen filled
- Low profile case, .045" high
- Ultra Flat Gain
- Broadband High Dynamic Range without external Matching Components



CASE STYLE: DL1721  
MIL Screening Available  
Please consult Applications Dept.

## Product Overview

CMA-62+ (RoHS compliant) is a wideband amplifier fabricated using HBT technology and offers ultra flat gain over a broad frequency range and with high IP3. In addition, the CMA-62+, has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability. The MMIC amplifier is bonded to a multilayer integrated LTCC substrate, and then hermetically sealed under a controlled nitrogen atmosphere with gold-plated covers and eutectic AuSn solder. These amplifiers are capable of meeting MIL requirements for gross leak, fine leak, thermal shock, vibration, acceleration, mechanical shock, and HTOL. The testing can be done if requested.

## Key Features

Feature	Advantages
Broad Band: 0.01 to 6.0 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX, SATELLITE IF
Ultra Flat Gain	±0.6 dB over 50 to 3000 MHz; ±0.10 dB over 700 to 2700 MHz eliminates need for gain flattening for most applications
High IP3 vs. DC power Consumption 39 dBm typical at 0.05 GHz 37 dBm typical at 0.8 GHz	The CMA-62+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and HBT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 20 dB above the P 1dB point to 0.8 GHz. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"><li>• Driver amplifiers for complex waveform up converter paths</li><li>• Drivers in linearized transmit systems</li></ul>
No External Matching Components Required	CMA-62+ provides Input and Output Return Loss of 10-23 dB up to 7 GHz without the need for any external matching components
Ceramic Hermetic Package	Low Inductance, repeatable performance, excellent reliability.



Flat Gain, High IP3

# Monolithic Amplifier

0.01-6 GHz

## Product Features

- Flat Gain,  $\pm 0.7$  dB over 50-4000 MHz
- Gain, 15.4 dB typ. at 2 GHz
- High Pout, P1dB 19 dBm typ. at 2 GHz
- High IP3, 39.0 dBm typ. at 50 MHz; 33.0 dBm at 2GHz
- Excellent ESD protection, Class 1C for HBM
- No external matching components required
- Small size - 3mm x 3mm x 1.14mm
- Ceramic, hermetic, Nitrogen filled


## Typical Applications

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

## General Description

CMA-62+ (RoHS compliant) is an advanced wideband amplifier fabricated using HBT technology and offers ultra flat gain over a broad frequency range and with high IP3. In addition, the CMA-62+ has good input and output return loss over a broad frequency range without the need for external matching components. Terminal finish is Ni-pd-Au and it has repeatable performance from lot to lot due to fully automated, tightly controlled semiconductor and assembly processes.

## simplified schematic and pin description




Generic photo used for illustration purposes only

CASE STYLE: DL1721

## CMA-62+

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Function	Pin Number	Description
RF IN	2	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	7	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2
GND	1,3,4,5,6,8, Bottom Center Paddle	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

Electrical Specifications<sup>1,2</sup> at 25°C, unless noted

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range <sup>2</sup>		0.01		6	GHz
Gain	0.05	15.5	16.6	18.0	dB
	0.8	14.5	15.6	16.5	
	2.0		15.4		
	3.0		15.4		
	4.0	14.0	15.2	16.0	
	6.0		13.7		
Gain Flatness	0.05 - 3.0		±0.6		dB
	0.7 - 2.6		±0.1		
Input Return Loss	0.05		16.5		dB
	0.8	10.0	13.6		
	2.0		14.7		
	3.0		22.7		
	4.0		25.9		
	6.0		13.9		
Output Return Loss	0.05		14.1		dB
	0.8	12.0	14.3		
	2.0		14.0		
	3.0		10.9		
	4.0		10.0		
	6.0		14.0		
Reverse Isolation	2.0		21.9		dB
Output Power @ 1 dB compression	0.05	17.5	19.9		dBm
	0.8	17.5	19.6		
	2.0	17.2	19.2		
	3.0		17.6		
	4.0		15.4		
	6.0		11.8		
Output IP3	0.05		39.0		dB
	1.0		36.5		
	2.0	31.5	33.4		
	3.0		29.6		
	4.0		27.3		
	6.0		23.2		
Noise Figure	0.05		4.8	6.2	dB
	1.0		5.2		
	2.0		5.4	6.6	
	3.0		5.3		
	4.0		5.6		
	6.0		5.7		
Device Operating Voltage		4.8	5.0	5.2	V
Device Operating Current		72	82	92	mA
Device Current Variation vs. Temperature <sup>3</sup>			62		µA/°C
Device Current Variation vs. Voltage			0.035		mA/mV
Thermal Resistance, junction-to-ground lead			64		°C/W

(1) Measured on Mini-Circuits Characterization test board TB-656-62+. See Characterization Test Circuit (Fig. 1)


(2) Low Frequency cut-off determined by external coupling capacitors and external bias choke.

(3) (Current at 85°C — Current at -45°C)/130


Absolute Maximum Ratings

Parameter	Ratings
Operating Temperature (ground lead)	-55°C to 105°C
Storage Temperature	-65°C to 125°C
Operating Current at 5V	120 mA
Power Dissipation	0.725 W
Input Power (CW)	24 dBm
DC Voltage on Pin 3	6V

Note:  
 Permanent damage may occur if any of these limits are exceeded.  
 Electrical maximum ratings are not intended for continuous normal operation.  
 For continuous operation, do not exceed 5.2V device voltage.



Characterization Test Circuit




**Fig 1.** Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-656-62+) Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent’s N5242A PNA-X microwave network analyzer.

**Conditions:**


1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Recommended Application Circuit



*Fig 2.* Test Board includes case, connectors, and components soldered to PCB for component values, please see evaluation board drawing.


Suggested PCB Layout (PL-366)



**NOTES:**

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
  - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Product Marking



<b>Additional Detailed Technical Information</b>	
<i>additional information is available on our dash board. To access this information <a href="#">click here</a></i>	
<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
<b>Case Style</b>	DL1721 <i>Ceramic package, exposed paddle, Terminal finish: Ni,Pd,Au</i>
<b>Tape &amp; Reel</b> Standard quantities available on reel	F66-1 <i>7" reels with 20, 50, 100, 200, 500 or 1K, 2K devices.</i>
<b>Suggested Layout for PCB Design</b>	PL-366
<b>Evaluation Board</b>	TB-656-62+
<b>Environmental Ratings</b>	ENV-68

### ESD Rating

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with ANSI/ESD STM 5.1 - 2001  
Machine Model (MM): Class M2 (100 to <200V) in accordance with ANSI/ESD STM5.2-1999

### MSL Rating

Moisture Sensitivity: MSL1 (these parts are hermetic, air cavity and therefore, MSL ratings do not strictly apply. For handling purpose, use MSL1)

### Qualification Testing

The table below shows the initial qualification testing performed. If required, parts can be subjected to 100% screening and qualifications testing per MIL standard requirement.

	<b>Test Description</b>	<b>Test Method/Process</b>	<b>Results</b>
1	Hermeticity (fine and gross leak)	MIL-STD-202 Method 112, Cond. C & D	Pass
2	Acceleration, 30Kg, Y1 Direction	MIL-STD-883 Method 2001 Cond. E	Pass
3	Vibration , 10-2000Hz sine, 20g, 3 axis	MIL-STD-202 Method 204, Cond. D	Pass
4	Mechanical shock	MIL-STD-202 Method 213, Cond . A	Pass
5	PIND 20G's @130 Hz	MIL-STD-750 Method 2052.2	Pass
6	Temp Cycle -55C/+125C, 1000 Cycles	MIL-STD-202 Method 107	Pass
7	Autoclave, 121C, RH 100%, 15 Psig, 96 hrs	JESD22-A102C	Pass
8	HTOL, 1000hrs, 105C at rated Voltage condition	MIL-STD-202 Method 108, Cond . D	Pass
9	Bend Test	JESD22-B113	Pass
10	Resistance to soldering heat, 3x reflow, 260C peak	JESD22-B102	Pass
11	Drop Test	JESD22-B111	Pass
12	Adhesion Strength	Push Test>10 lb	Pass

### Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 84.86 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.99	23.03	14.35	13.65	1.15	0.76	--	19.17	4.88
50.0	16.64	22.18	15.63	14.57	1.12	0.75	39.52	20.04	4.81
100.0	16.21	21.72	14.36	16.59	1.13	0.76	38.33	20.00	4.92
200.0	15.90	21.47	13.70	18.77	1.15	0.77	39.05	20.00	4.87
300.0	15.81	21.44	13.56	19.63	1.16	0.77	39.60	19.97	5.02
400.0	15.76	21.42	13.36	20.21	1.17	0.76	39.89	19.92	5.08
500.0	15.71	21.44	13.37	20.62	1.18	0.76	38.54	19.97	5.16
600.0	15.72	21.43	13.11	20.76	1.18	0.76	37.96	19.90	5.12
700.0	15.71	21.46	12.91	20.90	1.19	0.76	38.79	19.80	5.15
800.0	15.66	21.49	12.74	20.84	1.19	0.76	37.64	19.78	5.11
1000.0	15.68	21.50	12.50	20.50	1.18	0.77	36.94	19.87	5.19
1250.0	15.67	21.59	12.24	19.70	1.16	0.80	37.20	19.82	5.24
1500.0	15.67	21.60	12.16	18.43	1.14	0.82	35.77	19.68	5.19
1750.0	15.67	21.67	12.29	17.06	1.14	0.82	35.59	19.61	5.27
2000.0	15.65	21.72	12.56	15.64	1.17	0.79	34.41	19.36	5.25
2250.0	15.66	21.76	13.01	14.64	1.20	0.75	33.25	18.99	5.34
2500.0	15.69	21.80	13.79	13.78	1.22	0.71	32.21	18.94	5.31
2750.0	15.69	21.83	14.71	13.02	1.21	0.70	31.63	18.36	5.39
3000.0	15.71	21.82	15.81	12.37	1.19	0.71	30.87	17.89	5.28
3250.0	15.70	21.78	17.23	11.88	1.16	0.72	30.01	17.39	5.47
3500.0	15.68	21.79	18.98	11.53	1.15	0.72	29.52	16.82	5.36
3750.0	15.62	21.68	21.20	11.11	1.14	0.71	28.62	16.09	5.41
4000.0	15.52	21.67	23.81	10.87	1.16	0.69	28.24	15.59	5.46
4250.0	15.39	21.58	25.88	10.58	1.17	0.68	27.83	15.33	5.47
4500.0	15.21	21.44	26.11	10.48	1.17	0.68	27.25	14.71	5.49
4750.0	14.97	21.23	24.23	10.51	1.18	0.68	26.72	14.07	5.48
5000.0	14.81	21.11	21.89	10.48	1.19	0.67	26.44	13.68	5.48
5250.0	14.54	20.91	20.05	10.68	1.21	0.67	26.02	13.17	5.55
5500.0	14.30	20.76	18.35	10.91	1.22	0.68	25.30	12.77	5.60
5750.0	13.98	20.57	17.30	11.43	1.21	0.72	25.27	12.30	5.60
6000.0	13.59	20.39	16.56	11.99	1.21	0.77	24.79	12.09	5.57
6250.0	13.12	20.31	15.89	12.52	1.23	0.81	24.37	11.73	5.74
6500.0	12.56	20.22	15.27	13.02	1.31	0.82	23.93	11.28	5.75
6750.0	11.84	20.26	14.59	13.43	1.43	0.82	23.50	10.74	5.82
7000.0	11.26	20.06	13.60	12.97	1.48	0.83	23.11	10.55	5.89

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.8V, Id = 77.59 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.94	23.61	14.70	13.89	1.21	0.79	--	18.58	4.83
50.0	16.60	22.30	15.87	14.48	1.13	0.75	37.13	19.35	4.77
100.0	16.18	21.72	14.52	16.47	1.13	0.76	36.93	19.33	4.83
200.0	15.87	21.44	13.86	18.56	1.15	0.76	38.25	19.30	4.80
300.0	15.78	21.41	13.71	19.44	1.16	0.76	37.94	19.26	4.97
400.0	15.73	21.35	13.50	19.97	1.17	0.76	37.86	19.24	5.01
500.0	15.68	21.39	13.50	20.37	1.18	0.76	37.27	19.29	5.12
600.0	15.69	21.38	13.24	20.46	1.18	0.75	37.34	19.23	5.05
700.0	15.68	21.42	13.05	20.62	1.19	0.75	37.46	19.15	5.09
800.0	15.64	21.45	12.87	20.57	1.19	0.76	37.21	19.13	5.04
1000.0	15.65	21.45	12.62	20.24	1.18	0.77	35.78	19.18	5.09
1250.0	15.63	21.53	12.36	19.48	1.16	0.80	36.27	19.16	5.17
1500.0	15.63	21.56	12.27	18.21	1.14	0.82	35.43	19.08	5.09
1750.0	15.63	21.60	12.40	16.86	1.14	0.81	34.66	19.03	5.21
2000.0	15.61	21.69	12.68	15.46	1.17	0.79	33.94	18.84	5.21
2250.0	15.63	21.74	13.14	14.47	1.20	0.74	32.90	18.51	5.25
2500.0	15.65	21.73	13.93	13.61	1.21	0.71	31.87	18.49	5.25
2750.0	15.64	21.76	14.85	12.86	1.21	0.70	31.39	17.96	5.33
3000.0	15.65	21.76	15.97	12.23	1.19	0.71	30.60	17.52	5.20
3250.0	15.64	21.72	17.41	11.74	1.16	0.72	29.63	17.04	5.38
3500.0	15.62	21.70	19.20	11.41	1.15	0.72	29.34	16.45	5.31
3750.0	15.55	21.64	21.40	10.99	1.14	0.70	28.36	15.77	5.31
4000.0	15.45	21.63	24.02	10.77	1.16	0.69	27.92	15.26	5.35
4250.0	15.32	21.47	25.93	10.49	1.16	0.68	27.63	15.01	5.38
4500.0	15.13	21.36	26.05	10.41	1.17	0.68	27.06	14.39	5.43
4750.0	14.88	21.15	24.16	10.43	1.18	0.67	26.49	13.78	5.41
5000.0	14.73	21.03	21.83	10.43	1.19	0.67	26.30	13.38	5.37
5250.0	14.45	20.82	20.03	10.62	1.21	0.66	25.79	12.87	5.41
5500.0	14.21	20.67	18.33	10.87	1.22	0.68	25.04	12.44	5.53
5750.0	13.89	20.45	17.33	11.38	1.21	0.72	24.99	11.99	5.51
6000.0	13.50	20.27	16.62	11.93	1.20	0.77	24.54	11.77	5.50
6250.0	13.03	20.19	15.97	12.44	1.23	0.81	24.09	11.43	5.61
6500.0	12.47	20.12	15.33	12.95	1.31	0.82	23.64	10.97	5.63
6750.0	11.75	20.21	14.67	13.33	1.44	0.82	23.23	10.45	5.75
7000.0	11.17	19.99	13.69	12.88	1.48	0.82	22.82	10.28	5.79

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.2V, Id = 92.14 mA @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.97	23.22	14.87	13.89	1.18	0.77	--	19.59	5.00
50.0	16.66	22.43	15.53	14.68	1.14	0.76	40.16	20.63	4.94
100.0	16.23	21.79	14.22	16.73	1.13	0.76	39.93	20.56	4.96
200.0	15.93	21.55	13.58	18.95	1.15	0.77	39.69	20.60	4.94
300.0	15.83	21.44	13.43	19.82	1.16	0.77	42.37	20.57	5.17
400.0	15.78	21.47	13.25	20.39	1.17	0.76	40.24	20.48	5.15
500.0	15.73	21.45	13.25	20.84	1.18	0.76	38.92	20.51	5.19
600.0	15.75	21.46	13.00	20.95	1.18	0.76	40.00	20.45	5.21
700.0	15.73	21.47	12.81	21.12	1.19	0.76	39.04	20.31	5.25
800.0	15.69	21.51	12.64	21.08	1.19	0.76	39.68	20.29	5.21
1000.0	15.71	21.52	12.40	20.71	1.18	0.77	37.72	20.40	5.29
1250.0	15.69	21.57	12.14	19.93	1.16	0.80	37.30	20.27	5.35
1500.0	15.70	21.62	12.05	18.65	1.14	0.82	36.18	20.05	5.27
1750.0	15.70	21.70	12.19	17.26	1.14	0.82	35.22	19.97	5.38
2000.0	15.68	21.77	12.45	15.82	1.17	0.79	34.41	19.69	5.37
2250.0	15.70	21.80	12.91	14.80	1.20	0.75	33.18	19.29	5.43
2500.0	15.73	21.83	13.68	13.93	1.22	0.72	32.10	19.22	5.44
2750.0	15.73	21.88	14.59	13.17	1.21	0.71	31.66	18.63	5.50
3000.0	15.75	21.85	15.67	12.51	1.19	0.71	30.83	18.14	5.39
3250.0	15.75	21.84	17.08	12.01	1.16	0.72	29.72	17.63	5.58
3500.0	15.73	21.79	18.81	11.64	1.15	0.72	29.43	17.08	5.46
3750.0	15.68	21.74	21.02	11.22	1.15	0.71	28.50	16.38	5.52
4000.0	15.58	21.67	23.59	10.98	1.16	0.69	28.06	15.87	5.58
4250.0	15.46	21.59	25.72	10.67	1.16	0.68	27.62	15.56	5.60
4500.0	15.28	21.50	26.17	10.56	1.17	0.68	27.06	14.97	5.62
4750.0	15.04	21.30	24.24	10.58	1.18	0.68	26.55	14.33	5.63
5000.0	14.89	21.21	21.91	10.55	1.19	0.67	26.23	13.92	5.60
5250.0	14.62	20.95	20.05	10.74	1.21	0.67	25.74	13.40	5.69
5500.0	14.38	20.85	18.35	10.97	1.22	0.68	25.15	12.98	5.70
5750.0	14.06	20.62	17.27	11.48	1.21	0.72	25.03	12.53	5.74
6000.0	13.67	20.48	16.54	12.05	1.21	0.77	24.67	12.33	5.71
6250.0	13.21	20.36	15.84	12.59	1.23	0.81	24.26	11.95	5.86
6500.0	12.65	20.27	15.18	13.13	1.30	0.82	23.86	11.52	5.93
6750.0	11.92	20.36	14.49	13.54	1.43	0.83	23.47	10.99	6.00
7000.0	11.34	20.12	13.53	13.08	1.48	0.83	23.09	10.77	6.08



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 78.93 mA @ Temperature = -55degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.92	23.36	13.94	13.51	1.19	0.78		19.15	4.94
50.0	16.70	22.31	15.45	14.50	1.12	0.75	41.23	19.78	3.97
100.0	16.29	21.82	14.64	16.06	1.13	0.76	38.04	19.70	4.04
200.0	16.01	21.55	14.07	18.13	1.14	0.76	39.23	19.66	3.96
300.0	15.90	21.52	13.38	19.92	1.16	0.77	40.02	19.63	4.18
400.0	15.86	21.50	12.98	20.49	1.17	0.76	40.51	19.62	4.17
500.0	15.80	21.53	13.08	20.91	1.18	0.76	39.20	19.60	4.27
600.0	15.83	21.52	12.79	20.92	1.18	0.76	39.07	19.63	4.20
700.0	15.81	21.52	12.73	20.71	1.19	0.75	39.19	19.63	4.20
800.0	15.77	21.54	12.61	20.58	1.19	0.76	39.34	19.58	4.18
1000.0	15.78	21.57	12.45	20.28	1.18	0.77	37.75	19.64	4.24
1250.0	15.76	21.59	11.80	19.83	1.15	0.81	37.26	19.53	4.29
1500.0	15.76	21.65	11.64	18.57	1.13	0.83	37.03	19.58	4.27
1750.0	15.76	21.67	11.78	16.92	1.13	0.81	36.44	19.58	4.37
2000.0	15.72	21.76	11.84	15.41	1.16	0.78	35.51	19.38	4.37
2250.0	15.73	21.77	12.16	14.26	1.19	0.73	34.45	19.29	4.35
2500.0	15.78	21.77	12.94	13.26	1.20	0.70	33.58	19.19	4.36
2750.0	15.78	21.80	13.83	12.53	1.18	0.70	33.17	18.87	4.36
3000.0	15.80	21.78	14.40	12.06	1.15	0.72	32.39	18.41	4.22
3250.0	15.81	21.77	14.94	11.62	1.11	0.74	31.23	18.07	4.43
3500.0	15.81	21.71	16.07	11.08	1.10	0.73	30.85	17.62	4.46
3750.0	15.78	21.69	17.28	10.76	1.11	0.70	29.88	17.10	4.45
4000.0	15.72	21.68	18.58	10.38	1.14	0.67	29.53	16.42	4.39
4250.0	15.60	21.65	20.08	9.98	1.16	0.64	29.36	16.14	4.47
4500.0	15.48	21.59	22.72	9.67	1.17	0.63	29.11	15.67	4.45
4750.0	15.35	21.49	25.22	9.33	1.16	0.63	28.40	14.96	4.48
5000.0	15.22	21.32	26.39	9.32	1.15	0.63	28.31	14.74	4.54
5250.0	15.08	21.15	25.54	9.34	1.14	0.63	27.93	14.12	4.45
5500.0	14.94	20.85	23.57	9.78	1.13	0.65	27.08	13.67	4.51
5750.0	14.73	20.71	21.10	10.11	1.12	0.68	27.08	13.25	4.56
6000.0	14.43	20.49	18.97	10.57	1.12	0.71	26.62	12.99	4.51
6250.0	14.07	20.39	17.96	10.84	1.18	0.70	26.13	12.49	4.62
6500.0	13.57	20.37	16.69	10.98	1.25	0.70	25.89	12.17	4.67
6750.0	12.90	20.45	15.80	11.06	1.32	0.74	25.53	11.60	4.72
7000.0	12.30	20.26	14.95	10.97	1.32	0.78	25.10	11.27	4.85

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.8V, Id =71.11 mA @ Temperature = -55degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.98	23.24	13.93	13.43	1.17	0.77		19.15	4.82
50.0	16.67	22.30	15.67	14.39	1.13	0.75	38.06	19.78	3.91
100.0	16.26	21.79	14.83	15.91	1.13	0.75	36.61	19.70	3.95
200.0	15.97	21.50	14.23	17.94	1.14	0.76	37.95	19.66	3.89
300.0	15.87	21.45	13.54	19.66	1.16	0.76	38.15	19.63	4.07
400.0	15.82	21.41	13.13	20.25	1.16	0.76	37.37	19.62	4.09
500.0	15.76	21.51	13.21	20.61	1.18	0.76	38.48	19.60	4.23
600.0	15.80	21.48	12.92	20.64	1.18	0.75	39.18	19.63	4.12
700.0	15.78	21.44	12.87	20.43	1.18	0.75	37.93	19.63	4.13
800.0	15.74	21.50	12.74	20.33	1.19	0.76	37.68	19.58	4.10
1000.0	15.75	21.51	12.58	20.01	1.18	0.77	36.86	19.64	4.14
1250.0	15.73	21.52	11.91	19.58	1.14	0.80	36.94	19.53	4.20
1500.0	15.72	21.57	11.74	18.32	1.12	0.82	35.88	19.58	4.19
1750.0	15.72	21.62	11.90	16.72	1.13	0.81	35.63	19.58	4.28
2000.0	15.68	21.74	11.97	15.23	1.17	0.78	34.70	19.38	4.27
2250.0	15.69	21.74	12.28	14.05	1.20	0.73	33.87	19.29	4.28
2500.0	15.73	21.73	13.09	13.11	1.20	0.70	32.86	19.19	4.26
2750.0	15.73	21.73	14.00	12.36	1.18	0.70	32.49	18.87	4.29
3000.0	15.75	21.75	14.55	11.91	1.15	0.72	31.71	18.41	4.15
3250.0	15.76	21.70	15.10	11.48	1.11	0.74	30.65	18.07	4.34
3500.0	15.75	21.63	16.23	10.94	1.09	0.73	30.22	17.62	4.34
3750.0	15.71	21.62	17.47	10.63	1.11	0.70	29.36	17.10	4.38
4000.0	15.65	21.57	18.74	10.28	1.14	0.66	29.09	16.42	4.34
4250.0	15.52	21.60	20.26	9.88	1.16	0.64	28.90	16.14	4.39
4500.0	15.39	21.50	22.87	9.59	1.17	0.63	28.49	15.67	4.33
4750.0	15.26	21.41	25.37	9.27	1.16	0.62	27.82	14.96	4.39
5000.0	15.12	21.23	26.31	9.27	1.15	0.63	27.85	14.74	4.42
5250.0	14.98	21.02	25.41	9.31	1.14	0.63	27.40	14.12	4.34
5500.0	14.83	20.73	23.46	9.76	1.13	0.64	26.57	13.67	4.41
5750.0	14.62	20.58	21.05	10.09	1.12	0.68	26.53	13.25	4.43
6000.0	14.32	20.40	18.99	10.54	1.13	0.71	26.07	12.99	4.40
6250.0	13.95	20.28	17.99	10.80	1.18	0.70	25.53	12.49	4.52
6500.0	13.44	20.28	16.72	10.94	1.25	0.70	25.28	12.17	4.55
6750.0	12.77	20.36	15.84	11.01	1.32	0.74	24.94	11.60	4.57
7000.0	12.16	20.18	15.01	10.92	1.32	0.79	24.46	11.27	4.68

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.2V, Id = 85.96 mA @ Temperature = -55degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	17.03	23.64	13.81	13.71	1.20	0.79		19.80	4.99
50.0	16.74	22.37	15.32	14.59	1.13	0.75	39.52	20.47	4.06
100.0	16.32	21.85	14.51	16.16	1.13	0.76	39.70	20.38	4.07
200.0	16.03	21.58	13.93	18.26	1.14	0.76	39.86	20.37	4.00
300.0	15.92	21.52	13.27	20.10	1.16	0.77	40.57	20.35	4.24
400.0	15.88	21.55	12.88	20.65	1.17	0.77	42.24	20.31	4.25
500.0	15.82	21.56	12.98	21.10	1.18	0.76	39.69	20.31	4.37
600.0	15.85	21.53	12.70	21.13	1.18	0.76	39.97	20.31	4.29
700.0	15.83	21.55	12.65	20.90	1.19	0.76	40.04	20.29	4.29
800.0	15.79	21.57	12.51	20.82	1.19	0.76	40.29	20.26	4.22
1000.0	15.80	21.59	12.35	20.48	1.18	0.77	38.92	20.32	4.30
1250.0	15.78	21.62	11.72	20.05	1.14	0.81	38.82	20.23	4.35
1500.0	15.78	21.66	11.55	18.76	1.13	0.83	38.33	20.24	4.32
1750.0	15.78	21.69	11.70	17.10	1.13	0.82	37.02	20.23	4.45
2000.0	15.75	21.81	11.76	15.55	1.17	0.78	36.51	19.98	4.44
2250.0	15.76	21.82	12.06	14.38	1.20	0.74	35.14	19.83	4.43
2500.0	15.81	21.81	12.86	13.40	1.20	0.70	34.16	19.72	4.45
2750.0	15.83	21.82	13.75	12.63	1.18	0.70	33.43	19.33	4.46
3000.0	15.84	21.83	14.28	12.18	1.15	0.73	32.56	18.79	4.28
3250.0	15.86	21.84	14.82	11.74	1.11	0.75	31.54	18.42	4.53
3500.0	15.86	21.78	15.94	11.19	1.10	0.74	31.21	17.97	4.52
3750.0	15.84	21.68	17.18	10.83	1.11	0.70	30.25	17.43	4.56
4000.0	15.78	21.71	18.42	10.46	1.14	0.67	29.91	16.77	4.51
4250.0	15.67	21.70	19.90	10.06	1.16	0.64	29.76	16.47	4.57
4500.0	15.55	21.61	22.55	9.74	1.17	0.63	29.40	15.98	4.53
4750.0	15.42	21.58	25.06	9.38	1.16	0.63	28.65	15.30	4.57
5000.0	15.30	21.38	26.40	9.36	1.15	0.63	28.58	15.06	4.60
5250.0	15.16	21.21	25.69	9.37	1.14	0.63	28.26	14.46	4.53
5500.0	15.02	20.94	23.66	9.80	1.13	0.65	27.47	14.01	4.65
5750.0	14.82	20.80	21.14	10.12	1.12	0.68	27.41	13.56	4.71
6000.0	14.53	20.58	18.96	10.58	1.12	0.70	26.95	13.30	4.61
6250.0	14.17	20.47	17.91	10.86	1.18	0.70	26.46	12.81	4.72
6500.0	13.67	20.45	16.66	11.02	1.25	0.70	26.23	12.52	4.76
6750.0	13.00	20.51	15.72	11.09	1.31	0.74	25.94	11.91	4.83
7000.0	12.40	20.35	14.88	10.99	1.32	0.78	25.49	11.57	4.90

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 88.52 mA @ Temperature = +105degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.77	22.76	14.66	13.99	1.16	0.76	--	19.36	5.59
50.0	16.51	22.24	15.67	14.80	1.14	0.76	40.88	20.10	5.48
100.0	16.09	21.69	14.20	17.23	1.14	0.77	38.80	19.98	5.56
200.0	15.78	21.40	13.32	19.78	1.15	0.77	39.95	19.98	5.55
300.0	15.67	21.36	13.33	20.11	1.16	0.77	40.48	20.01	5.75
400.0	15.62	21.36	13.49	20.33	1.18	0.77	39.89	19.75	5.78
500.0	15.60	21.32	13.57	20.55	1.18	0.76	39.15	19.81	5.92
600.0	15.60	21.35	13.42	20.54	1.19	0.75	38.56	19.67	5.85
700.0	15.58	21.40	13.29	20.43	1.20	0.76	38.08	19.62	5.90
800.0	15.56	21.39	13.22	20.25	1.20	0.75	37.22	19.57	5.79
1000.0	15.57	21.43	13.09	19.99	1.19	0.76	35.76	19.69	5.82
1250.0	15.57	21.48	12.87	19.50	1.17	0.79	35.73	19.52	5.88
1500.0	15.58	21.56	12.74	18.66	1.16	0.81	33.94	19.28	5.87
1750.0	15.58	21.62	12.75	17.40	1.15	0.81	33.25	19.20	6.02
2000.0	15.57	21.69	13.01	16.10	1.17	0.79	32.55	18.82	6.04
2250.0	15.58	21.75	13.64	15.05	1.20	0.76	31.35	18.39	6.11
2500.0	15.60	21.77	14.76	14.19	1.22	0.72	30.24	18.11	6.14
2750.0	15.59	21.77	16.25	13.46	1.23	0.70	29.65	17.41	6.12
3000.0	15.59	21.73	18.22	12.87	1.21	0.70	28.64	16.91	5.99
3250.0	15.55	21.70	20.94	12.43	1.20	0.71	27.59	16.20	6.23
3500.0	15.49	21.64	24.54	12.04	1.19	0.70	26.89	15.65	6.18
3750.0	15.35	21.55	28.07	11.70	1.19	0.70	25.94	14.92	6.18
4000.0	15.16	21.50	27.90	11.48	1.20	0.70	25.51	14.40	6.19
4250.0	14.91	21.36	24.31	11.37	1.19	0.72	24.99	14.08	6.29
4500.0	14.63	21.20	21.21	11.37	1.19	0.74	24.55	13.45	6.28
4750.0	14.30	21.07	18.70	11.54	1.20	0.75	24.09	12.90	6.24
5000.0	13.96	20.90	16.78	11.76	1.23	0.76	23.68	12.46	6.34
5250.0	13.59	20.73	15.43	12.22	1.28	0.76	23.24	11.98	6.42
5500.0	13.18	20.55	14.34	12.70	1.32	0.76	22.97	11.59	6.35
5750.0	12.77	20.36	13.78	13.50	1.34	0.79	22.58	11.20	6.47
6000.0	12.30	20.24	13.56	14.36	1.36	0.84	22.25	10.91	6.51
6250.0	11.79	20.14	13.58	15.38	1.38	0.88	21.94	10.54	6.55
6500.0	11.18	20.04	13.65	16.06	1.44	0.91	21.49	10.21	6.65
6750.0	10.44	20.02	13.55	16.72	1.57	0.92	21.10	9.72	6.74
7000.0	9.87	19.89	12.60	15.20	1.64	0.91	20.97	9.72	6.86

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.8V, Id = 81.22 mA @ Temperature = +105degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	16.75	22.46	14.61	13.74	1.14	0.74	--	18.95	5.41
50.0	16.48	22.15	15.81	14.66	1.13	0.75	37.93	19.52	5.40
100.0	16.06	21.68	14.36	17.06	1.14	0.77	37.63	19.46	5.49
200.0	15.75	21.37	13.45	19.58	1.15	0.77	38.65	19.43	5.41
300.0	15.64	21.28	13.46	19.88	1.16	0.77	38.59	19.46	5.68
400.0	15.59	21.32	13.61	20.08	1.18	0.76	39.50	19.24	5.66
500.0	15.57	21.31	13.70	20.28	1.19	0.76	37.56	19.31	5.77
600.0	15.57	21.31	13.54	20.25	1.19	0.75	37.89	19.19	5.76
700.0	15.55	21.33	13.43	20.17	1.20	0.75	37.53	19.16	5.79
800.0	15.53	21.38	13.36	19.95	1.20	0.75	36.98	19.09	5.69
1000.0	15.53	21.41	13.23	19.70	1.20	0.76	35.66	19.20	5.74
1250.0	15.54	21.43	12.98	19.19	1.17	0.78	35.43	19.09	5.76
1500.0	15.55	21.50	12.85	18.35	1.15	0.81	34.48	18.90	5.78
1750.0	15.54	21.57	12.85	17.11	1.15	0.81	33.62	18.86	5.90
2000.0	15.53	21.63	13.11	15.86	1.17	0.79	32.82	18.52	5.91
2250.0	15.53	21.70	13.75	14.80	1.20	0.75	31.65	18.14	5.99
2500.0	15.55	21.72	14.84	13.94	1.22	0.72	30.59	17.87	6.01
2750.0	15.55	21.74	16.33	13.21	1.23	0.70	29.84	17.20	6.03
3000.0	15.54	21.70	18.28	12.63	1.21	0.70	28.81	16.72	5.90
3250.0	15.50	21.67	20.95	12.19	1.20	0.70	27.89	16.01	6.11
3500.0	15.44	21.62	24.51	11.80	1.19	0.70	27.18	15.44	6.05
3750.0	15.30	21.48	28.05	11.46	1.18	0.70	26.15	14.72	6.09
4000.0	15.12	21.45	28.08	11.25	1.19	0.70	25.66	14.21	6.09
4250.0	14.88	21.31	24.56	11.14	1.19	0.71	25.14	13.85	6.16
4500.0	14.60	21.16	21.36	11.15	1.19	0.73	24.61	13.24	6.16
4750.0	14.28	21.03	18.86	11.31	1.20	0.75	24.13	12.67	6.11
5000.0	13.94	20.83	16.93	11.54	1.23	0.75	23.75	12.22	6.22
5250.0	13.57	20.62	15.57	12.00	1.27	0.75	23.24	11.82	6.27
5500.0	13.17	20.46	14.47	12.46	1.31	0.75	22.89	11.35	6.21
5750.0	12.77	20.30	13.94	13.24	1.34	0.78	22.54	11.01	6.32
6000.0	12.31	20.14	13.69	14.08	1.35	0.83	22.15	10.71	6.37
6250.0	11.80	20.01	13.70	15.04	1.36	0.88	21.81	10.29	6.43
6500.0	11.20	19.95	13.80	15.67	1.43	0.90	21.33	9.99	6.54
6750.0	10.45	19.95	13.72	16.24	1.55	0.91	20.94	9.48	6.59
7000.0	9.88	19.80	12.72	14.81	1.62	0.90	20.80	9.50	6.68

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)


Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.2V, Id = 96.07 mA @ Temperature = +105degC


FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	16.82	22.20	14.35	13.73	1.11	0.72	--	19.60	5.70
50.0	16.54	22.18	15.49	14.87	1.13	0.75	39.47	20.54	5.56
100.0	16.12	21.75	14.09	17.36	1.14	0.77	38.64	20.34	5.66
200.0	15.80	21.45	13.19	20.00	1.15	0.78	39.07	20.39	5.70
300.0	15.69	21.38	13.22	20.31	1.16	0.77	40.42	20.42	5.93
400.0	15.65	21.39	13.35	20.59	1.18	0.77	39.03	20.11	5.87
500.0	15.62	21.39	13.43	20.82	1.19	0.76	37.88	20.17	6.00
600.0	15.62	21.38	13.30	20.79	1.19	0.76	38.06	20.03	5.91
700.0	15.60	21.44	13.18	20.74	1.20	0.76	36.95	19.96	5.98
800.0	15.58	21.43	13.11	20.51	1.20	0.76	37.08	19.88	5.89
1000.0	15.59	21.45	12.98	20.28	1.19	0.77	35.53	20.01	5.94
1250.0	15.60	21.51	12.77	19.81	1.17	0.79	34.68	19.77	5.98
1500.0	15.61	21.56	12.64	18.97	1.15	0.81	33.74	19.51	5.98
1750.0	15.61	21.64	12.68	17.67	1.15	0.81	32.93	19.41	6.11
2000.0	15.61	21.75	12.95	16.42	1.18	0.80	32.18	18.98	6.13
2250.0	15.61	21.73	13.62	15.36	1.20	0.76	31.00	18.57	6.22
2500.0	15.63	21.78	14.74	14.46	1.22	0.72	29.82	18.28	6.24
2750.0	15.63	21.82	16.27	13.74	1.23	0.71	29.27	17.57	6.24
3000.0	15.62	21.77	18.31	13.14	1.22	0.70	28.30	17.04	6.12
3250.0	15.58	21.72	21.06	12.72	1.20	0.71	27.32	16.33	6.33
3500.0	15.52	21.67	24.86	12.31	1.19	0.71	26.68	15.76	6.31
3750.0	15.37	21.58	28.34	11.97	1.20	0.70	25.83	15.05	6.31
4000.0	15.18	21.48	27.56	11.74	1.20	0.71	25.34	14.54	6.32
4250.0	14.92	21.40	23.87	11.65	1.20	0.72	24.85	14.20	6.41
4500.0	14.62	21.26	20.76	11.65	1.20	0.74	24.40	13.59	6.44
4750.0	14.28	21.10	18.37	11.84	1.21	0.76	23.98	13.07	6.38
5000.0	13.93	20.93	16.50	12.06	1.24	0.77	23.55	12.61	6.45
5250.0	13.54	20.74	15.19	12.51	1.28	0.77	23.18	12.24	6.59
5500.0	13.12	20.61	14.14	12.99	1.33	0.77	22.92	11.75	6.52
5750.0	12.71	20.43	13.60	13.81	1.36	0.80	22.58	11.41	6.65
6000.0	12.23	20.30	13.38	14.72	1.38	0.84	22.26	11.09	6.70
6250.0	11.71	20.15	13.39	15.83	1.40	0.89	21.97	10.73	6.71
6500.0	11.11	20.14	13.46	16.65	1.47	0.92	21.56	10.48	6.84
6750.0	10.36	20.10	13.36	17.38	1.59	0.93	21.20	9.94	6.89
7000.0	9.79	19.96	12.41	15.76	1.66	0.92	21.09	9.95	7.06

## Typical Performance Curves


**GAIN vs. FREQUENCY & TEMPERATURE**  
INPUT POWER = -25dBm, Vd = 5V




**GAIN vs. FREQUENCY & DEVICE VOLTAGE**  
INPUT POWER = -25dBm, Temperature = +25°C




**ISOLATION vs. FREQUENCY & TEMPERATURE**  
INPUT POWER = -25dBm, Vd = 5V




**ISOLATION vs. FREQUENCY & DEVICE VOLTAGE**  
INPUT POWER = -25dBm, Temperature = +25°C




**INPUT RETURN LOSS vs. FREQUENCY & TEMPERATURE**  
INPUT POWER = -25dBm, Vd = 5V




**INPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE**  
INPUT POWER = -25dBm, Temperature = +25°C



**OUTPUT RETURN LOSS vs. FREQUENCY & TEMPERATURE**  
INPUT POWER = -25dBm, Vd = 5V




**OUTPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE**  
INPUT POWER = -25dBm, Temperature = +25°C



## Typical Performance Curves


**OUTPUT IP3 vs. FREQUENCY & TEMPERATURE**

OUTPUT POWER = 0 dBm/tone, Vd = 5V




**OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE**

OUTPUT POWER = 0 dBm/tone, Temperature = +25°C




**P1dB vs. FREQUENCY & TEMPERATURE**

Vd = 5V




**P1dB vs. FREQUENCY & DEVICE VOLTAGE**

Temperature = +25°C




**NOISE FIGURE vs. FREQUENCY & TEMPERATURE**

Vd = 5V




**NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE**

Temperature = +25°C




**GAIN VARIATION vs. FREQUENCY & TEMPERATURE**

INPUT POWER = -25dBm, Vd = 5V






### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
DL1721	.118 (3.00)	.118 (3.00)	.045 (1.14)	.008 (0.20)	.075 (1.91)	.043 (1.09)	.012 (0.30)	.006 (0.15)	.022 (0.56)	.026 (0.66)	.117 (2.97)	.118 (3.00)	.075 (1.91)

CASE #	P	Q	R	S	T	WT. GRAM
DL1721	.018 (0.46)	.030 (0.76)	.041 (1.04)	.018 (0.46)	.008 (0.20)	.02

Dimensions are in inches (mm). Tolerances: 3Pl.  $\pm .004$ , unless otherwise specified.

#### Notes:

1. Case material: LTCC.
2. Termination finish: Nickel-Palladium-Gold plating.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F66-1



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M136376	NEW RELEASE	06/12/12	PW	DJ

**SUGGESTED MOUNTING CONFIGURATION FOR DL1721 CASE STYLE, "08AM09" PIN CONNECTION**



**NOTES:**

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES  
 TOLERANCES ON:  
 2 PL DECIMALS ±  
 3 PL DECIMALS ± .005  
 ANGLES ± 1°  
 FRACTIONS ±

	INITIALS	DATE
DRAWN	PW	05/18/12
CHECKED	IL	06/05/12
APPROVED	DJ	06/12/12



**Mini-Circuits®**



13 Neptune Avenue  
 Brooklyn NY 11235

**PL, 08AM09, DL1721, CMA TB-656+**

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-366	REV: OR
FILE: 98PL366	SCALE: 10:1	SHEET: 1 OF 1	


# Evaluation Board and Circuit



COMPONENT	DESCRIPTION
DUT	CMA-62+
C1	2.2 nF
C2,C3	.1 uF
L1	15 nH
R1	11.5 Ohm
BIAS TEE	Mini-Circuits TCBT-14+

## NOTES:

1. Vd voltage: +5V.
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C	Individual Model Data Sheet
Storage Temperature	-65° to 125° C	Individual Model Data Sheet
Thermal Shock (device level)	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107
Thermal Shock (board level)	-55° to 125°C, 1000 cycles	MIL-STD-202, Method 107
Constant Acceleration	Y1 plane only, 30 Kg	MIL-STD-883, Method 2001, Cond. E
Vibration	10-2000MHz sine, 20g, 3 axis	MIL-STD-202, Method 204, Cond. D
Mechanical Shock	Y1 plane, 5 pulses, .5ms, 1.5 Kg	MIL-STD-202, Method 213, Cond. A
PIND	20G's @130 Hz	MIL-STD-750, Method 2052.2
Resistance to Soldering Heat	3X Reflow, Peak Temperature 260°C, electrical End points	JESD22-B102
Resistance to Solvent	15 pieces, 5 pieces each solvent, marking permanency	MIL-STD-202, Method 215
Moisture Sensitivity Level	Hermetic device, MSL-1 by construction	JESD22-A113, MSL1/260
Hermeticity	Fine Leak, Gross Leak	MIL-STD-202, Method 112, Cond. C&D



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JEDEC-STD-22-B, Method A102