



# Monolithic Amplifier

### THE BIG DEAL

- Super Wideband, DC to 16 GHz
- Excellent Flat Gain,  $\pm 0.75$  dB up to 12 GHz
- Low Current, 20 mA
- Good Input & Output Return Loss ( $>10$  dB)
- Repeatable performance (HBT Process)
- Small Package (2x2mm 6L MCLP)



Generic photo used for illustration purposes only

CASE STYLE: MC1630-1

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

### APPLICATIONS

- Instrumentation
- Cable Infrastructure
- 5G

### PRODUCT OVERVIEW

The EHA-163L+ is a low current, wideband gain block that operates up to 16 GHz fabricated using highly reliable HBT process. This Darlington pair amplifier delivers excellent gain flatness, good return loss, low current with acceptable P1dB and OIP3 across a wide bandwidth without the need of external matching network. It has highly repeatable performance from lot to lot and it is enclosed in a 2mm x 2mm 6-lead package.

### KEY FEATURES

Feature	Advantages
Super Wideband: DC to 16 GHz	Generate purpose wideband amplifier is suitable for various applications.
Low Current, 20mA	Low current consumption is ideal for driver amplifier.
Excellent gain flatness, $\pm 0.75$ dB up to 12 GHz	As a desirable characteristic of a wideband amplifier, excellent gain flatness allows amplification of a signal without changing the waveform in time domain.
No external matching component required	EHA-163L+ provides input & output return loss of 10 dB up to 16 GHz without the need for any external matching components.



LOW CURRENT, WIDEBAND, FLAT GAIN

# Monolithic Amplifier

## EHA-163L+

50Ω DC to 16 GHz

### ELECTRICAL SPECIFICATIONS AT 25°C, V<sub>CC</sub> = +5V, R = 50Ω UNLESS NOTED OTHERWISE

Parameter	Condition (MHz)	V <sub>CC</sub> = +5V <sup>1</sup>			V <sub>CC</sub> = +5V <sup>2</sup>	Units
		Min.	Typ.	Max.	Typ.	
Frequency Range <sup>6</sup>		0.01		16	0.01-16	GHz
Gain	10	—	15.7	—	15.3	dB
	5000	—	15.6	—	14.8	
	8000	13.1	15.3	16.0	14.2	
	10000	—	14.9	—	13.5	
	12000	—	14.2	—	13.1	
	16000	—	11.6	—	8.9	
Input Return Loss	10		18		17	dB
	5000		13		18	
	8000		12		15	
	10000		12		15	
	12000		11		15	
	16000		16		12	
Output Return Loss	10		14		14	dB
	5000		13		14	
	8000		13		16	
	10000		14		16	
	12000		13		11	
	16000		15		8	
Reverse Isolation	8000		19		20	dB
Output Power @1dB Compression	10		7.7		6.2	dBm
	5000		6.0		5.2	
	8000		6.5		6.8	
	10000		4.4		3.9	
	12000		2.7		2.1	
	16000		2.0		0.3	
Output IP33	10		21.0		19	dBm
	5000		17.3		17.8	
	8000		15.6		16.2	
	10000		13.2		13.3	
	12000		12.0		11.6	
	16000		11.8		10.7	
Noise Figure	10		5.2		5.2	dB
	5000		5.0		5.0	
	8000		5.2		5.2	
	10000		5.5		5.3	
	12000		5.4		5.3	
	16000		5.2		6.2	
DC Supply (V <sub>CC</sub> )		+4.75	+5	+5.25	+5	V
Device operating current			20.9	24	19.3	mA
Device current variation vs. temperature <sup>4</sup>			59		59	μA/°C
Device current variation vs voltage <sup>5</sup>			0.0178		0.0178	mA/mV
Thermal Resistance, junction-to-ground lead at 85°C stage temp.			349		349	°C/W

1. Measured on Mini-Circuits Characterization test circuit TB-883-163L+. See Characterization Test Circuit (Fig. 1)  
 2. Measured on Mini-Circuits Recommended Application Circuit TB-995+. See Application Test Circuit (Fig. 2)  
 3. Tested at P<sub>out</sub> = -5 dBm / tone.  
 4. (Current at 85°C - Current at -45°C)/130  
 5. (Current at 5.25V - Current at 4.75V)/1000  
 6. Low frequency cut-off determined by external coupling capacitors & RF choke.

### MAXIMUM RATINGS<sup>7</sup>

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Junction Temperature	150°C
Power Dissipation	0.2W
Input Power (CW)	+22 dBm (5 minutes max.) +8 dBm (continuous)
V <sub>CC</sub> (Supply Voltage)	+6V

7. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.






LOW CURRENT, WIDEBAND, FLAT GAIN

# Monolithic Amplifier

## EHA-163L+

50Ω DC to 16 GHz

### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	2	RF input
RF-OUT and DC-IN	5	RF output and DC input
GND	Paddle	Ground
NC	1,3,4,6	No connections

### CHARACTERIZATION TEST CIRCUIT




Fig 1. Characterization Circuit

Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-883-163L+)

Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer. Rc=49.9 ohms

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -5 dBm/tone at output.






LOW CURRENT, WIDEBAND, FLAT GAIN

# Monolithic Amplifier

## EHA-163L+

50Ω DC to 16 GHz

### APPLICATION TEST CIRCUIT



Component	P/N	Supplier	Value	Size
DUT	EHA-163L+	MCL	NA	2mm x 2mm
C1,C2	LBB0402X104MGT1C8	Presidio Components Inc	0.1 $\mu$ F	0402
C3	GRM155R71E103KA01D	Murata	0.01 $\mu$ F	0402
R1	RK73H1JTTD4R99F	KOA	49.9 ohms	0603
L1	BCR-652JLC	Coilcraft	6.5 $\mu$ H	4422

Fig 2. Application Test Circuit

Note: (DUT soldered on Mini-Circuits Application test board TB-995+)

Gain, Return loss, Output power at 1 dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -5 dBm/tone at output.

### PRODUCT MARKING



Marking may contain other features or characters for internal lot control



LOW CURRENT, WIDEBAND, FLAT GAIN

# Monolithic Amplifier

## EHA-163L+

50Ω DC to 16 GHz


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	MC1630-1 Plastic package, exposed paddle, lead finish: Matte-Tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500, 1K, or 2K devices
Suggested Layout for PCB Design	PL-544
Evaluation Board	TB-995+
Environmental Ratings	ENV08T1

### ESD RATING

Human Body Model (HBM): Class 1A (Pass 250V) in accordance with ANSI/ESD STM 5.1 - 2001

### MSL FLOW CHART



#### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

- Input Return Loss = -S11 (dB)
- Gain(Power Gain) = S21 (dB)
- Reverse Isolation = -S12 (dB)
- Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 19.27mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	15.30	18.80	17.18	14.38	1.07	0.49	18.64	6.01	5.15
50	15.45	18.73	18.15	14.74	1.06	0.48	17.36	5.09	4.87
100	15.46	18.75	18.13	14.70	1.06	0.48	18.19	5.61	4.67
200	15.28	18.93	17.06	15.23	1.08	0.53	17.19	4.99	4.70
300	15.26	18.96	16.89	15.23	1.08	0.54	17.55	5.12	4.81
400	15.40	18.85	17.29	14.32	1.07	0.50	17.52	5.33	4.70
500	15.29	18.96	16.67	14.65	1.08	0.53	16.92	4.81	4.79
600	15.18	19.08	15.96	14.71	1.09	0.56	17.50	4.97	4.81
700	15.30	18.97	15.93	13.50	1.08	0.52	17.68	5.14	4.82
800	15.18	19.09	15.38	13.61	1.09	0.54	17.39	4.95	4.81
900	15.18	19.10	14.84	12.83	1.09	0.53	17.54	4.95	4.82
1000	15.13	19.15	14.62	12.84	1.09	0.55	16.71	4.43	4.81
1500	14.96	19.35	13.03	11.20	1.10	0.55	16.03	3.94	5.00
2000	14.83	19.47	12.56	10.71	1.11	0.56	15.80	3.62	5.05
2500	14.75	19.53	12.75	10.77	1.12	0.57	16.11	3.68	5.07
3000	14.71	19.53	13.23	11.11	1.13	0.59	16.88	4.00	5.11
3500	14.70	19.53	13.74	11.39	1.13	0.60	15.97	3.60	5.12
4000	14.68	19.47	14.51	11.65	1.14	0.61	16.30	3.85	5.09
4500	14.69	19.44	15.71	12.09	1.14	0.62	16.60	4.18	5.02
5000	14.71	19.39	17.55	12.76	1.14	0.61	17.76	4.83	4.91
5500	14.71	19.31	20.35	13.97	1.15	0.63	18.64	5.49	4.91
6000	14.64	19.33	20.10	14.99	1.16	0.65	18.63	5.78	4.87
6500	14.55	19.36	19.40	15.43	1.17	0.67	18.21	6.25	4.86
7000	14.47	19.37	20.98	16.09	1.18	0.68	17.60	6.76	4.98
7500	14.39	19.38	22.71	17.19	1.19	0.70	17.12	7.15	5.05
8000	14.29	19.42	21.25	19.02	1.20	0.73	16.25	6.81	5.14
8500	14.20	19.43	18.03	20.40	1.21	0.76	15.19	5.51	5.14
9000	14.05	19.55	16.15	20.33	1.23	0.79	14.76	5.04	5.30
9500	13.92	19.59	16.10	17.88	1.24	0.76	14.08	4.33	5.29
10000	13.80	19.60	17.36	15.12	1.25	0.73	13.50	4.11	5.27
10500	13.68	19.66	19.21	12.79	1.26	0.72	12.84	3.75	5.24
11000	13.55	19.62	21.02	11.38	1.24	0.73	12.40	3.04	5.21
11500	13.43	19.57	19.04	11.19	1.24	0.75	11.61	2.44	5.19
12000	13.27	19.50	15.10	11.96	1.25	0.77	11.60	2.17	5.19
12500	12.92	19.51	12.35	12.58	1.29	0.80	11.10	1.40	5.26
13000	12.46	19.60	10.92	11.70	1.34	0.82	10.86	0.81	5.42
13500	11.86	19.85	10.50	10.32	1.41	0.82	10.75	0.38	5.57
14000	11.20	20.01	11.29	9.60	1.50	0.78	10.86	0.31	5.67
14500	10.63	20.09	11.89	9.43	1.59	0.76	10.88	0.63	5.84
15000	10.22	19.97	12.43	9.53	1.65	0.75	11.04	0.64	6.08
15500	9.80	19.86	13.22	9.77	1.73	0.79	10.90	0.65	6.26
16000	9.37	19.72	13.92	10.05	1.80	0.85	10.90	0.47	6.24
16500	9.02	19.58	13.77	10.34	1.87	0.90	10.26	0.35	6.20
17000	8.50	19.65	12.60	10.60	1.95	0.91	9.98	-0.05	6.06
17500	7.97	19.71	12.39	10.95	2.06	0.90	9.25	-0.76	6.13
18000	7.47	19.88	13.46	11.40	2.24	0.88	8.68	-1.47	6.33

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 14.98mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	14.34	18.31	14.14	11.84	1.07	0.50	14.67	1.93	5.13
50	14.47	18.25	14.62	12.02	1.07	0.49	13.56	1.12	4.84
100	14.48	18.26	14.63	11.95	1.07	0.49	14.25	1.60	4.69
200	14.30	18.45	13.96	12.48	1.09	0.54	13.32	1.00	4.73
300	14.28	18.49	13.85	12.49	1.09	0.55	13.66	1.14	4.75
400	14.42	18.36	14.13	11.73	1.08	0.51	13.63	1.35	4.72
500	14.31	18.49	13.71	12.07	1.09	0.54	13.19	0.88	4.74
600	14.19	18.63	13.24	12.20	1.10	0.57	13.72	1.00	4.80
700	14.31	18.51	13.25	11.22	1.09	0.53	13.85	1.19	4.80
800	14.19	18.64	12.84	11.37	1.10	0.55	13.63	0.99	4.80
900	14.17	18.66	12.48	10.77	1.10	0.54	13.75	0.96	4.80
1000	14.12	18.71	12.31	10.78	1.10	0.55	13.14	0.49	4.83
1500	13.93	18.95	11.14	9.56	1.11	0.55	12.48	-0.03	4.98
2000	13.80	19.09	10.78	9.21	1.12	0.56	12.37	-0.32	5.06
2500	13.73	19.14	10.92	9.27	1.13	0.57	12.45	-0.25	5.07
3000	13.71	19.11	11.29	9.54	1.14	0.59	12.83	0.05	5.07
3500	13.72	19.09	11.66	9.80	1.15	0.60	12.11	-0.26	5.09
4000	13.74	19.01	12.24	10.04	1.15	0.61	12.20	-0.01	5.07
4500	13.79	18.95	13.10	10.45	1.15	0.61	12.60	0.36	4.98
5000	13.87	18.83	14.54	11.09	1.15	0.60	13.55	1.07	4.89
5500	13.94	18.68	17.33	12.51	1.15	0.61	14.95	1.81	4.95
6000	13.94	18.64	19.56	14.28	1.16	0.64	15.49	2.29	4.82
6500	13.88	18.63	21.53	15.93	1.17	0.67	16.25	2.82	4.86
7000	13.81	18.65	26.53	17.64	1.18	0.68	17.59	3.40	4.95
7500	13.72	18.68	38.07	20.08	1.20	0.71	19.05	3.93	5.00
8000	13.59	18.75	22.45	23.94	1.21	0.74	18.48	3.79	5.10
8500	13.45	18.81	17.60	26.71	1.22	0.78	16.53	2.35	5.11
9000	13.27	18.93	15.51	24.77	1.24	0.80	16.49	2.20	5.25
9500	13.11	18.99	15.45	20.49	1.26	0.79	16.02	1.80	5.23
10000	12.98	19.00	16.68	16.66	1.27	0.76	16.52	2.05	5.21
10500	12.85	19.04	17.84	13.75	1.27	0.76	15.90	2.06	5.17
11000	12.70	19.01	17.60	11.91	1.26	0.77	15.16	1.57	5.15
11500	12.55	18.98	15.26	11.22	1.25	0.77	14.08	1.04	5.13
12000	12.33	18.97	12.38	11.29	1.25	0.79	14.08	1.06	5.10
12500	11.91	19.04	10.42	11.09	1.30	0.82	13.42	0.53	5.20
13000	11.40	19.19	9.41	10.15	1.35	0.83	13.10	0.13	5.31
13500	10.79	19.46	9.21	9.20	1.43	0.82	13.07	-0.03	5.45
14000	10.18	19.62	9.95	8.86	1.54	0.79	12.98	0.22	5.57
14500	9.68	19.68	10.51	8.91	1.63	0.76	12.64	0.61	5.77
15000	9.33	19.54	11.08	9.16	1.69	0.76	12.36	0.75	5.93
15500	8.98	19.40	11.82	9.48	1.76	0.80	11.81	0.78	6.12
16000	8.65	19.22	12.64	9.87	1.83	0.87	11.43	0.50	6.14
16500	8.37	19.03	12.71	10.44	1.87	0.91	10.45	0.52	6.05
17000	7.92	19.06	12.01	11.00	1.95	0.92	10.01	-0.20	5.88
17500	7.44	19.10	12.00	11.68	2.07	0.91	9.29	-0.84	5.94
18000	6.94	19.28	12.95	12.41	2.24	0.90	8.83	-1.70	6.18

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 23.55mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	15.80	19.07	19.42	16.05	1.06	0.49	22.24	8.91	5.20
50	15.95	19.01	20.94	16.69	1.06	0.48	20.67	7.96	4.91
100	15.95	19.02	20.92	16.66	1.06	0.48	21.55	8.48	4.73
200	15.79	19.20	19.37	17.18	1.07	0.52	20.47	7.86	4.78
300	15.77	19.23	19.13	17.17	1.07	0.53	20.89	7.96	4.73
400	15.89	19.12	19.66	16.14	1.06	0.50	20.79	8.20	4.76
500	15.79	19.23	18.83	16.47	1.07	0.52	20.17	7.67	4.81
600	15.68	19.34	17.89	16.46	1.08	0.55	20.79	7.82	4.82
700	15.80	19.23	17.82	15.07	1.07	0.51	20.96	7.97	4.83
800	15.69	19.34	17.11	15.16	1.08	0.54	20.63	7.81	4.85
900	15.69	19.34	16.42	14.22	1.08	0.53	20.75	7.80	4.89
1000	15.65	19.39	16.16	14.24	1.08	0.54	19.92	7.26	4.86
1500	15.49	19.56	14.21	12.26	1.09	0.54	19.13	6.79	5.04
2000	15.36	19.68	13.67	11.65	1.10	0.55	18.75	6.45	5.10
2500	15.26	19.74	13.87	11.67	1.11	0.57	18.86	6.52	5.09
3000	15.19	19.74	14.44	12.01	1.12	0.58	19.47	6.80	5.15
3500	15.15	19.75	15.04	12.27	1.13	0.60	18.31	6.38	5.16
4000	15.10	19.70	16.00	12.49	1.13	0.61	18.30	6.63	5.14
4500	15.07	19.67	17.42	12.85	1.14	0.62	18.02	6.88	5.06
5000	15.05	19.65	19.64	13.31	1.14	0.62	18.51	7.45	4.99
5500	14.99	19.60	22.21	14.09	1.15	0.63	18.57	8.01	5.01
6000	14.90	19.63	20.01	14.45	1.16	0.65	18.06	8.11	4.92
6500	14.77	19.65	18.59	14.40	1.17	0.67	17.37	8.38	4.96
7000	14.70	19.64	19.40	14.81	1.17	0.67	16.79	8.52	5.05
7500	14.62	19.61	20.17	15.70	1.18	0.69	16.30	8.35	5.10
8000	14.54	19.60	19.12	17.36	1.19	0.72	15.49	7.73	5.22
8500	14.45	19.58	16.97	18.89	1.19	0.76	14.44	6.65	5.21
9000	14.30	19.67	15.43	19.47	1.21	0.78	13.87	6.04	5.37
9500	14.15	19.72	15.44	17.65	1.23	0.76	13.12	5.24	5.34
10000	14.01	19.72	16.58	15.14	1.24	0.72	12.56	4.79	5.34
10500	13.87	19.77	18.37	12.95	1.25	0.72	11.95	4.30	5.30
11000	13.73	19.73	20.64	11.66	1.24	0.73	11.55	3.57	5.23
11500	13.59	19.66	19.55	11.62	1.25	0.75	10.74	2.91	5.25
12000	13.41	19.58	15.72	12.54	1.26	0.77	10.71	2.48	5.26
12500	13.07	19.58	12.79	13.09	1.30	0.80	10.20	1.76	5.35
13000	12.57	19.67	11.31	11.84	1.34	0.82	10.02	1.10	5.50
13500	11.94	19.92	10.92	10.24	1.41	0.81	9.91	0.73	5.64
14000	11.27	20.08	11.71	9.41	1.50	0.77	10.08	0.60	5.76
14500	10.71	20.16	12.24	9.22	1.58	0.75	10.12	0.78	5.99
15000	10.30	20.03	12.94	9.31	1.65	0.74	10.29	0.75	6.16
15500	9.85	19.92	13.67	9.58	1.73	0.78	10.27	0.74	6.34
16000	9.45	19.76	14.43	9.89	1.80	0.84	10.32	0.56	6.38
16500	9.09	19.62	14.11	10.16	1.86	0.89	9.73	0.48	6.32
17000	8.57	19.67	12.80	10.43	1.94	0.90	9.56	-0.06	6.21
17500	8.06	19.73	12.50	10.76	2.06	0.89	8.88	-0.56	6.28
18000	7.58	19.89	13.54	11.26	2.22	0.88	8.21	-1.40	6.41



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 15.55mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	14.91	18.58	15.53	12.89	1.07	0.49	14.38	2.12	4.12
50	15.02	18.51	15.89	13.02	1.06	0.48	13.27	1.29	3.85
100	15.02	18.53	15.57	12.68	1.06	0.48	14.01	1.76	3.74
200	14.92	18.65	14.80	12.66	1.07	0.50	13.19	1.26	3.79
300	14.93	18.66	15.14	13.11	1.07	0.51	13.57	1.46	3.80
400	15.02	18.58	15.84	13.06	1.07	0.49	13.56	1.65	3.73
500	14.86	18.75	15.26	13.75	1.09	0.54	12.92	1.05	3.78
600	14.78	18.84	14.54	13.20	1.09	0.55	13.43	1.22	3.81
700	14.92	18.72	14.56	12.13	1.07	0.51	13.62	1.40	3.83
800	14.74	18.90	13.73	12.24	1.09	0.55	13.27	1.12	3.81
900	14.81	18.84	13.44	11.41	1.08	0.52	13.51	1.21	3.85
1000	14.69	18.96	13.18	11.74	1.09	0.55	12.70	0.62	3.86
1500	14.62	19.07	12.23	10.37	1.09	0.53	12.19	0.28	4.00
2000	14.45	19.25	11.58	9.89	1.11	0.55	11.96	-0.07	4.01
2500	14.40	19.29	11.51	9.66	1.11	0.55	12.08	0.00	4.03
3000	14.38	19.26	11.75	9.85	1.11	0.56	12.65	0.30	4.05
3500	14.40	19.23	12.32	10.20	1.12	0.58	11.63	-0.13	4.09
4000	14.44	19.12	13.45	10.82	1.12	0.58	11.93	0.23	4.06
4500	14.44	19.11	13.86	10.91	1.12	0.58	12.09	0.46	3.96
5000	14.52	19.00	15.60	11.80	1.12	0.58	12.94	1.04	3.88
5500	14.59	18.86	18.35	13.56	1.13	0.60	14.43	1.90	3.86
6000	14.59	18.82	18.81	15.59	1.13	0.63	14.99	2.34	3.78
6500	14.51	18.85	18.91	16.43	1.14	0.64	15.57	2.93	3.82
7000	14.48	18.86	22.72	17.40	1.15	0.65	16.62	3.40	3.91
7500	14.40	18.88	27.24	18.58	1.16	0.67	18.35	4.02	3.90
8000	14.31	18.94	23.66	19.07	1.17	0.70	18.32	3.88	3.98
8500	14.25	18.97	20.34	19.25	1.17	0.72	16.53	2.79	3.92
9000	14.16	19.03	17.58	19.99	1.18	0.73	16.25	2.64	4.05
9500	14.09	19.06	16.46	18.47	1.19	0.71	15.33	2.13	4.08
10000	14.01	19.06	17.46	15.25	1.19	0.69	16.01	2.49	4.07
10500	13.92	19.15	18.94	12.25	1.19	0.69	15.84	2.14	4.01
11000	13.84	19.13	18.60	10.96	1.17	0.69	15.89	1.90	3.98
11500	13.80	19.06	15.96	10.94	1.16	0.69	14.46	1.10	3.98
12000	13.77	18.91	14.19	12.43	1.16	0.71	15.00	1.47	3.91
12500	13.58	18.81	13.53	14.33	1.18	0.75	14.69	1.18	3.94
13000	13.15	18.93	11.98	14.18	1.23	0.79	14.20	0.81	4.09
13500	12.51	19.29	9.92	10.98	1.29	0.77	14.53	0.77	4.26
14000	11.79	19.58	9.78	9.07	1.35	0.70	15.12	0.88	4.32
14500	11.19	19.73	10.82	8.23	1.42	0.68	15.45	1.51	4.48
15000	10.88	19.58	12.90	8.48	1.47	0.71	15.08	1.87	4.58
15500	10.52	19.44	12.52	9.22	1.54	0.80	14.06	2.17	4.71
16000	10.17	19.30	11.40	9.91	1.59	0.88	13.26	1.88	4.81
16500	9.80	19.12	11.68	9.96	1.63	0.85	11.76	1.73	4.80
17000	9.46	18.99	13.06	10.28	1.70	0.81	11.37	1.10	4.62
17500	8.92	19.12	12.84	9.84	1.76	0.79	9.87	0.40	4.44
18000	8.25	19.42	10.99	9.48	1.87	0.80	9.32	-0.49	4.56

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 11.50mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	12.63	17.53	10.74	8.47	1.08	0.48	16.90	-4.38	4.21
50	12.75	17.57	10.86	8.79	1.09	0.49	20.97	-4.99	3.99
100	12.73	17.57	10.67	8.51	1.08	0.48	17.50	-4.65	3.89
200	12.61	17.70	10.29	8.57	1.10	0.51	17.29	-5.14	3.94
300	12.63	17.70	10.49	8.85	1.10	0.52	16.79	-4.90	4.00
400	12.75	17.60	10.86	8.73	1.09	0.50	16.59	-4.71	3.89
500	12.57	17.81	10.58	9.36	1.12	0.56	25.17	-5.19	3.90
600	12.48	17.93	10.23	9.14	1.12	0.57	20.29	-5.11	3.95
700	12.61	17.80	10.24	8.32	1.10	0.51	19.26	-4.94	3.93
800	12.41	18.02	9.78	8.58	1.12	0.56	19.06	-5.18	3.94
900	12.47	17.97	9.64	7.99	1.11	0.52	18.08	-5.14	3.99
1000	12.34	18.09	9.50	8.26	1.13	0.56	16.13	-5.56	3.99
1500	12.24	18.28	8.99	7.47	1.13	0.54	15.73	-5.97	4.17
2000	12.05	18.50	8.61	7.25	1.14	0.55	13.59	-6.34	4.16
2500	12.01	18.53	8.55	7.07	1.14	0.55	13.89	-6.36	4.16
3000	12.04	18.44	8.68	7.12	1.14	0.55	15.20	-6.20	4.21
3500	12.14	18.37	8.98	7.37	1.14	0.57	13.58	-6.47	4.19
4000	12.27	18.19	9.65	7.78	1.14	0.57	16.77	-6.25	4.18
4500	12.36	18.15	9.87	7.94	1.14	0.56	16.71	-6.00	4.05
5000	12.57	17.84	10.82	8.35	1.12	0.53	18.54	-5.42	3.96
5500	12.83	17.51	12.76	9.84	1.11	0.54	16.07	-4.66	3.96
6000	13.01	17.31	14.64	12.07	1.12	0.58	16.48	-4.20	3.87
6500	13.03	17.28	16.24	14.65	1.13	0.63	16.02	-3.64	3.88
7000	12.98	17.36	17.52	16.65	1.15	0.66	14.65	-3.37	3.98
7500	12.91	17.37	20.26	21.11	1.16	0.68	14.19	-2.92	4.02
8000	12.81	17.51	20.72	31.94	1.18	0.71	14.60	-3.04	4.06
8500	12.70	17.69	18.02	26.72	1.20	0.74	14.43	-4.01	3.98
9000	12.54	17.80	15.15	20.76	1.21	0.76	14.90	-3.91	4.13
9500	12.45	17.90	14.01	18.21	1.22	0.75	16.30	-4.19	4.10
10000	12.39	17.86	14.64	15.62	1.21	0.74	17.60	-3.75	4.09
10500	12.33	17.99	15.41	12.39	1.20	0.74	16.86	-3.99	4.03
11000	12.22	18.01	13.67	10.25	1.16	0.73	15.81	-4.26	4.00
11500	12.17	18.00	11.53	9.30	1.13	0.71	12.81	-4.98	3.99
12000	12.14	17.88	10.10	9.73	1.11	0.74	13.50	-4.54	3.94
12500	11.98	17.80	9.60	10.40	1.13	0.78	12.24	-4.54	3.92
13000	11.58	17.99	8.66	10.29	1.18	0.82	12.01	-4.56	4.07
13500	10.91	18.48	7.47	8.81	1.26	0.77	11.21	-4.36	4.23
14000	10.35	18.75	7.51	7.90	1.34	0.71	10.74	-3.29	4.33
14500	9.90	18.85	8.38	7.67	1.41	0.69	11.22	-1.79	4.44
15000	9.78	18.62	9.93	8.45	1.45	0.74	11.47	-0.53	4.59
15500	9.54	18.46	9.93	9.55	1.51	0.85	11.57	0.79	4.67
16000	9.26	18.37	9.28	10.39	1.54	0.93	11.72	0.59	4.75
16500	8.97	18.15	9.60	10.46	1.57	0.87	10.21	1.02	4.77
17000	8.77	17.94	11.01	11.32	1.63	0.83	9.98	0.29	4.54
17500	8.34	18.05	11.75	11.33	1.73	0.82	8.72	-0.22	4.45
18000	7.61	18.48	10.48	10.95	1.83	0.85	8.43	-1.17	4.56

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 19.76mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	15.71	19.02	18.64	15.40	1.06	0.49	19.28	6.25	4.19
50	15.83	18.94	19.41	15.66	1.06	0.47	17.70	5.33	3.88
100	15.84	18.97	18.93	15.27	1.06	0.47	18.53	5.82	3.77
200	15.74	19.07	17.73	15.15	1.06	0.49	17.62	5.30	3.79
300	15.74	19.09	18.22	15.74	1.07	0.50	18.13	5.49	3.79
400	15.83	19.02	19.23	15.74	1.06	0.49	18.05	5.67	3.74
500	15.67	19.18	18.35	16.47	1.08	0.53	17.29	5.07	3.77
600	15.60	19.26	17.30	15.64	1.08	0.54	17.87	5.24	3.85
700	15.74	19.13	17.30	14.36	1.07	0.50	18.09	5.42	3.78
800	15.57	19.30	16.16	14.37	1.08	0.54	17.68	5.14	3.83
900	15.64	19.24	15.74	13.37	1.07	0.51	17.98	5.25	3.83
1000	15.53	19.35	15.42	13.73	1.08	0.54	16.98	4.62	3.85
1500	15.48	19.43	14.16	11.98	1.08	0.52	16.50	4.31	3.97
2000	15.31	19.59	13.31	11.31	1.10	0.54	16.23	3.94	4.03
2500	15.26	19.63	13.21	11.04	1.10	0.54	16.53	4.02	4.06
3000	15.23	19.62	13.53	11.29	1.11	0.56	17.48	4.33	4.04
3500	15.23	19.61	14.26	11.70	1.11	0.58	16.27	3.83	4.09
4000	15.24	19.53	15.67	12.42	1.11	0.59	16.85	4.21	4.07
4500	15.22	19.54	16.07	12.41	1.12	0.59	17.04	4.41	3.98
5000	15.24	19.49	18.02	13.41	1.12	0.59	18.20	4.95	3.90
5500	15.25	19.42	19.37	15.00	1.12	0.61	19.58	5.72	3.89
6000	15.20	19.45	17.37	16.19	1.13	0.64	20.02	6.05	3.82
6500	15.08	19.50	16.50	15.86	1.14	0.65	20.11	6.61	3.85
7000	15.06	19.49	18.70	16.36	1.15	0.65	19.94	7.11	3.94
7500	14.99	19.52	19.57	16.46	1.16	0.66	19.61	7.76	4.00
8000	14.91	19.59	18.69	16.21	1.16	0.69	18.73	7.63	4.02
8500	14.88	19.58	17.93	16.16	1.17	0.70	17.64	6.54	3.98
9000	14.84	19.62	17.00	16.91	1.17	0.71	17.22	6.25	4.13
9500	14.80	19.64	16.44	16.06	1.18	0.68	16.68	5.52	4.12
10000	14.74	19.65	17.13	13.55	1.18	0.66	15.87	5.59	4.13
10500	14.66	19.76	18.16	11.09	1.17	0.65	15.28	5.02	4.02
11000	14.63	19.73	20.00	10.20	1.15	0.65	14.67	4.55	4.05
11500	14.65	19.64	18.96	10.60	1.15	0.66	13.70	3.76	4.04
12000	14.67	19.45	17.58	12.60	1.15	0.68	13.61	3.83	4.01
12500	14.52	19.34	16.88	15.71	1.17	0.71	13.00	3.35	4.01
13000	14.17	19.38	14.58	17.10	1.21	0.76	12.49	2.65	4.16
13500	13.60	19.65	11.67	12.77	1.26	0.75	12.64	2.28	4.33
14000	12.87	19.93	11.18	10.01	1.32	0.70	12.55	1.95	4.40
14500	12.22	20.10	12.25	8.75	1.37	0.68	12.63	2.12	4.60
15000	11.83	19.97	14.70	8.72	1.42	0.70	12.62	2.22	4.69
15500	11.37	19.85	13.63	9.28	1.49	0.77	12.49	2.33	4.79
16000	10.99	19.73	12.21	9.92	1.55	0.85	12.45	2.18	4.87
16500	10.55	19.53	12.68	9.92	1.60	0.83	11.53	1.97	4.89
17000	10.14	19.47	13.94	10.02	1.67	0.80	11.38	1.44	4.65
17500	9.45	19.71	12.32	9.16	1.74	0.78	10.08	0.67	4.57
18000	8.80	20.00	10.53	8.66	1.85	0.77	9.48	-0.01	4.70

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 22.49mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	15.46	18.87	17.97	15.12	1.06	0.49	21.49	8.48	5.81
50	15.61	18.82	19.52	15.71	1.06	0.49	20.01	7.48	5.71
100	15.62	18.82	19.93	15.99	1.06	0.49	20.86	8.04	5.53
200	15.36	19.09	18.69	17.76	1.09	0.56	19.71	7.26	5.54
300	15.37	19.09	18.44	17.22	1.09	0.55	20.18	7.48	5.50
400	15.53	18.94	18.40	15.26	1.07	0.51	20.10	7.73	5.51
500	15.44	19.03	17.46	15.20	1.08	0.53	19.51	7.25	5.60
600	15.35	19.13	16.74	15.26	1.09	0.55	20.17	7.42	5.61
700	15.41	19.08	16.28	14.05	1.08	0.53	20.22	7.48	5.63
800	15.33	19.16	15.72	13.91	1.08	0.54	19.95	7.25	5.64
900	15.26	19.23	14.92	13.27	1.09	0.55	19.96	7.18	5.67
1000	15.26	19.23	14.65	12.93	1.09	0.54	19.23	6.72	5.68
1500	15.06	19.43	13.13	11.55	1.10	0.56	18.48	6.26	5.84
2000	14.95	19.50	13.09	11.29	1.11	0.57	18.19	5.97	5.92
2500	14.83	19.56	13.47	11.52	1.12	0.58	18.42	6.06	5.90
3000	14.70	19.59	13.52	11.50	1.13	0.60	18.88	6.26	6.00
3500	14.57	19.64	13.57	11.39	1.15	0.62	17.84	5.87	6.02
4000	14.50	19.60	14.42	11.64	1.16	0.63	17.68	6.08	6.00
4500	14.47	19.51	16.25	12.12	1.16	0.64	17.47	6.29	5.88
5000	14.43	19.46	18.79	12.37	1.16	0.64	17.97	6.98	5.81
5500	14.35	19.38	23.15	12.73	1.17	0.64	17.74	7.43	5.80
6000	14.23	19.36	24.58	12.97	1.18	0.66	17.10	7.46	5.76
6500	14.10	19.32	23.62	13.49	1.19	0.68	16.27	7.48	5.80
7000	13.99	19.25	26.01	14.77	1.20	0.69	15.51	7.28	5.93
7500	13.88	19.18	23.81	17.24	1.21	0.72	14.90	6.82	6.01
8000	13.71	19.17	17.84	20.91	1.22	0.77	14.11	6.06	6.15
8500	13.48	19.19	15.36	23.46	1.23	0.81	13.12	5.04	6.09
9000	13.20	19.31	14.83	23.45	1.27	0.84	12.53	4.37	6.25
9500	12.94	19.38	15.89	20.17	1.31	0.83	11.84	3.62	6.26
10000	12.66	19.40	17.31	17.21	1.35	0.80	11.33	3.00	6.47
10500	12.39	19.47	17.82	14.79	1.37	0.79	10.82	2.61	6.30
11000	12.14	19.42	17.07	13.29	1.37	0.81	10.44	1.88	6.26
11500	11.87	19.39	15.18	12.53	1.39	0.82	9.90	1.35	6.26
12000	11.53	19.37	13.13	12.15	1.42	0.83	9.96	0.87	6.21
12500	10.99	19.48	11.25	10.93	1.47	0.83	9.60	0.22	6.33
13000	10.31	19.72	10.07	9.52	1.55	0.84	9.46	-0.24	6.50
13500	9.67	19.94	10.20	8.76	1.65	0.85	9.12	-0.57	6.60
14000	9.13	19.97	11.10	8.95	1.76	0.86	9.33	-0.49	6.79
14500	8.67	19.91	11.55	9.49	1.87	0.84	9.33	-0.38	7.02
15000	8.26	19.83	11.61	9.77	1.96	0.81	9.56	-0.27	7.28
15500	7.81	19.80	12.24	9.53	2.05	0.80	9.51	-0.42	7.54
16000	7.43	19.67	14.43	9.33	2.14	0.82	9.52	-0.59	7.48
16500	7.07	19.50	14.64	9.61	2.20	0.87	9.05	-0.76	7.38
17000	6.52	19.63	11.30	10.24	2.31	0.94	8.66	-1.14	7.28
17500	6.03	19.75	10.17	11.97	2.48	1.01	8.45	-1.71	7.61
18000	5.55	19.82	11.13	15.22	2.71	1.03	7.74	-2.57	8.02

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 18.28mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	14.85	18.56	15.85	13.33	1.07	0.50	18.26	5.50	5.76
50	15.00	18.50	16.72	13.69	1.07	0.49	16.89	4.59	5.64
100	15.02	18.50	17.05	13.89	1.07	0.49	17.71	5.13	5.47
200	14.76	18.77	16.21	15.38	1.09	0.57	16.59	4.41	5.49
300	14.77	18.77	16.02	14.94	1.09	0.56	17.01	4.56	5.46
400	14.93	18.63	16.03	13.35	1.08	0.51	16.98	4.81	5.47
500	14.83	18.73	15.35	13.37	1.08	0.53	16.43	4.32	5.55
600	14.74	18.84	14.80	13.47	1.09	0.56	17.04	4.49	5.57
700	14.79	18.79	14.48	12.44	1.09	0.53	17.09	4.56	5.55
800	14.71	18.87	14.04	12.34	1.09	0.55	16.85	4.42	5.59
900	14.64	18.95	13.41	11.83	1.10	0.55	16.89	4.29	5.60
1000	14.63	18.96	13.19	11.55	1.10	0.55	16.18	3.84	5.66
1500	14.43	19.19	11.97	10.43	1.11	0.56	15.48	3.37	5.78
2000	14.34	19.27	11.99	10.29	1.12	0.57	15.27	3.13	5.84
2500	14.26	19.32	12.34	10.57	1.13	0.59	15.58	3.15	5.86
3000	14.17	19.36	12.40	10.61	1.14	0.60	16.09	3.33	5.89
3500	14.09	19.41	12.44	10.55	1.15	0.62	15.34	3.08	5.98
4000	14.07	19.36	13.20	10.87	1.16	0.63	15.51	3.21	5.93
4500	14.12	19.25	14.75	11.52	1.16	0.63	15.81	3.58	5.81
5000	14.14	19.18	16.76	12.06	1.16	0.63	16.93	4.37	5.70
5500	14.12	19.09	19.95	12.88	1.17	0.64	17.38	4.93	5.74
6000	14.05	19.08	21.87	13.71	1.18	0.66	17.14	5.24	5.67
6500	13.96	19.06	23.09	14.69	1.19	0.68	16.52	5.61	5.72
7000	13.86	19.05	27.53	16.26	1.20	0.69	15.80	5.92	5.83
7500	13.75	19.03	27.56	19.17	1.22	0.72	15.27	5.88	5.93
8000	13.58	19.06	18.99	23.47	1.23	0.76	14.51	5.38	6.03
8500	13.38	19.11	16.05	26.16	1.24	0.81	13.55	4.16	6.01
9000	13.14	19.24	15.35	24.31	1.28	0.84	13.08	3.55	6.16
9500	12.91	19.30	16.44	19.71	1.31	0.82	12.39	2.91	6.15
10000	12.67	19.33	17.79	16.35	1.34	0.79	11.92	2.42	6.20
10500	12.43	19.39	18.01	13.93	1.35	0.78	11.40	2.14	6.17
11000	12.22	19.34	16.89	12.54	1.34	0.80	11.02	1.39	6.11
11500	11.99	19.30	14.92	11.92	1.35	0.81	10.51	0.94	6.11
12000	11.67	19.27	12.87	11.79	1.37	0.82	10.58	0.59	6.06
12500	11.15	19.37	10.97	10.94	1.43	0.83	10.24	-0.11	6.16
13000	10.50	19.60	9.76	9.71	1.51	0.84	10.08	-0.55	6.33
13500	9.87	19.82	9.87	8.98	1.60	0.86	9.75	-0.93	6.39
14000	9.33	19.85	10.80	9.15	1.72	0.86	9.94	-0.69	6.57
14500	8.86	19.80	11.30	9.75	1.82	0.85	9.94	-0.56	6.83
15000	8.43	19.75	11.29	10.02	1.92	0.81	10.17	-0.46	7.07
15500	7.95	19.73	11.90	9.73	2.01	0.80	10.09	-0.51	7.32
16000	7.56	19.59	14.04	9.48	2.10	0.82	10.03	-0.69	7.28
16500	7.18	19.46	14.41	9.67	2.17	0.87	9.54	-0.91	7.15
17000	6.62	19.59	11.16	10.18	2.28	0.94	9.04	-1.23	7.01
17500	6.08	19.71	9.98	11.74	2.44	1.01	8.90	-1.75	7.32
18000	5.56	19.79	10.93	15.01	2.68	1.03	8.22	-2.71	7.74

## Typical Performance Data

### Definitions:









Input Return Loss = -S11 (dB)  
 Gain(Power Gain) = S21 (dB)  
 Reverse Isolation = -S12 (dB)  
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 26.88mA @ Temperature = +85°C








FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10	15.82	19.07	19.99	16.39	1.06	0.49	24.52	10.71	5.87
50	15.97	19.02	21.93	17.29	1.06	0.48	22.56	9.74	5.77
100	15.98	19.03	22.46	17.65	1.06	0.48	23.42	10.31	5.59
200	15.73	19.28	20.69	19.55	1.08	0.55	22.27	9.59	5.62
300	15.74	19.28	20.31	18.91	1.08	0.54	22.72	9.75	5.58
400	15.89	19.14	20.19	16.70	1.06	0.50	22.61	9.97	5.59
500	15.81	19.22	19.02	16.64	1.07	0.52	22.03	9.46	5.70
600	15.71	19.32	18.12	16.68	1.08	0.54	22.78	9.69	5.70
700	15.78	19.26	17.47	15.26	1.07	0.52	22.87	9.73	5.69
800	15.70	19.33	16.79	15.06	1.08	0.53	22.63	9.60	5.72
900	15.63	19.39	15.84	14.30	1.08	0.54	22.72	9.49	5.76
1000	15.63	19.39	15.51	13.94	1.08	0.54	21.96	8.97	5.74
1500	15.41	19.56	13.70	12.27	1.09	0.55	21.41	8.52	5.93
2000	15.27	19.62	13.60	11.87	1.10	0.56	21.33	8.25	5.98
2500	15.10	19.66	13.95	11.97	1.11	0.58	21.78	8.36	5.99
3000	14.92	19.69	13.91	11.80	1.13	0.60	22.29	8.55	6.05
3500	14.73	19.73	13.90	11.57	1.14	0.62	20.85	8.13	6.14
4000	14.58	19.68	14.73	11.67	1.15	0.64	20.19	8.21	6.12
4500	14.49	19.57	16.60	11.93	1.16	0.64	19.32	8.32	6.00
5000	14.38	19.51	19.42	11.83	1.16	0.64	19.13	8.78	5.90
5500	14.24	19.41	25.07	11.80	1.16	0.64	18.32	8.85	5.88
6000	14.09	19.36	29.81	11.80	1.17	0.66	17.38	8.46	5.87
6500	13.95	19.25	27.31	12.24	1.17	0.67	16.35	8.01	5.91
7000	13.84	19.12	27.07	13.50	1.18	0.68	15.42	7.50	6.03
7500	13.71	18.99	21.45	15.84	1.19	0.72	14.68	6.86	6.11
8000	13.50	18.93	16.31	19.36	1.20	0.77	13.82	6.00	6.30
8500	13.22	18.95	14.22	21.92	1.21	0.83	12.83	4.98	6.27
9000	12.89	19.07	13.89	23.75	1.26	0.86	12.20	4.27	6.43
9500	12.58	19.13	14.99	22.33	1.32	0.85	11.52	3.51	6.41
10000	12.25	19.17	16.31	19.61	1.37	0.82	10.98	2.89	6.46
10500	11.92	19.23	16.70	16.60	1.41	0.82	10.47	2.35	6.47
11000	11.62	19.20	15.90	14.61	1.42	0.84	10.09	1.69	6.45
11500	11.31	19.19	14.31	13.33	1.44	0.84	9.54	1.09	6.42
12000	10.91	19.20	12.54	12.19	1.47	0.83	9.57	0.60	6.42
12500	10.29	19.36	10.87	10.27	1.53	0.83	9.21	-0.08	6.53
13000	9.56	19.66	9.81	8.71	1.62	0.83	9.06	-0.52	6.72
13500	8.92	19.88	10.01	8.05	1.72	0.84	8.71	-0.80	6.84
14000	8.43	19.88	10.98	8.29	1.83	0.85	8.92	-0.62	7.04
14500	8.01	19.78	11.48	8.95	1.94	0.83	8.91	-0.51	7.27
15000	7.62	19.73	11.37	9.26	2.03	0.80	9.14	-0.44	7.53
15500	7.19	19.67	11.91	9.06	2.12	0.79	9.08	-0.65	7.86
16000	6.88	19.52	14.09	8.88	2.20	0.81	9.14	-0.77	7.81
16500	6.59	19.32	14.81	9.30	2.26	0.86	8.65	-0.93	7.70
17000	6.15	19.35	11.41	10.26	2.34	0.94	8.33	-1.25	7.52
17500	5.68	19.42	10.01	12.32	2.49	1.02	8.10	-1.86	7.93
18000	5.16	19.52	10.78	16.35	2.73	1.04	7.36	-2.76	8.37



## Typical Performance Curves




## Typical Performance Curves






### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
MC1630-1	.079 (2.00)	.079 (2.00)	.039 (1.00)	.047 (1.20)	.024 (.60)	.010 (.25)	.014 (.35)	.026 (.65)	.008 (.20)	.002 (.05)	.106 (2.70)	.049 (1.25)	.026 (.65)	.031 (.80)

CASE #.	Q	R	WT, GRAM
MC1630-1	.012 (.30)	.012 (.30)	.006

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin-Silver over Nickel plated or Matte-Tin plated (See Data sheet).  
All models, (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

**Mini-Circuits®**


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M166967	NEW RELEASE	03/21/18	ITG	GL

SUGGESTED MOUNTING CONFIGURATION  
FOR MC1630-1 CASE STYLE, "06AM04" PIN CODE




NOTES:

1. LINE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010"±.001".  
 COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	ITG	03/21/18
	CHECKED	GF	03/21/18
	APPROVED	GL	03/21/18



**Mini-Circuits®**



13 Neptune Avenue  
 Brooklyn NY 11235

PL, 06AM04, MC1630-1, TB-995+

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-544	REV: OR
FILE: 98PL544	SCALE: 15:1	SHEET: 1 OF 1	

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
 EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
 AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
 DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
 THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
 PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit




COMPONENT	VALUE	SIZE
DUT	EHA-163L+	2X2 MM
C1,C2	0.1 $\mu$ F	0402
C3	0.01 $\mu$ F	
R1	50 Ohm	0603
L1	6.5 $\mu$ H	4422

Schematic Diagram

**Notes:**

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C or -45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
	monoethanolamine at 63°C to 70°C	