

# Monolithic Amplifier

DC-3 GHz

## Product Features

- DC-3 GHz
- Single Voltage Supply
- Internally Matched to 50 Ohms
- Unconditionally Stable
- Low Performance Variation Over Temperature
- Transient Protected
- Aqueous washable
- Protected By US Patent 6,943,629



Generic photo used for illustration purposes only

## ERA-3SM+

CASE STYLE: WW107

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Typical Applications

- Cellular/ PCS/ 3G Base Station
- CATV, Cable Modem & DBS
- Fixed Wireless & WLAN
- Microwave Radio & Test Equipment

## General Description

ERA-3SM+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a Micro-X package. ERA-3SM+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 9,000 years at 85°C case temperature.

## simplified schematic and pin description



Function	Pin Number	Description
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Electrical Specifications at 25°C and 35mA, unless noted

Parameter	Min.	Typ.	Max.	Units	Cpk	
Frequency Range*	DC		3	GHz		
Gain	f=0.1 GHz	21	23.4	24.4	dB	≥ 1.5
	f=1 GHz	—	21	—		
	f=2 GHz	17.6	18.7	20.7		
	f=3 GHz	15.4	16.4	18.5		
Magnitude of Gain Variation versus Temperature (values are negative)	f=0.1 GHz	—	0.0045	0.009	dB/°C	
	f=1 GHz	—	0.0051	0.010		
	f=2 GHz	—	0.0059	0.012		
	f=3 GHz	—	0.0064	0.013		
Input Return Loss	f=0.1 GHz		30		dB	
	f=1 GHz		19			
	f=2 GHz		18			
	f=3 GHz		18			
Output Return Loss	f=0.1 GHz		21		dB	
	f=1 GHz		17			
	f=2 GHz		17			
	f=3 GHz		17			
Reverse Isolation	f=2 GHz	21	24	—	dB	
Output Power @ 1 dB compression	f=0.1 GHz	—	12.5	—	dBm	≥ 1.5
	f=1 GHz	—	12.1	—		
	f=2 GHz	9	12.5	—		
	f=3 GHz	—	10.5	—		
Saturated Output Power (at 3dB compression)	f=0.1 GHz		13.6		dBm	
	f=1 GHz		13.3			
	f=2 GHz		13.1			
	f=3 GHz		12.1			
Output IP3	f=0.1 GHz	24	27	—	dBm	≥ 1.5
	f=1 GHz	24	27	—		
	f=2 GHz	23	26	—		
	f=3 GHz	21	24	—		
Noise Figure	f=0.1 GHz		2.7		dB	≥ 1.5
	f=1 GHz		2.6			
	f=2 GHz		2.8			
	f=3 GHz		2.9			
Group Delay	f=2 GHz		80		psec	
Recommended Device Operating Current			35		mA	
Device Operating Voltage	3.0	3.2	3.4		V	≥ 1.5
Device Voltage Variation vs. Temperature at 35mA		-2.3			mV/°C	
Device Voltage Variation vs. Current at 25°C		3.6			mV/mA	
Thermal Resistance, junction-to-case <sup>1</sup>		186			°C/W	

\*Guaranteed specification DC-3 GHz. Low frequency cut off determined by external coupling capacitors.

Absolute Maximum Ratings

Parameter	Ratings
Operating Temperature*	-45°C to 85°C
Storage Temperature	-65°C to 150°C
Operating Current	75mA
Power Dissipation	330mW
Input Power	13dBm


Note: Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.  
<sup>1</sup>Case is defined as ground leads.  
 \*Based on typical case temperature rise 5°C above ambient.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Product Marking



Markings in addition to model number designation may appear for internal quality control purposes.

Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Performance data, graphs, s-parameter data set (.zip file)

Case Style: WW107

Plastic micro-x, .085 body diameter, lead finish: Matte-Tin

Tape & Reel: F4


7" Reels with 20, 50, 100, 200, 500, 1K devices

Suggested Layout for PCB Design: PL-075

Evaluation Board: TB-408-3+

Environmental Ratings: ENV08T2

Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS	
Vcc	"1%" Res. Values (ohms) for Optimum Biasing
7	107
8	133
9	162
10	191
11	221
12	251
13	280
14	309
15	340
16	365
17	392
18	422
19	453
20	475

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**ESD Rating**

Human Body Model (HBM): Class 1A (250 v to < 500 v) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 (< 100 v) in accordance with ANSI/ESD STM 5.2 - 1999

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

**MSL Test Flow Chart**



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions  
or to view GRAPHS.**

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 35mA, Vd = 3.25V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	22.97	25.25	37.00	23.90	1.03	0.77	26.87	12.72	2.51
100	22.93	25.66	37.58	23.73	1.05	0.73	27.44	12.72	2.58
150	22.88	25.57	34.27	23.66	1.04	0.73	27.40	12.80	2.59
200	22.82	25.63	31.98	23.12	1.05	0.72	27.34	12.79	2.53
250	22.73	25.61	30.21	22.90	1.05	0.72	26.64	12.80	2.57
300	22.68	25.49	29.01	22.51	1.05	0.72	27.54	12.75	2.60
350	22.60	25.48	27.80	22.06	1.05	0.72	27.41	12.77	2.55
400	22.51	25.47	26.61	21.82	1.05	0.71	26.97	12.71	2.58
450	22.42	25.41	25.60	21.46	1.05	0.71	26.98	12.69	2.57
500	22.30	25.41	24.83	20.92	1.05	0.69	26.91	12.74	2.59
550	22.21	25.38	24.03	20.53	1.05	0.69	27.11	12.79	2.60
600	22.08	25.31	23.38	20.12	1.05	0.68	26.94	12.84	2.64
650	21.97	25.25	22.88	19.80	1.05	0.68	27.05	12.78	2.62
700	21.86	25.21	22.36	19.42	1.06	0.67	27.21	12.78	2.59
750	21.75	25.17	21.77	19.10	1.06	0.67	27.29	12.66	2.59
800	21.62	25.14	21.31	18.76	1.06	0.66	27.42	12.64	2.59
850	21.50	25.10	20.84	18.52	1.06	0.65	27.28	12.61	2.58
900	21.37	25.02	20.52	18.19	1.06	0.65	27.55	12.56	2.61
940	21.29	24.98	20.23	17.96	1.06	0.64	27.41	12.47	2.55
1000	21.13	24.93	19.84	17.66	1.06	0.63	27.45	12.53	2.55
1100	20.88	24.85	19.35	17.22	1.07	0.62	27.29	12.57	2.68
1200	20.63	24.78	18.91	16.80	1.07	0.60	27.16	12.47	2.60
1300	20.38	24.67	18.67	16.51	1.08	0.59	27.32	12.62	2.71
1400	20.13	24.58	18.35	16.23	1.08	0.58	26.84	12.68	2.67
1500	19.89	24.47	18.19	15.93	1.09	0.57	27.10	12.58	2.70
1600	19.64	24.46	17.93	15.76	1.10	0.56	27.27	12.50	2.70
1700	19.40	24.37	17.86	15.63	1.11	0.55	27.89	12.45	2.71
1800	19.16	24.27	17.81	15.52	1.12	0.54	27.69	12.56	2.72
1900	18.93	24.20	17.70	15.39	1.13	0.53	27.20	12.43	2.64
2000	18.70	24.10	17.70	15.32	1.14	0.52	27.39	12.51	2.63
2100	18.48	24.05	17.70	15.22	1.15	0.51	26.77	12.43	2.67
2200	18.25	24.02	17.70	15.16	1.17	0.50	26.85	12.40	2.61
2300	18.02	23.96	17.65	15.11	1.18	0.49	26.59	12.19	2.63
2400	17.79	23.93	17.65	15.08	1.20	0.48	26.55	12.08	2.54
2500	17.58	23.87	17.53	15.05	1.21	0.47	26.46	11.96	2.69
2600	17.38	23.79	17.50	15.15	1.23	0.47	26.02	11.61	2.58
2700	17.18	23.75	17.54	15.20	1.24	0.46	26.06	11.51	2.72
2800	16.97	23.69	17.51	15.26	1.26	0.46	25.63	11.16	2.61
2900	16.78	23.64	17.46	15.27	1.27	0.45	25.59	11.33	2.66
3000	16.57	23.58	17.43	15.33	1.29	0.44	25.24	10.81	2.74

REV. X1  
ERA-3SM+  
070816

Page 1 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I<sub>cc</sub> = 28mA, V<sub>d</sub> = 3.22V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	22.55	25.30	26.96	31.67	1.05	0.73	23.91	11.03	2.48
100	22.52	25.25	27.00	32.07	1.05	0.73	24.46	10.95	2.56
150	22.47	25.24	26.80	31.99	1.05	0.73	24.35	11.16	2.53
200	22.42	25.18	26.62	29.62	1.05	0.73	24.33	11.15	2.52
250	22.33	25.17	26.30	28.96	1.05	0.72	23.71	11.04	2.55
300	22.27	25.15	25.78	28.08	1.05	0.72	24.49	10.98	2.57
350	22.20	25.12	25.26	26.89	1.05	0.71	24.43	11.01	2.54
400	22.11	25.05	24.89	26.20	1.05	0.71	24.00	10.98	2.54
450	22.04	25.02	24.17	25.31	1.05	0.71	24.03	10.83	2.56
500	21.92	25.03	23.86	24.54	1.06	0.70	23.96	11.03	2.53
550	21.83	24.97	23.38	23.71	1.06	0.69	24.15	11.00	2.55
600	21.73	24.97	22.89	22.94	1.06	0.68	24.04	11.14	2.61
650	21.61	24.89	22.61	22.40	1.06	0.68	24.15	10.94	2.60
700	21.50	24.91	22.15	21.84	1.06	0.67	24.30	11.10	2.54
750	21.40	24.84	21.70	21.31	1.06	0.67	24.38	10.95	2.56
800	21.27	24.80	21.31	20.91	1.06	0.66	24.56	10.95	2.57
850	21.18	24.73	20.90	20.38	1.06	0.66	24.41	10.76	2.55
900	21.05	24.76	20.66	19.96	1.07	0.64	24.74	10.94	2.58
940	20.96	24.70	20.42	19.66	1.07	0.64	24.62	10.84	2.54
1000	20.81	24.62	20.02	19.21	1.07	0.63	24.68	10.83	2.54
1100	20.57	24.57	19.59	18.54	1.08	0.62	24.53	10.96	2.66
1200	20.32	24.50	19.19	18.01	1.08	0.61	24.45	10.71	2.58
1300	20.08	24.42	18.93	17.62	1.09	0.59	24.70	11.00	2.70
1400	19.84	24.35	18.61	17.21	1.10	0.58	24.40	11.02	2.67
1500	19.62	24.30	18.45	16.85	1.11	0.57	24.71	10.99	2.66
1600	19.37	24.23	18.18	16.58	1.11	0.56	24.93	10.95	2.66
1700	19.13	24.16	18.10	16.40	1.13	0.55	25.52	10.87	2.67
1800	18.91	24.14	18.00	16.20	1.14	0.54	25.61	10.93	2.65
1900	18.68	24.06	17.88	16.03	1.15	0.53	25.16	10.86	2.59
2000	18.46	23.99	17.85	15.87	1.16	0.52	25.52	10.97	2.62
2100	18.22	23.89	17.81	15.77	1.17	0.51	25.05	10.93	2.63
2200	18.01	23.88	17.79	15.67	1.19	0.50	25.28	10.95	2.58
2300	17.78	23.86	17.69	15.59	1.20	0.49	25.19	10.88	2.60
2400	17.57	23.82	17.65	15.50	1.22	0.48	25.15	10.91	2.51
2500	17.35	23.78	17.48	15.44	1.23	0.47	25.16	10.93	2.62
2600	17.16	23.74	17.42	15.47	1.25	0.47	24.74	10.66	2.51
2700	16.95	23.72	17.40	15.52	1.27	0.46	24.88	10.66	2.69
2800	16.75	23.68	17.35	15.55	1.29	0.45	24.42	10.31	2.59
2900	16.56	23.61	17.27	15.56	1.30	0.45	24.44	10.51	2.59
3000	16.36	23.58	17.20	15.57	1.32	0.44	24.22	10.00	2.67

REV. X1  
ERA-3SM+  
070816  
Page 2 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I<sub>cc</sub> = 42mA, V<sub>d</sub> = 3.27V @Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	23.23	25.85	31.94	20.35	1.04	0.74	29.25	13.70	2.56
100	23.19	25.81	31.13	20.70	1.04	0.74	29.84	13.79	2.61
150	23.14	25.91	30.65	20.63	1.05	0.73	29.83	13.80	2.60
200	23.08	25.84	28.99	20.38	1.04	0.73	29.73	13.80	2.59
250	23.00	25.82	27.89	20.30	1.05	0.72	28.93	13.89	2.62
300	22.92	25.83	27.33	19.91	1.05	0.72	29.92	13.87	2.64
350	22.84	25.72	26.15	19.78	1.05	0.72	29.73	13.74	2.57
400	22.75	25.73	25.25	19.52	1.05	0.71	29.26	13.67	2.63
450	22.66	25.68	24.52	19.32	1.05	0.70	29.19	13.82	2.63
500	22.55	25.64	23.74	18.98	1.05	0.70	29.12	13.74	2.62
550	22.43	25.60	23.13	18.67	1.05	0.69	29.28	13.87	2.64
600	22.32	25.57	22.48	18.48	1.05	0.68	29.04	13.84	2.66
650	22.20	25.47	22.04	18.17	1.05	0.68	29.12	13.90	2.67
700	22.09	25.47	21.56	17.96	1.05	0.67	29.23	13.69	2.61
750	21.97	25.41	21.06	17.72	1.05	0.66	29.29	13.68	2.63
800	21.84	25.34	20.65	17.47	1.05	0.66	29.36	13.61	2.63
850	21.72	25.27	20.22	17.30	1.05	0.65	29.19	13.65	2.64
900	21.60	25.22	19.89	17.06	1.05	0.65	29.36	13.49	2.64
940	21.49	25.19	19.63	16.87	1.05	0.64	29.17	13.38	2.61
1000	21.34	25.14	19.27	16.68	1.06	0.63	29.17	13.50	2.61
1100	21.08	25.03	18.83	16.34	1.06	0.62	28.91	13.42	2.72
1200	20.82	24.92	18.46	15.98	1.06	0.61	28.80	13.40	2.63
1300	20.57	24.82	18.26	15.79	1.07	0.59	28.73	13.51	2.76
1400	20.33	24.73	17.94	15.58	1.07	0.58	28.21	13.57	2.71
1500	20.08	24.65	17.80	15.37	1.08	0.57	28.44	13.34	2.77
1600	19.82	24.57	17.58	15.22	1.09	0.56	28.53	13.33	2.72
1700	19.59	24.46	17.52	15.12	1.10	0.55	29.01	13.24	2.76
1800	19.34	24.37	17.51	15.06	1.11	0.54	28.57	13.39	2.76
1900	19.11	24.32	17.42	14.99	1.12	0.53	28.11	13.20	2.68
2000	18.86	24.21	17.46	14.93	1.13	0.52	28.11	13.29	2.71
2100	18.64	24.13	17.50	14.87	1.14	0.51	27.49	13.16	2.69
2200	18.41	24.06	17.50	14.83	1.15	0.50	27.49	13.05	2.65
2300	18.19	24.02	17.49	14.81	1.17	0.49	27.17	12.84	2.67
2400	17.96	23.96	17.53	14.81	1.18	0.49	27.04	12.61	2.57
2500	17.74	23.92	17.45	14.81	1.20	0.48	26.90	12.51	2.71
2600	17.54	23.85	17.47	14.94	1.21	0.47	26.63	12.09	2.64
2700	17.33	23.76	17.52	14.99	1.23	0.47	26.65	11.99	2.77
2800	17.13	23.73	17.53	15.07	1.24	0.46	26.14	11.60	2.66
2900	16.93	23.66	17.50	15.12	1.26	0.45	26.12	11.80	2.76
3000	16.73	23.59	17.47	15.20	1.27	0.45	25.77	11.24	2.88

REV. X1  
ERA-3SM+  
070816  
Page 3 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 35mA, Vd = 3.42V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	23.08	25.71	37.23	23.12	1.04	0.74	27.58	13.34	2.16
100	23.05	25.72	37.81	24.02	1.04	0.73	28.14	13.31	2.16
150	23.02	25.63	33.36	24.38	1.04	0.74	28.04	13.42	2.16
200	22.95	25.65	30.59	23.93	1.04	0.73	28.01	13.36	2.16
250	22.88	25.65	29.05	23.43	1.05	0.73	27.37	13.40	2.18
300	22.81	25.62	27.89	22.68	1.05	0.72	28.24	13.35	2.25
350	22.74	25.58	26.86	22.21	1.05	0.72	28.19	13.34	2.12
400	22.65	25.54	25.94	21.72	1.05	0.71	27.78	13.28	2.15
450	22.57	25.50	25.20	21.33	1.05	0.71	27.83	13.24	2.14
500	22.47	25.42	24.51	20.72	1.05	0.71	27.80	13.31	2.12
550	22.36	25.41	23.97	20.30	1.05	0.70	27.99	13.30	2.17
600	22.26	25.35	23.51	19.88	1.05	0.70	27.83	13.39	2.22
650	22.14	25.32	23.19	19.46	1.05	0.69	27.96	13.30	2.18
700	22.03	25.28	22.63	19.20	1.05	0.68	28.11	13.35	2.12
750	21.93	25.19	21.97	18.89	1.05	0.68	28.20	13.23	2.14
800	21.81	25.16	21.39	18.56	1.05	0.67	28.37	13.25	2.12
850	21.69	25.09	20.91	18.31	1.05	0.67	28.19	13.13	2.15
900	21.57	25.08	20.54	17.93	1.05	0.66	28.53	13.16	2.13
940	21.47	25.04	20.32	17.67	1.05	0.65	28.36	13.12	2.08
1000	21.33	24.97	19.93	17.38	1.05	0.64	28.44	13.12	2.12
1100	21.07	24.88	19.30	16.96	1.06	0.63	28.29	13.18	2.20
1200	20.84	24.80	18.79	16.56	1.06	0.62	28.21	13.08	2.13
1300	20.60	24.69	18.54	16.30	1.07	0.61	28.40	13.27	2.22
1400	20.36	24.60	18.27	15.96	1.07	0.59	28.02	13.31	2.20
1500	20.12	24.53	18.09	15.64	1.08	0.58	28.36	13.27	2.23
1600	19.88	24.41	17.87	15.48	1.08	0.57	28.53	13.25	2.23
1700	19.65	24.35	17.72	15.39	1.09	0.56	29.18	13.20	2.24
1800	19.41	24.29	17.52	15.37	1.10	0.55	29.04	13.28	2.22
1900	19.19	24.18	17.37	15.27	1.11	0.54	28.58	13.22	2.17
2000	18.97	24.10	17.58	15.19	1.12	0.53	28.80	13.29	2.17
2100	18.74	24.04	17.79	15.03	1.13	0.53	28.16	13.21	2.15
2200	18.53	24.00	17.74	14.98	1.14	0.52	28.45	13.19	2.11
2300	18.32	23.91	17.51	14.99	1.15	0.51	28.13	13.08	2.10
2400	18.09	23.86	17.31	15.00	1.17	0.50	28.14	13.07	2.05
2500	17.88	23.80	17.28	14.97	1.18	0.49	28.06	12.99	2.16
2600	17.68	23.74	17.37	14.96	1.19	0.49	27.67	12.68	2.11
2700	17.47	23.68	17.52	14.96	1.21	0.48	27.86	12.62	2.19
2800	17.28	23.63	17.42	15.04	1.22	0.47	27.20	12.28	2.10
2900	17.09	23.56	17.32	15.01	1.23	0.47	27.32	12.44	2.14
3000	16.90	23.53	17.26	15.07	1.25	0.46	26.93	11.98	2.22

REV. X1  
ERA-3SM+  
070816  
Page 4 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see





# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 28mA, Vd = 3.39V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	22.74	25.58	28.13	28.75	1.05	0.72	24.34	11.73	2.07
100	22.70	25.38	27.60	31.21	1.05	0.73	24.88	11.45	2.11
150	22.65	25.37	26.33	31.44	1.05	0.73	24.72	11.67	2.13
200	22.61	25.33	26.06	29.75	1.05	0.73	24.70	11.63	2.13
250	22.53	25.14	25.95	29.06	1.04	0.74	24.18	11.59	2.15
300	22.48	25.27	25.75	27.53	1.05	0.72	24.91	11.49	2.18
350	22.39	25.25	25.52	26.62	1.05	0.72	24.92	11.52	2.07
400	22.33	25.16	25.15	25.54	1.05	0.72	24.53	11.54	2.10
450	22.25	25.14	24.62	24.72	1.05	0.71	24.61	11.38	2.12
500	22.14	25.14	24.25	23.85	1.05	0.70	24.58	11.51	2.10
550	22.05	25.10	23.93	23.01	1.05	0.70	24.78	11.43	2.12
600	21.94	25.07	23.51	22.34	1.05	0.69	24.67	11.58	2.18
650	21.84	24.99	23.19	21.64	1.05	0.69	24.79	11.38	2.13
700	21.73	24.99	22.67	21.18	1.06	0.68	24.96	11.58	2.06
750	21.62	24.92	22.09	20.74	1.06	0.68	25.03	11.38	2.12
800	21.50	24.90	21.56	20.33	1.06	0.67	25.23	11.43	2.10
850	21.40	24.85	21.14	19.88	1.06	0.66	25.07	11.17	2.10
900	21.28	24.83	20.89	19.42	1.06	0.66	25.41	11.36	2.09
940	21.19	24.77	20.65	19.05	1.06	0.65	25.29	11.30	2.06
1000	21.05	24.72	20.25	18.70	1.06	0.64	25.37	11.30	2.09
1100	20.81	24.63	19.63	18.10	1.07	0.63	25.24	11.38	2.16
1200	20.59	24.58	19.13	17.62	1.07	0.62	25.17	11.22	2.10
1300	20.34	24.46	18.92	17.28	1.08	0.61	25.49	11.48	2.18
1400	20.11	24.40	18.63	16.83	1.08	0.60	25.22	11.48	2.18
1500	19.87	24.36	18.48	16.45	1.09	0.58	25.60	11.45	2.15
1600	19.65	24.28	18.26	16.22	1.10	0.57	25.80	11.45	2.18
1700	19.42	24.21	18.07	16.09	1.11	0.56	26.41	11.40	2.18
1800	19.19	24.12	17.82	15.99	1.11	0.55	26.50	11.44	2.17
1900	18.97	24.08	17.69	15.83	1.12	0.54	26.14	11.41	2.13
2000	18.76	23.99	17.91	15.71	1.13	0.53	26.59	11.46	2.13
2100	18.54	23.96	18.06	15.54	1.15	0.52	26.18	11.44	2.10
2200	18.33	23.88	17.96	15.43	1.16	0.52	26.53	11.50	2.08
2300	18.11	23.81	17.67	15.41	1.17	0.51	26.43	11.46	2.05
2400	17.89	23.79	17.48	15.37	1.18	0.50	26.51	11.62	2.01
2500	17.68	23.74	17.43	15.30	1.20	0.49	26.55	11.69	2.11
2600	17.49	23.69	17.44	15.25	1.21	0.48	26.18	11.55	2.05
2700	17.28	23.65	17.56	15.24	1.23	0.48	26.38	11.57	2.15
2800	17.09	23.60	17.42	15.28	1.24	0.47	25.85	11.29	2.05
2900	16.90	23.58	17.31	15.24	1.26	0.46	26.00	11.47	2.07
3000	16.71	23.50	17.21	15.28	1.27	0.46	25.66	11.08	2.15

REV. X1  
ERA-3SM+  
070816  
Page 5 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I<sub>cc</sub> = 42mA, V<sub>d</sub> = 3.45V @Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	23.32	25.90	33.29	20.71	1.04	0.74	30.15	14.36	2.19
100	23.28	25.88	34.25	21.28	1.04	0.74	30.69	14.46	2.21
150	23.24	25.89	33.00	21.48	1.04	0.74	30.65	14.49	2.20
200	23.18	25.81	30.02	21.11	1.04	0.74	30.59	14.50	2.19
250	23.10	25.81	28.16	20.90	1.04	0.73	29.83	14.57	2.23
300	23.03	25.81	26.84	20.32	1.04	0.73	30.84	14.60	2.30
350	22.95	25.78	25.69	20.04	1.04	0.72	30.71	14.44	2.13
400	22.87	25.73	24.87	19.71	1.04	0.72	30.30	14.39	2.18
450	22.78	25.70	24.18	19.40	1.04	0.71	30.27	14.50	2.17
500	22.68	25.60	23.47	19.07	1.04	0.71	30.21	14.53	2.18
550	22.57	25.61	23.02	18.70	1.04	0.70	30.40	14.51	2.21
600	22.46	25.54	22.61	18.45	1.04	0.70	30.15	14.57	2.24
650	22.35	25.48	22.34	18.11	1.04	0.69	30.26	14.57	2.21
700	22.23	25.46	21.90	17.91	1.05	0.68	30.38	14.51	2.15
750	22.12	25.39	21.30	17.66	1.05	0.68	30.45	14.39	2.18
800	22.00	25.33	20.82	17.47	1.05	0.67	30.57	14.38	2.16
850	21.88	25.30	20.35	17.22	1.05	0.66	30.38	14.39	2.16
900	21.76	25.23	20.00	16.96	1.05	0.66	30.60	14.30	2.20
940	21.66	25.21	19.75	16.73	1.05	0.65	30.45	14.24	2.13
1000	21.51	25.12	19.42	16.50	1.05	0.65	30.51	14.27	2.17
1100	21.25	25.03	18.83	16.16	1.05	0.63	30.28	14.26	2.22
1200	21.01	24.94	18.31	15.87	1.05	0.62	30.18	14.24	2.20
1300	20.77	24.83	18.12	15.68	1.06	0.61	30.15	14.38	2.28
1400	20.53	24.71	17.87	15.39	1.06	0.60	29.71	14.47	2.24
1500	20.28	24.64	17.68	15.12	1.07	0.58	30.02	14.30	2.26
1600	20.04	24.56	17.50	15.01	1.07	0.57	30.08	14.31	2.25
1700	19.81	24.45	17.39	14.97	1.08	0.56	30.65	14.28	2.26
1800	19.57	24.35	17.19	14.98	1.09	0.55	30.20	14.38	2.26
1900	19.34	24.28	17.05	14.88	1.10	0.54	29.76	14.25	2.18
2000	19.12	24.18	17.26	14.83	1.11	0.54	29.83	14.35	2.18
2100	18.90	24.12	17.47	14.70	1.12	0.53	29.13	14.20	2.19
2200	18.68	24.05	17.49	14.68	1.13	0.52	29.24	14.10	2.15
2300	18.46	23.97	17.29	14.72	1.14	0.51	28.72	13.93	2.15
2400	18.23	23.90	17.15	14.76	1.15	0.50	28.82	13.81	2.10
2500	18.02	23.84	17.11	14.75	1.17	0.49	28.55	13.65	2.20
2600	17.82	23.75	17.21	14.77	1.18	0.49	28.30	13.25	2.17
2700	17.62	23.73	17.38	14.78	1.19	0.48	28.42	13.14	2.25
2800	17.42	23.66	17.33	14.88	1.21	0.48	27.83	12.79	2.14
2900	17.23	23.58	17.25	14.90	1.22	0.47	27.97	12.96	2.17
3000	17.03	23.50	17.22	14.95	1.23	0.47	27.47	12.51	2.27

REV. X1  
ERA-3SM+  
070816  
Page 6 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I<sub>cc</sub> = 35mA, V<sub>d</sub> = 3.12V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	22.78	25.50	34.44	25.22	1.05	0.73	26.54	12.44	2.91
100	22.72	25.45	35.14	25.21	1.05	0.73	27.14	12.46	2.96
150	22.68	25.45	33.56	24.49	1.05	0.73	27.12	12.50	2.96
200	22.62	25.46	32.03	23.76	1.05	0.72	27.06	12.50	2.95
250	22.53	25.42	31.24	23.33	1.05	0.72	26.28	12.58	2.99
300	22.46	25.45	30.08	23.03	1.05	0.71	27.22	12.44	3.02
350	22.38	25.39	28.58	22.94	1.05	0.70	27.05	12.36	2.94
400	22.30	25.35	27.19	22.61	1.05	0.70	26.57	12.34	2.98
450	22.19	25.32	25.87	22.39	1.06	0.69	26.51	12.37	2.98
500	22.08	25.27	24.95	21.86	1.06	0.69	26.42	12.33	2.96
550	21.98	25.27	24.09	21.40	1.06	0.68	26.56	12.46	3.04
600	21.86	25.19	23.45	20.94	1.06	0.68	26.37	12.42	3.06
650	21.75	25.12	22.92	20.47	1.06	0.67	26.45	12.44	3.05
700	21.62	25.08	22.36	20.16	1.06	0.66	26.57	12.32	2.98
750	21.50	25.07	21.71	19.82	1.06	0.65	26.63	12.30	2.99
800	21.38	25.00	21.14	19.54	1.06	0.65	26.73	12.18	3.01
850	21.27	24.95	20.57	19.37	1.07	0.64	26.57	12.17	3.02
900	21.13	24.91	20.15	19.07	1.07	0.64	26.79	12.12	3.02
940	21.04	24.88	19.81	18.84	1.07	0.63	26.65	12.00	2.98
1000	20.88	24.81	19.36	18.55	1.07	0.62	26.66	12.09	3.01
1100	20.63	24.76	18.87	18.05	1.08	0.61	26.46	12.08	3.09
1200	20.37	24.65	18.42	17.56	1.08	0.60	26.32	11.95	3.03
1300	20.12	24.58	18.10	17.33	1.09	0.58	26.35	12.12	3.15
1400	19.87	24.50	17.81	17.03	1.10	0.57	25.91	12.17	3.13
1500	19.61	24.42	17.76	16.70	1.11	0.56	26.09	11.96	3.15
1600	19.36	24.34	17.62	16.37	1.12	0.55	26.24	11.88	3.15
1700	19.12	24.30	17.64	16.24	1.13	0.53	26.74	11.77	3.13
1800	18.87	24.20	17.65	16.11	1.14	0.53	26.40	11.94	3.17
1900	18.64	24.14	17.60	15.90	1.15	0.52	25.92	11.73	3.06
2000	18.40	24.10	17.70	15.68	1.17	0.51	25.91	11.84	3.12
2100	18.17	24.03	17.76	15.55	1.18	0.50	25.36	11.65	3.12
2200	17.94	23.98	17.70	15.50	1.20	0.49	25.35	11.59	3.04
2300	17.71	23.97	17.58	15.43	1.21	0.48	25.04	11.37	3.11
2400	17.48	23.88	17.53	15.34	1.23	0.47	24.94	11.19	3.01
2500	17.24	23.88	17.32	15.26	1.25	0.46	24.79	11.10	3.17
2600	17.06	23.79	17.22	15.41	1.26	0.46	24.45	10.70	3.07
2700	16.84	23.75	17.12	15.49	1.28	0.45	24.49	10.62	3.21
2800	16.63	23.75	17.01	15.52	1.30	0.44	24.02	10.18	3.11
2900	16.43	23.65	16.92	15.53	1.31	0.44	23.96	10.42	3.10
3000	16.22	23.64	16.85	15.61	1.33	0.43	23.62	9.81	3.26

REV. X1  
ERA-3SM+  
070816  
Page 7 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: I<sub>cc</sub> = 28mA, V<sub>d</sub> = 3.09V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	22.34	24.92	24.66	38.63	1.04	0.74	23.76	11.00	2.85
100	22.28	24.94	25.71	37.49	1.04	0.74	24.33	10.95	2.91
150	22.23	25.01	26.13	33.92	1.05	0.73	24.32	11.14	2.92
200	22.18	24.97	26.18	30.96	1.05	0.72	24.25	11.15	2.94
250	22.10	24.98	26.20	29.95	1.05	0.72	23.55	11.07	2.95
300	22.04	24.98	25.30	28.79	1.05	0.71	24.38	10.97	2.99
350	21.94	24.94	24.85	27.98	1.06	0.71	24.27	10.98	2.91
400	21.87	24.90	24.02	27.01	1.06	0.70	23.80	10.95	2.97
450	21.78	24.88	23.27	26.25	1.06	0.70	23.79	10.84	2.96
500	21.67	24.88	23.00	25.43	1.06	0.69	23.70	10.92	2.94
550	21.57	24.85	22.43	24.51	1.06	0.68	23.86	10.97	2.94
600	21.45	24.81	22.18	23.77	1.06	0.68	23.73	11.08	3.01
650	21.35	24.79	21.80	23.06	1.07	0.67	23.81	10.90	3.01
700	21.24	24.69	21.52	22.57	1.07	0.67	23.94	10.93	2.93
750	21.13	24.66	21.04	22.10	1.07	0.66	24.00	10.82	2.96
800	21.00	24.66	20.56	21.67	1.07	0.65	24.16	10.77	2.94
850	20.90	24.62	20.12	21.26	1.07	0.64	24.02	10.62	2.96
900	20.77	24.57	19.81	20.92	1.08	0.64	24.30	10.75	2.99
940	20.68	24.56	19.53	20.52	1.08	0.63	24.21	10.65	2.95
1000	20.53	24.51	19.15	20.13	1.08	0.62	24.23	10.65	2.96
1100	20.28	24.47	18.72	19.39	1.09	0.61	24.06	10.72	3.05
1200	20.05	24.39	18.35	18.81	1.09	0.60	23.98	10.54	3.01
1300	19.79	24.33	18.09	18.50	1.10	0.58	24.18	10.79	3.10
1400	19.55	24.27	17.85	18.11	1.11	0.57	23.84	10.74	3.04
1500	19.31	24.19	17.81	17.64	1.12	0.56	24.09	10.68	3.12
1600	19.06	24.14	17.68	17.26	1.13	0.55	24.31	10.61	3.10
1700	18.83	24.08	17.67	17.03	1.14	0.54	24.87	10.52	3.10
1800	18.58	24.04	17.65	16.83	1.16	0.52	24.80	10.68	3.13
1900	18.37	23.98	17.58	16.52	1.17	0.52	24.33	10.52	3.01
2000	18.13	23.91	17.62	16.27	1.18	0.51	24.54	10.65	3.08
2100	17.91	23.89	17.58	16.11	1.20	0.50	24.03	10.51	3.04
2200	17.68	23.88	17.50	16.01	1.22	0.49	24.14	10.53	3.02
2300	17.46	23.77	17.32	15.91	1.23	0.48	23.94	10.31	3.05
2400	17.23	23.76	17.25	15.76	1.25	0.47	23.89	10.32	2.95
2500	17.00	23.78	17.01	15.63	1.27	0.46	23.76	10.28	3.05
2600	16.81	23.70	16.86	15.73	1.28	0.46	23.41	9.90	2.98
2700	16.60	23.67	16.72	15.78	1.30	0.45	23.46	9.86	3.16
2800	16.39	23.67	16.59	15.78	1.32	0.44	23.02	9.44	3.08
2900	16.19	23.61	16.50	15.79	1.34	0.43	22.99	9.69	3.05
3000	15.99	23.63	16.44	15.83	1.36	0.42	22.77	9.05	3.23

REV. X1  
ERA-3SM+  
070816  
Page 8 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# MMIC Amplifier

# ERA-3SM+

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Icc = 42mA, Vd = 3.14V @Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP3 Output	1dB Comp. Output	Noise Figure
					K	Delta			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Delta	(dBm)	(dBm)	(dB)
50	23.07	28.99	13.28	2.96	1.06	0.71	28.99	13.28	2.96
100	23.01	29.60	13.42	2.99	1.05	0.72	29.60	13.42	2.99
150	22.96	29.67	13.36	3.02	1.05	0.72	29.67	13.36	3.02
200	22.89	29.48	13.33	3.02	1.05	0.73	29.48	13.33	3.02
250	22.81	28.53	13.47	3.04	1.05	0.71	28.53	13.47	3.04
300	22.73	29.54	13.39	3.07	1.05	0.72	29.54	13.39	3.07
350	22.64	29.30	13.28	2.98	1.05	0.70	29.30	13.28	2.98
400	22.56	28.80	13.21	3.02	1.05	0.71	28.80	13.21	3.02
450	22.46	28.62	13.33	3.06	1.05	0.70	28.62	13.33	3.06
500	22.34	28.48	13.22	3.01	1.05	0.69	28.48	13.22	3.01
550	22.23	28.53	13.32	3.05	1.05	0.68	28.53	13.32	3.05
600	22.12	28.22	13.26	3.09	1.06	0.68	28.22	13.26	3.09
650	22.00	28.24	13.37	3.08	1.06	0.67	28.24	13.37	3.08
700	21.87	28.28	13.08	3.02	1.06	0.66	28.28	13.08	3.02
750	21.75	28.26	13.10	3.06	1.06	0.66	28.26	13.10	3.06
800	21.62	28.22	12.91	3.06	1.06	0.65	28.22	12.91	3.06
850	21.50	28.07	13.05	3.07	1.06	0.64	28.07	13.05	3.07
900	21.37	28.09	12.80	3.09	1.06	0.64	28.09	12.80	3.09
940	21.27	27.95	12.72	2.99	1.06	0.63	27.95	12.72	2.99
1000	21.10	27.85	12.79	3.02	1.07	0.62	27.85	12.79	3.02
1100	20.84	27.57	12.70	3.16	1.07	0.61	27.57	12.70	3.16
1200	20.59	27.39	12.65	3.07	1.07	0.60	27.39	12.65	3.07
1300	20.32	27.19	12.71	3.20	1.08	0.58	27.19	12.71	3.20
1400	20.07	26.73	12.86	3.16	1.09	0.57	26.73	12.86	3.16
1500	19.81	26.86	12.48	3.22	1.10	0.56	26.86	12.48	3.22
1600	19.55	26.85	12.43	3.21	1.11	0.55	26.85	12.43	3.21
1700	19.30	27.12	12.35	3.17	1.12	0.54	27.12	12.35	3.17
1800	19.06	26.56	12.50	3.20	1.13	0.53	26.56	12.50	3.20
1900	18.82	26.17	12.26	3.13	1.14	0.52	26.17	12.26	3.13
2000	18.58	26.04	12.39	3.18	1.15	0.51	26.04	12.39	3.18
2100	18.35	25.47	12.20	3.16	1.17	0.50	25.47	12.20	3.16
2200	18.12	25.47	12.12	3.09	1.18	0.49	25.47	12.12	3.09
2300	17.89	25.09	11.78	3.14	1.20	0.48	25.09	11.78	3.14
2400	17.65	24.97	11.65	3.04	1.21	0.48	24.97	11.65	3.04
2500	17.42	24.80	11.54	3.24	1.23	0.46	24.80	11.54	3.24
2600	17.23	24.49	11.03	3.09	1.25	0.46	24.49	11.03	3.09
2700	17.01	24.48	10.96	3.25	1.26	0.45	24.48	10.96	3.25
2800	16.80	24.04	10.49	3.17	1.28	0.44	24.04	10.49	3.17
2900	16.60	23.98	10.83	3.19	1.29	0.44	23.98	10.83	3.19
3000	16.39	23.69	10.18	3.33	1.32	0.43	23.69	10.18	3.33

REV. X1  
ERA-3SM+  
070816  
Page 9 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


**GAIN vs. TEMPERATURE**




**GAIN vs. CURRENT**




**ISOLATION vs. TEMPERATURE**




**ISOLATION vs. CURRENT**




**INPUT RETURN LOSS vs. TEMPERATURE**




**INPUT RETURN LOSS vs. CURRENT**



**OUTPUT RETURN LOSS vs. TEMPERATURE**



**OUTPUT RETURN LOSS vs. CURRENT**



REV. X1

ERA-3SM+

070816

Page 10 of 11



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Typical Performance Curves


**OUTPUT IP3 vs. TEMPERATURE**

INPUT POWER = -25dBm, CURRENT = 35mA




**OUTPUT IP3 vs. CURRENT**

INPUT POWER = -25dBm, Temperature = +25°C




**OUTPUT POWER at 1dB Compression vs. TEMPERATURE**

CURRENT = 35mA




**OUTPUT POWER at 1dB Compression vs. CURRENT**

Temperature = +25°C




**Noise Figure vs. TEMPERATURE**

CURRENT = 35mA




**Noise Figure vs. CURRENT**

Temperature = +25°C




## Typical Performance Curves


**GAIN vs. TEMPERATURE**




**GAIN vs. CURRENT**




**ISOLATION vs. TEMPERATURE**




**ISOLATION vs. CURRENT**




**INPUT RETURN LOSS vs. TEMPERATURE**




**INPUT RETURN LOSS vs. CURRENT**



**OUTPUT RETURN LOSS vs. TEMPERATURE**



**OUTPUT RETURN LOSS vs. CURRENT**



REV. X1  
ERA-3SM+  
070816  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see






## Typical Performance Curves


**OUTPUT IP3 vs. TEMPERATURE**

INPUT POWER = -25dBm, CURRENT = 35mA




**OUTPUT IP3 vs. CURRENT**

INPUT POWER = -25dBm, Temperature = +25°C




**OUTPUT POWER at 1dB Compression vs. TEMPERATURE**

CURRENT = 35mA




**OUTPUT POWER at 1dB Compression vs. CURRENT**

Temperature = +25°C




**Noise Figure vs. TEMPERATURE**

CURRENT = 35mA




**Noise Figure vs. CURRENT**


Temperature = +25°C



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAMS
WW107	.012 (0.30)	.10 (2.54)	.020 (0.51)	.092 (2.34)	.085 (2.16)	.060 (1.52)	.007 (0.18)	.026 (0.66)	.235 (5.97)	.118 (3.00)	.235 (5.97)	.118 (3.00)	.072 (1.83)	.040 (1.02)	.020 (0.51)	.015

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Matte tin Plate.  
For RoHS-5 Case Styles: Tin-Lead plate.
- RF input termination (1) identified by one or both of the following at factory option:
  - diagonally cut termination, which may be  $45^\circ$  (ref) in either direction;
  - orientation mark on the case. Model dash number is identified by color dot or alphanumeric code on case. See specification data sheet.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-1

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F4

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		7	Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M100215	ADDED "PACKAGE OUTLINE" & UPDATED NOTES	08/12/05	MMG	MM
B	M100944	REMOVED AF190 & UPDATED NOTES	09/23/05	GT	MM
C	M102713	ADDED "...WITH SMOBC"	01/14/06	GF	IL
D	M108434	UPDATED DRAWING PER TB-408+	11/14/06	PW	IG

SUGGESTED MOUNTING CONFIGURATION FOR WW107 CASE STYLE, "cb" PIN CONNECTION



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. IF PCB DESIGN RULES ALLOW, PLACE GROUND VIAS UNDER THE LAND PATTERN FOR BETTER RF PERFORMANCE. OTHERWISE PLACE GROUND VIAS AS CLOSE TO LAND PATTERN AS POSSIBLE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	07/18/02
TOLERANCES ON:	CHECKED LC	08/01/02
2 PL DECIMALS ±	APPROVED DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



**Mini-Circuits®**


13 Neptune Avenue  
Brooklyn NY 11235

PL, cb, WW107, ERA, TB-408-XX+


Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-075	D
FILE:	98PL075	SCALE: 8:1	SHEET: 1 OF 1

# Evaluation Board and Circuit



TB-408-3+



COMPONENT	VALUE
A1	ERA-3SM(+)
C1 (NOTE 4)	2400 pF
C2 (NOTE 4)	2400 pF
C3 (bypass)	0.1 uF
R1	249 Ohms, 0.75W
R2	2.21 Ohms, 0.25W
CHK	Mini-Circuits TCCH-80+

Schematic Diagram

**NOTE:**

1. Vcc voltage:  $+12 \pm 0.2V$ .
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.
4. Capacitors, C1 & C2 should be free of resonance up to the highest frequency specified.

Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 85°C or -40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
	monoethanolamine at 63°C to 70°C	