

High IP3


Frequency Mixer

HJK-251H+

Level 17 (LO Power +17 dBm) 40 to 250 MHz

The Big Deal

- Low conversion loss, 7.0 dB typ.
- High IP3, 32 dBm typ.
- Excellent L-R isolation, 50 dB typ.



CASE STYLE: TTT881

Product Overview

Mini-Circuits' HJK-251H+ is a surface mount, level 17 FET-based frequency mixer with an RF frequency range from 40 to 250 MHz, LO frequency range from 10 to 220 MHz, and IF frequency range from 10 to 90 MHz. Its double-balanced FET configuration achieves an outstanding combination of low conversion loss, low noise figure and high IP3 performance without the need for a DC bias current, ideal for sensitive receiver applications including base stations, mobile radio, radar, and more. The mixer comes housed in a miniature, shielded 6-lead package (0.38 x 0.5 x 0.23"), saving space in tight PCB layouts.

Key Features

| Feature | Advantages |
|---|---|
| High IP3, +32 dBm | Minimizes third order intermodulation products and improves dynamic range in demanding environments where multiple carriers may be present. |
| Excellent P1dB compression, +20 dBm typ. | Whereas the 1-dB compression point of a diode-based mixer is typically 4 to 6 dB lower than the LO power level, the 1-dB compression point of HJK-251H+ FET-based mixer is +20 dBm higher than the LO signal power. This results in excellent linearity and high dynamic range. |
| High isolation: <ul style="list-style-type: none">• L-R isolation, 50 dB• L-I isolation, 45 dB | Preserves signal integrity from input to output by reducing undesirable signal responses that can degrade system performance. |
| Low conversion loss, 7 dB | Low conversion loss results in higher output IP3 and better overall system dynamic range. |
| Small size (0.38 x 0.5 x 0.23") | Saves PCB real estate and accommodates crowded layouts. |

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High IP3

Frequency Mixer

Level 17 (LO Power +17 dBm) 40 to 250 MHz

HJK-251H+



Generic photo used for illustration purposes only

CASE STYLE: TTT881

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel |
|-----------|----------------------|
| 7" | 10, 20, 50, 100, 200 |
| 13" | 500 |

Maximum Ratings


| | |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| LO Power* | +19 dBm |
| RF Power | +20 dBm |

Permanent damage may occur if any of these limits are exceeded.
* Over temperature

Pad Connections

| | |
|--------|-------|
| LO | 2 |
| RF | 1 |
| IF | 3 |
| GROUND | 4,5,6 |


Outline Drawing



Outline Dimensions (inch)

| A | B | C | D | E | F | G | H | J | K |
|------|-------|-------|------|------|-------|-------|-------|-------|------|
| .38 | .50 | .23 | .020 | .075 | .250 | .425 | .187 | .050 | .050 |
| 9.65 | 12.70 | 5.84 | 0.51 | 1.91 | 6.35 | 10.80 | 4.75 | 1.27 | 1.27 |
| L | M | N | P | Q | R | S | T | wt. | |
| .070 | .270 | .540 | .060 | .095 | .445 | .208 | .415 | grams | |
| 1.78 | 6.86 | 13.72 | 1.52 | 2.41 | 11.30 | 5.28 | 10.54 | 0.8 | |

Demo Board MCL P/N: TB-12 Suggested PCB Layout (PL-079)



NOTE:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - THE USE OF SOLDER MASK OVER THE GROUND AREA UNDER THE UNIT AS SHOWN IS RECOMMENDED TO PREVENT POTENTIAL SHORTING. IF USER CHOOSES TO EXPOSE METAL UNDER THE ENTIRE UNIT GROUND PAD FOR IMPROVED GROUNDING, IT IS RECOMMENDED A SOLDER MASK DAM BE APPLIED AROUND EACH GROUND PAD TO ENSURE FILLET AND CONNECTION AT GROUND PADS.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER), SEE NOTE 2.
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- high IP3, 32 dBm typ.
- excellent L-R isolation, 50 dB typ.;
- L-I isolation, 45 dB typ.

Applications

- base stations
- amateur radio
- aeronautical
- mobile radio
- radar
- emergency


Electrical Specifications at 25°C

| Parameter | Min. | Typ. | Max. | Unit |
|------------------------------------|------|------|------|------|
| Frequency Range, RF | 40 | — | 250 | MHz |
| Frequency Range, LO | 10 | — | 220 | MHz |
| Frequency Range, IF | 10 | — | 90 | MHz |
| Conversion Loss | — | 7.0 | 8.5 | dB |
| LO to RF Isolation | 36 | 50 | — | dB |
| LO to IF Isolation | 32 | 45 | — | dB |
| IP3 | — | 32 | — | dBm |
| RF Input Power at 1 dB Compression | — | +20 | — | dBm |
| LO Power | — | +17 | +20 | dBm |

Typical Performance Data

| Frequency | | Conversion Loss (dB) | Isolation L-R | Isolation L-I | VSWR RF Port | VSWR LO Port | IP3 (dBm) |
|-----------|--------|----------------------|---------------|---------------|--------------|--------------|-----------|
| RF MHz | LO MHz | LO +17dBm | LO +17dBm | LO +17dBm | LO +17dBm | LO +17dBm | LO +17dBm |
| 40.10 | 10.10 | 6.52 | 65.14 | 64.99 | 2.40 | 2.19 | 36.56 |
| 52.10 | 22.10 | 6.66 | 65.97 | 59.83 | 2.36 | 2.23 | 33.25 |
| 64.10 | 34.10 | 6.81 | 63.22 | 56.26 | 2.30 | 2.27 | 34.75 |
| 79.10 | 49.10 | 7.02 | 60.32 | 52.67 | 2.30 | 2.33 | 34.43 |
| 91.10 | 61.10 | 7.05 | 57.80 | 50.17 | 2.27 | 2.39 | 39.59 |
| 106.10 | 76.10 | 6.93 | 56.82 | 48.33 | 2.24 | 2.50 | 35.00 |
| 118.10 | 88.10 | 6.82 | 56.80 | 47.71 | 2.20 | 2.59 | 33.89 |
| 130.10 | 100.10 | 6.78 | 55.93 | 47.18 | 2.18 | 2.70 | 33.58 |
| 145.10 | 115.10 | 6.77 | 54.76 | 46.40 | 2.13 | 2.82 | 32.73 |
| 157.10 | 127.10 | 6.86 | 53.76 | 45.29 | 2.13 | 2.93 | 32.58 |
| 172.10 | 142.10 | 7.00 | 52.76 | 44.04 | 2.08 | 3.04 | 33.52 |
| 184.10 | 154.10 | 7.05 | 52.05 | 43.57 | 2.05 | 3.12 | 33.10 |
| 196.10 | 166.10 | 7.04 | 52.05 | 43.50 | 2.03 | 3.18 | 30.97 |
| 211.10 | 181.10 | 6.99 | 52.45 | 43.72 | 1.99 | 3.25 | 30.11 |
| 223.10 | 193.10 | 6.95 | 52.57 | 43.65 | 1.95 | 3.28 | 29.58 |
| 238.10 | 208.10 | 6.90 | 52.53 | 43.42 | 2.01 | 3.31 | 30.89 |
| 250.10 | 220.10 | 6.92 | 52.06 | 42.97 | 1.95 | 3.31 | 32.31 |








Electrical Schematic



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M155381
ED-14451/4
HJK-251H+
WL/CP/AM
160304
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

HJK-251H+

Typical Performance Data

| RF (IN) (MHz) | LO (MHz) | CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB) | | | RF (IN) (MHz) | LO (MHz) | IP-3 INPUT (dBm) | | | RF (IN) (MHz) | LO (MHz) | COMPRESSION @RF IN=+20dBm (dB) | | |
|---------------|----------|--|------|------|---------------|----------|------------------|-------|-------|---------------|----------|--------------------------------|------|------|
| | | @LO (dBm) | | | | | @LO (dBm) | | | | | @LO (dBm) | | |
| | | +14 | +17 | +20 | | | +14 | +17 | +20 | | | +14 | +17 | +20 |
| 40.1 | 10.1 | 6.60 | 6.52 | 6.46 | 40.1 | 10.1 | 34.86 | 38.45 | 41.82 | 40.1 | 10.1 | 0.28 | 0.12 | 0.08 |
| 52.1 | 22.1 | 6.70 | 6.66 | 6.59 | 52.1 | 22.1 | 33.64 | 34.87 | 32.92 | 52.1 | 22.1 | 0.35 | 0.13 | 0.06 |
| 64.1 | 34.1 | 6.91 | 6.81 | 6.76 | 64.1 | 34.1 | 31.76 | 34.66 | 36.86 | 64.1 | 34.1 | 0.36 | 0.20 | 0.09 |
| 79.1 | 49.1 | 7.10 | 7.02 | 6.99 | 79.1 | 49.1 | 31.83 | 35.07 | 39.42 | 79.1 | 49.1 | 0.30 | 0.14 | 0.05 |
| 91.1 | 61.1 | 7.12 | 7.05 | 7.02 | 91.1 | 61.1 | 32.41 | 39.88 | 36.28 | 91.1 | 61.1 | 0.30 | 0.14 | 0.06 |
| 106.1 | 76.1 | 7.00 | 6.93 | 6.88 | 106.1 | 76.1 | 34.46 | 34.95 | 36.79 | 106.1 | 76.1 | 0.33 | 0.16 | 0.10 |
| 118.1 | 88.1 | 6.91 | 6.82 | 6.78 | 118.1 | 88.1 | 34.12 | 33.76 | 36.29 | 118.1 | 88.1 | 0.34 | 0.17 | 0.07 |
| 130.1 | 100.1 | 6.88 | 6.78 | 6.70 | 130.1 | 100.1 | 35.29 | 33.03 | 35.15 | 130.1 | 100.1 | 0.37 | 0.16 | 0.08 |
| 145.1 | 115.1 | 6.86 | 6.77 | 6.70 | 145.1 | 115.1 | 32.00 | 32.47 | 34.83 | 145.1 | 115.1 | 0.49 | 0.22 | 0.11 |
| 157.1 | 127.1 | 6.94 | 6.86 | 6.77 | 157.1 | 127.1 | 31.07 | 32.36 | 35.50 | 157.1 | 127.1 | 0.45 | 0.20 | 0.11 |
| 172.1 | 142.1 | 7.08 | 7.00 | 6.91 | 172.1 | 142.1 | 31.10 | 33.05 | 36.47 | 172.1 | 142.1 | 0.37 | 0.15 | 0.08 |
| 184.1 | 154.1 | 7.15 | 7.05 | 6.98 | 184.1 | 154.1 | 30.72 | 33.32 | 35.55 | 184.1 | 154.1 | 0.48 | 0.21 | 0.11 |
| 196.1 | 166.1 | 7.14 | 7.04 | 6.96 | 196.1 | 166.1 | 28.91 | 30.87 | 34.35 | 196.1 | 166.1 | 0.58 | 0.26 | 0.12 |
| 211.1 | 181.1 | 7.10 | 6.99 | 6.90 | 211.1 | 181.1 | 28.11 | 30.38 | 33.89 | 211.1 | 181.1 | 0.69 | 0.29 | 0.15 |
| 223.1 | 193.1 | 7.07 | 6.95 | 6.86 | 223.1 | 193.1 | 27.55 | 29.45 | 32.55 | 223.1 | 193.1 | 0.88 | 0.35 | 0.16 |
| 238.1 | 208.1 | 7.03 | 6.90 | 6.80 | 238.1 | 208.1 | 28.19 | 30.87 | 33.31 | 238.1 | 208.1 | 1.04 | 0.42 | 0.20 |
| 250.1 | 220.1 | 7.04 | 6.92 | 6.82 | 250.1 | 220.1 | 29.22 | 32.12 | 34.71 | 250.1 | 220.1 | 0.91 | 0.36 | 0.18 |
| 262.1 | 232.1 | 7.16 | 7.03 | 6.93 | 262.1 | 232.1 | 28.12 | 30.89 | 33.08 | 262.1 | 232.1 | 1.00 | 0.37 | 0.17 |
| 277.1 | 247.1 | 7.27 | 7.13 | 7.04 | 277.1 | 247.1 | 27.18 | 29.30 | 31.23 | 277.1 | 247.1 | 1.46 | 0.51 | 0.21 |
| 289.1 | 259.1 | 7.30 | 7.16 | 7.05 | 289.1 | 259.1 | 26.60 | 28.76 | 31.13 | 289.1 | 259.1 | 1.70 | 0.60 | 0.26 |
| 304.1 | 274.1 | 7.34 | 7.19 | 7.05 | 304.1 | 274.1 | 26.49 | 28.75 | 31.07 | 304.1 | 274.1 | 2.35 | 0.85 | 0.33 |
| 316.1 | 286.1 | 7.36 | 7.19 | 7.05 | 316.1 | 286.1 | 26.03 | 28.62 | 31.69 | 316.1 | 286.1 | 3.00 | 1.25 | 0.40 |
| 331.1 | 301.1 | 7.32 | 7.16 | 7.03 | 331.1 | 301.1 | 24.37 | 27.19 | 32.19 | 331.1 | 301.1 | 3.06 | 1.31 | 0.40 |
| 343.1 | 313.1 | 7.40 | 7.23 | 7.10 | 343.1 | 313.1 | 23.69 | 26.59 | 31.07 | 343.1 | 313.1 | 3.01 | 1.29 | 0.38 |
| 355.1 | 325.1 | 7.57 | 7.41 | 7.28 | 355.1 | 325.1 | 22.96 | 25.93 | 30.24 | 355.1 | 325.1 | 3.59 | 1.71 | 0.46 |
| 370.1 | 340.1 | 7.69 | 7.53 | 7.39 | 370.1 | 340.1 | 21.36 | 23.49 | 25.81 | 370.1 | 340.1 | 4.27 | 2.27 | 0.73 |
| 382.1 | 352.1 | 7.76 | 7.59 | 7.45 | 382.1 | 352.1 | 20.11 | 21.64 | 23.31 | 382.1 | 352.1 | 4.55 | 2.58 | 0.96 |
| 397.1 | 367.1 | 7.88 | 7.69 | 7.56 | 397.1 | 367.1 | 19.28 | 20.32 | 21.54 | 397.1 | 367.1 | 5.32 | 3.26 | 1.46 |
| 409.1 | 379.1 | 7.78 | 7.56 | 7.38 | 409.1 | 379.1 | 19.19 | 20.48 | 22.01 | 409.1 | 379.1 | 5.88 | 3.75 | 1.85 |
| 421.1 | 391.1 | 7.70 | 7.43 | 7.23 | 421.1 | 391.1 | 19.13 | 21.21 | 23.73 | 421.1 | 391.1 | 5.93 | 3.78 | 1.92 |
| 436.1 | 406.1 | 7.76 | 7.45 | 7.21 | 436.1 | 406.1 | 18.34 | 19.70 | 21.92 | 436.1 | 406.1 | 5.84 | 3.76 | 1.96 |
| 448.1 | 418.1 | 7.83 | 7.51 | 7.26 | 448.1 | 418.1 | 18.63 | 19.51 | 20.27 | 448.1 | 418.1 | 6.22 | 4.03 | 2.09 |
| 463.1 | 433.1 | 7.84 | 7.53 | 7.30 | 463.1 | 433.1 | 18.96 | 20.46 | 21.45 | 463.1 | 433.1 | 6.57 | 4.36 | 2.35 |
| 475.1 | 445.1 | 7.97 | 7.64 | 7.40 | 475.1 | 445.1 | 18.58 | 20.80 | 22.54 | 475.1 | 445.1 | 6.80 | 4.60 | 2.58 |
| 487.1 | 457.1 | 8.10 | 7.75 | 7.48 | 487.1 | 457.1 | 18.29 | 20.90 | 23.28 | 487.1 | 457.1 | 7.24 | 5.03 | 2.95 |
| 502.1 | 472.1 | 8.19 | 7.79 | 7.52 | 502.1 | 472.1 | 17.95 | 20.91 | 23.68 | 502.1 | 472.1 | 7.69 | 5.51 | 3.39 |
| 514.1 | 484.1 | 8.24 | 7.84 | 7.55 | 514.1 | 484.1 | 17.48 | 20.36 | 23.43 | 514.1 | 484.1 | 7.61 | 5.43 | 3.35 |
| 529.1 | 499.1 | 8.35 | 7.93 | 7.60 | 529.1 | 499.1 | 17.30 | 20.19 | 23.57 | 529.1 | 499.1 | 7.64 | 5.45 | 3.35 |
| 541.1 | 511.1 | 8.41 | 7.94 | 7.64 | 541.1 | 511.1 | 17.15 | 19.99 | 23.57 | 541.1 | 511.1 | 7.59 | 5.35 | 3.25 |
| 556.1 | 526.1 | 8.62 | 8.14 | 7.81 | 556.1 | 526.1 | 16.45 | 19.01 | 22.28 | 556.1 | 526.1 | 7.63 | 5.45 | 3.44 |

Frequency Mixer

HJK-251H+

Typical Performance Data

| IF (OUT) (MHz) | LO (MHz) | CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=182.1MHz (dB) |
|----------------|----------|--|
| | | @LO (dBm) |
| | | +17 |
| 172.0 | 10.1 | 6.91 |
| 164.0 | 18.1 | 6.92 |
| 156.0 | 26.1 | 6.93 |
| 148.0 | 34.1 | 6.98 |
| 139.0 | 43.1 | 7.05 |
| 131.0 | 51.1 | 7.03 |
| 123.0 | 59.1 | 7.02 |
| 115.0 | 67.1 | 7.01 |
| 106.0 | 76.1 | 7.07 |
| 98.0 | 84.1 | 7.04 |
| 89.0 | 93.1 | 6.91 |
| 81.0 | 101.1 | 6.93 |
| 72.0 | 110.1 | 7.06 |
| 64.0 | 118.1 | 7.08 |
| 56.0 | 126.1 | 7.12 |
| 48.0 | 134.1 | 7.08 |
| 39.0 | 143.1 | 7.08 |
| 31.0 | 151.1 | 7.07 |
| 23.0 | 159.1 | 7.09 |
| 15.0 | 167.1 | 7.21 |
| 10.0 | 192.1 | 7.58 |
| 26.0 | 208.1 | 7.22 |
| 42.0 | 224.1 | 7.13 |
| 58.0 | 240.1 | 7.11 |
| 74.0 | 256.1 | 7.07 |
| 90.0 | 272.1 | 7.06 |
| 106.0 | 288.1 | 7.30 |
| 122.0 | 304.1 | 7.26 |
| 138.0 | 320.1 | 7.39 |
| 154.0 | 336.1 | 7.34 |
| 170.0 | 352.1 | 7.34 |
| 186.0 | 368.1 | 7.52 |
| 202.0 | 384.1 | 7.53 |
| 218.0 | 400.1 | 7.52 |
| 234.0 | 416.1 | 7.61 |
| 250.0 | 432.1 | 7.65 |
| 266.0 | 448.1 | 7.70 |
| 282.0 | 464.1 | 7.82 |
| 298.0 | 480.1 | 7.81 |
| 314.0 | 496.1 | 7.93 |

| IF (OUT) (MHz) | LO (MHz) | CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=145.1MHz (dB) |
|----------------|----------|--|
| | | @LO (dBm) |
| | | +17 |
| 11.0 | 156.1 | 7.22 |
| 16.0 | 161.1 | 6.94 |
| 26.0 | 171.1 | 6.95 |
| 36.0 | 181.1 | 6.91 |
| 46.0 | 191.1 | 6.89 |
| 56.0 | 201.1 | 6.86 |
| 66.0 | 211.1 | 6.88 |
| 76.0 | 221.1 | 6.77 |
| 86.0 | 231.1 | 6.85 |
| 96.0 | 241.1 | 6.90 |
| 101.0 | 246.1 | 6.93 |
| 111.0 | 256.1 | 6.89 |
| 121.0 | 266.1 | 6.96 |
| 131.0 | 276.1 | 6.99 |
| 141.0 | 286.1 | 7.08 |
| 151.0 | 296.1 | 7.13 |
| 161.0 | 306.1 | 7.15 |
| 171.0 | 316.1 | 7.23 |
| 181.0 | 326.1 | 7.20 |
| 191.0 | 336.1 | 7.25 |
| 196.0 | 341.1 | 7.25 |
| 206.0 | 351.1 | 7.19 |
| 216.0 | 361.1 | 7.28 |
| 226.0 | 371.1 | 7.24 |
| 236.0 | 381.1 | 7.27 |
| 246.0 | 391.1 | 7.18 |
| 256.0 | 401.1 | 7.24 |
| 266.0 | 411.1 | 7.25 |
| 276.0 | 421.1 | 7.36 |
| 286.0 | 431.1 | 7.32 |
| 291.0 | 436.1 | 7.31 |
| 301.0 | 446.1 | 7.46 |
| 311.0 | 456.1 | 7.58 |
| 321.0 | 466.1 | 7.66 |
| 331.0 | 476.1 | 7.64 |
| 341.0 | 486.1 | 7.75 |
| 351.0 | 496.1 | 7.86 |
| 361.0 | 506.1 | 7.86 |
| 371.0 | 516.1 | 7.94 |
| 381.0 | 526.1 | 7.94 |

| IF (OUT) (MHz) | LO (MHz) | CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=220.1MHz (dB) |
|----------------|----------|--|
| | | @LO (dBm) |
| | | +17 |
| 210.0 | 10.1 | 6.72 |
| 206.0 | 14.1 | 6.73 |
| 200.0 | 20.1 | 6.73 |
| 196.0 | 24.1 | 6.75 |
| 190.0 | 30.1 | 6.76 |
| 186.0 | 34.1 | 6.76 |
| 180.0 | 40.1 | 6.84 |
| 176.0 | 44.1 | 6.85 |
| 170.0 | 50.1 | 6.86 |
| 166.0 | 54.1 | 6.87 |
| 160.0 | 60.1 | 6.86 |
| 156.0 | 64.1 | 6.86 |
| 150.0 | 70.1 | 6.88 |
| 144.0 | 76.1 | 6.89 |
| 140.0 | 80.1 | 6.87 |
| 134.0 | 86.1 | 6.87 |
| 130.0 | 90.1 | 6.87 |
| 124.0 | 96.1 | 6.90 |
| 120.0 | 100.1 | 6.91 |
| 114.0 | 106.1 | 6.93 |
| 108.0 | 112.1 | 6.80 |
| 102.0 | 118.1 | 6.82 |
| 98.0 | 122.1 | 6.83 |
| 92.0 | 128.1 | 6.90 |
| 88.0 | 132.1 | 6.88 |
| 82.0 | 138.1 | 6.90 |
| 76.0 | 144.1 | 6.93 |
| 72.0 | 148.1 | 6.93 |
| 66.0 | 154.1 | 6.93 |
| 62.0 | 158.1 | 6.95 |
| 56.0 | 164.1 | 6.93 |
| 52.0 | 168.1 | 6.95 |
| 46.0 | 174.1 | 6.98 |
| 42.0 | 178.1 | 6.97 |
| 36.0 | 184.1 | 7.02 |
| 32.0 | 188.1 | 7.01 |
| 26.0 | 194.1 | 7.02 |
| 22.0 | 198.1 | 7.01 |
| 16.0 | 204.1 | 7.05 |
| 10.0 | 210.1 | 7.43 |

Frequency Mixer

HJK-251H+

Typical Performance Data

| LO (MHz) | LO-RF ISOLATION (dB) | | | LO-IF ISOLATION (dB) | | |
|-------------|-------------------------|-------|-------|-------------------------|-------|-------|
| | @LO (dBm) | | | @LO (dBm) | | |
| | +14 | +17 | +20 | +14 | +17 | +20 |
| 10.1 | 72.66 | 65.14 | 79.51 | 65.44 | 64.99 | 65.48 |
| 22.1 | 65.16 | 65.97 | 66.75 | 59.60 | 59.83 | 59.98 |
| 34.1 | 64.80 | 63.22 | 64.21 | 56.37 | 56.26 | 56.36 |
| 49.1 | 60.03 | 60.32 | 61.05 | 52.62 | 52.67 | 52.89 |
| 61.1 | 57.70 | 57.80 | 58.35 | 50.16 | 50.17 | 50.69 |
| 76.1 | 56.87 | 56.82 | 57.45 | 48.34 | 48.33 | 48.68 |
| 88.1 | 56.48 | 56.80 | 56.88 | 47.72 | 47.71 | 47.83 |
| 100.1 | 55.56 | 55.93 | 55.74 | 47.20 | 47.18 | 47.22 |
| 115.1 | 54.42 | 54.76 | 54.78 | 46.42 | 46.40 | 46.40 |
| 127.1 | 53.37 | 53.76 | 53.80 | 45.32 | 45.29 | 45.29 |
| 142.1 | 52.35 | 52.76 | 52.75 | 44.08 | 44.04 | 44.02 |
| 154.1 | 51.74 | 52.05 | 52.11 | 43.63 | 43.57 | 43.56 |
| 166.1 | 52.00 | 52.05 | 52.21 | 43.57 | 43.50 | 43.49 |
| 181.1 | 52.28 | 52.45 | 52.50 | 43.80 | 43.72 | 43.71 |
| 193.1 | 52.36 | 52.57 | 52.62 | 43.75 | 43.65 | 43.63 |
| 208.1 | 52.23 | 52.53 | 52.65 | 43.48 | 43.42 | 43.37 |
| 220.1 | 52.00 | 52.06 | 52.18 | 43.08 | 42.97 | 42.94 |
| 232.1 | 51.24 | 51.28 | 51.38 | 42.82 | 42.72 | 42.66 |
| 247.1 | 51.31 | 51.35 | 51.42 | 43.06 | 42.96 | 42.91 |
| 259.1 | 51.87 | 51.88 | 52.05 | 43.44 | 43.33 | 43.28 |
| 274.1 | 51.79 | 51.79 | 51.83 | 43.89 | 43.76 | 43.68 |
| 286.1 | 51.20 | 51.23 | 51.34 | 43.96 | 43.79 | 43.72 |
| 301.1 | 51.03 | 50.93 | 51.03 | 43.66 | 43.48 | 43.37 |
| 313.1 | 50.76 | 50.59 | 50.63 | 43.44 | 43.23 | 43.11 |
| 325.1 | 50.60 | 50.33 | 50.26 | 43.35 | 43.13 | 42.99 |
| 340.1 | 51.36 | 51.18 | 51.22 | 43.65 | 43.39 | 43.23 |
| 352.1 | 52.64 | 52.35 | 52.30 | 44.04 | 43.78 | 43.59 |
| 367.1 | 55.07 | 54.75 | 54.63 | 44.64 | 44.33 | 44.13 |
| 379.1 | 57.50 | 57.88 | 58.38 | 44.99 | 44.69 | 44.47 |
| 391.1 | 58.49 | 58.54 | 58.36 | 45.49 | 45.14 | 44.88 |
| 406.1 | 58.23 | 57.96 | 57.68 | 45.94 | 45.52 | 45.23 |
| 418.1 | 58.00 | 57.49 | 56.89 | 46.67 | 46.24 | 45.93 |
| 433.1 | 56.92 | 56.24 | 55.54 | 47.70 | 47.24 | 46.91 |
| 445.1 | 55.91 | 55.18 | 54.51 | 48.95 | 48.41 | 48.00 |
| 457.1 | 55.36 | 54.61 | 53.91 | 50.25 | 49.70 | 49.25 |
| 472.1 | 54.40 | 53.58 | 52.93 | 51.63 | 50.87 | 50.30 |
| 484.1 | 55.28 | 54.40 | 53.66 | 53.10 | 52.30 | 51.60 |
| 499.1 | 52.54 | 51.74 | 51.11 | 56.20 | 54.83 | 53.67 |
| 511.1 | 53.01 | 52.11 | 51.55 | 58.13 | 56.09 | 54.49 |
| 526.1 | 52.01 | 51.20 | 50.65 | 59.78 | 57.09 | 55.11 |

| RF (IN) (MHz) | LO (MHz) | RF-IF ISOLATION (dB) | | |
|---------------------|-------------|-------------------------|-------|-------|
| | | @LO (dBm) | | |
| | | +14 | +17 | +20 |
| 40.1 | 10.1 | 52.94 | 49.44 | 54.77 |
| 52.1 | 22.1 | 47.18 | 46.47 | 47.96 |
| 64.1 | 34.1 | 62.29 | 63.24 | 64.83 |
| 79.1 | 49.1 | 57.41 | 57.81 | 58.57 |
| 91.1 | 61.1 | 56.91 | 55.65 | 56.49 |
| 106.1 | 76.1 | 54.34 | 50.47 | 55.49 |
| 118.1 | 88.1 | 58.29 | 57.94 | 58.21 |
| 130.1 | 100.1 | 54.32 | 54.50 | 54.22 |
| 145.1 | 115.1 | 54.76 | 52.78 | 50.88 |
| 157.1 | 127.1 | 53.78 | 53.50 | 53.82 |
| 172.1 | 142.1 | 52.82 | 53.53 | 53.00 |
| 184.1 | 154.1 | 52.79 | 51.92 | 50.23 |
| 196.1 | 166.1 | 53.11 | 52.41 | 51.61 |
| 211.1 | 181.1 | 48.23 | 49.41 | 49.47 |
| 223.1 | 193.1 | 48.46 | 48.76 | 48.88 |
| 238.1 | 208.1 | 48.26 | 48.27 | 48.11 |
| 250.1 | 220.1 | 46.69 | 46.87 | 46.61 |
| 262.1 | 232.1 | 48.30 | 48.56 | 48.96 |
| 277.1 | 247.1 | 50.44 | 50.77 | 51.75 |
| 289.1 | 259.1 | 49.07 | 49.84 | 50.04 |
| 304.1 | 274.1 | 46.57 | 47.19 | 47.77 |
| 316.1 | 286.1 | 45.64 | 45.68 | 46.19 |
| 331.1 | 301.1 | 43.19 | 43.24 | 42.88 |
| 343.1 | 313.1 | 40.97 | 40.97 | 40.72 |
| 355.1 | 325.1 | 39.56 | 39.07 | 38.88 |
| 370.1 | 340.1 | 37.15 | 36.67 | 36.20 |
| 382.1 | 352.1 | 35.60 | 34.92 | 34.44 |
| 397.1 | 367.1 | 36.00 | 35.74 | 35.51 |
| 409.1 | 379.1 | 35.62 | 35.45 | 34.50 |
| 421.1 | 391.1 | 35.45 | 35.72 | 35.60 |
| 436.1 | 406.1 | 35.84 | 36.05 | 36.02 |
| 448.1 | 418.1 | 35.63 | 35.90 | 35.90 |
| 463.1 | 433.1 | 35.02 | 35.14 | 35.30 |
| 475.1 | 445.1 | 33.86 | 33.77 | 33.52 |
| 487.1 | 457.1 | 33.06 | 32.91 | 32.33 |
| 502.1 | 472.1 | 31.73 | 31.30 | 30.97 |
| 514.1 | 484.1 | 30.30 | 29.67 | 29.10 |
| 529.1 | 499.1 | 28.79 | 27.97 | 27.58 |
| 541.1 | 511.1 | 27.97 | 27.25 | 26.86 |
| 556.1 | 526.1 | 27.00 | 26.04 | 25.43 |

Frequency Mixer

HJK-251H+

Typical Performance Data

| RF (IN) (MHz) | LO (MHz) | RF VSWR (:1) | | | LO (MHz) | LO VSWR (:1) | | | IF (OUT) (MHz) | IF VSWR @LO=190MHz (:1) | | |
|------------------|-------------|--------------|------|------|-------------|--------------|------|------|-------------------|-------------------------|------|------|
| | | @LO (dBm) | | | | @LO (dBm) | | | | @LO (dBm) | | |
| | | +14 | +17 | +20 | | +14 | +17 | +20 | | +14 | +17 | +20 |
| 40.1 | 10.1 | 2.37 | 2.40 | 2.43 | 10.1 | 2.17 | 2.19 | 1.77 | 10.1 | 1.60 | 1.47 | 1.75 |
| 52.1 | 22.1 | 2.31 | 2.36 | 2.40 | 22.1 | 2.21 | 2.23 | 1.89 | 12.1 | 1.58 | 1.66 | 1.56 |
| 64.1 | 34.1 | 2.26 | 2.30 | 2.35 | 34.1 | 2.26 | 2.27 | 2.10 | 16.1 | 1.57 | 1.57 | 1.55 |
| 79.1 | 49.1 | 2.26 | 2.30 | 2.35 | 49.1 | 2.31 | 2.33 | 2.05 | 20.1 | 1.60 | 1.49 | 1.46 |
| 91.1 | 61.1 | 2.21 | 2.27 | 2.31 | 61.1 | 2.38 | 2.39 | 1.98 | 24.1 | 1.56 | 1.53 | 1.45 |
| 106.1 | 76.1 | 2.19 | 2.24 | 2.28 | 76.1 | 2.49 | 2.50 | 2.20 | 28.1 | 1.50 | 1.51 | 1.51 |
| 118.1 | 88.1 | 2.17 | 2.20 | 2.26 | 88.1 | 2.58 | 2.59 | 2.51 | 32.1 | 1.55 | 1.51 | 1.53 |
| 130.1 | 100.1 | 2.14 | 2.18 | 2.23 | 100.1 | 2.69 | 2.70 | 2.68 | 36.1 | 1.53 | 1.52 | 1.50 |
| 145.1 | 115.1 | 2.08 | 2.13 | 2.17 | 115.1 | 2.81 | 2.82 | 2.82 | 40.1 | 1.52 | 1.47 | 1.47 |
| 157.1 | 127.1 | 2.09 | 2.13 | 2.17 | 127.1 | 2.92 | 2.93 | 2.92 | 44.1 | 1.48 | 1.46 | 1.42 |
| 172.1 | 142.1 | 2.04 | 2.08 | 2.13 | 142.1 | 3.04 | 3.04 | 3.04 | 48.1 | 1.46 | 1.47 | 1.43 |
| 184.1 | 154.1 | 2.01 | 2.05 | 2.10 | 154.1 | 3.12 | 3.12 | 3.11 | 52.1 | 1.47 | 1.48 | 1.41 |
| 196.1 | 166.1 | 1.99 | 2.03 | 2.07 | 166.1 | 3.18 | 3.18 | 3.18 | 56.1 | 1.48 | 1.43 | 1.43 |
| 211.1 | 181.1 | 1.94 | 1.99 | 2.02 | 181.1 | 3.25 | 3.25 | 3.24 | 60.1 | 1.47 | 1.45 | 1.42 |
| 223.1 | 193.1 | 1.91 | 1.95 | 1.99 | 193.1 | 3.28 | 3.28 | 3.27 | 62.1 | 1.51 | 1.48 | 1.44 |
| 238.1 | 208.1 | 1.96 | 2.01 | 2.05 | 208.1 | 3.30 | 3.31 | 3.30 | 66.1 | 1.57 | 1.52 | 1.51 |
| 250.1 | 220.1 | 1.90 | 1.95 | 2.00 | 220.1 | 3.31 | 3.31 | 3.30 | 70.1 | 1.52 | 1.49 | 1.46 |
| 262.1 | 232.1 | 1.89 | 1.94 | 1.98 | 232.1 | 3.31 | 3.31 | 3.30 | 74.1 | 1.50 | 1.48 | 1.44 |
| 277.1 | 247.1 | 1.87 | 1.92 | 1.97 | 247.1 | 3.28 | 3.28 | 3.27 | 78.1 | 1.51 | 1.48 | 1.46 |
| 289.1 | 259.1 | 1.83 | 1.88 | 1.93 | 259.1 | 3.25 | 3.25 | 3.25 | 82.1 | 1.52 | 1.49 | 1.47 |
| 304.1 | 274.1 | 1.80 | 1.84 | 1.89 | 274.1 | 3.21 | 3.21 | 3.21 | 86.1 | 1.53 | 1.49 | 1.46 |
| 316.1 | 286.1 | 1.78 | 1.82 | 1.86 | 286.1 | 3.18 | 3.18 | 3.17 | 90.1 | 1.51 | 1.49 | 1.45 |
| 331.1 | 301.1 | 1.71 | 1.74 | 1.78 | 301.1 | 3.12 | 3.12 | 3.12 | 94.1 | 1.51 | 1.49 | 1.46 |
| 343.1 | 313.1 | 1.70 | 1.73 | 1.76 | 313.1 | 3.08 | 3.08 | 3.08 | 98.1 | 1.53 | 1.49 | 1.46 |
| 355.1 | 325.1 | 1.67 | 1.69 | 1.71 | 325.1 | 3.04 | 3.04 | 3.03 | 102.1 | 1.53 | 1.51 | 1.47 |
| 370.1 | 340.1 | 1.62 | 1.63 | 1.64 | 340.1 | 2.96 | 2.96 | 2.95 | 106.1 | 1.53 | 1.50 | 1.48 |
| 382.1 | 352.1 | 1.65 | 1.65 | 1.66 | 352.1 | 2.91 | 2.91 | 2.90 | 110.1 | 1.55 | 1.53 | 1.51 |
| 397.1 | 367.1 | 1.67 | 1.67 | 1.68 | 367.1 | 2.85 | 2.84 | 2.83 | 112.1 | 1.54 | 1.52 | 1.50 |
| 409.1 | 379.1 | 1.70 | 1.71 | 1.73 | 379.1 | 2.80 | 2.79 | 2.78 | 116.1 | 1.54 | 1.51 | 1.49 |
| 421.1 | 391.1 | 1.75 | 1.77 | 1.79 | 391.1 | 2.77 | 2.76 | 2.75 | 120.1 | 1.56 | 1.51 | 1.50 |
| 436.1 | 406.1 | 1.83 | 1.85 | 1.88 | 406.1 | 2.72 | 2.71 | 2.70 | 124.1 | 1.54 | 1.51 | 1.48 |
| 448.1 | 418.1 | 1.85 | 1.88 | 1.92 | 418.1 | 2.69 | 2.68 | 2.67 | 128.1 | 1.51 | 1.49 | 1.47 |
| 463.1 | 433.1 | 1.91 | 1.95 | 2.00 | 433.1 | 2.65 | 2.65 | 2.64 | 132.1 | 1.49 | 1.48 | 1.46 |
| 475.1 | 445.1 | 1.94 | 1.99 | 2.05 | 445.1 | 2.62 | 2.61 | 2.60 | 136.1 | 1.50 | 1.47 | 1.44 |
| 487.1 | 457.1 | 1.95 | 2.01 | 2.08 | 457.1 | 2.58 | 2.58 | 2.57 | 140.1 | 1.48 | 1.46 | 1.44 |
| 502.1 | 472.1 | 2.00 | 2.05 | 2.12 | 472.1 | 2.54 | 2.54 | 2.53 | 144.1 | 1.49 | 1.46 | 1.43 |
| 514.1 | 484.1 | 2.04 | 2.10 | 2.17 | 484.1 | 2.50 | 2.50 | 2.49 | 148.1 | 1.50 | 1.48 | 1.44 |
| 529.1 | 499.1 | 2.06 | 2.13 | 2.20 | 499.1 | 2.47 | 2.46 | 2.46 | 152.1 | 1.52 | 1.49 | 1.46 |
| 541.1 | 511.1 | 2.11 | 2.18 | 2.25 | 511.1 | 2.43 | 2.43 | 2.42 | 156.1 | 1.54 | 1.52 | 1.48 |
| 556.1 | 526.1 | 2.13 | 2.20 | 2.27 | 526.1 | 2.39 | 2.39 | 2.38 | 160.1 | 1.54 | 1.51 | 1.49 |

Harmonics Tables

RF HARMONICS ORDER

| | (-dBm) | (-dBc) | | | | | | | | | | |
|----|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0 | --- | --- | 17.16 | 35.04 | 43.12 | 41.75 | 38.25 | 33.50 | 42.64 | 35.38 | 51.62 | 39.99 |
| 1 | --- | 44.24 | --- | 60.75 | 9.90 | 61.44 | 15.41 | 54.30 | 19.01 | 67.21 | 24.50 | 72.62 |
| 2 | 104.19 | 55.42 | 62.67 | 57.33 | 85.33 | 57.51 | 68.55 | 55.62 | 67.47 | 54.54 | 71.45 | 56.28 |
| 3 | 112.54 | 78.77 | 78.21 | 81.76 | 70.12 | 80.53 | 67.36 | 79.80 | 61.06 | 79.18 | 60.42 | 78.28 |
| 4 | 121.67 | 89.49 | 95.69 | 90.84 | 97.46 | 90.63 | 116.04 | 94.52 | 97.23 | 87.71 | 92.86 | 85.19 |
| 5 | 121.38 | 88.98 | 84.53 | 89.35 | 81.22 | 89.37 | 86.89 | 89.85 | 86.90 | 89.39 | 80.60 | 88.44 |
| 6 | 120.63 | 100.59 | 115.09 | 97.42 | 115.19 | 94.42 | 114.46 | 90.24 | 105.37 | 102.10 | 110.63 | 103.41 |
| 7 | 122.71 | 104.72 | 92.65 | 101.92 | 90.14 | 101.92 | 89.61 | 100.88 | 90.87 | 102.93 | 90.90 | 102.46 |
| 8 | 122.31 | 118.46 | 116.92 | 113.45 | 115.31 | 107.74 | 117.71 | 103.91 | 115.81 | 94.37 | 117.37 | 95.72 |
| 9 | 121.37 | 115.06 | 109.70 | 115.56 | 104.28 | 112.74 | 105.14 | 114.09 | 101.68 | 110.57 | 99.85 | 114.33 |
| 10 | 121.61 | 117.97 | 117.84 | 115.84 | 119.32 | 118.28 | 115.01 | 117.40 | 116.19 | 118.49 | 116.82 | 113.37 |
| | RF CAL | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |

LO HARMONICS ORDER

Test conditions: RF IN: 183 MHz; 0 dBm.
 LO IN: 153 MHz; +17.00 dBm
 IF OUT: 30 MHz; - 7.06 dBm

RF HARMONICS ORDER








| | (-dBm) | (-dBc) | | | | | | | | | | |
|----|--------|--------|--------|--------|--------|--------|-------|-------|-------|--------|-------|--------|
| 0 | --- | --- | 21.10 | 28.50 | 41.10 | 39.13 | 43.08 | 38.87 | 50.06 | 41.73 | 64.38 | 44.81 |
| 1 | --- | 30.34 | --- | 49.77 | 10.11 | 55.83 | 15.97 | 52.68 | 20.36 | 76.89 | 26.59 | 69.31 |
| 2 | 93.53 | 45.66 | 50.51 | 46.77 | 58.16 | 47.37 | 57.40 | 47.06 | 62.36 | 47.41 | 72.41 | 51.43 |
| 3 | 103.31 | 72.32 | 56.63 | 74.11 | 50.90 | 73.81 | 47.66 | 71.80 | 43.74 | 70.21 | 42.51 | 81.52 |
| 4 | 107.59 | 68.35 | 67.68 | 69.64 | 65.20 | 71.54 | 66.62 | 70.59 | 64.77 | 65.55 | 65.90 | 63.39 |
| 5 | 105.17 | 84.32 | 68.45 | 85.14 | 75.46 | 84.50 | 67.95 | 84.45 | 65.32 | 82.27 | 69.65 | 80.76 |
| 6 | 106.43 | 78.97 | 86.02 | 80.81 | 82.47 | 80.38 | 82.00 | 84.91 | 82.49 | 86.88 | 80.49 | 82.69 |
| 7 | 106.21 | 87.81 | 77.24 | 86.22 | 80.64 | 87.78 | 81.17 | 86.28 | 79.09 | 85.70 | 80.05 | 85.11 |
| 8 | 106.72 | 92.20 | 104.83 | 90.77 | 115.60 | 89.82 | 99.99 | 89.83 | 99.49 | 94.36 | 97.50 | 93.15 |
| 9 | 106.96 | 96.19 | 86.01 | 94.03 | 85.12 | 91.36 | 79.96 | 91.52 | 83.44 | 90.65 | 82.97 | 90.15 |
| 10 | 107.62 | 109.13 | 101.78 | 110.74 | 99.69 | 106.38 | 96.15 | 99.92 | 97.74 | 100.29 | 97.03 | 105.82 |
| | RF CAL | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |

LO HARMONICS ORDER







Test conditions: RF IN: 183 MHz; 10 dBm.
 LO IN: 153 MHz; +17.00 dBm
 IF OUT: 30 MHz; 2.73 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT
 3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

Typical Performance Curves



Typical Performance Curves



Harmonics Tables

RF HARMONICS ORDER

| | (-dBm) | (-dBc) | | | | | | | | | | |
|----|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0 | --- | --- | 17.16 | 35.04 | 43.12 | 41.75 | 38.25 | 33.50 | 42.64 | 35.38 | 51.62 | 39.99 |
| 1 | --- | 44.24 | --- | 60.75 | 9.90 | 61.44 | 15.41 | 54.30 | 19.01 | 67.21 | 24.50 | 72.62 |
| 2 | 104.19 | 55.42 | 62.67 | 57.33 | 85.33 | 57.51 | 68.55 | 55.62 | 67.47 | 54.54 | 71.45 | 56.28 |
| 3 | 112.54 | 78.77 | 78.21 | 81.76 | 70.12 | 80.53 | 67.36 | 79.80 | 61.06 | 79.18 | 60.42 | 78.28 |
| 4 | 121.67 | 89.49 | 95.69 | 90.84 | 97.46 | 90.63 | 116.04 | 94.52 | 97.23 | 87.71 | 92.86 | 85.19 |
| 5 | 121.38 | 88.98 | 84.53 | 89.35 | 81.22 | 89.37 | 86.89 | 89.85 | 86.90 | 89.39 | 80.60 | 88.44 |
| 6 | 120.63 | 100.59 | 115.09 | 97.42 | 115.19 | 94.42 | 114.46 | 90.24 | 105.37 | 102.10 | 110.63 | 103.41 |
| 7 | 122.71 | 104.72 | 92.65 | 101.92 | 90.14 | 101.92 | 89.61 | 100.88 | 90.87 | 102.93 | 90.90 | 102.46 |
| 8 | 122.31 | 118.46 | 116.92 | 113.45 | 115.31 | 107.74 | 117.71 | 103.91 | 115.81 | 94.37 | 117.37 | 95.72 |
| 9 | 121.37 | 115.06 | 109.70 | 115.56 | 104.28 | 112.74 | 105.14 | 114.09 | 101.68 | 110.57 | 99.85 | 114.33 |
| 10 | 121.61 | 117.97 | 117.84 | 115.84 | 119.32 | 118.28 | 115.01 | 117.40 | 116.19 | 118.49 | 116.82 | 113.37 |
| | RF CAL | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |

LO HARMONICS ORDER

Test conditions: RF IN: 183 MHz; 0 dBm.
 LO IN: 153 MHz; +17.00 dBm
 IF OUT: 30 MHz; - 7.06 dBm

RF HARMONICS ORDER

| | (-dBm) | (-dBc) | | | | | | | | | | |
|----|--------|--------|--------|--------|--------|--------|-------|-------|-------|--------|-------|--------|
| 0 | --- | --- | 21.10 | 28.50 | 41.10 | 39.13 | 43.08 | 38.87 | 50.06 | 41.73 | 64.38 | 44.81 |
| 1 | --- | 30.34 | --- | 49.77 | 10.11 | 55.83 | 15.97 | 52.68 | 20.36 | 76.89 | 26.59 | 69.31 |
| 2 | 93.53 | 45.66 | 50.51 | 46.77 | 58.16 | 47.37 | 57.40 | 47.06 | 62.36 | 47.41 | 72.41 | 51.43 |
| 3 | 103.31 | 72.32 | 56.63 | 74.11 | 50.90 | 73.81 | 47.66 | 71.80 | 43.74 | 70.21 | 42.51 | 81.52 |
| 4 | 107.59 | 68.35 | 67.68 | 69.64 | 65.20 | 71.54 | 66.62 | 70.59 | 64.77 | 65.55 | 65.90 | 63.39 |
| 5 | 105.17 | 84.32 | 68.45 | 85.14 | 75.46 | 84.50 | 67.95 | 84.45 | 65.32 | 82.27 | 69.65 | 80.76 |
| 6 | 106.43 | 78.97 | 86.02 | 80.81 | 82.47 | 80.38 | 82.00 | 84.91 | 82.49 | 86.88 | 80.49 | 82.69 |
| 7 | 106.21 | 87.81 | 77.24 | 86.22 | 80.64 | 87.78 | 81.17 | 86.28 | 79.09 | 85.70 | 80.05 | 85.11 |
| 8 | 106.72 | 92.20 | 104.83 | 90.77 | 115.60 | 89.82 | 99.99 | 89.83 | 99.49 | 94.36 | 97.50 | 93.15 |
| 9 | 106.96 | 96.19 | 86.01 | 94.03 | 85.12 | 91.36 | 79.96 | 91.52 | 83.44 | 90.65 | 82.97 | 90.15 |
| 10 | 107.62 | 109.13 | 101.78 | 110.74 | 99.69 | 106.38 | 96.15 | 99.92 | 97.74 | 100.29 | 97.03 | 105.82 |
| | RF CAL | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |


LO HARMONICS ORDER

Test conditions: RF IN: 183 MHz; 10 dBm.
 LO IN: 153 MHz; +17.00 dBm
 IF OUT: 30 MHz; 2.73 dBm


- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT
 3. RF Cal represents the Harmonics level of the RF Input Signal to the mixer

Outline Dimensions

TTT881



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

| CASE # | A | B | C | D | E | F | G | H | J | K | L | M | N |
|--------|---------------|----------------|---------------|----------------|----------------|----------------|-----------------|----------------|----------------|----------------|----------------|----------------|-----------------|
| TTT881 | .38 (9.65) | .50 (12.70) | .23 (5.84) | .020 (0.51) | .075 (1.91) | .250 (6.35) | .425 (10.80) | .187 (4.75) | .050 (1.27) | .050 (1.27) | .070 (1.78) | .270 (6.86) | .540 (13.72) |

| CASE # | P | Q | R | S | T | WT. GRAM |
|--------|----------------|----------------|-----------------|----------------|-----------------|-------------|
| TTT881 | .060 (1.52) | .095 (2.41) | .445 (11.30) | .208 (5.28) | .415 (10.54) | .8 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Note:

- Case material: Nickel-Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F12



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|----------------|-------------------------|-------------------|-------------------------------------|-----|
| 24 | 12 | 7 | Small quantity standards (see note) | 10 |
| | | | | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | 13 | Standard | 500 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

 **Mini-Circuits**[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-----------------------------|----------|-----|------|
| A | M86762 | ADDED CONNECTIONS "lp & lq" | 05/23/03 | MMG | WL |
| B | M94598 | ADDED CONNECTION "hk" | 10/08/04 | MMG | HY |
| C | M102713 | UPDATED NOTES & DESCRIPTION | 01/14/06 | GF | IL |
| D | M132989 | UPDATED NOTE 2 | 08/24/11 | GF | DJ |

SUGGESTED MOUNTING CONFIGURATION FOR
TTT166/167 CASE STYLE, "hk"/"lp"/"lq"
"x"/"ck"/"ec" PIN CONNECTIONS



NOTE:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. THE USE OF SOLDER MASK OVER THE GROUND AREA UNDER THE UNIT AS SHOWN IS RECOMMENDED TO PREVENT POTENTIAL SHORTING. IF USER CHOOSES TO EXPOSE METAL UNDER THE ENTIRE UNIT GROUND PAD FOR IMPROVED GROUNDING, IT IS RECOMMENDED A SOLDER MASK DAM BE APPLIED AROUND EACH GROUND PAD TO ENSURE FILLET AND CONNECTION AT GROUND PADS.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER), SEE NOTE 2.
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES
 TOLERANCES ON:
 2 PL DECIMALS ±
 3 PL DECIMALS ± .005
 ANGLES ±
 FRACTIONS ±

| | INITIALS | DATE |
|----------|----------|----------|
| DRAWN | GF | 03/18/03 |
| CHECKED | IL | 04/15/03 |
| APPROVED | DJ | 04/15/03 |



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, hk/lp/lq/x/ck/ec, TTT166/167,
SYM/HJK/SYAS/SYPD, TB-12

| | | | |
|------------------|---------------------|--------------------------|-----------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-079 | REV: D |
| FILE: 98PL079 | SCALE: 5:1 | SHEET: 1 OF 1 | |

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit


For Pin Connections Refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |