



MMIC SURFACE MOUNT


Wideband Amplifier

LVA-273PN+

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

THE BIG DEAL

- Wide Bandwidth 0.01 to 26.5GHz
- Ultra-low Phase Noise Typ. -172dBc/Hz @ 10kHz Offset
- Output P1dB Typ. +18dBm
- Output IP3 Typ. +28dBm
- Supply Voltage: +5V and 85mA
- 4x4mm 24-Lead QFN-style Package




Generic photo used for illustration purposes only

APPLICATIONS

- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems
- 5G MIMO and Back Haul Radio Systems
- Signal Distribution Networks

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits LVA-273PN+ is an ultra-low phase noise distributed MMIC amplifier fabricated on a GaAs HBT process technology. Operating from 0.01 to 26.5GHz, this amplifier features high dynamic range and ultra-low phase noise along with 18dB gain, +18dBm P1dB, +28dBm OIP3, and 3.7dB noise figure. The LVA-273PN+ is ideal for use with low noise signal sources and highly sensitive transceiver signal chains for commercial, industrial, and defense applications.

KEY FEATURES

| Features | Advantages |
|--|---|
| Wide Bandwidth: 0.01 to 26.5GHz | Supports a broad variety of applications including Test and Measurement Equipment, 5G Microwave Radio, Radar, and Electronic Warfare Systems. |
| Ultra-low Phase Noise: -172dBc/Hz @ 10kHz offset | Enables the detection of signal levels in the presence of noise. |
| High Dynamic Range: <ul style="list-style-type: none"> • +18dBm P1dB • 18dB Gain • 3.7dB Noise Figure | The MMIC amplifier's unique combination of ultra-low phase noise, high operating P1dB, high gain, and low noise features enable optimum performance for high dynamic range transceiver systems. |
| 4x4mm 24-Lead QFN-style package | Small footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. |



MMIC SURFACE MOUNT

Wideband Amplifier

LVA-273PN+

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

ELECTRICAL SPECIFICATIONS¹ AT +25°C, V_{CC} = +5V, V_C = +5V, V_B = +5V, & Z₀ = 50Ω UNLESS NOTED OTHERWISE

| Parameter | Condition (GHz) | Min. | Typ. | Max. | Units |
|--|-----------------|-------|-------|-------|--------|
| Frequency Range | | 0.01 | | 26.5 | GHz |
| Gain | 0.01 | | 19.5 | | dB |
| | 5 | | 17.7 | | |
| | 10 | | 17.7 | | |
| | 20 | | 17.2 | | |
| | 26.5 | | 17.9 | | |
| Input Return Loss | 0.01 | | 16.4 | | dB |
| | 5 | | 16.5 | | |
| | 10 | | 20.0 | | |
| | 20 | | 12.8 | | |
| | 26.5 | | 15.2 | | |
| Output Return Loss | 0.01 | | 18.2 | | dB |
| | 5 | | 14.3 | | |
| | 10 | | 14.4 | | |
| | 20 | | 13.7 | | |
| | 26.5 | | 9.1 | | |
| Isolation | 0.01-26.5 | | 41.2 | | dB |
| Output Power at 1dB Compression (P _{1dB}) ² | 0.01 | | +19.9 | | dBm |
| | 5 | | +17.6 | | |
| | 10 | | +18.3 | | |
| | 20 | | +16.1 | | |
| | 26.5 | | +11.0 | | |
| Output Power at 3dB Compression (P _{3dB}) ³ | 0.01 | | +21.6 | | dBm |
| | 5 | | +21.2 | | |
| | 10 | | +20.6 | | |
| | 20 | | +17.6 | | |
| | 26.5 | | +13.1 | | |
| Output Third-Order Intercept Point (P _{OUT} = -2dBm/Tone) | 0.01 | | +27.4 | | dBm |
| | 5 | | +27.1 | | |
| | 10 | | +27.8 | | |
| | 20 | | +26.4 | | |
| | 26.5 | | +19.3 | | |
| Input Third-Order Intercept Point (P _{OUT} = -2dBm/Tone) | 0.01 | | +7.9 | | dBm |
| | 5 | | +9.4 | | |
| | 10 | | +10.1 | | |
| | 20 | | +9.2 | | |
| | 26.5 | | +1.4 | | |
| Noise Figure | 2 | | 7.7 | | dB |
| | 5 | | 4.3 | | |
| | 10 | | 3.7 | | |
| | 20 | | 5.6 | | |
| | 26.5 | | 9.2 | | |
| Additive Phase Noise (@10kHz Offset) | | | -172 | | dBc/Hz |
| Device Operating Voltage (V _{CC}) | | +4.75 | +5 | +5.25 | V |
| Device Operating Current (I _{CC}) ⁴ | | | 85 | | mA |
| Control Voltage (V _C) | | | +5 | | V |
| Control Current (I _C) | | | 1.2 | | mA |
| Base Voltage (V _B) | | | +5 | | V |
| Base Current (I _B) | | | 4.5 | | mA |
| Device Current Variation Vs. Temperature ⁵ | | | 7 | | uA/°C |
| Device Current Variation Vs. Voltage ⁶ | | | 0.013 | | mA/mV |

1. Tested on Mini-Circuits Characterization Test Board TB-LVA-273PNC+. See Figure 2. De-embedded to the device reference plane.

2. Defined as Output Power at which Gain is compressed by 1dB.

3. Defined as Output Power at which Gain is compressed by 3dB.

4. Current at P_{IN} = -25dBm. Increases to 105mA at P_{3dB}.

5. ((Current in mA at +105°C) - (Current in mA at -45°C))/(+150 °C)

6. ((Current in mA at +5.25V) - (Current in mA at +4.75V))/((+5.25V - +4.75V) * 1000mA/mV)







TYPICAL PERFORMANCE GRAPHS

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.


GAIN vs. TEMPERATURE
 $P_{IN} = -25dBm$




ISOLATION vs. TEMPERATURE
 $P_{IN} = -25dBm$




INPUT RETURN LOSS vs. TEMPERATURE
 $P_{IN} = -25dBm$




OUTPUT RETURN LOSS vs. TEMPERATURE
 $P_{IN} = -25dBm$



INPUT IP3 vs. TEMPERATURE
 $P_{OUT} = -2dBm/TONE$









OUTPUT IP3 vs. TEMPERATURE
 $P_{OUT} = -2dBm/TONE$





TYPICAL PERFORMANCE GRAPHS







Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS





Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.





TYPICAL PERFORMANCE GRAPHS

Note: All data taken at nominal conditions $V_{CC} = +5V$ and $V_C = +5V$ unless noted otherwise.





MMIC SURFACE MOUNT

Wideband Amplifier


LVA-273PN+

Mini-Circuits

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

TYPICAL PERFORMANCE GRAPHS

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.





MMIC SURFACE MOUNT

Wideband Amplifier

LVA-273PN+

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

ABSOLUTE MAXIMUM RATINGS⁷

| Parameter | Ratings |
|--|-----------------|
| Operating Temperature (ground lead) | -45°C to +105°C |
| Storage Temperature | -65°C to +150°C |
| Total Power Dissipation | 1.54W |
| Junction Temperature ⁸ | +150°C |
| Input Power (CW), $V_{CC} = +5V$, $V_C = +5V$, $V_B = +5V$ | +25dBm |
| DC Voltage on RF-OUT & V_{CC} | +10V |
| DC Voltage on RF-IN | +10V |
| Current I_{CC} | 150mA |
| DC Voltage on V_C | +10V |
| Current I_C | 5mA |
| DC Voltage on V_B | +10V |
| Current I_B | 14mA |

7. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

8. Peak temperature on top of Die.

THERMAL RESISTANCE

| Parameter | Ratings |
|---|----------|
| Thermal Resistance (Θ_{jc}) ⁹ | 29.2°C/W |

9. Θ_{jc} = (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

ESD RATING

| | Class | Voltage Range | Reference Standard |
|-----|-------|-----------------|-----------------------------|
| HBM | 1B | 500V to < 1000V | ANSI/ESDA/JEDEC JS-001-2017 |
| CDM | C2 | 500V to < 1000V | JESD22-C101F |



ESD HANDLING PRECAUTION: This device is designed to be Class 1B for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure, industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E/JEDEC J-STD-033C





MMIC SURFACE MOUNT

Wideband Amplifier

LVA-273PN+

Mini-Circuits

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

FUNCTIONAL DIAGRAM




Figure 1. LVA-273PN+ Functional Diagram

PAD DESCRIPTION

| Function | Pad Number | Application Description (Refer to Figure 2) |
|--------------------------|---------------------------|---|
| RF-IN | 22 | RF-IN Pad connects to RF input port. |
| RF-OUT & V _{CC} | 10 | RF-OUT Pad connects to RF output and V _{CC} port. |
| V _C | 1 | DC Input Pad connects to voltage input port, V _C . |
| V _B | 3 | DC Input Pad connects to voltage input port, V _B . |
| CG ₁ | 6 | Connects to AC ground through external capacitor C9. |
| CG ₂ | 5 | Connects to AC ground through external capacitor C8. |
| CG ₃ | 17 | Connects to AC ground through external capacitor C3. |
| CG ₄ | 18 | Connects to AC ground through external capacitor C2. |
| CG ₅ | 20 | Connects to AC ground through external capacitor C1. |
| GND | 9, 11, 21, 23, & Paddle | Connects to ground. |
| NC | 2, 4, 7, 8, 12-16, 19, 24 | Not used internally. Connects to ground on evaluation board. |

EVALUATION BOARD




Figure 2. DUT soldered on Mini-Circuits Evaluation Board: TB-LVA-273PNC+

Electrical Parameters and Conditions

Gain, Return Loss, Output Power at 1dB Compression (P1dB), Output Power at 3dB Compression (P3dB), Output IP3 (OIP3), and Noise Figure measured using N5247B PNA-X Microwave Network Analyzer.

Conditions:

1. Gain, Noise Figure, and Return Loss: P_{IN} = -25dBm.
2. Output IP3 (OIP3): Two tones, spaced 1MHz apart, -2dBm/tone at output.

Power ON/Power OFF Sequence

Caution: Permanent damage to the device will occur if the Power ON and Power OFF Sequences are not followed.

Power ON:

- 1) Set V_{CC} = +5V.
- 2) Set V_C = +5V.
- 3) Set V_B = +5V.
- 4) Turn on V_{CC}, V_C, and V_B.
- 5) Apply RF Signal.

Power OFF:

- 1) Turn off RF Signal.
- 2) Turn off V_{CC}, V_C, and V_B.

Note: Bias Tee ZBT-V543-FT+ is external to the Evaluation Board TB-LVA-273PNC+

| Component | Value | Size | Part Number | Manufacturer |
|------------|--------|------|--------------------|--------------|
| C1 | 5100pF | 0603 | GCM1885C1H512JA16D | Murata |
| C2 | 1μF | 0603 | GCM188R71E105KA64J | Murata |
| C3, C9 | 1000pF | 0402 | GRM1555C1H102JA01D | Murata |
| C4, C6 | 100pF | 0402 | GRM1555C1H101JA01D | Murata |
| C5, C7, C8 | 0.1μF | 0402 | GRM155R71H104KE14J | Murata |
| R1, R2 | 0Ω | 0402 | RK73Z1ETTP | KOA Spear |





MMIC SURFACE MOUNT


Wideband Amplifier

LVA-273PN+

Mini-Circuits


50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

CASE STYLE DRAWING



Weight: .04 Grams
Dimensions are in inches [mm]. Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MMIC SURFACE MOUNT

Wideband Amplifier

LVA-273PN+

50Ω 0.01 to 26.5GHz Ultra-Low Additive Phase

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD

[CLICK HERE](#)

| | |
|--|--|
| Performance Data & Graphs | Data |
| | Graphs |
| | S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style | DG1847 Plastic package, exposed paddle, Lead Finish: Matte-Tin |
| RoHs Status | Compliant |
| Tape & Reel Standard quantities available on reel | F68 7" reels with 20, 50, 100, 200, 500, or 1K devices |
| Suggested Layout for PCB Design | PL-756 |
| Evaluation Board | TB-LVA-273PNC+ |
| | Gerber File |
| Environmental Ratings | ENV08T1 |

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{cc} = +5V, V_B = +5V, V_C = +5V, I_{cc} = 85mA, I_B = 4.7mA, I_C = 1.2mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 19.4 | 46.8 | -16.4 | -18.1 | 11.5 | 1.0 | - | - | 20.1 | 21.8 | 21.6 |
| 0.02 | 19.2 | 62.5 | -16.6 | -19.1 | 71.8 | 1.0 | 10.7 | 29.9 | 20.1 | 21.8 | 20.6 |
| 0.03 | 19.1 | 63.5 | -16.2 | -19.3 | 80.6 | 1.0 | 11.7 | 30.9 | 20.0 | 21.8 | 20.9 |
| 0.04 | 19.1 | 61.6 | -16.1 | -19.3 | 65.2 | 1.0 | 12.3 | 31.4 | 20.1 | 21.8 | 20.9 |
| 0.05 | 19.0 | 60.4 | -16.1 | -19.3 | 57.2 | 1.0 | 12.1 | 31.2 | 20.1 | 22.1 | 21.0 |
| 0.06 | 19.0 | 73.3 | -16.1 | -19.1 | 252.2 | 1.0 | 11.3 | 30.3 | 20.0 | 22.0 | 20.9 |
| 0.07 | 18.9 | 68.7 | -16.1 | -19.1 | 149.1 | 1.0 | 9.3 | 28.2 | 20.0 | 21.9 | 20.9 |
| 0.08 | 19.0 | 67.6 | -16.1 | -19.2 | 131.5 | 1.0 | 10.3 | 29.2 | 20.1 | 22.0 | 20.7 |
| 0.09 | 18.9 | 67.1 | -16.1 | -19.3 | 124.8 | 1.0 | 10.7 | 29.6 | 20.0 | 21.9 | 20.6 |
| 0.10 | 18.9 | 68.4 | -16.1 | -19.3 | 145.9 | 1.0 | 11.3 | 30.2 | 19.9 | 21.9 | 20.6 |
| 0.20 | 18.7 | 88.2 | -16.5 | -20.3 | 1466.8 | 1.0 | 11.3 | 30.0 | 19.3 | 21.5 | 19.3 |
| 0.25 | 18.7 | 88.2 | -16.5 | -20.3 | 1466.8 | 1.0 | 11.3 | 30.0 | 19.3 | 21.2 | 19.3 |
| 0.50 | 18.2 | 59.3 | -15.7 | -21.6 | 55.9 | 1.0 | 9.7 | 27.9 | 18.1 | 20.9 | 15.6 |
| 1.00 | 17.2 | 72.1 | -14.1 | -29.2 | 273.9 | 1.0 | 10.0 | 27.2 | 17.2 | 20.4 | 11.6 |
| 1.50 | 17.2 | 56.7 | -14.2 | -21.5 | 46.6 | 1.0 | 9.3 | 26.5 | 17.2 | 20.6 | 9.1 |
| 2.00 | 17.3 | 54.0 | -14.2 | -18.4 | 34.1 | 1.0 | 9.7 | 27.0 | 17.1 | 20.6 | 7.6 |
| 2.50 | 17.3 | 52.2 | -13.8 | -17.0 | 27.5 | 1.0 | 9.5 | 26.8 | 17.4 | 20.9 | 6.7 |
| 3.00 | 17.1 | 52.8 | -13.0 | -16.7 | 30.1 | 1.0 | 9.0 | 26.1 | 17.5 | 20.9 | 6.0 |
| 3.50 | 17.2 | 57.2 | -13.3 | -16.0 | 49.7 | 1.0 | 9.9 | 27.0 | 17.6 | 21.0 | 5.4 |
| 4.00 | 17.3 | 56.9 | -14.3 | -15.3 | 48.1 | 1.0 | 10.2 | 27.5 | 17.7 | 21.0 | 4.9 |
| 4.50 | 17.3 | 52.5 | -15.8 | -14.2 | 29.0 | 1.0 | 9.7 | 27.1 | 17.7 | 21.0 | 4.5 |
| 5.00 | 17.3 | 51.8 | -17.4 | -13.4 | 26.9 | 1.0 | 9.7 | 27.0 | 17.7 | 21.1 | 4.1 |
| 5.50 | 17.3 | 49.0 | -18.4 | -13.5 | 19.8 | 1.0 | 10.4 | 27.6 | 17.6 | 21.0 | 3.9 |
| 6.00 | 17.3 | 47.7 | -18.8 | -14.6 | 17.5 | 1.0 | 10.1 | 27.4 | 17.8 | 21.0 | 3.6 |
| 6.50 | 17.3 | 46.6 | -19.2 | -16.3 | 15.7 | 1.0 | 9.7 | 27.0 | 17.9 | 20.9 | 3.5 |
| 7.00 | 17.3 | 45.3 | -19.5 | -18.2 | 13.7 | 1.0 | 10.5 | 27.7 | 17.8 | 20.9 | 3.4 |
| 7.50 | 17.2 | 44.1 | -19.7 | -19.4 | 12.1 | 1.0 | 9.9 | 27.1 | 17.9 | 20.7 | 3.4 |
| 8.00 | 17.3 | 43.3 | -20.8 | -19.4 | 11.2 | 1.0 | 10.0 | 27.3 | 17.9 | 20.5 | 3.4 |
| 8.50 | 17.3 | 42.3 | -22.4 | -18.7 | 10.0 | 1.0 | 9.8 | 27.0 | 18.0 | 20.5 | 3.4 |
| 9.00 | 17.2 | 40.9 | -20.4 | -17.5 | 8.5 | 1.0 | 10.2 | 27.4 | 18.2 | 20.6 | 3.4 |
| 9.50 | 17.3 | 41.4 | -17.6 | -15.1 | 8.8 | 1.0 | 10.4 | 27.7 | 18.4 | 20.6 | 3.5 |
| 10.00 | 17.2 | 41.4 | -16.4 | -13.2 | 8.7 | 1.0 | 10.4 | 27.7 | 18.4 | 20.6 | 3.5 |
| 10.50 | 17.3 | 40.6 | -17.3 | -12.3 | 7.8 | 1.0 | 11.0 | 28.3 | 18.4 | 20.4 | 3.5 |
| 11.00 | 17.4 | 39.6 | -20.7 | -12.4 | 7.1 | 0.9 | 10.5 | 27.9 | 18.3 | 20.2 | 3.6 |
| 11.50 | 17.4 | 39.2 | -29.9 | -13.9 | 6.9 | 1.0 | 10.7 | 28.2 | 18.1 | 19.9 | 3.7 |
| 12.00 | 17.4 | 38.3 | -29.8 | -17.7 | 6.4 | 1.0 | 10.2 | 27.7 | 18.2 | 19.9 | 3.8 |
| 12.50 | 17.3 | 37.6 | -21.7 | -24.2 | 6.1 | 1.0 | 10.2 | 27.5 | 17.9 | 19.4 | 3.9 |
| 13.00 | 17.1 | 37.2 | -18.7 | -20.4 | 5.9 | 1.0 | 11.0 | 28.1 | 17.4 | 19.0 | 3.9 |
| 13.50 | 16.8 | 37.2 | -17.8 | -16.7 | 6.1 | 1.0 | 11.3 | 28.1 | 17.4 | 19.0 | 4.2 |
| 14.00 | 16.5 | 38.1 | -18.2 | -15.0 | 6.9 | 1.0 | 12.4 | 29.0 | 17.4 | 19.0 | 4.6 |
| 14.50 | 16.4 | 39.1 | -19.5 | -13.3 | 7.8 | 1.0 | 11.1 | 27.5 | 17.3 | 18.9 | 4.8 |
| 15.00 | 16.6 | 37.6 | -22.1 | -12.7 | 6.4 | 0.9 | 11.7 | 28.4 | 17.5 | 19.1 | 4.7 |
| 15.50 | 16.8 | 36.4 | -23.7 | -12.2 | 5.5 | 0.9 | 12.1 | 29.0 | 17.5 | 19.0 | 4.8 |
| 16.00 | 16.9 | 35.6 | -22.8 | -11.2 | 4.9 | 0.9 | 10.5 | 27.5 | 17.6 | 19.0 | 4.8 |
| 16.50 | 17.1 | 34.9 | -22.8 | -10.7 | 4.4 | 0.9 | 11.1 | 28.2 | 17.5 | 18.8 | 5.0 |
| 17.00 | 17.3 | 34.4 | -24.1 | -10.8 | 4.1 | 0.9 | 9.6 | 26.8 | 17.1 | 18.5 | 5.1 |
| 17.50 | 17.5 | 33.3 | -26.4 | -10.8 | 3.6 | 0.9 | 10.3 | 27.8 | 17.1 | 18.5 | 5.2 |
| 18.00 | 17.7 | 32.3 | -26.9 | -11.5 | 3.2 | 0.9 | 8.5 | 26.2 | 16.9 | 18.3 | 5.4 |
| 18.50 | 17.8 | 31.5 | -20.9 | -15.0 | 3.0 | 1.0 | 8.0 | 25.8 | 16.3 | 17.9 | 5.5 |
| 19.00 | 17.8 | 31.3 | -15.5 | -24.6 | 3.0 | 1.0 | 8.0 | 25.8 | 15.8 | 17.5 | 5.5 |
| 19.50 | 17.5 | 31.6 | -13.5 | -17.6 | 3.1 | 1.0 | 8.7 | 26.2 | 16.0 | 17.5 | 5.5 |
| 20.00 | 17.3 | 31.5 | -14.2 | -15.1 | 3.1 | 1.0 | 8.8 | 26.1 | 16.1 | 17.5 | 5.7 |
| 20.50 | 17.4 | 31.3 | -16.9 | -15.9 | 3.1 | 1.0 | 8.7 | 26.1 | 16.1 | 17.5 | 5.7 |
| 21.00 | 17.6 | 30.9 | -20.4 | -17.7 | 2.9 | 1.0 | 8.5 | 26.1 | 15.8 | 17.3 | 5.7 |
| 21.50 | 17.8 | 30.6 | -24.5 | -17.9 | 2.8 | 1.0 | 7.1 | 24.9 | 15.6 | 17.1 | 5.8 |
| 22.00 | 17.9 | 30.3 | -26.8 | -15.7 | 2.7 | 0.9 | 6.9 | 24.8 | 15.5 | 17.2 | 5.9 |
| 22.50 | 17.9 | 30.1 | -24.2 | -13.5 | 2.6 | 0.9 | 6.5 | 24.4 | 15.2 | 17.0 | 6.0 |
| 23.00 | 17.7 | 30.2 | -23.6 | -12.3 | 2.7 | 0.9 | 5.9 | 23.6 | 14.7 | 16.7 | 6.3 |
| 23.50 | 17.6 | 30.2 | -25.4 | -11.9 | 2.7 | 0.9 | 5.8 | 23.3 | 14.4 | 16.2 | 6.6 |
| 24.00 | 17.5 | 30.3 | -19.0 | -11.8 | 2.7 | 0.9 | 4.3 | 21.8 | 14.1 | 16.0 | 6.8 |
| 24.50 | 17.4 | 30.1 | -14.9 | -11.8 | 2.7 | 0.9 | 4.0 | 21.4 | 13.8 | 15.8 | 7.1 |
| 25.00 | 17.6 | 29.9 | -14.1 | -12.8 | 2.6 | 0.9 | 3.7 | 21.3 | 13.4 | 15.6 | 7.4 |
| 25.50 | 18.0 | 29.2 | -17.7 | -18.6 | 2.5 | 1.0 | 3.0 | 21.0 | 13.1 | 15.0 | 7.9 |
| 26.00 | 18.2 | 28.7 | -31.3 | -21.7 | 2.3 | 0.9 | 2.1 | 20.3 | 11.9 | 13.6 | 8.4 |
| 26.50 | 17.9 | 29.1 | -17.7 | -11.0 | 2.3 | 0.9 | 1.4 | 19.2 | 11.1 | 12.9 | 9.1 |
| 27.00 | 16.8 | 30.2 | -14.9 | -7.6 | 2.6 | 0.8 | 2.6 | 19.4 | 10.8 | 12.6 | 10.1 |
| 27.50 | 15.0 | 32.3 | -12.6 | -6.5 | 3.7 | 0.8 | 2.7 | 17.8 | 9.7 | 11.7 | 11.5 |
| 28.00 | 13.3 | 33.9 | -10.6 | -7.2 | 5.4 | 0.9 | 4.2 | 17.4 | 9.7 | 11.7 | 12.7 |
| 28.50 | 11.5 | 35.4 | -9.5 | -9.9 | 8.4 | 1.0 | 6.3 | 17.9 | 9.8 | 11.9 | 13.9 |
| 29.00 | 9.9 | 36.5 | -9.5 | -15.5 | 12.5 | 1.1 | 7.2 | 17.1 | 9.0 | 11.2 | 14.6 |
| 29.50 | 8.3 | 37.2 | -11.0 | -18.5 | 17.3 | 1.1 | 6.6 | 14.9 | 8.1 | 10.4 | 15.4 |
| 30.00 | 6.7 | 38.7 | -13.3 | -14.7 | 25.1 | 1.0 | 6.3 | 13.0 | 6.6 | 9.2 | 16.3 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{cc} = +5V, V_B = +5.4V, V_C = +5V, I_{cc} = 94mA, I_B = 5.2mA, I_C = 1.3mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 19.5 | 71.7 | -16.4 | -18.1 | 198.0 | 1.0 | - | - | 20.8 | 22.1 | 22.0 |
| 0.02 | 19.4 | 54.2 | -16.5 | -19.3 | 26.9 | 1.0 | 10.1 | 29.5 | 20.7 | 22.1 | 21.0 |
| 0.03 | 19.3 | 64.3 | -16.2 | -19.2 | 86.9 | 1.0 | 10.1 | 29.4 | 20.6 | 22.0 | 21.3 |
| 0.04 | 19.2 | 64.5 | -16.0 | -19.3 | 89.1 | 1.0 | 11.8 | 31.0 | 20.8 | 22.4 | 21.2 |
| 0.05 | 19.2 | 59.7 | -16.1 | -19.1 | 51.5 | 1.0 | 11.4 | 30.6 | 20.7 | 22.4 | 21.3 |
| 0.06 | 19.1 | 60.2 | -16.0 | -19.1 | 55.2 | 1.0 | 13.9 | 33.1 | 20.7 | 22.2 | 21.2 |
| 0.07 | 19.1 | 64.4 | -16.1 | -19.1 | 89.2 | 1.0 | 11.3 | 30.4 | 20.7 | 22.2 | 21.2 |
| 0.08 | 19.1 | 67.0 | -16.1 | -19.2 | 120.1 | 1.0 | 12.9 | 32.1 | 20.7 | 22.3 | 21.0 |
| 0.09 | 19.1 | 62.6 | -16.1 | -19.3 | 73.3 | 1.0 | 12.6 | 31.7 | 20.6 | 22.2 | 21.0 |
| 0.10 | 19.1 | 68.2 | -16.1 | -19.3 | 139.2 | 1.0 | 11.1 | 30.2 | 20.5 | 22.1 | 20.9 |
| 0.20 | 19.0 | 68.5 | -16.4 | -20.3 | 147.0 | 1.0 | 10.4 | 29.4 | 19.7 | 21.9 | 19.6 |
| 0.25 | 19.0 | 68.5 | -16.4 | -20.3 | 147.0 | 1.0 | 10.4 | 29.4 | 19.7 | 21.5 | 19.6 |
| 0.50 | 18.6 | 66.3 | -15.7 | -21.7 | 118.6 | 1.0 | 9.3 | 28.0 | 18.5 | 21.2 | 15.8 |
| 1.00 | 17.6 | 62.3 | -14.1 | -29.5 | 84.5 | 1.0 | 9.9 | 27.6 | 17.5 | 20.7 | 11.9 |
| 1.50 | 17.6 | 58.0 | -14.2 | -21.6 | 51.5 | 1.0 | 9.3 | 27.0 | 17.4 | 21.0 | 9.4 |
| 2.00 | 17.7 | 57.2 | -14.2 | -18.5 | 46.8 | 1.0 | 9.4 | 27.2 | 17.5 | 21.0 | 7.7 |
| 2.50 | 17.7 | 52.6 | -13.8 | -17.1 | 27.3 | 1.0 | 9.4 | 27.1 | 17.6 | 21.3 | 6.8 |
| 3.00 | 17.6 | 53.4 | -13.0 | -16.8 | 30.5 | 1.0 | 8.8 | 26.3 | 17.7 | 21.4 | 6.1 |
| 3.50 | 17.6 | 56.1 | -13.3 | -16.0 | 41.6 | 1.0 | 9.5 | 27.1 | 18.0 | 21.4 | 5.6 |
| 4.00 | 17.7 | 57.0 | -14.3 | -15.3 | 46.4 | 1.0 | 10.1 | 27.8 | 18.0 | 21.4 | 5.0 |
| 4.50 | 17.8 | 52.6 | -15.8 | -14.2 | 28.0 | 1.0 | 9.6 | 27.4 | 17.9 | 21.4 | 4.6 |
| 5.00 | 17.8 | 50.6 | -17.5 | -13.3 | 22.5 | 1.0 | 9.5 | 27.2 | 18.0 | 21.5 | 4.2 |
| 5.50 | 17.7 | 48.8 | -18.5 | -13.4 | 18.5 | 1.0 | 9.8 | 27.5 | 18.0 | 21.3 | 3.9 |
| 6.00 | 17.7 | 47.3 | -18.8 | -14.5 | 15.7 | 1.0 | 9.6 | 27.3 | 18.1 | 21.3 | 3.7 |
| 6.50 | 17.7 | 46.4 | -19.3 | -16.2 | 14.6 | 1.0 | 9.6 | 27.3 | 18.1 | 21.4 | 3.5 |
| 7.00 | 17.7 | 45.3 | -19.5 | -18.0 | 13.1 | 1.0 | 10.1 | 27.8 | 18.1 | 21.3 | 3.5 |
| 7.50 | 17.7 | 44.5 | -19.7 | -19.3 | 12.1 | 1.0 | 9.7 | 27.4 | 18.1 | 21.1 | 3.4 |
| 8.00 | 17.7 | 43.3 | -20.8 | -19.4 | 10.6 | 1.0 | 9.8 | 27.5 | 18.3 | 21.0 | 3.4 |
| 8.50 | 17.7 | 42.1 | -22.4 | -18.8 | 9.3 | 1.0 | 9.4 | 27.1 | 18.4 | 21.0 | 3.5 |
| 9.00 | 17.7 | 41.2 | -20.5 | -17.7 | 8.3 | 1.0 | 10.3 | 28.0 | 18.6 | 21.1 | 3.5 |
| 9.50 | 17.7 | 41.2 | -17.6 | -15.2 | 8.3 | 1.0 | 10.1 | 27.8 | 18.7 | 21.1 | 3.5 |
| 10.00 | 17.7 | 41.2 | -16.4 | -13.3 | 8.0 | 1.0 | 10.2 | 27.9 | 18.8 | 21.1 | 3.6 |
| 10.50 | 17.7 | 40.5 | -17.2 | -12.3 | 7.3 | 1.0 | 10.7 | 28.4 | 18.8 | 20.9 | 3.6 |
| 11.00 | 17.8 | 39.7 | -20.5 | -12.4 | 6.8 | 0.9 | 10.6 | 28.4 | 18.7 | 20.7 | 3.7 |
| 11.50 | 17.9 | 39.0 | -29.2 | -13.8 | 6.4 | 1.0 | 10.1 | 28.0 | 18.5 | 20.4 | 3.7 |
| 12.00 | 17.9 | 38.3 | -30.5 | -17.5 | 6.1 | 1.0 | 9.9 | 27.7 | 18.6 | 20.4 | 3.8 |
| 12.50 | 17.8 | 37.7 | -21.9 | -24.2 | 5.9 | 1.0 | 9.3 | 27.1 | 18.1 | 20.0 | 3.8 |
| 13.00 | 17.6 | 37.4 | -18.7 | -21.0 | 5.7 | 1.0 | 9.9 | 27.5 | 17.7 | 19.5 | 4.0 |
| 13.50 | 17.3 | 37.4 | -17.7 | -17.1 | 5.9 | 1.0 | 11.1 | 28.4 | 17.8 | 19.6 | 4.2 |
| 14.00 | 17.0 | 38.0 | -18.0 | -15.3 | 6.5 | 1.0 | 11.2 | 28.2 | 17.8 | 19.5 | 4.6 |
| 14.50 | 16.9 | 39.0 | -19.3 | -13.4 | 7.3 | 1.0 | 10.5 | 27.4 | 17.7 | 19.5 | 4.8 |
| 15.00 | 17.1 | 37.6 | -21.8 | -12.7 | 6.1 | 0.9 | 10.4 | 27.5 | 17.9 | 19.6 | 4.7 |
| 15.50 | 17.3 | 36.5 | -23.3 | -12.1 | 5.2 | 0.9 | 10.5 | 27.8 | 18.0 | 19.6 | 4.7 |
| 16.00 | 17.4 | 35.6 | -22.4 | -11.1 | 4.6 | 0.9 | 9.9 | 27.2 | 18.2 | 19.6 | 4.8 |
| 16.50 | 17.5 | 35.1 | -22.4 | -10.6 | 4.3 | 0.9 | 10.1 | 27.6 | 18.0 | 19.5 | 5.0 |
| 17.00 | 17.7 | 34.6 | -23.6 | -10.6 | 4.0 | 0.9 | 8.7 | 26.5 | 17.7 | 19.1 | 5.1 |
| 17.50 | 18.0 | 33.5 | -25.9 | -10.5 | 3.5 | 0.9 | 8.9 | 26.9 | 17.6 | 19.1 | 5.3 |
| 18.00 | 18.2 | 32.4 | -27.6 | -11.1 | 3.0 | 0.9 | 8.3 | 26.5 | 17.5 | 19.0 | 5.4 |
| 18.50 | 18.4 | 31.6 | -21.5 | -14.2 | 2.8 | 0.9 | 6.9 | 25.3 | 16.8 | 18.5 | 5.7 |
| 19.00 | 18.3 | 31.3 | -15.6 | -23.4 | 2.8 | 1.0 | 7.9 | 26.2 | 16.1 | 18.1 | 5.6 |
| 19.50 | 18.0 | 31.5 | -13.4 | -17.7 | 2.9 | 1.0 | 7.3 | 25.3 | 16.3 | 18.1 | 5.6 |
| 20.00 | 17.8 | 31.6 | -13.9 | -15.0 | 3.0 | 1.0 | 8.1 | 25.9 | 16.5 | 18.1 | 5.5 |
| 20.50 | 17.9 | 31.3 | -16.5 | -15.7 | 2.9 | 1.0 | 8.3 | 26.2 | 16.5 | 18.1 | 5.6 |
| 21.00 | 18.1 | 31.0 | -20.0 | -17.5 | 2.8 | 1.0 | 8.0 | 26.1 | 16.3 | 17.8 | 5.7 |
| 21.50 | 18.3 | 30.6 | -24.4 | -18.2 | 2.7 | 1.0 | 6.2 | 24.5 | 16.1 | 17.7 | 5.8 |
| 22.00 | 18.4 | 30.2 | -27.8 | -16.3 | 2.6 | 0.9 | 6.6 | 25.0 | 16.0 | 17.8 | 5.9 |
| 22.50 | 18.4 | 30.2 | -24.5 | -14.0 | 2.5 | 0.9 | 6.3 | 24.7 | 15.6 | 17.6 | 6.0 |
| 23.00 | 18.3 | 30.1 | -23.4 | -12.7 | 2.5 | 0.9 | 5.3 | 23.6 | 15.1 | 17.2 | 6.2 |
| 23.50 | 18.1 | 30.1 | -25.3 | -12.2 | 2.5 | 0.9 | 5.2 | 23.3 | 14.8 | 16.8 | 6.5 |
| 24.00 | 18.0 | 30.2 | -19.1 | -12.0 | 2.6 | 0.9 | 4.0 | 22.0 | 14.4 | 16.5 | 6.8 |
| 24.50 | 17.9 | 30.3 | -14.8 | -11.8 | 2.6 | 0.9 | 3.7 | 21.6 | 14.1 | 16.4 | 7.0 |
| 25.00 | 18.0 | 30.1 | -13.8 | -12.4 | 2.5 | 0.9 | 4.1 | 22.2 | 13.7 | 16.2 | 7.4 |
| 25.50 | 18.4 | 29.4 | -16.7 | -16.7 | 2.4 | 0.9 | 2.9 | 21.3 | 13.6 | 15.6 | 7.8 |
| 26.00 | 18.8 | 28.8 | -28.0 | -28.1 | 2.2 | 0.9 | 1.8 | 20.7 | 12.2 | 14.1 | 8.2 |
| 26.50 | 18.7 | 28.7 | -17.8 | -12.1 | 2.1 | 0.9 | 0.6 | 19.3 | 11.1 | 13.4 | 8.9 |
| 27.00 | 17.8 | 29.8 | -14.7 | -7.8 | 2.2 | 0.8 | 1.5 | 19.3 | 10.6 | 12.9 | 9.9 |
| 27.50 | 16.1 | 31.5 | -12.3 | -6.3 | 2.9 | 0.8 | 1.6 | 17.7 | 9.3 | 11.8 | 11.2 |
| 28.00 | 14.3 | 33.5 | -10.3 | -6.8 | 4.4 | 0.9 | 3.2 | 17.5 | 9.0 | 11.8 | 12.5 |
| 28.50 | 12.5 | 34.7 | -9.3 | -9.1 | 6.7 | 1.0 | 5.6 | 18.1 | 9.5 | 12.2 | 13.7 |
| 29.00 | 10.8 | 35.8 | -9.3 | -14.0 | 10.3 | 1.1 | 6.6 | 17.4 | 9.1 | 11.6 | 14.5 |
| 29.50 | 9.3 | 37.5 | -10.7 | -17.5 | 15.9 | 1.1 | 6.8 | 16.1 | 8.2 | 10.9 | 15.3 |
| 30.00 | 7.6 | 38.0 | -13.2 | -14.6 | 20.7 | 1.0 | 6.4 | 14.0 | 7.1 | 9.9 | 16.0 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.8V, V_C = +5V, I_{CC} = 104mA, I_B = 5.7mA, I_C = 1.4mA @ Temperature = +25°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 19.7 | 55.6 | -16.3 | -18.3 | 30.7 | 1.0 | - | - | 21.1 | 22.3 | 22.3 |
| 0.02 | 19.5 | 51.9 | -16.4 | -19.2 | 20.5 | 1.0 | 10.3 | 29.8 | 21.2 | 22.3 | 21.2 |
| 0.03 | 19.4 | 63.8 | -16.1 | -19.2 | 80.6 | 1.0 | 14.6 | 34.0 | 21.1 | 22.2 | 21.6 |
| 0.04 | 19.3 | 65.6 | -16.1 | -19.3 | 100.4 | 1.0 | 11.8 | 31.2 | 21.4 | 22.7 | 21.6 |
| 0.05 | 19.3 | 68.6 | -16.1 | -19.2 | 141.6 | 1.0 | 11.0 | 30.3 | 21.4 | 22.6 | 21.6 |
| 0.06 | 19.3 | 70.1 | -16.0 | -19.1 | 169.5 | 1.0 | 10.8 | 30.0 | 21.2 | 22.5 | 21.5 |
| 0.07 | 19.3 | 72.2 | -16.0 | -19.1 | 216.1 | 1.0 | 13.5 | 32.7 | 21.2 | 22.4 | 21.5 |
| 0.08 | 19.3 | 73.7 | -16.0 | -19.2 | 255.7 | 1.0 | 13.6 | 32.9 | 21.1 | 22.5 | 21.3 |
| 0.09 | 19.2 | 75.9 | -16.1 | -19.2 | 333.1 | 1.0 | 11.9 | 31.2 | 21.1 | 22.5 | 21.3 |
| 0.10 | 19.2 | 63.6 | -16.1 | -19.3 | 80.4 | 1.0 | 11.9 | 31.1 | 21.0 | 22.4 | 21.2 |
| 0.20 | 19.2 | 68.8 | -16.4 | -20.3 | 149.2 | 1.0 | 11.0 | 30.2 | 20.2 | 22.1 | 20.0 |
| 0.25 | 19.2 | 68.8 | -16.4 | -20.3 | 149.2 | 1.0 | 11.0 | 30.2 | 20.2 | 21.8 | 20.0 |
| 0.50 | 18.9 | 62.4 | -15.7 | -21.9 | 73.1 | 1.0 | 8.3 | 27.2 | 18.9 | 21.5 | 16.2 |
| 1.00 | 18.0 | 63.0 | -14.1 | -30.0 | 88.2 | 1.0 | 9.4 | 27.4 | 17.9 | 21.0 | 12.1 |
| 1.50 | 18.0 | 59.0 | -14.2 | -21.7 | 55.6 | 1.0 | 8.9 | 26.8 | 17.7 | 21.4 | 9.6 |
| 2.00 | 18.1 | 54.9 | -14.2 | -18.6 | 34.3 | 1.0 | 9.5 | 27.6 | 17.9 | 21.4 | 8.0 |
| 2.50 | 18.1 | 53.0 | -13.8 | -17.2 | 27.5 | 1.0 | 8.8 | 26.9 | 17.9 | 21.6 | 7.0 |
| 3.00 | 17.9 | 52.6 | -13.0 | -16.8 | 26.8 | 1.0 | 8.5 | 26.3 | 18.1 | 21.7 | 6.2 |
| 3.50 | 17.9 | 56.4 | -13.3 | -16.0 | 41.7 | 1.0 | 9.6 | 27.6 | 18.3 | 21.8 | 5.6 |
| 4.00 | 18.1 | 54.8 | -14.3 | -15.3 | 34.5 | 1.0 | 9.2 | 27.3 | 18.4 | 21.7 | 5.0 |
| 4.50 | 18.1 | 53.2 | -15.8 | -14.2 | 28.9 | 1.0 | 9.1 | 27.3 | 18.3 | 21.7 | 4.6 |
| 5.00 | 18.1 | 51.1 | -17.5 | -13.3 | 22.6 | 1.0 | 8.9 | 27.1 | 18.3 | 21.8 | 4.3 |
| 5.50 | 18.1 | 49.5 | -18.5 | -13.4 | 19.1 | 1.0 | 9.1 | 27.2 | 18.3 | 21.7 | 4.1 |
| 6.00 | 18.1 | 47.8 | -18.8 | -14.4 | 16.0 | 1.0 | 9.1 | 27.2 | 18.3 | 21.8 | 3.8 |
| 6.50 | 18.1 | 46.2 | -19.3 | -16.0 | 13.7 | 1.0 | 8.9 | 27.0 | 18.4 | 21.8 | 3.7 |
| 7.00 | 18.1 | 45.6 | -19.5 | -17.9 | 13.0 | 1.0 | 9.6 | 27.7 | 18.4 | 21.7 | 3.5 |
| 7.50 | 18.0 | 44.4 | -19.7 | -19.2 | 11.4 | 1.0 | 9.5 | 27.5 | 18.5 | 21.6 | 3.5 |
| 8.00 | 18.0 | 43.6 | -20.8 | -19.5 | 10.5 | 1.0 | 9.5 | 27.6 | 18.6 | 21.4 | 3.4 |
| 8.50 | 18.0 | 42.3 | -22.4 | -18.9 | 9.2 | 1.0 | 9.2 | 27.2 | 18.8 | 21.5 | 3.5 |
| 9.00 | 18.0 | 41.2 | -20.6 | -17.9 | 8.1 | 1.0 | 9.7 | 27.7 | 18.9 | 21.5 | 3.5 |
| 9.50 | 18.0 | 41.2 | -17.7 | -15.4 | 7.9 | 1.0 | 10.4 | 28.5 | 19.0 | 21.6 | 3.5 |
| 10.00 | 18.0 | 41.4 | -16.4 | -13.4 | 7.9 | 1.0 | 9.9 | 27.9 | 19.2 | 21.5 | 3.5 |
| 10.50 | 18.1 | 40.5 | -17.2 | -12.4 | 7.1 | 1.0 | 10.2 | 28.3 | 19.2 | 21.3 | 3.6 |
| 11.00 | 18.1 | 39.9 | -20.4 | -12.4 | 6.7 | 0.9 | 9.7 | 27.8 | 19.1 | 21.1 | 3.7 |
| 11.50 | 18.2 | 39.1 | -28.7 | -13.7 | 6.3 | 1.0 | 10.0 | 28.2 | 18.9 | 20.9 | 3.7 |
| 12.00 | 18.2 | 38.4 | -30.9 | -17.3 | 5.9 | 1.0 | 9.7 | 27.9 | 19.0 | 20.8 | 3.8 |
| 12.50 | 18.2 | 37.8 | -22.0 | -24.2 | 5.6 | 1.0 | 9.0 | 27.2 | 18.5 | 20.4 | 3.9 |
| 13.00 | 18.0 | 37.4 | -18.7 | -21.6 | 5.5 | 1.0 | 9.5 | 27.5 | 18.0 | 19.9 | 4.0 |
| 13.50 | 17.7 | 37.2 | -17.6 | -17.5 | 5.5 | 1.0 | 9.9 | 27.6 | 18.2 | 20.1 | 4.2 |
| 14.00 | 17.4 | 38.2 | -17.9 | -15.5 | 6.4 | 1.0 | 10.5 | 27.8 | 18.2 | 20.0 | 4.6 |
| 14.50 | 17.2 | 38.7 | -19.2 | -13.5 | 6.8 | 1.0 | 9.7 | 26.9 | 18.1 | 20.0 | 4.8 |
| 15.00 | 17.4 | 37.4 | -21.5 | -12.7 | 5.8 | 0.9 | 9.8 | 27.2 | 18.4 | 20.1 | 4.7 |
| 15.50 | 17.6 | 36.4 | -23.1 | -12.1 | 5.0 | 0.9 | 9.8 | 27.4 | 18.4 | 20.1 | 4.7 |
| 16.00 | 17.7 | 35.8 | -22.1 | -11.1 | 4.6 | 0.9 | 8.9 | 26.6 | 18.7 | 20.1 | 4.8 |
| 16.50 | 17.8 | 35.0 | -22.1 | -10.5 | 4.1 | 0.9 | 9.0 | 26.9 | 18.5 | 20.0 | 5.0 |
| 17.00 | 18.0 | 34.5 | -23.3 | -10.4 | 3.8 | 0.9 | 8.0 | 26.1 | 18.2 | 19.6 | 5.1 |
| 17.50 | 18.3 | 33.4 | -25.5 | -10.3 | 3.3 | 0.9 | 7.9 | 26.2 | 18.1 | 19.6 | 5.3 |
| 18.00 | 18.5 | 32.3 | -27.9 | -10.7 | 2.9 | 0.9 | 6.8 | 25.4 | 17.8 | 19.5 | 5.4 |
| 18.50 | 18.7 | 31.6 | -21.9 | -13.6 | 2.7 | 0.9 | 6.3 | 25.0 | 17.1 | 19.0 | 5.5 |
| 19.00 | 18.7 | 31.3 | -15.6 | -22.3 | 2.7 | 1.0 | 7.3 | 26.1 | 16.4 | 18.6 | 5.5 |
| 19.50 | 18.4 | 31.5 | -13.3 | -17.8 | 2.8 | 1.0 | 6.4 | 24.9 | 16.5 | 18.5 | 5.5 |
| 20.00 | 18.2 | 31.6 | -13.7 | -15.0 | 2.8 | 1.0 | 8.0 | 26.1 | 16.9 | 18.6 | 5.6 |
| 20.50 | 18.2 | 31.3 | -16.3 | -15.5 | 2.8 | 1.0 | 7.5 | 25.7 | 16.9 | 18.6 | 5.6 |
| 21.00 | 18.5 | 31.0 | -19.7 | -17.4 | 2.7 | 1.0 | 7.4 | 25.8 | 16.7 | 18.3 | 5.6 |
| 21.50 | 18.7 | 30.6 | -24.1 | -18.5 | 2.6 | 1.0 | 6.1 | 24.7 | 16.4 | 18.2 | 5.7 |
| 22.00 | 18.8 | 30.4 | -28.5 | -16.9 | 2.5 | 0.9 | 6.2 | 25.0 | 16.4 | 18.3 | 5.9 |
| 22.50 | 18.8 | 30.1 | -25.0 | -14.6 | 2.4 | 0.9 | 5.9 | 24.7 | 15.9 | 18.1 | 6.0 |
| 23.00 | 18.7 | 30.1 | -23.4 | -13.1 | 2.4 | 0.9 | 4.7 | 23.3 | 15.4 | 17.7 | 6.2 |
| 23.50 | 18.5 | 30.3 | -25.4 | -12.5 | 2.5 | 0.9 | 4.7 | 23.2 | 15.0 | 17.2 | 6.4 |
| 24.00 | 18.3 | 30.3 | -19.2 | -12.2 | 2.5 | 0.9 | 3.8 | 22.2 | 14.7 | 16.9 | 6.7 |
| 24.50 | 18.2 | 30.4 | -14.8 | -11.8 | 2.5 | 0.9 | 3.4 | 21.7 | 14.6 | 16.9 | 7.0 |
| 25.00 | 18.3 | 30.1 | -13.6 | -12.1 | 2.5 | 0.9 | 3.6 | 21.9 | 14.1 | 16.6 | 7.4 |
| 25.50 | 18.6 | 29.5 | -16.1 | -15.4 | 2.3 | 0.9 | 2.5 | 21.2 | 14.0 | 16.0 | 7.7 |
| 26.00 | 19.1 | 28.8 | -25.7 | -46.9 | 2.2 | 0.9 | 1.4 | 20.5 | 12.6 | 14.6 | 8.1 |
| 26.50 | 19.2 | 28.7 | -17.9 | -13.6 | 2.0 | 0.9 | -0.3 | 18.9 | 11.5 | 13.7 | 8.8 |
| 27.00 | 18.6 | 29.2 | -14.5 | -8.2 | 2.0 | 0.8 | 0.5 | 19.1 | 10.7 | 13.2 | 9.7 |
| 27.50 | 16.9 | 31.2 | -12.1 | -6.2 | 2.6 | 0.8 | 0.5 | 17.3 | 9.2 | 11.8 | 11.0 |
| 28.00 | 15.1 | 32.7 | -10.1 | -6.4 | 3.6 | 0.8 | 2.0 | 17.0 | 8.9 | 11.8 | 12.3 |
| 28.50 | 13.2 | 34.3 | -9.1 | -8.4 | 5.7 | 1.0 | 4.4 | 17.7 | 9.5 | 12.4 | 13.4 |
| 29.00 | 11.6 | 35.7 | -9.2 | -12.8 | 9.1 | 1.1 | 6.1 | 17.7 | 9.1 | 12.0 | 14.3 |
| 29.50 | 10.0 | 36.7 | -10.6 | -16.5 | 13.1 | 1.1 | 6.1 | 16.1 | 8.5 | 11.2 | 15.1 |
| 30.00 | 8.4 | 37.9 | -13.1 | -14.4 | 18.7 | 1.0 | 6.1 | 14.6 | 7.4 | 10.4 | 15.9 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5V, V_C = +5V, I_{CC} = 85mA, I_B = 4.5mA, I_C = 1.2mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 20.7 | 59.6 | -16.4 | -18.5 | 43.5 | 1.0 | - | - | 20.2 | 22.1 | 21.0 |
| 0.02 | 20.4 | 58.3 | -16.5 | -19.4 | 38.5 | 1.0 | 12.8 | 33.2 | 20.2 | 22.1 | 19.9 |
| 0.03 | 20.4 | 61.4 | -16.2 | -19.6 | 55.0 | 1.0 | 7.9 | 28.3 | 20.1 | 22.0 | 20.2 |
| 0.04 | 20.3 | 65.0 | -16.1 | -19.5 | 83.4 | 1.0 | 9.3 | 29.6 | 20.2 | 22.5 | 20.3 |
| 0.05 | 20.3 | 67.0 | -16.1 | -19.5 | 105.4 | 1.0 | 9.7 | 30.0 | 20.2 | 22.5 | 20.2 |
| 0.06 | 20.2 | 65.0 | -16.0 | -19.4 | 83.9 | 1.0 | 8.7 | 28.9 | 20.1 | 22.3 | 20.2 |
| 0.07 | 20.2 | 64.9 | -16.1 | -19.3 | 84.0 | 1.0 | 11.0 | 31.2 | 20.1 | 22.2 | 20.1 |
| 0.08 | 20.2 | 62.1 | -16.2 | -19.5 | 60.5 | 1.0 | 12.6 | 32.8 | 20.1 | 22.3 | 19.9 |
| 0.09 | 20.2 | 67.0 | -16.1 | -19.4 | 107.1 | 1.0 | 11.8 | 31.9 | 20.0 | 22.2 | 19.9 |
| 0.10 | 20.1 | 73.0 | -16.2 | -19.5 | 215.2 | 1.0 | 11.2 | 31.3 | 20.0 | 22.2 | 19.8 |
| 0.20 | 19.9 | 69.0 | -16.5 | -20.6 | 140.0 | 1.0 | 10.2 | 30.1 | 19.3 | 21.6 | 18.6 |
| 0.25 | 19.9 | 69.0 | -16.5 | -20.6 | 140.0 | 1.0 | 10.2 | 30.1 | 19.3 | 21.3 | 18.6 |
| 0.50 | 19.3 | 64.6 | -15.7 | -22.9 | 90.1 | 1.0 | 8.4 | 27.7 | 18.3 | 21.0 | 14.9 |
| 1.00 | 18.3 | 64.9 | -14.0 | -32.1 | 104.9 | 1.0 | 9.7 | 28.0 | 17.4 | 20.5 | 10.8 |
| 1.50 | 18.3 | 57.6 | -14.2 | -22.0 | 45.8 | 1.0 | 8.7 | 27.0 | 17.3 | 20.7 | 8.4 |
| 2.00 | 18.3 | 55.4 | -14.3 | -18.6 | 35.3 | 1.0 | 9.6 | 28.0 | 17.3 | 20.8 | 6.9 |
| 2.50 | 18.3 | 51.8 | -13.8 | -17.3 | 23.2 | 1.0 | 8.9 | 27.2 | 17.5 | 21.0 | 5.9 |
| 3.00 | 18.1 | 52.8 | -12.8 | -17.3 | 26.5 | 1.0 | 8.3 | 26.5 | 17.6 | 21.0 | 5.3 |
| 3.50 | 18.2 | 57.6 | -12.9 | -16.3 | 46.2 | 1.0 | 10.1 | 28.2 | 17.8 | 21.2 | 4.6 |
| 4.00 | 18.3 | 56.3 | -14.0 | -15.4 | 39.5 | 1.0 | 10.7 | 29.0 | 17.9 | 21.1 | 4.1 |
| 4.50 | 18.4 | 54.4 | -15.5 | -14.5 | 31.6 | 1.0 | 9.1 | 27.5 | 18.0 | 21.2 | 3.7 |
| 5.00 | 18.4 | 51.7 | -17.0 | -13.6 | 23.5 | 1.0 | 9.4 | 27.8 | 17.9 | 21.3 | 3.4 |
| 5.50 | 18.4 | 49.3 | -18.0 | -13.3 | 17.9 | 1.0 | 9.9 | 28.2 | 18.0 | 21.1 | 3.2 |
| 6.00 | 18.4 | 47.7 | -18.5 | -14.0 | 15.1 | 1.0 | 9.3 | 27.6 | 18.0 | 21.1 | 3.0 |
| 6.50 | 18.4 | 46.3 | -18.7 | -15.7 | 13.1 | 1.0 | 9.2 | 27.5 | 18.1 | 21.2 | 2.8 |
| 7.00 | 18.4 | 45.2 | -18.5 | -17.8 | 11.7 | 1.0 | 9.8 | 28.2 | 18.1 | 21.1 | 2.6 |
| 7.50 | 18.4 | 44.5 | -18.8 | -19.2 | 11.0 | 1.0 | 9.2 | 27.6 | 18.1 | 20.9 | 2.6 |
| 8.00 | 18.4 | 43.5 | -20.2 | -19.1 | 9.8 | 1.0 | 10.4 | 28.9 | 18.1 | 20.8 | 2.6 |
| 8.50 | 18.4 | 42.3 | -21.5 | -18.4 | 8.6 | 1.0 | 9.2 | 27.6 | 18.3 | 20.8 | 2.6 |
| 9.00 | 18.4 | 40.7 | -20.4 | -18.5 | 7.2 | 1.0 | 10.2 | 28.6 | 18.5 | 20.8 | 2.6 |
| 9.50 | 18.4 | 41.2 | -18.1 | -16.1 | 7.5 | 1.0 | 10.0 | 28.5 | 18.7 | 20.9 | 2.5 |
| 10.00 | 18.4 | 41.1 | -16.5 | -13.6 | 7.3 | 1.0 | 11.4 | 29.8 | 18.7 | 20.8 | 2.5 |
| 10.50 | 18.5 | 40.4 | -16.4 | -12.4 | 6.5 | 1.0 | 10.1 | 28.6 | 18.8 | 20.7 | 2.7 |
| 11.00 | 18.5 | 40.0 | -18.6 | -12.4 | 6.3 | 1.0 | 10.2 | 28.8 | 18.7 | 20.5 | 2.7 |
| 11.50 | 18.6 | 39.3 | -25.3 | -13.7 | 6.0 | 1.0 | 10.0 | 28.7 | 18.5 | 20.3 | 2.8 |
| 12.00 | 18.7 | 38.5 | -32.7 | -16.6 | 5.6 | 1.0 | 10.3 | 29.0 | 18.6 | 20.2 | 2.9 |
| 12.50 | 18.6 | 37.7 | -22.2 | -23.9 | 5.2 | 1.0 | 10.2 | 28.9 | 18.2 | 19.8 | 3.0 |
| 13.00 | 18.5 | 37.2 | -18.9 | -23.3 | 5.0 | 1.0 | 10.2 | 28.6 | 17.7 | 19.3 | 3.0 |
| 13.50 | 18.2 | 37.1 | -17.1 | -16.9 | 5.0 | 1.0 | 10.2 | 28.3 | 17.7 | 19.4 | 3.2 |
| 14.00 | 17.9 | 37.8 | -16.6 | -15.4 | 5.6 | 1.0 | 11.9 | 29.8 | 17.7 | 19.2 | 3.5 |
| 14.50 | 17.7 | 39.5 | -17.3 | -13.9 | 6.8 | 1.0 | 10.8 | 28.5 | 17.5 | 19.1 | 3.7 |
| 15.00 | 17.9 | 37.9 | -20.2 | -12.6 | 5.6 | 0.9 | 11.3 | 29.1 | 17.8 | 19.4 | 3.7 |
| 15.50 | 18.1 | 36.5 | -22.7 | -11.9 | 4.7 | 0.9 | 10.7 | 28.8 | 17.9 | 19.4 | 3.6 |
| 16.00 | 18.3 | 35.7 | -22.3 | -11.7 | 4.2 | 0.9 | 9.8 | 28.1 | 18.1 | 19.4 | 3.7 |
| 16.50 | 18.4 | 35.0 | -22.2 | -10.8 | 3.8 | 0.9 | 10.5 | 28.9 | 17.9 | 19.2 | 3.8 |
| 17.00 | 18.5 | 34.6 | -23.5 | -10.0 | 3.5 | 0.9 | 10.3 | 28.9 | 17.6 | 19.0 | 3.9 |
| 17.50 | 18.8 | 33.6 | -24.8 | -9.8 | 3.1 | 0.9 | 10.2 | 28.9 | 17.6 | 18.9 | 4.0 |
| 18.00 | 19.1 | 32.3 | -27.9 | -10.4 | 2.6 | 0.9 | 7.6 | 26.7 | 17.5 | 18.8 | 4.2 |
| 18.50 | 19.3 | 31.3 | -25.6 | -11.9 | 2.4 | 0.9 | 7.0 | 26.3 | 16.9 | 18.4 | 4.3 |
| 19.00 | 19.4 | 31.0 | -16.4 | -18.4 | 2.4 | 1.0 | 7.9 | 27.3 | 16.2 | 17.9 | 4.4 |
| 19.50 | 19.2 | 31.3 | -12.2 | -19.4 | 2.4 | 1.0 | 6.9 | 26.1 | 16.3 | 17.9 | 4.4 |
| 20.00 | 18.8 | 31.4 | -11.9 | -13.4 | 2.5 | 1.0 | 8.6 | 27.4 | 16.7 | 18.0 | 4.3 |
| 20.50 | 18.8 | 31.2 | -14.7 | -13.8 | 2.5 | 1.0 | 8.1 | 26.9 | 16.7 | 18.0 | 4.4 |
| 21.00 | 19.1 | 30.6 | -19.3 | -16.7 | 2.3 | 0.9 | 8.7 | 27.9 | 16.6 | 17.8 | 4.3 |
| 21.50 | 19.4 | 30.5 | -21.5 | -19.1 | 2.3 | 0.9 | 7.1 | 26.5 | 16.5 | 17.8 | 4.4 |
| 22.00 | 19.5 | 30.1 | -26.4 | -16.6 | 2.2 | 0.9 | 7.1 | 26.6 | 16.3 | 17.8 | 4.6 |
| 22.50 | 19.5 | 29.9 | -23.8 | -13.3 | 2.1 | 0.9 | 6.7 | 26.2 | 16.1 | 17.7 | 4.7 |
| 23.00 | 19.5 | 29.8 | -21.2 | -12.8 | 2.1 | 0.9 | 5.1 | 24.7 | 15.8 | 17.5 | 4.8 |
| 23.50 | 19.6 | 29.7 | -26.0 | -13.5 | 2.1 | 0.9 | 4.8 | 24.3 | 15.4 | 17.0 | 5.0 |
| 24.00 | 19.4 | 29.8 | -22.1 | -11.6 | 2.1 | 0.9 | 4.4 | 23.8 | 14.8 | 16.6 | 5.2 |
| 24.50 | 19.2 | 29.9 | -14.5 | -10.7 | 2.0 | 0.9 | 4.3 | 23.5 | 14.8 | 16.7 | 5.6 |
| 25.00 | 19.3 | 29.7 | -12.5 | -11.9 | 2.0 | 0.9 | 4.2 | 23.5 | 14.6 | 16.7 | 5.8 |
| 25.50 | 19.5 | 29.2 | -13.5 | -13.7 | 1.9 | 0.9 | 3.2 | 22.7 | 14.5 | 16.5 | 6.1 |
| 26.00 | 20.1 | 28.4 | -17.3 | -20.0 | 1.8 | 0.9 | 2.0 | 22.1 | 13.8 | 15.4 | 6.5 |
| 26.50 | 20.7 | 27.7 | -18.0 | -16.3 | 1.5 | 0.9 | 1.2 | 21.9 | 12.9 | 14.5 | 7.0 |
| 27.00 | 20.5 | 28.2 | -14.5 | -7.4 | 1.4 | 0.7 | 0.6 | 21.1 | 12.0 | 13.9 | 7.9 |
| 27.50 | 19.4 | 29.6 | -11.9 | -5.0 | 1.5 | 0.7 | -0.4 | 19.0 | 10.1 | 12.1 | 9.0 |
| 28.00 | 17.7 | 31.3 | -9.7 | -5.3 | 2.0 | 0.8 | 1.9 | 19.6 | 9.6 | 12.0 | 10.3 |
| 28.50 | 15.6 | 33.1 | -8.4 | -6.2 | 3.1 | 0.9 | 4.2 | 19.8 | 10.4 | 12.9 | 11.6 |
| 29.00 | 13.6 | 35.0 | -8.0 | -10.3 | 5.7 | 1.1 | 5.8 | 19.4 | 10.2 | 12.5 | 12.6 |
| 29.50 | 12.0 | 35.7 | -8.7 | -16.5 | 8.5 | 1.1 | 6.5 | 18.5 | 9.7 | 12.2 | 13.5 |
| 30.00 | 10.2 | 37.0 | -11.5 | -11.8 | 12.4 | 1.0 | 6.6 | 16.7 | 8.8 | 11.3 | 14.2 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.4V, V_C = +5V, I_{CC} = 95mA, I_B = 5.1mA, I_C = 1.2mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 20.8 | 67.8 | -16.3 | -18.4 | 109.0 | 1.0 | - | - | 20.9 | 22.3 | 21.3 |
| 0.02 | 20.6 | 55.5 | -16.5 | -19.7 | 27.3 | 1.0 | 8.7 | 29.3 | 20.9 | 22.4 | 20.3 |
| 0.03 | 20.5 | 64.0 | -16.2 | -19.5 | 73.0 | 1.0 | 10.7 | 31.2 | 20.9 | 22.3 | 20.5 |
| 0.04 | 20.5 | 59.8 | -16.1 | -19.5 | 44.9 | 1.0 | 14.1 | 34.5 | 20.9 | 22.8 | 20.6 |
| 0.05 | 20.4 | 66.0 | -16.1 | -19.6 | 92.3 | 1.0 | 10.4 | 30.9 | 20.8 | 22.7 | 20.6 |
| 0.06 | 20.4 | 62.8 | -16.0 | -19.3 | 64.5 | 1.0 | 9.9 | 30.3 | 20.9 | 22.6 | 20.4 |
| 0.07 | 20.4 | 68.2 | -16.1 | -19.3 | 119.3 | 1.0 | 10.6 | 31.0 | 20.7 | 22.5 | 20.4 |
| 0.08 | 20.4 | 60.9 | -16.1 | -19.5 | 51.5 | 1.0 | 10.6 | 31.0 | 20.8 | 22.6 | 20.2 |
| 0.09 | 20.3 | 61.1 | -16.1 | -19.4 | 53.5 | 1.0 | 10.7 | 31.0 | 20.7 | 22.5 | 20.2 |
| 0.10 | 20.3 | 72.6 | -16.1 | -19.5 | 200.3 | 1.0 | 13.8 | 34.1 | 20.6 | 22.5 | 20.1 |
| 0.20 | 20.1 | 69.1 | -16.5 | -20.6 | 138.1 | 1.0 | 9.9 | 30.0 | 19.8 | 22.0 | 18.9 |
| 0.25 | 20.1 | 69.1 | -16.5 | -20.6 | 138.1 | 1.0 | 9.9 | 30.0 | 19.8 | 21.6 | 18.9 |
| 0.50 | 19.7 | 62.6 | -15.7 | -23.0 | 69.1 | 1.0 | 8.6 | 28.2 | 18.6 | 21.3 | 15.2 |
| 1.00 | 18.7 | 60.0 | -14.0 | -32.7 | 57.5 | 1.0 | 9.5 | 28.2 | 17.8 | 20.9 | 11.3 |
| 1.50 | 18.7 | 58.9 | -14.2 | -22.1 | 50.4 | 1.0 | 8.8 | 27.5 | 17.6 | 21.1 | 8.7 |
| 2.00 | 18.8 | 56.1 | -14.3 | -18.6 | 36.4 | 1.0 | 8.6 | 27.4 | 17.8 | 21.1 | 7.0 |
| 2.50 | 18.8 | 52.5 | -13.8 | -17.3 | 24.0 | 1.0 | 8.4 | 27.1 | 17.8 | 21.3 | 6.0 |
| 3.00 | 18.6 | 52.3 | -12.8 | -17.3 | 23.8 | 1.0 | 8.6 | 27.2 | 17.9 | 21.4 | 5.3 |
| 3.50 | 18.6 | 55.3 | -12.9 | -16.3 | 33.8 | 1.0 | 8.9 | 27.5 | 18.2 | 21.5 | 4.7 |
| 4.00 | 18.8 | 55.9 | -14.1 | -15.4 | 35.8 | 1.0 | 9.9 | 28.6 | 18.3 | 21.4 | 4.2 |
| 4.50 | 18.8 | 54.2 | -15.6 | -14.5 | 29.4 | 1.0 | 9.1 | 28.0 | 18.3 | 21.5 | 3.7 |
| 5.00 | 18.8 | 50.9 | -17.0 | -13.6 | 20.4 | 1.0 | 9.1 | 27.9 | 18.3 | 21.6 | 3.5 |
| 5.50 | 18.8 | 49.3 | -18.0 | -13.3 | 16.9 | 1.0 | 9.4 | 28.2 | 18.3 | 21.5 | 3.2 |
| 6.00 | 18.8 | 47.8 | -18.6 | -13.9 | 14.5 | 1.0 | 9.4 | 28.2 | 18.5 | 21.6 | 3.0 |
| 6.50 | 18.8 | 46.9 | -18.7 | -15.5 | 13.3 | 1.0 | 9.4 | 28.2 | 18.4 | 21.6 | 2.8 |
| 7.00 | 18.8 | 45.3 | -18.6 | -17.7 | 11.2 | 1.0 | 9.5 | 28.4 | 18.6 | 21.4 | 2.8 |
| 7.50 | 18.8 | 44.3 | -18.9 | -19.1 | 10.2 | 1.0 | 9.4 | 28.2 | 18.5 | 21.3 | 2.6 |
| 8.00 | 18.8 | 43.6 | -20.2 | -19.1 | 9.5 | 1.0 | 9.3 | 28.1 | 18.6 | 21.2 | 2.6 |
| 8.50 | 18.8 | 42.5 | -21.6 | -18.5 | 8.4 | 1.0 | 9.2 | 28.0 | 18.8 | 21.3 | 2.6 |
| 9.00 | 18.8 | 41.0 | -20.5 | -18.7 | 7.1 | 1.0 | 9.8 | 28.7 | 19.0 | 21.3 | 2.6 |
| 9.50 | 18.9 | 41.6 | -18.2 | -16.3 | 7.5 | 1.0 | 10.3 | 29.2 | 19.1 | 21.4 | 2.6 |
| 10.00 | 18.9 | 41.2 | -16.6 | -13.8 | 7.0 | 1.0 | 9.8 | 28.7 | 19.2 | 21.3 | 2.6 |
| 10.50 | 18.9 | 40.8 | -16.4 | -12.4 | 6.5 | 1.0 | 10.5 | 29.4 | 19.2 | 21.2 | 2.7 |
| 11.00 | 19.0 | 40.0 | -18.4 | -12.4 | 6.0 | 1.0 | 11.0 | 30.0 | 19.2 | 21.0 | 2.7 |
| 11.50 | 19.1 | 39.1 | -24.7 | -13.6 | 5.6 | 1.0 | 10.1 | 29.2 | 19.0 | 20.7 | 2.8 |
| 12.00 | 19.1 | 38.5 | -33.6 | -16.4 | 5.3 | 1.0 | 9.3 | 28.4 | 19.0 | 20.7 | 2.8 |
| 12.50 | 19.1 | 37.6 | -22.4 | -23.4 | 4.9 | 1.0 | 9.5 | 28.6 | 18.6 | 20.3 | 2.9 |
| 13.00 | 18.9 | 37.2 | -18.9 | -24.2 | 4.7 | 1.0 | 9.9 | 28.8 | 18.1 | 19.8 | 3.0 |
| 13.50 | 18.6 | 37.0 | -17.0 | -17.3 | 4.7 | 1.0 | 10.6 | 29.3 | 18.2 | 19.9 | 3.2 |
| 14.00 | 18.3 | 38.0 | -16.4 | -15.7 | 5.4 | 1.0 | 11.4 | 29.7 | 18.2 | 19.8 | 3.4 |
| 14.50 | 18.2 | 39.4 | -17.1 | -14.0 | 6.5 | 1.0 | 10.3 | 28.4 | 18.0 | 19.7 | 3.7 |
| 15.00 | 18.3 | 37.8 | -19.9 | -12.6 | 5.3 | 0.9 | 10.9 | 29.2 | 18.4 | 20.0 | 3.6 |
| 15.50 | 18.5 | 36.7 | -22.3 | -11.9 | 4.6 | 0.9 | 10.0 | 28.5 | 18.4 | 20.0 | 3.6 |
| 16.00 | 18.7 | 35.8 | -21.9 | -11.6 | 4.0 | 0.9 | 9.7 | 28.4 | 18.6 | 20.0 | 3.6 |
| 16.50 | 18.8 | 35.2 | -21.7 | -10.7 | 3.7 | 0.9 | 8.4 | 27.2 | 18.6 | 19.9 | 3.8 |
| 17.00 | 18.9 | 34.8 | -22.9 | -9.9 | 3.4 | 0.9 | 9.5 | 28.4 | 18.3 | 19.6 | 3.9 |
| 17.50 | 19.2 | 33.7 | -24.0 | -9.6 | 2.9 | 0.9 | 8.5 | 27.7 | 18.2 | 19.6 | 4.0 |
| 18.00 | 19.5 | 32.5 | -27.1 | -10.0 | 2.5 | 0.9 | 7.7 | 27.2 | 18.1 | 19.5 | 4.2 |
| 18.50 | 19.8 | 31.4 | -27.1 | -11.4 | 2.2 | 0.9 | 6.3 | 26.1 | 17.5 | 19.0 | 4.4 |
| 19.00 | 19.9 | 31.2 | -16.7 | -17.2 | 2.2 | 1.0 | 7.3 | 27.2 | 16.6 | 18.5 | 4.4 |
| 19.50 | 19.7 | 31.2 | -12.1 | -19.8 | 2.3 | 1.0 | 6.5 | 26.2 | 16.7 | 18.4 | 4.3 |
| 20.00 | 19.3 | 31.6 | -11.7 | -13.4 | 2.4 | 1.0 | 8.2 | 27.5 | 17.1 | 18.6 | 4.2 |
| 20.50 | 19.3 | 31.2 | -14.4 | -13.6 | 2.3 | 0.9 | 8.1 | 27.4 | 17.2 | 18.6 | 4.3 |
| 21.00 | 19.6 | 30.9 | -18.9 | -16.5 | 2.3 | 0.9 | 8.0 | 27.6 | 17.1 | 18.5 | 4.3 |
| 21.50 | 19.8 | 30.4 | -21.0 | -19.2 | 2.2 | 0.9 | 6.3 | 26.1 | 17.0 | 18.4 | 4.4 |
| 22.00 | 20.0 | 30.1 | -26.3 | -17.0 | 2.1 | 0.9 | 6.4 | 26.4 | 17.0 | 18.4 | 4.6 |
| 22.50 | 20.0 | 29.9 | -24.5 | -13.7 | 2.0 | 0.9 | 6.7 | 26.7 | 16.7 | 18.4 | 4.6 |
| 23.00 | 20.0 | 29.8 | -21.1 | -13.2 | 2.0 | 0.9 | 5.6 | 25.7 | 16.4 | 18.1 | 4.7 |
| 23.50 | 20.0 | 29.7 | -25.5 | -14.1 | 2.0 | 0.9 | 4.2 | 24.2 | 15.8 | 17.6 | 4.8 |
| 24.00 | 19.9 | 29.9 | -22.4 | -12.0 | 2.0 | 0.9 | 4.4 | 24.2 | 15.4 | 17.1 | 5.2 |
| 24.50 | 19.7 | 30.1 | -14.5 | -10.9 | 2.0 | 0.9 | 4.0 | 23.7 | 15.3 | 17.3 | 5.5 |
| 25.00 | 19.7 | 29.9 | -12.3 | -11.8 | 2.0 | 0.9 | 4.0 | 23.7 | 15.2 | 17.3 | 5.8 |
| 25.50 | 19.9 | 29.4 | -13.1 | -13.3 | 1.9 | 0.9 | 3.2 | 23.0 | 15.1 | 17.0 | 6.1 |
| 26.00 | 20.4 | 28.7 | -16.2 | -17.4 | 1.8 | 0.9 | 2.2 | 22.6 | 14.5 | 15.9 | 6.3 |
| 26.50 | 21.2 | 27.9 | -17.4 | -20.5 | 1.5 | 0.9 | 0.9 | 22.1 | 13.5 | 15.1 | 6.9 |
| 27.00 | 21.3 | 28.0 | -14.3 | -8.3 | 1.3 | 0.8 | -0.2 | 21.1 | 12.5 | 14.4 | 7.6 |
| 27.50 | 20.4 | 29.0 | -11.7 | -5.0 | 1.3 | 0.6 | -1.4 | 19.1 | 10.2 | 12.4 | 8.8 |
| 28.00 | 18.7 | 30.9 | -9.3 | -5.1 | 1.7 | 0.7 | 0.4 | 19.1 | 9.4 | 11.9 | 10.0 |
| 28.50 | 16.6 | 33.0 | -8.1 | -5.6 | 2.6 | 0.8 | 3.1 | 19.7 | 10.4 | 13.1 | 11.3 |
| 29.00 | 14.5 | 34.3 | -7.7 | -9.2 | 4.6 | 1.0 | 5.4 | 20.0 | 10.3 | 12.9 | 12.4 |
| 29.50 | 12.9 | 35.4 | -8.4 | -15.4 | 7.2 | 1.1 | 5.8 | 18.6 | 10.0 | 12.6 | 13.2 |
| 30.00 | 11.1 | 36.9 | -11.2 | -11.7 | 11.0 | 1.0 | 6.5 | 17.5 | 9.2 | 11.8 | 13.9 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.8V, V_C = +5V, I_{CC} = 105mA, I_B = 5.6mA, I_C = 1.3mA @ Temperature = -45°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 20.9 | 59.8 | -16.2 | -18.5 | 43.0 | 1.0 | - | - | 21.5 | 22.6 | 21.5 |
| 0.02 | 20.7 | 54.1 | -16.6 | -19.4 | 22.7 | 1.0 | 9.8 | 30.5 | 21.5 | 22.6 | 20.6 |
| 0.03 | 20.7 | 61.2 | -16.2 | -19.6 | 51.8 | 1.0 | 9.8 | 30.4 | 21.4 | 22.5 | 20.9 |
| 0.04 | 20.6 | 57.0 | -16.0 | -19.6 | 32.2 | 1.0 | 14.3 | 34.9 | 21.6 | 23.0 | 20.8 |
| 0.05 | 20.6 | 66.8 | -16.1 | -19.5 | 99.5 | 1.0 | 14.2 | 34.8 | 21.5 | 23.0 | 20.9 |
| 0.06 | 20.5 | 61.9 | -16.0 | -19.3 | 56.7 | 1.0 | 9.3 | 29.9 | 21.4 | 22.8 | 20.8 |
| 0.07 | 20.5 | 65.7 | -16.1 | -19.4 | 88.6 | 1.0 | 12.2 | 32.7 | 21.3 | 22.7 | 20.8 |
| 0.08 | 20.5 | 61.0 | -16.1 | -19.3 | 51.5 | 1.0 | 9.8 | 30.3 | 21.3 | 22.8 | 20.6 |
| 0.09 | 20.5 | 69.9 | -16.1 | -19.4 | 143.8 | 1.0 | 14.2 | 34.6 | 21.2 | 22.8 | 20.5 |
| 0.10 | 20.5 | 61.0 | -16.1 | -19.5 | 51.7 | 1.0 | 9.9 | 30.3 | 21.1 | 22.7 | 20.4 |
| 0.20 | 20.3 | 82.4 | -16.4 | -20.6 | 619.4 | 1.0 | 10.1 | 30.4 | 20.4 | 22.3 | 19.3 |
| 0.25 | 20.3 | 82.4 | -16.4 | -20.6 | 619.4 | 1.0 | 10.1 | 30.4 | 20.4 | 22.0 | 19.3 |
| 0.50 | 20.0 | 67.3 | -15.7 | -23.1 | 113.4 | 1.0 | 8.2 | 28.2 | 19.1 | 21.6 | 15.5 |
| 1.00 | 19.0 | 60.5 | -14.0 | -33.0 | 58.4 | 1.0 | 9.3 | 28.3 | 18.1 | 21.1 | 11.4 |
| 1.50 | 19.0 | 58.4 | -14.2 | -22.1 | 46.1 | 1.0 | 8.2 | 27.2 | 18.1 | 21.5 | 8.9 |
| 2.00 | 19.1 | 54.8 | -14.3 | -18.6 | 30.0 | 1.0 | 8.6 | 27.8 | 18.1 | 21.5 | 7.2 |
| 2.50 | 19.1 | 51.7 | -13.9 | -17.4 | 21.0 | 1.0 | 8.9 | 28.0 | 18.2 | 21.7 | 6.2 |
| 3.00 | 18.9 | 52.4 | -12.8 | -17.4 | 23.2 | 1.0 | 8.1 | 27.0 | 18.3 | 21.8 | 5.4 |
| 3.50 | 18.9 | 56.9 | -12.9 | -16.3 | 38.9 | 1.0 | 9.2 | 28.1 | 18.5 | 21.9 | 4.9 |
| 4.00 | 19.1 | 56.2 | -14.1 | -15.4 | 35.5 | 1.0 | 9.4 | 28.5 | 18.6 | 21.8 | 4.3 |
| 4.50 | 19.2 | 54.2 | -15.6 | -14.5 | 28.5 | 1.0 | 8.5 | 27.6 | 18.7 | 21.9 | 3.9 |
| 5.00 | 19.2 | 51.2 | -17.1 | -13.5 | 20.1 | 1.0 | 8.5 | 27.7 | 18.6 | 21.9 | 3.6 |
| 5.50 | 19.2 | 49.6 | -18.0 | -13.2 | 16.9 | 1.0 | 9.9 | 29.1 | 18.7 | 21.8 | 3.3 |
| 6.00 | 19.2 | 48.1 | -18.6 | -13.8 | 14.5 | 1.0 | 9.3 | 28.4 | 18.8 | 21.9 | 3.1 |
| 6.50 | 19.2 | 46.2 | -18.8 | -15.4 | 11.8 | 1.0 | 9.0 | 28.2 | 18.8 | 22.0 | 2.9 |
| 7.00 | 19.2 | 46.0 | -18.6 | -17.5 | 11.8 | 1.0 | 9.4 | 28.5 | 18.9 | 21.9 | 2.7 |
| 7.50 | 19.2 | 44.7 | -18.9 | -19.0 | 10.3 | 1.0 | 9.1 | 28.3 | 19.0 | 21.8 | 2.7 |
| 8.00 | 19.2 | 43.0 | -20.2 | -19.0 | 8.4 | 1.0 | 9.3 | 28.4 | 19.0 | 21.6 | 2.6 |
| 8.50 | 19.2 | 42.3 | -21.6 | -18.6 | 7.9 | 1.0 | 8.9 | 28.1 | 19.2 | 21.7 | 2.7 |
| 9.00 | 19.2 | 41.0 | -20.6 | -18.9 | 6.9 | 1.0 | 9.7 | 28.9 | 19.3 | 21.8 | 2.6 |
| 9.50 | 19.2 | 41.3 | -18.2 | -16.5 | 6.9 | 1.0 | 9.7 | 28.9 | 19.6 | 21.9 | 2.6 |
| 10.00 | 19.2 | 41.3 | -16.6 | -13.9 | 6.8 | 1.0 | 9.2 | 28.4 | 19.6 | 21.8 | 2.6 |
| 10.50 | 19.2 | 41.1 | -16.3 | -12.5 | 6.5 | 1.0 | 9.9 | 29.1 | 19.6 | 21.6 | 2.7 |
| 11.00 | 19.3 | 40.1 | -18.3 | -12.4 | 5.8 | 1.0 | 8.9 | 28.3 | 19.5 | 21.4 | 2.7 |
| 11.50 | 19.4 | 39.0 | -24.3 | -13.6 | 5.3 | 1.0 | 9.3 | 28.7 | 19.3 | 21.2 | 2.8 |
| 12.00 | 19.4 | 38.5 | -34.4 | -16.2 | 5.1 | 1.0 | 8.9 | 28.4 | 19.3 | 21.2 | 2.9 |
| 12.50 | 19.4 | 37.8 | -22.7 | -22.9 | 4.8 | 1.0 | 9.2 | 28.7 | 19.0 | 20.7 | 2.9 |
| 13.00 | 19.3 | 37.2 | -18.9 | -25.2 | 4.6 | 1.0 | 9.2 | 28.4 | 18.6 | 20.3 | 3.0 |
| 13.50 | 19.0 | 37.3 | -17.0 | -17.8 | 4.7 | 1.0 | 9.2 | 28.2 | 18.6 | 20.4 | 3.2 |
| 14.00 | 18.7 | 38.1 | -16.3 | -16.0 | 5.3 | 1.0 | 10.5 | 29.2 | 18.6 | 20.3 | 3.5 |
| 14.50 | 18.5 | 39.4 | -17.0 | -14.0 | 6.2 | 1.0 | 9.6 | 28.1 | 18.5 | 20.3 | 3.7 |
| 15.00 | 18.7 | 37.9 | -19.7 | -12.6 | 5.2 | 0.9 | 10.0 | 28.7 | 18.8 | 20.5 | 3.6 |
| 15.50 | 18.8 | 36.7 | -21.9 | -11.9 | 4.4 | 0.9 | 9.5 | 28.3 | 18.9 | 20.5 | 3.5 |
| 16.00 | 19.0 | 35.8 | -21.4 | -11.6 | 3.9 | 0.9 | 9.2 | 28.2 | 19.2 | 20.5 | 3.7 |
| 16.50 | 19.1 | 35.2 | -21.3 | -10.6 | 3.5 | 0.9 | 9.4 | 28.5 | 19.1 | 20.4 | 3.9 |
| 17.00 | 19.3 | 35.0 | -22.3 | -9.7 | 3.3 | 0.9 | 8.0 | 27.2 | 18.8 | 20.1 | 3.9 |
| 17.50 | 19.5 | 33.7 | -23.3 | -9.3 | 2.8 | 0.9 | 7.8 | 27.3 | 18.8 | 20.1 | 4.1 |
| 18.00 | 19.9 | 32.4 | -26.3 | -9.7 | 2.4 | 0.9 | 7.6 | 27.4 | 18.7 | 20.0 | 4.2 |
| 18.50 | 20.1 | 31.4 | -28.5 | -10.9 | 2.2 | 0.9 | 6.0 | 26.1 | 17.8 | 19.5 | 4.4 |
| 19.00 | 20.3 | 31.1 | -16.9 | -16.3 | 2.1 | 0.9 | 6.3 | 26.6 | 16.9 | 18.9 | 4.4 |
| 19.50 | 20.1 | 31.3 | -12.0 | -20.3 | 2.2 | 1.0 | 6.5 | 26.6 | 17.0 | 18.9 | 4.3 |
| 20.00 | 19.6 | 31.5 | -11.5 | -13.4 | 2.3 | 1.0 | 8.0 | 27.6 | 17.4 | 19.1 | 4.3 |
| 20.50 | 19.6 | 31.3 | -14.1 | -13.4 | 2.3 | 0.9 | 7.8 | 27.4 | 17.7 | 19.1 | 4.3 |
| 21.00 | 19.9 | 30.9 | -18.5 | -16.3 | 2.2 | 0.9 | 7.3 | 27.2 | 17.4 | 19.0 | 4.2 |
| 21.50 | 20.1 | 30.5 | -20.6 | -19.1 | 2.1 | 0.9 | 6.7 | 26.8 | 17.4 | 18.9 | 4.4 |
| 22.00 | 20.3 | 30.2 | -26.0 | -17.4 | 2.0 | 0.9 | 6.8 | 27.1 | 17.3 | 19.0 | 4.5 |
| 22.50 | 20.4 | 30.0 | -25.0 | -14.2 | 1.9 | 0.9 | 5.6 | 26.0 | 17.1 | 18.9 | 4.6 |
| 23.00 | 20.4 | 29.8 | -21.0 | -13.7 | 1.9 | 0.9 | 4.7 | 25.1 | 16.7 | 18.6 | 4.6 |
| 23.50 | 20.4 | 29.7 | -25.2 | -14.6 | 1.9 | 0.9 | 3.5 | 23.9 | 16.2 | 18.0 | 4.8 |
| 24.00 | 20.2 | 29.9 | -22.7 | -12.4 | 1.9 | 0.9 | 4.2 | 24.4 | 15.7 | 17.5 | 5.1 |
| 24.50 | 20.0 | 30.1 | -14.5 | -11.0 | 1.9 | 0.9 | 3.6 | 23.6 | 15.8 | 17.8 | 5.5 |
| 25.00 | 20.0 | 29.9 | -12.2 | -11.8 | 1.9 | 0.9 | 3.8 | 23.8 | 15.6 | 17.7 | 5.7 |
| 25.50 | 20.1 | 29.6 | -12.8 | -12.9 | 1.9 | 0.9 | 2.7 | 22.8 | 15.5 | 17.3 | 6.0 |
| 26.00 | 20.6 | 28.8 | -15.6 | -15.6 | 1.7 | 0.9 | 2.1 | 22.7 | 15.0 | 16.4 | 6.3 |
| 26.50 | 21.4 | 28.0 | -16.9 | -27.7 | 1.5 | 0.9 | 0.6 | 22.0 | 14.1 | 15.5 | 6.7 |
| 27.00 | 21.8 | 27.9 | -14.2 | -9.5 | 1.3 | 0.8 | -0.9 | 21.0 | 12.8 | 14.9 | 7.5 |
| 27.50 | 21.2 | 28.7 | -11.5 | -5.0 | 1.1 | 0.6 | -2.7 | 18.5 | 10.3 | 12.7 | 8.6 |
| 28.00 | 19.5 | 30.6 | -9.1 | -4.9 | 1.5 | 0.7 | -1.1 | 18.5 | 9.0 | 11.8 | 9.8 |
| 28.50 | 17.4 | 32.6 | -7.9 | -5.1 | 2.2 | 0.8 | 2.0 | 19.3 | 10.2 | 13.1 | 11.1 |
| 29.00 | 15.2 | 34.1 | -7.5 | -8.3 | 3.9 | 1.0 | 4.6 | 19.8 | 10.3 | 13.1 | 12.1 |
| 29.50 | 13.6 | 34.7 | -8.2 | -14.3 | 6.0 | 1.1 | 5.0 | 18.7 | 10.1 | 12.9 | 13.1 |
| 30.00 | 11.9 | 36.2 | -10.9 | -11.6 | 9.3 | 1.0 | 5.9 | 17.7 | 9.4 | 12.2 | 13.8 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{cc} = +5V, V_B = +5V, V_C = +5V, I_{cc} = 85mA, I_B = 4.6mA, I_C = 1.3mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.4 | 66.5 | -16.4 | -17.8 | 124.0 | 1.0 | - | - | 20.1 | 21.6 | 22.0 |
| 0.02 | 18.2 | 63.3 | -16.5 | -18.7 | 87.4 | 1.0 | 14.7 | 32.9 | 19.8 | 21.4 | 21.4 |
| 0.03 | 18.1 | 58.6 | -16.3 | -19.0 | 51.3 | 1.0 | 13.9 | 32.1 | 19.9 | 21.6 | 21.5 |
| 0.04 | 18.1 | 55.2 | -16.1 | -19.1 | 35.0 | 1.0 | 12.7 | 30.8 | 19.9 | 21.8 | 21.5 |
| 0.05 | 18.0 | 68.6 | -16.1 | -19.0 | 164.4 | 1.0 | 11.8 | 29.8 | 19.9 | 21.8 | 21.5 |
| 0.06 | 18.0 | 58.3 | -16.1 | -18.9 | 50.4 | 1.0 | 12.8 | 30.8 | 19.9 | 21.7 | 21.5 |
| 0.07 | 18.0 | 63.8 | -16.1 | -18.9 | 94.8 | 1.0 | 13.2 | 31.2 | 19.8 | 21.6 | 21.4 |
| 0.08 | 17.9 | 60.3 | -16.1 | -18.9 | 64.0 | 1.0 | 11.5 | 29.4 | 19.7 | 21.7 | 21.3 |
| 0.09 | 17.9 | 65.6 | -16.1 | -19.0 | 118.2 | 1.0 | 11.9 | 29.9 | 19.7 | 21.6 | 21.2 |
| 0.10 | 17.9 | 65.8 | -16.1 | -19.1 | 120.8 | 1.0 | 11.6 | 29.5 | 19.6 | 21.6 | 21.1 |
| 0.20 | 17.7 | 67.5 | -16.4 | -20.0 | 151.6 | 1.0 | 12.1 | 29.8 | 19.0 | 21.4 | 19.9 |
| 0.25 | 17.7 | 67.5 | -16.4 | -20.0 | 151.6 | 1.0 | 12.1 | 29.8 | 19.0 | 21.1 | 19.9 |
| 0.50 | 17.2 | 66.3 | -15.7 | -21.1 | 139.8 | 1.0 | 10.9 | 28.1 | 17.8 | 20.9 | 16.1 |
| 1.00 | 16.2 | 65.8 | -14.2 | -27.8 | 149.3 | 1.0 | 10.5 | 26.7 | 16.8 | 20.4 | 12.3 |
| 1.50 | 16.2 | 59.1 | -14.2 | -21.3 | 69.3 | 1.0 | 10.1 | 26.3 | 16.5 | 20.5 | 9.8 |
| 2.00 | 16.2 | 55.4 | -14.1 | -18.2 | 44.8 | 1.0 | 10.2 | 26.5 | 16.6 | 20.6 | 8.2 |
| 2.50 | 16.2 | 53.4 | -13.7 | -16.9 | 35.5 | 1.0 | 10.4 | 26.6 | 16.8 | 20.7 | 7.2 |
| 3.00 | 16.1 | 52.9 | -13.0 | -16.5 | 34.1 | 1.0 | 11.0 | 27.0 | 17.0 | 20.9 | 6.6 |
| 3.50 | 16.1 | 56.5 | -13.4 | -15.8 | 52.2 | 1.0 | 10.7 | 26.8 | 17.1 | 21.0 | 6.0 |
| 4.00 | 16.2 | 56.7 | -14.5 | -15.1 | 53.1 | 1.0 | 10.8 | 27.0 | 17.2 | 21.0 | 5.5 |
| 4.50 | 16.3 | 53.0 | -16.1 | -14.3 | 34.9 | 1.0 | 11.1 | 27.3 | 17.1 | 21.0 | 5.1 |
| 5.00 | 16.2 | 50.4 | -17.9 | -13.5 | 26.4 | 1.0 | 10.9 | 27.2 | 17.1 | 20.8 | 4.6 |
| 5.50 | 16.2 | 49.1 | -19.0 | -13.6 | 23.0 | 1.0 | 10.5 | 26.6 | 17.1 | 21.0 | 4.4 |
| 6.00 | 16.1 | 47.0 | -19.3 | -14.9 | 18.5 | 1.0 | 10.3 | 26.5 | 17.3 | 21.2 | 4.3 |
| 6.50 | 16.1 | 46.2 | -19.7 | -17.0 | 17.2 | 1.0 | 11.0 | 27.1 | 17.3 | 20.8 | 4.2 |
| 7.00 | 16.1 | 45.1 | -19.7 | -18.7 | 15.5 | 1.0 | 10.4 | 26.5 | 17.3 | 20.7 | 4.2 |
| 7.50 | 16.1 | 44.1 | -20.3 | -19.3 | 14.0 | 1.0 | 11.3 | 27.4 | 17.4 | 20.7 | 4.2 |
| 8.00 | 16.1 | 43.4 | -21.9 | -18.8 | 13.0 | 1.0 | 10.8 | 26.9 | 17.4 | 20.7 | 4.2 |
| 8.50 | 16.0 | 42.1 | -22.8 | -18.0 | 11.2 | 1.0 | 11.2 | 27.2 | 17.5 | 20.6 | 4.4 |
| 9.00 | 16.0 | 41.0 | -20.0 | -16.8 | 9.9 | 1.0 | 11.2 | 27.3 | 17.7 | 20.4 | 4.3 |
| 9.50 | 16.0 | 41.5 | -17.6 | -14.5 | 10.3 | 1.0 | 11.7 | 27.7 | 17.8 | 20.5 | 4.3 |
| 10.00 | 16.0 | 41.1 | -16.7 | -12.8 | 9.7 | 1.0 | 11.4 | 27.4 | 17.9 | 20.5 | 4.5 |
| 10.50 | 16.0 | 40.2 | -17.8 | -12.3 | 8.8 | 1.0 | 11.2 | 27.2 | 17.8 | 20.0 | 4.5 |
| 11.00 | 16.1 | 39.5 | -21.3 | -12.7 | 8.2 | 1.0 | 11.0 | 27.1 | 17.9 | 20.1 | 4.6 |
| 11.50 | 16.1 | 39.1 | -32.1 | -14.2 | 8.0 | 1.0 | 11.2 | 27.3 | 17.8 | 19.8 | 4.6 |
| 12.00 | 16.1 | 38.2 | -28.4 | -18.2 | 7.5 | 1.0 | 10.4 | 26.5 | 17.7 | 19.6 | 4.7 |
| 12.50 | 16.0 | 37.5 | -21.1 | -24.0 | 7.1 | 1.0 | 11.3 | 27.2 | 17.1 | 19.0 | 4.9 |
| 13.00 | 15.7 | 37.2 | -18.8 | -18.7 | 7.0 | 1.0 | 11.1 | 26.9 | 16.7 | 18.5 | 5.1 |
| 13.50 | 15.4 | 37.2 | -18.5 | -15.9 | 7.2 | 1.0 | 12.5 | 27.9 | 17.0 | 18.8 | 5.4 |
| 14.00 | 15.1 | 38.1 | -19.3 | -14.9 | 8.2 | 1.0 | 12.1 | 27.2 | 17.1 | 18.9 | 5.7 |
| 14.50 | 15.1 | 38.5 | -21.1 | -13.7 | 8.6 | 1.0 | 12.3 | 27.3 | 17.1 | 18.9 | 5.9 |
| 15.00 | 15.3 | 37.1 | -24.3 | -12.8 | 7.2 | 0.9 | 11.5 | 26.8 | 17.1 | 19.0 | 5.8 |
| 15.50 | 15.4 | 36.1 | -24.3 | -12.1 | 6.2 | 0.9 | 10.9 | 26.4 | 17.2 | 18.9 | 5.8 |
| 16.00 | 15.5 | 35.5 | -22.4 | -11.1 | 5.7 | 0.9 | 11.0 | 26.5 | 16.9 | 18.6 | 6.0 |
| 16.50 | 15.6 | 34.7 | -22.5 | -10.7 | 5.1 | 0.9 | 10.8 | 26.5 | 17.0 | 18.7 | 6.1 |
| 17.00 | 15.8 | 34.0 | -25.1 | -11.4 | 4.7 | 0.9 | 10.1 | 25.9 | 16.5 | 18.1 | 6.2 |
| 17.50 | 16.1 | 32.9 | -27.9 | -12.4 | 4.2 | 0.9 | 9.8 | 25.9 | 16.2 | 18.0 | 6.3 |
| 18.00 | 16.1 | 32.1 | -24.7 | -13.8 | 3.8 | 0.9 | 9.0 | 25.2 | 16.0 | 17.9 | 6.6 |
| 18.50 | 16.1 | 31.6 | -19.3 | -18.2 | 3.7 | 1.0 | 9.2 | 25.4 | 15.8 | 17.8 | 6.8 |
| 19.00 | 16.0 | 31.6 | -15.3 | -26.3 | 3.8 | 1.0 | 8.2 | 24.2 | 15.1 | 17.1 | 6.8 |
| 19.50 | 15.7 | 31.8 | -14.1 | -16.6 | 3.9 | 1.0 | 8.1 | 23.9 | 15.0 | 16.8 | 6.9 |
| 20.00 | 15.7 | 31.6 | -15.9 | -15.7 | 3.9 | 1.0 | 8.5 | 24.1 | 14.8 | 16.6 | 6.9 |
| 20.50 | 15.8 | 31.2 | -19.9 | -17.8 | 3.7 | 1.0 | 9.2 | 24.9 | 15.1 | 17.0 | 7.0 |
| 21.00 | 15.9 | 30.9 | -23.2 | -19.8 | 3.6 | 1.0 | 8.2 | 24.2 | 14.9 | 17.0 | 7.1 |
| 21.50 | 16.0 | 30.7 | -25.6 | -18.1 | 3.5 | 1.0 | 8.2 | 24.1 | 14.5 | 16.6 | 7.1 |
| 22.00 | 15.9 | 30.6 | -25.3 | -14.7 | 3.5 | 0.9 | 7.4 | 23.3 | 14.0 | 16.2 | 7.3 |
| 22.50 | 15.7 | 30.5 | -23.0 | -12.8 | 3.5 | 0.9 | 7.0 | 22.7 | 13.8 | 16.2 | 7.5 |
| 23.00 | 15.5 | 30.5 | -23.5 | -12.0 | 3.5 | 0.9 | 6.9 | 22.4 | 13.3 | 15.7 | 7.9 |
| 23.50 | 15.3 | 30.6 | -23.2 | -11.5 | 3.6 | 0.9 | 6.1 | 21.4 | 12.9 | 15.3 | 8.2 |
| 24.00 | 15.2 | 30.5 | -18.4 | -12.0 | 3.6 | 0.9 | 4.5 | 19.7 | 12.3 | 14.8 | 8.6 |
| 24.50 | 15.3 | 30.4 | -16.3 | -13.8 | 3.6 | 1.0 | 4.9 | 20.2 | 11.7 | 14.4 | 8.9 |
| 25.00 | 15.4 | 30.2 | -17.4 | -17.4 | 3.6 | 1.0 | 4.9 | 20.3 | 11.1 | 14.0 | 9.4 |
| 25.50 | 15.3 | 29.9 | -25.1 | -31.2 | 3.6 | 1.0 | 3.3 | 18.7 | 10.1 | 12.7 | 10.0 |
| 26.00 | 14.9 | 30.1 | -21.9 | -14.6 | 3.8 | 1.0 | 2.4 | 17.2 | 8.9 | 11.3 | 10.6 |
| 26.50 | 13.8 | 31.1 | -17.2 | -10.0 | 4.5 | 0.9 | 3.8 | 17.6 | 9.3 | 11.8 | 11.5 |
| 27.00 | 12.4 | 32.7 | -15.8 | -8.8 | 6.0 | 0.9 | 4.9 | 17.3 | 9.0 | 11.5 | 12.5 |
| 27.50 | 10.7 | 34.0 | -13.6 | -8.7 | 8.4 | 0.9 | 6.5 | 17.1 | 8.0 | 10.5 | 13.6 |
| 28.00 | 9.0 | 35.8 | -11.5 | -9.5 | 12.3 | 0.9 | 6.8 | 15.8 | 7.8 | 10.4 | 14.7 |
| 28.50 | 7.4 | 37.3 | -10.6 | -12.5 | 18.3 | 1.0 | 7.4 | 14.8 | 7.3 | 9.9 | 15.8 |
| 29.00 | 6.0 | 37.2 | -10.5 | -20.7 | 22.6 | 1.1 | 7.4 | 13.4 | 6.4 | 9.1 | 16.6 |
| 29.50 | 4.6 | 38.7 | -11.5 | -21.7 | 32.5 | 1.1 | 7.0 | 11.5 | 5.2 | 8.2 | 17.5 |
| 30.00 | 3.1 | 40.4 | -13.3 | -16.6 | 48.1 | 1.0 | 7.1 | 10.2 | 3.4 | 6.7 | 18.3 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.4V, V_C = +5V, I_{CC} = 94mA, I_B = 5.2mA, I_C = 1.4mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.5 | 61.6 | -16.5 | -18.0 | 69.7 | 1.0 | - | - | 20.7 | 21.8 | 22.3 |
| 0.02 | 18.4 | 53.6 | -16.4 | -18.9 | 28.3 | 1.0 | 13.5 | 31.9 | 20.5 | 21.7 | 21.9 |
| 0.03 | 18.3 | 57.1 | -16.4 | -18.9 | 42.6 | 1.0 | 11.9 | 30.2 | 20.6 | 21.9 | 21.9 |
| 0.04 | 18.2 | 61.7 | -16.1 | -18.9 | 72.5 | 1.0 | 13.2 | 31.4 | 20.6 | 22.0 | 21.8 |
| 0.05 | 18.2 | 59.3 | -16.1 | -19.0 | 55.4 | 1.0 | 12.9 | 31.0 | 20.7 | 22.1 | 21.9 |
| 0.06 | 18.2 | 63.1 | -16.1 | -19.0 | 85.6 | 1.0 | 13.1 | 31.2 | 20.6 | 22.0 | 21.8 |
| 0.07 | 18.1 | 57.9 | -16.1 | -18.9 | 47.6 | 1.0 | 11.8 | 30.0 | 20.5 | 21.9 | 21.8 |
| 0.08 | 18.1 | 66.7 | -16.1 | -18.9 | 131.3 | 1.0 | 12.7 | 30.8 | 20.4 | 22.0 | 21.5 |
| 0.09 | 18.1 | 71.7 | -16.1 | -19.0 | 234.0 | 1.0 | 13.1 | 31.2 | 20.4 | 21.9 | 21.6 |
| 0.10 | 18.1 | 67.8 | -16.1 | -19.1 | 149.1 | 1.0 | 12.2 | 30.3 | 20.4 | 21.9 | 21.5 |
| 0.20 | 17.9 | 73.8 | -16.4 | -20.0 | 306.0 | 1.0 | 11.2 | 29.1 | 19.7 | 21.7 | 20.2 |
| 0.25 | 17.9 | 73.8 | -16.4 | -20.0 | 306.0 | 1.0 | 11.2 | 29.1 | 19.7 | 21.5 | 20.2 |
| 0.50 | 17.6 | 73.3 | -15.7 | -21.2 | 300.1 | 1.0 | 10.5 | 28.0 | 18.4 | 21.2 | 16.4 |
| 1.00 | 16.6 | 64.9 | -14.1 | -28.2 | 128.1 | 1.0 | 9.9 | 26.5 | 17.3 | 20.7 | 12.5 |
| 1.50 | 16.6 | 57.4 | -14.2 | -21.4 | 54.7 | 1.0 | 9.5 | 26.1 | 17.1 | 20.9 | 10.0 |
| 2.00 | 16.6 | 55.3 | -14.1 | -18.3 | 42.7 | 1.0 | 10.1 | 26.8 | 17.2 | 21.1 | 8.4 |
| 2.50 | 16.6 | 52.9 | -13.6 | -17.0 | 32.2 | 1.0 | 10.1 | 26.8 | 17.4 | 21.1 | 7.5 |
| 3.00 | 16.5 | 53.0 | -13.0 | -16.6 | 33.1 | 1.0 | 10.1 | 26.6 | 17.5 | 21.4 | 6.8 |
| 3.50 | 16.5 | 55.8 | -13.3 | -15.8 | 45.7 | 1.0 | 10.5 | 27.0 | 17.7 | 21.4 | 6.2 |
| 4.00 | 16.6 | 55.8 | -14.4 | -15.2 | 45.6 | 1.0 | 10.5 | 27.1 | 17.7 | 21.5 | 5.5 |
| 4.50 | 16.7 | 52.6 | -16.1 | -14.3 | 31.9 | 1.0 | 10.8 | 27.4 | 17.7 | 21.4 | 5.1 |
| 5.00 | 16.6 | 49.8 | -17.9 | -13.5 | 23.4 | 1.0 | 10.4 | 27.0 | 17.6 | 21.2 | 4.5 |
| 5.50 | 16.6 | 50.5 | -19.0 | -13.6 | 25.7 | 1.0 | 10.2 | 26.8 | 17.7 | 21.4 | 4.5 |
| 6.00 | 16.5 | 47.9 | -19.4 | -14.8 | 19.5 | 1.0 | 10.0 | 26.5 | 17.8 | 21.6 | 4.4 |
| 6.50 | 16.5 | 46.5 | -19.7 | -16.8 | 17.0 | 1.0 | 10.6 | 27.1 | 17.8 | 21.2 | 4.3 |
| 7.00 | 16.5 | 45.4 | -19.8 | -18.6 | 15.4 | 1.0 | 10.1 | 26.6 | 17.8 | 21.2 | 4.2 |
| 7.50 | 16.5 | 44.1 | -20.3 | -19.3 | 13.4 | 1.0 | 10.6 | 27.1 | 17.9 | 21.2 | 4.2 |
| 8.00 | 16.4 | 43.2 | -21.9 | -18.8 | 12.2 | 1.0 | 10.3 | 26.7 | 18.0 | 21.1 | 4.2 |
| 8.50 | 16.4 | 41.9 | -22.8 | -18.2 | 10.6 | 1.0 | 10.8 | 27.2 | 18.1 | 21.1 | 4.3 |
| 9.00 | 16.4 | 41.4 | -20.1 | -17.0 | 9.9 | 1.0 | 10.9 | 27.3 | 18.2 | 20.9 | 4.4 |
| 9.50 | 16.4 | 41.2 | -17.7 | -14.7 | 9.5 | 1.0 | 11.0 | 27.4 | 18.3 | 21.0 | 4.4 |
| 10.00 | 16.4 | 41.1 | -16.7 | -12.9 | 9.3 | 1.0 | 10.5 | 26.9 | 18.4 | 21.0 | 4.5 |
| 10.50 | 16.4 | 40.4 | -17.8 | -12.3 | 8.5 | 1.0 | 10.3 | 26.7 | 18.2 | 20.5 | 4.5 |
| 11.00 | 16.5 | 39.8 | -21.3 | -12.7 | 8.0 | 1.0 | 10.6 | 27.1 | 18.3 | 20.6 | 4.6 |
| 11.50 | 16.5 | 39.0 | -31.5 | -14.2 | 7.6 | 1.0 | 10.2 | 26.7 | 18.2 | 20.3 | 4.7 |
| 12.00 | 16.5 | 38.2 | -28.8 | -18.0 | 7.1 | 1.0 | 9.8 | 26.3 | 18.1 | 20.2 | 4.7 |
| 12.50 | 16.4 | 37.5 | -21.2 | -24.2 | 6.8 | 1.0 | 10.9 | 27.3 | 17.5 | 19.5 | 4.9 |
| 13.00 | 16.1 | 37.4 | -18.8 | -19.1 | 6.8 | 1.0 | 10.3 | 26.4 | 17.1 | 19.0 | 5.0 |
| 13.50 | 15.8 | 37.4 | -18.5 | -16.2 | 7.0 | 1.0 | 11.2 | 27.0 | 17.5 | 19.4 | 5.3 |
| 14.00 | 15.5 | 38.3 | -19.2 | -15.0 | 8.0 | 1.0 | 11.5 | 27.0 | 17.7 | 19.5 | 5.8 |
| 14.50 | 15.5 | 38.4 | -21.0 | -13.7 | 8.2 | 1.0 | 11.7 | 27.1 | 17.6 | 19.4 | 5.9 |
| 15.00 | 15.7 | 37.2 | -24.1 | -12.8 | 6.9 | 0.9 | 10.6 | 26.3 | 17.6 | 19.6 | 5.7 |
| 15.50 | 15.8 | 36.3 | -24.1 | -12.1 | 6.1 | 0.9 | 10.4 | 26.2 | 17.8 | 19.5 | 5.8 |
| 16.00 | 15.9 | 35.5 | -22.1 | -11.0 | 5.4 | 0.9 | 10.3 | 26.2 | 17.4 | 19.2 | 5.9 |
| 16.50 | 16.0 | 34.7 | -22.3 | -10.5 | 4.9 | 0.9 | 9.5 | 25.6 | 17.6 | 19.3 | 6.1 |
| 17.00 | 16.2 | 34.1 | -24.9 | -11.2 | 4.5 | 0.9 | 8.9 | 25.1 | 17.1 | 18.7 | 6.3 |
| 17.50 | 16.5 | 33.1 | -28.1 | -12.1 | 4.0 | 0.9 | 9.1 | 25.5 | 16.8 | 18.6 | 6.4 |
| 18.00 | 16.6 | 32.1 | -25.4 | -13.3 | 3.6 | 0.9 | 8.8 | 25.3 | 16.5 | 18.5 | 6.6 |
| 18.50 | 16.6 | 31.7 | -19.6 | -17.4 | 3.6 | 1.0 | 8.3 | 24.9 | 16.3 | 18.4 | 6.8 |
| 19.00 | 16.5 | 31.6 | -15.2 | -26.6 | 3.6 | 1.0 | 8.0 | 24.4 | 15.5 | 17.7 | 6.8 |
| 19.50 | 16.2 | 31.6 | -14.0 | -16.7 | 3.6 | 1.0 | 7.1 | 23.3 | 15.4 | 17.4 | 6.8 |
| 20.00 | 16.1 | 31.6 | -15.7 | -15.6 | 3.7 | 1.0 | 8.1 | 24.2 | 15.3 | 17.2 | 6.9 |
| 20.50 | 16.2 | 31.4 | -19.6 | -17.7 | 3.6 | 1.0 | 8.3 | 24.5 | 15.6 | 17.6 | 6.9 |
| 21.00 | 16.4 | 30.9 | -22.9 | -20.0 | 3.5 | 1.0 | 8.1 | 24.4 | 15.5 | 17.6 | 7.0 |
| 21.50 | 16.4 | 30.8 | -25.7 | -18.7 | 3.4 | 1.0 | 7.4 | 23.8 | 15.0 | 17.2 | 7.1 |
| 22.00 | 16.4 | 30.4 | -26.0 | -15.3 | 3.3 | 0.9 | 7.1 | 23.5 | 14.5 | 16.8 | 7.3 |
| 22.50 | 16.2 | 30.4 | -23.3 | -13.2 | 3.3 | 0.9 | 6.5 | 22.7 | 14.3 | 16.8 | 7.6 |
| 23.00 | 16.0 | 30.5 | -23.5 | -12.2 | 3.4 | 0.9 | 5.9 | 21.9 | 13.8 | 16.3 | 7.8 |
| 23.50 | 15.8 | 30.7 | -23.1 | -11.6 | 3.5 | 0.9 | 6.1 | 21.9 | 13.4 | 15.8 | 8.2 |
| 24.00 | 15.7 | 30.6 | -18.3 | -11.9 | 3.5 | 0.9 | 4.3 | 20.0 | 12.9 | 15.5 | 8.5 |
| 24.50 | 15.7 | 30.6 | -16.1 | -13.5 | 3.5 | 1.0 | 4.7 | 20.4 | 12.3 | 15.0 | 8.9 |
| 25.00 | 15.8 | 30.3 | -16.9 | -16.4 | 3.5 | 1.0 | 4.4 | 20.2 | 11.6 | 14.5 | 9.4 |
| 25.50 | 15.9 | 30.0 | -24.2 | -27.1 | 3.5 | 1.0 | 2.6 | 18.5 | 10.5 | 13.2 | 9.8 |
| 26.00 | 15.6 | 30.0 | -23.0 | -16.0 | 3.5 | 1.0 | 1.3 | 16.9 | 9.1 | 11.6 | 10.4 |
| 26.50 | 14.6 | 30.8 | -17.1 | -10.4 | 4.0 | 0.9 | 2.8 | 17.5 | 9.5 | 12.1 | 11.2 |
| 27.00 | 13.3 | 32.1 | -15.6 | -8.8 | 5.0 | 0.9 | 4.0 | 17.3 | 9.3 | 11.9 | 12.3 |
| 27.50 | 11.5 | 33.7 | -13.4 | -8.5 | 7.2 | 0.9 | 5.3 | 16.8 | 8.1 | 10.8 | 13.4 |
| 28.00 | 9.8 | 35.1 | -11.4 | -9.0 | 10.2 | 0.9 | 5.9 | 15.7 | 8.1 | 10.8 | 14.5 |
| 28.50 | 8.2 | 36.4 | -10.5 | -11.7 | 14.8 | 1.0 | 6.7 | 15.0 | 7.7 | 10.4 | 15.6 |
| 29.00 | 6.8 | 37.1 | -10.4 | -18.7 | 20.2 | 1.1 | 7.1 | 13.9 | 6.6 | 9.6 | 16.4 |
| 29.50 | 5.4 | 38.9 | -11.4 | -21.5 | 30.2 | 1.1 | 6.8 | 12.2 | 5.5 | 8.8 | 17.2 |
| 30.00 | 3.9 | 39.8 | -13.2 | -16.5 | 40.4 | 1.0 | 6.2 | 10.1 | 4.1 | 7.4 | 18.1 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.8V, V_C = +5V, I_{CC} = 104mA, I_B = 5.7mA, I_C = 1.4mA @ Temperature = +85°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.6 | 62.7 | -16.5 | -17.8 | 77.6 | 1.0 | - | - | 21.1 | 22.1 | 22.7 |
| 0.02 | 18.5 | 61.5 | -16.4 | -18.6 | 68.3 | 1.0 | 11.9 | 30.4 | 20.9 | 21.9 | 22.1 |
| 0.03 | 18.4 | 59.1 | -16.3 | -19.0 | 52.7 | 1.0 | 14.1 | 32.5 | 21.1 | 22.1 | 22.2 |
| 0.04 | 18.3 | 57.0 | -16.1 | -19.0 | 41.8 | 1.0 | 12.6 | 30.9 | 21.1 | 22.3 | 22.1 |
| 0.05 | 18.3 | 69.6 | -16.1 | -18.9 | 177.8 | 1.0 | 13.9 | 32.2 | 21.2 | 22.3 | 22.2 |
| 0.06 | 18.3 | 61.8 | -16.1 | -18.9 | 73.1 | 1.0 | 12.6 | 30.8 | 21.1 | 22.2 | 22.1 |
| 0.07 | 18.3 | 74.9 | -16.1 | -18.9 | 329.4 | 1.0 | 15.5 | 33.8 | 21.0 | 22.1 | 22.1 |
| 0.08 | 18.2 | 71.7 | -16.1 | -18.9 | 229.4 | 1.0 | 11.9 | 30.1 | 21.0 | 22.2 | 21.9 |
| 0.09 | 18.2 | 78.5 | -16.0 | -19.0 | 499.5 | 1.0 | 12.7 | 30.9 | 20.9 | 22.2 | 21.8 |
| 0.10 | 18.2 | 69.8 | -16.1 | -19.0 | 183.7 | 1.0 | 11.3 | 29.5 | 20.8 | 22.2 | 21.7 |
| 0.20 | 18.1 | 64.1 | -16.4 | -20.0 | 98.2 | 1.0 | 11.6 | 29.7 | 20.2 | 22.0 | 20.5 |
| 0.25 | 18.1 | 64.1 | -16.4 | -20.0 | 98.2 | 1.0 | 11.6 | 29.7 | 20.2 | 21.8 | 20.5 |
| 0.50 | 17.8 | 71.8 | -15.7 | -21.4 | 245.6 | 1.0 | 10.3 | 28.1 | 18.8 | 21.5 | 16.7 |
| 1.00 | 16.9 | 60.0 | -14.1 | -28.7 | 70.6 | 1.0 | 9.7 | 26.5 | 17.8 | 21.1 | 12.8 |
| 1.50 | 16.8 | 58.0 | -14.1 | -21.5 | 56.8 | 1.0 | 9.4 | 26.2 | 17.5 | 21.3 | 10.2 |
| 2.00 | 16.9 | 54.7 | -14.0 | -18.4 | 38.4 | 1.0 | 9.7 | 26.6 | 17.6 | 21.4 | 8.6 |
| 2.50 | 16.9 | 52.5 | -13.6 | -17.0 | 29.8 | 1.0 | 9.8 | 26.7 | 17.8 | 21.5 | 7.6 |
| 3.00 | 16.7 | 52.1 | -13.0 | -16.6 | 28.9 | 1.0 | 10.1 | 26.9 | 18.0 | 21.7 | 6.9 |
| 3.50 | 16.8 | 55.9 | -13.3 | -15.8 | 44.8 | 1.0 | 10.1 | 26.9 | 18.1 | 21.8 | 6.3 |
| 4.00 | 16.9 | 56.3 | -14.4 | -15.2 | 47.2 | 1.0 | 10.3 | 27.3 | 18.1 | 21.8 | 5.7 |
| 4.50 | 16.9 | 52.2 | -16.1 | -14.3 | 29.4 | 1.0 | 10.5 | 27.5 | 18.1 | 21.8 | 5.1 |
| 5.00 | 16.9 | 50.6 | -17.9 | -13.4 | 24.9 | 1.0 | 10.3 | 27.2 | 18.0 | 21.5 | 4.7 |
| 5.50 | 16.8 | 49.4 | -19.0 | -13.5 | 22.0 | 1.0 | 9.6 | 26.4 | 18.1 | 21.8 | 4.5 |
| 6.00 | 16.8 | 47.6 | -19.3 | -14.7 | 18.4 | 1.0 | 10.1 | 26.9 | 18.2 | 22.0 | 4.5 |
| 6.50 | 16.8 | 46.5 | -19.7 | -16.7 | 16.5 | 1.0 | 10.4 | 27.2 | 18.2 | 21.6 | 4.3 |
| 7.00 | 16.8 | 45.6 | -19.8 | -18.5 | 15.1 | 1.0 | 10.0 | 26.8 | 18.2 | 21.6 | 4.2 |
| 7.50 | 16.7 | 44.3 | -20.4 | -19.3 | 13.2 | 1.0 | 10.9 | 27.6 | 18.4 | 21.6 | 4.3 |
| 8.00 | 16.7 | 43.3 | -21.9 | -18.8 | 11.9 | 1.0 | 10.5 | 27.3 | 18.4 | 21.6 | 4.2 |
| 8.50 | 16.7 | 41.8 | -22.9 | -18.3 | 10.0 | 1.0 | 10.4 | 27.1 | 18.5 | 21.6 | 4.4 |
| 9.00 | 16.7 | 41.0 | -20.1 | -17.2 | 9.2 | 1.0 | 10.3 | 27.0 | 18.7 | 21.3 | 4.4 |
| 9.50 | 16.7 | 40.9 | -17.7 | -14.8 | 9.0 | 1.0 | 10.6 | 27.3 | 18.7 | 21.5 | 4.4 |
| 10.00 | 16.7 | 41.1 | -16.8 | -13.0 | 9.0 | 1.0 | 10.3 | 26.9 | 18.8 | 21.5 | 4.5 |
| 10.50 | 16.7 | 40.2 | -17.8 | -12.4 | 8.1 | 1.0 | 10.1 | 26.8 | 18.6 | 21.0 | 4.6 |
| 11.00 | 16.8 | 39.7 | -21.3 | -12.7 | 7.7 | 1.0 | 10.3 | 27.1 | 18.7 | 21.0 | 4.6 |
| 11.50 | 16.8 | 38.8 | -31.4 | -14.1 | 7.2 | 1.0 | 10.7 | 27.5 | 18.5 | 20.8 | 4.7 |
| 12.00 | 16.8 | 38.2 | -29.0 | -17.9 | 6.9 | 1.0 | 9.0 | 25.8 | 18.4 | 20.6 | 4.8 |
| 12.50 | 16.7 | 37.8 | -21.3 | -24.4 | 6.8 | 1.0 | 9.6 | 26.2 | 17.9 | 19.9 | 4.9 |
| 13.00 | 16.4 | 37.2 | -18.8 | -19.5 | 6.4 | 1.0 | 9.5 | 25.9 | 17.4 | 19.5 | 5.1 |
| 13.50 | 16.1 | 37.4 | -18.4 | -16.4 | 6.8 | 1.0 | 10.7 | 26.7 | 17.8 | 19.9 | 5.4 |
| 14.00 | 15.8 | 38.2 | -19.2 | -15.2 | 7.6 | 1.0 | 10.8 | 26.6 | 18.0 | 20.0 | 5.8 |
| 14.50 | 15.8 | 38.3 | -20.9 | -13.8 | 7.8 | 1.0 | 10.9 | 26.6 | 17.9 | 19.9 | 5.9 |
| 15.00 | 15.9 | 37.2 | -24.0 | -12.8 | 6.7 | 0.9 | 10.2 | 26.2 | 18.0 | 20.1 | 5.8 |
| 15.50 | 16.1 | 36.2 | -24.0 | -12.0 | 5.8 | 0.9 | 9.7 | 25.8 | 18.3 | 20.0 | 5.8 |
| 16.00 | 16.2 | 35.4 | -22.0 | -11.0 | 5.2 | 0.9 | 10.0 | 26.1 | 17.9 | 19.8 | 6.0 |
| 16.50 | 16.3 | 34.9 | -22.2 | -10.5 | 4.9 | 0.9 | 8.6 | 24.9 | 17.9 | 19.8 | 6.1 |
| 17.00 | 16.5 | 34.3 | -24.8 | -11.0 | 4.5 | 0.9 | 8.0 | 24.5 | 17.6 | 19.2 | 6.3 |
| 17.50 | 16.7 | 33.1 | -28.1 | -11.9 | 3.9 | 0.9 | 8.0 | 24.7 | 17.1 | 19.1 | 6.5 |
| 18.00 | 16.9 | 32.4 | -25.6 | -13.0 | 3.6 | 0.9 | 7.7 | 24.6 | 16.8 | 19.0 | 6.6 |
| 18.50 | 16.9 | 31.7 | -19.7 | -16.8 | 3.4 | 1.0 | 7.1 | 24.0 | 16.6 | 18.9 | 6.8 |
| 19.00 | 16.8 | 31.6 | -15.2 | -27.0 | 3.5 | 1.0 | 7.1 | 23.9 | 15.8 | 18.2 | 6.9 |
| 19.50 | 16.5 | 31.8 | -13.9 | -16.9 | 3.6 | 1.0 | 6.7 | 23.1 | 15.6 | 17.8 | 6.8 |
| 20.00 | 16.4 | 31.7 | -15.6 | -15.5 | 3.6 | 1.0 | 7.5 | 23.8 | 15.6 | 17.6 | 6.9 |
| 20.50 | 16.5 | 31.3 | -19.4 | -17.6 | 3.5 | 1.0 | 7.4 | 23.9 | 16.0 | 18.1 | 6.9 |
| 21.00 | 16.6 | 31.0 | -22.7 | -20.2 | 3.4 | 1.0 | 7.0 | 23.6 | 15.8 | 18.1 | 7.0 |
| 21.50 | 16.7 | 30.7 | -25.6 | -19.2 | 3.3 | 1.0 | 6.9 | 23.6 | 15.3 | 17.6 | 7.2 |
| 22.00 | 16.7 | 30.7 | -26.3 | -15.8 | 3.3 | 1.0 | 6.1 | 22.8 | 14.7 | 17.2 | 7.3 |
| 22.50 | 16.5 | 30.5 | -23.4 | -13.6 | 3.2 | 0.9 | 5.7 | 22.2 | 14.6 | 17.2 | 7.5 |
| 23.00 | 16.3 | 30.6 | -23.5 | -12.5 | 3.3 | 0.9 | 5.6 | 21.9 | 14.0 | 16.7 | 7.8 |
| 23.50 | 16.1 | 30.6 | -23.2 | -11.8 | 3.4 | 0.9 | 5.4 | 21.5 | 13.6 | 16.2 | 8.2 |
| 24.00 | 16.0 | 30.6 | -18.3 | -11.9 | 3.4 | 0.9 | 3.8 | 19.8 | 13.3 | 15.9 | 8.5 |
| 24.50 | 16.0 | 30.6 | -16.0 | -13.2 | 3.4 | 0.9 | 4.2 | 20.2 | 12.6 | 15.4 | 8.9 |
| 25.00 | 16.0 | 30.4 | -16.7 | -15.6 | 3.4 | 1.0 | 4.3 | 20.3 | 11.9 | 14.9 | 9.5 |
| 25.50 | 16.1 | 30.1 | -23.4 | -23.3 | 3.4 | 1.0 | 2.2 | 18.3 | 10.8 | 13.6 | 9.7 |
| 26.00 | 16.0 | 30.0 | -24.1 | -17.9 | 3.4 | 1.0 | 0.8 | 16.8 | 9.1 | 11.8 | 10.3 |
| 26.50 | 15.2 | 30.5 | -17.2 | -11.1 | 3.7 | 0.9 | 2.0 | 17.1 | 9.5 | 12.3 | 11.1 |
| 27.00 | 13.9 | 31.7 | -15.5 | -9.0 | 4.5 | 0.9 | 3.3 | 17.2 | 9.3 | 12.2 | 12.1 |
| 27.50 | 12.1 | 33.5 | -13.2 | -8.4 | 6.6 | 0.9 | 4.6 | 16.8 | 8.1 | 11.0 | 13.4 |
| 28.00 | 10.4 | 35.1 | -11.3 | -8.7 | 9.3 | 0.9 | 5.4 | 15.8 | 7.9 | 11.0 | 14.4 |
| 28.50 | 8.8 | 36.1 | -10.3 | -10.9 | 13.2 | 1.0 | 6.1 | 15.0 | 7.7 | 10.7 | 15.4 |
| 29.00 | 7.5 | 37.0 | -10.3 | -17.0 | 18.4 | 1.1 | 6.7 | 14.2 | 6.9 | 9.9 | 16.3 |
| 29.50 | 6.1 | 37.8 | -11.3 | -20.7 | 24.6 | 1.1 | 6.5 | 12.6 | 5.9 | 9.1 | 17.1 |
| 30.00 | 4.6 | 39.4 | -13.2 | -16.5 | 35.7 | 1.0 | 6.0 | 10.6 | 4.6 | 7.9 | 18.0 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5V, V_C = +5V, I_{CC} = 85mA, I_B = 4.7mA, I_C = 1.3mA @ Temperature = +105°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.1 | 60.0 | -16.4 | -17.9 | 60.7 | 1.0 | - | - | 20.0 | 21.5 | 22.4 |
| 0.02 | 17.9 | 73.5 | -16.6 | -18.8 | 292.8 | 1.0 | 8.6 | 26.6 | 19.9 | 21.6 | 21.3 |
| 0.03 | 17.8 | 63.9 | -16.3 | -18.9 | 97.9 | 1.0 | 11.1 | 28.9 | 20.0 | 21.5 | 21.7 |
| 0.04 | 17.8 | 61.3 | -16.3 | -18.9 | 72.5 | 1.0 | 13.0 | 30.8 | 20.0 | 21.9 | 21.6 |
| 0.05 | 17.7 | 61.5 | -16.2 | -18.9 | 74.6 | 1.0 | 12.9 | 30.7 | 19.9 | 21.8 | 21.7 |
| 0.06 | 17.7 | 68.5 | -16.2 | -18.9 | 169.4 | 1.0 | 15.1 | 32.8 | 19.8 | 21.7 | 21.6 |
| 0.07 | 17.7 | 76.5 | -16.2 | -18.8 | 425.6 | 1.0 | 12.2 | 29.9 | 19.8 | 21.6 | 21.6 |
| 0.08 | 17.7 | 82.5 | -16.2 | -18.9 | 845.8 | 1.0 | 13.3 | 31.0 | 19.9 | 21.7 | 21.5 |
| 0.09 | 17.6 | 76.2 | -16.2 | -18.9 | 412.3 | 1.0 | 12.7 | 30.3 | 19.8 | 21.6 | 21.4 |
| 0.10 | 17.6 | 67.9 | -16.2 | -19.0 | 160.4 | 1.0 | 12.4 | 30.0 | 19.7 | 21.6 | 21.3 |
| 0.20 | 17.4 | 77.4 | -16.5 | -19.9 | 489.6 | 1.0 | 12.2 | 29.6 | 19.0 | 21.3 | 20.1 |
| 0.25 | 17.4 | 77.4 | -16.5 | -19.9 | 489.6 | 1.0 | 12.2 | 29.6 | 19.0 | 21.0 | 20.1 |
| 0.50 | 16.9 | 69.1 | -15.7 | -20.7 | 199.8 | 1.0 | 10.0 | 26.9 | 17.8 | 20.7 | 16.3 |
| 1.00 | 15.9 | 62.4 | -14.2 | -27.1 | 104.7 | 1.0 | 11.0 | 26.8 | 16.8 | 20.3 | 12.4 |
| 1.50 | 15.8 | 58.6 | -14.1 | -21.2 | 68.0 | 1.0 | 10.2 | 26.0 | 16.6 | 20.6 | 10.0 |
| 2.00 | 15.9 | 56.8 | -14.0 | -18.2 | 55.0 | 1.0 | 10.7 | 26.6 | 16.7 | 20.5 | 8.5 |
| 2.50 | 15.9 | 54.3 | -13.6 | -16.8 | 41.2 | 1.0 | 10.4 | 26.2 | 16.7 | 20.7 | 7.5 |
| 3.00 | 15.8 | 53.4 | -13.1 | -16.3 | 37.7 | 1.0 | 9.8 | 25.6 | 16.9 | 20.9 | 6.8 |
| 3.50 | 15.8 | 58.2 | -13.4 | -15.7 | 65.9 | 1.0 | 10.7 | 26.5 | 17.1 | 20.9 | 6.2 |
| 4.00 | 15.9 | 56.0 | -14.5 | -15.1 | 51.0 | 1.0 | 11.1 | 27.0 | 17.2 | 20.8 | 5.7 |
| 4.50 | 15.9 | 54.1 | -16.3 | -14.1 | 41.3 | 1.0 | 10.5 | 26.4 | 17.0 | 20.8 | 5.3 |
| 5.00 | 15.9 | 50.8 | -18.1 | -13.4 | 28.7 | 1.0 | 10.2 | 26.0 | 17.0 | 21.0 | 5.1 |
| 5.50 | 15.8 | 48.7 | -18.9 | -13.7 | 22.8 | 1.0 | 11.2 | 27.0 | 17.1 | 20.8 | 4.8 |
| 6.00 | 15.8 | 47.4 | -19.2 | -15.0 | 20.1 | 1.0 | 10.9 | 26.7 | 17.2 | 20.8 | 4.6 |
| 6.50 | 15.8 | 46.6 | -19.8 | -16.9 | 18.8 | 1.0 | 10.5 | 26.3 | 17.1 | 20.8 | 4.4 |
| 7.00 | 15.7 | 44.9 | -20.1 | -18.6 | 15.8 | 1.0 | 10.8 | 26.5 | 17.2 | 20.7 | 4.5 |
| 7.50 | 15.7 | 44.0 | -20.5 | -19.3 | 14.4 | 1.0 | 10.8 | 26.5 | 17.3 | 20.5 | 4.4 |
| 8.00 | 15.7 | 43.5 | -22.2 | -18.8 | 13.7 | 1.0 | 11.4 | 27.1 | 17.2 | 20.3 | 4.4 |
| 8.50 | 15.7 | 42.0 | -23.4 | -17.8 | 11.7 | 1.0 | 10.5 | 26.2 | 17.4 | 20.3 | 4.5 |
| 9.00 | 15.7 | 41.1 | -19.9 | -16.3 | 10.4 | 1.0 | 10.8 | 26.5 | 17.5 | 20.3 | 4.5 |
| 9.50 | 15.7 | 41.1 | -17.2 | -14.3 | 10.3 | 1.0 | 12.0 | 27.7 | 17.6 | 20.3 | 4.5 |
| 10.00 | 15.6 | 40.7 | -16.4 | -12.8 | 9.6 | 1.0 | 11.0 | 26.6 | 17.7 | 20.3 | 4.6 |
| 10.50 | 15.7 | 40.2 | -17.9 | -12.2 | 9.2 | 1.0 | 11.4 | 27.0 | 17.7 | 20.1 | 4.7 |
| 11.00 | 15.7 | 39.5 | -22.1 | -12.6 | 8.6 | 0.9 | 11.5 | 27.2 | 17.6 | 19.8 | 4.8 |
| 11.50 | 15.7 | 38.7 | -35.6 | -14.5 | 8.0 | 1.0 | 11.3 | 27.0 | 17.5 | 19.7 | 4.9 |
| 12.00 | 15.7 | 38.0 | -27.1 | -18.6 | 7.7 | 1.0 | 10.9 | 26.6 | 17.6 | 19.6 | 5.1 |
| 12.50 | 15.5 | 37.4 | -21.0 | -22.1 | 7.3 | 1.0 | 11.2 | 26.8 | 17.2 | 19.1 | 5.1 |
| 13.00 | 15.3 | 37.2 | -19.0 | -18.6 | 7.3 | 1.0 | 11.7 | 27.0 | 16.7 | 18.6 | 5.3 |
| 13.50 | 15.0 | 37.3 | -18.8 | -16.1 | 7.7 | 1.0 | 12.1 | 27.1 | 16.8 | 18.8 | 5.7 |
| 14.00 | 14.7 | 38.2 | -19.6 | -14.7 | 8.7 | 1.0 | 12.7 | 27.4 | 16.9 | 18.7 | 6.0 |
| 14.50 | 14.7 | 38.2 | -21.4 | -13.5 | 8.7 | 1.0 | 11.6 | 26.3 | 16.7 | 18.6 | 6.1 |
| 15.00 | 14.9 | 37.0 | -24.7 | -12.7 | 7.4 | 0.9 | 11.7 | 26.5 | 16.7 | 18.7 | 6.1 |
| 15.50 | 15.0 | 36.0 | -25.4 | -11.7 | 6.4 | 0.9 | 11.5 | 26.5 | 16.7 | 18.6 | 6.2 |
| 16.00 | 15.1 | 35.3 | -23.1 | -10.9 | 5.8 | 0.9 | 10.6 | 25.7 | 16.7 | 18.5 | 6.3 |
| 16.50 | 15.2 | 34.6 | -23.3 | -11.0 | 5.4 | 0.9 | 10.2 | 25.4 | 16.5 | 18.3 | 6.4 |
| 17.00 | 15.4 | 34.0 | -25.0 | -11.8 | 5.0 | 0.9 | 9.9 | 25.3 | 16.2 | 18.0 | 6.6 |
| 17.50 | 15.6 | 33.0 | -26.8 | -12.7 | 4.5 | 0.9 | 9.9 | 25.4 | 16.1 | 17.9 | 6.7 |
| 18.00 | 15.6 | 32.2 | -23.5 | -14.6 | 4.1 | 1.0 | 9.4 | 25.0 | 15.7 | 17.7 | 6.9 |
| 18.50 | 15.6 | 31.7 | -18.5 | -20.5 | 4.0 | 1.0 | 8.4 | 23.9 | 15.3 | 17.4 | 7.0 |
| 19.00 | 15.4 | 31.7 | -15.4 | -23.9 | 4.1 | 1.0 | 9.6 | 25.0 | 14.8 | 17.0 | 7.1 |
| 19.50 | 15.2 | 31.9 | -14.7 | -17.5 | 4.3 | 1.0 | 8.9 | 24.1 | 14.9 | 17.0 | 7.2 |
| 20.00 | 15.1 | 31.6 | -16.4 | -16.6 | 4.2 | 1.0 | 9.1 | 24.2 | 14.9 | 16.9 | 7.3 |
| 20.50 | 15.2 | 31.3 | -19.8 | -18.1 | 4.1 | 1.0 | 8.7 | 23.8 | 14.7 | 16.8 | 7.3 |
| 21.00 | 15.3 | 31.0 | -23.1 | -18.9 | 3.9 | 1.0 | 8.6 | 23.9 | 14.4 | 16.5 | 7.5 |
| 21.50 | 15.3 | 30.8 | -25.1 | -17.5 | 3.9 | 1.0 | 7.2 | 22.5 | 14.2 | 16.4 | 7.7 |
| 22.00 | 15.2 | 30.5 | -24.3 | -14.7 | 3.8 | 1.0 | 8.0 | 23.2 | 13.8 | 16.2 | 7.8 |
| 22.50 | 14.9 | 30.8 | -23.0 | -12.5 | 3.9 | 0.9 | 7.7 | 22.6 | 13.2 | 15.8 | 8.1 |
| 23.00 | 14.7 | 30.8 | -24.2 | -11.6 | 4.0 | 0.9 | 7.1 | 21.8 | 12.8 | 15.5 | 8.4 |
| 23.50 | 14.5 | 30.7 | -23.9 | -11.9 | 4.0 | 0.9 | 6.5 | 21.0 | 12.5 | 15.1 | 8.6 |
| 24.00 | 14.4 | 30.8 | -19.0 | -12.7 | 4.1 | 0.9 | 5.2 | 19.6 | 12.0 | 14.7 | 9.0 |
| 24.50 | 14.4 | 30.6 | -16.8 | -14.3 | 4.1 | 1.0 | 5.6 | 20.0 | 11.4 | 14.3 | 9.3 |
| 25.00 | 14.4 | 30.5 | -18.4 | -19.4 | 4.3 | 1.0 | 5.4 | 19.8 | 10.8 | 14.0 | 9.8 |
| 25.50 | 14.2 | 30.4 | -24.8 | -24.0 | 4.4 | 1.0 | 4.8 | 18.9 | 10.0 | 12.8 | 10.4 |
| 26.00 | 13.5 | 30.9 | -20.0 | -13.9 | 4.9 | 1.0 | 4.1 | 17.6 | 9.2 | 11.9 | 11.0 |
| 26.50 | 12.3 | 32.0 | -17.5 | -10.6 | 5.9 | 0.9 | 4.4 | 16.7 | 8.6 | 11.4 | 12.1 |
| 27.00 | 10.8 | 33.4 | -16.3 | -9.4 | 7.9 | 0.9 | 6.4 | 17.3 | 8.3 | 11.1 | 13.1 |
| 27.50 | 9.1 | 34.4 | -13.6 | -9.3 | 10.7 | 0.9 | 5.8 | 14.9 | 7.6 | 10.7 | 14.3 |
| 28.00 | 7.6 | 36.2 | -11.5 | -10.5 | 15.7 | 1.0 | 7.2 | 14.7 | 7.3 | 10.3 | 15.4 |
| 28.50 | 6.1 | 37.0 | -10.5 | -13.6 | 21.2 | 1.0 | 8.4 | 14.5 | 6.6 | 9.7 | 16.4 |
| 29.00 | 4.7 | 38.3 | -10.7 | -20.7 | 30.1 | 1.1 | 8.5 | 13.2 | 5.6 | 8.7 | 17.2 |
| 29.50 | 3.3 | 39.0 | -11.8 | -24.5 | 39.4 | 1.1 | 7.6 | 10.9 | 4.2 | 7.6 | 18.0 |
| 30.00 | 1.8 | 40.3 | -13.6 | -17.3 | 54.7 | 1.0 | 7.6 | 9.4 | 2.5 | 6.1 | 18.9 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)

Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.4V, V_C = +5V, I_{CC} = 94mA, I_B = 5.3mA, I_C = 1.4mA @ Temperature = +105°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.3 | 57.0 | -16.5 | -17.8 | 42.1 | 1.0 | - | - | 20.6 | 21.8 | 22.7 |
| 0.02 | 18.1 | 54.7 | -16.6 | -18.9 | 33.0 | 1.0 | 9.6 | 27.6 | 20.5 | 21.8 | 21.7 |
| 0.03 | 18.0 | 57.0 | -16.4 | -18.8 | 43.7 | 1.0 | 14.0 | 32.0 | 20.6 | 21.7 | 22.1 |
| 0.04 | 17.9 | 57.0 | -16.2 | -19.0 | 43.4 | 1.0 | 13.9 | 31.9 | 20.6 | 22.0 | 22.0 |
| 0.05 | 17.9 | 59.3 | -16.2 | -18.9 | 57.4 | 1.0 | 14.4 | 32.3 | 20.5 | 22.0 | 22.0 |
| 0.06 | 17.9 | 69.8 | -16.1 | -18.8 | 192.1 | 1.0 | 13.1 | 30.9 | 20.5 | 21.9 | 22.0 |
| 0.07 | 17.8 | 70.7 | -16.1 | -18.8 | 213.2 | 1.0 | 12.6 | 30.5 | 20.4 | 21.8 | 22.0 |
| 0.08 | 17.8 | 63.6 | -16.2 | -18.8 | 94.6 | 1.0 | 12.4 | 30.2 | 20.5 | 21.9 | 21.8 |
| 0.09 | 17.8 | 61.4 | -16.1 | -18.9 | 74.2 | 1.0 | 13.7 | 31.5 | 20.4 | 21.9 | 21.7 |
| 0.10 | 17.8 | 60.7 | -16.2 | -18.9 | 67.9 | 1.0 | 12.7 | 30.4 | 20.3 | 21.8 | 21.6 |
| 0.20 | 17.6 | 69.7 | -16.5 | -19.8 | 198.3 | 1.0 | 11.3 | 28.9 | 19.6 | 21.6 | 20.3 |
| 0.25 | 17.6 | 69.7 | -16.5 | -19.8 | 198.3 | 1.0 | 11.3 | 28.9 | 19.6 | 21.3 | 20.3 |
| 0.50 | 17.2 | 68.2 | -15.7 | -20.8 | 174.4 | 1.0 | 9.6 | 26.9 | 18.3 | 21.0 | 16.5 |
| 1.00 | 16.2 | 61.8 | -14.1 | -27.5 | 93.7 | 1.0 | 10.6 | 26.8 | 17.4 | 20.7 | 12.7 |
| 1.50 | 16.2 | 57.9 | -14.1 | -21.3 | 59.9 | 1.0 | 10.0 | 26.2 | 17.2 | 20.9 | 10.2 |
| 2.00 | 16.3 | 54.5 | -14.0 | -18.3 | 40.2 | 1.0 | 10.3 | 26.6 | 17.1 | 21.0 | 8.6 |
| 2.50 | 16.3 | 53.0 | -13.6 | -16.8 | 33.8 | 1.0 | 10.0 | 26.2 | 17.3 | 21.2 | 7.7 |
| 3.00 | 16.1 | 53.6 | -13.0 | -16.4 | 36.9 | 1.0 | 9.8 | 25.9 | 17.5 | 21.2 | 6.9 |
| 3.50 | 16.2 | 57.2 | -13.4 | -15.8 | 56.3 | 1.0 | 10.5 | 26.7 | 17.6 | 21.3 | 6.4 |
| 4.00 | 16.3 | 56.5 | -14.5 | -15.1 | 51.5 | 1.0 | 10.8 | 27.0 | 17.6 | 21.2 | 5.8 |
| 4.50 | 16.3 | 52.3 | -16.2 | -14.1 | 32.3 | 1.0 | 10.3 | 26.6 | 17.6 | 21.3 | 5.4 |
| 5.00 | 16.2 | 50.9 | -18.1 | -13.4 | 27.7 | 1.0 | 10.3 | 26.6 | 17.6 | 21.3 | 5.1 |
| 5.50 | 16.2 | 48.5 | -18.9 | -13.6 | 21.6 | 1.0 | 11.1 | 27.3 | 17.5 | 21.2 | 4.8 |
| 6.00 | 16.2 | 46.5 | -19.2 | -14.9 | 17.5 | 1.0 | 10.2 | 26.4 | 17.6 | 21.1 | 4.7 |
| 6.50 | 16.1 | 46.0 | -19.8 | -16.7 | 16.9 | 1.0 | 10.7 | 26.9 | 17.7 | 21.2 | 4.5 |
| 7.00 | 16.1 | 44.8 | -20.1 | -18.4 | 14.9 | 1.0 | 10.8 | 26.9 | 17.7 | 21.0 | 4.4 |
| 7.50 | 16.1 | 44.3 | -20.6 | -19.3 | 14.4 | 1.0 | 10.3 | 26.4 | 17.7 | 21.0 | 4.4 |
| 8.00 | 16.1 | 43.0 | -22.3 | -18.9 | 12.4 | 1.0 | 11.1 | 27.2 | 17.8 | 20.8 | 4.5 |
| 8.50 | 16.0 | 41.9 | -23.5 | -17.9 | 11.0 | 1.0 | 10.8 | 26.8 | 18.0 | 20.8 | 4.5 |
| 9.00 | 16.0 | 41.1 | -20.0 | -16.5 | 10.0 | 1.0 | 10.8 | 26.8 | 18.1 | 20.8 | 4.6 |
| 9.50 | 16.0 | 41.3 | -17.3 | -14.4 | 10.1 | 1.0 | 11.3 | 27.3 | 18.2 | 20.8 | 4.6 |
| 10.00 | 16.0 | 40.7 | -16.5 | -12.9 | 9.3 | 1.0 | 11.5 | 27.5 | 18.1 | 20.7 | 4.7 |
| 10.50 | 16.0 | 40.0 | -17.9 | -12.3 | 8.5 | 1.0 | 11.3 | 27.4 | 18.1 | 20.5 | 4.7 |
| 11.00 | 16.1 | 39.4 | -22.0 | -12.6 | 8.2 | 0.9 | 10.8 | 26.8 | 18.2 | 20.2 | 4.9 |
| 11.50 | 16.1 | 38.8 | -35.1 | -14.5 | 7.8 | 1.0 | 10.6 | 26.7 | 17.9 | 20.1 | 5.0 |
| 12.00 | 16.0 | 37.8 | -27.4 | -18.5 | 7.2 | 1.0 | 10.4 | 26.4 | 18.0 | 20.0 | 5.0 |
| 12.50 | 15.9 | 37.2 | -21.1 | -22.4 | 6.9 | 1.0 | 10.8 | 26.7 | 17.6 | 19.6 | 5.2 |
| 13.00 | 15.7 | 37.2 | -19.0 | -18.9 | 7.0 | 1.0 | 10.6 | 26.2 | 17.2 | 19.1 | 5.3 |
| 13.50 | 15.3 | 37.5 | -18.8 | -16.3 | 7.5 | 1.0 | 11.3 | 26.6 | 17.4 | 19.2 | 5.6 |
| 14.00 | 15.1 | 37.9 | -19.5 | -14.8 | 8.1 | 1.0 | 12.1 | 27.2 | 17.3 | 19.2 | 6.0 |
| 14.50 | 15.0 | 38.1 | -21.3 | -13.6 | 8.2 | 1.0 | 11.3 | 26.4 | 17.3 | 19.1 | 6.1 |
| 15.00 | 15.2 | 37.0 | -24.5 | -12.8 | 7.2 | 0.9 | 10.8 | 26.0 | 17.2 | 19.2 | 6.0 |
| 15.50 | 15.3 | 36.0 | -25.1 | -11.7 | 6.2 | 0.9 | 10.8 | 26.1 | 17.3 | 19.1 | 6.1 |
| 16.00 | 15.4 | 35.4 | -23.0 | -10.9 | 5.7 | 0.9 | 9.8 | 25.2 | 17.3 | 19.0 | 6.3 |
| 16.50 | 15.6 | 34.8 | -23.0 | -10.9 | 5.2 | 0.9 | 9.7 | 25.3 | 17.1 | 18.9 | 6.5 |
| 17.00 | 15.7 | 34.0 | -24.9 | -11.6 | 4.8 | 0.9 | 9.3 | 25.1 | 16.7 | 18.6 | 6.6 |
| 17.50 | 15.9 | 33.2 | -27.0 | -12.4 | 4.4 | 0.9 | 9.7 | 25.7 | 16.6 | 18.5 | 6.8 |
| 18.00 | 16.0 | 32.1 | -24.0 | -14.2 | 3.9 | 0.9 | 8.0 | 24.0 | 16.3 | 18.3 | 7.0 |
| 18.50 | 16.0 | 31.8 | -18.6 | -19.6 | 3.9 | 1.0 | 7.5 | 23.4 | 15.7 | 17.9 | 7.2 |
| 19.00 | 15.8 | 31.8 | -15.3 | -24.1 | 4.0 | 1.0 | 8.8 | 24.6 | 15.3 | 17.5 | 7.1 |
| 19.50 | 15.6 | 31.8 | -14.6 | -17.6 | 4.0 | 1.0 | 8.2 | 23.8 | 15.4 | 17.5 | 7.2 |
| 20.00 | 15.5 | 31.7 | -16.2 | -16.5 | 4.0 | 1.0 | 9.1 | 24.6 | 15.4 | 17.4 | 7.4 |
| 20.50 | 15.6 | 31.4 | -19.6 | -18.0 | 3.9 | 1.0 | 8.2 | 23.8 | 15.3 | 17.4 | 7.5 |
| 21.00 | 15.7 | 31.0 | -23.0 | -19.2 | 3.8 | 1.0 | 8.0 | 23.7 | 15.0 | 17.0 | 7.5 |
| 21.50 | 15.7 | 30.7 | -25.3 | -18.0 | 3.7 | 1.0 | 6.9 | 22.6 | 14.6 | 16.9 | 7.7 |
| 22.00 | 15.6 | 30.6 | -24.9 | -15.2 | 3.6 | 1.0 | 7.2 | 22.8 | 14.4 | 16.7 | 7.8 |
| 22.50 | 15.4 | 30.6 | -23.1 | -12.8 | 3.7 | 0.9 | 7.2 | 22.6 | 13.8 | 16.4 | 8.0 |
| 23.00 | 15.1 | 30.8 | -24.1 | -11.8 | 3.8 | 0.9 | 6.5 | 21.6 | 13.4 | 16.0 | 8.3 |
| 23.50 | 14.9 | 30.8 | -23.8 | -12.0 | 3.9 | 0.9 | 6.0 | 21.0 | 13.1 | 15.6 | 8.6 |
| 24.00 | 14.8 | 30.8 | -18.9 | -12.6 | 4.0 | 0.9 | 4.8 | 19.6 | 12.6 | 15.2 | 8.9 |
| 24.50 | 14.8 | 30.7 | -16.6 | -13.9 | 4.0 | 1.0 | 5.5 | 20.3 | 12.1 | 14.8 | 9.3 |
| 25.00 | 14.8 | 30.5 | -18.0 | -18.1 | 4.1 | 1.0 | 4.9 | 19.7 | 11.5 | 14.4 | 9.6 |
| 25.50 | 14.7 | 30.4 | -25.2 | -26.5 | 4.2 | 1.0 | 4.2 | 18.9 | 10.6 | 13.2 | 10.3 |
| 26.00 | 14.1 | 30.7 | -20.7 | -15.0 | 4.4 | 1.0 | 3.4 | 17.5 | 9.6 | 12.3 | 10.9 |
| 26.50 | 13.1 | 31.5 | -17.5 | -10.9 | 5.2 | 0.9 | 3.6 | 16.7 | 8.9 | 11.7 | 11.8 |
| 27.00 | 11.7 | 32.9 | -16.2 | -9.4 | 6.8 | 0.9 | 5.7 | 17.3 | 8.7 | 11.4 | 12.9 |
| 27.50 | 9.9 | 34.7 | -13.5 | -9.1 | 10.0 | 0.9 | 4.9 | 14.8 | 8.0 | 10.9 | 14.1 |
| 28.00 | 8.3 | 35.8 | -11.3 | -10.1 | 13.6 | 1.0 | 6.5 | 14.8 | 7.7 | 10.6 | 15.2 |
| 28.50 | 6.8 | 37.5 | -10.4 | -12.8 | 20.3 | 1.0 | 7.9 | 14.7 | 7.2 | 10.1 | 16.2 |
| 29.00 | 5.5 | 37.9 | -10.6 | -18.9 | 26.3 | 1.1 | 7.8 | 13.2 | 6.3 | 9.2 | 17.1 |
| 29.50 | 4.1 | 38.9 | -11.8 | -24.1 | 35.8 | 1.1 | 7.1 | 11.2 | 5.1 | 8.1 | 17.9 |
| 30.00 | 2.6 | 39.8 | -13.6 | -17.3 | 47.3 | 1.0 | 7.1 | 9.7 | 3.4 | 6.8 | 18.7 |

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = S11 (dB)

Gain(Power Gain) = S21 (dB)

Isolation = -S12 (dB)







Output Return Loss = S22 (dB)

TEST CONDITIONS: V_{CC} = +5V, V_B = +5.8V, V_C = +5V, I_{CC} = 104mA, I_B = 5.9mA, I_C = 1.5mA @ Temperature = +105°C

| FREQ | Gain | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Input | IP-3 Output | 1dB Comp. Output | 3dB Comp. Output | Noise Figure |
|-------|------|-----------|-------------------|--------------------|-----------|---------|------------|-------------|------------------|------------------|--------------|
| | | | | | K | Measure | | | | | |
| (GHz) | (dB) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dBm) | (dBm) | (dB) |
| 0.01 | 18.4 | 54.0 | -16.4 | -17.9 | 29.5 | 1.0 | - | - | 20.9 | 21.9 | 22.9 |
| 0.02 | 18.2 | 57.8 | -16.5 | -18.8 | 46.3 | 1.0 | 11.1 | 29.3 | 20.9 | 22.0 | 22.0 |
| 0.03 | 18.1 | 72.9 | -16.2 | -18.9 | 267.2 | 1.0 | 12.2 | 30.3 | 20.9 | 21.9 | 22.3 |
| 0.04 | 18.1 | 57.2 | -16.2 | -18.8 | 44.2 | 1.0 | 13.9 | 32.0 | 21.1 | 22.3 | 22.3 |
| 0.05 | 18.0 | 57.5 | -16.2 | -18.9 | 45.9 | 1.0 | 13.5 | 31.5 | 21.0 | 22.2 | 22.3 |
| 0.06 | 18.0 | 65.3 | -16.1 | -18.8 | 113.4 | 1.0 | 15.6 | 33.6 | 20.9 | 22.1 | 22.3 |
| 0.07 | 18.0 | 67.3 | -16.1 | -18.8 | 142.3 | 1.0 | 11.5 | 29.5 | 20.9 | 22.0 | 22.2 |
| 0.08 | 18.0 | 62.8 | -16.1 | -18.9 | 84.7 | 1.0 | 12.8 | 30.7 | 20.8 | 22.1 | 22.1 |
| 0.09 | 17.9 | 64.9 | -16.1 | -18.9 | 108.8 | 1.0 | 11.1 | 29.0 | 20.9 | 22.1 | 22.0 |
| 0.10 | 17.9 | 73.0 | -16.1 | -18.9 | 276.9 | 1.0 | 13.2 | 31.1 | 20.8 | 22.0 | 22.0 |
| 0.20 | 17.8 | 76.6 | -16.5 | -19.9 | 428.9 | 1.0 | 11.3 | 29.1 | 20.1 | 21.8 | 20.7 |
| 0.25 | 17.8 | 76.6 | -16.5 | -19.9 | 428.9 | 1.0 | 11.3 | 29.1 | 20.1 | 21.6 | 20.7 |
| 0.50 | 17.5 | 80.2 | -15.7 | -21.0 | 672.6 | 1.0 | 9.7 | 27.2 | 18.8 | 21.3 | 16.9 |
| 1.00 | 16.5 | 68.5 | -14.1 | -28.0 | 195.8 | 1.0 | 10.7 | 27.2 | 17.8 | 20.9 | 12.9 |
| 1.50 | 16.5 | 59.1 | -14.0 | -21.4 | 67.2 | 1.0 | 10.3 | 26.8 | 17.6 | 21.3 | 10.4 |
| 2.00 | 16.5 | 54.9 | -13.9 | -18.4 | 41.0 | 1.0 | 10.7 | 27.2 | 17.6 | 21.3 | 8.8 |
| 2.50 | 16.5 | 54.0 | -13.5 | -16.9 | 36.7 | 1.0 | 10.4 | 26.9 | 17.8 | 21.5 | 7.8 |
| 3.00 | 16.4 | 53.5 | -13.0 | -16.4 | 35.3 | 1.0 | 10.1 | 26.5 | 17.9 | 21.6 | 7.1 |
| 3.50 | 16.4 | 56.8 | -13.3 | -15.8 | 52.1 | 1.0 | 10.3 | 26.7 | 18.0 | 21.6 | 6.4 |
| 4.00 | 16.5 | 56.6 | -14.4 | -15.2 | 51.0 | 1.0 | 11.2 | 27.8 | 18.0 | 21.5 | 6.0 |
| 4.50 | 16.6 | 52.7 | -16.2 | -14.1 | 32.8 | 1.0 | 10.3 | 26.8 | 18.0 | 21.5 | 5.4 |
| 5.00 | 16.5 | 50.0 | -18.0 | -13.3 | 24.4 | 1.0 | 10.2 | 26.7 | 18.0 | 21.7 | 5.2 |
| 5.50 | 16.5 | 49.8 | -18.9 | -13.6 | 24.1 | 1.0 | 10.7 | 27.2 | 18.1 | 21.5 | 4.9 |
| 6.00 | 16.4 | 46.9 | -19.1 | -14.9 | 17.7 | 1.0 | 10.4 | 26.8 | 18.0 | 21.5 | 4.8 |
| 6.50 | 16.4 | 45.9 | -19.8 | -16.6 | 16.2 | 1.0 | 10.6 | 27.0 | 18.1 | 21.6 | 4.6 |
| 7.00 | 16.3 | 45.0 | -20.1 | -18.3 | 14.9 | 1.0 | 11.2 | 27.5 | 18.1 | 21.4 | 4.5 |
| 7.50 | 16.3 | 44.2 | -20.6 | -19.3 | 13.8 | 1.0 | 10.2 | 26.5 | 18.1 | 21.3 | 4.5 |
| 8.00 | 16.3 | 43.3 | -22.3 | -19.0 | 12.5 | 1.0 | 10.5 | 26.8 | 18.2 | 21.1 | 4.5 |
| 8.50 | 16.3 | 42.0 | -23.5 | -18.0 | 10.9 | 1.0 | 10.6 | 26.9 | 18.4 | 21.2 | 4.6 |
| 9.00 | 16.3 | 41.2 | -20.0 | -16.6 | 9.8 | 1.0 | 10.4 | 26.7 | 18.5 | 21.2 | 4.6 |
| 9.50 | 16.3 | 41.1 | -17.3 | -14.5 | 9.5 | 1.0 | 10.7 | 27.0 | 18.5 | 21.2 | 4.6 |
| 10.00 | 16.2 | 40.6 | -16.5 | -13.0 | 9.0 | 1.0 | 10.8 | 27.1 | 18.5 | 21.1 | 4.7 |
| 10.50 | 16.3 | 40.2 | -17.9 | -12.3 | 8.5 | 1.0 | 10.8 | 27.0 | 18.5 | 20.9 | 4.8 |
| 11.00 | 16.3 | 39.4 | -22.0 | -12.6 | 7.9 | 0.9 | 10.5 | 26.8 | 18.4 | 20.6 | 4.9 |
| 11.50 | 16.3 | 38.8 | -34.9 | -14.4 | 7.6 | 1.0 | 10.4 | 26.8 | 18.3 | 20.5 | 5.0 |
| 12.00 | 16.3 | 38.2 | -27.4 | -18.4 | 7.4 | 1.0 | 10.1 | 26.4 | 18.2 | 20.4 | 5.1 |
| 12.50 | 16.1 | 37.5 | -21.1 | -22.6 | 6.9 | 1.0 | 9.8 | 26.0 | 17.9 | 20.0 | 5.2 |
| 13.00 | 15.9 | 37.1 | -19.0 | -19.3 | 6.8 | 1.0 | 10.4 | 26.3 | 17.5 | 19.5 | 5.4 |
| 13.50 | 15.6 | 37.3 | -18.8 | -16.5 | 7.1 | 1.0 | 10.9 | 26.5 | 17.6 | 19.7 | 5.7 |
| 14.00 | 15.3 | 38.0 | -19.5 | -15.0 | 8.0 | 1.0 | 11.2 | 26.5 | 17.6 | 19.7 | 6.0 |
| 14.50 | 15.3 | 38.4 | -21.2 | -13.6 | 8.4 | 1.0 | 10.1 | 25.4 | 17.5 | 19.6 | 6.2 |
| 15.00 | 15.4 | 37.1 | -24.4 | -12.8 | 7.1 | 0.9 | 10.1 | 25.6 | 17.6 | 19.6 | 6.1 |
| 15.50 | 15.6 | 36.2 | -25.1 | -11.7 | 6.2 | 0.9 | 10.4 | 26.0 | 17.5 | 19.6 | 6.3 |
| 16.00 | 15.6 | 35.3 | -22.9 | -10.8 | 5.5 | 0.9 | 9.4 | 25.1 | 17.6 | 19.4 | 6.4 |
| 16.50 | 15.8 | 34.8 | -23.0 | -10.8 | 5.1 | 0.9 | 9.7 | 25.5 | 17.4 | 19.3 | 6.6 |
| 17.00 | 16.0 | 34.2 | -24.8 | -11.5 | 4.7 | 0.9 | 8.5 | 24.5 | 17.1 | 19.0 | 6.7 |
| 17.50 | 16.2 | 33.0 | -27.1 | -12.2 | 4.1 | 0.9 | 8.4 | 24.5 | 16.8 | 18.9 | 6.9 |
| 18.00 | 16.2 | 32.2 | -24.2 | -13.9 | 3.8 | 0.9 | 7.5 | 23.8 | 16.5 | 18.7 | 7.1 |
| 18.50 | 16.2 | 31.8 | -18.7 | -19.1 | 3.8 | 1.0 | 7.0 | 23.2 | 16.0 | 18.3 | 7.1 |
| 19.00 | 16.1 | 31.8 | -15.3 | -24.6 | 3.9 | 1.0 | 8.0 | 24.0 | 15.4 | 17.9 | 7.3 |
| 19.50 | 15.8 | 31.8 | -14.5 | -17.7 | 3.9 | 1.0 | 7.7 | 23.5 | 15.6 | 17.9 | 7.3 |
| 20.00 | 15.7 | 31.7 | -16.1 | -16.5 | 3.9 | 1.0 | 8.3 | 24.0 | 15.6 | 17.8 | 7.4 |
| 20.50 | 15.8 | 31.4 | -19.6 | -17.9 | 3.8 | 1.0 | 7.6 | 23.4 | 15.6 | 17.8 | 7.4 |
| 21.00 | 15.9 | 31.1 | -22.9 | -19.4 | 3.7 | 1.0 | 7.7 | 23.7 | 15.2 | 17.4 | 7.5 |
| 21.50 | 15.9 | 30.8 | -25.5 | -18.5 | 3.6 | 1.0 | 6.5 | 22.4 | 14.8 | 17.3 | 7.6 |
| 22.00 | 15.9 | 30.7 | -25.0 | -15.7 | 3.6 | 1.0 | 6.6 | 22.5 | 14.6 | 17.1 | 7.8 |
| 22.50 | 15.6 | 30.6 | -23.3 | -13.2 | 3.6 | 0.9 | 6.8 | 22.4 | 14.0 | 16.7 | 8.1 |
| 23.00 | 15.4 | 30.8 | -24.1 | -12.1 | 3.7 | 0.9 | 6.2 | 21.6 | 13.6 | 16.4 | 8.3 |
| 23.50 | 15.2 | 30.9 | -23.9 | -12.1 | 3.8 | 0.9 | 5.7 | 20.9 | 13.3 | 15.9 | 8.6 |
| 24.00 | 15.0 | 31.0 | -18.9 | -12.6 | 3.9 | 0.9 | 4.6 | 19.7 | 13.0 | 15.6 | 8.9 |
| 24.50 | 15.0 | 30.8 | -16.5 | -13.6 | 3.9 | 1.0 | 5.2 | 20.2 | 12.2 | 15.1 | 9.3 |
| 25.00 | 15.0 | 30.7 | -17.8 | -17.0 | 4.0 | 1.0 | 4.7 | 19.6 | 11.7 | 14.6 | 9.7 |
| 25.50 | 14.9 | 30.4 | -25.0 | -26.4 | 4.1 | 1.0 | 3.8 | 18.7 | 10.8 | 13.6 | 10.2 |
| 26.00 | 14.5 | 30.7 | -21.3 | -16.3 | 4.3 | 1.0 | 2.7 | 17.2 | 9.7 | 12.5 | 10.9 |
| 26.50 | 13.5 | 31.4 | -17.5 | -11.5 | 4.9 | 0.9 | 2.9 | 16.4 | 8.9 | 11.8 | 11.7 |
| 27.00 | 12.2 | 32.6 | -16.1 | -9.6 | 6.3 | 0.9 | 4.7 | 16.9 | 8.6 | 11.6 | 12.7 |
| 27.50 | 10.5 | 34.2 | -13.4 | -9.0 | 8.8 | 0.9 | 4.2 | 14.7 | 7.9 | 11.0 | 13.9 |
| 28.00 | 8.9 | 35.7 | -11.3 | -9.8 | 12.5 | 1.0 | 5.8 | 14.7 | 7.6 | 10.7 | 15.0 |
| 28.50 | 7.3 | 37.1 | -10.3 | -12.0 | 18.0 | 1.0 | 7.4 | 14.7 | 7.2 | 10.3 | 16.1 |
| 29.00 | 6.0 | 37.7 | -10.5 | -17.2 | 23.8 | 1.1 | 7.6 | 13.6 | 6.3 | 9.5 | 16.9 |
| 29.50 | 4.7 | 38.5 | -11.7 | -23.2 | 31.7 | 1.1 | 6.6 | 11.3 | 5.2 | 8.5 | 17.8 |
| 30.00 | 3.3 | 39.9 | -13.5 | -17.5 | 44.4 | 1.0 | 6.6 | 9.9 | 3.8 | 7.1 | 18.5 |







Typical Performance Curves

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.









Typical Performance Curves

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.







Typical Performance Curves

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.




Typical Performance Curves

Note: All data taken at nominal conditions $V_{CC} = +5V$ and $V_C = +5V$ unless noted otherwise.




Typical Performance Curves

Note: All data taken at nominal conditions $V_{CC} = +5V$, $V_C = +5V$, and $V_B = +5V$ unless noted otherwise.



Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note | |
|----------------|-------------------------|-------------------|---------------------------|------|
| 12 | 8 | 7 | Small quantity standard | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | 7 | Standard | 1000 |
| | | 13 | Standard | 2000 |
| | | | | 3000 |
| 4000 | | | | |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|------------|-------------|----------|-----|------|
| OR | ECO-018510 | NEW RELEASE | 07/12/23 | ITG | IL |
| | | | | | |
| | | | | | |


**SUGGESTED MOUNTING CONFIGURATION
FOR DG1847 CASE STYLE**




| COMPONENT | SIZE |
|-----------|------|
| C1,C2 | 0603 |
| C3-C9 | 0402 |
| R1-R2 | 0402 |

NOTES:

- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066". COPPER: 1 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
- CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-LVA-273PNC+.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|----------|----------|
| DIMENSIONS ARE IN INCHES | ITG | 07/12/23 |
| TOLERANCES ON: | GF | 07/12/23 |
| 2 PL DECIMALS ± | IL | 07/12/23 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, DG1847, TB-LVA-273PNC+

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|-------|------------|-------------|---------------|
| A | 15542 | 98-PL-756 | OR |
| FILE: | 98PL756 | SCALE: 5:1 | SHEET: 1 OF 1 |


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit

SEE DETAIL "A"



DETAIL "A"
LOCATION OF UNITS COMPONENTS
(SCALE 2:1)



SCHEMATIC DIAGRAM

| Component | Size | Value | Part Number | Manufacturer |
|-----------|------|--------|--------------------|--------------|
| C1 | 0603 | 5100pF | GCM1885C1H512JA16D | Murata |
| C2 | 0603 | 1uF | GCM188R71E105KA64J | Murata |
| C3,C9 | 0402 | 1000pF | GRM1555C1H102JA01D | Murata |
| C4,C6 | 0402 | 100pF | GRM1555C1H101JA01D | Murata |
| C5,C7,C8 | 0402 | 0.1uF | GRM155R71H104KE14J | Murata |
| R1,R2 | 0402 | 00hm | RK73Z1ETTP | KOA Speer |

Notes:

- 2.92mm Female Connectors.
- PCB Material: Roger R04350B or equivalent,
Dielectric constant=3.5, Thickness=0.0066 inch

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|---|
| Operating Temperature | -40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C or -65° to 150° Ambient Environment | Individual Model Data Sheet |
| HTOL | 1000 hours at 125°C | MIL-STD-883, Method 1005, Condition B |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Mechanical Shock | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak | MIL-STD-883, Method 2007, Condition B |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102, Condition C |
| HAST | 130°C, 85% RH, 96 hours | JESD22-A110 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|-------------------------|
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |