

Surface Mount

# Monolithic Amplifier

LEE-9+

50Ω DC to 8 GHz

## The Big Deal

- Low Gain
- Excellent Gain flatness,  $\pm 0.5$  dB up to 8 GHz
- Broadband matched



Generic photo used for illustration purposes only

3mm x 3mm MCLP package

## Product Overview

LEE-9+ (RoHS compliant) is wideband current driven amplifier fabricated using HBT technology. In addition, the LEE-9+, has good input and output return loss over a broad frequency range without the need for external matching components. Lead finish is SnAgNi. It has repeatable performance from lot to lot and is enclosed in a 3mm x 3mm x 0.89mm MCLP package for very good thermal performance.

## Key Features

Feature	Advantages
Broadband, DC* to 8 GHz (* Low frequency cut off determined by external coupling capacitors)	A single amplifier covering DC* to C band. <ul style="list-style-type: none"><li>• Reduced component inventory</li><li>• Ideal for wideband applications such as instrumentation and military</li></ul>
Low gain: 8.5 dB typ. at 0.1 GHz and 7.7 dB at 8 GHz	Ideal for increasing the gain of amplifier chain by low value. Typically small gain change may need two components; an amplifier and an attenuator. Use of LEE-9+ reduces component count.
Outstanding Gain Flatness: $\pm 0.4$ dB	No need for gain flatness compensation over 8 GHz band to realize published gain flatness.
Wideband matched Input return loss: 17-29 dB typ. Output return loss: 12-34 dB typ.	No external matching required to realize published return loss.
MCLP Package	Low inductance, repeatable transitions, excellent thermal pad.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Monolithic Amplifier

DC-8 GHz

## Product Features

- DC-8 GHz
- Gain, 8.4 dB typ. at 2 GHz
- Outstanding gain flatness,  $\pm 0.5$  dB typ.
- Output power, 13.9 dBm typ. at 2 GHz
- Internally Matched to 50 Ohms
- Aqueous washable
- Protected by US Patent 6,943,629



Generic photo used for illustration purposes only

## LEE-9+

CASE STYLE: FG873

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Typical Applications

- Cellular
- PCS
- Communication receivers & transmitters
- Satellite communication, military

## General Description

LEE-9+ (RoHS compliant) is a wideband amplifier offering medium dynamic range. It has repeatable performance from lot to lot. It is enclosed in a 3X3mm MCLP molded plastic package.

## simplified schematic and pin description



Function	Pin Number	Description
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Electrical Specifications<sup>1</sup> at 25°C and 50mA, unless noted

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range <sup>2</sup>		DC		8	GHz
Gain	0.1	—	8.5	—	dB
	1	—	8.5	—	
	2	7.6	8.4	9.3	
	4	—	8.2	—	
	5	—	8.0	—	
	8	—	7.7	—	
Input Return Loss	0.1		24.0		dB
	1		23.8		
	2		22.6		
	4		20.2		
	5		23.1		
	8		23.5		
Output Return Loss	0.1		33.0		dB
	1		29.7		
	2		26.1		
	4		22.0		
	5		20.9		
	8		13.3		
Output IP3	0.1		31.3		dBm
	1		30.5		
	2		29.7		
	4		25.4		
	5		23.4		
	8		19.7		
Output Power @ 1 dB compression	0.1	—	14.1	—	dBm
	1	—	14.0	—	
	2	12.0	13.9	—	
	4	—	12.4	—	
	5	—	11.9	—	
	8	—	7.9	—	
Noise Figure	0.1		5.1		dB
	1		5.1		
	2		5.3		
	4		5.3		
	5		5.2		
	8		5.3		
Recommended Device Operating Current (I <sub>d</sub> )			50		mA
Device Operating Voltage (V <sub>d</sub> )		3.6	4.0	4.4	V
Device Voltage Variation vs. Temperature at 50 mA			-2.7		mV/°C
Device Voltage Variation vs. Current at 25°C			17.3		mV/mA
Thermal Resistance, junction-to-case			138		°C/W

- 1. Measured on Mini-Circuits test board TB-154
- 2. Low frequency cut off determined by external coupling capacitors.

Absolute Maximum Ratings<sup>3</sup>

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Operating Current	74 mA
Input Power <sup>4</sup>	26 dBm (5 min max.) 15 dBm (continuous)


- 3. Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.
- 4. For continuous operation 15 dBm max.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Characterization Test Circuit




**Fig 1.** Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-154) Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent’s N5242A PNA-X microwave network analyzer.

**Conditions:**

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, -5 dBm/tone at output.

Recommended Application Circuit



Test Board includes case, connectors, and components (in bold) soldered to PCB

Product Marking



R BIAS	
Vcc	“1%” Res. Values (ohms) for Optimum Biasing
7	61.9
8	80.6
9	100
10	121
11	140
12	165
13	182
14	200
15	221
16	237
17	261
18	274
19	301
20	316

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit’s applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, “Standard Terms”); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits’ website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Additional Detailed Technical Information	
<i>additional information is available on our dash board. To access this information <a href="#">click here</a></i>	
<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
<b>Case Style</b>	FG873, MCLP Plastic package, exposed paddle, lead finish: Matte-Tin
<b>Tape &amp; Reel</b>	F68 7" Reels with 20, 50, 100, 200, 500, 1K devices 13" Reels with 2K, 3K, 4K devices
<b>Suggested Layout for PCB Design</b>	98-PL-252
<b>Evaluation Board</b>	TB-413-9+
<b>Environmental Ratings</b>	ENV08T1

**ESD Rating**


Human Body Model (HBM): Class 1B (500 to <1000V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (25V) in accordance with ANSI/ESD STM5.2-1999

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**MSL Test Flow Chart**



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =50mA, Vd = 4.09V, @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.58	14.86	23.90	34.36	1.27	0.77	30.35	13.85	5.19
50.0	8.60	15.18	23.90	45.16	1.30	0.78	34.10	14.41	5.12
100.0	8.58	15.13	24.20	44.85	1.29	0.78	31.86	14.28	5.09
200.0	8.58	15.11	24.17	44.04	1.29	0.78	32.65	14.11	5.05
300.0	8.56	15.13	24.16	44.51	1.30	0.78	32.66	14.17	5.17
400.0	8.56	15.13	24.08	45.51	1.30	0.78	32.56	14.18	5.25
500.0	8.56	15.12	24.19	46.82	1.30	0.78	32.66	14.15	5.24
600.0	8.55	15.12	24.16	46.20	1.30	0.78	32.08	14.20	5.28
700.0	8.55	15.13	24.06	45.25	1.30	0.78	32.78	14.15	5.27
800.0	8.55	15.13	24.07	44.73	1.30	0.78	31.85	14.15	5.22
1000.0	8.54	15.11	24.00	42.16	1.30	0.78	30.60	14.04	5.22
1250.0	8.53	15.11	23.88	37.34	1.30	0.78	32.43	14.02	5.26
1500.0	8.51	15.09	23.71	33.65	1.30	0.78	30.98	14.04	5.23
1750.0	8.49	15.11	23.21	31.23	1.30	0.79	30.73	14.07	5.20
2000.0	8.48	15.10	22.66	29.01	1.30	0.79	30.04	13.96	5.31
2250.0	8.46	15.07	21.94	26.95	1.30	0.79	29.57	13.88	5.30
2500.0	8.42	15.08	21.29	25.69	1.30	0.79	28.65	13.78	5.22
2750.0	8.41	15.04	20.70	24.31	1.29	0.79	28.13	13.70	5.26
3000.0	8.38	15.04	20.36	23.43	1.30	0.79	27.77	13.48	5.24
3250.0	8.33	15.06	19.91	23.03	1.30	0.79	27.08	13.29	5.22
3500.0	8.31	15.01	19.89	22.46	1.30	0.79	26.53	12.97	5.22
3750.0	8.25	15.03	19.74	22.73	1.31	0.79	25.85	12.71	5.26
4000.0	8.24	14.96	20.22	22.44	1.30	0.79	25.63	12.36	5.19
4250.0	8.25	14.84	20.76	21.83	1.29	0.78	24.85	11.92	5.17
4500.0	8.20	14.78	21.88	21.73	1.29	0.78	24.47	11.74	5.23
4750.0	8.09	14.87	22.63	22.05	1.31	0.79	24.28	11.55	5.27
5000.0	8.04	14.74	24.84	20.67	1.30	0.78	23.38	11.01	5.20
5250.0	7.97	14.82	25.70	20.54	1.31	0.79	23.09	10.76	5.21
5500.0	7.89	14.87	26.43	19.95	1.33	0.79	23.22	10.72	5.05
5750.0	7.76	14.58	36.41	17.26	1.30	0.77	22.61	10.21	5.21
6000.0	7.81	14.85	31.83	18.06	1.33	0.79	22.16	10.01	5.29
6250.0	7.79	14.63	44.33	16.23	1.30	0.77	21.97	9.67	5.20
6500.0	7.64	14.77	35.46	16.20	1.33	0.78	21.54	9.39	5.27
6750.0	7.29	14.73	27.51	15.51	1.36	0.79	20.88	8.99	5.36
7000.0	7.55	14.46	30.39	14.47	1.30	0.76	20.93	8.85	5.30
7250.0	7.69	14.54	33.63	14.49	1.29	0.76	20.79	8.65	5.24
7500.0	7.72	14.53	31.27	14.38	1.28	0.75	20.04	8.25	5.17
7750.0	7.73	14.40	27.85	13.81	1.27	0.74	19.86	8.06	5.30
8000.0	7.74	14.28	24.81	13.21	1.25	0.73	19.82	7.92	5.19

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =40mA, Vd = 3.91V, @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.19	14.93	17.57	22.10	1.30	0.79	28.03	12.07	5.26
50.0	8.44	14.98	22.87	35.73	1.29	0.78	29.11	12.14	5.08
100.0	8.42	15.01	23.29	36.69	1.30	0.78	28.22	12.11	5.07
200.0	8.42	15.04	23.18	36.89	1.30	0.79	28.62	11.83	4.99
300.0	8.41	15.03	23.22	36.70	1.30	0.79	28.44	11.93	5.19
400.0	8.40	15.03	23.20	36.28	1.30	0.79	28.71	12.08	5.21
500.0	8.40	15.02	23.22	37.25	1.30	0.79	29.05	11.96	5.15
600.0	8.40	15.02	23.26	37.67	1.30	0.79	29.13	12.10	5.22
700.0	8.40	15.02	23.10	37.81	1.30	0.79	29.12	12.06	5.24
800.0	8.40	15.02	23.13	38.03	1.30	0.79	28.68	12.08	5.15
1000.0	8.38	15.01	23.08	38.34	1.30	0.79	28.01	11.94	5.21
1250.0	8.38	15.02	22.88	36.21	1.30	0.79	28.67	11.87	5.18
1500.0	8.37	15.01	22.68	33.27	1.30	0.79	28.43	11.94	5.19
1750.0	8.35	14.99	22.32	30.76	1.30	0.79	28.16	12.06	5.21
2000.0	8.33	14.98	21.81	28.47	1.30	0.79	27.80	11.87	5.22
2250.0	8.32	14.98	21.14	26.31	1.30	0.79	27.23	11.79	5.22
2500.0	8.29	14.97	20.57	24.96	1.30	0.79	27.19	11.74	5.22
2750.0	8.28	14.94	19.99	23.70	1.30	0.79	26.73	11.88	5.27
3000.0	8.25	14.93	19.68	22.90	1.30	0.79	26.41	11.83	5.22
3250.0	8.21	14.96	19.34	22.58	1.30	0.79	25.64	11.72	5.11
3500.0	8.19	14.91	19.30	22.15	1.30	0.79	25.29	11.59	5.19
3750.0	8.14	14.93	19.12	22.39	1.30	0.79	24.66	11.47	5.16
4000.0	8.13	14.85	19.56	22.17	1.30	0.79	24.34	11.13	5.16
4250.0	8.15	14.72	20.19	21.69	1.28	0.78	23.71	10.83	5.08
4500.0	8.11	14.67	21.12	21.56	1.28	0.78	23.60	10.65	5.15
4750.0	7.99	14.73	21.90	21.91	1.30	0.79	23.23	10.43	5.20
5000.0	7.95	14.62	24.23	20.51	1.29	0.78	22.37	10.03	5.18
5250.0	7.88	14.70	25.07	20.43	1.31	0.79	21.96	9.78	5.17
5500.0	7.79	14.77	25.84	19.90	1.32	0.79	22.13	9.66	5.01
5750.0	7.69	14.46	38.53	17.25	1.30	0.77	21.44	9.22	5.10
6000.0	7.73	14.74	31.69	18.05	1.32	0.79	21.04	9.02	5.07
6250.0	7.71	14.50	47.19	16.23	1.29	0.77	21.02	8.71	5.08
6500.0	7.55	14.63	43.40	16.22	1.32	0.78	20.49	8.42	5.20
6750.0	7.18	14.58	29.83	15.40	1.36	0.79	19.85	8.00	5.26
7000.0	7.47	14.36	31.00	14.49	1.29	0.76	19.87	7.84	5.17
7250.0	7.60	14.43	32.34	14.47	1.29	0.76	19.69	7.64	5.11
7500.0	7.63	14.41	29.97	14.38	1.28	0.75	19.03	7.29	5.11
7750.0	7.64	14.27	26.57	13.77	1.26	0.74	18.82	7.10	5.19
8000.0	7.64	14.15	23.69	13.21	1.24	0.73	18.78	6.97	5.14

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =60mA, Vd = 4.27V, @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	8.68	15.00	25.75	35.45	1.27	0.77	30.93	14.54	5.27
50.0	8.67	15.24	24.59	55.01	1.30	0.78	38.32	15.64	5.17
100.0	8.66	15.16	24.91	59.68	1.29	0.78	34.35	15.41	5.16
200.0	8.65	15.16	24.80	60.22	1.29	0.78	35.26	15.40	5.17
300.0	8.64	15.15	24.84	59.73	1.29	0.78	33.72	15.45	5.26
400.0	8.64	15.16	24.76	68.74	1.29	0.78	35.73	15.33	5.32
500.0	8.63	15.16	24.81	52.38	1.29	0.78	33.10	15.34	5.35
600.0	8.63	15.15	24.82	50.05	1.29	0.78	36.85	15.33	5.36
700.0	8.63	15.18	24.69	46.89	1.29	0.78	34.42	15.24	5.36
800.0	8.63	15.17	24.74	44.71	1.29	0.78	33.72	15.21	5.23
1000.0	8.61	15.15	24.68	41.08	1.29	0.78	32.21	15.17	5.31
1250.0	8.60	15.13	24.53	36.43	1.29	0.78	32.47	15.18	5.34
1500.0	8.59	15.14	24.36	33.40	1.29	0.78	31.93	15.12	5.30
1750.0	8.57	15.13	23.80	31.17	1.29	0.78	31.70	15.04	5.29
2000.0	8.55	15.14	23.26	29.09	1.30	0.78	30.72	14.98	5.32
2250.0	8.52	15.11	22.49	27.15	1.29	0.78	30.52	14.90	5.39
2500.0	8.49	15.13	21.79	25.92	1.30	0.79	29.90	14.70	5.36
2750.0	8.48	15.09	21.15	24.53	1.29	0.79	28.91	14.52	5.36
3000.0	8.45	15.07	20.80	23.74	1.29	0.79	28.74	14.22	5.33
3250.0	8.40	15.08	20.30	23.37	1.30	0.79	28.06	14.01	5.25
3500.0	8.37	15.04	20.29	22.76	1.30	0.79	27.20	13.72	5.36
3750.0	8.31	15.08	20.12	23.09	1.31	0.79	26.58	13.49	5.30
4000.0	8.30	15.00	20.58	22.72	1.30	0.79	26.12	13.18	5.28
4250.0	8.31	14.88	21.14	22.10	1.29	0.78	25.38	12.69	5.23
4500.0	8.26	14.84	22.30	21.89	1.29	0.78	25.13	12.55	5.34
4750.0	8.14	14.92	22.97	22.23	1.31	0.79	24.99	12.39	5.37
5000.0	8.10	14.78	25.29	20.69	1.30	0.78	24.19	11.80	5.33
5250.0	8.02	14.88	25.87	20.62	1.32	0.79	23.86	11.57	5.32
5500.0	7.93	14.95	26.16	20.07	1.33	0.79	24.03	11.60	5.26
5750.0	7.84	14.63	34.25	17.31	1.30	0.77	23.27	11.01	5.27
6000.0	7.85	14.93	30.44	18.19	1.33	0.79	22.84	10.80	5.29
6250.0	7.85	14.69	37.23	16.32	1.30	0.77	22.70	10.50	5.30
6500.0	7.68	14.81	31.84	16.27	1.33	0.78	22.25	10.25	5.43
6750.0	7.30	14.73	25.70	15.34	1.36	0.79	21.59	9.78	5.48
7000.0	7.61	14.54	29.63	14.55	1.30	0.76	21.61	9.61	5.32
7250.0	7.74	14.61	33.28	14.53	1.29	0.76	21.47	9.43	5.38
7500.0	7.78	14.58	31.97	14.48	1.29	0.75	20.83	9.05	5.30
7750.0	7.80	14.44	28.54	13.87	1.27	0.74	20.51	8.85	5.43
8000.0	7.81	14.33	25.73	13.28	1.25	0.73	20.52	8.71	5.38



## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =50mA, Vd = 4.3V, @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.68	15.24	24.79	42.97	1.30	0.78	28.46	13.85	4.42
50.0	8.67	15.23	23.29	41.88	1.29	0.78	35.06	14.46	4.36
100.0	8.66	15.15	22.81	36.74	1.29	0.78	32.61	14.38	4.32
200.0	8.66	15.15	22.55	35.51	1.29	0.78	32.83	14.19	4.24
300.0	8.64	15.13	23.74	42.99	1.29	0.78	33.28	14.28	4.46
400.0	8.66	15.13	24.50	55.14	1.29	0.78	31.95	14.36	4.44
500.0	8.66	15.13	24.38	51.94	1.29	0.78	32.77	14.33	4.44
600.0	8.66	15.11	24.18	48.53	1.28	0.78	33.19	14.37	4.50
700.0	8.66	15.11	23.90	46.71	1.28	0.78	32.66	14.34	4.50
800.0	8.66	15.10	23.89	46.57	1.28	0.78	32.56	14.35	4.42
1000.0	8.65	15.09	23.11	41.22	1.28	0.78	32.23	14.24	4.49
1250.0	8.65	15.08	23.59	39.86	1.28	0.78	32.42	14.23	4.47
1500.0	8.64	15.06	23.88	35.14	1.28	0.78	32.18	14.28	4.44
1750.0	8.63	15.03	23.46	32.40	1.28	0.78	32.10	14.35	4.40
2000.0	8.62	15.03	23.06	30.41	1.28	0.78	31.44	14.23	4.48
2250.0	8.60	15.01	22.92	27.73	1.28	0.78	31.03	14.17	4.48
2500.0	8.57	15.01	22.20	25.84	1.28	0.78	30.46	14.10	4.42
2750.0	8.56	14.95	21.22	24.18	1.27	0.77	29.44	14.12	4.46
3000.0	8.53	14.94	20.45	23.95	1.27	0.77	29.74	14.00	4.47
3250.0	8.49	14.95	19.90	23.78	1.28	0.78	28.58	13.87	4.30
3500.0	8.47	14.90	20.10	22.78	1.27	0.77	27.65	13.64	4.47
3750.0	8.41	14.91	19.74	23.10	1.28	0.78	27.14	13.43	4.40
4000.0	8.40	14.84	19.91	22.88	1.27	0.78	26.89	13.11	4.34
4250.0	8.41	14.72	20.42	22.50	1.26	0.77	26.18	12.67	4.32
4500.0	8.38	14.66	21.68	21.97	1.26	0.76	26.19	12.49	4.45
4750.0	8.26	14.73	22.03	22.79	1.28	0.78	25.61	12.31	4.42
5000.0	8.22	14.66	23.93	21.86	1.28	0.77	24.86	11.89	4.38
5250.0	8.19	14.60	26.21	20.49	1.27	0.77	24.47	11.55	4.42
5500.0	8.10	14.67	27.25	19.73	1.29	0.77	24.60	11.52	4.24
5750.0	7.83	14.64	28.58	18.15	1.31	0.78	24.00	10.99	4.46
6000.0	8.01	14.65	30.77	18.12	1.29	0.77	23.59	10.80	4.38
6250.0	8.00	14.43	33.14	16.11	1.26	0.75	23.31	10.55	4.37
6500.0	7.91	14.55	32.52	16.12	1.28	0.76	22.90	10.26	4.36
6750.0	7.74	14.59	27.76	15.69	1.30	0.76	22.10	9.83	4.43
7000.0	7.68	14.30	26.30	14.29	1.27	0.74	22.17	9.69	4.39
7250.0	7.89	14.40	29.65	14.43	1.26	0.74	22.03	9.50	4.41
7500.0	7.94	14.38	29.33	14.25	1.25	0.73	21.20	9.11	4.35
7750.0	7.91	14.22	27.35	13.68	1.24	0.72	21.20	8.96	4.44
8000.0	8.02	14.19	26.67	13.24	1.22	0.70	21.25	8.86	4.39

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =40mA, Vd = 4.11V, @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.38	17.67	18.55	23.14	1.59	0.90	28.25	12.14	4.43
50.0	8.54	15.16	22.59	36.33	1.30	0.79	29.81	12.07	4.30
100.0	8.52	15.06	22.15	33.31	1.29	0.78	29.33	11.93	4.27
200.0	8.52	15.06	21.89	32.56	1.29	0.78	29.46	11.64	4.22
300.0	8.50	15.00	22.96	37.18	1.29	0.78	29.16	11.73	4.34
400.0	8.53	15.04	23.68	42.09	1.29	0.78	30.68	11.97	4.38
500.0	8.52	15.05	23.47	41.91	1.29	0.78	29.46	11.81	4.45
600.0	8.53	15.04	23.42	40.36	1.29	0.78	29.46	11.92	4.44
700.0	8.53	15.03	23.13	40.16	1.29	0.78	29.84	11.93	4.46
800.0	8.53	15.03	23.09	40.25	1.29	0.78	30.08	11.97	4.32
1000.0	8.53	15.01	22.42	36.87	1.29	0.78	29.08	11.78	4.37
1250.0	8.52	14.99	22.77	39.44	1.29	0.78	29.58	11.75	4.40
1500.0	8.52	14.98	22.99	35.18	1.28	0.78	29.02	11.86	4.37
1750.0	8.51	14.96	22.72	32.12	1.28	0.78	29.25	12.00	4.38
2000.0	8.49	14.95	22.34	30.04	1.28	0.78	29.03	11.82	4.42
2250.0	8.48	14.91	22.15	27.40	1.28	0.78	28.73	11.80	4.43
2500.0	8.45	14.94	21.56	25.52	1.28	0.78	28.29	11.78	4.37
2750.0	8.44	14.89	20.66	23.82	1.28	0.78	27.53	11.91	4.39
3000.0	8.42	14.86	19.91	23.55	1.27	0.78	27.64	11.97	4.38
3250.0	8.38	14.86	19.45	23.35	1.28	0.78	26.90	11.98	4.30
3500.0	8.37	14.81	19.58	22.50	1.27	0.78	26.52	11.92	4.38
3750.0	8.31	14.82	19.22	22.76	1.28	0.78	26.38	11.99	4.33
4000.0	8.31	14.75	19.43	22.64	1.27	0.78	25.84	11.71	4.29
4250.0	8.32	14.63	20.02	22.27	1.26	0.77	25.28	11.53	4.25
4500.0	8.29	14.56	21.15	21.68	1.26	0.76	25.03	11.37	4.33
4750.0	8.17	14.62	21.50	22.62	1.28	0.78	24.58	11.14	4.31
5000.0	8.13	14.57	23.46	21.82	1.28	0.77	23.98	10.89	4.37
5250.0	8.10	14.52	25.83	20.46	1.27	0.77	23.51	10.57	4.32
5500.0	8.02	14.58	27.28	19.66	1.28	0.77	23.48	10.51	4.18
5750.0	7.74	14.56	29.27	18.31	1.31	0.78	23.05	10.07	4.31
6000.0	7.93	14.57	32.12	18.15	1.29	0.77	22.66	9.88	4.28
6250.0	7.93	14.34	37.25	16.06	1.26	0.74	22.44	9.63	4.29
6500.0	7.85	14.44	37.23	16.07	1.28	0.75	21.96	9.37	4.30
6750.0	7.69	14.49	30.76	15.69	1.30	0.76	21.24	8.95	4.31
7000.0	7.60	14.21	27.82	14.23	1.27	0.74	21.21	8.77	4.28
7250.0	7.83	14.32	32.97	14.34	1.26	0.74	21.09	8.60	4.26
7500.0	7.89	14.30	32.64	14.12	1.25	0.73	20.37	8.26	4.30
7750.0	7.82	14.10	28.13	13.53	1.23	0.71	20.24	8.11	4.32
8000.0	7.95	14.09	26.77	13.13	1.22	0.70	20.32	7.98	4.30

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =60mA, Vd = 4.48V, @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.70	15.07	24.04	45.47	1.28	0.77	32.59	15.01	4.51
50.0	8.74	15.16	23.95	46.09	1.28	0.78	35.13	15.90	4.40
100.0	8.72	15.19	23.23	40.25	1.29	0.78	35.49	15.74	4.36
200.0	8.72	15.19	23.02	38.42	1.29	0.78	37.62	15.66	4.35
300.0	8.70	15.15	24.30	46.96	1.28	0.78	33.98	15.74	4.50
400.0	8.72	15.16	25.09	44.83	1.28	0.78	35.95	15.68	4.51
500.0	8.72	15.16	24.91	44.92	1.28	0.78	36.73	15.69	4.50
600.0	8.72	15.16	24.76	45.64	1.28	0.78	33.91	15.70	4.54
700.0	8.72	15.15	24.46	46.35	1.28	0.78	35.24	15.63	4.58
800.0	8.73	15.14	24.46	45.16	1.28	0.78	35.87	15.64	4.48
1000.0	8.72	15.13	23.58	43.29	1.28	0.78	34.75	15.57	4.51
1250.0	8.71	15.11	24.08	38.28	1.28	0.78	33.43	15.57	4.50
1500.0	8.70	15.10	24.41	34.12	1.28	0.77	33.67	15.55	4.52
1750.0	8.69	15.09	23.99	31.90	1.28	0.78	32.55	15.55	4.50
2000.0	8.67	15.07	23.55	30.14	1.28	0.77	32.64	15.47	4.54
2250.0	8.66	15.03	23.40	27.60	1.27	0.77	32.20	15.40	4.57
2500.0	8.62	15.05	22.70	25.90	1.28	0.78	30.83	15.29	4.50
2750.0	8.61	15.01	21.68	24.37	1.27	0.77	30.20	15.17	4.50
3000.0	8.58	14.99	20.79	24.26	1.27	0.77	30.21	14.96	4.49
3250.0	8.54	14.99	20.29	24.09	1.28	0.78	29.28	14.74	4.43
3500.0	8.52	14.94	20.44	23.03	1.27	0.77	28.43	14.48	4.51
3750.0	8.45	14.98	20.06	23.42	1.28	0.78	27.91	14.23	4.46
4000.0	8.45	14.88	20.23	23.14	1.27	0.78	27.50	13.94	4.38
4250.0	8.45	14.77	20.73	22.71	1.26	0.77	26.73	13.45	4.40
4500.0	8.41	14.71	21.98	22.10	1.26	0.77	26.66	13.29	4.48
4750.0	8.29	14.78	22.29	22.90	1.28	0.78	26.58	13.14	4.77
5000.0	8.24	14.70	24.17	21.85	1.28	0.77	25.71	12.68	4.49
5250.0	8.22	14.66	26.13	20.61	1.28	0.77	25.08	12.28	4.49
5500.0	8.12	14.73	26.93	19.82	1.29	0.77	25.21	12.36	4.36
5750.0	7.86	14.64	27.89	17.86	1.30	0.77	24.60	11.81	4.48
6000.0	8.03	14.72	29.58	18.20	1.30	0.77	24.23	11.58	4.44
6250.0	8.02	14.50	31.01	16.24	1.27	0.75	23.90	11.34	4.48
6500.0	7.92	14.62	30.10	16.23	1.29	0.76	23.61	11.05	4.45
6750.0	7.74	14.65	26.26	15.76	1.31	0.77	22.84	10.57	4.50
7000.0	7.70	14.37	25.34	14.35	1.28	0.74	22.89	10.43	4.54
7250.0	7.91	14.47	28.01	14.52	1.27	0.74	22.66	10.31	4.47
7500.0	7.95	14.43	27.69	14.34	1.26	0.73	21.94	9.87	4.50
7750.0	7.94	14.28	26.64	13.75	1.24	0.72	21.97	9.77	4.53
8000.0	8.04	14.25	26.10	13.33	1.23	0.71	22.07	9.68	4.51

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =50mA, Vd = 3.94V, @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.51	15.08	24.58	40.27	1.30	0.78	36.00	13.64	5.71
50.0	8.53	15.05	24.08	42.76	1.29	0.78	35.77	14.20	5.60
100.0	8.52	15.08	25.08	50.10	1.30	0.78	30.77	14.13	5.55
200.0	8.52	15.07	25.76	47.77	1.30	0.78	32.32	14.01	5.52
300.0	8.50	15.07	25.50	46.07	1.30	0.78	33.06	14.05	5.65
400.0	8.50	15.07	24.67	46.16	1.30	0.78	31.74	14.01	5.70
500.0	8.49	15.10	24.39	44.44	1.30	0.79	31.38	14.00	5.76
600.0	8.49	15.10	24.19	42.91	1.30	0.79	31.09	14.00	5.76
700.0	8.48	15.10	23.99	40.48	1.30	0.79	32.25	13.95	5.75
800.0	8.48	15.09	23.90	39.40	1.30	0.79	32.07	13.94	5.66
1000.0	8.46	15.09	23.49	37.94	1.30	0.79	30.70	13.84	5.74
1250.0	8.45	15.09	23.11	35.57	1.30	0.79	31.20	13.81	5.73
1500.0	8.44	15.08	22.92	33.16	1.30	0.79	30.66	13.80	5.69
1750.0	8.42	15.07	22.47	30.93	1.30	0.79	29.82	13.78	5.73
2000.0	8.40	15.09	22.13	28.75	1.30	0.79	29.48	13.68	5.76
2250.0	8.38	15.07	21.61	26.54	1.30	0.79	28.83	13.60	5.80
2500.0	8.35	15.08	21.04	25.11	1.30	0.79	27.67	13.41	5.73
2750.0	8.34	15.05	20.49	23.77	1.30	0.79	27.47	13.27	5.76
3000.0	8.31	15.03	20.09	22.84	1.30	0.79	27.19	12.98	5.66
3250.0	8.26	15.05	19.74	22.39	1.31	0.79	26.12	12.75	5.63
3500.0	8.25	15.00	19.85	21.89	1.30	0.79	25.56	12.40	5.81
3750.0	8.18	15.04	19.70	22.29	1.31	0.80	25.27	12.16	5.71
4000.0	8.17	14.94	20.16	22.07	1.30	0.79	24.71	11.80	5.73
4250.0	8.18	14.85	20.74	21.56	1.29	0.79	23.96	11.35	5.62
4500.0	8.13	14.82	21.92	21.52	1.30	0.79	23.66	11.16	5.76
4750.0	7.96	14.91	23.05	21.88	1.32	0.80	23.54	10.96	5.74
5000.0	8.00	14.74	24.84	20.16	1.30	0.78	22.47	10.42	5.73
5250.0	7.87	14.79	27.15	19.46	1.32	0.79	22.22	10.16	5.71
5500.0	7.75	14.90	27.86	19.07	1.34	0.80	22.40	10.10	5.65
5750.0	7.75	14.58	42.66	16.69	1.30	0.77	21.63	9.58	5.65
6000.0	7.59	14.74	40.14	16.52	1.33	0.78	21.27	9.28	5.73
6250.0	7.50	14.73	37.06	15.82	1.34	0.78	21.06	8.98	5.75
6500.0	7.34	14.61	30.70	15.02	1.34	0.78	20.78	8.70	5.77
6750.0	7.16	14.34	26.11	13.79	1.32	0.76	20.15	8.36	5.83
7000.0	7.43	14.48	28.52	14.19	1.31	0.76	20.05	8.15	5.75
7250.0	7.62	14.58	28.91	14.33	1.29	0.77	19.94	7.95	5.68
7500.0	7.52	14.45	26.49	14.04	1.29	0.76	19.40	7.60	5.70
7750.0	7.50	14.33	24.11	13.71	1.27	0.75	19.09	7.41	5.81
8000.0	7.57	14.26	22.43	13.31	1.25	0.75	18.94	7.16	5.74

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Id =40mA, Vd = 3.78V, @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
10.0	8.42	15.13	24.12	34.47	1.31	0.79	26.83	11.89	5.66
50.0	8.40	14.98	23.21	35.43	1.30	0.78	28.79	12.21	5.55
100.0	8.39	15.00	23.80	38.71	1.30	0.79	28.14	12.17	5.53
200.0	8.38	14.99	24.52	44.81	1.30	0.78	28.10	11.96	5.48
300.0	8.37	15.01	24.28	40.28	1.30	0.79	28.25	11.98	5.61
400.0	8.37	15.00	23.63	37.15	1.30	0.79	28.35	12.09	5.68
500.0	8.36	15.00	23.24	36.56	1.30	0.79	27.86	12.02	5.62
600.0	8.36	15.00	23.13	36.09	1.30	0.79	28.59	12.10	5.72
700.0	8.35	15.01	22.96	35.59	1.30	0.79	28.62	12.06	5.72
800.0	8.35	15.01	22.91	34.87	1.30	0.79	28.50	12.09	5.66
1000.0	8.34	15.02	22.54	34.24	1.31	0.79	27.71	11.92	5.67
1250.0	8.33	15.01	22.19	33.22	1.30	0.79	28.16	11.87	5.68
1500.0	8.32	15.00	22.00	31.72	1.30	0.79	27.60	11.93	5.70
1750.0	8.30	14.99	21.61	30.03	1.30	0.79	27.73	12.03	5.69
2000.0	8.28	15.02	21.35	28.17	1.31	0.79	27.58	11.86	5.78
2250.0	8.27	14.99	20.80	26.15	1.30	0.79	27.01	11.77	5.74
2500.0	8.24	14.99	20.29	24.69	1.30	0.79	26.30	11.71	5.70
2750.0	8.23	14.96	19.79	23.35	1.30	0.79	25.96	11.77	5.73
3000.0	8.20	14.96	19.37	22.49	1.30	0.79	25.52	11.62	5.70
3250.0	8.16	14.97	19.09	21.98	1.31	0.79	25.07	11.46	5.59
3500.0	8.15	14.91	19.20	21.50	1.30	0.79	24.47	11.22	5.68
3750.0	8.08	14.95	19.12	21.99	1.31	0.80	24.14	11.04	5.65
4000.0	8.08	14.88	19.51	21.78	1.30	0.79	23.47	10.66	5.59
4250.0	8.10	14.76	20.03	21.39	1.29	0.79	22.89	10.34	5.58
4500.0	8.04	14.72	21.10	21.42	1.29	0.79	22.60	10.14	5.62
4750.0	7.86	14.81	22.57	21.84	1.32	0.80	22.32	9.88	5.69
5000.0	7.92	14.65	23.78	20.33	1.30	0.78	21.45	9.48	5.66
5250.0	7.81	14.68	26.20	19.52	1.31	0.79	21.17	9.19	5.64
5500.0	7.68	14.80	27.33	19.17	1.34	0.80	21.28	9.05	5.52
5750.0	7.72	14.50	35.40	16.81	1.30	0.77	20.60	8.62	5.58
6000.0	7.52	14.63	44.01	16.64	1.33	0.78	20.21	8.34	5.60
6250.0	7.38	14.58	39.75	15.75	1.33	0.78	20.11	8.04	5.65
6500.0	7.29	14.50	31.94	15.13	1.33	0.78	19.66	7.76	5.67
6750.0	7.16	14.24	26.68	13.89	1.31	0.76	19.15	7.44	5.65
7000.0	7.36	14.43	28.49	14.39	1.31	0.77	19.03	7.22	5.64
7250.0	7.51	14.52	27.80	14.46	1.30	0.77	18.84	7.00	5.52
7500.0	7.45	14.38	25.49	14.16	1.29	0.76	18.31	6.66	5.60
7750.0	7.43	14.25	23.09	13.81	1.27	0.76	18.05	6.39	5.66
8000.0	7.48	14.16	21.77	13.46	1.25	0.75	17.88	6.26	5.63

## Typical Performance Data

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)








TEST CONDITIONS: Id =60mA, Vd = 4.11V, @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)			(dBm)	(dBm)	(dB)
10.0	8.63	15.31	26.23	36.24	1.31	0.79	29.11	13.64	5.73
50.0	8.62	15.12	24.97	48.71	1.29	0.78	35.02	15.24	5.67
100.0	8.60	15.12	25.95	44.73	1.29	0.78	34.31	15.06	5.62
200.0	8.60	15.13	26.73	39.55	1.29	0.78	33.94	15.10	5.62
300.0	8.59	15.14	26.20	41.80	1.29	0.78	34.12	15.15	5.72
400.0	8.58	15.15	25.49	47.14	1.30	0.78	33.62	14.96	5.80
500.0	8.57	15.14	25.17	46.45	1.30	0.78	33.21	14.98	5.78
600.0	8.57	15.16	24.98	44.43	1.30	0.78	33.99	14.95	5.80
700.0	8.56	15.16	24.78	42.16	1.30	0.78	33.06	14.85	5.84
800.0	8.56	15.15	24.57	41.54	1.30	0.78	33.26	14.80	5.76
1000.0	8.55	15.16	24.18	39.49	1.30	0.79	32.21	14.77	5.75
1250.0	8.53	15.13	23.71	36.40	1.30	0.79	32.17	14.82	5.80
1500.0	8.52	15.13	23.50	33.46	1.30	0.79	31.54	14.70	5.78
1750.0	8.50	15.12	23.05	31.14	1.30	0.79	31.63	14.57	5.77
2000.0	8.48	15.13	22.70	28.85	1.30	0.79	30.07	14.52	5.88
2250.0	8.46	15.11	22.16	26.74	1.30	0.79	29.48	14.44	5.86
2500.0	8.43	15.12	21.56	25.38	1.30	0.79	28.81	14.15	5.84
2750.0	8.40	15.10	21.00	24.03	1.30	0.79	28.52	13.97	5.85
3000.0	8.38	15.10	20.60	23.04	1.30	0.79	27.58	13.64	5.80
3250.0	8.33	15.11	20.25	22.67	1.31	0.79	26.97	13.44	5.74
3500.0	8.31	15.06	20.29	22.12	1.30	0.79	26.46	13.11	5.85
3750.0	8.24	15.11	20.14	22.61	1.31	0.80	25.80	12.89	5.82
4000.0	8.23	15.04	20.66	22.26	1.31	0.79	25.28	12.58	5.78
4250.0	8.24	14.93	21.28	21.74	1.30	0.79	24.62	12.11	5.75
4500.0	8.18	14.87	22.41	21.62	1.30	0.79	24.44	11.93	5.82
4750.0	8.03	14.97	23.38	21.90	1.32	0.80	24.26	11.81	5.82
5000.0	8.05	14.80	25.60	20.13	1.30	0.78	23.28	11.17	5.80
5250.0	7.93	14.85	27.65	19.45	1.32	0.79	23.06	10.97	5.84
5500.0	7.79	14.98	27.90	19.06	1.35	0.80	23.21	10.94	5.75
5750.0	7.78	14.69	41.19	16.73	1.31	0.77	22.40	10.37	5.76
6000.0	7.61	14.83	34.56	16.58	1.34	0.79	21.99	10.12	5.86
6250.0	7.58	14.83	34.87	15.95	1.34	0.78	21.95	9.79	5.83
6500.0	7.36	14.70	28.95	15.03	1.35	0.78	21.40	9.51	5.97
6750.0	7.13	14.47	25.48	13.92	1.34	0.77	20.93	9.13	5.94
7000.0	7.47	14.54	28.32	14.15	1.31	0.76	20.83	9.00	5.87
7250.0	7.67	14.62	29.16	14.20	1.29	0.76	20.72	8.82	5.85
7500.0	7.58	14.51	27.50	14.05	1.29	0.76	20.16	8.42	5.85
7750.0	7.56	14.38	25.05	13.75	1.28	0.75	19.78	8.19	5.98
8000.0	7.64	14.29	23.23	13.33	1.25	0.74	19.63	7.95	5.89

## Typical Performance Curves




## Typical Performance Curves






### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P
FG873	.118 (3.00)	.118 (3.00)	.035 (0.89)	.008 (0.20)	.07 (1.78)	.024 (0.60)	.017 (0.43)	.018 (0.46)	.021 (0.52)	.024 (0.61)	.061 (1.55)	.186 (4.72)	.186 (4.72)	.032 (0.81)

CASE #	Q	R	S	T	WT. GRAM
FG873	.064 (1.63)	.032 (0.81)	.064 (1.63)	.050 (1.27)	.02

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .004$

#### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin per Data Sheet.  
All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F68

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
4000				

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M108436	NEW RELEASE	11/14/06	PW	IG

SUGGESTED MOUNTING CONFIGURATION  
FOR FG873 CASE STYLE, "cb" PIN CONNECTION




NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.030" \pm .002"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$ .005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	PW 11/11/06
	CHECKED	IL 11/14/06
	APPROVED	IG 11/14/06



Mini-Circuits®


13 Neptune Avenue  
Brooklyn NY 11235

PL, cb, FG873, LEE, TB-413-XX+


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-252	REV: OR
FILE: 98PL252	SCALE: 10:1	SHEET: 1 OF 1	

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit



TB-413-9+



COMPONENT	VALUE
A1	LEE-9(+)
C1 (NOTE 4)	2400 pF
C2 (NOTE 4)	2400 pF
C3 (bypass)	0.1 uF
R1	165 Ohms, 0.75W
R2	0 Ohm, 0.25W
CHK	Mini-Circuits TCCH-80+


## Schematic Diagram

### NOTE:


1. Vcc voltage:  $+12 \pm 0.2V$ .
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.
4. Capacitors, C1 & C2 should be free of resonance up to the highest frequency specified.
5. Insertion loss of Input/Output line :

Frequency, GHz	1.0	2.0	4.0	8.0
Loss,dB*	0.5	0.8	1.2	1.6

\* Add PCB loss to measured Gain to get DUT Gain.

 **Mini-Circuits®**



 Mini-Circuits THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.	ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED			
	SIZE A	CODE IDENT 15542	DRAWING NO: TB-413-9-20+	REV: A
	FILE: WTB-413-9+		SCALE: NONE	SHEET: 3 OF 3
	ASHEETL2.DWG REV:A DATE: 01/12/94			

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215