

Flat Gain, Ultra-Wideband

# Monolithic Amplifier

LVA-123+

50Ω 0.01 to 12 GHz



CASE STYLE: DQ849

## The Big Deal

- Ultra broadband performance
- Excellent Gain Flatness through 8 GHz
- Broadband without external matching components

## Product Overview

LVA-123+ (RoHS compliant) is an advanced ultra-wideband amplifier fabricated using GaAs HBT technology and offers excellent gain flatness over a broad frequency range. In addition, the LVA-123+ has good input and output return loss over this frequency range without the need for external matching components. Lead finish is tin-silver over nickel. It has repeatable performance from lot to lot and is enclosed in a 3x3 mm 8-lead package for very good thermal performance.

## Key Features

| Feature  | Advantages  |
|--|---|
| Ultra Broad Band: 0.01 to 12 GHz   | Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX in a single amplifier.                              |
| Ultra Flat Gain<br>±0.6 dB typ. 0.05 - 6 GHz<br>±1.0 dB typ. 0.05 - 8 GHz      | Ultra Flat Gain, eliminates need for compensation networks to achieve published results   |
| Wideband Bias-Tee, TCBT-123+   | Enables customer to realize full BW without changing any components   |
| No External Matching Components Required                                       | LVA-123+ provides good Input and Output Return Loss of 12-28 dB over 0.05 - 6 GHz without the need for any external matching components |
| Excellent ESD<br>HBM: class 1C (1000 to <2000V)<br>MM: class M2 (100 to <200V) | Simplifies ESD handling.  |



Flat Gain, Ultra-Wideband

# Monolithic Amplifier

0.01-12 GHz

## Product Features

- Excellent Gain Flatness,  $\pm 0.6$  dB, 0.05-6 GHz
- Gain, 17.3 dB typ. at 2 GHz
- Excellent input return loss, 20 dB typ., 2 GHz



Generic photo used for illustration purposes only

## LVA-123+

CASE STYLE: DQ849

## Typical Applications

- Base station infrastructure
- Test instruments
- MMDS & Wireless LAN
- LTE
- Satellite communication
- Avionics



**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## General Description

LVA-123+ (RoHS compliant) is an advanced ultra-wideband amplifier fabricated using GaAs HBT technology and offers excellent gain flatness over a broad frequency range. In addition, the LVA-123+ has good input and output return loss over this frequency range without the need for external matching components. Lead finish is tin-silver over nickel. It has repeatable performance from lot to lot and is enclosed in a 3x3 mm 8-lead package for very good thermal performance.

## simplified schematic and pin description



| Function         | Pin Number  | Description   |
|------------------|-------------|---|
| RF IN            | 2           | RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.   |
| RF-OUT and DC-IN | 5           | RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2 |
| GND              | Paddle      | Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.   |
| NC               | 1,3,4,6,7,8 | No connection   |

**Electrical Specifications<sup>1</sup> at 25°C and Vcc=5V, R= 16.5Ω unless noted**

| Parameter   | Condition (GHz) | Min. | Typ.  | Max. | Units |
|---|-----------------|------|-------|------|-------|
| Frequency range                                       |                 | 0.01 |       | 12.0 | GHz   |
| Gain  | 0.05            | —    | 16.5  | —    | dB    |
|   | 0.85            | —    | 17.4  | —    |       |
|   | 2.0             | 15.6 | 17.3  | 19.0 |       |
|   | 6.0             | —    | 16.7  | —    |       |
|   | 8.0             | —    | 14.7  | —    |       |
|   | 10.0            | —    | 11.6  | —    |       |
|   | 12.0            | —    | 8.1   | —    |       |
| Gain flatness   | 0.05-6          |      | ±0.6  |      | dB    |
| Input return loss                                     | 0.05            | —    | 13.7  | —    | dB    |
|   | 0.85            | —    | 25.0  | —    |       |
|   | 2.0             | 16.0 | 25.0  | —    |       |
|   | 6.0             | —    | 18.3  | —    |       |
|   | 8.0             | —    | 9.7   | —    |       |
|   | 10.0            | —    | 6.9   | —    |       |
|   | 12.0            | —    | 5.2   | —    |       |
| Output return loss                                    | 0.05            |      | 13.5  |      | dB    |
|   | 0.85            |      | 21.3  |      |       |
|   | 2.0             |      | 16.5  |      |       |
|   | 6.0             |      | 11.6  |      |       |
|   | 8.0             |      | 7.1   |      |       |
|   | 10.0            |      | 6.2   |      |       |
|   | 12.0            |      | 5.2   |      |       |
| Reverse isolation                                     | 6.0             |      | 19.2  |      | dB    |
| Output power at 1dB compression                       | 0.05            |      | 17.2  |      | dBm   |
|   | 0.85            |      | 16.5  |      |       |
|   | 2.0             |      | 15.6  |      |       |
|   | 6.0             |      | 13.3  |      |       |
|   | 8.0             |      | 10.8  |      |       |
|   | 10.0            |      | 7.8   |      |       |
|   | 12.0            |      | 5.3   |      |       |
| Output IP3  | 0.2             |      | 29.0  |      | dBm   |
|   | 0.85            |      | 30.3  |      |       |
|   | 2.0             |      | 28.2  |      |       |
|   | 6.0             |      | 23.6  |      |       |
|   | 8.0             |      | 22.1  |      |       |
|   | 10.0            |      | 18.5  |      |       |
|   | 12.0            |      | 15.5  |      |       |
| Noise figure  | 0.2             |      | 3.7   |      | dB    |
|   | 0.85            |      | 3.7   |      |       |
|   | 2.0             |      | 3.9   |      |       |
|   | 6.0             |      | 4.1   |      |       |
|   | 8.0             |      | 4.4   |      |       |
|   | 10.0            |      | 5.2   |      |       |
|   | 12.0            |      | 5.9   |      |       |
| Supply operating voltage (Vcc)                        |                 | 4.8  | 5.0   | 5.2  | V     |
| Device operating current                              |                 | —    | 52    | 57   | mA    |
| Device current variation vs. temperature <sup>2</sup> |                 |      | 59    |      | μA/°C |
| Device current variation vs. voltage                  |                 |      | 0.019 |      | mA/mV |
| Thermal resistance, junction-to-ground lead           |                 |      | 156   |      | °C/W  |

1. Measured on Mini-Circuits Characterization test board TB-841+. See Characterization Test Circuit (Fig. 1)

2. (Current at 85°C — Current at -45°C)/130


**Absolute Maximum Ratings<sup>3</sup>**

| Parameter                                      | Ratings                                    |
|--|--|
| Operating temperature (ground lead)            | -40°C to 85°C                              |
| Storage temperature                            | -65°C to 150°C                             |
| Operating current at 5V (Vcc) & 16.5Ω resistor | 100 mA                                     |
| Power dissipation                              | 0.34 W                                     |
| Input power (CW)                               | 28 dBm (5 min max.)<br>11 dBm (continuous) |
| DC voltage on Pad 5                            | 6 V  |

3. Permanent damage may occur if any of these limits are exceeded.  
Electrical maximum ratings are not intended for continuous normal operation.



### Characterization Test Circuit




**Fig 1.** Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-841+) Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent’s N5242A PNA-X microwave network analyzer. (R=16.5Ω)

**Conditions:**


1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

### Recommended Application Circuit



**Fig 2.** Test Board includes case, connectors, and components soldered to PCB (Cblock=0.001 μF, Cbypass=0.1 μF, R=16.5Ω)

### Product Marking



| Additional Detailed Technical Information   |   |
|---|---|
| <i>additional information is available on our dash board. To access this information <a href="#">click here</a></i> |   |
| <b>Performance Data</b>   | Data Table  |
|   | Swept Graphs  |
|   | S-Parameter (S2P Files) Data Set (.zip file)                      |
| <b>Case Style</b>   | DQ849 Plastic package, exposed paddle, lead finish: Matte-Tin     |
| <b>Tape &amp; Reel</b><br>Standard quantities available on reel   | F104<br>7" reels with 10, 20, 50, 100, 200, 500, 1K or 2K devices |
| <b>Suggested Layout for PCB Design</b>  | PL-473  |
| <b>Evaluation Board</b>   | TB-877+   |
| <b>Environmental Ratings</b>  | ENV08T1   |

**ESD Rating\***

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M2 (100 to <200V) in accordance with ANSI/ESD STM5.2-1999

\*Measured in industry standard SOT-89 package

**MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**MSL Test Flow Chart**



**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 46.90mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.50 | 21.05     | 13.80             | 13.66              | 1.09      | 0.62    | 19.33       | 17.07            | 5.26         |
| 100   | 17.51 | 19.98     | 18.53             | 18.36              | 1.04      | 0.41    | 26.62       | 15.63            | 4.12         |
| 200   | 17.67 | 19.85     | 27.67             | 24.23              | 1.03      | 0.39    | 29.95       | 15.96            | 3.59         |
| 400   | 17.51 | 20.07     | 43.68             | 24.53              | 1.04      | 0.44    | 30.74       | 16.42            | 3.60         |
| 600   | 17.44 | 20.16     | 56.02             | 23.55              | 1.05      | 0.46    | 30.39       | 16.52            | 3.62         |
| 800   | 17.40 | 20.19     | 64.71             | 22.62              | 1.05      | 0.47    | 30.81       | 16.53            | 3.70         |
| 1000  | 17.38 | 20.21     | 47.72             | 21.71              | 1.05      | 0.47    | 29.48       | 16.35            | 3.66         |
| 1200  | 17.35 | 20.22     | 40.89             | 20.82              | 1.05      | 0.47    | 30.27       | 16.37            | 3.75         |
| 1400  | 17.33 | 20.23     | 36.17             | 19.98              | 1.05      | 0.47    | 30.09       | 16.30            | 3.78         |
| 1600  | 17.32 | 20.23     | 33.07             | 19.39              | 1.05      | 0.47    | 30.12       | 16.33            | 3.77         |
| 1800  | 17.30 | 20.23     | 30.38             | 18.68              | 1.05      | 0.47    | 30.42       | 16.37            | 3.82         |
| 2000  | 17.29 | 20.23     | 28.30             | 18.05              | 1.05      | 0.47    | 29.84       | 16.24            | 3.82         |
| 2200  | 17.27 | 20.21     | 26.97             | 17.61              | 1.05      | 0.47    | 29.14       | 15.78            | 3.84         |
| 2400  | 17.26 | 20.20     | 25.56             | 17.02              | 1.05      | 0.47    | 29.33       | 15.86            | 3.81         |
| 2600  | 17.25 | 20.18     | 24.68             | 16.75              | 1.05      | 0.46    | 29.20       | 15.82            | 3.92         |
| 2800  | 17.24 | 20.16     | 23.61             | 16.40              | 1.04      | 0.46    | 28.79       | 15.82            | 3.93         |
| 3000  | 17.22 | 20.13     | 22.85             | 16.05              | 1.04      | 0.46    | 28.24       | 15.49            | 3.81         |
| 3200  | 17.21 | 20.09     | 22.36             | 15.93              | 1.04      | 0.46    | 27.88       | 15.63            | 3.90         |
| 3400  | 17.20 | 20.06     | 21.85             | 15.59              | 1.04      | 0.45    | 27.75       | 15.44            | 3.89         |
| 3600  | 17.19 | 20.01     | 21.86             | 15.57              | 1.04      | 0.45    | 27.33       | 15.21            | 3.88         |
| 3800  | 17.18 | 19.96     | 21.61             | 15.44              | 1.03      | 0.44    | 27.11       | 15.26            | 3.92         |
| 4000  | 17.17 | 19.91     | 21.78             | 15.25              | 1.03      | 0.44    | 26.63       | 15.11            | 3.98         |
| 4500  | 17.12 | 19.76     | 22.98             | 15.08              | 1.02      | 0.43    | 25.88       | 14.58            | 3.95         |
| 5000  | 17.07 | 19.59     | 26.15             | 14.54              | 1.01      | 0.41    | 24.88       | 14.00            | 4.00         |
| 5500  | 16.95 | 19.42     | 27.51             | 13.85              | 1.00      | 0.41    | 24.92       | 13.84            | 4.04         |
| 6000  | 16.74 | 19.31     | 23.38             | 12.50              | 1.00      | 0.41    | 24.18       | 13.43            | 4.07         |
| 6500  | 16.45 | 19.25     | 18.92             | 11.16              | 0.99      | 0.41    | 23.99       | 12.86            | 4.17         |
| 7000  | 16.07 | 19.24     | 15.47             | 9.95               | 0.98      | 0.43    | 23.77       | 12.21            | 4.17         |
| 7500  | 15.60 | 19.29     | 13.06             | 8.99               | 0.98      | 0.46    | 23.17       | 11.43            | 4.24         |
| 8000  | 15.07 | 19.38     | 11.44             | 8.33               | 0.98      | 0.52    | 23.03       | 10.73            | 4.30         |
| 8500  | 14.48 | 19.50     | 10.31             | 7.85               | 0.98      | 0.58    | 22.02       | 10.05            | 4.39         |
| 9000  | 13.84 | 19.65     | 9.25              | 7.68               | 0.98      | 0.66    | 21.06       | 9.18             | 4.57         |
| 9500  | 13.19 | 19.81     | 8.80              | 7.76               | 0.99      | 0.74    | 20.64       | 8.66             | 4.74         |
| 10000 | 12.56 | 19.99     | 8.45              | 7.80               | 1.01      | 0.81    | 19.34       | 8.15             | 4.92         |
| 10500 | 11.88 | 20.20     | 7.85              | 7.76               | 1.01      | 0.89    | 18.99       | 7.60             | 5.04         |
| 11000 | 11.13 | 20.42     | 7.38              | 7.69               | 1.03      | 0.95    | 18.49       | 7.12             | 5.14         |
| 11500 | 10.32 | 20.71     | 6.98              | 7.30               | 1.06      | 0.99    | 18.06       | 6.69             | 5.36         |
| 12000 | 9.46  | 21.03     | 6.47              | 6.85               | 1.09      | 1.01    | 16.48       | 6.20             | 5.49         |
| 12500 | 8.59  | 21.31     | 6.13              | 6.26               | 1.13      | 1.01    | 16.22       | 5.77             | 5.53         |
| 13000 | 7.56  | 21.71     | 5.60              | 5.74               | 1.18      | 1.00    | 15.38       | 5.50             | 5.75         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 42.29mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.42 | 20.98     | 13.94             | 13.51              | 1.09      | 0.62    | 24.33       | 15.89            | 5.21         |
| 100   | 17.41 | 19.91     | 18.48             | 18.15              | 1.04      | 0.41    | 27.46       | 13.91            | 4.07         |
| 200   | 17.57 | 19.79     | 26.64             | 23.45              | 1.03      | 0.39    | 28.37       | 14.75            | 3.57         |
| 400   | 17.42 | 20.01     | 37.25             | 23.51              | 1.04      | 0.44    | 29.21       | 15.42            | 3.61         |
| 600   | 17.35 | 20.09     | 42.33             | 22.63              | 1.05      | 0.46    | 29.00       | 15.56            | 3.56         |
| 800   | 17.31 | 20.13     | 42.91             | 21.79              | 1.05      | 0.47    | 29.22       | 15.59            | 3.64         |
| 1000  | 17.28 | 20.15     | 39.72             | 20.96              | 1.05      | 0.47    | 28.07       | 15.39            | 3.66         |
| 1200  | 17.26 | 20.16     | 36.44             | 20.14              | 1.05      | 0.48    | 28.84       | 15.38            | 3.68         |
| 1400  | 17.24 | 20.17     | 33.31             | 19.35              | 1.05      | 0.48    | 28.57       | 15.31            | 3.74         |
| 1600  | 17.22 | 20.17     | 30.90             | 18.79              | 1.05      | 0.48    | 28.80       | 15.36            | 3.73         |
| 1800  | 17.20 | 20.17     | 28.78             | 18.12              | 1.05      | 0.48    | 29.14       | 15.42            | 3.77         |
| 2000  | 17.19 | 20.16     | 27.05             | 17.52              | 1.05      | 0.47    | 28.68       | 15.30            | 3.78         |
| 2200  | 17.17 | 20.15     | 25.87             | 17.10              | 1.05      | 0.47    | 27.76       | 14.80            | 3.80         |
| 2400  | 17.15 | 20.13     | 24.64             | 16.54              | 1.05      | 0.47    | 28.15       | 14.89            | 3.77         |
| 2600  | 17.14 | 20.11     | 23.88             | 16.27              | 1.05      | 0.47    | 28.11       | 14.87            | 3.88         |
| 2800  | 17.13 | 20.09     | 22.89             | 15.93              | 1.04      | 0.46    | 27.90       | 14.90            | 3.89         |
| 3000  | 17.11 | 20.06     | 22.21             | 15.59              | 1.04      | 0.46    | 27.34       | 14.60            | 3.79         |
| 3200  | 17.10 | 20.02     | 21.75             | 15.48              | 1.04      | 0.46    | 27.07       | 14.78            | 3.85         |
| 3400  | 17.09 | 19.98     | 21.30             | 15.14              | 1.04      | 0.45    | 27.02       | 14.60            | 3.85         |
| 3600  | 17.08 | 19.93     | 21.31             | 15.12              | 1.03      | 0.45    | 26.61       | 14.41            | 3.85         |
| 3800  | 17.06 | 19.88     | 21.09             | 14.99              | 1.03      | 0.45    | 26.50       | 14.52            | 3.85         |
| 4000  | 17.05 | 19.82     | 21.26             | 14.80              | 1.03      | 0.44    | 26.06       | 14.40            | 3.94         |
| 4500  | 17.00 | 19.66     | 22.41             | 14.66              | 1.02      | 0.43    | 25.45       | 13.95            | 3.91         |
| 5000  | 16.93 | 19.49     | 25.30             | 14.12              | 1.01      | 0.42    | 24.48       | 13.43            | 3.96         |
| 5500  | 16.81 | 19.31     | 26.63             | 13.47              | 1.00      | 0.41    | 24.60       | 13.32            | 3.99         |
| 6000  | 16.59 | 19.19     | 23.14             | 12.19              | 0.99      | 0.41    | 23.90       | 12.97            | 4.00         |
| 6500  | 16.29 | 19.13     | 18.86             | 10.91              | 0.99      | 0.42    | 23.72       | 12.45            | 4.13         |
| 7000  | 15.91 | 19.11     | 15.45             | 9.73               | 0.98      | 0.43    | 23.48       | 11.87            | 4.13         |
| 7500  | 15.42 | 19.17     | 13.04             | 8.80               | 0.98      | 0.47    | 22.81       | 11.13            | 4.16         |
| 8000  | 14.88 | 19.26     | 11.43             | 8.16               | 0.97      | 0.52    | 22.67       | 10.40            | 4.24         |
| 8500  | 14.29 | 19.38     | 10.30             | 7.68               | 0.97      | 0.58    | 21.58       | 9.75             | 4.31         |
| 9000  | 13.65 | 19.53     | 9.25              | 7.51               | 0.97      | 0.66    | 20.60       | 8.87             | 4.49         |
| 9500  | 12.99 | 19.70     | 8.79              | 7.59               | 0.99      | 0.74    | 20.19       | 8.34             | 4.68         |
| 10000 | 12.36 | 19.87     | 8.44              | 7.62               | 1.01      | 0.81    | 18.85       | 7.86             | 4.83         |
| 10500 | 11.68 | 20.08     | 7.85              | 7.59               | 1.01      | 0.88    | 18.44       | 7.27             | 4.96         |
| 11000 | 10.94 | 20.31     | 7.38              | 7.54               | 1.03      | 0.95    | 17.95       | 6.79             | 5.08         |
| 11500 | 10.14 | 20.59     | 6.98              | 7.17               | 1.06      | 0.98    | 17.47       | 6.37             | 5.21         |
| 12000 | 9.29  | 20.90     | 6.48              | 6.76               | 1.09      | 1.01    | 15.91       | 5.88             | 5.37         |
| 12500 | 8.43  | 21.19     | 6.14              | 6.20               | 1.13      | 1.00    | 15.65       | 5.41             | 5.40         |
| 13000 | 7.41  | 21.59     | 5.61              | 5.70               | 1.18      | 1.00    | 14.90       | 5.17             | 5.62         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 51.82mA @ Temperature = +25°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.54 | 21.00     | 15.22             | 15.25              | 1.09      | 0.63    | 22.38       | 17.96            | 5.11         |
| 100   | 17.48 | 20.15     | 19.29             | 18.84              | 1.04      | 0.44    | 24.55       | 17.36            | 4.14         |
| 200   | 17.72 | 19.93     | 28.89             | 24.74              | 1.03      | 0.39    | 29.38       | 17.26            | 3.61         |
| 400   | 17.58 | 20.12     | 58.48             | 25.42              | 1.04      | 0.44    | 32.16       | 17.34            | 3.67         |
| 600   | 17.51 | 20.21     | 44.51             | 24.37              | 1.05      | 0.46    | 31.84       | 17.38            | 3.70         |
| 800   | 17.48 | 20.24     | 44.57             | 23.36              | 1.05      | 0.47    | 32.27       | 17.38            | 3.74         |
| 1000  | 17.45 | 20.26     | 47.12             | 22.38              | 1.05      | 0.47    | 30.68       | 17.23            | 3.73         |
| 1200  | 17.43 | 20.27     | 44.76             | 21.43              | 1.05      | 0.47    | 31.51       | 17.24            | 3.78         |
| 1400  | 17.41 | 20.28     | 39.11             | 20.54              | 1.05      | 0.47    | 31.34       | 17.17            | 3.82         |
| 1600  | 17.40 | 20.29     | 35.30             | 19.92              | 1.05      | 0.47    | 31.37       | 17.19            | 3.82         |
| 1800  | 17.38 | 20.29     | 31.96             | 19.18              | 1.05      | 0.47    | 31.69       | 17.21            | 3.87         |
| 2000  | 17.37 | 20.28     | 29.49             | 18.52              | 1.05      | 0.47    | 30.82       | 17.09            | 3.85         |
| 2200  | 17.36 | 20.27     | 28.02             | 18.06              | 1.05      | 0.47    | 30.10       | 16.69            | 3.87         |
| 2400  | 17.34 | 20.26     | 26.42             | 17.46              | 1.05      | 0.47    | 30.19       | 16.73            | 3.87         |
| 2600  | 17.34 | 20.24     | 25.48             | 17.17              | 1.05      | 0.46    | 29.98       | 16.67            | 3.96         |
| 2800  | 17.33 | 20.22     | 24.32             | 16.82              | 1.04      | 0.46    | 29.55       | 16.62            | 3.99         |
| 3000  | 17.32 | 20.19     | 23.48             | 16.45              | 1.04      | 0.46    | 28.90       | 16.29            | 3.86         |
| 3200  | 17.31 | 20.16     | 22.97             | 16.33              | 1.04      | 0.45    | 28.52       | 16.39            | 3.94         |
| 3400  | 17.30 | 20.12     | 22.40             | 15.98              | 1.04      | 0.45    | 28.31       | 16.17            | 3.94         |
| 3600  | 17.29 | 20.08     | 22.40             | 15.96              | 1.04      | 0.45    | 27.88       | 15.93            | 3.93         |
| 3800  | 17.28 | 20.03     | 22.14             | 15.82              | 1.03      | 0.44    | 27.56       | 15.93            | 3.96         |
| 4000  | 17.27 | 19.98     | 22.30             | 15.63              | 1.03      | 0.44    | 27.08       | 15.70            | 4.01         |
| 4500  | 17.24 | 19.84     | 23.58             | 15.49              | 1.02      | 0.43    | 26.24       | 15.11            | 3.99         |
| 5000  | 17.19 | 19.68     | 27.04             | 14.90              | 1.01      | 0.41    | 25.22       | 14.51            | 4.08         |
| 5500  | 17.08 | 19.52     | 28.27             | 14.17              | 1.01      | 0.40    | 25.22       | 14.27            | 4.11         |
| 6000  | 16.88 | 19.41     | 23.46             | 12.76              | 1.00      | 0.40    | 24.40       | 13.84            | 4.12         |
| 6500  | 16.60 | 19.36     | 18.90             | 11.36              | 0.99      | 0.41    | 24.23       | 13.23            | 4.23         |
| 7000  | 16.24 | 19.34     | 15.45             | 10.12              | 0.99      | 0.42    | 24.03       | 12.56            | 4.23         |
| 7500  | 15.78 | 19.40     | 13.04             | 9.13               | 0.98      | 0.46    | 23.47       | 11.76            | 4.28         |
| 8000  | 15.25 | 19.49     | 11.43             | 8.46               | 0.98      | 0.51    | 23.33       | 11.07            | 4.36         |
| 8500  | 14.68 | 19.60     | 10.30             | 7.97               | 0.98      | 0.57    | 22.41       | 10.41            | 4.47         |
| 9000  | 14.05 | 19.75     | 9.25              | 7.79               | 0.98      | 0.65    | 21.49       | 9.50             | 4.66         |
| 9500  | 13.40 | 19.92     | 8.80              | 7.89               | 0.99      | 0.74    | 21.11       | 9.01             | 4.85         |
| 10000 | 12.77 | 20.09     | 8.46              | 7.91               | 1.01      | 0.81    | 19.90       | 8.51             | 5.00         |
| 10500 | 12.09 | 20.30     | 7.86              | 7.90               | 1.01      | 0.89    | 19.60       | 7.96             | 5.16         |
| 11000 | 11.34 | 20.53     | 7.40              | 7.81               | 1.03      | 0.95    | 19.13       | 7.43             | 5.31         |
| 11500 | 10.53 | 20.81     | 6.98              | 7.41               | 1.06      | 0.99    | 18.68       | 7.05             | 5.47         |
| 12000 | 9.66  | 21.13     | 6.48              | 6.93               | 1.09      | 1.02    | 17.07       | 6.50             | 5.65         |
| 12500 | 8.78  | 21.43     | 6.13              | 6.31               | 1.12      | 1.01    | 16.83       | 6.11             | 5.70         |
| 13000 | 7.73  | 21.83     | 5.59              | 5.78               | 1.18      | 1.01    | 15.98       | 5.84             | 5.93         |



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 43.20mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.62 | 21.17     | 13.52             | 13.51              | 1.09      | 0.62    | 27.66       | 16.26            | 4.47         |
| 100   | 17.66 | 20.06     | 18.41             | 18.12              | 1.03      | 0.40    | 28.50       | 14.10            | 3.38         |
| 200   | 17.84 | 19.92     | 27.64             | 24.04              | 1.03      | 0.38    | 29.23       | 14.96            | 2.89         |
| 400   | 17.69 | 20.14     | 47.97             | 25.09              | 1.04      | 0.43    | 30.08       | 15.62            | 2.93         |
| 600   | 17.63 | 20.22     | 44.81             | 23.99              | 1.04      | 0.45    | 29.92       | 15.79            | 2.95         |
| 800   | 17.60 | 20.25     | 45.67             | 22.99              | 1.04      | 0.45    | 30.31       | 15.82            | 2.97         |
| 1000  | 17.58 | 20.26     | 47.04             | 22.17              | 1.04      | 0.46    | 29.14       | 15.58            | 2.96         |
| 1200  | 17.56 | 20.27     | 61.39             | 21.23              | 1.04      | 0.46    | 29.84       | 15.60            | 3.03         |
| 1400  | 17.55 | 20.27     | 48.68             | 20.40              | 1.04      | 0.46    | 29.71       | 15.55            | 3.04         |
| 1600  | 17.54 | 20.27     | 40.67             | 19.67              | 1.04      | 0.45    | 29.96       | 15.65            | 3.08         |
| 1800  | 17.53 | 20.26     | 35.75             | 18.89              | 1.04      | 0.45    | 30.22       | 15.76            | 3.07         |
| 2000  | 17.52 | 20.25     | 33.61             | 18.29              | 1.04      | 0.45    | 29.82       | 15.63            | 3.10         |
| 2200  | 17.51 | 20.23     | 32.07             | 17.88              | 1.04      | 0.45    | 28.90       | 15.04            | 3.09         |
| 2400  | 17.50 | 20.20     | 30.49             | 17.24              | 1.04      | 0.44    | 29.51       | 15.24            | 3.08         |
| 2600  | 17.50 | 20.18     | 29.61             | 16.90              | 1.04      | 0.44    | 29.34       | 15.28            | 3.17         |
| 2800  | 17.49 | 20.15     | 27.70             | 16.46              | 1.03      | 0.43    | 29.17       | 15.33            | 3.20         |
| 3000  | 17.49 | 20.12     | 26.97             | 16.07              | 1.03      | 0.43    | 28.57       | 15.06            | 3.06         |
| 3200  | 17.49 | 20.08     | 26.37             | 15.86              | 1.03      | 0.42    | 28.38       | 15.25            | 3.12         |
| 3400  | 17.48 | 20.04     | 25.99             | 15.37              | 1.03      | 0.41    | 28.31       | 15.12            | 3.14         |
| 3600  | 17.48 | 19.99     | 26.34             | 15.23              | 1.02      | 0.41    | 27.97       | 14.92            | 3.10         |
| 3800  | 17.47 | 19.94     | 25.53             | 14.97              | 1.02      | 0.40    | 27.85       | 15.09            | 3.14         |
| 4000  | 17.47 | 19.89     | 25.86             | 14.66              | 1.02      | 0.39    | 27.33       | 15.06            | 3.17         |
| 4500  | 17.46 | 19.73     | 27.07             | 14.13              | 1.01      | 0.37    | 26.74       | 14.67            | 3.16         |
| 5000  | 17.44 | 19.57     | 30.39             | 13.42              | 1.00      | 0.35    | 25.65       | 14.02            | 3.20         |
| 5500  | 17.38 | 19.40     | 28.15             | 12.62              | 0.98      | 0.33    | 25.72       | 14.12            | 3.24         |
| 6000  | 17.23 | 19.28     | 22.45             | 11.17              | 0.97      | 0.31    | 24.87       | 13.95            | 3.26         |
| 6500  | 17.02 | 19.23     | 18.14             | 9.81               | 0.96      | 0.30    | 24.60       | 13.52            | 3.37         |
| 7000  | 16.73 | 19.21     | 14.80             | 8.66               | 0.95      | 0.30    | 24.63       | 13.10            | 3.39         |
| 7500  | 16.35 | 19.27     | 12.46             | 7.67               | 0.94      | 0.32    | 24.12       | 12.36            | 3.41         |
| 8000  | 15.92 | 19.35     | 11.14             | 7.05               | 0.93      | 0.35    | 23.92       | 11.59            | 3.48         |
| 8500  | 15.45 | 19.44     | 10.05             | 6.61               | 0.92      | 0.40    | 22.87       | 10.89            | 3.54         |
| 9000  | 14.93 | 19.59     | 9.09              | 6.42               | 0.91      | 0.48    | 22.19       | 9.95             | 3.73         |
| 9500  | 14.44 | 19.69     | 8.89              | 6.58               | 0.91      | 0.57    | 21.69       | 9.42             | 3.87         |
| 10000 | 13.93 | 19.83     | 8.54              | 6.70               | 0.91      | 0.65    | 20.37       | 8.89             | 4.05         |
| 10500 | 13.45 | 19.96     | 8.17              | 6.89               | 0.90      | 0.74    | 20.06       | 8.31             | 4.13         |
| 11000 | 12.90 | 20.10     | 7.80              | 7.02               | 0.89      | 0.83    | 19.66       | 7.82             | 4.24         |
| 11500 | 12.22 | 20.32     | 7.42              | 6.85               | 0.89      | 0.89    | 19.22       | 7.41             | 4.37         |
| 12000 | 11.52 | 20.58     | 6.82              | 6.73               | 0.88      | 0.96    | 17.65       | 6.89             | 4.52         |
| 12500 | 10.74 | 20.83     | 6.50              | 6.10               | 0.87      | 0.96    | 17.99       | 6.45             | 4.49         |
| 13000 | 9.72  | 21.25     | 5.78              | 5.68               | 0.88      | 0.99    | 16.21       | 6.11             | 4.68         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 38.51mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               |           |         | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.53 | 21.08     | 13.71             | 13.41              | 1.09      | 0.61    | 28.71       | 13.77            | 4.40         |
| 100   | 17.56 | 19.99     | 18.38             | 17.94              | 1.03      | 0.40    | 26.55       | 12.49            | 3.35         |
| 200   | 17.74 | 19.86     | 26.52             | 23.27              | 1.03      | 0.38    | 27.41       | 13.63            | 2.92         |
| 400   | 17.60 | 20.07     | 39.21             | 23.97              | 1.04      | 0.43    | 28.08       | 14.35            | 2.88         |
| 600   | 17.53 | 20.15     | 43.22             | 22.98              | 1.04      | 0.45    | 27.97       | 14.52            | 2.92         |
| 800   | 17.50 | 20.18     | 45.85             | 22.10              | 1.04      | 0.45    | 28.28       | 14.55            | 3.00         |
| 1000  | 17.48 | 20.19     | 48.22             | 21.36              | 1.04      | 0.46    | 27.25       | 14.37            | 2.92         |
| 1200  | 17.46 | 20.20     | 42.85             | 20.50              | 1.04      | 0.46    | 27.91       | 14.36            | 3.01         |
| 1400  | 17.45 | 20.20     | 39.53             | 19.73              | 1.04      | 0.46    | 27.91       | 14.33            | 3.02         |
| 1600  | 17.44 | 20.19     | 35.71             | 19.04              | 1.04      | 0.46    | 28.21       | 14.44            | 3.01         |
| 1800  | 17.42 | 20.19     | 32.80             | 18.30              | 1.04      | 0.45    | 28.51       | 14.52            | 3.05         |
| 2000  | 17.41 | 20.17     | 31.29             | 17.74              | 1.04      | 0.45    | 28.11       | 14.44            | 3.06         |
| 2200  | 17.41 | 20.15     | 29.99             | 17.35              | 1.04      | 0.45    | 27.20       | 13.81            | 3.08         |
| 2400  | 17.40 | 20.13     | 28.80             | 16.73              | 1.04      | 0.44    | 27.73       | 14.01            | 3.04         |
| 2600  | 17.39 | 20.10     | 28.10             | 16.41              | 1.04      | 0.44    | 27.81       | 14.08            | 3.15         |
| 2800  | 17.38 | 20.07     | 26.46             | 15.98              | 1.03      | 0.43    | 27.70       | 14.14            | 3.18         |
| 3000  | 17.37 | 20.03     | 25.87             | 15.61              | 1.03      | 0.43    | 27.18       | 13.91            | 3.04         |
| 3200  | 17.37 | 19.99     | 25.33             | 15.40              | 1.03      | 0.42    | 27.02       | 14.12            | 3.10         |
| 3400  | 17.36 | 19.95     | 25.03             | 14.92              | 1.02      | 0.42    | 27.10       | 14.03            | 3.08         |
| 3600  | 17.36 | 19.90     | 25.32             | 14.79              | 1.02      | 0.41    | 26.83       | 13.85            | 3.07         |
| 3800  | 17.35 | 19.85     | 24.62             | 14.54              | 1.02      | 0.40    | 26.77       | 14.06            | 3.11         |
| 4000  | 17.35 | 19.79     | 24.95             | 14.25              | 1.01      | 0.40    | 26.37       | 14.11            | 3.16         |
| 4500  | 17.33 | 19.63     | 26.04             | 13.73              | 1.00      | 0.38    | 25.91       | 13.85            | 3.13         |
| 5000  | 17.30 | 19.46     | 28.88             | 13.05              | 0.99      | 0.35    | 24.89       | 13.20            | 3.16         |
| 5500  | 17.24 | 19.28     | 27.41             | 12.28              | 0.98      | 0.33    | 25.11       | 13.45            | 3.22         |
| 6000  | 17.08 | 19.15     | 22.38             | 10.89              | 0.97      | 0.31    | 24.36       | 13.34            | 3.22         |
| 6500  | 16.87 | 19.09     | 18.12             | 9.58               | 0.96      | 0.30    | 24.19       | 13.00            | 3.32         |
| 7000  | 16.57 | 19.08     | 14.78             | 8.47               | 0.95      | 0.30    | 24.13       | 12.65            | 3.32         |
| 7500  | 16.17 | 19.14     | 12.45             | 7.52               | 0.94      | 0.32    | 23.58       | 11.97            | 3.37         |
| 8000  | 15.73 | 19.22     | 11.13             | 6.90               | 0.92      | 0.36    | 23.38       | 11.20            | 3.41         |
| 8500  | 15.25 | 19.31     | 10.03             | 6.47               | 0.91      | 0.40    | 22.31       | 10.54            | 3.50         |
| 9000  | 14.73 | 19.46     | 9.08              | 6.28               | 0.90      | 0.48    | 21.59       | 9.61             | 3.66         |
| 9500  | 14.22 | 19.57     | 8.87              | 6.43               | 0.91      | 0.57    | 21.13       | 9.07             | 3.82         |
| 10000 | 13.74 | 19.71     | 8.52              | 6.54               | 0.91      | 0.64    | 19.79       | 8.56             | 3.98         |
| 10500 | 13.24 | 19.83     | 8.16              | 6.72               | 0.89      | 0.74    | 19.47       | 7.97             | 4.05         |
| 11000 | 12.69 | 19.97     | 7.79              | 6.86               | 0.89      | 0.82    | 19.06       | 7.49             | 4.18         |
| 11500 | 12.02 | 20.19     | 7.42              | 6.70               | 0.88      | 0.88    | 18.57       | 7.08             | 4.27         |
| 12000 | 11.33 | 20.44     | 6.84              | 6.63               | 0.88      | 0.95    | 17.03       | 6.51             | 4.43         |
| 12500 | 10.57 | 20.69     | 6.53              | 6.02               | 0.87      | 0.96    | 17.27       | 6.05             | 4.44         |
| 13000 | 9.57  | 21.10     | 5.80              | 5.64               | 0.88      | 0.99    | 15.61       | 5.74             | 4.60         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 47.64mA @ Temperature = -45°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.68 | 21.23     | 13.40             | 13.59              | 1.09      | 0.62    | 19.42       | 17.53            | 4.52         |
| 100   | 17.73 | 20.11     | 18.42             | 18.23              | 1.03      | 0.40    | 29.16       | 15.74            | 3.44         |
| 200   | 17.91 | 19.97     | 28.47             | 24.58              | 1.03      | 0.37    | 30.81       | 16.09            | 2.98         |
| 400   | 17.76 | 20.19     | 52.03             | 25.97              | 1.04      | 0.43    | 31.58       | 16.66            | 2.94         |
| 600   | 17.70 | 20.27     | 40.25             | 24.78              | 1.04      | 0.44    | 31.43       | 16.78            | 2.96         |
| 800   | 17.67 | 20.30     | 40.01             | 23.70              | 1.04      | 0.45    | 31.59       | 16.81            | 3.02         |
| 1000  | 17.65 | 20.31     | 40.33             | 22.80              | 1.04      | 0.45    | 30.57       | 16.59            | 3.00         |
| 1200  | 17.63 | 20.32     | 44.79             | 21.80              | 1.04      | 0.45    | 31.29       | 16.61            | 3.05         |
| 1400  | 17.62 | 20.32     | 48.94             | 20.93              | 1.04      | 0.45    | 31.12       | 16.55            | 3.08         |
| 1600  | 17.61 | 20.32     | 46.26             | 20.17              | 1.04      | 0.45    | 31.25       | 16.64            | 3.06         |
| 1800  | 17.60 | 20.31     | 38.46             | 19.35              | 1.04      | 0.45    | 31.67       | 16.72            | 3.13         |
| 2000  | 17.59 | 20.30     | 35.60             | 18.73              | 1.04      | 0.45    | 31.16       | 16.61            | 3.13         |
| 2200  | 17.59 | 20.28     | 33.86             | 18.31              | 1.04      | 0.44    | 30.27       | 16.05            | 3.10         |
| 2400  | 17.58 | 20.26     | 31.86             | 17.65              | 1.04      | 0.44    | 30.61       | 16.21            | 3.10         |
| 2600  | 17.58 | 20.23     | 30.87             | 17.30              | 1.04      | 0.44    | 30.66       | 16.23            | 3.21         |
| 2800  | 17.58 | 20.21     | 28.77             | 16.84              | 1.03      | 0.43    | 30.14       | 16.23            | 3.21         |
| 3000  | 17.57 | 20.17     | 27.88             | 16.45              | 1.03      | 0.43    | 29.66       | 15.95            | 3.09         |
| 3200  | 17.57 | 20.14     | 27.22             | 16.23              | 1.03      | 0.42    | 29.30       | 16.10            | 3.15         |
| 3400  | 17.57 | 20.10     | 26.77             | 15.72              | 1.03      | 0.41    | 29.17       | 15.97            | 3.16         |
| 3600  | 17.57 | 20.06     | 27.14             | 15.59              | 1.02      | 0.41    | 28.76       | 15.77            | 3.14         |
| 3800  | 17.57 | 20.01     | 26.25             | 15.33              | 1.02      | 0.40    | 28.58       | 15.86            | 3.16         |
| 4000  | 17.57 | 19.96     | 26.59             | 15.02              | 1.02      | 0.39    | 28.01       | 15.78            | 3.20         |
| 4500  | 17.56 | 19.81     | 27.89             | 14.47              | 1.01      | 0.37    | 27.32       | 15.27            | 3.20         |
| 5000  | 17.54 | 19.65     | 31.62             | 13.73              | 1.00      | 0.35    | 26.12       | 14.61            | 3.28         |
| 5500  | 17.49 | 19.49     | 28.60             | 12.90              | 0.99      | 0.33    | 26.07       | 14.65            | 3.27         |
| 6000  | 17.35 | 19.37     | 22.47             | 11.40              | 0.98      | 0.31    | 25.23       | 14.43            | 3.31         |
| 6500  | 17.15 | 19.32     | 18.10             | 9.98               | 0.97      | 0.29    | 24.96       | 13.95            | 3.44         |
| 7000  | 16.88 | 19.31     | 14.77             | 8.82               | 0.96      | 0.29    | 24.91       | 13.48            | 3.44         |
| 7500  | 16.50 | 19.37     | 12.45             | 7.81               | 0.94      | 0.31    | 24.47       | 12.69            | 3.48         |
| 8000  | 16.08 | 19.44     | 11.13             | 7.17               | 0.93      | 0.35    | 24.37       | 11.89            | 3.51         |
| 8500  | 15.62 | 19.54     | 10.04             | 6.73               | 0.92      | 0.40    | 23.29       | 11.20            | 3.60         |
| 9000  | 15.11 | 19.68     | 9.09              | 6.53               | 0.91      | 0.48    | 22.61       | 10.23            | 3.79         |
| 9500  | 14.62 | 19.79     | 8.89              | 6.70               | 0.91      | 0.57    | 22.12       | 9.72             | 3.94         |
| 10000 | 14.14 | 19.93     | 8.54              | 6.84               | 0.91      | 0.65    | 20.81       | 9.18             | 4.13         |
| 10500 | 13.64 | 20.05     | 8.18              | 7.03               | 0.90      | 0.75    | 20.57       | 8.61             | 4.19         |
| 11000 | 13.08 | 20.20     | 7.80              | 7.17               | 0.89      | 0.83    | 20.16       | 8.15             | 4.33         |
| 11500 | 12.39 | 20.42     | 7.42              | 6.97               | 0.89      | 0.89    | 19.75       | 7.75             | 4.44         |
| 12000 | 11.68 | 20.68     | 6.81              | 6.84               | 0.88      | 0.96    | 18.27       | 7.22             | 4.60         |
| 12500 | 10.89 | 20.94     | 6.49              | 6.16               | 0.87      | 0.97    | 18.65       | 6.80             | 4.59         |
| 13000 | 9.85  | 21.35     | 5.75              | 5.72               | 0.88      | 1.00    | 16.79       | 6.44             | 4.77         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 50.52mA @ Temperature = +85°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.39 | 20.84     | 16.42             | 15.45              | 1.10      | 0.63    | 23.95       | 17.44            | 5.49         |
| 100   | 17.23 | 20.07     | 19.91             | 18.88              | 1.05      | 0.46    | 26.06       | 16.99            | 4.71         |
| 200   | 17.48 | 19.84     | 28.17             | 24.10              | 1.04      | 0.41    | 29.42       | 16.86            | 4.22         |
| 400   | 17.35 | 20.02     | 40.82             | 23.96              | 1.05      | 0.45    | 31.74       | 16.90            | 4.25         |
| 600   | 17.28 | 20.10     | 46.46             | 22.97              | 1.05      | 0.47    | 31.26       | 16.93            | 4.29         |
| 800   | 17.24 | 20.14     | 45.27             | 22.23              | 1.05      | 0.48    | 31.32       | 16.90            | 4.32         |
| 1000  | 17.20 | 20.16     | 38.52             | 21.26              | 1.05      | 0.49    | 29.78       | 16.78            | 4.35         |
| 1200  | 17.18 | 20.18     | 34.66             | 20.42              | 1.06      | 0.49    | 30.67       | 16.78            | 4.41         |
| 1400  | 17.16 | 20.19     | 31.23             | 19.51              | 1.06      | 0.49    | 30.37       | 16.70            | 4.44         |
| 1600  | 17.13 | 20.20     | 28.82             | 18.86              | 1.06      | 0.49    | 30.46       | 16.69            | 4.42         |
| 1800  | 17.11 | 20.20     | 26.45             | 18.22              | 1.06      | 0.49    | 30.61       | 16.67            | 4.51         |
| 2000  | 17.09 | 20.20     | 24.68             | 17.57              | 1.06      | 0.49    | 29.81       | 16.53            | 4.52         |
| 2200  | 17.07 | 20.19     | 23.31             | 17.10              | 1.06      | 0.49    | 29.06       | 16.23            | 4.51         |
| 2400  | 17.05 | 20.18     | 21.92             | 16.55              | 1.06      | 0.48    | 29.26       | 16.20            | 4.50         |
| 2600  | 17.03 | 20.17     | 21.42             | 16.36              | 1.05      | 0.48    | 28.79       | 16.10            | 4.60         |
| 2800  | 17.01 | 20.15     | 20.56             | 16.02              | 1.05      | 0.48    | 28.32       | 16.00            | 4.64         |
| 3000  | 16.99 | 20.12     | 19.97             | 15.83              | 1.05      | 0.48    | 27.82       | 15.69            | 4.54         |
| 3200  | 16.97 | 20.08     | 19.72             | 15.99              | 1.05      | 0.48    | 27.51       | 15.70            | 4.60         |
| 3400  | 16.95 | 20.05     | 19.03             | 15.83              | 1.05      | 0.48    | 27.23       | 15.45            | 4.60         |
| 3600  | 16.93 | 20.00     | 19.14             | 15.80              | 1.05      | 0.48    | 26.85       | 15.17            | 4.60         |
| 3800  | 16.91 | 19.95     | 19.16             | 16.05              | 1.04      | 0.48    | 26.59       | 15.08            | 4.60         |
| 4000  | 16.87 | 19.90     | 19.10             | 15.86              | 1.04      | 0.48    | 26.14       | 14.82            | 4.68         |
| 4500  | 16.79 | 19.74     | 20.39             | 16.45              | 1.04      | 0.48    | 25.47       | 14.17            | 4.66         |
| 5000  | 16.67 | 19.57     | 23.08             | 16.64              | 1.03      | 0.48    | 24.62       | 13.50            | 4.74         |
| 5500  | 16.46 | 19.43     | 25.51             | 15.90              | 1.03      | 0.48    | 24.58       | 13.07            | 4.79         |
| 6000  | 16.15 | 19.32     | 22.93             | 14.48              | 1.03      | 0.50    | 23.78       | 12.44            | 4.81         |
| 6500  | 15.75 | 19.27     | 18.49             | 13.16              | 1.03      | 0.53    | 23.29       | 11.83            | 4.92         |
| 7000  | 15.23 | 19.30     | 14.80             | 11.50              | 1.04      | 0.56    | 22.63       | 11.07            | 4.97         |
| 7500  | 14.69 | 19.33     | 13.02             | 10.65              | 1.04      | 0.61    | 21.67       | 10.34            | 5.01         |
| 8000  | 14.05 | 19.41     | 11.07             | 10.01              | 1.05      | 0.67    | 21.47       | 9.73             | 5.09         |
| 8500  | 13.31 | 19.58     | 9.92              | 9.32               | 1.06      | 0.74    | 20.42       | 9.11             | 5.19         |
| 9000  | 12.61 | 19.72     | 9.16              | 9.12               | 1.08      | 0.80    | 19.42       | 8.26             | 5.39         |
| 9500  | 11.83 | 19.93     | 8.40              | 8.92               | 1.10      | 0.88    | 19.11       | 7.81             | 5.61         |
| 10000 | 11.08 | 20.13     | 8.09              | 8.80               | 1.14      | 0.93    | 17.96       | 7.32             | 5.81         |
| 10500 | 10.29 | 20.37     | 7.57              | 8.43               | 1.17      | 0.98    | 17.54       | 6.77             | 5.97         |
| 11000 | 9.40  | 20.68     | 7.15              | 7.89               | 1.22      | 1.01    | 17.07       | 6.29             | 6.14         |
| 11500 | 8.44  | 21.02     | 6.63              | 7.49               | 1.30      | 1.03    | 16.64       | 5.90             | 6.33         |
| 12000 | 7.50  | 21.36     | 6.30              | 6.74               | 1.37      | 1.02    | 15.29       | 5.38             | 6.46         |
| 12500 | 6.55  | 21.72     | 6.02              | 6.20               | 1.48      | 1.01    | 14.89       | 4.98             | 6.54         |
| 13000 | 5.54  | 22.08     | 5.67              | 5.69               | 1.60      | 0.99    | 14.62       | 4.81             | 6.82         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 45.40mA @ Temperature = +85°C

| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 16.32 | 20.88     | 14.26             | 13.69              | 1.10      | 0.62    | 19.66       | 16.54            | 5.84         |
| 100   | 17.28 | 19.86     | 18.58             | 18.31              | 1.04      | 0.43    | 25.29       | 15.31            | 4.69         |
| 200   | 17.42 | 19.73     | 26.51             | 23.48              | 1.03      | 0.41    | 28.97       | 15.62            | 4.24         |
| 400   | 17.26 | 19.94     | 35.34             | 22.99              | 1.05      | 0.45    | 29.84       | 15.98            | 4.23         |
| 600   | 17.19 | 20.03     | 38.20             | 22.07              | 1.05      | 0.47    | 29.56       | 16.06            | 4.23         |
| 800   | 17.14 | 20.07     | 38.32             | 21.39              | 1.05      | 0.48    | 29.75       | 16.04            | 4.30         |
| 1000  | 17.11 | 20.10     | 34.72             | 20.49              | 1.05      | 0.49    | 28.45       | 15.90            | 4.28         |
| 1200  | 17.08 | 20.11     | 32.08             | 19.71              | 1.06      | 0.49    | 29.31       | 15.89            | 4.38         |
| 1400  | 17.06 | 20.13     | 29.45             | 18.86              | 1.06      | 0.49    | 29.02       | 15.83            | 4.39         |
| 1600  | 17.03 | 20.13     | 27.42             | 18.24              | 1.06      | 0.49    | 29.14       | 15.82            | 4.39         |
| 1800  | 17.01 | 20.13     | 25.37             | 17.63              | 1.06      | 0.49    | 29.37       | 15.82            | 4.44         |
| 2000  | 16.99 | 20.13     | 23.81             | 17.02              | 1.06      | 0.49    | 28.87       | 15.66            | 4.44         |
| 2200  | 16.96 | 20.13     | 22.54             | 16.57              | 1.06      | 0.49    | 27.92       | 15.34            | 4.47         |
| 2400  | 16.94 | 20.12     | 21.32             | 16.05              | 1.06      | 0.49    | 28.28       | 15.33            | 4.46         |
| 2600  | 16.92 | 20.10     | 20.84             | 15.86              | 1.05      | 0.49    | 28.05       | 15.26            | 4.57         |
| 2800  | 16.90 | 20.08     | 20.05             | 15.54              | 1.05      | 0.48    | 27.62       | 15.19            | 4.60         |
| 3000  | 16.87 | 20.05     | 19.50             | 15.35              | 1.05      | 0.48    | 27.08       | 14.90            | 4.47         |
| 3200  | 16.85 | 20.01     | 19.26             | 15.50              | 1.05      | 0.48    | 26.87       | 14.94            | 4.54         |
| 3400  | 16.83 | 19.97     | 18.61             | 15.34              | 1.05      | 0.48    | 26.65       | 14.74            | 4.55         |
| 3600  | 16.81 | 19.93     | 18.74             | 15.30              | 1.05      | 0.48    | 26.32       | 14.45            | 4.53         |
| 3800  | 16.79 | 19.87     | 18.77             | 15.52              | 1.04      | 0.48    | 26.14       | 14.46            | 4.56         |
| 4000  | 16.74 | 19.82     | 18.71             | 15.33              | 1.04      | 0.48    | 25.70       | 14.24            | 4.60         |
| 4500  | 16.66 | 19.65     | 19.96             | 15.86              | 1.04      | 0.48    | 25.14       | 13.67            | 4.61         |
| 5000  | 16.53 | 19.47     | 22.48             | 16.01              | 1.03      | 0.48    | 24.29       | 13.06            | 4.67         |
| 5500  | 16.31 | 19.32     | 24.74             | 15.34              | 1.03      | 0.49    | 24.35       | 12.67            | 4.71         |
| 6000  | 16.00 | 19.21     | 22.59             | 14.03              | 1.03      | 0.50    | 23.57       | 12.07            | 4.74         |
| 6500  | 15.59 | 19.15     | 18.39             | 12.80              | 1.03      | 0.53    | 23.08       | 11.49            | 4.87         |
| 7000  | 15.06 | 19.18     | 14.77             | 11.22              | 1.03      | 0.56    | 22.37       | 10.76            | 4.88         |
| 7500  | 14.51 | 19.21     | 13.00             | 10.39              | 1.04      | 0.61    | 21.38       | 10.04            | 4.95         |
| 8000  | 13.87 | 19.29     | 11.07             | 9.77               | 1.05      | 0.67    | 21.16       | 9.44             | 4.99         |
| 8500  | 13.12 | 19.47     | 9.91              | 9.09               | 1.06      | 0.73    | 20.08       | 8.79             | 5.09         |
| 9000  | 12.42 | 19.60     | 9.15              | 8.89               | 1.07      | 0.80    | 19.00       | 7.95             | 5.31         |
| 9500  | 11.64 | 19.81     | 8.40              | 8.69               | 1.10      | 0.87    | 18.69       | 7.47             | 5.50         |
| 10000 | 10.89 | 20.02     | 8.08              | 8.58               | 1.14      | 0.93    | 17.50       | 7.02             | 5.70         |
| 10500 | 10.10 | 20.26     | 7.56              | 8.24               | 1.17      | 0.97    | 17.05       | 6.45             | 5.83         |
| 11000 | 9.22  | 20.56     | 7.15              | 7.73               | 1.22      | 1.00    | 16.59       | 5.99             | 6.00         |
| 11500 | 8.27  | 20.90     | 6.62              | 7.37               | 1.29      | 1.03    | 16.18       | 5.56             | 6.18         |
| 12000 | 7.34  | 21.24     | 6.30              | 6.65               | 1.36      | 1.02    | 14.82       | 5.08             | 6.30         |
| 12500 | 6.40  | 21.59     | 6.02              | 6.14               | 1.47      | 1.00    | 14.43       | 4.67             | 6.45         |
| 13000 | 5.40  | 21.95     | 5.67              | 5.64               | 1.59      | 0.98    | 14.16       | 4.45             | 6.63         |

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)









Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 58.21mA @ Temperature = +85°C








| FREQ  | Gain  | Isolation | Input Return Loss | Output Return Loss | Stability |         | IP-3 Output | 1dB Comp. Output | Noise Figure |
|-------|-------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
|       |       |           |                   |                    | K         | Measure |             |                  |              |
| (MHz) | (dB)  | (dB)      | (dB)              | (dB)               | K         | Measure | (dBm)       | (dBm)            | (dB)         |
| 50    | 17.02 | 20.47     | 25.83             | 20.39              | 1.07      | 0.55    | 21.42       | 17.89            | 4.59         |
| 100   | 17.22 | 20.25     | 27.99             | 22.08              | 1.06      | 0.50    | 24.05       | 18.09            | 4.47         |
| 200   | 17.42 | 20.08     | 35.59             | 24.79              | 1.05      | 0.46    | 32.87       | 17.97            | 4.29         |
| 400   | 17.40 | 20.14     | 46.17             | 24.78              | 1.05      | 0.46    | 34.06       | 17.90            | 4.31         |
| 600   | 17.36 | 20.20     | 44.27             | 23.95              | 1.05      | 0.48    | 33.35       | 17.84            | 4.34         |
| 800   | 17.33 | 20.23     | 44.05             | 23.19              | 1.05      | 0.48    | 32.74       | 17.81            | 4.41         |
| 1000  | 17.30 | 20.24     | 43.82             | 22.15              | 1.05      | 0.49    | 31.28       | 17.71            | 4.38         |
| 1200  | 17.28 | 20.26     | 38.72             | 21.25              | 1.05      | 0.49    | 31.94       | 17.73            | 4.45         |
| 1400  | 17.26 | 20.26     | 33.90             | 20.27              | 1.06      | 0.49    | 31.34       | 17.66            | 4.51         |
| 1600  | 17.24 | 20.27     | 30.90             | 19.57              | 1.06      | 0.49    | 31.11       | 17.62            | 4.51         |
| 1800  | 17.22 | 20.27     | 28.04             | 18.89              | 1.06      | 0.49    | 30.93       | 17.59            | 4.55         |
| 2000  | 17.20 | 20.27     | 25.95             | 18.20              | 1.06      | 0.49    | 30.10       | 17.46            | 4.56         |
| 2200  | 17.18 | 20.26     | 24.35             | 17.71              | 1.06      | 0.49    | 29.52       | 17.30            | 4.60         |
| 2400  | 17.16 | 20.25     | 22.81             | 17.14              | 1.06      | 0.48    | 29.18       | 17.21            | 4.60         |
| 2600  | 17.14 | 20.23     | 22.24             | 16.94              | 1.05      | 0.48    | 28.86       | 17.08            | 4.70         |
| 2800  | 17.12 | 20.22     | 21.32             | 16.59              | 1.05      | 0.48    | 28.24       | 16.90            | 4.71         |
| 3000  | 17.10 | 20.19     | 20.67             | 16.39              | 1.05      | 0.48    | 27.76       | 16.63            | 4.59         |
| 3200  | 17.08 | 20.15     | 20.42             | 16.56              | 1.05      | 0.48    | 27.38       | 16.55            | 4.66         |
| 3400  | 17.06 | 20.12     | 19.67             | 16.40              | 1.05      | 0.48    | 27.14       | 16.25            | 4.66         |
| 3600  | 17.04 | 20.07     | 19.78             | 16.37              | 1.05      | 0.48    | 26.78       | 15.93            | 4.67         |
| 3800  | 17.02 | 20.02     | 19.81             | 16.63              | 1.05      | 0.48    | 26.43       | 15.79            | 4.70         |
| 4000  | 16.98 | 19.98     | 19.71             | 16.44              | 1.04      | 0.47    | 26.03       | 15.45            | 4.74         |
| 4500  | 16.90 | 19.83     | 21.15             | 17.08              | 1.04      | 0.47    | 25.34       | 14.73            | 4.74         |
| 5000  | 16.78 | 19.66     | 24.19             | 17.27              | 1.04      | 0.47    | 24.55       | 13.97            | 4.83         |
| 5500  | 16.58 | 19.53     | 26.80             | 16.43              | 1.03      | 0.48    | 24.32       | 13.47            | 4.88         |
| 6000  | 16.29 | 19.43     | 23.29             | 14.87              | 1.03      | 0.50    | 23.60       | 12.78            | 4.90         |
| 6500  | 15.90 | 19.38     | 18.56             | 13.45              | 1.04      | 0.52    | 23.06       | 12.15            | 5.04         |
| 7000  | 15.40 | 19.41     | 14.81             | 11.70              | 1.04      | 0.56    | 22.39       | 11.37            | 5.08         |
| 7500  | 14.87 | 19.44     | 13.04             | 10.83              | 1.04      | 0.60    | 21.50       | 10.65            | 5.12         |
| 8000  | 14.25 | 19.52     | 11.09             | 10.17              | 1.05      | 0.66    | 21.24       | 10.03            | 5.24         |
| 8500  | 13.53 | 19.69     | 9.95              | 9.47               | 1.06      | 0.73    | 20.34       | 9.39             | 5.34         |
| 9000  | 12.84 | 19.82     | 9.19              | 9.29               | 1.08      | 0.80    | 19.38       | 8.52             | 5.59         |
| 9500  | 12.07 | 20.03     | 8.45              | 9.11               | 1.10      | 0.87    | 19.10       | 8.07             | 5.79         |
| 10000 | 11.34 | 20.23     | 8.15              | 9.01               | 1.14      | 0.93    | 18.08       | 7.58             | 6.00         |
| 10500 | 10.55 | 20.47     | 7.64              | 8.65               | 1.17      | 0.98    | 17.64       | 7.01             | 6.19         |
| 11000 | 9.67  | 20.78     | 7.23              | 8.11               | 1.22      | 1.01    | 17.23       | 6.55             | 6.35         |
| 11500 | 8.70  | 21.12     | 6.69              | 7.69               | 1.30      | 1.04    | 16.83       | 6.17             | 6.59         |
| 12000 | 7.76  | 21.48     | 6.37              | 6.90               | 1.37      | 1.03    | 15.55       | 5.65             | 6.72         |
| 12500 | 6.80  | 21.84     | 6.08              | 6.33               | 1.48      | 1.01    | 15.16       | 5.27             | 6.85         |
| 13000 | 5.78  | 22.23     | 5.72              | 5.78               | 1.60      | 0.99    | 14.94       | 5.07             | 7.13         |



## Typical Performance Curves



## Typical Performance Curves





### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | M              | N              |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| DQ849  | .118<br>(3.00) | .118<br>(3.00) | .035<br>(0.89) | .008<br>(0.20) | .067<br>(1.70) | .067<br>(1.70) | .012<br>(0.30) | .046<br>(1.17) | .016<br>(0.41) | .026<br>(0.66) | .148<br>(3.76) | .148<br>(3.76) | .067<br>(1.70) |

| CASE # | P              | Q              | R              | S              | T              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------|
| DQ849  | .012<br>(0.30) | .031<br>(0.79) | .067<br>(1.70) | .061<br>(1.55) | .041<br>(1.04) | .02      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm.01$ ; 3 Pl.  $\pm.004$

#### Notes:

- Case material: Plastic.
- Termination finish:  
 For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin plated. All models, (+) suffix. See Data sheet.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models. no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F104



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         | 7                 | Standard                            | 2000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


| REV | ECN No. | DESCRIPTION | DATE     | DR  | AUTH |
|-----|---------|-------------|----------|-----|------|
| OR  | M154458 | NEW RELEASE | 01/04/16 | ITG | MM   |
|     |         |             |          |     |      |
|     |         |             |          |     |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
DQ849 CASE STYLE, "08AM15" PIN CODE



**NOTES:**

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.020" \pm .0015"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED   | INITIALS |     | DATE     |
|--|----------|-----|----------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .005<br>ANGLES ±<br>FRACTIONS ± | DRAWN    | ITG | 12/31/15 |
|  | CHECKED  | GF  | 12/31/15 |
|  | APPROVED | MM  | 01/04/16 |





**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

**PL, 08AM15, DQ849, TB-877+**

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

|                  |                     |                          |            |
|------------------|---------------------|--------------------------|------------|
| SIZE<br>A        | CODE IDENT<br>15542 | DRAWING NO:<br>98-PL-473 | REV:<br>OR |
| FILE:<br>98PL473 | SCALE:<br>10:1      | SHEET:<br>1 OF 1         |            |

# Evaluation Board and Circuit




| COMPONENT | VALUE                   | SIZE   |
|-----------|-------------------------|--------|
| DUT       | LVA-123+                | SOT-89 |
| C1        | .1 uF                   | 0805   |
| C2        | 0.001 uF                | 0402   |
| R1        | 16.5 Ohm                | 0603   |
| BIAS TEE  | Mini-Circuits TCBT-123+ |        |

## Schematic Diagram

### NOTES:

1. Vdd voltage:  $+5 \pm 0.2V$ .
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition  | Reference/Spec  |
|--------------------------------|--|---|
| Operating Temperature          | -40° to 85°C or -45° to 85°C<br>Ambient Environment  | Individual Model Data Sheet                                     |
| Storage Temperature            | -55° to 100° C or -65° to 150°<br>Ambient Environment  | Individual Model Data Sheet                                     |
| Thermal Shock                  | -55° to 100°C, 100 cycles  | MIL-STD-202, Method 107, Condition A-3, except +100°C           |
| Mechanical Shock               | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only   | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak   | MIL-STD-883, Method 2007, Condition B                           |
| Autoclave                      | 15 psig, 100% RH, 121°C, 96 hours  | JESD22-A102, Condition C  |
| HAST                           | 130°C, 85% RH, 96 hours  | JESD22-A110   |
| Solderability                  | 10X Magnification  | J-STD-002, Para 4.2.5, Test S, 95% Coverage                     |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak   | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1                   |
| Moisture Sensitivity: Level 1  | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak                                 | J-STD-020   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + | MIL-STD-202, Method 215   |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition        | Reference/Spec |
|---------------|----------------------------------|----------------|
|               | monoethanolamine at 63°C to 70°C |                |