


Surface Mount

Dual Matched MMIC Amplifier

MGVA-62+

50Ω 0.04 to 3 GHz



CASE STYLE: DL1020

The Big Deal

- Excellent gain flatness, ± 0.5 dB
- Dual matched amplifier for push-pull & balanced amplifiers
- High dynamic range

Product Overview

MGVA-62+ is a dual matched wideband amplifier fabricated using advanced InGaP HBT technology, offering high dynamic range (High IP3 and Low NF) for use in 50 and 75 ohm applications. This model has demonstrated high IP2 in wideband amplifier evaluation boards. Combining this performance with low noise figure makes it suitable for use in very high dynamic range amplifiers.

Key Features

| Feature | Advantages |
|---|---|
| Broadband | Covers many communication bands including cellular, cable TV, PCS, SATCOM, WiMAX, and more. |
| Excellent Gain Flatness: ± 0.5 dB over 0.05-3 GHz | Requires no gain compensation in most wideband applications. |
| Matched pair for use in high IP3 and IP2 amplifiers | Typical gain match of 0.2 dB and phase match of 0.7° , enables it to be used in push-pull amplifiers. Outstanding IP2. |
| High IP2, 70 dBm at 0.9 GHz (Push-Pull amplifier) | Excellent suppression of unwanted second harmonics in wide band applications |
| High IP3, up to 38 dBm | Ideal for suppressing unwanted intermods in the presence of multiple carriers, now common in many communication systems. |
| High P1dB: Up to 19.8 dBm | High P1dB enables the amplifier to operate in linear region in the presence of strong interfering signals. |
| Medium Noise Figure: 4.7-5.3 dB typical | Together with High OIP3/P1dB, results in high dynamic range |




Surface Mount Dual Matched MMIC Amplifier

.04-3GHz

Product Features

- Two matched amplifiers in one package
- High IP3, +37.9 dBm at 0.9 GHz
- High IP2, +70 dBm at 0.9 GHz in push-pull configuration
- Gain, 15.7 dB typ at 0.9 GHz
- Excellent Gain flatness, ± 0.5 dB (0.05-3 GHz)
- P1dB, +19.6 dBm typ at 0.9 GHz



Generic photo used for illustration purposes only

MGVA-62+

CASE STYLE: DL1020

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Typical Applications

- SATCOM
- CATV
- FTTH
- Optical networks
- Base station infrastructure
- Balanced amplifiers
- 75 Ohm push-pull and balanced amplifiers

General Description

MGVA-62+ (RoHS compliant) is an advanced ultra-flat gain amplifier fabricated using InGaP HBT technology and offers high dynamic range over a broad frequency range. In addition, the MGVA-62+ has good input and output return loss over a broad frequency range without the need for external matching components. Lead finish is SnAgNi and is enclosed in a 4.9 x 6 mm MCLP package for good thermal performance.

simplified schematic (each of A1, A2) and pad description



| Function | Pad Number | Description |
|----------------------|------------------|--|
| RF IN, A1 | 1 | RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation. (see Application circuit, Fig 2.) |
| RF-OUT and DC-IN, A1 | 8 | RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig 2 |
| RF IN, A2 | 4 | RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation. (see Application circuit, Fig 2.) |
| RF-OUT and DC-IN, A2 | 5 | RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig 2 |
| GND | 2,3,6,7 & paddle | Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance. |

* Enhancement mode pseudomorphic High Electron Mobility Transistor.

Electrical Specifications¹ at 25°C, Zo=50Ω and Device Voltage 5V, unless noted
(Specifications (other than Matching or where defined as push-pull) are for each of the two matched amplifiers in the package)

| Parameter | Condition (GHz) | Min. | Typ. | Max. | Units | |
|--|---------------------|------|-------|------|-------|------|
| Frequency Range | | 0.04 | | 3.0 | GHz | |
| Gain | 0.04 | — | 16.7 | — | dB | |
| | 0.5 | — | 15.7 | — | | |
| | 0.9 | 14.1 | 15.7 | 17.3 | | |
| | 2.0 | — | 15.8 | — | | |
| | 2.6 | — | 15.8 | — | | |
| | 3.0 | — | 15.7 | — | | |
| Gain Flatness | 0.05-3.0 | | ±0.5 | | dB | |
| Input Return Loss | 0.04 | | 16.7 | | dB | |
| | 0.5 | | 13.3 | | | |
| | 0.9 | | 12.2 | | | |
| | 2.0 | | 9.3 | | | |
| | 2.6 | | 8.0 | | | |
| | 3.0 | | 7.1 | | | |
| Output Return Loss | 0.04 | | 12.5 | | dB | |
| | 0.5 | | 18.1 | | | |
| | 0.9 | | 19.4 | | | |
| | 2.0 | | 18.2 | | | |
| | 2.6 | | 12.9 | | | |
| | 3.0 | | 10.2 | | | |
| Output Power @ 1 dB compression ^(2,3) | 0.04 | | 19.8 | | dBm | |
| | 0.5 | | 19.8 | | | |
| | 0.9 | | 19.6 | | | |
| | 2.0 | | 19.4 | | | |
| | 2.6 | | 18.4 | | | |
| | 3.0 | | 17.4 | | | |
| Output IP3 ⁽³⁾ | 0.04 | — | 36.3 | — | dBm | |
| | 0.5 | — | 37.9 | — | | |
| | 0.9 | 34.8 | 37.9 | — | | |
| | 2.0 | — | 34.3 | — | | |
| | 2.6 | — | 31.7 | — | | |
| | 3.0 | — | 29.9 | — | | |
| Noise Figure | 0.04 | | 4.7 | | dB | |
| | 0.5 | | 4.8 | | | |
| | 0.9 | | 4.8 | | | |
| | 2.0 | | 5.1 | | | |
| | 2.6 | | 5.4 | | | |
| | 3.0 | | 5.3 | | | |
| Matching between A1, A2 | Amplitude Unbalance | 0.04 | — | 0.0 | — | dB |
| | | 0.5 | — | 0.1 | — | |
| | | 0.9 | — | 0.1 | 0.5 | |
| | | 2.0 | — | 0.1 | — | |
| | | 2.6 | — | 0.1 | — | |
| | | 3.0 | — | 0.2 | — | |
| | Phase Unbalance | 0.04 | — | 0.0 | — | deg. |
| | | 0.5 | — | 0.1 | — | |
| | | 0.9 | — | 0.3 | 5.0 | |
| | | 2.0 | — | 0.7 | — | |
| 2.6 | | — | 0.7 | — | | |
| | 3.0 | — | 0.6 | — | | |
| Device Operating Voltage | | 4.8 | 5.0 | 5.2 | V | |
| Device Operating Current (each amplifier) | | | 82 | 92 | mA | |
| Device Current Variation vs. Temperature | | | 61 | | μA/°C | |
| Device Current Variation vs Voltage | | | 0.036 | | mA/mV | |
| Thermal Resistance, junction-to-ground lead ⁽⁴⁾ | | | 39 | | °C/W | |

⁽¹⁾ Measured on Mini-Circuits Test Board TB-561-62+, see characterization circuit, Fig 1.
⁽²⁾ Current increases at P1dB

⁽³⁾ Per single ended amplifier
⁽⁴⁾ $\theta_{jc} = (\text{Junction Temperature} - 85^\circ\text{C}) / (\text{Voltage} \times \text{sum of current in A1 \& A2})$

Absolute Maximum Ratings for each Amplifier⁽⁶⁾

| Parameter | Ratings |
|------------------------------------|----------------|
| Operating Temperature ⁷ | -40°C to 85°C |
| Storage Temperature | -55°C to 150°C |
| Operating Current at 5V | 120 mA |
| Power Dissipation | 0.725 W |
| Input Power (CW) | 24 dBm |
| DC Voltage (pads 5, 8) | 6.0 |

⁽⁶⁾ Permanent damage may occur if any of these limits are exceeded.
 These ratings are not intended for continuous normal operation.
⁽⁷⁾ Defined with reference to ground pad temperature.

Push-Pull Amplifier Typical Performance ⁽⁵⁾

| Freq. GHz | TB-666-50-62+ (50Ω) | | |
|-----------|---------------------|------------------|------------------|
| | Gain (dB) | Output IP3 (dBm) | Output IP2 (dBm) |
| 0.04 | 13.3 | 36.4 | 68.7 |
| 0.5 | 13.1 | 37.0 | 69.5 |
| 0.9 | 12.9 | 39.5 | 70.0 |
| 2.0 | 12.7 | 35.6 | 50.6 |
| 2.6 | 12.4 | 32.3 | 72.6 |
| 3.0 | 11.2 | 31.4 | 68.0 |

⁽⁵⁾ Measured on evaluation boards TB-666-50-62+ (push-pull amplifier)



Characterization Test Circuit





Fig 1a. Block Diagram of Test Circuit used for characterization. (DUT tested in Mini-Circuits Test board TB-561-62+, except for IP2). Gain, Return loss, Output Power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent’s N5242A PNA-X micro-wave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1MHz apart, 0 dBm/tone at output.




Mini-Circuits Evaluation Boards, 50Ω Push-Pull Amplifiers TB-666-50-62+ (MGVA-62+ inside)

Fig 1b. Block Diagram of Test Set up used for characterization of Gain, IP2, IP3 of push-pull amplifier. Measured using Agilent’s signal generators E8527D and Spectrum analyzer N9020A.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 & IP2: Two tones, spaced 1MHz apart, 8 dBm/tone at output. IP2 is measured at the sum frequency of the tones.


Recommended Application Circuit



| COMPONENT | VALUE | SIZE |
|-----------|--|----------------|
| A1 | Mini-Circuits MGVA-62+ | PER DATA SHEET |
| C1,C2 | .039 uF | 0805 |
| C3,C4 | .001 uF | 0402 |
| C5,C6 | .2 pF | 0402 |
| C7,C8 | 1.1 pF | 0402 |
| C9 | 1.0 uF | 1311 |
| C10 | .4 pF | 0603 |
| C11 | 270 pF | 0805 |
| C12 | .4 pF | 0402 |
| C13 | .7 pF | 0402 |
| C14 | .3 pF | 0402 |
| C15 | .6 pF | 0402 |
| C16 | 1.0 pF | 0402 |
| D1 | Diode, Schottky Rectifier Vf=.385V @ .5A, Vr=10V MAX | - |
| L1,L2 | 1.1 nH | .073"X.054" |
| L3 | 1.5 uH | 1008 |
| R1,R2 | 5.11 Ohm | 1206 |
| R3,R4 | 7.50 Ohm | 1206 |
| T1 | Mini-Circuits TCM2-33WX+ | PER DATA SHEET |
| T2 | Mini-Circuits TCM2-43X+ | PER DATA SHEET |
| P1,P2 | Mini-Circuits TCBT-6G+ | PER DATA SHEET |

Fig 2. Recommended Application Circuit. Mini-Circuits Evaluation Board 50Ω: TB-666-50-62+

Product Marking



| Additional Detailed Technical Information | |
|---|---|
| <i>additional information is available on our dash board. To access this information click here</i> | |
| Performance Data | Data Table |
| | Swept Graphs |
| | S-Parameter (S4P Files) Data Set (.zip file) |
| Case Style | DL1020 <i>Plastic package, exposed paddle lead finish: tin-silver over nickel</i> |
| Tape & Reel Standard quantities available on reel | F68 <i>7" reels with 20, 50, 100, 200, 500 or 1K devices 13" reels with 2K, 3K, 4K devices</i> |
| Suggested Layout for PCB Design | PL-322 |
| Evaluation Board | TB-666-50-62+ (50Ω) |
| Environmental Ratings | ENV08T2 |


ESD Rating

Human Body Model (HBM): Class 1C (1000 to <2000V) in accordance with ANSI/ESD STM 5.1 - 2001
Machine Model (MM): Class M2 (100 to <200V) in accordance with ANSI/ESD STM5.2-1999

MSL Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL Test Flow Chart



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id1 (A1) = 82.19 mA and Id2 (A2) = 81.91 mA @ Temperature = +25degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 10.0 | 16.96 | 17.00 | 0.04 | 0.02 | 22.92 | 21.00 | 11.26 | 1.14 | 0.70 | -- | 19.54 | 4.37 |
| 20.0 | 16.92 | 16.93 | 0.01 | 0.04 | 22.76 | 19.89 | 11.63 | 1.13 | 0.71 | 40.57 | 19.38 | 4.79 |
| 30.0 | 16.82 | 16.83 | 0.01 | 0.02 | 22.56 | 18.97 | 12.02 | 1.13 | 0.71 | 37.75 | 19.88 | 4.70 |
| 40.0 | 16.70 | 16.71 | 0.01 | 0.00 | 22.39 | 18.17 | 12.46 | 1.12 | 0.72 | 41.26 | 20.26 | 4.62 |
| 50.0 | 16.60 | 16.60 | 0.00 | 0.01 | 22.43 | 17.60 | 12.92 | 1.14 | 0.73 | 41.56 | 20.03 | 4.69 |
| 60.0 | 16.46 | 16.47 | 0.01 | 0.06 | 22.15 | 17.07 | 13.36 | 1.13 | 0.73 | 40.10 | 20.06 | 4.65 |
| 70.0 | 16.37 | 16.38 | 0.01 | 0.07 | 22.08 | 16.70 | 13.78 | 1.13 | 0.74 | 38.48 | 20.07 | 4.65 |
| 80.0 | 16.29 | 16.29 | 0.00 | 0.07 | 21.96 | 16.41 | 14.18 | 1.13 | 0.74 | 38.48 | 20.16 | 4.68 |
| 90.0 | 16.22 | 16.23 | 0.01 | 0.07 | 21.90 | 16.19 | 14.53 | 1.14 | 0.75 | 39.57 | 20.19 | 4.75 |
| 100.0 | 16.16 | 16.17 | 0.01 | 0.07 | 21.86 | 16.01 | 14.82 | 1.14 | 0.75 | 38.41 | 20.14 | 4.76 |
| 200.0 | 15.90 | 15.91 | 0.01 | 0.09 | 21.60 | 15.24 | 16.56 | 1.15 | 0.76 | 38.71 | 20.21 | 4.70 |
| 400.0 | 15.81 | 15.82 | 0.01 | 0.12 | 21.51 | 14.78 | 17.55 | 1.15 | 0.77 | 39.66 | 20.14 | 4.90 |
| 600.0 | 15.80 | 15.80 | 0.00 | 0.18 | 21.55 | 14.29 | 18.41 | 1.16 | 0.78 | 38.76 | 20.15 | 4.98 |
| 800.0 | 15.82 | 15.82 | 0.00 | 0.18 | 21.53 | 13.75 | 19.18 | 1.15 | 0.78 | 38.50 | 20.12 | 4.94 |
| 1000.0 | 15.85 | 15.85 | 0.00 | 0.25 | 21.51 | 13.26 | 20.05 | 1.15 | 0.78 | 37.16 | 20.20 | 5.00 |
| 1200.0 | 15.88 | 15.88 | 0.00 | 0.29 | 21.55 | 12.74 | 20.70 | 1.15 | 0.79 | 37.30 | 20.06 | 5.03 |
| 1400.0 | 15.93 | 15.92 | 0.01 | 0.35 | 21.55 | 12.26 | 21.03 | 1.14 | 0.79 | 36.19 | 20.08 | 5.07 |
| 1600.0 | 15.99 | 15.97 | 0.02 | 0.44 | 21.55 | 11.79 | 20.78 | 1.14 | 0.78 | 35.67 | 19.90 | 5.06 |
| 1800.0 | 16.02 | 16.01 | 0.01 | 0.59 | 21.63 | 11.28 | 20.23 | 1.14 | 0.78 | 34.95 | 19.98 | 5.09 |
| 2000.0 | 16.10 | 16.08 | 0.02 | 0.57 | 21.60 | 10.88 | 18.69 | 1.13 | 0.77 | 34.94 | 19.79 | 5.10 |
| 2200.0 | 16.15 | 16.12 | 0.03 | 0.66 | 21.60 | 10.41 | 17.18 | 1.12 | 0.76 | 33.11 | 19.18 | 5.18 |
| 2400.0 | 16.15 | 16.16 | 0.01 | 0.78 | 21.62 | 9.85 | 15.75 | 1.12 | 0.75 | 32.89 | 19.21 | 5.21 |
| 2600.0 | 16.19 | 16.16 | 0.03 | 0.77 | 21.69 | 9.30 | 14.15 | 1.11 | 0.74 | 32.10 | 18.74 | 5.36 |
| 2800.0 | 16.17 | 16.14 | 0.03 | 0.89 | 21.71 | 8.61 | 12.46 | 1.10 | 0.72 | 30.90 | 18.37 | 5.49 |
| 3000.0 | 16.11 | 16.08 | 0.03 | 1.20 | 21.80 | 7.90 | 10.88 | 1.09 | 0.70 | 30.54 | 18.00 | 5.47 |
| 3200.0 | 15.99 | 15.95 | 0.04 | 1.15 | 21.96 | 7.18 | 9.37 | 1.09 | 0.68 | 29.29 | 17.29 | 5.65 |
| 3400.0 | 15.77 | 15.77 | 0.00 | 1.24 | 22.12 | 6.44 | 8.02 | 1.08 | 0.65 | 28.61 | 16.98 | 5.70 |
| 3600.0 | 15.51 | 15.50 | 0.01 | 1.38 | 22.29 | 5.81 | 6.78 | 1.07 | 0.60 | 27.85 | 16.38 | 5.86 |
| 3800.0 | 15.14 | 15.15 | 0.01 | 1.62 | 22.56 | 5.23 | 5.69 | 1.05 | 0.56 | 27.40 | 15.94 | 6.04 |
| 4000.0 | 14.73 | 14.73 | 0.00 | 1.81 | 22.85 | 4.74 | 4.86 | 1.04 | 0.53 | 27.18 | 15.55 | 6.13 |
| 4200.0 | 14.28 | 14.28 | 0.00 | 1.58 | 23.16 | 4.38 | 4.17 | 1.03 | 0.49 | 26.27 | 14.84 | 6.27 |
| 4400.0 | 13.76 | 13.76 | 0.00 | 1.62 | 23.54 | 4.07 | 3.62 | 1.02 | 0.47 | 26.00 | 14.30 | 6.51 |
| 4600.0 | 13.26 | 13.26 | 0.00 | 1.66 | 23.75 | 3.86 | 3.23 | 1.01 | 0.45 | 25.38 | 13.81 | 6.76 |
| 4800.0 | 12.71 | 12.75 | 0.04 | 1.87 | 24.02 | 3.69 | 2.89 | 1.00 | 0.43 | 25.07 | 13.34 | 6.83 |
| 5000.0 | 12.22 | 12.22 | 0.00 | 1.88 | 24.23 | 3.63 | 2.70 | 1.00 | 0.43 | 24.54 | 12.71 | 7.11 |
| 5200.0 | 11.70 | 11.78 | 0.08 | 2.08 | 24.50 | 3.53 | 2.52 | 1.00 | 0.42 | 24.23 | 12.35 | 7.10 |
| 5400.0 | 11.21 | 11.23 | 0.02 | 2.25 | 24.26 | 3.64 | 2.52 | 1.01 | 0.43 | 24.40 | 11.68 | 7.42 |
| 5600.0 | 10.63 | 10.73 | 0.10 | 2.19 | 24.62 | 3.61 | 2.46 | 1.01 | 0.46 | 22.72 | 11.51 | 7.30 |
| 5800.0 | 10.07 | 10.19 | 0.12 | 1.90 | 24.70 | 3.63 | 2.47 | 1.02 | 0.49 | 22.82 | 11.06 | 7.72 |
| 6000.0 | 9.50 | 9.66 | 0.16 | 2.08 | 24.72 | 3.67 | 2.50 | 1.05 | 0.51 | 22.49 | 10.55 | 7.90 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id1 (A1) = 73.65 mA and Id2 (A2) = 73.59 mA @ Temperature = +25degC

| FREQ | A1 | | A2 | | A1 & A2 | | A1 | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| | (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) |
| 10.0 | 16.94 | 16.92 | 0.02 | 0.13 | 23.63 | 20.77 | 11.55 | 1.20 | 0.75 | -- | 19.02 | 4.36 |
| 20.0 | 16.88 | 16.88 | 0.00 | 0.02 | 22.82 | 20.27 | 11.54 | 1.14 | 0.71 | 36.90 | 18.64 | 4.76 |
| 30.0 | 16.77 | 16.78 | 0.01 | 0.01 | 22.58 | 19.34 | 11.91 | 1.13 | 0.71 | 37.34 | 19.13 | 4.65 |
| 40.0 | 16.65 | 16.66 | 0.01 | 0.01 | 22.42 | 18.49 | 12.36 | 1.13 | 0.72 | 38.33 | 19.48 | 4.57 |
| 50.0 | 16.55 | 16.55 | 0.00 | 0.02 | 22.35 | 17.87 | 12.81 | 1.14 | 0.73 | 37.13 | 19.25 | 4.65 |
| 60.0 | 16.42 | 16.42 | 0.00 | 0.05 | 22.00 | 17.37 | 13.21 | 1.12 | 0.72 | 36.92 | 19.27 | 4.65 |
| 70.0 | 16.33 | 16.33 | 0.00 | 0.05 | 22.00 | 16.94 | 13.65 | 1.13 | 0.74 | 37.06 | 19.27 | 4.66 |
| 80.0 | 16.24 | 16.25 | 0.01 | 0.06 | 21.90 | 16.66 | 14.03 | 1.13 | 0.74 | 37.19 | 19.35 | 4.65 |
| 90.0 | 16.18 | 16.18 | 0.00 | 0.08 | 21.86 | 16.43 | 14.37 | 1.14 | 0.74 | 37.52 | 19.36 | 4.71 |
| 100.0 | 16.12 | 16.12 | 0.00 | 0.06 | 21.78 | 16.25 | 14.67 | 1.14 | 0.75 | 36.77 | 19.34 | 4.69 |
| 200.0 | 15.85 | 15.86 | 0.01 | 0.10 | 21.54 | 15.46 | 16.38 | 1.15 | 0.76 | 37.10 | 19.36 | 4.65 |
| 400.0 | 15.77 | 15.77 | 0.00 | 0.12 | 21.52 | 14.98 | 17.36 | 1.16 | 0.77 | 38.19 | 19.30 | 4.88 |
| 600.0 | 15.76 | 15.76 | 0.00 | 0.18 | 21.49 | 14.48 | 18.18 | 1.16 | 0.77 | 37.16 | 19.29 | 4.99 |
| 800.0 | 15.77 | 15.77 | 0.00 | 0.21 | 21.47 | 13.94 | 18.93 | 1.15 | 0.78 | 37.63 | 19.31 | 4.91 |
| 1000.0 | 15.81 | 15.81 | 0.00 | 0.27 | 21.47 | 13.41 | 19.75 | 1.15 | 0.78 | 36.04 | 19.33 | 4.94 |
| 1200.0 | 15.84 | 15.84 | 0.00 | 0.31 | 21.50 | 12.89 | 20.33 | 1.15 | 0.78 | 36.14 | 19.25 | 5.03 |
| 1400.0 | 15.89 | 15.88 | 0.01 | 0.38 | 21.48 | 12.41 | 20.67 | 1.14 | 0.78 | 35.55 | 19.28 | 5.04 |
| 1600.0 | 15.94 | 15.93 | 0.01 | 0.48 | 21.52 | 11.94 | 20.41 | 1.14 | 0.78 | 35.14 | 19.23 | 5.03 |
| 1800.0 | 15.98 | 15.97 | 0.01 | 0.64 | 21.53 | 11.43 | 19.86 | 1.14 | 0.78 | 34.60 | 19.36 | 5.02 |
| 2000.0 | 16.05 | 16.03 | 0.02 | 0.63 | 21.53 | 11.01 | 18.36 | 1.13 | 0.77 | 34.11 | 19.20 | 5.09 |
| 2200.0 | 16.10 | 16.07 | 0.03 | 0.72 | 21.54 | 10.53 | 16.92 | 1.12 | 0.76 | 32.61 | 18.67 | 5.13 |
| 2400.0 | 16.11 | 16.11 | 0.00 | 0.86 | 21.57 | 9.97 | 15.50 | 1.12 | 0.75 | 32.40 | 18.70 | 5.13 |
| 2600.0 | 16.14 | 16.11 | 0.03 | 0.83 | 21.56 | 9.41 | 13.92 | 1.11 | 0.73 | 31.73 | 18.24 | 5.35 |
| 2800.0 | 16.12 | 16.09 | 0.03 | 0.97 | 21.66 | 8.72 | 12.27 | 1.10 | 0.71 | 30.47 | 17.87 | 5.47 |
| 3000.0 | 16.05 | 16.02 | 0.03 | 1.28 | 21.73 | 7.99 | 10.71 | 1.09 | 0.69 | 30.02 | 17.50 | 5.45 |
| 3200.0 | 15.93 | 15.88 | 0.05 | 1.22 | 21.86 | 7.26 | 9.24 | 1.09 | 0.66 | 28.73 | 16.77 | 5.56 |
| 3400.0 | 15.70 | 15.69 | 0.01 | 1.29 | 22.01 | 6.50 | 7.89 | 1.08 | 0.63 | 27.98 | 16.47 | 5.66 |
| 3600.0 | 15.43 | 15.41 | 0.02 | 1.45 | 22.23 | 5.87 | 6.68 | 1.07 | 0.60 | 27.23 | 15.86 | 5.80 |
| 3800.0 | 15.05 | 15.05 | 0.00 | 1.69 | 22.48 | 5.28 | 5.61 | 1.05 | 0.55 | 26.73 | 15.43 | 5.99 |
| 4000.0 | 14.63 | 14.62 | 0.01 | 1.89 | 22.76 | 4.80 | 4.78 | 1.04 | 0.52 | 26.49 | 15.07 | 6.12 |
| 4200.0 | 14.16 | 14.15 | 0.01 | 1.66 | 23.09 | 4.43 | 4.11 | 1.03 | 0.48 | 25.69 | 14.33 | 6.22 |
| 4400.0 | 13.63 | 13.62 | 0.01 | 1.68 | 23.43 | 4.12 | 3.58 | 1.02 | 0.46 | 25.33 | 13.80 | 6.43 |
| 4600.0 | 13.12 | 13.11 | 0.01 | 1.76 | 23.65 | 3.91 | 3.19 | 1.01 | 0.44 | 24.73 | 13.32 | 6.75 |
| 4800.0 | 12.57 | 12.59 | 0.02 | 1.95 | 23.95 | 3.74 | 2.86 | 1.00 | 0.43 | 24.40 | 12.83 | 6.77 |
| 5000.0 | 12.07 | 12.05 | 0.02 | 2.01 | 24.10 | 3.67 | 2.68 | 1.00 | 0.42 | 23.87 | 12.24 | 7.05 |
| 5200.0 | 11.54 | 11.60 | 0.06 | 2.18 | 24.41 | 3.58 | 2.51 | 1.00 | 0.42 | 23.55 | 11.85 | 7.01 |
| 5400.0 | 11.05 | 11.05 | 0.00 | 2.38 | 24.14 | 3.68 | 2.51 | 1.00 | 0.43 | 23.72 | 11.21 | 7.32 |
| 5600.0 | 10.47 | 10.54 | 0.07 | 2.33 | 24.52 | 3.65 | 2.46 | 1.01 | 0.46 | 22.02 | 11.03 | 7.24 |
| 5800.0 | 9.91 | 10.00 | 0.09 | 2.10 | 24.53 | 3.66 | 2.47 | 1.01 | 0.49 | 22.11 | 10.59 | 7.65 |
| 6000.0 | 9.34 | 9.47 | 0.13 | 2.26 | 24.62 | 3.70 | 2.50 | 1.05 | 0.51 | 21.76 | 10.13 | 7.86 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id1 (A1) = 90.94mA and Id2 (A2) = 91.01 mA @ Temperature = +25degC

| FREQ | A1 | | A2 | | A1 & A2 | | A1 | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| | (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) |
| 10.0 | 17.00 | 17.01 | 0.01 | 0.16 | 23.51 | 20.56 | 11.74 | 1.19 | 0.74 | -- | 20.18 | 4.48 |
| 20.0 | 16.96 | 16.96 | 0.00 | 0.02 | 22.80 | 19.59 | 11.70 | 1.13 | 0.71 | 40.96 | 20.06 | 4.85 |
| 30.0 | 16.85 | 16.85 | 0.00 | 0.01 | 22.75 | 18.74 | 12.11 | 1.14 | 0.72 | 41.14 | 20.57 | 4.77 |
| 40.0 | 16.73 | 16.73 | 0.00 | 0.01 | 22.53 | 17.97 | 12.54 | 1.13 | 0.73 | 39.01 | 20.99 | 4.70 |
| 50.0 | 16.63 | 16.63 | 0.00 | 0.02 | 22.34 | 17.35 | 13.01 | 1.13 | 0.73 | 41.55 | 20.76 | 4.78 |
| 60.0 | 16.49 | 16.49 | 0.00 | 0.04 | 22.07 | 16.82 | 13.43 | 1.12 | 0.73 | 42.00 | 20.77 | 4.77 |
| 70.0 | 16.40 | 16.40 | 0.00 | 0.04 | 22.11 | 16.50 | 13.88 | 1.13 | 0.74 | 40.99 | 20.77 | 4.77 |
| 80.0 | 16.32 | 16.32 | 0.00 | 0.04 | 21.98 | 16.21 | 14.27 | 1.13 | 0.75 | 38.97 | 20.87 | 4.75 |
| 90.0 | 16.25 | 16.25 | 0.00 | 0.04 | 21.93 | 15.98 | 14.61 | 1.14 | 0.75 | 40.77 | 20.90 | 4.84 |
| 100.0 | 16.19 | 16.19 | 0.00 | 0.05 | 21.84 | 15.82 | 14.91 | 1.13 | 0.75 | 39.83 | 20.84 | 4.83 |
| 200.0 | 15.93 | 15.93 | 0.00 | 0.07 | 21.59 | 15.07 | 16.70 | 1.15 | 0.76 | 41.00 | 20.94 | 4.74 |
| 400.0 | 15.84 | 15.84 | 0.00 | 0.10 | 21.52 | 14.61 | 17.74 | 1.15 | 0.77 | 40.61 | 20.84 | 4.99 |
| 600.0 | 15.83 | 15.82 | 0.01 | 0.15 | 21.56 | 14.14 | 18.60 | 1.15 | 0.78 | 39.08 | 20.85 | 5.07 |
| 800.0 | 15.84 | 15.84 | 0.00 | 0.21 | 21.57 | 13.61 | 19.39 | 1.15 | 0.78 | 39.71 | 20.78 | 5.08 |
| 1000.0 | 15.88 | 15.87 | 0.01 | 0.24 | 21.57 | 13.13 | 20.25 | 1.15 | 0.79 | 37.77 | 20.84 | 5.09 |
| 1200.0 | 15.91 | 15.90 | 0.01 | 0.30 | 21.57 | 12.62 | 20.97 | 1.15 | 0.79 | 37.79 | 20.54 | 5.16 |
| 1400.0 | 15.96 | 15.94 | 0.02 | 0.38 | 21.62 | 12.15 | 21.38 | 1.15 | 0.79 | 36.81 | 20.52 | 5.14 |
| 1600.0 | 16.01 | 15.99 | 0.02 | 0.45 | 21.60 | 11.69 | 21.18 | 1.14 | 0.79 | 35.85 | 20.28 | 5.16 |
| 1800.0 | 16.05 | 16.04 | 0.01 | 0.60 | 21.66 | 11.19 | 20.60 | 1.14 | 0.79 | 35.13 | 20.32 | 5.18 |
| 2000.0 | 16.13 | 16.10 | 0.03 | 0.59 | 21.62 | 10.79 | 19.00 | 1.13 | 0.78 | 34.91 | 20.09 | 5.22 |
| 2200.0 | 16.18 | 16.14 | 0.04 | 0.71 | 21.66 | 10.32 | 17.46 | 1.12 | 0.77 | 33.16 | 19.45 | 5.29 |
| 2400.0 | 16.19 | 16.19 | 0.00 | 0.81 | 21.68 | 9.76 | 16.00 | 1.12 | 0.76 | 32.83 | 19.48 | 5.28 |
| 2600.0 | 16.23 | 16.19 | 0.04 | 0.81 | 21.71 | 9.22 | 14.37 | 1.11 | 0.74 | 32.16 | 19.04 | 5.50 |
| 2800.0 | 16.22 | 16.18 | 0.04 | 0.93 | 21.76 | 8.54 | 12.64 | 1.10 | 0.73 | 31.09 | 18.65 | 5.59 |
| 3000.0 | 16.15 | 16.12 | 0.03 | 1.23 | 21.84 | 7.84 | 11.04 | 1.09 | 0.71 | 30.73 | 18.31 | 5.55 |
| 3200.0 | 16.04 | 16.00 | 0.04 | 1.17 | 21.98 | 7.12 | 9.52 | 1.09 | 0.68 | 29.36 | 17.60 | 5.72 |
| 3400.0 | 15.84 | 15.82 | 0.02 | 1.23 | 22.17 | 6.38 | 8.13 | 1.08 | 0.65 | 28.81 | 17.29 | 5.79 |
| 3600.0 | 15.58 | 15.56 | 0.02 | 1.40 | 22.38 | 5.77 | 6.89 | 1.07 | 0.61 | 28.08 | 16.70 | 5.94 |
| 3800.0 | 15.22 | 15.22 | 0.00 | 1.63 | 22.66 | 5.18 | 5.78 | 1.06 | 0.57 | 27.64 | 16.25 | 6.16 |
| 4000.0 | 14.82 | 14.80 | 0.02 | 1.81 | 22.96 | 4.70 | 4.93 | 1.05 | 0.54 | 27.42 | 15.88 | 6.25 |
| 4200.0 | 14.37 | 14.36 | 0.01 | 1.60 | 23.29 | 4.33 | 4.23 | 1.04 | 0.50 | 26.57 | 15.15 | 6.42 |
| 4400.0 | 13.86 | 13.85 | 0.01 | 1.59 | 23.59 | 4.03 | 3.68 | 1.02 | 0.47 | 26.27 | 14.63 | 6.62 |
| 4600.0 | 13.37 | 13.35 | 0.02 | 1.68 | 23.86 | 3.82 | 3.27 | 1.01 | 0.45 | 25.67 | 14.12 | 6.91 |
| 4800.0 | 12.83 | 12.84 | 0.01 | 1.86 | 24.09 | 3.66 | 2.93 | 1.00 | 0.43 | 25.33 | 13.64 | 6.96 |
| 5000.0 | 12.35 | 12.31 | 0.04 | 1.89 | 24.26 | 3.59 | 2.73 | 0.99 | 0.43 | 24.81 | 13.01 | 7.23 |
| 5200.0 | 11.83 | 11.87 | 0.04 | 2.08 | 24.64 | 3.50 | 2.55 | 1.00 | 0.43 | 24.49 | 12.65 | 7.22 |
| 5400.0 | 11.35 | 11.32 | 0.03 | 2.30 | 24.32 | 3.61 | 2.54 | 1.00 | 0.44 | 24.63 | 11.99 | 7.56 |
| 5600.0 | 10.77 | 10.82 | 0.05 | 2.24 | 24.71 | 3.58 | 2.48 | 1.00 | 0.47 | 22.98 | 11.78 | 7.49 |
| 5800.0 | 10.21 | 10.28 | 0.07 | 2.04 | 24.74 | 3.60 | 2.49 | 1.01 | 0.49 | 23.05 | 11.36 | 7.89 |
| 6000.0 | 9.64 | 9.75 | 0.11 | 2.20 | 24.83 | 3.64 | 2.52 | 1.05 | 0.52 | 22.72 | 10.92 | 8.06 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id1 (A1) = 77.47 mA and Id2 (A2) = 77.59 mA @ Temperature = -45degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 10.0 | 17.06 | 17.06 | 0.00 | 0.16 | 23.17 | 20.34 | 11.35 | 1.15 | 0.72 | -- | 19.52 | 3.73 |
| 20.0 | 17.02 | 17.02 | 0.00 | 0.03 | 22.93 | 19.62 | 11.63 | 1.14 | 0.71 | 39.48 | 19.25 | 4.09 |
| 30.0 | 16.91 | 16.91 | 0.00 | 0.03 | 22.73 | 18.86 | 11.97 | 1.13 | 0.72 | 40.82 | 19.73 | 4.00 |
| 40.0 | 16.79 | 16.78 | 0.01 | 0.00 | 22.62 | 18.13 | 12.35 | 1.13 | 0.73 | 41.26 | 20.06 | 3.89 |
| 50.0 | 16.68 | 16.68 | 0.00 | 0.00 | 22.54 | 17.52 | 12.77 | 1.14 | 0.74 | 41.46 | 19.85 | 3.94 |
| 60.0 | 16.55 | 16.54 | 0.01 | 0.03 | 22.16 | 17.23 | 13.13 | 1.12 | 0.73 | 39.16 | 19.85 | 3.95 |
| 70.0 | 16.46 | 16.46 | 0.00 | 0.03 | 22.14 | 16.86 | 13.47 | 1.13 | 0.74 | 40.06 | 19.85 | 3.94 |
| 80.0 | 16.38 | 16.37 | 0.01 | 0.04 | 22.05 | 16.62 | 13.82 | 1.13 | 0.74 | 40.17 | 19.92 | 3.95 |
| 90.0 | 16.31 | 16.31 | 0.00 | 0.05 | 21.96 | 16.47 | 14.08 | 1.13 | 0.74 | 39.82 | 19.97 | 4.02 |
| 100.0 | 16.25 | 16.25 | 0.00 | 0.06 | 21.93 | 16.36 | 14.33 | 1.14 | 0.74 | 39.10 | 19.93 | 4.00 |
| 200.0 | 16.01 | 16.00 | 0.01 | 0.08 | 21.68 | 15.56 | 16.10 | 1.15 | 0.76 | 39.47 | 19.94 | 3.91 |
| 400.0 | 15.92 | 15.92 | 0.00 | 0.14 | 21.63 | 14.49 | 17.74 | 1.15 | 0.77 | 39.22 | 19.89 | 4.17 |
| 600.0 | 15.92 | 15.91 | 0.01 | 0.17 | 21.58 | 14.12 | 18.49 | 1.15 | 0.78 | 39.36 | 19.91 | 4.26 |
| 800.0 | 15.94 | 15.93 | 0.01 | 0.28 | 21.56 | 13.70 | 18.89 | 1.14 | 0.78 | 39.28 | 19.93 | 4.19 |
| 1000.0 | 15.98 | 15.96 | 0.02 | 0.31 | 21.58 | 13.25 | 19.67 | 1.14 | 0.78 | 37.74 | 19.93 | 4.23 |
| 1200.0 | 16.01 | 16.00 | 0.01 | 0.36 | 21.56 | 12.57 | 20.60 | 1.14 | 0.78 | 38.26 | 19.91 | 4.33 |
| 1400.0 | 16.05 | 16.03 | 0.02 | 0.48 | 21.57 | 11.95 | 21.04 | 1.13 | 0.78 | 37.24 | 19.96 | 4.33 |
| 1600.0 | 16.11 | 16.08 | 0.03 | 0.55 | 21.54 | 11.48 | 20.68 | 1.12 | 0.78 | 36.49 | 19.97 | 4.30 |
| 1800.0 | 16.14 | 16.12 | 0.02 | 0.73 | 21.59 | 11.01 | 20.03 | 1.12 | 0.78 | 36.85 | 20.15 | 4.35 |
| 2000.0 | 16.23 | 16.19 | 0.04 | 0.73 | 21.51 | 10.59 | 18.62 | 1.11 | 0.76 | 35.96 | 19.99 | 4.33 |
| 2200.0 | 16.27 | 16.22 | 0.05 | 0.92 | 21.49 | 9.97 | 17.05 | 1.10 | 0.75 | 34.19 | 19.50 | 4.44 |
| 2400.0 | 16.29 | 16.27 | 0.02 | 0.97 | 21.57 | 9.43 | 15.65 | 1.10 | 0.75 | 34.03 | 19.60 | 4.42 |
| 2600.0 | 16.32 | 16.28 | 0.04 | 1.02 | 21.58 | 8.90 | 14.04 | 1.09 | 0.73 | 33.12 | 19.14 | 4.62 |
| 2800.0 | 16.32 | 16.27 | 0.05 | 1.14 | 21.62 | 8.21 | 12.50 | 1.08 | 0.72 | 32.08 | 18.84 | 4.71 |
| 3000.0 | 16.25 | 16.20 | 0.05 | 1.43 | 21.68 | 7.43 | 10.86 | 1.07 | 0.69 | 31.66 | 18.44 | 4.74 |
| 3200.0 | 16.13 | 16.07 | 0.06 | 1.40 | 21.86 | 6.63 | 9.27 | 1.06 | 0.67 | 30.06 | 17.74 | 4.83 |
| 3400.0 | 15.94 | 15.90 | 0.04 | 1.53 | 22.02 | 5.92 | 7.95 | 1.05 | 0.64 | 29.54 | 17.51 | 4.90 |
| 3600.0 | 15.71 | 15.66 | 0.05 | 1.69 | 22.21 | 5.32 | 6.76 | 1.03 | 0.60 | 28.71 | 16.95 | 5.04 |
| 3800.0 | 15.36 | 15.35 | 0.01 | 2.03 | 22.49 | 4.71 | 5.66 | 1.02 | 0.56 | 28.25 | 16.51 | 5.23 |
| 4000.0 | 14.96 | 14.95 | 0.01 | 1.87 | 22.83 | 4.21 | 4.78 | 1.01 | 0.52 | 28.06 | 16.11 | 5.34 |
| 4200.0 | 14.51 | 14.50 | 0.01 | 1.94 | 23.16 | 3.83 | 4.03 | 1.00 | 0.47 | 27.03 | 15.42 | 5.48 |
| 4400.0 | 14.04 | 14.01 | 0.03 | 2.07 | 23.50 | 3.54 | 3.45 | 0.98 | 0.44 | 26.69 | 14.91 | 5.71 |
| 4600.0 | 13.58 | 13.54 | 0.04 | 1.99 | 23.81 | 3.32 | 3.03 | 0.97 | 0.41 | 26.21 | 14.48 | 5.93 |
| 4800.0 | 13.10 | 13.11 | 0.01 | 2.22 | 24.12 | 3.16 | 2.67 | 0.95 | 0.38 | 26.02 | 13.98 | 5.98 |
| 5000.0 | 12.67 | 12.65 | 0.02 | 2.09 | 24.31 | 3.12 | 2.43 | 0.94 | 0.37 | 25.16 | 13.43 | 6.22 |
| 5200.0 | 12.24 | 12.25 | 0.01 | 2.47 | 24.46 | 3.10 | 2.28 | 0.93 | 0.36 | 25.39 | 13.07 | 6.21 |
| 5400.0 | 11.81 | 11.77 | 0.04 | 2.82 | 24.42 | 3.17 | 2.18 | 0.93 | 0.35 | 25.43 | 12.44 | 6.50 |
| 5600.0 | 11.32 | 11.35 | 0.03 | 2.60 | 24.69 | 3.14 | 2.07 | 0.92 | 0.36 | 24.07 | 12.26 | 6.44 |
| 5800.0 | 10.78 | 10.79 | 0.01 | 2.42 | 24.89 | 3.16 | 2.02 | 0.92 | 0.38 | 24.40 | 11.82 | 6.77 |
| 6000.0 | 10.24 | 10.29 | 0.05 | 2.60 | 24.91 | 3.20 | 2.00 | 0.93 | 0.40 | 23.74 | 11.40 | 6.95 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id1 (A1) = 69.2 mA and Id2 (A2) = 69.23 mA @ Temperature = -45degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| | (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) |
| 10.0 | 17.03 | 17.02 | 0.01 | 0.05 | 22.73 | 21.17 | 11.27 | 1.12 | 0.69 | -- | 18.68 | 3.62 |
| 20.0 | 16.98 | 16.98 | 0.00 | 0.02 | 22.72 | 19.96 | 11.49 | 1.12 | 0.70 | 38.34 | 18.40 | 4.00 |
| 30.0 | 16.87 | 16.87 | 0.00 | 0.02 | 22.66 | 19.12 | 11.89 | 1.13 | 0.71 | 38.59 | 18.88 | 3.89 |
| 40.0 | 16.75 | 16.75 | 0.00 | 0.00 | 22.44 | 18.40 | 12.26 | 1.12 | 0.71 | 38.03 | 19.17 | 3.81 |
| 50.0 | 16.64 | 16.64 | 0.00 | 0.01 | 22.24 | 17.85 | 12.61 | 1.12 | 0.72 | 37.72 | 18.94 | 3.88 |
| 60.0 | 16.51 | 16.51 | 0.00 | 0.02 | 22.29 | 17.45 | 12.99 | 1.13 | 0.73 | 39.82 | 18.99 | 3.89 |
| 70.0 | 16.42 | 16.42 | 0.00 | 0.01 | 22.07 | 17.10 | 13.36 | 1.13 | 0.73 | 37.85 | 18.99 | 3.87 |
| 80.0 | 16.34 | 16.33 | 0.01 | 0.02 | 22.02 | 16.86 | 13.69 | 1.13 | 0.74 | 37.75 | 19.03 | 3.87 |
| 90.0 | 16.27 | 16.27 | 0.00 | 0.03 | 21.94 | 16.71 | 13.95 | 1.13 | 0.74 | 38.16 | 19.07 | 3.92 |
| 100.0 | 16.22 | 16.21 | 0.01 | 0.03 | 21.86 | 16.60 | 14.18 | 1.13 | 0.74 | 37.11 | 19.02 | 3.94 |
| 200.0 | 15.97 | 15.97 | 0.00 | 0.08 | 21.63 | 15.79 | 15.94 | 1.15 | 0.76 | 37.10 | 18.97 | 3.89 |
| 400.0 | 15.88 | 15.88 | 0.00 | 0.11 | 21.53 | 14.65 | 17.51 | 1.15 | 0.77 | 38.42 | 19.01 | 4.10 |
| 600.0 | 15.88 | 15.88 | 0.00 | 0.15 | 21.53 | 14.30 | 18.24 | 1.15 | 0.77 | 38.08 | 18.99 | 4.19 |
| 800.0 | 15.90 | 15.90 | 0.00 | 0.28 | 21.52 | 13.85 | 18.68 | 1.14 | 0.77 | 38.09 | 19.02 | 4.13 |
| 1000.0 | 15.94 | 15.93 | 0.01 | 0.31 | 21.50 | 13.40 | 19.41 | 1.14 | 0.77 | 36.29 | 18.96 | 4.18 |
| 1200.0 | 15.98 | 15.97 | 0.01 | 0.40 | 21.51 | 12.71 | 20.30 | 1.14 | 0.78 | 36.98 | 18.97 | 4.23 |
| 1400.0 | 16.02 | 16.00 | 0.02 | 0.47 | 21.51 | 12.08 | 20.69 | 1.13 | 0.78 | 36.42 | 18.97 | 4.26 |
| 1600.0 | 16.08 | 16.05 | 0.03 | 0.55 | 21.50 | 11.60 | 20.30 | 1.13 | 0.78 | 35.93 | 19.07 | 4.21 |
| 1800.0 | 16.11 | 16.09 | 0.02 | 0.73 | 21.54 | 11.11 | 19.65 | 1.12 | 0.78 | 35.35 | 19.28 | 4.25 |
| 2000.0 | 16.19 | 16.16 | 0.03 | 0.79 | 21.46 | 10.70 | 18.30 | 1.11 | 0.76 | 34.98 | 19.21 | 4.28 |
| 2200.0 | 16.23 | 16.19 | 0.04 | 0.95 | 21.47 | 10.07 | 16.79 | 1.10 | 0.75 | 33.54 | 18.85 | 4.39 |
| 2400.0 | 16.25 | 16.24 | 0.01 | 1.02 | 21.54 | 9.53 | 15.43 | 1.10 | 0.75 | 33.08 | 18.99 | 4.37 |
| 2600.0 | 16.29 | 16.24 | 0.05 | 1.07 | 21.50 | 8.98 | 13.84 | 1.09 | 0.73 | 32.40 | 18.55 | 4.54 |
| 2800.0 | 16.28 | 16.23 | 0.05 | 1.20 | 21.51 | 8.28 | 12.30 | 1.07 | 0.71 | 31.44 | 18.29 | 4.69 |
| 3000.0 | 16.21 | 16.16 | 0.05 | 1.50 | 21.59 | 7.49 | 10.70 | 1.06 | 0.68 | 30.87 | 17.89 | 4.63 |
| 3200.0 | 16.08 | 16.02 | 0.06 | 1.48 | 21.79 | 6.69 | 9.13 | 1.06 | 0.66 | 29.38 | 17.23 | 4.71 |
| 3400.0 | 15.88 | 15.85 | 0.03 | 1.61 | 21.96 | 5.97 | 7.82 | 1.05 | 0.63 | 28.86 | 17.01 | 4.82 |
| 3600.0 | 15.64 | 15.60 | 0.04 | 1.78 | 22.13 | 5.37 | 6.65 | 1.03 | 0.59 | 28.08 | 16.44 | 4.96 |
| 3800.0 | 15.28 | 15.27 | 0.01 | 2.14 | 22.41 | 4.76 | 5.57 | 1.02 | 0.55 | 27.58 | 16.02 | 5.15 |
| 4000.0 | 14.87 | 14.86 | 0.01 | 2.02 | 22.76 | 4.24 | 4.70 | 1.01 | 0.51 | 27.38 | 15.65 | 5.25 |
| 4200.0 | 14.42 | 14.40 | 0.02 | 2.07 | 23.12 | 3.87 | 3.95 | 1.00 | 0.46 | 26.39 | 14.95 | 5.39 |
| 4400.0 | 13.93 | 13.90 | 0.03 | 2.19 | 23.45 | 3.58 | 3.39 | 0.98 | 0.43 | 25.94 | 14.46 | 5.60 |
| 4600.0 | 13.47 | 13.44 | 0.03 | 2.13 | 23.74 | 3.36 | 2.98 | 0.97 | 0.40 | 25.50 | 14.03 | 5.87 |
| 4800.0 | 12.98 | 12.99 | 0.01 | 2.38 | 24.01 | 3.20 | 2.63 | 0.95 | 0.37 | 25.35 | 13.53 | 5.89 |
| 5000.0 | 12.54 | 12.52 | 0.02 | 2.25 | 24.25 | 3.17 | 2.40 | 0.94 | 0.36 | 24.43 | 12.99 | 6.12 |
| 5200.0 | 12.10 | 12.12 | 0.02 | 2.69 | 24.42 | 3.13 | 2.25 | 0.93 | 0.36 | 24.61 | 12.65 | 6.11 |
| 5400.0 | 11.67 | 11.64 | 0.03 | 2.99 | 24.35 | 3.21 | 2.15 | 0.93 | 0.35 | 24.70 | 12.01 | 6.38 |
| 5600.0 | 11.18 | 11.21 | 0.03 | 2.78 | 24.56 | 3.17 | 2.06 | 0.92 | 0.36 | 23.28 | 11.81 | 6.35 |
| 5800.0 | 10.63 | 10.66 | 0.03 | 2.58 | 24.75 | 3.18 | 2.01 | 0.92 | 0.38 | 23.57 | 11.39 | 6.65 |
| 6000.0 | 10.09 | 10.16 | 0.07 | 2.80 | 24.76 | 3.24 | 1.99 | 0.92 | 0.39 | 22.99 | 10.95 | 6.90 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB) 85.89 85.98

TEST CONDITIONS: Vd =5.25V, Id1 A1) = 85.89 mA and Id2 (A2) =85.98 mA @ Temperature = -45degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 10.0 | 17.09 | 17.08 | 0.01 | 0.23 | 23.21 | 20.14 | 11.40 | 1.15 | 0.72 | -- | 20.12 | 3.74 |
| 20.0 | 17.05 | 17.04 | 0.01 | 0.01 | 23.01 | 19.36 | 11.69 | 1.14 | 0.72 | 39.11 | 19.96 | 4.16 |
| 30.0 | 16.94 | 16.94 | 0.00 | 0.01 | 22.73 | 18.58 | 12.03 | 1.13 | 0.72 | 41.73 | 20.46 | 4.05 |
| 40.0 | 16.82 | 16.82 | 0.00 | 0.00 | 22.58 | 17.93 | 12.42 | 1.13 | 0.72 | 40.36 | 20.82 | 3.92 |
| 50.0 | 16.71 | 16.71 | 0.00 | 0.00 | 22.55 | 17.30 | 12.83 | 1.13 | 0.74 | 42.17 | 20.58 | 4.03 |
| 60.0 | 16.58 | 16.57 | 0.01 | 0.01 | 22.20 | 17.01 | 13.18 | 1.12 | 0.73 | 40.18 | 20.61 | 4.01 |
| 70.0 | 16.49 | 16.49 | 0.00 | 0.03 | 22.18 | 16.68 | 13.54 | 1.13 | 0.74 | 42.87 | 20.63 | 3.99 |
| 80.0 | 16.41 | 16.40 | 0.01 | 0.05 | 22.09 | 16.46 | 13.89 | 1.13 | 0.74 | 43.03 | 20.73 | 4.02 |
| 90.0 | 16.34 | 16.33 | 0.01 | 0.05 | 22.03 | 16.33 | 14.16 | 1.13 | 0.75 | 41.34 | 20.77 | 4.06 |
| 100.0 | 16.28 | 16.28 | 0.00 | 0.07 | 21.96 | 16.17 | 14.42 | 1.13 | 0.75 | 40.81 | 20.71 | 4.04 |
| 200.0 | 16.03 | 16.03 | 0.00 | 0.09 | 21.71 | 15.40 | 16.24 | 1.15 | 0.76 | 41.17 | 20.76 | 4.04 |
| 400.0 | 15.95 | 15.95 | 0.00 | 0.18 | 21.66 | 14.34 | 17.88 | 1.15 | 0.78 | 41.82 | 20.74 | 4.22 |
| 600.0 | 15.94 | 15.94 | 0.00 | 0.22 | 21.60 | 14.00 | 18.64 | 1.15 | 0.78 | 39.61 | 20.75 | 4.32 |
| 800.0 | 15.97 | 15.96 | 0.01 | 0.31 | 21.59 | 13.57 | 19.08 | 1.14 | 0.78 | 40.79 | 20.78 | 4.27 |
| 1000.0 | 16.00 | 15.99 | 0.01 | 0.36 | 21.59 | 13.13 | 19.88 | 1.14 | 0.78 | 39.19 | 20.81 | 4.31 |
| 1200.0 | 16.04 | 16.02 | 0.02 | 0.44 | 21.58 | 12.46 | 20.88 | 1.14 | 0.78 | 38.88 | 20.72 | 4.35 |
| 1400.0 | 16.08 | 16.06 | 0.02 | 0.56 | 21.59 | 11.86 | 21.34 | 1.13 | 0.78 | 38.03 | 20.75 | 4.39 |
| 1600.0 | 16.14 | 16.11 | 0.03 | 0.64 | 21.59 | 11.39 | 20.96 | 1.13 | 0.78 | 37.39 | 20.63 | 4.39 |
| 1800.0 | 16.17 | 16.15 | 0.02 | 0.82 | 21.64 | 10.92 | 20.31 | 1.12 | 0.78 | 37.02 | 20.75 | 4.38 |
| 2000.0 | 16.26 | 16.22 | 0.04 | 0.87 | 21.58 | 10.52 | 18.88 | 1.11 | 0.77 | 36.40 | 20.54 | 4.43 |
| 2200.0 | 16.30 | 16.25 | 0.05 | 1.05 | 21.57 | 9.90 | 17.28 | 1.10 | 0.76 | 34.60 | 19.97 | 4.51 |
| 2400.0 | 16.32 | 16.30 | 0.02 | 1.12 | 21.61 | 9.38 | 15.90 | 1.10 | 0.75 | 34.68 | 20.07 | 4.52 |
| 2600.0 | 16.36 | 16.31 | 0.05 | 1.17 | 21.65 | 8.84 | 14.24 | 1.09 | 0.74 | 33.65 | 19.61 | 4.71 |
| 2800.0 | 16.36 | 16.31 | 0.05 | 1.30 | 21.67 | 8.15 | 12.67 | 1.08 | 0.72 | 32.68 | 19.29 | 4.80 |
| 3000.0 | 16.30 | 16.25 | 0.05 | 1.62 | 21.75 | 7.38 | 11.02 | 1.07 | 0.70 | 32.08 | 18.89 | 4.79 |
| 3200.0 | 16.18 | 16.12 | 0.06 | 1.60 | 21.88 | 6.59 | 9.41 | 1.06 | 0.68 | 30.72 | 18.21 | 4.87 |
| 3400.0 | 16.00 | 15.96 | 0.04 | 1.72 | 22.06 | 5.88 | 8.07 | 1.05 | 0.65 | 30.10 | 17.97 | 4.97 |
| 3600.0 | 15.77 | 15.73 | 0.04 | 1.90 | 22.28 | 5.30 | 6.86 | 1.04 | 0.61 | 29.36 | 17.40 | 5.11 |
| 3800.0 | 15.43 | 15.42 | 0.01 | 2.28 | 22.53 | 4.69 | 5.74 | 1.02 | 0.56 | 28.93 | 16.94 | 5.33 |
| 4000.0 | 15.04 | 15.03 | 0.01 | 2.15 | 22.87 | 4.17 | 4.86 | 1.01 | 0.53 | 28.65 | 16.53 | 5.48 |
| 4200.0 | 14.60 | 14.59 | 0.01 | 2.21 | 23.22 | 3.80 | 4.08 | 1.00 | 0.48 | 27.69 | 15.87 | 5.60 |
| 4400.0 | 14.14 | 14.11 | 0.03 | 2.30 | 23.59 | 3.51 | 3.50 | 0.98 | 0.45 | 27.34 | 15.33 | 5.78 |
| 4600.0 | 13.69 | 13.65 | 0.04 | 2.23 | 23.82 | 3.29 | 3.07 | 0.97 | 0.41 | 26.88 | 14.91 | 6.04 |
| 4800.0 | 13.22 | 13.22 | 0.00 | 2.49 | 24.21 | 3.12 | 2.70 | 0.95 | 0.39 | 26.74 | 14.40 | 6.11 |
| 5000.0 | 12.79 | 12.77 | 0.02 | 2.40 | 24.39 | 3.09 | 2.46 | 0.94 | 0.37 | 25.89 | 13.83 | 6.33 |
| 5200.0 | 12.37 | 12.39 | 0.02 | 2.85 | 24.53 | 3.05 | 2.29 | 0.93 | 0.36 | 26.07 | 13.50 | 6.31 |
| 5400.0 | 11.94 | 11.91 | 0.03 | 3.12 | 24.46 | 3.14 | 2.19 | 0.92 | 0.35 | 26.14 | 12.83 | 6.59 |
| 5600.0 | 11.46 | 11.49 | 0.03 | 2.93 | 24.73 | 3.11 | 2.08 | 0.91 | 0.36 | 24.84 | 12.68 | 6.51 |
| 5800.0 | 10.91 | 10.94 | 0.03 | 2.75 | 25.02 | 3.12 | 2.02 | 0.92 | 0.38 | 25.15 | 12.22 | 6.92 |
| 6000.0 | 10.38 | 10.45 | 0.07 | 2.98 | 25.00 | 3.18 | 2.01 | 0.92 | 0.40 | 24.50 | 11.80 | 7.09 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id1(A1) = 85.19 mA and Id2 (A2) = 85.14 mA @ Temperature = +85degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|---------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) | (dB) |
| 10.0 | 16.89 | 16.88 | 0.01 | 0.11 | 22.46 | 21.78 | 11.09 | 1.11 | 0.68 | -- | 19.77 | 4.91 |
| 20.0 | 16.86 | 16.85 | 0.01 | 0.01 | 22.71 | 20.05 | 11.66 | 1.13 | 0.71 | 38.08 | 19.48 | 5.35 |
| 30.0 | 16.75 | 16.75 | 0.00 | 0.01 | 22.56 | 19.12 | 12.05 | 1.13 | 0.71 | 41.43 | 20.02 | 5.24 |
| 40.0 | 16.63 | 16.63 | 0.00 | 0.01 | 22.41 | 18.27 | 12.51 | 1.13 | 0.72 | 39.48 | 20.40 | 5.17 |
| 50.0 | 16.53 | 16.53 | 0.00 | 0.00 | 22.32 | 17.67 | 12.99 | 1.14 | 0.73 | 40.17 | 20.19 | 5.24 |
| 60.0 | 16.40 | 16.39 | 0.01 | 0.01 | 22.16 | 17.08 | 13.50 | 1.14 | 0.74 | 41.30 | 20.16 | 5.27 |
| 70.0 | 16.31 | 16.31 | 0.00 | 0.01 | 21.97 | 16.64 | 13.99 | 1.13 | 0.74 | 40.62 | 20.15 | 5.23 |
| 80.0 | 16.22 | 16.22 | 0.00 | 0.00 | 21.93 | 16.30 | 14.43 | 1.14 | 0.75 | 39.30 | 20.24 | 5.27 |
| 90.0 | 16.16 | 16.15 | 0.01 | 0.00 | 21.83 | 16.06 | 14.83 | 1.14 | 0.75 | 38.86 | 20.28 | 5.30 |
| 100.0 | 16.10 | 16.10 | 0.00 | 0.00 | 21.79 | 15.82 | 15.18 | 1.14 | 0.75 | 38.97 | 20.23 | 5.30 |
| 200.0 | 15.82 | 15.82 | 0.00 | 0.04 | 21.54 | 14.84 | 17.14 | 1.15 | 0.77 | 38.44 | 20.32 | 5.30 |
| 400.0 | 15.73 | 15.73 | 0.00 | 0.06 | 21.50 | 14.75 | 17.68 | 1.16 | 0.77 | 40.87 | 20.20 | 5.52 |
| 600.0 | 15.72 | 15.72 | 0.00 | 0.14 | 21.46 | 14.39 | 18.44 | 1.16 | 0.78 | 38.31 | 20.19 | 5.61 |
| 800.0 | 15.74 | 15.73 | 0.01 | 0.18 | 21.47 | 13.97 | 19.03 | 1.16 | 0.78 | 37.90 | 20.13 | 5.55 |
| 1000.0 | 15.77 | 15.76 | 0.01 | 0.23 | 21.49 | 13.54 | 19.81 | 1.16 | 0.78 | 36.78 | 20.21 | 5.58 |
| 1200.0 | 15.81 | 15.80 | 0.01 | 0.29 | 21.53 | 13.04 | 20.47 | 1.16 | 0.79 | 36.34 | 19.94 | 5.67 |
| 1400.0 | 15.86 | 15.84 | 0.02 | 0.38 | 21.53 | 12.53 | 21.06 | 1.15 | 0.79 | 35.66 | 19.89 | 5.67 |
| 1600.0 | 15.91 | 15.89 | 0.02 | 0.49 | 21.53 | 12.03 | 21.06 | 1.15 | 0.78 | 34.77 | 19.64 | 5.70 |
| 1800.0 | 15.95 | 15.93 | 0.02 | 0.65 | 21.61 | 11.45 | 20.51 | 1.15 | 0.78 | 33.80 | 19.63 | 5.70 |
| 2000.0 | 16.03 | 16.00 | 0.03 | 0.65 | 21.57 | 11.02 | 18.83 | 1.14 | 0.77 | 33.43 | 19.43 | 5.72 |
| 2200.0 | 16.07 | 16.03 | 0.04 | 0.81 | 21.60 | 10.55 | 17.17 | 1.13 | 0.76 | 32.14 | 18.76 | 5.80 |
| 2400.0 | 16.08 | 16.07 | 0.01 | 0.79 | 21.69 | 10.09 | 15.72 | 1.13 | 0.76 | 31.56 | 18.72 | 5.81 |
| 2600.0 | 16.11 | 16.07 | 0.04 | 0.88 | 21.69 | 9.58 | 14.07 | 1.13 | 0.74 | 31.06 | 18.25 | 6.01 |
| 2800.0 | 16.09 | 16.04 | 0.05 | 1.00 | 21.75 | 8.97 | 12.42 | 1.12 | 0.72 | 30.02 | 17.83 | 6.11 |
| 3000.0 | 16.01 | 15.96 | 0.05 | 1.45 | 21.83 | 8.31 | 10.87 | 1.11 | 0.70 | 29.56 | 17.48 | 6.07 |
| 3200.0 | 15.89 | 15.84 | 0.05 | 1.21 | 21.94 | 7.62 | 9.45 | 1.10 | 0.67 | 28.20 | 16.75 | 6.20 |
| 3400.0 | 15.65 | 15.64 | 0.01 | 1.35 | 22.08 | 6.87 | 8.10 | 1.10 | 0.64 | 27.51 | 16.37 | 6.26 |
| 3600.0 | 15.38 | 15.35 | 0.03 | 1.62 | 22.26 | 6.24 | 6.85 | 1.09 | 0.60 | 26.73 | 15.79 | 6.41 |
| 3800.0 | 14.96 | 14.98 | 0.02 | 1.81 | 22.53 | 5.62 | 5.77 | 1.08 | 0.57 | 26.26 | 15.30 | 6.64 |
| 4000.0 | 14.53 | 14.48 | 0.05 | 1.75 | 22.79 | 5.11 | 4.94 | 1.07 | 0.53 | 25.89 | 14.91 | 6.73 |
| 4200.0 | 14.02 | 14.01 | 0.01 | 1.85 | 23.07 | 4.72 | 4.25 | 1.06 | 0.50 | 25.02 | 14.20 | 6.87 |
| 4400.0 | 13.45 | 13.46 | 0.01 | 1.82 | 23.40 | 4.40 | 3.74 | 1.05 | 0.49 | 24.67 | 13.63 | 7.10 |
| 4600.0 | 12.90 | 12.90 | 0.00 | 1.92 | 23.65 | 4.19 | 3.37 | 1.04 | 0.48 | 24.05 | 13.15 | 7.39 |
| 4800.0 | 12.29 | 12.32 | 0.03 | 2.05 | 23.97 | 4.01 | 3.08 | 1.04 | 0.47 | 23.55 | 12.62 | 7.45 |
| 5000.0 | 11.76 | 11.76 | 0.00 | 1.98 | 24.03 | 3.94 | 2.94 | 1.04 | 0.48 | 23.22 | 12.00 | 7.74 |
| 5200.0 | 11.19 | 11.24 | 0.05 | 2.04 | 24.27 | 3.88 | 2.82 | 1.04 | 0.50 | 22.60 | 11.64 | 7.74 |
| 5400.0 | 10.64 | 10.67 | 0.03 | 2.20 | 24.13 | 3.96 | 2.86 | 1.05 | 0.52 | 22.68 | 11.03 | 8.04 |
| 5600.0 | 10.08 | 10.11 | 0.03 | 2.15 | 24.30 | 3.91 | 2.85 | 1.07 | 0.55 | 21.22 | 10.80 | 7.98 |
| 5800.0 | 9.52 | 9.55 | 0.03 | 2.16 | 24.43 | 3.90 | 2.90 | 1.08 | 0.58 | 21.16 | 10.44 | 8.40 |
| 6000.0 | 8.92 | 8.97 | 0.05 | 2.33 | 24.42 | 3.92 | 2.95 | 1.11 | 0.61 | 21.00 | 9.96 | 8.58 |

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id1(A1) = 76.59 mA and Id2 (A2) = 76.5 mA @ Temperature = +85degC

| FREQ | A1 | A2 | A1 & A2 | | A1 | | | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| | (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) |
| 10.0 | 16.84 | 16.84 | 0.00 | 0.05 | 22.93 | 22.08 | 11.17 | 1.15 | 0.70 | -- | 18.80 | 4.85 |
| 20.0 | 16.81 | 16.80 | 0.01 | 0.03 | 22.73 | 20.45 | 11.55 | 1.14 | 0.71 | 38.81 | 18.77 | 5.25 |
| 30.0 | 16.71 | 16.70 | 0.01 | 0.02 | 22.58 | 19.47 | 11.94 | 1.14 | 0.72 | 39.71 | 19.29 | 5.13 |
| 40.0 | 16.59 | 16.58 | 0.01 | 0.01 | 22.35 | 18.59 | 12.43 | 1.13 | 0.72 | 37.79 | 19.64 | 5.09 |
| 50.0 | 16.49 | 16.48 | 0.01 | 0.01 | 22.35 | 17.98 | 12.91 | 1.14 | 0.73 | 37.71 | 19.40 | 5.18 |
| 60.0 | 16.35 | 16.35 | 0.00 | 0.01 | 21.97 | 17.28 | 13.38 | 1.13 | 0.73 | 38.33 | 19.42 | 5.16 |
| 70.0 | 16.27 | 16.26 | 0.01 | 0.01 | 21.98 | 16.89 | 13.84 | 1.14 | 0.74 | 38.24 | 19.44 | 5.16 |
| 80.0 | 16.18 | 16.18 | 0.00 | 0.01 | 21.84 | 16.53 | 14.29 | 1.14 | 0.74 | 37.34 | 19.51 | 5.18 |
| 90.0 | 16.11 | 16.11 | 0.00 | 0.01 | 21.77 | 16.28 | 14.66 | 1.14 | 0.75 | 37.27 | 19.55 | 5.23 |
| 100.0 | 16.06 | 16.05 | 0.01 | 0.00 | 21.72 | 16.06 | 15.04 | 1.14 | 0.75 | 36.67 | 19.50 | 5.23 |
| 200.0 | 15.78 | 15.78 | 0.00 | 0.05 | 21.50 | 15.05 | 16.97 | 1.15 | 0.77 | 37.19 | 19.55 | 5.21 |
| 400.0 | 15.69 | 15.69 | 0.00 | 0.04 | 21.43 | 14.97 | 17.47 | 1.16 | 0.77 | 37.79 | 19.47 | 5.42 |
| 600.0 | 15.68 | 15.67 | 0.01 | 0.12 | 21.43 | 14.61 | 18.20 | 1.16 | 0.77 | 36.78 | 19.44 | 5.50 |
| 800.0 | 15.70 | 15.69 | 0.01 | 0.17 | 21.46 | 14.17 | 18.79 | 1.16 | 0.78 | 37.07 | 19.43 | 5.48 |
| 1000.0 | 15.73 | 15.72 | 0.01 | 0.22 | 21.46 | 13.71 | 19.50 | 1.16 | 0.78 | 35.79 | 19.48 | 5.52 |
| 1200.0 | 15.77 | 15.76 | 0.01 | 0.28 | 21.44 | 13.21 | 20.13 | 1.15 | 0.78 | 35.83 | 19.34 | 5.57 |
| 1400.0 | 15.82 | 15.80 | 0.02 | 0.36 | 21.46 | 12.69 | 20.66 | 1.15 | 0.78 | 35.09 | 19.34 | 5.60 |
| 1600.0 | 15.88 | 15.85 | 0.03 | 0.45 | 21.48 | 12.17 | 20.60 | 1.15 | 0.78 | 34.69 | 19.17 | 5.55 |
| 1800.0 | 15.91 | 15.89 | 0.02 | 0.63 | 21.52 | 11.60 | 20.10 | 1.15 | 0.78 | 33.77 | 19.22 | 5.59 |
| 2000.0 | 15.98 | 15.95 | 0.03 | 0.60 | 21.51 | 11.15 | 18.42 | 1.14 | 0.77 | 33.22 | 19.02 | 5.64 |
| 2200.0 | 16.03 | 15.98 | 0.05 | 0.73 | 21.56 | 10.68 | 16.84 | 1.14 | 0.76 | 32.13 | 18.38 | 5.71 |
| 2400.0 | 16.04 | 16.02 | 0.02 | 0.71 | 21.62 | 10.22 | 15.44 | 1.13 | 0.75 | 31.57 | 18.36 | 5.72 |
| 2600.0 | 16.05 | 16.02 | 0.03 | 0.78 | 21.64 | 9.69 | 13.82 | 1.13 | 0.73 | 30.87 | 17.86 | 5.92 |
| 2800.0 | 16.03 | 15.98 | 0.05 | 0.93 | 21.65 | 9.07 | 12.22 | 1.12 | 0.71 | 29.84 | 17.46 | 6.01 |
| 3000.0 | 15.95 | 15.90 | 0.05 | 1.35 | 21.70 | 8.42 | 10.71 | 1.11 | 0.69 | 29.49 | 17.11 | 5.99 |
| 3200.0 | 15.82 | 15.77 | 0.05 | 1.11 | 21.86 | 7.71 | 9.30 | 1.10 | 0.66 | 27.96 | 16.36 | 6.11 |
| 3400.0 | 15.58 | 15.56 | 0.02 | 1.23 | 22.02 | 6.96 | 7.97 | 1.10 | 0.64 | 27.31 | 15.99 | 6.15 |
| 3600.0 | 15.30 | 15.26 | 0.04 | 1.50 | 22.17 | 6.32 | 6.74 | 1.09 | 0.59 | 26.49 | 15.38 | 6.31 |
| 3800.0 | 14.86 | 14.88 | 0.02 | 1.70 | 22.43 | 5.68 | 5.68 | 1.08 | 0.56 | 25.94 | 14.92 | 6.52 |
| 4000.0 | 14.43 | 14.36 | 0.07 | 1.66 | 22.70 | 5.17 | 4.86 | 1.07 | 0.52 | 25.62 | 14.52 | 6.64 |
| 4200.0 | 13.91 | 13.88 | 0.03 | 1.70 | 22.99 | 4.78 | 4.19 | 1.05 | 0.50 | 24.72 | 13.79 | 6.75 |
| 4400.0 | 13.32 | 13.33 | 0.01 | 1.70 | 23.30 | 4.46 | 3.68 | 1.05 | 0.48 | 24.37 | 13.23 | 7.02 |
| 4600.0 | 12.76 | 12.75 | 0.01 | 1.80 | 23.57 | 4.24 | 3.32 | 1.04 | 0.47 | 23.69 | 12.74 | 7.29 |
| 4800.0 | 12.15 | 12.16 | 0.01 | 1.92 | 23.82 | 4.06 | 3.04 | 1.04 | 0.47 | 23.19 | 12.27 | 7.34 |
| 5000.0 | 11.61 | 11.60 | 0.01 | 1.84 | 23.94 | 3.99 | 2.90 | 1.03 | 0.47 | 22.86 | 11.63 | 7.64 |
| 5200.0 | 11.04 | 11.06 | 0.02 | 1.93 | 24.20 | 3.93 | 2.80 | 1.04 | 0.49 | 22.23 | 11.27 | 7.62 |
| 5400.0 | 10.48 | 10.50 | 0.02 | 2.03 | 24.01 | 3.99 | 2.83 | 1.05 | 0.52 | 22.33 | 10.60 | 7.90 |
| 5600.0 | 9.92 | 9.93 | 0.01 | 2.02 | 24.23 | 3.95 | 2.82 | 1.07 | 0.55 | 20.80 | 10.40 | 7.85 |
| 5800.0 | 9.36 | 9.37 | 0.01 | 1.99 | 24.36 | 3.93 | 2.88 | 1.09 | 0.58 | 20.71 | 9.98 | 8.25 |
| 6000.0 | 8.76 | 8.79 | 0.03 | 2.14 | 24.36 | 3.94 | 2.92 | 1.12 | 0.61 | 20.57 | 9.55 | 8.42 |



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)









Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)









TEST CONDITIONS: Vd = 5.25V, Id1(A1) = 94.35 mA and Id2 (A2) = 94.19 mA @ Temperature = +85degC

| FREQ | A1 | | A2 | | A1 & A2 | | A1 | | | | | |
|--------|-------|-------|-----------|-------------|-----------|-------------------|--------------------|-----------|------|-------------|------------------|--------------|
| | Gain | | Amp Unbal | Phase Unbal | Isolation | Input Return Loss | Output Return Loss | Stability | | IP-3 Output | 1dB Comp. Output | Noise Figure |
| | (MHz) | (dB) | (dB) | (dB) | (Deg) | (dB) | (dB) | (dB) | K | Measure | (dBm) | (dBm) |
| 10.0 | 16.93 | 16.95 | 0.02 | 0.03 | 22.85 | 21.28 | 11.53 | 1.14 | 0.70 | -- | 20.03 | 5.00 |
| 20.0 | 16.89 | 16.88 | 0.01 | 0.04 | 22.71 | 19.71 | 11.70 | 1.13 | 0.71 | 39.56 | 20.04 | 5.40 |
| 30.0 | 16.78 | 16.78 | 0.00 | 0.03 | 22.69 | 18.90 | 12.14 | 1.14 | 0.72 | 40.34 | 20.55 | 5.33 |
| 40.0 | 16.67 | 16.66 | 0.01 | 0.02 | 22.41 | 18.02 | 12.61 | 1.13 | 0.72 | 41.93 | 21.00 | 5.25 |
| 50.0 | 16.56 | 16.56 | 0.00 | 0.00 | 22.18 | 17.36 | 13.08 | 1.12 | 0.73 | 42.81 | 20.79 | 5.34 |
| 60.0 | 16.43 | 16.42 | 0.01 | 0.02 | 22.19 | 16.78 | 13.57 | 1.14 | 0.74 | 40.64 | 20.72 | 5.35 |
| 70.0 | 16.34 | 16.33 | 0.01 | 0.01 | 22.07 | 16.44 | 14.08 | 1.14 | 0.75 | 41.42 | 20.73 | 5.33 |
| 80.0 | 16.25 | 16.25 | 0.00 | 0.00 | 21.96 | 16.09 | 14.53 | 1.14 | 0.75 | 39.86 | 20.83 | 5.37 |
| 90.0 | 16.19 | 16.18 | 0.01 | 0.00 | 21.88 | 15.84 | 14.94 | 1.14 | 0.75 | 40.50 | 20.85 | 5.39 |
| 100.0 | 16.13 | 16.12 | 0.01 | 0.01 | 21.82 | 15.61 | 15.30 | 1.14 | 0.76 | 40.45 | 20.78 | 5.38 |
| 200.0 | 15.85 | 15.85 | 0.00 | 0.03 | 21.58 | 14.65 | 17.32 | 1.15 | 0.77 | 39.12 | 20.90 | 5.31 |
| 400.0 | 15.76 | 15.76 | 0.00 | 0.06 | 21.51 | 14.59 | 17.86 | 1.16 | 0.77 | 39.89 | 20.72 | 5.56 |
| 600.0 | 15.75 | 15.74 | 0.01 | 0.08 | 21.54 | 14.24 | 18.66 | 1.16 | 0.78 | 39.52 | 20.70 | 5.68 |
| 800.0 | 15.77 | 15.76 | 0.01 | 0.12 | 21.54 | 13.82 | 19.27 | 1.16 | 0.78 | 38.49 | 20.55 | 5.66 |
| 1000.0 | 15.80 | 15.79 | 0.01 | 0.18 | 21.56 | 13.39 | 20.06 | 1.16 | 0.79 | 36.79 | 20.62 | 5.68 |
| 1200.0 | 15.84 | 15.82 | 0.02 | 0.23 | 21.56 | 12.91 | 20.80 | 1.16 | 0.79 | 36.51 | 20.25 | 5.73 |
| 1400.0 | 15.89 | 15.87 | 0.02 | 0.28 | 21.58 | 12.42 | 21.47 | 1.15 | 0.79 | 35.24 | 20.20 | 5.74 |
| 1600.0 | 15.94 | 15.92 | 0.02 | 0.37 | 21.59 | 11.92 | 21.49 | 1.15 | 0.79 | 34.30 | 19.87 | 5.75 |
| 1800.0 | 15.98 | 15.96 | 0.02 | 0.52 | 21.65 | 11.36 | 21.00 | 1.15 | 0.79 | 33.69 | 19.85 | 5.76 |
| 2000.0 | 16.06 | 16.02 | 0.04 | 0.50 | 21.62 | 10.93 | 19.20 | 1.14 | 0.78 | 32.89 | 19.64 | 5.84 |
| 2200.0 | 16.10 | 16.06 | 0.04 | 0.63 | 21.66 | 10.47 | 17.47 | 1.14 | 0.77 | 31.57 | 18.94 | 5.91 |
| 2400.0 | 16.12 | 16.10 | 0.02 | 0.60 | 21.71 | 10.02 | 15.96 | 1.13 | 0.76 | 31.34 | 18.89 | 5.90 |
| 2600.0 | 16.14 | 16.10 | 0.04 | 0.66 | 21.77 | 9.51 | 14.29 | 1.13 | 0.74 | 30.64 | 18.44 | 6.10 |
| 2800.0 | 16.12 | 16.08 | 0.04 | 0.80 | 21.78 | 8.92 | 12.62 | 1.12 | 0.72 | 29.63 | 18.03 | 6.23 |
| 3000.0 | 16.05 | 16.00 | 0.05 | 1.20 | 21.88 | 8.29 | 11.05 | 1.11 | 0.70 | 29.33 | 17.68 | 6.17 |
| 3200.0 | 15.93 | 15.88 | 0.05 | 0.97 | 21.94 | 7.60 | 9.60 | 1.10 | 0.68 | 28.01 | 16.97 | 6.31 |
| 3400.0 | 15.70 | 15.68 | 0.02 | 1.07 | 22.12 | 6.86 | 8.24 | 1.10 | 0.65 | 27.47 | 16.58 | 6.37 |
| 3600.0 | 15.43 | 15.40 | 0.03 | 1.34 | 22.36 | 6.23 | 6.97 | 1.09 | 0.61 | 26.66 | 15.99 | 6.57 |
| 3800.0 | 15.01 | 15.03 | 0.02 | 1.51 | 22.53 | 5.61 | 5.88 | 1.08 | 0.57 | 26.19 | 15.51 | 6.77 |
| 4000.0 | 14.59 | 14.52 | 0.07 | 1.50 | 22.86 | 5.12 | 5.04 | 1.07 | 0.54 | 25.84 | 15.13 | 6.81 |
| 4200.0 | 14.08 | 14.07 | 0.01 | 1.49 | 23.18 | 4.72 | 4.35 | 1.06 | 0.52 | 25.02 | 14.44 | 6.99 |
| 4400.0 | 13.51 | 13.52 | 0.01 | 1.47 | 23.41 | 4.40 | 3.82 | 1.05 | 0.50 | 24.68 | 13.91 | 7.26 |
| 4600.0 | 12.96 | 12.96 | 0.00 | 1.60 | 23.71 | 4.20 | 3.46 | 1.05 | 0.49 | 24.04 | 13.36 | 7.52 |
| 4800.0 | 12.36 | 12.38 | 0.02 | 1.65 | 23.98 | 4.01 | 3.16 | 1.04 | 0.49 | 23.56 | 12.86 | 7.62 |
| 5000.0 | 11.82 | 11.82 | 0.00 | 1.61 | 24.07 | 3.94 | 3.02 | 1.04 | 0.49 | 23.27 | 12.27 | 7.87 |
| 5200.0 | 11.25 | 11.29 | 0.04 | 1.67 | 24.32 | 3.88 | 2.91 | 1.05 | 0.51 | 22.67 | 11.93 | 7.94 |
| 5400.0 | 10.70 | 10.72 | 0.02 | 1.75 | 24.19 | 3.95 | 2.94 | 1.06 | 0.54 | 22.71 | 11.26 | 8.18 |
| 5600.0 | 10.13 | 10.16 | 0.03 | 1.71 | 24.35 | 3.91 | 2.95 | 1.08 | 0.57 | 21.37 | 11.10 | 8.20 |
| 5800.0 | 9.57 | 9.59 | 0.02 | 1.69 | 24.47 | 3.89 | 3.00 | 1.09 | 0.61 | 21.27 | 10.64 | 8.56 |
| 6000.0 | 8.97 | 9.01 | 0.04 | 1.85 | 24.50 | 3.91 | 3.04 | 1.12 | 0.63 | 21.12 | 10.16 | 8.74 |




Typical Performance Curves




Typical Performance Curves




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L | M | N |
|--------|----|----------------|----------------|----------------|----|----------------|----------------|----------------|----|----------------|----|----------------|----------------|
| DL1020 | -- | .193 (4.90) | .035 (0.90) | .236 (6.00) | -- | .050 (1.27) | .017 (0.42) | .008 (0.20) | -- | .024 (0.60) | -- | .050 (1.27) | .030 (0.76) |

| CASE # | P | Q | R | S | T | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----|----------|
| DL1020 | .270 (6.86) | .030 (0.76) | .110 (2.79) | .020 (0.51) | -- | .08 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note | |
|----------------|-------------------------|-------------------|---------------------------|------|
| 12 | 8 | 7 | Small quantity standard | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | 7 | Standard | 1000 |
| | | 13 | Standard | 2000 |
| | | | | 3000 |
| 4000 | | | | |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------|----------|-----|------|
| OR | M125629 | NEW RELEASE | 04/20/10 | MMG | RD |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR
DL1020 CASE STYLE, "08AM04" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. RECOMMEND TO PLUG 15 PTH UNDER THE UNIT TO AVOID SOLDER WICKING.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|-------------|----------|
| DIMENSIONS ARE IN INCHES | DRAWN MMG | 01/26/10 |
| TOLERANCES ON: | CHECKED IL | 04/20/10 |
| 2 PL DECIMALS ± | APPROVED RD | 04/20/10 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |




Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 08AM04, DL1020

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|--------------------|---------------|-------------|---------------|
| A | 15542 | 98-PL-322 | OR |
| FILE: | 98PL322 | SCALE: | SHEET: 1 OF 1 |
| ASHEETA1.DWG REV:A | DATE:01/12/95 | | |


Evaluation Board and Circuit




TB-666-50-62+

NOTES:

1. SMA Female connectors.
2. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.

 **Mini-Circuits®**

Evaluation Board and Circuit




Note:

Numbers inside the boxes indicate Pin Numbers.

| COMPONENT | VALUE | SIZE |
|-----------|--|----------------|
| A1 | Mini-Circuits MGVA-62+ | PER DATA SHEET |
| C1,C2 | .039 μ F | 0805 |
| C3,C4 | .001 μ F | 0402 |
| C5,C6 | .2 pF | 0402 |
| C7,C8 | 1.1 pF | 0402 |
| C9 | 1.0 μ F | 1311 |
| C10 | .4 pF | 0603 |
| C11 | 270 pF | 0805 |
| C12 | .4 pF | 0402 |
| C13 | .7 pF | 0402 |
| C14 | .3 pF | 0402 |
| C15 | .6 pF | 0402 |
| C16 | 1.0 pF | 0402 |
| D1 | Diode, Schottky Rectifier Vf=.385V @ .5A, Vr=10V MAX | - |
| L1,L2 | 1.1 nH | .073"X.054" |
| L3 | 1.5 μ H | 1008 |
| R1,R2 | 5.11 Ohm | 1206 |
| R3,R4 | 7.50 Ohm | 1206 |
| T1 | Mini-Circuits TCM2-33WX+ | PER DATA SHEET |
| T2 | Mini-Circuits TCM2-43X+ | PER DATA SHEET |
| P1,P2 | Mini-Circuits TCBT-6G+ | PER DATA SHEET |

Schematic Diagram

 Mini-Circuits[®]

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|---|
| Operating Temperature | -45° to 85°C or -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -65° to 150° C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Mechanical Shock | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak | MIL-STD-883, Method 2007, Condition B |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102, Condition C |
| HAST | 130°C, 85% RH, 96 hours | JESD22-A110 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + | MIL-STD-202, Method 215 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------|----------------------------------|-----------------------|
| | monoethanolamine at 63°C to 70°C | |