



MMIC DIE

# SPDT RF Switch

# M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver


### THE BIG DEAL

- Wideband, DC to 30 GHz
- Low Insertion Loss, Typ. 1.1 dB
- High Isolation RF1-RF2, Typ. 67 dB
- High Input IP3, Typ. +48 dBm
- Fast Rise/Fall Time, Typ. 6.9 ns/7.1 ns

### APPLICATIONS

- Radar, EW and ECM Defense Systems
- Communication Infrastructure
- Test and Measurements

### FUNCTIONAL DIAGRAM



SEE ORDERING INFORMATION ON THE LAST PAGE

### PRODUCT OVERVIEW

Mini-Circuits' M3SWA2-34DR-D+ is a GaAs MMIC SPDT absorptive switch with an internal driver designed for wideband operation from DC to 30 GHz. This switch enables fast, nano-second switching across a wide frequency range with no gate lag effects. This model provides excellent isolation, high linearity and is capable of withstanding +27 dBm RF input power. The M3SWA2-34DR-D+ die is suitable for chip and wire assemblies.

### KEY FEATURES

| Features   | Advantages   |
|--|--|
| Absorptive Design  | Absorptive switch design enables excellent return loss on all ports, minimizing reflection at the unselected port.   |
| High Isolation: <ul style="list-style-type: none"> <li>• 62 dB Typ. RFC to RF1/RF2</li> <li>• 67 dB Typ. RF1 to RF2</li> </ul>   | High isolation significantly reduces leakage of power into OFF ports.  |
| High linearity and Input Power: <ul style="list-style-type: none"> <li>• Input Power at P1dB, 25.2 dBm Typ.</li> <li>• Input IP3, +48 dBm Typ.</li> <li>• Max RF Input Power, +27 dBm CW</li> </ul>    | High linearity minimizes unwanted intermodulation products which are difficult or impossible to filter in multi-carrier environments, or in the presence of strong interfering signal from adjacent circuitry. High RF input power tolerance protects the device from damage due to unexpected spikes in signal level. |
| Fast RF Switching Time: <ul style="list-style-type: none"> <li>• Rise/Fall Time, Typ. 6.9 ns/7.1 ns</li> <li>• On/Off Time, Typ. 23.3 ns/16.5 ns</li> <li>• Settling to 0.05 dB, Typ. 29 ns</li> </ul> | Fast switching makes this model suitable for applications where extremely fast transition between ports is required, such as automated switching networks.   |
| Unpackaged Die   | Suitable for chip and wire hybrid assemblies   |

REV. A  
ECO-022246  
M3SWA2-34DR-D+  
MCL NY  
240710





MMIC DIE

# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### ELECTRICAL SPECIFICATIONS<sup>1,2,3</sup> AT +25° C, V<sub>DD</sub> = +3.3 V, V<sub>EE</sub> = -3.3 V UNLESS NOTED OTHERWISE

| Parameter                                    | Condition (GHz) | Min. | Typ.  | Max. | Units |
|--|-----------------|------|-------|------|-------|
| Frequency Range                              |                 | DC   |       | 30   | GHz   |
| Insertion Loss                               | 0.01            |      | 0.5   |      | dB    |
|  | 0.1             |      | 0.6   |      |       |
|  | 1.0             |      | 0.6   |      |       |
|  | 10              |      | 0.9   |      |       |
|  | 20              |      | 1.8   |      |       |
|  | 30              |      | 2.4   |      |       |
| Isolation Between Ports, RF1 & RF2           | 0.01            |      | 83    |      | dB    |
|  | 0.1             |      | 80    |      |       |
|  | 1.0             |      | 69    |      |       |
|  | 10              |      | 64    |      |       |
|  | 20              |      | 52    |      |       |
|  | 30              |      | 51    |      |       |
| Isolation Between RFC & RF1/RF2 Ports        | 0.01            |      | 81    |      | dB    |
|  | 0.1             |      | 79    |      |       |
|  | 1.0             |      | 67    |      |       |
|  | 10              |      | 51    |      |       |
|  | 20              |      | 48    |      |       |
|  | 30              |      | 46    |      |       |
| Return Loss - RFC                            | 0.01            |      | 19    |      | dB    |
|  | 0.1             |      | 22    |      |       |
|  | 1.0             |      | 22    |      |       |
|  | 10              |      | 18    |      |       |
|  | 20              |      | 11    |      |       |
|  | 30              |      | 11    |      |       |
| Return Loss - RF1 & RF2 (On & Off State)     | 0.01            |      | 19    |      | dB    |
|  | 0.1             |      | 22    |      |       |
|  | 1.0             |      | 22    |      |       |
|  | 10              |      | 18    |      |       |
|  | 20              |      | 11    |      |       |
|  | 30              |      | 11    |      |       |
| Input Power at P1dB                          | 0.01            |      | +19.8 |      | dBm   |
|  | 0.1             |      | +24.7 |      |       |
|  | 1.0             |      | +26.4 |      |       |
|  | 10              |      | +27.3 |      |       |
|  | 20              |      | +27.8 |      |       |
|  | 30              |      | +25.1 |      |       |
| Input Power at P0.1 dB                       | 0.01            |      | +17.8 |      | dBm   |
|  | 0.1             |      | +21.3 |      |       |
|  | 1.0             |      | +23.6 |      |       |
|  | 10              |      | +25.6 |      |       |
|  | 20              |      | +27.0 |      |       |
|  | 30              |      | +23.9 |      |       |
| Input IP3<br>(P <sub>IN</sub> = +5 dBm/Tone) | 0.01            |      | +46   |      | dBm   |
|  | 0.1             |      | +49   |      |       |
|  | 1.0             |      | +52   |      |       |
|  | 10              |      | +49   |      |       |
|  | 20              |      | +48   |      |       |
|  | 30              |      | +43   |      |       |

1. Tested on Mini-Circuits Die Characterization Test Board. See Figure 3.
2. Bi-directional, refer to S-Parameters for actual performance.
3. All RF-ports must be DC blocked or held at 0 V DC.





MMIC DIE

# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### DC ELECTRICAL SPECIFICATIONS<sup>4</sup>

| Parameter                         | Min. | Typ. | Max. | Units   |
|-----------------------------------|------|------|------|---------|
| Positive Supply Voltage, $V_{DD}$ | +3.3 |      | +3.6 | V       |
| Negative Supply Voltage, $V_{EE}$ | -3.6 |      | -3.3 | V       |
| Positive Supply Current, $I_{DD}$ |      | 2.7  | 2.9  | mA      |
| Negative Supply Current, $I_{EE}$ |      | 1.6  | 1.8  | mA      |
| Control Voltage Low               |      | 0    | +0.8 | V       |
| Control Voltage High              | +1.8 | +2   | +3.6 | V       |
| Control Current Low               |      | 0.01 | 1    | $\mu$ A |
| Control Current High              |      | 5    | 9    | mA      |

4. DC electrical performance was measured on packaged model M3SWA2-34DR+ on its Mini-Circuits Characterization Test Board TB-M3SWA234DRC+.

### SWITCHING SPECIFICATIONS<sup>5</sup>

| Parameter   | Condition   | Min. | Typ. | Max. | Units |
|---|---|------|------|------|-------|
| ON Time, 50% Control to 90% RF output                   | RF $P_{IN}$ at RFC = 0 dBm<br>RF Frequency = 150 MHz<br>Control Frequency = 1 kHz<br>Control High = +2 V<br>Control Low = 0 V |      | 23   |      | ns    |
| OFF Time, 50% Control to 10% RF output                  |   |      | 17   |      | ns    |
| Video Leakage   |   |      | +5.4 |      | mV    |
| Rise Time, 10% to 90% of RF output                      |   |      | 6.9  |      | ns    |
| Fall Time, 90% to 10% of RF output                      |   |      | 7.1  |      | ns    |
| Settling time (50% VCTRL to 0.05 dB of final RF output) |   |      | 29   |      | ns    |

5. Switching specifications were measured on packaged model M3SWA2-34DR+ on its Mini-Circuits Characterization Test Board TB-M3SWA234DRC+.

### TRUTH TABLE

| State of Control Voltage | RFC to RF1 | RFC to RF2 |
|--------------------------|------------|------------|
| Low                      | ON         | OFF        |
| High                     | OFF        | ON         |





MMIC DIE







# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### TYPICAL PERFORMANCE GRAPHS

Temperature = +25° C,  $V_{DD} = +3.3$  V,  $V_{EE} = -3.3$  V



6. RF OUT is defined as either RF1 (ON) or RF2 (ON)  
 7. RF OUT is defined as either RF1 (OFF) or RF2 (OFF)



MMIC DIE







# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### TYPICAL PERFORMANCE GRAPHS

Temperature = +25° C,  $V_{DD} = +3.3$  V,  $V_{EE} = -3.3$  V





MMIC DIE



# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### TYPICAL PERFORMANCE GRAPHS

Temperature = +25° C,  $V_{DD} = +3.3$  V,  $V_{EE} = -3.3$  V





MMIC DIE

# SPDT RF Switch


# M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

## ABSOLUTE MAXIMUM RATINGS<sup>8</sup>

| Parameter  | Ratings                                 |
|--|---|
| Operating Temperature <sup>9</sup>   | -55°C to +105°C                         |
| Storage Temperature (for Die) <sup>10</sup>  | -65°C to +150°C                         |
| Junction Temperature <sup>11</sup>   | +150°C                                  |
| Total Power Dissipation  | 0.43 W                                  |
| Through Path @ +105°C <sup>12,13</sup><br>Input Power at RFC (CW),<br>(V <sub>DD</sub> = +3.5 V, V <sub>EE</sub> = -3.5 V)<br>Input Power at RF1/RF2 (CW), RF Applied to Selected Power<br>(V <sub>DD</sub> = +3.5 V, V <sub>EE</sub> = -3.5 V)<br>Input Power at RF1/RF2 (CW), RF Applied to Unselected Power<br>V <sub>DD</sub> = +3.5 V, V <sub>EE</sub> = -3.5 V | +29 dBm<br>+29 dBm<br>+29 dBm           |
| Hot Switching @ +105°C <sup>12</sup><br>Input Power at RFC (CW), (V <sub>DD</sub> = +3.5 V, V <sub>EE</sub> = -3.5 V)  | +24 dBm @ < 2 GHz<br>+27 dBm @ 2-30 GHz |
| DC Voltage (V <sub>DD</sub> )  | 0 V to +5 V                             |
| DC Voltage (V <sub>EE</sub> )  | -5 V to 0 V                             |

- 8. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.
- 9. Bottom of Die.
- 10. For die shipped in Gel-Pak see ENV-80 (limited by packaging)
- 11. Peak temperature on top of Die.
- 12. Max. Input Power was measured on packaged model M3SWA2-34DR+ on its Mini-Circuits Characterization Test Board TB-M3SWA234DRC+ and validated at +105°C.
- 13. See derating curve at right for power derating over frequency



## THERMAL RESISTANCE

| Parameter   | Ratings |
|---|---------|
| Thermal Resistance (Θ <sub>JC</sub> ) <sup>14</sup> | 363°C/W |

14. Θ<sub>JC</sub> = (Hot Spot Temperature on Die - Temperature at Ground Lead)/Dissipated Power

## ESD RATING<sup>15</sup>

|     | Class | Voltage Range    | Reference Standard          |
|-----|-------|------------------|-----------------------------|
| HBM | 1A    | 250 V to < 500 V | ANSI/ESDA/JEDEC JS-001-2017 |
| CDM | C3    | ≥ 1000 V         | JESD22-C101F                |



ESD HANDLING PRECAUTION: This device is designed to be Class 1A for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

15. Tested in 3x3 mm 16-Lead QFN style package.



MMIC DIE

# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### FUNCTIONAL DIAGRAM




Figure 1. M3SWA2-34DR-D+ Functional Diagram

### PAD DESCRIPTION

| Function   | Pad Number          | Application Description (Refer to Fig 2) |
|--|---------------------|--|
| RF Input Port  | 1                   | RF Input Port.                           |
| RF Output Port 1   | 4                   | RF Output Port 1.                        |
| RF Output Port 2   | 11                  | RF Output Port 2.                        |
| Negative DC Input Port   | 6                   | Negative DC Input Port.                  |
| Switch control DC Input Port   | 7                   | Switch control DC Input Port.            |
| Positive DC Input Port   | 9                   | Positive DC Input Port.                  |
| Connected to die backside through vias. Bond wires to ground are optional. | 2,3,5,8,10,12, & 13 |  |

### DIE OUTLINE: inches [mm], Typical




Figure 2. M3SWA2-34DR-D+ Die Outline

### DIMENSIONS: inches [mm], Typical

|                                |                                 |
|--------------------------------|---------------------------------|
| Die Size                       | 0.0669 x 0.0650 [1.700 x 1.650] |
| Die Thickness                  | 0.0040 [0.100]                  |
| Bond Pad Sizes:                |                                 |
| Pads 1                         | 0.0060 x 0.0040 [0.152 x 0.102] |
| Pad 4 & 11                     | 0.0040 x 0.0060 [0.102 x 0.152] |
| Pads 2 & 13                    | 0.0031 x 0.0035 [0.080 x 0.090] |
| Pads 3, 5, 10 & 12             | 0.0035 x 0.0031 [0.090 x 0.080] |
| Pads 6, 7, 8 & 9               | 0.0031 x 0.0031 [0.080 x 0.080] |
| Plating (Pads & Bottom of Die) | Gold                            |





MMIC DIE

# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

### CHARACTERIZATION AND APPLICATION CIRCUIT




Figure 3. M3SWA2-34DR-D+ Characterization and Application Circuit

#### Electrical Parameters and Conditions

Insertion Loss, Isolation, Return Loss, Input Power at 1dB Compression (P1dB), & Input IP3 tested using PNA-X N5247B microwave network analyzer.

#### Conditions:

1. Insertion Loss, Isolation, & Return Loss:  $P_{IN} = 0$  dBm
2. Input IP3(IIP3): Two tones, spaced 1 MHz apart, +5 dBm/Tone at input

| Component | Value          | Size    | Part Number        | Manufacturer     |
|-----------|----------------|---------|--------------------|------------------|
| C2, C3    | 100 pF         | 0402    | GRM1555C1H101JAO1D | Murata           |
| C1, C4    | 0.1 uF         | 0402    | GRM155R71C104KA88D | Murata           |
| R1, R2    | 11.5 Ω         | 0402    | RP73PF1E11R5BTDF   | TE Connectivity  |
| R3        | 100 Ω          | 0402    | RK73H1ETTP1000F    | KOA              |
| D1, D2    | $V_z = +5.6$ V | SOD-123 | SZMMSZ5232BT1G     | ON Semiconductor |



## ASSEMBLY DIAGRAM





Figure 4. M3SWA2-34DR-D+ Assembly Diagram

- Refer to the table in Figure 3 for more details on the passive components
- Bond wire diameter: 1 mil
- Bond wire lengths from Die Pad to PCB at:
  - RFC &  $V_{CTRL}$  ports:  $24 \pm 2$  mils
  - RF-OUT ports:  $22 \pm 2$  mils
  - $V_{DD}$  &  $V_{EE}$  ports:  $25 \pm 2$  mils
- Typical Gap from Die edge to PCB edge: 3 mils
- PCB thickness and material: 6.6 mil Rogers RO4350B (Thickness: 1 oz copper on each side)

## ASSEMBLY AND HANDLING PROCEDURE

1. Storage  
Die should be stored in a dry nitrogen purged desiccator or equivalent.
2.  ESD Precautions  
MMIC die are susceptible to electrostatic and mechanical damage. Die are supplied in anti-static protected material, which should be opened only in clean room conditions at an appropriately grounded anti-static workstation.
3. Die Handling and Attachment  
Devices require careful handling using tools appropriate for manipulating semiconductor chips. It is recommended to handle the chips along the edges with a custom designed collet. The surface of the chips have exposed air bridges and should not be touched with a vacuum collet, tweezers or fingers. The die mounting surface must be clean and flat. Using conductive silver-filled epoxy, apply sufficient adhesive to meet the required bond line thickness, fillet height and coverage around the total periphery of the device. The recommended epoxy is Ablestik 84-1 LMISR4 or equivalent. Parts should be cured in a nitrogen-filled atmosphere per manufacturer's recommended cure profile.
4. Wire Bonding  
Openings in the surface passivation above the gold bond pads are provided to allow wire bonding to the die. Thermosonic bonding is recommended with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. The suggested interconnect is pure gold, 1 mil diameter wire. Bonds are recommended to be made from the bond pads on the die to the package or substrate. All bond wire length and bond wire height should be kept as short as possible, unless specified by design, to minimize performance degradation due to undesirable series inductance.



MMIC DIE

# SPDT RF Switch

## M3SWA2-34DR-D+

50Ω DC to 30 GHz Absorptive RF Switch with Internal Driver

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD [CLICK HERE](#)

|  |   |                   |           |                                   |                 |  |                 |                           |                 |
|--|---|-------------------|-----------|-----------------------------------|-----------------|--|-----------------|---------------------------|-----------------|
| <b>Performance Data &amp; Graphs</b>           | Data<br>Graphs<br>S-Parameter (S3P Files) Data Set (.zip file)  |                   |           |                                   |                 |  |                 |                           |                 |
| <b>Case Style</b>                              | Die   |                   |           |                                   |                 |  |                 |                           |                 |
| <b>RoHS Status</b>                             | Compliant   |                   |           |                                   |                 |  |                 |                           |                 |
| <b>Die Ordering and Packaging Information</b>  | <table border="0"> <tr> <td>Quantity, Package</td> <td>Model No.</td> </tr> <tr> <td>Gel - Pak: 5, 10, 50, or 100 KGD*</td> <td>M3SWA2-34DR-DG+</td> </tr> <tr> <td>Medium<sup>†</sup>, Partial wafer: KGD* &lt;729</td> <td>M3SWA2-34DR-DP+</td> </tr> <tr> <td>+ Full wafer<sup>†</sup></td> <td>M3SWA2-34DR-DF+</td> </tr> </table> <sup>†</sup> Available upon request contact sales representative. Refer to <a href="#">AN-60-067</a> | Quantity, Package | Model No. | Gel - Pak: 5, 10, 50, or 100 KGD* | M3SWA2-34DR-DG+ | Medium <sup>†</sup> , Partial wafer: KGD* <729 | M3SWA2-34DR-DP+ | + Full wafer <sup>†</sup> | M3SWA2-34DR-DF+ |
| Quantity, Package                              | Model No.   |                   |           |                                   |                 |  |                 |                           |                 |
| Gel - Pak: 5, 10, 50, or 100 KGD*              | M3SWA2-34DR-DG+   |                   |           |                                   |                 |  |                 |                           |                 |
| Medium <sup>†</sup> , Partial wafer: KGD* <729 | M3SWA2-34DR-DP+   |                   |           |                                   |                 |  |                 |                           |                 |
| + Full wafer <sup>†</sup>                      | M3SWA2-34DR-DF+   |                   |           |                                   |                 |  |                 |                           |                 |
| <b>Die Marking</b>                             | JTX_02  |                   |           |                                   |                 |  |                 |                           |                 |
| <b>Environmental Ratings</b>                   | ENV-80  |                   |           |                                   |                 |  |                 |                           |                 |

\* Known Good Die ("KGD") means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a high degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of known good die (KGD) (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on KGD.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Typical Performance Data







Definitions:

| STATE | CONTROL INPUT | RFC TO RF1 | RFC TO RF2 |
|-------|---------------|------------|------------|
| 1     | HIGH          | OFF        | ON         |
| 2     | LOW           | ON         | OFF        |

TEST CONDITIONS: V<sub>DD</sub>= +3.3V, V<sub>EE</sub> = -3.3V @ Temperature = +25°C







| FREQ  | Insertion Loss  |                 | Isolation       |                 |                 |                 | Return Loss |             |             |             |             |             | FREQ  | Input Power at 1dB Comp. |             | Input Power at 0.1dB Comp. |             | FREQ  | Input IP3   |             |
|-------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-------------|-------------|-------------|-------------|-------------|-------------|-------|--------------------------|-------------|----------------------------|-------------|-------|-------------|-------------|
|       | RFC-RF1 State 2 | RFC-RF2 State 1 | RFC-RF1 State 1 | RFC-RF2 State 2 | RF1-RF2 State 2 | RF1-RF2 State 1 | RFC State 2 | RFC State 1 | RF1 State 2 | RF1 State 1 | RF2 State 2 | RF2 State 1 |       | RF1 State 2              | RF2 State 1 | RF1 State 2                | RF2 State 1 |       | RF1 State 2 | RF2 State 1 |
| (GHz) | (dB)            | (dB)            | (dB)            | (dB)            | (dB)            | (dB)            | (dB)        | (dB)        | (dB)        | (dB)        | (dB)        | (dB)        | (MHz) | (dBm)                    | (dBm)       | (dBm)                      | (dBm)       | (MHz) | (dBm)       | (dBm)       |
| 0.01  | 0.5             | 0.5             | 82              | 81              | 83              | 83              | 19.2        | 19.3        | 19.3        | 19.2        | 19.2        | 19.3        | 0.25  | 18.3                     | 18.3        | 15.2                       | 15.0        | 0.25  | 46.6        | 46.6        |
| 0.05  | 0.6             | 0.5             | 82              | 84              | 84              | 83              | 23.5        | 23.5        | 23.8        | 20.3        | 20.4        | 23.7        | 0.5   | 18.3                     | 18.3        | 15.1                       | 15.1        | 0.50  | 46.4        | 46.4        |
| 0.1   | 0.6             | 0.6             | 79              | 79              | 80              | 80              | 23.5        | 23.5        | 23.8        | 20.5        | 20.5        | 23.8        | 0.7   | 18.3                     | 18.3        | 15.2                       | 15.1        | 0.75  | 46.6        | 46.5        |
| 0.3   | 0.6             | 0.6             | 75              | 76              | 77              | 78              | 23.0        | 23.0        | 23.3        | 20.6        | 20.7        | 23.3        | 1     | 18.3                     | 18.3        | 15.3                       | 15.2        | 1     | 46.7        | 46.6        |
| 0.5   | 0.6             | 0.6             | 72              | 74              | 74              | 75              | 22.5        | 22.5        | 23.2        | 20.6        | 20.7        | 23.2        | 10    | 19.8                     | 19.8        | 17.8                       | 17.8        | 10    | 46.3        | 46.3        |
| 0.8   | 0.6             | 0.6             | 69              | 70              | 71              | 72              | 22.1        | 22.1        | 23.4        | 20.6        | 20.6        | 23.4        | 100   | 24.7                     | 24.7        | 21.3                       | 21.3        | 100   | 49.5        | 49.5        |
| 1.0   | 0.6             | 0.6             | 67              | 68              | 69              | 71              | 22.1        | 22.1        | 23.8        | 20.5        | 20.5        | 23.8        | 200   | 25.0                     | 25.0        | 21.8                       | 21.8        | 125   | 50.3        | 50.3        |
| 2.0   | 0.6             | 0.6             | 61              | 63              | 65              | 67              | 23.2        | 22.9        | 27.0        | 20.4        | 20.1        | 27.2        | 400   | 25.5                     | 25.5        | 22.4                       | 22.4        | 150   | 50.5        | 50.4        |
| 3.0   | 0.7             | 0.7             | 59              | 60              | 64              | 66              | 21.3        | 21.5        | 23.3        | 19.4        | 19.4        | 23.6        | 600   | 25.7                     | 25.7        | 22.8                       | 22.8        | 175   | 50.5        | 50.5        |
| 4.0   | 0.7             | 0.7             | 57              | 58              | 64              | 68              | 20.2        | 20.6        | 21.6        | 18.1        | 18.5        | 22.0        | 800   | 26.2                     | 26.2        | 23.1                       | 23.1        | 200   | 50.5        | 50.5        |
| 5.0   | 0.7             | 0.7             | 55              | 57              | 64              | 70              | 23.1        | 23.3        | 25.9        | 17.4        | 17.7        | 26.1        | 1000  | 26.4                     | 26.4        | 23.6                       | 23.6        | 225   | 49.8        | 49.8        |
| 6.0   | 0.7             | 0.7             | 54              | 56              | 66              | 72              | 25.0        | 24.7        | 31.2        | 18.4        | 18.3        | 32.6        | 2000  | 26.7                     | 26.7        | 23.7                       | 23.8        | 250   | 50.6        | 50.6        |
| 7.0   | 0.7             | 0.7             | 54              | 55              | 68              | 76              | 22.7        | 22.6        | 27.4        | 18.5        | 18.2        | 28.7        | 4000  | 26.8                     | 26.8        | 25.7                       | 25.7        | 275   | 50.7        | 50.7        |
| 8.0   | 0.8             | 0.8             | 53              | 54              | 69              | 70              | 22.0        | 22.4        | 25.4        | 15.9        | 16.2        | 26.7        | 6000  | 27.5                     | 27.4        | 26.3                       | 26.3        | 300   | 50.2        | 50.2        |
| 9.0   | 0.8             | 0.8             | 52              | 53              | 68              | 67              | 23.1        | 23.4        | 24.6        | 14.5        | 14.8        | 25.6        | 8000  | 26.8                     | 26.8        | 25.6                       | 25.6        | 325   | 50.3        | 50.3        |
| 10.0  | 0.9             | 0.9             | 51              | 53              | 66              | 64              | 19.1        | 19.2        | 20.3        | 14.8        | 14.9        | 20.4        | 10000 | 27.3                     | 27.3        | 25.5                       | 25.6        | 350   | 49.9        | 49.8        |
| 11.0  | 0.9             | 0.9             | 50              | 52              | 65              | 63              | 17.5        | 17.8        | 19.7        | 15.5        | 16.0        | 19.8        | 15000 | 28.3                     | 28.3        | 27.1                       | 27.1        | 375   | 51.1        | 51.2        |
| 12.0  | 1.0             | 1.0             | 50              | 51              | 63              | 60              | 16.5        | 17.3        | 17.7        | 14.5        | 15.6        | 19.1        | 20000 | 27.8                     | 27.8        | 27.0                       | 27.0        | 400   | 52.1        | 52.1        |
| 13.0  | 1.1             | 1.1             | 49              | 51              | 61              | 58              | 15.1        | 15.6        | 15.0        | 13.3        | 14.0        | 15.9        | 25000 | 27.0                     | 26.9        | 26.0                       | 26.0        | 425   | 51.4        | 51.4        |
| 14.0  | 1.3             | 1.3             | 49              | 51              | 60              | 56              | 13.0        | 13.1        | 13.1        | 12.9        | 12.9        | 13.2        | 30000 | 25.2                     | 25.0        | 24.0                       | 23.9        | 450   | 51.4        | 51.3        |
| 15.0  | 1.5             | 1.5             | 48              | 51              | 57              | 55              | 11.8        | 11.8        | 12.4        | 12.8        | 12.7        | 12.2        |       |                          |             |                            |             | 475   | 51.3        | 51.3        |
| 16.0  | 1.5             | 1.5             | 48              | 50              | 56              | 54              | 12.2        | 12.3        | 12.8        | 12.7        | 13.1        | 13.1        |       |                          |             |                            |             | 500   | 52.0        | 51.9        |
| 17.0  | 1.4             | 1.4             | 48              | 50              | 55              | 54              | 13.7        | 13.8        | 14.2        | 12.9        | 13.6        | 14.6        |       |                          |             |                            |             | 1000  | 51.8        | 51.8        |
| 18.0  | 1.5             | 1.5             | 47              | 49              | 55              | 53              | 14.2        | 13.9        | 14.6        | 13.0        | 13.1        | 14.3        |       |                          |             |                            |             | 2000  | 51.8        | 51.7        |
| 19.0  | 1.7             | 1.7             | 48              | 49              | 54              | 52              | 12.6        | 12.5        | 12.6        | 11.7        | 11.7        | 12.5        |       |                          |             |                            |             | 6000  | 50.2        | 50.3        |
| 20.0  | 1.8             | 1.8             | 48              | 49              | 54              | 52              | 12.1        | 12.0        | 12.3        | 10.2        | 10.6        | 12.5        |       |                          |             |                            |             | 10000 | 49.0        | 49.1        |
| 21.0  | 1.5             | 1.6             | 47              | 48              | 54              | 53              | 14.9        | 14.4        | 17.0        | 10.2        | 10.5        | 16.9        |       |                          |             |                            |             | 15000 | 47.4        | 47.4        |
| 22.0  | 1.4             | 1.5             | 46              | 47              | 55              | 53              | 18.2        | 17.6        | 28.5        | 11.4        | 11.5        | 28.4        |       |                          |             |                            |             | 20000 | 48.3        | 48.2        |
| 23.0  | 1.4             | 1.5             | 46              | 46              | 54              | 53              | 20.5        | 20.1        | 26.6        | 11.9        | 11.9        | 26.9        |       |                          |             |                            |             | 25000 | 50.0        | 49.9        |
| 24.0  | 1.5             | 1.5             | 47              | 47              | 54              | 52              | 23.2        | 21.4        | 29.4        | 10.5        | 11.1        | 30.5        |       |                          |             |                            |             | 30000 | 43.3        | 43.1        |
| 25.0  | 1.6             | 1.6             | 48              | 48              | 55              | 53              | 20.3        | 19.1        | 23.0        | 9.9         | 10.4        | 26.9        |       |                          |             |                            |             |       |             |             |
| 26.0  | 1.8             | 1.7             | 48              | 48              | 55              | 54              | 15.4        | 15.9        | 16.9        | 10.2        | 10.2        | 18.9        |       |                          |             |                            |             |       |             |             |
| 27.0  | 2.0             | 2.0             | 48              | 48              | 55              | 53              | 13.5        | 13.9        | 14.9        | 10.3        | 10.1        | 15.2        |       |                          |             |                            |             |       |             |             |
| 28.0  | 2.2             | 2.2             | 48              | 47              | 54              | 53              | 12.6        | 12.7        | 12.8        | 9.5         | 9.8         | 12.9        |       |                          |             |                            |             |       |             |             |
| 29.0  | 2.4             | 2.4             | 48              | 46              | 54              | 52              | 11.8        | 12.1        | 10.9        | 9.7         | 10.1        | 11.4        |       |                          |             |                            |             |       |             |             |
| 30.0  | 2.4             | 2.4             | 47              | 46              | 53              | 51              | 12.0        | 12.3        | 11.2        | 11.3        | 11.4        | 11.5        |       |                          |             |                            |             |       |             |             |

## Typical Performance Curves





- 6. RF OUT is defined as either RF1 (ON) or RF2 (ON)
- 7. RF OUT is defined as either RF1 (OFF) or RF2 (OFF)

## Typical Performance Curves



## Typical Performance Curves



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition  | Reference/Spec                       |
|--------------------------------|--|--------------------------------------|
| Operating Temperature          | -40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C<br>Ambient Environment | Refer to Individual Model Data Sheet |
| Storage Environment (Die)      | -65° to 150°C  | Individual Model Data Sheet          |
| Storage Environment(Packaging) | -40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)                           |                                      |