



Mini-Circuits

ULTRA LINEAR LOW NOISE

Monolithic Amplifier

PGA-103+

50Ω 0.05 to 4 GHz

THE BIG DEAL

- 5V/3V operation
- High IP3, 45 dBm typ. at 2 GHz, Vd=5V
- Low Noise Figure, 0.6 at 1 GHz; 0.9 dB at 2 GHz
- Gain, 11.0 dB typ. at 2 GHz
- P1dB 22.5 dBm typ. at 2 GHz at Vd=5V
- Protected under US Patent 8,803,612
- May be used as a replacement for RFMD SPF-5189Z^{a,b}



Generic photo used for illustration purposes only

CASE STYLE: DF782

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

PRODUCT OVERVIEW

PGA-103+ (RoHS compliant) is an advanced wideband amplifier fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PGA-103+ has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability. It has repeatable performance from lot to lot and is enclosed in a SOT-89 package for very good thermal performance.

KEY FEATURES

Feature	Advantages
Broad Band: 0.05 to 4.0 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX
Ultra High IP3 Versus DC power Consumption: 45 dBm typical at 2 GHz at +5.0V Supply Voltage and only 97mA	The PGA-103+ provides excellent IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 20 dB above the P 1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"> • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems • Secondary amplifiers in ultra High Dynamic range receivers
Low Noise Figure: 0.6 dB up to 1.0 GHz	A unique feature of the PGA-103+ which separates this design from all competitors is the low noise figure performance in combination with the high dynamic range.

A. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

B. The RFMD SPF-5189Z part number is used for identification and comparison purposes only.

REV. B
ECO-011959
PGA-103+
TH/RS/CP
220218



ULTRA LINEAR LOW NOISE

Monolithic Amplifier

PGA-103+

Mini-Circuits®

ELECTRICAL SPECIFICATIONS⁽¹⁾ AT 25°C, 50Ω, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Vd=5V			Vd=3V Typ.	Units
		Min.	Typ.	Max.		
Frequency Range		0.05		4.0		GHz
Gain	0.05	—	26.5	—	25.9	dB
	0.4	—	22.1	—	21.6	
	1.0	14.7	16.2	18.0	15.8	
	2.0	—	11.0	—	10.6	
	3.0	—	8.1	—	7.7	
	4.0	—	6.2	—	5.9	
Noise Figure	0.05		0.5		0.5	dB
	0.4		0.5		0.5	
	1.0		0.6		0.6	
	2.0		0.9		0.9	
	3.0		1.2		1.2	
	4.0		1.5		1.4	
Input Return Loss	0.05	—	6.7	—	6.1	dB
	0.4	—	11.3	—	10.4	
	1.0	10.0	13.0	—	12.0	
	2.0	—	12.8	—	13.0	
	3.0	—	13.7	—	13.0	
	4.0	—	15.0	—	14.2	
Output Return Loss	0.05	—	14.1	—	13.8	dB
	0.4	—	23.8	—	25.5	
	1.0	10.0	21.8	—	30.6	
	2.0	—	20.6	—	26.4	
	3.0	—	17.2	—	20.8	
	4.0	—	16.0	—	19.2	
Reverse Isolation	1.0		21.2		20.5	dB
Output Power @1 dB compression ⁽²⁾	0.05		20.0		15.4	dBm
	0.4		21.5		18.2	
	1.0		22.5		18.7	
	2.0		22.5		19.3	
	3.0		22.9		20.0	
	4.0		23.2		20.7	
Output IP3	0.05	—	36.7	—	32.4	dBm
	0.4	—	39.0	—	34.1	
	1.0	—	41.9	—	34.5	
	2.0	40.0	44.6	—	35.6	
	3.0	—	44.3	—	35.6	
	4.0	—	45.4	—	35.3	
Device Operating Voltage		4.8	5.0	5.2	3.0	V
Device Operating Current			97	120	60	mA
Device Current Variation vs. Temperature			-178		-54	µA/°C
Device Current Variation vs Voltage			0.014		0.018	mA/mV
Thermal Resistance, junction-to-ground lead			36		36	°C/W

(1) Measured on Mini-Circuits Characterization test board TB-313. See Characterization Test Circuit (Fig. 1)

(2) Current increases at P1dB

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Operating Current at 5.0V	200 mA
Power Dissipation at 5.0V	1W
Input Power (CW)	+21 dBm (50 to 2000 MHz) +26 dBm (2000 to 4000 MHz)
DC Voltage on Pin 3	6V

Permanent damage may occur if any of these limits are exceeded.

Electrical maximum ratings are not intended for continuous normal operation.

Mini-Circuits®




ULTRA LINEAR LOW NOISE

Monolithic Amplifier

PGA-103+

Mini-Circuits®

SIMPLIFIED SCHEMATIC AND PIN DESCRIPTION



Function	Pin Number	Description
RF-IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.

CHARACTERIZATION TEST CIRCUIT




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT tested on Mini-Circuits Characterization test board TB-313)
Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.





ULTRA LINEAR LOW NOISE

Monolithic Amplifier

PGA-103+


Mini-Circuits®

RECOMMENDED APPLICATION CIRCUIT

Cblock=0.001 μ F, Bias-Tee=TCBT-14+, Cbypass=0.1 μ F

SEQ	Manufacturer P/N / Value	Size
A1	PGA-103+	—
C1, C2	.01 uF	0805
C3	0.33 uF	1206
C4	10 uF	1206
C5	330 pF	0603
L1	TCCH-80+	—
L2	620 nH	.115X.110
R2	150 Ohm	0603

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Mini-Circuits®



ULTRA LINEAR LOW NOISE

Monolithic Amplifier

PGA-103+

Mini-Circuits®

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DF782 (SOT 89) Plastic package, exposed paddle lead finish: tin-silver over nickel
Tape & Reel Standard quantities available on reel	F55 7" reels with 20, 50, 100, 200, 500 or 1K devices
Suggested Layout for PCB Design	PL-313
Evaluation Board	TB-678-103+ TB-761-103+ (see Application Note AN-60-064)
Environmental Ratings	ENV08T1

ESD RATING


Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001
 Machine Model (MM): Class M1(25V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

**Attention**

Observe precautions
for handling electrostatic
sensitive devices

MSL TEST FLOW CHART**NOTES**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®

*Typical Performance Data***NOTE: Use PDF Bookmarks to view DATA at required conditions****Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 88.67mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.82	30.76	6.94	13.93	0.90	0.77	37.23	19.36	0.50
100.0	25.98	29.84	8.94	19.87	0.99	0.71	37.63	19.77	0.45
200.0	24.77	28.90	10.32	24.88	1.04	0.70	37.77	20.68	0.41
400.0	22.16	26.72	12.06	24.77	1.09	0.71	39.45	21.41	0.50
500.0	20.94	25.63	12.66	23.77	1.10	0.71	39.77	21.50	0.57
600.0	19.83	24.59	13.06	23.26	1.11	0.71	41.30	21.76	0.59
700.0	18.82	23.63	13.32	23.01	1.11	0.71	40.99	21.74	0.62
800.0	17.89	22.80	13.51	22.57	1.11	0.72	41.82	21.82	0.63
900.0	17.04	21.98	13.62	22.37	1.12	0.72	43.04	22.11	0.67
1000.0	16.27	21.21	13.67	22.31	1.11	0.73	41.72	21.91	0.75
1100.0	15.56	20.51	13.75	22.19	1.11	0.73	42.23	21.97	0.72
1200.0	14.91	19.85	13.70	22.21	1.11	0.73	43.08	22.16	0.81
1300.0	14.30	19.26	13.68	22.18	1.11	0.73	43.63	22.15	0.82
1400.0	13.74	18.69	13.66	22.06	1.11	0.73	43.43	22.22	0.83
1500.0	13.21	18.18	13.64	22.00	1.11	0.73	43.32	22.19	0.87
1600.0	12.72	17.65	13.64	21.85	1.11	0.73	44.26	22.37	0.92
1700.0	12.25	17.21	13.63	21.63	1.11	0.73	43.39	22.47	0.94
1800.0	11.83	16.79	13.61	21.37	1.11	0.73	46.06	22.47	0.98
1900.0	11.42	16.37	13.69	21.10	1.11	0.73	44.49	22.44	0.93
2000.0	11.04	15.96	13.72	20.82	1.10	0.73	44.23	22.48	0.97
2100.0	10.67	15.59	13.75	20.36	1.10	0.73	47.74	22.38	1.00
2200.0	10.33	15.23	13.83	20.06	1.10	0.73	45.10	22.30	1.00
2300.0	9.99	14.92	13.98	19.74	1.10	0.73	45.05	22.35	0.93
2400.0	9.68	14.57	13.93	19.40	1.10	0.73	47.36	22.57	1.00
2500.0	9.40	14.27	14.02	19.05	1.10	0.72	45.43	22.52	1.09
2600.0	9.11	13.97	14.18	18.66	1.09	0.72	45.53	22.65	1.16
2700.0	8.83	13.71	14.28	18.39	1.10	0.72	45.75	22.47	1.24
2800.0	8.58	13.42	14.40	17.93	1.09	0.72	44.81	22.68	1.27
2900.0	8.34	13.17	14.58	17.65	1.09	0.71	47.26	22.77	1.32
3000.0	8.11	12.89	14.64	17.44	1.09	0.71	44.55	22.63	1.07
3200.0	7.69	12.42	14.93	16.79	1.08	0.70	46.89	22.58	1.21
3300.0	7.49	12.17	14.92	16.68	1.08	0.70	48.88	22.96	1.22
3400.0	7.29	11.95	15.05	16.57	1.08	0.69	45.18	22.74	1.25
3500.0	7.11	11.75	15.18	16.22	1.08	0.69	47.33	22.79	1.24
3600.0	6.93	11.56	15.24	16.14	1.08	0.69	45.90	22.85	1.22
3700.0	6.72	11.41	15.49	16.01	1.08	0.69	45.68	22.98	1.33
3800.0	6.57	11.15	15.48	15.98	1.07	0.68	47.02	22.91	1.33
4000.0	6.27	10.79	15.52	15.80	1.07	0.68	48.70	22.93	1.33



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
www.minicircuits.comThe Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 1 of 18

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 84.90mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.78	29.80	7.02	14.04	0.88	0.68	36.68	18.95	0.52
100.0	25.94	29.81	8.90	19.78	0.99	0.72	37.85	19.35	0.45
200.0	24.74	28.91	10.26	24.93	1.04	0.71	37.59	20.37	0.45
400.0	22.14	26.72	12.01	25.22	1.09	0.71	38.95	21.19	0.49
500.0	20.91	25.61	12.66	24.27	1.10	0.71	39.11	21.29	0.48
600.0	19.81	24.56	13.00	23.72	1.10	0.71	40.04	21.54	0.59
700.0	18.80	23.57	13.27	23.42	1.11	0.71	40.59	21.55	0.66
800.0	17.87	22.74	13.44	23.07	1.11	0.72	41.76	21.62	0.61
900.0	17.03	21.93	13.51	22.83	1.11	0.72	42.59	21.88	0.67
1000.0	16.25	21.17	13.62	22.73	1.11	0.72	41.50	21.72	0.73
1100.0	15.55	20.47	13.68	22.71	1.11	0.73	42.03	21.79	0.74
1200.0	14.89	19.82	13.68	22.60	1.11	0.73	42.97	21.96	0.75
1300.0	14.28	19.21	13.64	22.61	1.11	0.73	43.35	21.96	0.81
1400.0	13.72	18.66	13.60	22.50	1.11	0.73	43.32	22.03	0.84
1500.0	13.20	18.13	13.60	22.43	1.11	0.73	43.01	22.02	0.89
1600.0	12.70	17.65	13.61	22.28	1.11	0.73	42.48	22.19	0.90
1700.0	12.23	17.18	13.58	22.05	1.11	0.73	43.15	22.29	0.87
1800.0	11.81	16.73	13.58	21.78	1.11	0.73	43.52	22.27	0.94
1900.0	11.40	16.31	13.64	21.47	1.10	0.73	43.27	22.22	0.91
2000.0	11.02	15.91	13.67	21.22	1.10	0.73	44.48	22.30	0.95
2100.0	10.65	15.55	13.73	20.74	1.10	0.73	45.48	22.16	0.99
2200.0	10.31	15.19	13.80	20.40	1.10	0.73	45.48	22.19	0.98
2300.0	9.98	14.87	13.93	20.04	1.10	0.73	44.72	22.21	0.94
2400.0	9.67	14.54	13.90	19.71	1.10	0.73	46.70	22.44	0.99
2500.0	9.38	14.22	14.02	19.34	1.09	0.72	47.58	22.35	1.08
2600.0	9.10	13.94	14.16	18.92	1.09	0.72	46.35	22.48	1.11
2700.0	8.83	13.64	14.20	18.56	1.09	0.72	44.02	22.32	1.24
2800.0	8.57	13.37	14.35	18.19	1.09	0.71	46.20	22.57	1.21
2900.0	8.34	13.10	14.49	17.95	1.09	0.71	46.81	22.58	1.29
3000.0	8.11	12.84	14.53	17.69	1.09	0.71	43.74	22.45	1.03
3200.0	7.67	12.40	14.96	17.09	1.09	0.70	45.62	22.53	1.12
3300.0	7.48	12.14	14.90	16.91	1.08	0.70	47.34	22.73	1.18
3400.0	7.28	11.92	15.03	16.74	1.08	0.69	45.15	22.64	1.14
3500.0	7.09	11.70	15.13	16.43	1.08	0.69	45.50	22.65	1.20
3600.0	6.92	11.51	15.20	16.37	1.07	0.69	44.70	22.78	1.32
3700.0	6.68	11.38	15.48	16.47	1.08	0.69	45.28	22.88	1.36
3800.0	6.56	11.09	15.45	16.21	1.07	0.68	46.08	22.72	1.28
4000.0	6.26	10.77	15.52	16.03	1.07	0.68	43.74	22.72	1.33



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 2 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 92.31mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.84	30.88	6.93	14.02	0.89	0.80	37.17	19.71	0.53
100.0	26.01	29.80	8.98	19.92	0.99	0.71	38.04	20.13	0.46
200.0	24.80	28.89	10.37	24.90	1.04	0.70	38.20	20.95	0.46
400.0	22.18	26.80	12.11	24.50	1.09	0.71	39.58	21.59	0.52
500.0	20.96	25.67	12.72	23.54	1.10	0.71	39.91	21.66	0.53
600.0	19.85	24.67	13.10	22.97	1.11	0.72	41.02	21.93	0.59
700.0	18.84	23.70	13.37	22.66	1.11	0.72	41.29	21.91	0.63
800.0	17.91	22.79	13.54	22.24	1.11	0.72	41.54	21.98	0.66
900.0	17.06	22.01	13.66	22.09	1.12	0.72	42.69	22.28	0.65
1000.0	16.29	21.20	13.71	22.00	1.11	0.72	42.34	22.05	0.74
1100.0	15.58	20.54	13.79	21.88	1.12	0.73	42.69	22.11	0.71
1200.0	14.92	19.89	13.75	21.88	1.11	0.73	43.99	22.30	0.76
1300.0	14.32	19.31	13.72	21.86	1.11	0.73	43.48	22.30	0.84
1400.0	13.75	18.73	13.69	21.74	1.11	0.73	44.03	22.36	0.85
1500.0	13.22	18.21	13.68	21.68	1.11	0.73	44.02	22.31	0.90
1600.0	12.73	17.72	13.69	21.55	1.11	0.73	43.67	22.50	0.89
1700.0	12.27	17.23	13.67	21.30	1.11	0.73	44.15	22.60	0.89
1800.0	11.84	16.80	13.63	21.10	1.11	0.73	45.10	22.60	0.97
1900.0	11.43	16.38	13.72	20.84	1.11	0.73	44.97	22.59	0.94
2000.0	11.05	15.99	13.74	20.54	1.10	0.73	44.16	22.61	0.94
2100.0	10.68	15.63	13.79	20.12	1.10	0.73	46.28	22.51	1.04
2200.0	10.34	15.23	13.87	19.82	1.10	0.73	44.35	22.48	0.94
2300.0	10.00	14.92	14.01	19.51	1.10	0.73	45.68	22.47	0.93
2400.0	9.70	14.60	13.96	19.18	1.10	0.73	46.90	22.69	1.01
2500.0	9.41	14.30	14.07	18.82	1.10	0.72	46.09	22.66	1.08
2600.0	9.12	13.99	14.21	18.46	1.09	0.72	47.79	22.76	1.12
2700.0	8.84	13.73	14.32	18.21	1.10	0.72	45.68	22.50	1.26
2800.0	8.59	13.45	14.42	17.74	1.09	0.72	45.67	22.72	1.31
2900.0	8.35	13.20	14.63	17.46	1.09	0.71	46.70	22.92	1.32
3000.0	8.12	12.93	14.67	17.26	1.09	0.71	44.99	22.75	1.09
3200.0	7.70	12.46	14.96	16.64	1.08	0.70	46.62	22.67	1.31
3300.0	7.50	12.22	14.94	16.53	1.08	0.70	49.11	23.09	1.23
3400.0	7.30	11.99	15.06	16.42	1.08	0.70	45.27	22.82	1.31
3500.0	7.12	11.78	15.18	16.04	1.08	0.69	46.97	22.90	1.17
3600.0	6.94	11.58	15.27	15.98	1.08	0.69	44.74	22.95	1.34
3700.0	6.73	11.44	15.51	15.87	1.08	0.69	46.12	23.10	1.35
3800.0	6.58	11.19	15.49	15.81	1.07	0.68	48.10	23.10	1.33
4000.0	6.28	10.83	15.54	15.63	1.07	0.68	45.86	22.92	1.32



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 3 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 100.15mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	27.07	29.65	7.61	14.48	0.86	0.65	38.95	19.72	0.40
100.0	26.09	29.66	10.12	21.61	0.99	0.68	41.00	20.14	0.33
200.0	24.87	28.74	11.82	37.86	1.05	0.66	40.84	21.57	0.32
400.0	22.30	26.60	13.46	28.08	1.09	0.66	41.60	22.73	0.38
500.0	21.10	25.54	14.12	26.15	1.11	0.67	42.47	22.82	0.42
600.0	20.03	24.48	14.40	25.21	1.11	0.67	43.87	22.97	0.45
700.0	19.04	23.53	14.49	24.35	1.11	0.67	43.61	22.98	0.46
800.0	18.13	22.67	14.63	23.71	1.11	0.68	44.25	23.06	0.46
900.0	17.30	21.86	14.61	23.85	1.11	0.68	43.33	23.17	0.45
1000.0	16.54	21.10	14.53	23.97	1.11	0.68	46.03	23.19	0.55
1100.0	15.85	20.40	14.61	23.89	1.10	0.68	44.09	23.26	0.53
1200.0	15.20	19.74	14.56	23.99	1.10	0.69	44.74	23.36	0.58
1300.0	14.59	19.15	14.33	24.07	1.10	0.69	44.34	23.33	0.58
1400.0	14.05	18.56	14.29	24.11	1.10	0.69	44.83	23.41	0.62
1500.0	13.53	18.05	14.30	24.30	1.10	0.69	45.24	23.48	0.63
1600.0	13.04	17.54	14.17	24.28	1.09	0.69	44.27	23.60	0.66
1700.0	12.58	17.08	14.09	23.99	1.09	0.69	46.71	23.70	0.63
1800.0	12.16	16.60	14.12	23.85	1.09	0.69	44.27	23.63	0.67
1900.0	11.76	16.22	14.16	23.65	1.09	0.69	43.92	23.56	0.65
2000.0	11.38	15.81	14.11	23.09	1.09	0.69	44.05	23.74	0.65
2100.0	11.02	15.45	14.22	22.46	1.08	0.69	43.76	23.51	0.71
2200.0	10.68	15.07	14.33	22.16	1.08	0.68	45.94	23.91	0.66
2300.0	10.36	14.74	14.32	21.75	1.08	0.68	46.62	23.88	0.63
2400.0	10.06	14.40	14.46	21.19	1.08	0.68	45.85	23.98	0.69
2500.0	9.77	14.09	14.62	20.78	1.08	0.67	45.42	23.84	0.74
2600.0	9.48	13.80	14.60	20.25	1.07	0.67	45.20	23.95	0.82
2700.0	9.22	13.50	14.88	19.65	1.07	0.67	44.73	24.00	0.89
2800.0	8.98	13.22	15.10	19.29	1.07	0.66	47.38	24.17	0.94
2900.0	8.74	12.93	14.97	18.92	1.06	0.66	45.70	23.99	1.00
3000.0	8.52	12.68	15.28	18.27	1.06	0.65	47.55	24.07	0.72
3200.0	8.08	12.21	15.41	18.00	1.06	0.65	47.23	24.27	0.83
3300.0	7.89	11.97	15.48	17.67	1.06	0.64	44.93	23.99	0.79
3400.0	7.69	11.75	16.04	17.32	1.06	0.64	45.99	24.24	0.77
3500.0	7.51	11.53	15.71	17.14	1.05	0.64	45.97	24.23	0.86
3600.0	7.35	11.31	15.64	17.07	1.05	0.63	46.85	24.46	0.81
3700.0	7.15	11.12	15.95	17.18	1.05	0.63	45.95	24.38	0.86
3800.0	6.99	10.93	15.77	17.16	1.05	0.63	47.21	24.14	0.87
4000.0	6.69	10.56	16.04	16.92	1.05	0.62	48.99	24.34	0.80



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 4 of 18

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 94.90mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	27.02	29.93	7.51	14.47	0.86	0.70	39.48	19.27	0.39
100.0	26.05	29.64	10.03	21.57	0.99	0.68	40.60	19.68	0.33
200.0	24.83	28.78	11.70	37.45	1.05	0.67	40.34	21.24	0.30
400.0	22.27	26.61	13.36	28.51	1.10	0.67	41.67	22.44	0.36
500.0	21.08	25.50	13.99	26.22	1.10	0.67	41.64	22.54	0.57
600.0	20.00	24.44	14.29	25.42	1.10	0.67	44.01	22.64	0.45
700.0	19.01	23.50	14.39	24.53	1.11	0.67	43.33	22.67	0.47
800.0	18.10	22.60	14.57	23.89	1.11	0.67	43.12	22.74	0.43
900.0	17.27	21.84	14.49	24.12	1.11	0.68	42.34	22.83	0.45
1000.0	16.51	21.06	14.44	24.13	1.10	0.68	44.44	22.88	0.56
1100.0	15.82	20.39	14.52	24.01	1.10	0.69	43.67	22.95	0.51
1200.0	15.17	19.74	14.51	24.07	1.10	0.69	43.33	23.04	0.56
1300.0	14.57	19.12	14.26	24.30	1.10	0.69	44.69	23.00	0.58
1400.0	14.02	18.55	14.21	24.28	1.10	0.69	43.41	23.08	0.58
1500.0	13.50	18.02	14.23	24.46	1.10	0.69	44.37	23.18	0.64
1600.0	13.01	17.54	14.12	24.48	1.10	0.69	43.31	23.28	0.69
1700.0	12.55	17.07	14.02	24.14	1.09	0.69	43.97	23.38	0.60
1800.0	12.13	16.62	14.04	23.98	1.09	0.69	43.59	23.30	0.69
1900.0	11.73	16.19	14.12	23.76	1.09	0.69	44.42	23.25	0.64
2000.0	11.35	15.80	14.02	23.22	1.09	0.69	43.84	23.44	0.67
2100.0	10.99	15.43	14.17	22.54	1.08	0.69	42.66	23.15	0.66
2200.0	10.66	15.04	14.26	22.26	1.08	0.68	43.92	23.61	0.71
2300.0	10.33	14.74	14.28	21.85	1.08	0.68	44.14	23.56	0.65
2400.0	10.03	14.40	14.40	21.29	1.08	0.68	43.73	23.63	0.68
2500.0	9.74	14.09	14.57	20.87	1.08	0.68	44.96	23.50	0.72
2600.0	9.46	13.80	14.55	20.30	1.08	0.68	44.15	23.64	0.80
2700.0	9.20	13.50	14.79	19.72	1.07	0.67	44.41	23.74	0.92
2800.0	8.95	13.21	15.03	19.35	1.07	0.67	46.41	23.88	0.89
2900.0	8.71	12.94	14.93	18.93	1.07	0.66	43.71	23.65	0.95
3000.0	8.49	12.68	15.19	18.32	1.06	0.66	46.52	23.76	0.72
3200.0	8.05	12.22	15.35	18.07	1.06	0.65	44.95	23.94	0.84
3300.0	7.87	11.97	15.41	17.67	1.06	0.65	43.61	23.64	0.78
3400.0	7.67	11.74	15.94	17.42	1.06	0.64	45.15	23.91	0.72
3500.0	7.49	11.53	15.66	17.19	1.05	0.64	45.77	23.94	0.81
3600.0	7.33	11.31	15.60	17.10	1.05	0.63	44.30	24.18	0.88
3700.0	7.12	11.12	15.87	17.27	1.05	0.63	46.11	24.10	0.83
3800.0	6.97	10.91	15.72	17.22	1.05	0.63	45.42	23.86	0.86
4000.0	6.66	10.55	16.00	16.99	1.05	0.62	45.60	24.04	0.78



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 5 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 105.35mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	27.12	29.74	7.54	14.60	0.85	0.67	38.67	20.21	0.43
100.0	26.15	29.67	10.10	21.83	0.99	0.67	39.96	20.61	0.36
200.0	24.92	28.86	11.79	39.59	1.05	0.67	40.92	22.00	0.34
400.0	22.33	26.62	13.46	27.72	1.09	0.66	42.45	23.10	0.38
500.0	21.14	25.55	14.01	25.76	1.10	0.67	42.81	23.20	0.53
600.0	20.05	24.51	14.35	24.83	1.11	0.67	44.76	23.35	0.45
700.0	19.05	23.59	14.46	24.08	1.11	0.68	43.72	23.36	0.49
800.0	18.14	22.69	14.64	23.43	1.11	0.68	44.16	23.43	0.44
900.0	17.31	21.87	14.56	23.60	1.11	0.68	43.39	23.55	0.50
1000.0	16.54	21.08	14.50	23.65	1.10	0.68	44.58	23.57	0.56
1100.0	15.85	20.41	14.58	23.57	1.10	0.69	45.87	23.64	0.52
1200.0	15.19	19.76	14.57	23.55	1.10	0.69	46.62	23.74	0.56
1300.0	14.59	19.15	14.32	23.81	1.10	0.69	46.55	23.70	0.63
1400.0	14.04	18.58	14.26	23.75	1.10	0.69	45.66	23.79	0.63
1500.0	13.52	18.04	14.28	23.90	1.10	0.69	45.19	23.85	0.68
1600.0	13.03	17.55	14.17	23.85	1.09	0.69	44.82	23.98	0.66
1700.0	12.57	17.09	14.08	23.61	1.09	0.69	45.84	24.07	0.68
1800.0	12.15	16.64	14.09	23.49	1.09	0.69	46.99	24.00	0.76
1900.0	11.75	16.23	14.16	23.25	1.09	0.69	48.33	23.93	0.72
2000.0	11.37	15.83	14.10	22.70	1.09	0.69	45.75	24.13	0.70
2100.0	11.01	15.45	14.23	22.09	1.08	0.69	44.65	23.84	0.72
2200.0	10.67	15.08	14.31	21.80	1.08	0.68	49.23	24.15	0.72
2300.0	10.35	14.76	14.33	21.44	1.08	0.69	49.08	24.18	0.69
2400.0	10.04	14.43	14.47	20.93	1.08	0.68	45.09	24.27	0.78
2500.0	9.75	14.11	14.62	20.53	1.08	0.68	46.93	24.15	0.78
2600.0	9.47	13.81	14.61	19.98	1.07	0.68	46.31	24.27	0.84
2700.0	9.21	13.53	14.84	19.40	1.07	0.67	45.86	24.27	0.92
2800.0	8.96	13.23	15.09	19.10	1.07	0.67	48.67	24.44	0.92
2900.0	8.72	12.98	14.99	18.68	1.07	0.67	47.07	24.30	0.93
3000.0	8.50	12.70	15.25	18.07	1.06	0.66	49.68	24.33	0.79
3200.0	8.06	12.25	15.40	17.83	1.06	0.65	48.43	24.49	0.93
3300.0	7.88	12.00	15.46	17.44	1.06	0.65	45.79	24.29	0.88
3400.0	7.67	11.81	16.15	17.17	1.06	0.64	47.69	24.49	0.85
3500.0	7.50	11.57	15.73	16.92	1.05	0.64	47.28	24.49	0.87
3600.0	7.33	11.34	15.63	16.90	1.05	0.63	48.13	24.68	0.89
3700.0	7.13	11.15	15.94	17.03	1.05	0.63	47.15	24.63	0.97
3800.0	6.98	10.94	15.73	16.94	1.05	0.63	46.59	24.39	0.93
4000.0	6.66	10.59	16.09	16.77	1.05	0.62	50.66	24.61	0.87



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 6 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 77.70mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
50.0	26.35	29.79	6.24	12.60	0.87	0.71	35.39	18.06	0.64
100.0	25.64	29.67	7.77	16.11	0.98	0.73	35.60	18.57	0.58
200.0	24.49	28.78	8.97	18.56	1.02	0.73	35.66	19.01	0.54
400.0	21.92	26.59	10.80	19.79	1.06	0.74	37.00	19.48	0.66
500.0	20.69	25.54	11.39	19.99	1.08	0.74	37.12	19.59	0.69
600.0	19.59	24.57	11.83	20.07	1.09	0.75	38.08	19.90	0.74
700.0	18.58	23.68	12.27	20.25	1.11	0.75	38.33	19.86	0.77
800.0	17.64	22.81	12.55	20.15	1.11	0.76	38.96	19.94	0.77
900.0	16.78	22.01	12.70	19.77	1.11	0.76	39.63	20.26	0.85
1000.0	16.02	21.27	12.91	19.60	1.12	0.76	38.68	19.97	0.91
1100.0	15.31	20.60	12.99	19.81	1.12	0.76	39.51	20.03	0.90
1200.0	14.65	19.97	12.99	19.84	1.12	0.76	40.02	20.25	0.95
1300.0	14.04	19.34	13.16	19.58	1.12	0.76	40.49	20.26	0.97
1400.0	13.47	18.84	13.17	19.42	1.12	0.77	40.08	20.31	1.04
1500.0	12.94	18.31	13.08	19.46	1.12	0.77	40.43	20.23	1.10
1600.0	12.45	17.81	13.20	19.41	1.12	0.77	40.43	20.41	1.13
1700.0	11.98	17.34	13.26	19.27	1.12	0.77	40.79	20.55	1.12
1800.0	11.55	16.91	13.22	19.00	1.12	0.77	41.42	20.61	1.21
1900.0	11.14	16.49	13.37	18.63	1.12	0.76	42.22	20.63	1.14
2000.0	10.76	16.08	13.48	18.55	1.12	0.76	41.57	20.56	1.20
2100.0	10.39	15.76	13.39	18.45	1.12	0.77	42.81	20.64	1.25
2200.0	10.04	15.38	13.48	18.16	1.12	0.76	41.39	20.48	1.23
2300.0	9.70	15.07	13.75	17.84	1.12	0.76	41.89	20.48	1.21
2400.0	9.39	14.75	13.53	17.79	1.12	0.76	41.82	20.76	1.30
2500.0	9.10	14.42	13.49	17.62	1.11	0.76	42.42	20.74	1.37
2600.0	8.81	14.14	13.81	17.38	1.11	0.76	43.16	20.84	1.47
2700.0	8.53	13.87	13.88	17.23	1.11	0.76	42.86	20.50	1.61
2800.0	8.27	13.61	13.80	16.87	1.11	0.76	42.07	20.81	1.57
2900.0	8.04	13.35	14.05	16.70	1.11	0.75	43.25	21.08	1.68
3000.0	7.80	13.08	14.04	16.78	1.11	0.75	42.56	20.84	1.40
3200.0	7.37	12.63	14.34	16.10	1.11	0.74	41.81	20.72	1.57
3300.0	7.17	12.39	14.41	16.02	1.10	0.74	43.42	21.38	1.58
3400.0	6.97	12.15	14.31	16.11	1.10	0.74	41.81	20.98	1.54
3500.0	6.79	11.94	14.43	15.82	1.10	0.73	42.00	20.97	1.58
3600.0	6.59	11.78	14.75	15.68	1.10	0.73	42.20	21.05	1.59
3700.0	6.38	11.65	14.86	15.50	1.11	0.74	42.73	21.20	1.68
3800.0	6.24	11.38	14.88	15.29	1.10	0.73	43.24	21.31	1.61
4000.0	5.93	11.01	14.91	15.33	1.09	0.72	42.41	21.18	1.67



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 7 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 75.14mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.32	29.81	6.28	12.58	0.88	0.71	35.01	17.77	0.64
100.0	25.61	29.68	7.74	16.13	0.97	0.73	35.31	18.27	0.55
200.0	24.46	28.94	8.92	18.63	1.02	0.75	35.55	18.78	0.54
400.0	21.90	26.52	10.76	20.06	1.06	0.73	36.81	19.29	0.62
500.0	20.67	25.53	11.34	20.28	1.08	0.74	37.18	19.42	0.64
600.0	19.57	24.55	11.79	20.44	1.09	0.75	38.00	19.73	0.73
700.0	18.56	23.56	12.21	20.64	1.10	0.75	38.08	19.71	0.76
800.0	17.61	22.73	12.49	20.58	1.11	0.75	38.80	19.78	0.77
900.0	16.77	21.93	12.64	20.18	1.11	0.76	39.74	20.10	0.82
1000.0	16.00	21.24	12.86	20.08	1.12	0.76	38.40	19.84	0.89
1100.0	15.29	20.50	12.95	20.23	1.12	0.76	39.18	19.90	0.90
1200.0	14.63	19.88	12.94	20.26	1.12	0.76	39.98	20.10	0.95
1300.0	14.02	19.30	13.12	20.00	1.12	0.76	40.09	20.14	1.00
1400.0	13.45	18.74	13.12	19.88	1.12	0.76	40.29	20.20	1.07
1500.0	12.92	18.25	13.04	19.90	1.12	0.77	40.16	20.10	1.09
1600.0	12.43	17.76	13.13	19.83	1.12	0.77	40.64	20.33	1.14
1700.0	11.97	17.31	13.22	19.73	1.12	0.77	40.44	20.44	1.15
1800.0	11.53	16.84	13.17	19.41	1.12	0.76	41.29	20.47	1.21
1900.0	11.13	16.46	13.33	19.04	1.12	0.76	41.45	20.51	1.13
2000.0	10.75	16.06	13.44	18.94	1.12	0.76	41.28	20.48	1.16
2100.0	10.37	15.71	13.36	18.85	1.12	0.76	42.53	20.58	1.28
2200.0	10.03	15.31	13.43	18.50	1.11	0.76	41.16	20.36	1.26
2300.0	9.69	15.02	13.72	18.20	1.12	0.76	41.91	20.43	1.19
2400.0	9.38	14.66	13.49	18.13	1.11	0.76	42.08	20.71	1.35
2500.0	9.09	14.37	13.47	17.96	1.11	0.76	42.13	20.60	1.36
2600.0	8.80	14.08	13.77	17.69	1.11	0.76	42.56	20.67	1.43
2700.0	8.52	13.81	13.83	17.54	1.11	0.76	41.66	20.53	1.58
2800.0	8.26	13.53	13.79	17.19	1.11	0.75	41.45	20.75	1.60
2900.0	8.02	13.29	14.01	16.99	1.11	0.75	43.79	20.97	1.64
3000.0	7.78	13.04	14.02	17.09	1.11	0.75	41.87	20.80	1.39
3200.0	7.36	12.57	14.35	16.38	1.11	0.74	42.00	20.70	1.62
3300.0	7.15	12.34	14.38	16.27	1.10	0.74	42.77	21.33	1.56
3400.0	6.95	12.09	14.30	16.38	1.10	0.74	41.43	20.86	1.65
3500.0	6.77	11.88	14.42	16.10	1.10	0.73	42.08	20.88	1.61
3600.0	6.57	11.72	14.75	15.93	1.10	0.73	41.39	21.03	1.62
3700.0	6.36	11.57	14.85	15.75	1.11	0.73	41.87	21.19	1.70
3800.0	6.22	11.32	14.89	15.55	1.10	0.72	42.15	21.19	1.73
4000.0	5.91	10.97	14.93	15.57	1.09	0.72	42.11	21.04	1.64



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 8 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 80.20mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.38	30.44	6.24	12.58	0.89	0.78	35.40	18.32	0.62
100.0	25.67	29.76	7.82	16.10	0.98	0.73	35.71	18.85	0.58
200.0	24.51	28.86	9.02	18.45	1.02	0.73	35.86	19.23	0.56
400.0	21.94	26.67	10.84	19.64	1.07	0.74	37.41	19.64	0.63
500.0	20.71	25.66	11.45	19.79	1.09	0.75	37.74	19.74	0.67
600.0	19.60	24.66	11.88	19.84	1.10	0.75	38.35	20.04	0.74
700.0	18.60	23.75	12.32	20.01	1.11	0.76	38.48	20.02	0.78
800.0	17.65	22.83	12.59	19.88	1.11	0.76	38.95	20.08	0.79
900.0	16.80	22.05	12.74	19.51	1.12	0.76	39.90	20.39	0.81
1000.0	16.03	21.31	12.95	19.33	1.12	0.76	38.76	20.10	0.96
1100.0	15.32	20.61	13.03	19.53	1.12	0.76	39.37	20.15	0.94
1200.0	14.66	20.01	13.01	19.54	1.12	0.77	40.34	20.33	0.98
1300.0	14.05	19.43	13.20	19.29	1.12	0.77	40.53	20.37	0.98
1400.0	13.49	18.87	13.21	19.15	1.12	0.77	40.46	20.40	1.07
1500.0	12.95	18.35	13.11	19.19	1.12	0.77	40.69	20.32	1.10
1600.0	12.47	17.84	13.23	19.13	1.12	0.77	40.81	20.49	1.15
1700.0	12.00	17.39	13.30	19.01	1.12	0.77	40.57	20.63	1.15
1800.0	11.56	16.94	13.24	18.72	1.12	0.77	41.15	20.66	1.24
1900.0	11.16	16.52	13.39	18.38	1.12	0.76	41.47	20.70	1.18
2000.0	10.78	16.16	13.50	18.32	1.12	0.76	41.76	20.66	1.23
2100.0	10.40	15.79	13.43	18.21	1.12	0.77	42.46	20.73	1.25
2200.0	10.06	15.42	13.49	17.93	1.12	0.76	41.46	20.52	1.33
2300.0	9.72	15.12	13.78	17.60	1.12	0.76	42.15	20.52	1.17
2400.0	9.41	14.78	13.55	17.58	1.12	0.76	43.10	20.82	1.30
2500.0	9.12	14.47	13.53	17.39	1.11	0.76	42.46	20.81	1.35
2600.0	8.83	14.18	13.84	17.16	1.12	0.76	43.02	20.95	1.46
2700.0	8.55	13.93	13.89	17.02	1.12	0.76	42.41	20.65	1.63
2800.0	8.29	13.64	13.83	16.70	1.11	0.76	42.43	20.90	1.57
2900.0	8.05	13.40	14.06	16.49	1.11	0.75	43.28	21.18	1.63
3000.0	7.81	13.13	14.07	16.56	1.11	0.75	42.07	20.97	1.45
3200.0	7.38	12.67	14.36	15.94	1.11	0.74	42.19	20.84	1.51
3300.0	7.18	12.42	14.42	15.83	1.10	0.74	44.56	21.47	1.55
3400.0	6.98	12.20	14.32	15.91	1.10	0.74	43.09	21.03	1.59
3500.0	6.80	11.99	14.44	15.64	1.10	0.74	42.40	21.09	1.54
3600.0	6.60	11.81	14.75	15.51	1.10	0.73	42.68	21.10	1.66
3700.0	6.39	11.68	14.85	15.34	1.11	0.74	43.18	21.25	1.64
3800.0	6.25	11.41	14.91	15.11	1.10	0.73	44.05	21.39	1.69
4000.0	5.94	11.06	14.91	15.16	1.10	0.72	42.25	21.23	1.71



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 9 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 56.45mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
50.0	26.21	30.04	6.42	13.65	0.88	0.78	32.83	14.82	0.46
100.0	25.41	29.44	8.11	18.53	0.97	0.76	32.85	15.29	0.43
200.0	24.25	28.30	9.36	22.89	1.01	0.73	32.94	16.89	0.42
400.0	21.72	26.07	11.03	27.99	1.05	0.72	34.19	18.23	0.48
500.0	20.52	25.00	11.61	29.27	1.07	0.72	34.30	18.40	0.45
600.0	19.43	23.93	12.00	30.05	1.08	0.71	34.58	18.55	0.53
700.0	18.43	22.99	12.28	30.85	1.08	0.72	34.77	18.61	0.62
800.0	17.51	22.13	12.46	31.20	1.09	0.72	35.15	18.71	0.57
900.0	16.67	21.31	12.58	30.85	1.09	0.72	35.60	18.83	0.60
1000.0	15.90	20.53	12.66	30.99	1.09	0.72	34.79	18.87	0.71
1100.0	15.20	19.87	12.74	31.08	1.10	0.72	35.27	18.94	0.69
1200.0	14.55	19.23	12.75	30.81	1.10	0.72	35.91	19.08	0.74
1300.0	13.94	18.62	12.72	30.90	1.10	0.72	35.70	19.02	0.78
1400.0	13.38	18.05	12.70	30.52	1.09	0.72	35.61	19.10	0.79
1500.0	12.86	17.55	12.72	30.16	1.10	0.72	35.71	19.18	0.83
1600.0	12.37	17.05	12.71	29.75	1.09	0.72	35.88	19.32	0.86
1700.0	11.90	16.59	12.72	29.32	1.09	0.72	36.13	19.46	0.87
1800.0	11.48	16.17	12.73	28.45	1.09	0.72	36.22	19.39	0.89
1900.0	11.07	15.74	12.79	27.71	1.09	0.72	36.43	19.37	0.87
2000.0	10.70	15.34	12.82	27.00	1.09	0.72	36.20	19.51	0.93
2100.0	10.33	14.99	12.89	26.17	1.09	0.72	35.55	19.15	0.91
2200.0	10.00	14.63	12.95	25.51	1.09	0.72	36.65	19.65	0.94
2300.0	9.66	14.30	13.10	24.97	1.09	0.72	36.23	19.60	0.90
2400.0	9.36	13.97	13.10	24.43	1.09	0.71	36.49	19.79	0.94
2500.0	9.08	13.66	13.21	23.75	1.08	0.71	35.95	19.59	1.02
2600.0	8.80	13.38	13.35	23.19	1.08	0.71	36.08	19.77	1.07
2700.0	8.52	13.09	13.46	22.69	1.08	0.71	36.16	19.87	1.19
2800.0	8.28	12.82	13.60	22.01	1.08	0.71	36.19	20.07	1.22
2900.0	8.04	12.58	13.77	21.68	1.08	0.70	35.91	19.77	1.19
3000.0	7.82	12.31	13.80	21.32	1.08	0.70	35.49	19.88	0.95
3200.0	7.39	11.85	14.16	20.55	1.08	0.69	36.12	20.16	1.10
3300.0	7.20	11.60	14.16	20.25	1.07	0.69	35.23	19.85	1.15
3400.0	7.00	11.38	14.29	20.00	1.07	0.69	35.41	20.10	1.05
3500.0	6.82	11.16	14.43	19.59	1.07	0.68	35.20	20.13	1.13
3600.0	6.65	10.98	14.50	19.48	1.07	0.68	36.16	20.51	1.24
3700.0	6.42	10.83	14.72	19.66	1.08	0.68	35.79	20.41	1.18
3800.0	6.29	10.59	14.75	19.29	1.07	0.67	35.00	20.12	1.35
4000.0	5.99	10.24	14.82	19.11	1.07	0.67	35.19	20.38	1.24



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 10 of 18

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 51.08mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.00	29.60	6.21	13.63	0.86	0.78	31.54	13.83	0.45
100.0	25.22	29.27	7.84	18.05	0.96	0.77	31.57	14.30	0.43
200.0	24.07	28.24	9.06	21.99	1.00	0.75	31.49	15.98	0.40
400.0	21.57	25.86	10.69	26.88	1.04	0.72	32.59	17.39	0.50
500.0	20.37	24.74	11.26	28.63	1.06	0.72	32.71	17.56	0.53
600.0	19.28	23.72	11.65	30.06	1.07	0.72	32.83	17.69	0.55
700.0	18.29	22.78	11.92	31.20	1.08	0.72	32.84	17.77	0.59
800.0	17.36	21.91	12.11	32.09	1.08	0.72	33.20	17.85	0.59
900.0	16.53	21.12	12.23	32.24	1.09	0.72	33.48	17.96	0.61
1000.0	15.76	20.37	12.31	32.59	1.09	0.72	32.94	18.03	0.70
1100.0	15.06	19.67	12.39	32.62	1.09	0.72	33.27	18.09	0.71
1200.0	14.41	19.01	12.38	32.32	1.09	0.72	33.87	18.22	0.75
1300.0	13.80	18.43	12.37	32.17	1.09	0.72	33.42	18.19	0.77
1400.0	13.24	17.86	12.36	31.77	1.09	0.72	33.51	18.25	0.80
1500.0	12.72	17.37	12.37	31.24	1.09	0.72	33.59	18.35	0.82
1600.0	12.23	16.87	12.38	30.78	1.09	0.72	33.70	18.47	0.86
1700.0	11.77	16.44	12.39	30.44	1.09	0.72	33.97	18.61	0.85
1800.0	11.34	15.98	12.38	29.60	1.09	0.72	33.88	18.53	0.88
1900.0	10.94	15.57	12.47	28.82	1.09	0.72	34.15	18.54	0.90
2000.0	10.57	15.18	12.50	28.17	1.09	0.72	34.03	18.70	0.91
2100.0	10.20	14.81	12.56	27.36	1.09	0.72	33.38	18.31	0.92
2200.0	9.86	14.46	12.65	26.65	1.09	0.72	34.44	18.83	0.98
2300.0	9.53	14.14	12.78	26.22	1.09	0.72	33.95	18.84	0.89
2400.0	9.23	13.81	12.77	25.61	1.08	0.71	34.06	18.88	0.95
2500.0	8.95	13.49	12.89	24.96	1.08	0.71	33.72	18.81	1.03
2600.0	8.67	13.20	13.04	24.39	1.08	0.71	33.82	18.95	1.09
2700.0	8.39	12.94	13.14	23.93	1.08	0.71	33.91	19.09	1.18
2800.0	8.15	12.66	13.27	23.28	1.08	0.71	34.00	19.26	1.19
2900.0	7.92	12.40	13.46	22.81	1.08	0.70	33.59	19.00	1.22
3000.0	7.69	12.14	13.51	22.51	1.08	0.70	33.35	19.08	0.96
3200.0	7.28	11.65	13.85	21.58	1.07	0.69	33.73	19.50	1.15
3300.0	7.08	11.43	13.83	21.35	1.07	0.69	33.12	19.02	1.06
3400.0	6.89	11.21	13.98	21.11	1.07	0.68	33.32	19.35	1.25
3500.0	6.70	11.00	14.11	20.66	1.07	0.68	33.12	19.37	1.13
3600.0	6.53	10.81	14.17	20.57	1.07	0.68	33.90	19.82	1.17
3700.0	6.33	10.67	14.43	20.53	1.07	0.68	33.50	19.66	1.24
3800.0	6.18	10.42	14.44	20.40	1.07	0.67	32.88	19.33	1.22
4000.0	5.88	10.08	14.50	20.15	1.06	0.67	32.99	19.59	1.21



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 11 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.30V, Id = 61.85mA @ Temperature = 25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.37	30.75	6.46	13.70	0.90	0.83	33.90	15.77	0.48
100.0	25.56	29.59	8.31	18.89	0.97	0.75	34.11	16.19	0.43
200.0	24.39	28.48	9.59	23.56	1.02	0.72	34.13	17.70	0.41
400.0	21.84	26.21	11.30	27.89	1.06	0.71	35.64	18.97	0.48
500.0	20.63	25.12	11.91	28.39	1.08	0.71	35.67	19.12	0.45
600.0	19.55	24.11	12.28	28.58	1.09	0.71	36.13	19.29	0.57
700.0	18.54	23.13	12.56	28.69	1.09	0.71	36.37	19.36	0.63
800.0	17.62	22.29	12.75	28.64	1.10	0.72	36.78	19.43	0.60
900.0	16.78	21.49	12.86	28.53	1.10	0.72	37.71	19.57	0.60
1000.0	16.01	20.72	12.95	28.42	1.10	0.72	36.57	19.60	0.72
1100.0	15.31	20.03	13.00	28.44	1.10	0.72	36.97	19.68	0.68
1200.0	14.65	19.39	13.02	28.19	1.10	0.72	37.93	19.81	0.77
1300.0	14.05	18.79	13.00	28.25	1.10	0.72	37.49	19.77	0.78
1400.0	13.49	18.22	12.98	28.06	1.10	0.72	37.44	19.83	0.81
1500.0	12.96	17.71	12.98	27.82	1.10	0.72	37.68	19.92	0.85
1600.0	12.47	17.19	12.98	27.48	1.10	0.72	38.00	20.04	0.83
1700.0	12.01	16.77	12.97	27.09	1.10	0.73	38.06	20.18	0.86
1800.0	11.58	16.30	12.98	26.54	1.10	0.72	38.46	20.10	0.90
1900.0	11.18	15.90	13.06	25.93	1.10	0.72	38.59	20.07	0.91
2000.0	10.80	15.51	13.08	25.42	1.09	0.72	38.25	20.24	0.90
2100.0	10.43	15.14	13.15	24.65	1.09	0.72	38.03	19.89	0.93
2200.0	10.09	14.78	13.22	24.07	1.09	0.72	38.85	20.39	0.95
2300.0	9.76	14.46	13.35	23.59	1.09	0.72	38.60	20.29	0.88
2400.0	9.46	14.13	13.34	23.07	1.09	0.72	38.38	20.44	0.97
2500.0	9.17	13.81	13.46	22.53	1.09	0.71	38.66	20.33	1.02
2600.0	8.89	13.52	13.61	21.96	1.09	0.71	38.44	20.40	1.09
2700.0	8.63	13.23	13.65	21.44	1.08	0.71	38.76	20.50	1.19
2800.0	8.37	12.97	13.85	20.96	1.08	0.71	38.57	20.71	1.21
2900.0	8.13	12.72	13.95	20.61	1.08	0.71	38.49	20.52	1.26
3000.0	7.91	12.45	14.00	20.30	1.08	0.70	37.88	20.54	1.02
3200.0	7.47	12.00	14.46	19.56	1.08	0.69	38.35	20.83	1.16
3300.0	7.28	11.75	14.40	19.30	1.08	0.69	37.89	20.55	1.10
3400.0	7.09	11.51	14.54	19.09	1.07	0.69	37.96	20.79	1.16
3500.0	6.91	11.31	14.64	18.71	1.07	0.68	37.74	20.84	1.12
3600.0	6.73	11.12	14.72	18.61	1.07	0.68	38.45	21.22	1.17
3700.0	6.50	11.00	14.99	18.78	1.08	0.69	38.34	21.03	1.31
3800.0	6.38	10.74	14.97	18.42	1.07	0.68	37.79	20.74	1.32
4000.0	6.07	10.38	15.07	18.25	1.07	0.67	38.01	20.95	1.14



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 12 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 56.11mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.47	29.23	6.94	13.83	0.84	0.69	33.78	14.85	0.41
100.0	25.56	29.24	9.13	19.90	0.97	0.70	34.63	15.35	0.37
200.0	24.40	28.33	10.66	27.74	1.03	0.69	34.50	17.22	0.33
400.0	21.94	26.25	12.32	31.72	1.08	0.68	36.17	18.75	0.38
500.0	20.79	25.23	12.95	29.30	1.09	0.69	36.10	18.87	0.46
600.0	19.72	24.22	13.33	28.08	1.10	0.69	37.24	18.95	0.42
700.0	18.74	23.27	13.48	26.97	1.10	0.69	37.37	19.02	0.47
800.0	17.85	22.43	13.69	26.32	1.10	0.69	38.51	19.10	0.45
900.0	17.03	21.63	13.70	26.62	1.10	0.70	39.53	19.16	0.47
1000.0	16.27	20.89	13.67	26.54	1.10	0.70	37.67	19.26	0.59
1100.0	15.58	20.20	13.77	26.38	1.10	0.70	38.71	19.32	0.52
1200.0	14.93	19.54	13.76	26.38	1.10	0.70	40.10	19.45	0.54
1300.0	14.34	18.98	13.56	26.69	1.10	0.71	39.73	19.38	0.59
1400.0	13.79	18.41	13.55	26.54	1.10	0.70	39.92	19.45	0.59
1500.0	13.27	17.89	13.55	26.55	1.10	0.71	39.42	19.56	0.64
1600.0	12.79	17.38	13.46	26.57	1.09	0.71	40.21	19.67	0.65
1700.0	12.33	16.94	13.40	26.15	1.09	0.71	40.78	19.81	0.65
1800.0	11.91	16.48	13.42	25.80	1.09	0.70	41.02	19.71	0.69
1900.0	11.51	16.08	13.49	25.40	1.09	0.71	41.18	19.71	0.62
2000.0	11.13	15.67	13.42	24.79	1.09	0.70	40.87	19.89	0.72
2100.0	10.77	15.29	13.55	23.94	1.09	0.70	40.51	19.43	0.67
2200.0	10.44	14.93	13.66	23.52	1.08	0.70	40.59	20.05	0.68
2300.0	10.11	14.60	13.67	23.07	1.08	0.70	40.33	20.00	0.63
2400.0	9.82	14.28	13.79	22.41	1.08	0.70	41.27	20.07	0.69
2500.0	9.53	13.95	13.94	21.84	1.08	0.69	40.96	19.94	0.71
2600.0	9.25	13.66	13.95	21.34	1.08	0.69	40.71	20.09	0.79
2700.0	8.99	13.39	14.18	20.65	1.08	0.69	40.44	20.26	0.86
2800.0	8.74	13.09	14.38	20.23	1.07	0.68	41.03	20.51	0.87
2900.0	8.51	12.82	14.32	19.76	1.07	0.68	40.02	20.07	0.93
3000.0	8.29	12.55	14.56	19.14	1.06	0.67	39.45	20.33	0.65
3200.0	7.85	12.09	14.76	18.85	1.06	0.67	40.23	20.69	0.82
3300.0	7.67	11.85	14.82	18.47	1.06	0.66	38.57	20.03	0.75
3400.0	7.46	11.65	15.39	18.13	1.06	0.66	38.94	20.58	0.77
3500.0	7.29	11.41	15.06	17.87	1.06	0.65	38.56	20.57	0.82
3600.0	7.13	11.20	15.01	17.85	1.05	0.65	40.30	21.04	0.70
3700.0	6.93	10.99	15.28	17.96	1.06	0.65	39.58	20.78	0.76
3800.0	6.78	10.80	15.15	17.84	1.05	0.64	37.65	20.39	0.89
4000.0	6.47	10.44	15.46	17.69	1.05	0.64	37.75	20.82	0.80



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 13 of 18

*Typical Performance Data***Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 47.98mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.15	29.71	6.59	13.16	0.85	0.78	32.44	13.72	0.40
100.0	25.25	28.94	8.81	18.84	0.97	0.71	33.11	14.23	0.35
200.0	24.15	28.09	10.32	24.83	1.03	0.69	33.01	16.18	0.32
400.0	21.79	26.20	12.01	28.20	1.08	0.70	34.86	17.75	0.35
500.0	20.67	25.17	12.71	27.04	1.09	0.70	34.85	17.87	0.42
600.0	19.63	24.23	13.15	25.89	1.10	0.70	35.99	17.95	0.41
700.0	18.67	23.33	13.32	25.09	1.10	0.70	35.87	18.02	0.45
800.0	17.79	22.51	13.55	24.47	1.11	0.71	36.90	18.10	0.44
900.0	16.98	21.73	13.57	24.78	1.11	0.71	37.77	18.16	0.45
1000.0	16.23	21.00	13.58	24.65	1.11	0.71	36.19	18.28	0.49
1100.0	15.55	20.35	13.69	24.49	1.11	0.71	37.01	18.34	0.49
1200.0	14.91	19.69	13.68	24.49	1.11	0.71	38.25	18.46	0.53
1300.0	14.32	19.11	13.52	24.71	1.11	0.72	37.80	18.40	0.56
1400.0	13.78	18.57	13.49	24.51	1.11	0.72	37.91	18.46	0.57
1500.0	13.26	18.05	13.51	24.61	1.10	0.72	38.03	18.57	0.58
1600.0	12.78	17.54	13.40	24.57	1.10	0.72	38.39	18.67	0.61
1700.0	12.32	17.09	13.34	24.28	1.10	0.72	38.70	18.81	0.62
1800.0	11.91	16.65	13.38	23.97	1.10	0.72	39.11	18.72	0.63
1900.0	11.50	16.23	13.43	23.68	1.10	0.72	38.70	18.74	0.66
2000.0	11.13	15.84	13.36	23.18	1.09	0.72	38.48	18.91	0.61
2100.0	10.77	15.47	13.47	22.51	1.09	0.72	37.70	18.51	0.68
2200.0	10.44	15.08	13.58	22.13	1.09	0.71	38.85	19.14	0.68
2300.0	10.12	14.75	13.60	21.72	1.09	0.71	37.99	19.04	0.59
2400.0	9.82	14.43	13.70	21.15	1.08	0.71	38.25	19.14	0.65
2500.0	9.53	14.12	13.82	20.72	1.08	0.71	37.51	19.01	0.70
2600.0	9.25	13.81	13.86	20.22	1.08	0.70	37.39	19.14	0.75
2700.0	9.00	13.53	14.07	19.65	1.08	0.70	37.70	19.41	0.91
2800.0	8.75	13.24	14.28	19.27	1.08	0.69	37.36	19.48	0.85
2900.0	8.52	12.98	14.22	18.84	1.07	0.69	36.67	19.12	0.87
3000.0	8.30	12.70	14.47	18.26	1.07	0.68	36.53	19.35	0.63
3200.0	7.86	12.24	14.63	17.99	1.07	0.68	36.68	19.81	0.74
3300.0	7.68	12.01	14.67	17.62	1.06	0.67	35.57	19.13	0.73
3400.0	7.49	11.80	15.22	17.26	1.06	0.67	35.75	19.63	0.75
3500.0	7.31	11.55	14.94	17.15	1.06	0.66	35.54	19.61	0.69
3600.0	7.14	11.34	14.85	17.08	1.05	0.66	36.60	20.13	0.72
3700.0	6.95	11.14	15.12	17.19	1.06	0.66	35.97	19.86	0.81
3800.0	6.79	10.94	15.07	17.10	1.05	0.65	34.86	19.57	0.86
4000.0	6.49	10.57	15.30	16.92	1.05	0.65	34.68	19.93	0.68



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 14 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.30V, Id = 63.03mA @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	26.62	29.57	7.01	14.07	0.85	0.71	34.95	15.86	0.34
100.0	25.70	29.36	9.27	20.39	0.98	0.70	35.77	16.37	0.31
200.0	24.53	28.47	10.81	29.11	1.03	0.68	35.86	18.31	0.26
400.0	22.03	26.35	12.47	31.44	1.08	0.68	37.55	19.64	0.32
500.0	20.85	25.32	13.12	28.82	1.10	0.69	37.68	19.73	0.48
600.0	19.78	24.28	13.45	27.68	1.10	0.69	38.81	19.79	0.46
700.0	18.80	23.38	13.60	26.65	1.10	0.69	38.94	19.84	0.46
800.0	17.90	22.46	13.79	26.01	1.10	0.69	40.13	19.91	0.43
900.0	17.07	21.68	13.79	26.18	1.10	0.70	40.65	19.97	0.50
1000.0	16.31	20.95	13.78	26.13	1.10	0.70	39.22	20.07	0.56
1100.0	15.62	20.24	13.86	26.04	1.10	0.70	39.80	20.14	0.55
1200.0	14.97	19.58	13.86	25.96	1.10	0.70	41.31	20.24	0.59
1300.0	14.37	18.99	13.68	26.30	1.10	0.70	41.52	20.19	0.61
1400.0	13.82	18.43	13.63	26.09	1.10	0.70	41.41	20.25	0.62
1500.0	13.30	17.91	13.65	26.26	1.10	0.70	41.92	20.35	0.65
1600.0	12.81	17.41	13.55	26.22	1.10	0.70	42.19	20.46	0.67
1700.0	12.35	16.96	13.50	25.78	1.10	0.71	41.91	20.59	0.71
1800.0	11.94	16.51	13.52	25.42	1.09	0.70	42.23	20.48	0.70
1900.0	11.53	16.06	13.60	25.15	1.09	0.70	42.36	20.50	0.71
2000.0	11.16	15.70	13.52	24.55	1.09	0.70	42.82	20.68	0.66
2100.0	10.80	15.32	13.64	23.67	1.09	0.70	43.96	20.27	0.66
2200.0	10.46	14.94	13.76	23.23	1.08	0.70	44.25	20.90	0.65
2300.0	10.13	14.62	13.78	22.86	1.08	0.70	43.30	20.86	0.64
2400.0	9.83	14.29	13.88	22.17	1.08	0.69	45.98	20.92	0.72
2500.0	9.55	13.97	14.05	21.70	1.08	0.69	45.52	20.74	0.83
2600.0	9.27	13.67	14.05	21.14	1.08	0.69	47.43	20.88	0.80
2700.0	9.01	13.39	14.27	20.53	1.08	0.68	44.07	21.06	1.23
2800.0	8.76	13.10	14.47	20.07	1.07	0.68	45.83	21.27	1.19
2900.0	8.53	12.84	14.41	19.64	1.07	0.68	46.14	20.84	0.92
3000.0	8.30	12.56	14.66	19.06	1.07	0.67	44.34	21.07	0.67
3200.0	7.86	12.11	14.88	18.72	1.07	0.67	45.61	21.44	0.90
3300.0	7.68	11.86	14.89	18.31	1.06	0.66	46.24	20.84	0.78
3400.0	7.48	11.64	15.36	18.02	1.06	0.65	45.28	21.35	0.90
3500.0	7.30	11.43	15.17	17.81	1.06	0.65	44.15	21.31	0.82
3600.0	7.14	11.21	15.11	17.71	1.05	0.65	46.34	21.80	0.82
3700.0	6.94	11.03	15.38	17.91	1.06	0.65	45.70	21.51	0.85
3800.0	6.79	10.82	15.26	17.76	1.05	0.64	44.95	21.19	0.89
4000.0	6.48	10.46	15.54	17.57	1.05	0.64	44.19	21.54	0.83



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 15 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 51.36mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
50.0	25.74	29.50	5.65	12.43	0.86	0.77	31.93	14.41	0.59
100.0	25.06	29.34	7.00	15.56	0.95	0.78	31.81	14.82	0.53
200.0	23.95	28.30	8.11	18.10	0.98	0.78	31.75	15.94	0.51
400.0	21.46	25.86	9.87	20.88	1.02	0.75	33.05	16.94	0.63
500.0	20.25	24.71	10.43	22.25	1.04	0.75	33.05	17.08	0.62
600.0	19.16	23.75	10.88	23.31	1.05	0.75	33.55	17.38	0.75
700.0	18.16	22.82	11.30	24.04	1.07	0.75	33.60	17.45	0.74
800.0	17.22	21.97	11.57	24.49	1.08	0.75	34.16	17.52	0.75
900.0	16.38	21.20	11.74	24.67	1.08	0.75	34.68	17.83	0.81
1000.0	15.62	20.50	11.94	24.91	1.09	0.75	33.72	17.70	0.91
1100.0	14.91	19.81	12.05	25.41	1.09	0.75	34.23	17.86	0.89
1200.0	14.26	19.18	12.06	25.52	1.09	0.75	34.97	18.00	0.98
1300.0	13.65	18.60	12.21	25.15	1.10	0.75	34.87	18.03	0.98
1400.0	13.09	18.05	12.24	25.20	1.10	0.75	34.82	18.12	1.00
1500.0	12.56	17.53	12.18	25.52	1.10	0.75	34.85	18.13	1.07
1600.0	12.07	17.04	12.29	25.33	1.10	0.75	35.08	18.36	1.12
1700.0	11.61	16.61	12.38	24.96	1.10	0.75	35.36	18.47	1.07
1800.0	11.17	16.17	12.34	24.48	1.10	0.75	35.75	18.43	1.19
1900.0	10.78	15.75	12.49	23.98	1.10	0.75	35.65	18.44	1.14
2000.0	10.40	15.37	12.59	23.73	1.10	0.75	35.65	18.54	1.17
2100.0	10.02	15.02	12.55	23.57	1.10	0.75	35.31	18.36	1.16
2200.0	9.68	14.64	12.64	23.05	1.10	0.75	35.96	18.58	1.19
2300.0	9.35	14.36	12.90	22.62	1.10	0.75	35.72	18.58	1.18
2400.0	9.04	14.00	12.73	22.52	1.10	0.75	36.00	18.82	1.29
2500.0	8.76	13.71	12.73	22.34	1.10	0.75	35.80	18.71	1.28
2600.0	8.47	13.44	13.00	21.90	1.10	0.75	35.77	18.85	1.37
2700.0	8.19	13.15	13.10	21.52	1.10	0.74	35.96	18.84	1.56
2800.0	7.94	12.90	13.09	21.17	1.10	0.74	35.73	19.02	1.53
2900.0	7.71	12.63	13.31	20.94	1.10	0.74	35.98	18.95	1.58
3000.0	7.47	12.38	13.33	21.01	1.10	0.74	35.37	18.94	1.30
3200.0	7.05	11.94	13.67	20.06	1.10	0.73	35.76	19.01	1.58
3300.0	6.85	11.69	13.73	19.82	1.09	0.73	35.37	19.06	1.48
3400.0	6.65	11.46	13.67	19.93	1.09	0.73	35.32	19.09	1.54
3500.0	6.47	11.25	13.80	19.52	1.09	0.72	35.22	19.08	1.53
3600.0	6.28	11.10	14.12	19.28	1.09	0.72	35.72	19.54	1.52
3700.0	6.07	10.94	14.21	19.18	1.10	0.72	35.51	19.46	1.65
3800.0	5.94	10.69	14.27	18.85	1.09	0.71	35.13	19.24	1.67
4000.0	5.63	10.37	14.34	18.87	1.09	0.71	35.36	19.46	1.64



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-103+

6/1/2012

Page 16 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id= 46.68mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	25.53	30.40	5.41	12.35	0.88	0.88	30.80	13.43	0.57
100.0	24.86	29.28	6.79	15.40	0.95	0.80	30.53	13.91	0.56
200.0	23.76	28.06	7.86	17.82	0.97	0.79	30.51	15.13	0.53
400.0	21.28	25.52	9.59	20.62	1.00	0.75	31.65	16.24	0.66
500.0	20.08	24.46	10.12	22.17	1.02	0.75	31.65	16.40	0.63
600.0	18.98	23.47	10.56	23.40	1.04	0.75	32.00	16.70	0.71
700.0	17.99	22.58	10.98	24.07	1.05	0.75	31.85	16.76	0.77
800.0	17.05	21.74	11.22	24.65	1.07	0.75	32.41	16.87	0.78
900.0	16.21	20.97	11.40	25.08	1.07	0.75	32.81	17.12	0.80
1000.0	15.45	20.22	11.59	25.60	1.08	0.75	32.05	17.04	0.90
1100.0	14.75	19.54	11.69	26.09	1.08	0.75	32.57	17.17	0.91
1200.0	14.09	18.93	11.71	26.20	1.09	0.75	33.10	17.33	0.94
1300.0	13.49	18.37	11.86	25.93	1.09	0.75	32.85	17.35	0.99
1400.0	12.93	17.79	11.88	26.07	1.09	0.75	32.96	17.43	1.03
1500.0	12.40	17.28	11.84	26.40	1.09	0.75	33.14	17.44	1.07
1600.0	11.91	16.82	11.93	26.30	1.09	0.75	33.25	17.66	1.09
1700.0	11.45	16.35	12.02	25.92	1.10	0.75	33.40	17.77	1.08
1800.0	11.02	15.92	11.99	25.52	1.09	0.75	33.61	17.77	1.14
1900.0	10.62	15.52	12.15	25.15	1.09	0.75	33.61	17.76	1.13
2000.0	10.24	15.13	12.25	24.82	1.10	0.75	33.57	17.87	1.15
2100.0	9.87	14.80	12.21	24.60	1.10	0.75	33.19	17.72	1.23
2200.0	9.53	14.42	12.30	24.12	1.09	0.75	34.03	17.91	1.14
2300.0	9.19	14.13	12.56	23.81	1.10	0.75	33.85	17.96	1.19
2400.0	8.89	13.79	12.40	23.70	1.09	0.75	33.93	18.13	1.31
2500.0	8.60	13.49	12.41	23.60	1.09	0.75	33.61	18.03	1.27
2600.0	8.32	13.21	12.67	23.13	1.10	0.74	33.63	18.15	1.40
2700.0	8.05	12.93	12.77	22.66	1.10	0.74	33.76	18.25	1.50
2800.0	7.79	12.67	12.77	22.49	1.09	0.74	33.78	18.39	1.53
2900.0	7.56	12.42	13.00	22.28	1.09	0.74	33.74	18.26	1.53
3000.0	7.33	12.16	13.02	22.30	1.09	0.73	33.36	18.17	1.34
3200.0	6.91	11.72	13.35	21.32	1.09	0.73	33.66	18.56	1.60
3300.0	6.71	11.47	13.42	21.04	1.09	0.72	33.19	18.43	1.52
3400.0	6.51	11.26	13.38	21.15	1.09	0.72	33.35	18.46	1.49
3500.0	6.34	11.05	13.51	20.72	1.09	0.72	33.16	18.57	1.54
3600.0	6.14	10.89	13.82	20.44	1.09	0.72	33.86	18.89	1.60
3700.0	5.94	10.74	13.92	20.44	1.09	0.72	33.60	18.86	1.72
3800.0	5.80	10.49	13.97	20.10	1.09	0.71	33.25	18.68	1.76
4000.0	5.50	10.15	14.07	20.05	1.09	0.71	33.27	18.85	1.65



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR

PGA-103+

6/1/2012

Page 17 of 18

Monolithic Amplifier

PGA-103+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.30V, Id = 56.14mA @ Temperature = 85degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50.0	25.89	30.65	5.80	12.37	0.91	0.83	32.83	15.08	0.61
100.0	25.20	29.56	7.18	15.77	0.96	0.78	32.68	15.54	0.54
200.0	24.09	28.35	8.29	18.33	0.99	0.76	32.71	16.55	0.50
400.0	21.58	26.03	10.08	20.94	1.03	0.75	34.08	17.47	0.61
500.0	20.37	24.95	10.66	22.09	1.05	0.75	34.00	17.59	0.68
600.0	19.27	23.90	11.11	22.92	1.06	0.74	34.85	17.92	0.74
700.0	18.27	23.03	11.55	23.59	1.08	0.75	34.90	17.95	0.76
800.0	17.33	22.14	11.82	23.83	1.08	0.75	35.60	18.06	0.77
900.0	16.49	21.38	11.97	23.72	1.09	0.75	36.24	18.35	0.79
1000.0	15.73	20.62	12.18	23.82	1.09	0.75	34.97	18.21	0.87
1100.0	15.02	20.01	12.29	24.32	1.10	0.75	35.55	18.34	0.89
1200.0	14.36	19.32	12.30	24.39	1.10	0.75	36.55	18.50	0.96
1300.0	13.76	18.74	12.46	24.02	1.10	0.75	36.20	18.53	0.98
1400.0	13.19	18.24	12.48	23.98	1.10	0.76	36.41	18.62	1.00
1500.0	12.66	17.71	12.42	24.19	1.10	0.76	36.55	18.62	1.06
1600.0	12.18	17.21	12.52	24.01	1.10	0.75	36.64	18.86	1.08
1700.0	11.71	16.76	12.60	23.77	1.11	0.76	36.83	18.99	1.07
1800.0	11.28	16.33	12.57	23.32	1.10	0.76	37.14	18.96	1.15
1900.0	10.88	15.91	12.72	22.83	1.10	0.75	37.37	18.92	1.13
2000.0	10.50	15.52	12.83	22.62	1.10	0.75	37.12	19.06	1.18
2100.0	10.12	15.17	12.78	22.43	1.10	0.75	37.10	18.94	1.23
2200.0	9.78	14.82	12.85	22.00	1.10	0.75	37.51	19.08	1.23
2300.0	9.45	14.49	13.13	21.54	1.11	0.75	37.34	19.09	1.14
2400.0	9.14	14.18	12.94	21.48	1.10	0.75	37.98	19.34	1.28
2500.0	8.85	13.87	12.95	21.26	1.10	0.75	37.43	19.23	1.31
2600.0	8.56	13.60	13.23	20.84	1.10	0.75	37.66	19.35	1.43
2700.0	8.29	13.32	13.33	20.58	1.10	0.75	37.38	19.27	1.60
2800.0	8.03	13.04	13.30	20.23	1.10	0.74	37.31	19.55	1.60
2900.0	7.80	12.79	13.51	19.91	1.10	0.74	37.67	19.57	1.55
3000.0	7.56	12.55	13.56	20.01	1.10	0.74	37.00	19.50	1.37
3200.0	7.14	12.08	13.87	19.12	1.10	0.73	37.06	19.62	1.47
3300.0	6.94	11.85	13.93	18.93	1.10	0.73	37.24	19.65	1.51
3400.0	6.74	11.62	13.87	19.04	1.09	0.73	37.10	19.61	1.54
3500.0	6.56	11.41	13.99	18.67	1.09	0.72	36.82	19.67	1.48
3600.0	6.36	11.24	14.33	18.45	1.10	0.72	37.33	19.92	1.58
3700.0	6.15	11.09	14.41	18.27	1.10	0.73	37.23	19.97	1.61
3800.0	6.02	10.85	14.47	18.01	1.09	0.72	37.01	19.84	1.74
4000.0	5.72	10.49	14.51	18.01	1.09	0.71	36.81	19.88	1.62



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com









REV. OR

PGA-103+








6/1/2012

Page 18 of 18









Typical Performance Curves










Typical Performance Curves



Typical Performance Curves



Typical Performance Curves




Case Style


DF

DF782

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	L	M
DF782	.102 (2.59)	.090 (2.29)	.181 (4.60)	.173 (4.39)	.063 (1.60)	.167 (4.24)	.155 (3.94)	.059 (1.50)	.118 (3.00)	.015 (0.38)	.041 (1.04)	.016 (0.41)

CASE #	N	P	Q	WT. GRAM
DF782	.019 (0.48)	.065 (1.65)	.062 (1.57)	.2

Dimensions are in inches (mm). Tolerances: 2 Pl. ±.01; 3Pl. ±.005

Notes:

1. Case material: Plastic.
2. Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin.
All models, (+) suffix. See model Data sheet.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F55

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standard (see note)	20
			50	50
			100	100
			200	200
			500	500
			Standard	1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVIEWS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M123948	NEW RELEASE	08/18/09	MMG	DJ

SUGGESTED MOUNTING CONFIGURATION
FOR DF782 CASE STYLE, "04AM03" PIN CODE



- NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.020" \pm .0015"$; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

CHECKED

APPROVED

MMG

AV

DJ

08/17/09

08/17/09

08/18/09

TOLERANCES ON:

2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$ ANGLES \pm FRACTIONS \pm 

MINI-CIRCUITS®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95





Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 04AM03, DF782, TB-545-1+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-313	OR
FILE: 98PL313	SCALE: 10:1	SHEET: 1	OF 1

Evaluation Board and Circuit



COMPONENT	VALUE
DUT	PGA-103+
C1 (bypass)	0.1 uF(SIZE 0805)
C2-C4 (Note 4)	0.001 uF(SIZE 0402)
BIAS TEE	Mini-Circuits TCBT-14+


Schematic Diagram

NOTES:


1. Vcc voltage: $+5 \pm 0.2V / 3 \pm 0.2V$.
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.020 inch.
4. Capacitor C2-C4 should be free of resonance up to the highest frequency specified.

 Mini-Circuits®

Evaluation Board and Circuit



TB-761-103+



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.
3. ON Semiconductor P/N ESD7L5.0DT5G+ (Optional)

Mini-Circuits®



Environmental Specifications

ENV08T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215