

Ultra Linear Low Noise


Monolithic Amplifier Die

PGA-103-D+

50Ω 0.05 to 4 GHz

The Big Deal

- Ultra High IP3
- Broadband High Dynamic Range



Product Overview

PGA-103-D+ (RoHS compliant) is an advanced wideband amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PGA-103-D+ has good input and output return loss over a broad frequency range without the need for external matching components and has demonstrated excellent reliability.

Key Features

Feature	Advantages
Broad Band: 0.05 to 4.0 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX
Ultra High IP3 Versus DC power Consumption: 42 dBm typical at 2 GHz at +5.0V Supply Voltage and only 97mA	The PGA-103-D+ provides excellent IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 20 dB above the P 1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none">• Driver amplifiers for complex waveform up converter paths• Drivers in linearized transmit systems• Secondary amplifiers in ultra High Dynamic range receivers
Low Noise Figure: 0.6 dB up to 1.0 GHz	A unique feature of the PGA-103-D+ which separates this design from all competitors is the low noise figure performance in combination with the high dynamic range.



Ultra Linear Low Noise Monolithic Amplifier Die

PGA-103-D+

50Ω 0.05 to 4 GHz

Product Features


- 5V/3V operation
- High IP3, 42 dBm typ. at 2 GHz, Vd=5V
- Low Noise Figure, 0.6 at 1 GHz; 0.8 dB at 2 GHz
- Gain, 11.3 dB typ. at 2 GHz
- P1dB 22.3 dBm typ. at 2 GHz at Vd=5V
- Protected under US Patent 8,803,612

Typical Applications

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

General Description

PGA-103-D+ (RoHS compliant) is an advanced wideband amplifier fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PGA-103-D+ has good input and output return loss over a broad frequency range without the need for external matching components.




+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

Simplified Schematic and Pad description



Pad	Description
RF IN	RF input pad. This pad requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	RF output and bias pad. DC voltage is present on this pad; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2
GND	Connections to ground.

Note: 1. Bond Pad material - Gold
2. Bottom of Die - Gold plated

Electrical Specifications¹ at 25°C, 50Ω unless noted

Parameter	Condition (GHz)	Vd=5.0V			Vd=3V	Units
		Min.	Typ.	Max.	Typ.	
Frequency range		0.05		4.0	0.05-4.0	GHz
Gain	0.05		26.7		26.1	dB
	0.4		22.3		21.8	
	1.0		16.5		16.1	
	2.0		11.3		10.8	
	3.0		8.1		7.7	
	4.0		6.1		5.6	
Noise figure	0.05		0.4		0.3	dB
	0.4		0.7		0.7	
	1.0		0.6		0.6	
	2.0		0.8		0.8	
	3.0		1.4		1.4	
	4.0		1.6		1.5	
Input return loss	0.05		6.8		6.1	dB
	0.8		11.5		10.4	
	2.0		14.0		12.8	
	3.0		14.5		13.1	
	4.0		12.1		11.2	
	6.0		11.5		10.7	
Output return loss	0.05		13.8		13.4	dB
	0.8		20.0		21.9	
	2.0		16.8		20.7	
	3.0		16.0		20.1	
	4.0		19.1		22.5	
	6.0		18.6		19.7	
Reverse isolation	2.0		21.4			dB
Output power @ 1dB compression ²	0.05		19.1		14.8	dBm
	0.8		21.1		17.9	
	2.0		21.5		18.8	
	3.0		22.3		19.5	
	4.0		22.2		19.9	
	6.0		22.8		20.5	
Output IP3	0.05		35.8		31.1	dBm
	0.8		38.0		32.6	
	2.0		40.3		33.4	
	3.0		41.6		34.2	
	4.0		42.2		33.1	
	6.0		42.8		32.4	
Device operating voltage			5.0		3.0	V
Device operating current		72	97	120	60	mA
Device current variation vs voltage			0.035		0.018	mA/mV
Thermal resistance, junction-to-ground lead			32		32	°C/W

1. Measured on Mini-Circuits Die Characterization test board. See Characterization Test Circuit (Fig. 1)

2. Current increases at P1dB

Absolute Maximum Ratings³

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Operating Current at 5.0V	200 mA
Power Dissipation at 5.0V	1W
Input Power (CW)	+21 dBm (50 to 2000 MHz) +26 dBm (2000 to 4000 MHz)
DC Voltage on RF-OUT & DC-IN	6V

3. Permanent damage may occur if any of these limits are exceeded.
Electrical maximum ratings are not intended for continuous normal operation.
Measured in industry standard SOT-89 package.



Characterization Test Circuit




Fig 1. Block Diagram of Test Circuit used for characterization. Gain, Return loss, Output power at 1dB compression (P1 dB) , output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pad= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

Recommended Application Circuit




Fig 2a. Simplified




Fig 2b. Unconditionally stable (see note AN-60-064)

SEQ	Manufacturer P/N / Value	Size
A1	PGA-103-D+ in industry standard SOT-89	—
C1, C2	.01 uF	0805
C3	0.33 uF	1206
C4	10 uF	1206
C5	330 pF	0603
L1	TCCH-80+	—
L2	620 nH	.115X.110
R2	150 Ohm	0603

Die Layout




Fig 3. Die Layout

Critical Dimensions

Parameter	Values
Die Thickness, µm	100
Die Width, µm	820
Die Length, µm	731
Bond Pad Size, µm	150 x 75

Bonding Pad Position
(Dimensions in µm, Typical)





Fig 4. Bonding Pad Positions

Monolithic E-PHEMT MMIC Amplifier Die

Assembly and Handling Procedure

1. Storage
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD
MMIC E-PHEMPT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.


Assembly Diagram



Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
RF-IN, RF-OUT + DC-IN	0.6	0.15
GROUND	0.3	0.15

RF Reference Plane - No port extension



Additional Detailed Technical Information <i>additional information is available on our dash board.</i>	
Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
Case Style	Die
Die Ordering and packaging information	Quantity, Package Model No.
	Small, Gel - Pak: 10,50,100 KGD* PGA-103-DG+ Medium†, Partial wafer: KGD*<1975 PGA-103-DP+ Large†, Full Wafer PGA-103-DF+
	†Available upon request contact sales representative
	Refer to AN-60-067
Environmental Ratings	ENV-80

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard SOT-89 package.

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 56mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.25	30.61	6.29	13.66	0.89	0.83	31.22	14.88	0.33
100	25.46	29.55	7.94	18.00	0.97	0.76	31.60	14.91	0.46
200	24.36	28.43	9.07	21.23	1.00	0.74	31.79	16.77	0.49
400	21.89	26.16	10.62	24.05	1.04	0.72	32.65	18.08	0.68
500	20.72	25.06	11.23	24.71	1.05	0.72	32.87	18.19	0.68
600	19.65	24.08	11.72	24.87	1.06	0.72	33.00	18.46	0.69
700	18.67	23.14	12.15	24.91	1.07	0.71	33.15	18.50	0.67
800	17.77	22.28	12.50	24.80	1.08	0.71	33.22	18.57	0.60
900	16.94	21.50	12.81	24.56	1.08	0.71	33.43	18.69	0.58
1000	16.17	20.73	13.10	24.28	1.08	0.71	33.56	18.87	0.60
1100	15.47	20.06	13.33	24.15	1.09	0.71	33.57	18.90	0.61
1200	14.82	19.40	13.55	23.83	1.09	0.71	33.72	18.90	0.63
1300	14.21	18.80	13.73	23.60	1.09	0.70	33.95	18.97	0.65
1400	13.65	18.26	13.86	23.53	1.09	0.71	33.97	19.07	0.67
1500	13.12	17.71	13.95	23.40	1.09	0.70	34.12	19.17	0.69
1600	12.63	17.22	13.99	23.42	1.09	0.70	34.07	19.35	0.71
1700	12.16	16.74	14.01	23.54	1.09	0.70	34.28	19.41	0.73
1800	11.72	16.28	13.96	23.88	1.09	0.70	34.38	19.49	0.74
1900	11.30	15.85	13.90	24.27	1.09	0.70	34.36	19.49	0.75
2000	10.92	15.44	13.79	24.59	1.09	0.70	34.30	19.59	0.77
2100	10.54	15.06	13.67	25.10	1.09	0.70	34.38	19.70	0.78
2200	10.19	14.69	13.53	25.71	1.09	0.70	34.20	19.84	0.81
2300	9.85	14.33	13.36	26.30	1.09	0.70	34.24	19.84	0.85
2400	9.53	13.98	13.20	26.87	1.08	0.70	33.96	19.84	0.90
2500	9.22	13.65	13.03	27.39	1.08	0.70	33.86	19.85	0.97
2600	8.92	13.34	12.88	27.78	1.08	0.70	33.89	19.93	1.04
2700	8.64	13.04	12.71	27.72	1.08	0.70	33.86	19.97	1.13
2800	8.37	12.76	12.60	27.50	1.08	0.70	33.61	20.08	1.19
2900	8.10	12.47	12.49	26.90	1.07	0.70	33.30	20.07	1.22
3000	7.85	12.22	12.43	26.19	1.07	0.70	33.31	20.03	1.24
3200	7.38	11.69	12.36	24.61	1.07	0.69	33.35	20.22	1.21
3300	7.16	11.45	12.34	24.07	1.07	0.69	33.14	20.39	1.21
3400	6.94	11.21	12.37	23.36	1.07	0.69	33.18	20.37	1.23
3500	6.73	10.99	12.42	22.78	1.07	0.68	32.98	20.39	1.26
3600	6.53	10.76	12.51	22.20	1.06	0.68	32.92	20.32	1.30
3700	6.35	10.55	12.60	21.57	1.06	0.68	32.92	20.43	1.35
3800	6.16	10.33	12.73	21.05	1.06	0.67	32.97	20.52	1.38
4000	5.81	9.96	12.95	20.19	1.06	0.66	32.94	20.63	1.47



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 50mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.04	30.66	6.09	13.65	0.89	0.86	30.18	14.88	0.36
100	25.25	29.38	7.68	17.61	0.96	0.78	30.29	14.91	0.49
200	24.16	28.24	8.78	20.55	0.99	0.75	30.53	16.77	0.51
400	21.70	25.89	10.29	23.38	1.02	0.73	30.98	18.08	0.69
500	20.53	24.80	10.88	24.33	1.04	0.72	31.22	18.19	0.69
600	19.47	23.80	11.34	24.94	1.05	0.72	31.43	18.46	0.72
700	18.49	22.87	11.76	25.49	1.06	0.72	31.58	18.50	0.68
800	17.59	22.01	12.09	25.75	1.07	0.71	31.68	18.57	0.62
900	16.76	21.22	12.41	25.88	1.07	0.71	31.81	18.69	0.59
1000	16.00	20.49	12.67	25.98	1.08	0.71	31.92	18.87	0.62
1100	15.29	19.80	12.89	25.98	1.08	0.71	32.00	18.90	0.63
1200	14.64	19.15	13.09	25.86	1.08	0.71	32.10	18.90	0.65
1300	14.04	18.57	13.26	25.78	1.09	0.71	32.18	18.97	0.67
1400	13.48	18.01	13.40	25.87	1.09	0.70	32.29	19.07	0.70
1500	12.95	17.46	13.47	25.81	1.09	0.70	32.45	19.17	0.71
1600	12.46	16.97	13.51	26.03	1.09	0.70	32.56	19.35	0.73
1700	11.99	16.49	13.51	26.17	1.09	0.70	32.67	19.41	0.74
1800	11.55	16.05	13.47	26.70	1.09	0.70	32.70	19.49	0.75
1900	11.14	15.61	13.41	27.17	1.09	0.70	32.78	19.49	0.76
2000	10.75	15.21	13.30	27.56	1.09	0.70	32.79	19.59	0.78
2100	10.38	14.82	13.19	28.19	1.08	0.70	32.81	19.70	0.79
2200	10.02	14.45	13.05	28.77	1.08	0.70	32.77	19.84	0.81
2300	9.68	14.10	12.88	29.08	1.08	0.70	32.68	19.84	0.85
2400	9.36	13.76	12.74	29.28	1.08	0.70	32.56	19.84	0.91
2500	9.05	13.43	12.57	29.14	1.08	0.70	32.56	19.85	0.98
2600	8.76	13.12	12.43	28.61	1.08	0.69	32.46	19.93	1.06
2700	8.48	12.83	12.27	27.84	1.07	0.69	32.40	19.97	1.13
2800	8.20	12.54	12.18	27.01	1.07	0.69	32.30	20.08	1.20
2900	7.94	12.26	12.06	26.06	1.07	0.69	32.22	20.07	1.23
3000	7.69	12.00	12.02	25.16	1.07	0.69	32.15	20.03	1.25
3200	7.22	11.49	11.94	23.61	1.07	0.69	31.95	20.22	1.25
3300	7.00	11.25	11.94	23.07	1.07	0.68	31.94	20.39	1.24
3400	6.78	11.02	11.97	22.42	1.06	0.68	31.86	20.37	1.28
3500	6.58	10.79	12.02	21.97	1.06	0.68	31.81	20.39	1.30
3600	6.38	10.57	12.11	21.46	1.06	0.67	31.77	20.32	1.34
3700	6.19	10.36	12.20	20.95	1.06	0.67	31.79	20.43	1.37
3800	6.01	10.15	12.34	20.59	1.06	0.67	31.75	20.52	1.41
4000	5.66	9.75	12.58	19.93	1.06	0.66	31.71	20.63	1.44



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.30V, Id = 62mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.43	30.18	6.42	13.96	0.88	0.77	32.38	15.50	0.35
100	25.63	29.65	8.16	18.32	0.97	0.75	32.63	16.02	0.48
200	24.52	28.59	9.33	21.71	1.01	0.72	33.19	17.44	0.51
400	22.04	26.34	10.93	24.06	1.05	0.72	34.20	18.61	0.69
500	20.87	25.31	11.54	24.28	1.06	0.72	34.64	18.83	0.69
600	19.80	24.30	12.05	23.95	1.07	0.72	34.96	18.99	0.71
700	18.82	23.38	12.49	23.65	1.08	0.71	35.26	19.16	0.67
800	17.91	22.50	12.84	23.28	1.08	0.71	35.42	19.18	0.60
900	17.08	21.71	13.17	22.92	1.09	0.71	35.68	19.30	0.59
1000	16.32	20.97	13.46	22.52	1.09	0.71	35.84	19.45	0.63
1100	15.61	20.29	13.71	22.27	1.10	0.71	36.03	19.50	0.64
1200	14.95	19.64	13.93	21.93	1.10	0.71	36.19	19.50	0.66
1300	14.35	19.03	14.12	21.73	1.10	0.71	36.37	19.55	0.68
1400	13.78	18.46	14.26	21.55	1.10	0.71	36.56	19.63	0.71
1500	13.25	17.93	14.34	21.41	1.10	0.71	36.70	19.69	0.72
1600	12.76	17.44	14.39	21.44	1.10	0.70	36.73	19.83	0.75
1700	12.29	16.95	14.42	21.45	1.10	0.70	36.77	19.93	0.76
1800	11.85	16.50	14.37	21.73	1.10	0.70	36.95	20.02	0.76
1900	11.44	16.06	14.30	21.98	1.09	0.70	37.05	20.04	0.77
2000	11.05	15.66	14.18	22.28	1.09	0.70	37.00	20.09	0.78
2100	10.67	15.26	14.07	22.67	1.09	0.70	37.02	20.21	0.79
2200	10.31	14.90	13.92	23.21	1.09	0.70	37.18	20.30	0.81
2300	9.98	14.53	13.74	23.74	1.09	0.70	37.24	20.24	0.85
2400	9.66	14.19	13.58	24.26	1.09	0.70	37.23	20.23	0.90
2500	9.35	13.86	13.38	24.79	1.08	0.70	37.30	20.24	0.97
2600	9.05	13.55	13.22	25.32	1.08	0.70	37.32	20.33	1.04
2700	8.77	13.24	13.06	25.63	1.08	0.70	37.17	20.37	1.11
2800	8.49	12.94	12.94	25.92	1.08	0.70	36.92	20.41	1.18
2900	8.23	12.67	12.82	25.85	1.08	0.70	36.84	20.44	1.21
3000	7.98	12.40	12.77	25.51	1.08	0.70	36.58	20.37	1.23
3200	7.51	11.89	12.68	24.48	1.07	0.70	36.24	20.52	1.24
3300	7.28	11.64	12.65	24.02	1.07	0.70	36.24	20.61	1.23
3400	7.07	11.40	12.69	23.38	1.07	0.69	36.16	20.57	1.27
3500	6.86	11.17	12.73	22.84	1.07	0.69	36.15	20.59	1.31
3600	6.66	10.94	12.81	22.25	1.07	0.69	36.07	20.58	1.35
3700	6.47	10.73	12.90	21.59	1.06	0.68	36.09	20.81	1.37
3800	6.28	10.52	13.05	21.08	1.06	0.68	36.05	20.88	1.41
4000	5.94	10.13	13.26	20.20	1.06	0.67	36.00	20.96	1.43



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 91mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	26.90	30.89	6.94	13.94	0.91	0.77	35.84	19.28	0.40
100	26.07	29.98	8.81	19.12	0.99	0.71	36.13	19.53	0.51
200	24.94	29.04	10.05	22.43	1.03	0.70	36.86	20.45	0.53
400	22.41	26.94	11.72	21.92	1.08	0.71	38.04	21.16	0.71
500	21.22	25.91	12.36	21.22	1.09	0.71	38.45	21.22	0.71
600	20.14	24.92	12.87	20.39	1.10	0.71	39.04	21.48	0.72
700	19.14	24.01	13.34	19.76	1.10	0.72	39.74	21.54	0.70
800	18.23	23.12	13.70	19.27	1.11	0.72	39.96	21.57	0.63
900	17.39	22.31	14.06	18.85	1.11	0.72	40.06	21.74	0.60
1000	16.62	21.57	14.35	18.47	1.11	0.72	40.73	21.65	0.63
1100	15.91	20.89	14.61	18.21	1.11	0.72	41.23	21.73	0.64
1200	15.25	20.22	14.85	17.93	1.11	0.71	41.10	21.79	0.66
1300	14.64	19.63	15.05	17.74	1.11	0.71	41.49	21.84	0.68
1400	14.07	19.07	15.20	17.58	1.11	0.71	41.84	21.95	0.70
1500	13.54	18.53	15.29	17.47	1.11	0.71	41.33	22.03	0.72
1600	13.05	18.01	15.35	17.43	1.11	0.71	41.67	22.04	0.75
1700	12.57	17.54	15.37	17.43	1.11	0.71	42.67	22.09	0.77
1800	12.13	17.08	15.31	17.58	1.11	0.71	42.46	22.25	0.78
1900	11.71	16.65	15.23	17.74	1.11	0.71	42.08	22.30	0.79
2000	11.32	16.23	15.11	17.91	1.10	0.71	41.59	22.33	0.81
2100	10.95	15.83	14.97	18.14	1.10	0.71	42.68	22.41	0.82
2200	10.59	15.46	14.80	18.44	1.10	0.71	43.43	22.45	0.84
2300	10.25	15.09	14.60	18.77	1.10	0.71	43.07	22.51	0.89
2400	9.93	14.74	14.42	19.12	1.10	0.72	42.91	22.55	0.94
2500	9.62	14.42	14.22	19.51	1.09	0.72	42.86	22.67	1.01
2600	9.33	14.08	14.04	19.90	1.09	0.72	42.61	22.74	1.09
2700	9.05	13.78	13.85	20.21	1.09	0.72	42.82	22.84	1.17
2800	8.77	13.47	13.71	20.59	1.09	0.72	43.13	22.80	1.24
2900	8.51	13.19	13.56	20.84	1.08	0.72	43.63	22.53	1.28
3000	8.26	12.91	13.51	20.97	1.08	0.72	44.18	22.27	1.30
3200	7.79	12.39	13.39	20.94	1.08	0.71	43.58	22.54	1.29
3300	7.56	12.13	13.36	20.87	1.08	0.71	43.58	22.81	1.30
3400	7.35	11.89	13.38	20.64	1.08	0.71	43.46	22.93	1.33
3500	7.14	11.65	13.43	20.34	1.07	0.70	44.65	22.98	1.36
3600	6.93	11.41	13.52	20.10	1.07	0.70	44.62	22.99	1.40
3700	6.75	11.20	13.60	19.68	1.07	0.70	44.62	23.04	1.45
3800	6.55	10.98	13.75	19.33	1.07	0.69	43.96	23.01	1.49
4000	6.20	10.58	13.98	18.65	1.07	0.68	44.30	22.84	1.57

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 85mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	26.87	30.54	6.92	13.76	0.90	0.74	36.67	18.77	0.39
100	26.04	29.93	8.76	19.08	0.99	0.71	36.84	19.06	0.50
200	24.90	28.98	10.01	22.49	1.03	0.70	37.21	20.09	0.52
400	22.37	26.91	11.66	22.21	1.08	0.71	37.70	20.88	0.71
500	21.19	25.84	12.30	21.49	1.09	0.71	38.31	20.98	0.70
600	20.11	24.87	12.82	20.68	1.10	0.71	38.92	21.15	0.73
700	19.12	23.95	13.29	20.07	1.10	0.72	39.36	21.26	0.70
800	18.21	23.10	13.65	19.56	1.11	0.72	39.79	21.33	0.63
900	17.37	22.29	14.00	19.12	1.11	0.72	40.27	21.38	0.60
1000	16.60	21.54	14.30	18.75	1.11	0.72	40.57	21.38	0.64
1100	15.89	20.84	14.56	18.48	1.11	0.72	40.86	21.43	0.64
1200	15.23	20.19	14.79	18.19	1.11	0.71	40.95	21.48	0.66
1300	14.62	19.59	15.00	17.98	1.11	0.71	41.21	21.52	0.68
1400	14.05	19.01	15.13	17.84	1.11	0.71	41.48	21.67	0.71
1500	13.52	18.50	15.23	17.70	1.11	0.71	41.51	21.73	0.72
1600	13.02	17.98	15.28	17.67	1.11	0.71	41.80	21.75	0.75
1700	12.55	17.49	15.29	17.68	1.11	0.71	42.03	21.79	0.77
1800	12.11	17.04	15.25	17.82	1.11	0.71	42.17	21.88	0.78
1900	11.69	16.61	15.17	17.98	1.11	0.71	42.26	22.02	0.79
2000	11.30	16.19	15.05	18.15	1.10	0.71	42.41	22.07	0.81
2100	10.92	15.80	14.90	18.41	1.10	0.71	42.61	22.14	0.83
2200	10.57	15.42	14.74	18.73	1.10	0.71	42.90	22.18	0.85
2300	10.23	15.05	14.54	19.08	1.10	0.71	43.05	22.26	0.88
2400	9.91	14.71	14.37	19.42	1.10	0.72	43.27	22.32	0.94
2500	9.60	14.37	14.16	19.78	1.09	0.72	43.24	22.40	1.01
2600	9.31	14.04	13.97	20.22	1.09	0.72	43.24	22.47	1.09
2700	9.03	13.74	13.79	20.55	1.09	0.72	43.26	22.50	1.17
2800	8.75	13.44	13.66	20.94	1.09	0.72	42.95	22.45	1.23
2900	8.49	13.15	13.51	21.19	1.08	0.72	43.24	22.28	1.26
3000	8.24	12.88	13.46	21.32	1.08	0.72	43.63	22.00	1.28
3200	7.76	12.35	13.35	21.24	1.08	0.71	44.14	22.27	1.28
3300	7.54	12.10	13.31	21.12	1.08	0.71	44.14	22.54	1.28
3400	7.32	11.85	13.33	20.85	1.07	0.71	44.37	22.67	1.32
3500	7.12	11.62	13.37	20.55	1.07	0.70	44.13	22.66	1.36
3600	6.91	11.38	13.47	20.27	1.07	0.70	44.19	22.70	1.40
3700	6.72	11.17	13.56	19.85	1.07	0.70	44.09	22.77	1.43
3800	6.53	10.95	13.70	19.49	1.07	0.69	44.02	22.82	1.47
4000	6.19	10.55	13.92	18.81	1.07	0.68	44.05	22.68	1.54

Typical Performance Data

Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 93mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
					K	Measure			
50	26.92	30.83	6.98	14.23	0.91	0.77	35.70	19.56	0.41
100	26.09	29.93	8.83	19.09	0.99	0.71	35.98	19.76	0.51
200	24.95	29.09	10.06	22.25	1.04	0.70	36.74	20.62	0.53
400	22.42	27.00	11.73	21.70	1.08	0.71	37.99	21.20	0.71
500	21.23	25.94	12.38	20.96	1.09	0.71	38.64	21.32	0.71
600	20.15	24.95	12.90	20.15	1.10	0.71	39.23	21.48	0.73
700	19.15	24.01	13.37	19.55	1.10	0.72	39.68	21.58	0.69
800	18.24	23.16	13.74	19.07	1.11	0.72	40.07	21.60	0.63
900	17.40	22.35	14.09	18.64	1.11	0.72	40.45	21.76	0.62
1000	16.63	21.63	14.38	18.28	1.11	0.72	40.79	21.68	0.65
1100	15.92	20.92	14.65	18.02	1.11	0.72	40.92	21.72	0.66
1200	15.26	20.26	14.88	17.75	1.11	0.72	41.24	21.80	0.68
1300	14.65	19.66	15.08	17.53	1.11	0.72	41.36	21.85	0.70
1400	14.08	19.09	15.25	17.39	1.11	0.71	41.34	21.96	0.73
1500	13.55	18.55	15.33	17.28	1.11	0.71	41.48	22.02	0.74
1600	13.05	18.05	15.38	17.23	1.11	0.71	41.88	22.00	0.76
1700	12.58	17.57	15.40	17.26	1.11	0.71	42.16	22.02	0.78
1800	12.14	17.11	15.34	17.39	1.11	0.71	42.34	22.16	0.79
1900	11.72	16.69	15.26	17.53	1.11	0.71	42.46	22.30	0.80
2000	11.33	16.27	15.14	17.70	1.11	0.71	42.79	22.35	0.82
2100	10.95	15.86	15.00	17.93	1.10	0.71	42.98	22.45	0.84
2200	10.60	15.48	14.83	18.25	1.10	0.72	43.25	22.45	0.85
2300	10.26	15.12	14.63	18.56	1.10	0.72	43.12	22.51	0.90
2400	9.94	14.77	14.45	18.89	1.10	0.72	44.15	22.58	0.96
2500	9.63	14.45	14.25	19.24	1.09	0.72	43.97	22.70	1.03
2600	9.34	14.11	14.06	19.66	1.09	0.72	43.98	22.78	1.11
2700	9.06	13.81	13.86	19.97	1.09	0.72	44.17	22.81	1.19
2800	8.78	13.50	13.74	20.39	1.09	0.72	44.10	22.73	1.26
2900	8.52	13.22	13.58	20.65	1.09	0.72	44.49	22.48	1.29
3000	8.26	12.94	13.53	20.77	1.08	0.72	43.66	22.18	1.31
3200	7.79	12.41	13.42	20.74	1.08	0.71	43.95	22.48	1.31
3300	7.57	12.16	13.37	20.58	1.08	0.71	43.95	22.83	1.31
3400	7.35	11.92	13.40	20.41	1.08	0.71	44.41	23.02	1.34
3500	7.14	11.68	13.44	20.11	1.07	0.71	44.68	23.00	1.38
3600	6.94	11.44	13.55	19.89	1.07	0.70	44.91	23.07	1.42
3700	6.76	11.22	13.63	19.49	1.07	0.70	45.26	23.06	1.46
3800	6.56	11.00	13.76	19.16	1.07	0.69	45.24	23.03	1.50
4000	6.21	10.59	14.01	18.53	1.07	0.69	44.59	22.90	1.59

MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.00V, Id = 56mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.33	29.88	6.29	13.54	0.87	0.76	31.22	14.88	0.33
100	25.52	29.46	7.94	17.99	0.96	0.75	31.60	14.91	0.46
200	24.40	28.38	9.07	21.21	0.99	0.73	31.79	16.77	0.49
400	21.90	26.17	10.62	24.11	1.04	0.72	32.65	18.08	0.68
500	20.71	25.10	11.23	24.79	1.05	0.72	32.87	18.19	0.68
600	19.63	24.09	11.72	24.96	1.06	0.72	33.00	18.46	0.69
700	18.63	23.17	12.15	24.99	1.07	0.72	33.15	18.50	0.67
800	17.72	22.35	12.50	24.92	1.08	0.72	33.22	18.57	0.60
900	16.88	21.57	12.81	24.69	1.09	0.72	33.43	18.69	0.58
1000	16.10	20.84	13.10	24.44	1.10	0.72	33.56	18.87	0.60
1100	15.38	20.15	13.33	24.22	1.10	0.72	33.57	18.90	0.61
1200	14.72	19.52	13.55	23.97	1.10	0.72	33.72	18.90	0.63
1300	14.11	18.92	13.73	23.70	1.11	0.72	33.95	18.97	0.65
1400	13.53	18.36	13.86	23.64	1.11	0.72	33.97	19.07	0.67
1500	12.99	17.85	13.95	23.54	1.11	0.72	34.12	19.17	0.69
1600	12.49	17.35	13.99	23.57	1.11	0.72	34.07	19.35	0.71
1700	12.01	16.87	14.01	23.69	1.11	0.72	34.28	19.41	0.73
1800	11.56	16.43	13.96	24.02	1.11	0.72	34.38	19.49	0.74
1900	11.14	16.02	13.90	24.38	1.11	0.72	34.36	19.49	0.75
2000	10.74	15.61	13.79	24.77	1.11	0.72	34.30	19.59	0.77
2100	10.36	15.23	13.67	25.30	1.11	0.72	34.38	19.70	0.78
2200	9.99	14.88	13.53	25.96	1.11	0.73	34.20	19.84	0.81
2300	9.65	14.54	13.36	26.50	1.11	0.73	34.24	19.84	0.85
2400	9.32	14.20	13.20	27.11	1.11	0.73	33.96	19.84	0.90
2500	9.00	13.88	13.03	27.66	1.11	0.73	33.86	19.85	0.97
2600	8.70	13.58	12.88	28.02	1.11	0.73	33.89	19.93	1.04
2700	8.41	13.29	12.71	28.02	1.11	0.73	33.86	19.97	1.13
2800	8.12	13.01	12.60	27.80	1.11	0.73	33.61	20.08	1.19
2900	7.85	12.73	12.49	27.26	1.11	0.73	33.30	20.07	1.22
3000	7.59	12.49	12.43	26.50	1.11	0.73	33.31	20.03	1.24
3200	7.10	11.98	12.36	24.94	1.11	0.73	33.35	20.22	1.21
3300	6.87	11.76	12.34	24.38	1.11	0.73	33.14	20.39	1.21
3400	6.65	11.52	12.37	23.68	1.10	0.73	33.18	20.37	1.23
3500	6.44	11.30	12.42	23.13	1.10	0.73	32.98	20.39	1.26
3600	6.23	11.08	12.51	22.60	1.10	0.73	32.92	20.32	1.30
3700	6.03	10.87	12.60	21.98	1.10	0.72	32.92	20.43	1.35
3800	5.84	10.68	12.73	21.54	1.10	0.72	32.97	20.52	1.38
4000	5.48	10.29	12.95	20.76	1.10	0.71	32.94	20.63	1.47



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 2.70V, Id = 50mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.11	30.26	6.04	13.78	0.87	0.83	30.18	14.88	0.36
100	25.31	29.37	7.62	17.56	0.95	0.77	30.29	14.91	0.49
200	24.20	28.19	8.74	20.50	0.98	0.74	30.53	16.77	0.51
400	21.71	25.85	10.29	23.42	1.02	0.72	30.98	18.08	0.69
500	20.53	24.78	10.89	24.35	1.04	0.72	31.22	18.19	0.69
600	19.44	23.82	11.36	24.94	1.05	0.72	31.43	18.46	0.72
700	18.45	22.91	11.79	25.45	1.06	0.72	31.58	18.50	0.68
800	17.54	22.08	12.13	25.82	1.07	0.72	31.68	18.57	0.62
900	16.70	21.29	12.46	25.97	1.08	0.72	31.81	18.69	0.59
1000	15.92	20.58	12.74	26.02	1.09	0.72	31.92	18.87	0.62
1100	15.21	19.89	12.98	26.03	1.09	0.72	32.00	18.90	0.63
1200	14.55	19.25	13.19	25.93	1.10	0.72	32.10	18.90	0.65
1300	13.93	18.68	13.37	25.82	1.10	0.72	32.18	18.97	0.67
1400	13.36	18.12	13.51	25.91	1.10	0.72	32.29	19.07	0.70
1500	12.82	17.58	13.59	25.94	1.10	0.72	32.45	19.17	0.71
1600	12.32	17.11	13.66	26.10	1.11	0.72	32.56	19.35	0.73
1700	11.84	16.65	13.66	26.30	1.11	0.72	32.67	19.41	0.74
1800	11.40	16.19	13.64	26.79	1.11	0.72	32.70	19.49	0.75
1900	10.98	15.79	13.57	27.28	1.11	0.72	32.78	19.49	0.76
2000	10.57	15.39	13.48	27.71	1.11	0.72	32.79	19.59	0.78
2100	10.19	15.02	13.39	28.28	1.11	0.72	32.81	19.70	0.79
2200	9.83	14.65	13.27	28.85	1.11	0.72	32.77	19.84	0.81
2300	9.48	14.29	13.12	29.28	1.11	0.72	32.68	19.84	0.85
2400	9.15	13.97	12.97	29.46	1.11	0.73	32.56	19.84	0.91
2500	8.83	13.66	12.80	29.38	1.11	0.73	32.56	19.85	0.98
2600	8.53	13.36	12.67	28.88	1.11	0.73	32.46	19.93	1.06
2700	8.24	13.06	12.52	28.15	1.10	0.73	32.40	19.97	1.13
2800	7.96	12.78	12.44	27.30	1.10	0.73	32.30	20.08	1.20
2900	7.69	12.53	12.33	26.29	1.10	0.73	32.22	20.07	1.23
3000	7.43	12.27	12.30	25.44	1.10	0.73	32.15	20.03	1.25
3200	6.94	11.78	12.24	23.87	1.10	0.73	31.95	20.22	1.25
3300	6.71	11.54	12.23	23.35	1.10	0.73	31.94	20.39	1.24
3400	6.49	11.32	12.28	22.74	1.10	0.73	31.86	20.37	1.28
3500	6.28	11.10	12.33	22.28	1.10	0.72	31.81	20.39	1.30
3600	6.07	10.89	12.44	21.77	1.10	0.72	31.77	20.32	1.34
3700	5.88	10.69	12.52	21.26	1.10	0.72	31.79	20.43	1.37
3800	5.68	10.48	12.70	20.93	1.10	0.72	31.75	20.52	1.41
4000	5.32	10.10	12.94	20.27	1.10	0.71	31.71	20.63	1.44



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.30V, Id = 62mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.50	30.41	6.38	13.96	0.88	0.79	32.38	15.50	0.35
100	25.68	29.59	8.11	18.26	0.97	0.74	32.63	16.02	0.48
200	24.56	28.54	9.29	21.68	1.00	0.72	33.19	17.44	0.51
400	22.04	26.34	10.91	24.03	1.05	0.71	34.20	18.61	0.69
500	20.86	25.30	11.54	24.30	1.06	0.72	34.64	18.83	0.69
600	19.77	24.33	12.07	24.05	1.08	0.72	34.96	18.99	0.71
700	18.78	23.44	12.53	23.70	1.09	0.72	35.26	19.16	0.67
800	17.86	22.54	12.89	23.35	1.09	0.72	35.42	19.18	0.60
900	17.02	21.77	13.23	23.01	1.10	0.72	35.68	19.30	0.59
1000	16.24	21.04	13.52	22.66	1.10	0.72	35.84	19.45	0.63
1100	15.52	20.36	13.79	22.38	1.11	0.72	36.03	19.50	0.64
1200	14.86	19.74	14.03	22.05	1.11	0.72	36.19	19.50	0.66
1300	14.24	19.16	14.22	21.84	1.11	0.72	36.37	19.55	0.68
1400	13.66	18.59	14.36	21.68	1.11	0.72	36.56	19.63	0.71
1500	13.12	18.05	14.47	21.59	1.11	0.72	36.70	19.69	0.72
1600	12.62	17.57	14.53	21.59	1.12	0.72	36.73	19.83	0.75
1700	12.14	17.09	14.56	21.65	1.12	0.72	36.77	19.93	0.76
1800	11.69	16.66	14.53	21.93	1.12	0.73	36.95	20.02	0.76
1900	11.27	16.23	14.46	22.18	1.12	0.73	37.05	20.04	0.77
2000	10.87	15.83	14.36	22.51	1.12	0.73	37.00	20.09	0.78
2100	10.48	15.45	14.26	22.92	1.12	0.73	37.02	20.21	0.79
2200	10.12	15.09	14.11	23.42	1.12	0.73	37.18	20.30	0.81
2300	9.77	14.74	13.94	23.98	1.12	0.73	37.24	20.24	0.85
2400	9.44	14.39	13.79	24.52	1.11	0.73	37.23	20.23	0.90
2500	9.12	14.08	13.61	25.05	1.11	0.73	37.30	20.24	0.97
2600	8.82	13.77	13.46	25.57	1.11	0.74	37.32	20.33	1.04
2700	8.53	13.48	13.30	25.86	1.11	0.74	37.17	20.37	1.11
2800	8.24	13.19	13.20	26.20	1.11	0.74	36.92	20.41	1.18
2900	7.98	12.91	13.07	26.15	1.11	0.74	36.84	20.44	1.21
3000	7.72	12.66	13.03	25.77	1.11	0.74	36.58	20.37	1.23
3200	7.23	12.16	12.96	24.73	1.11	0.74	36.24	20.52	1.24
3300	6.99	11.92	12.93	24.29	1.11	0.74	36.24	20.61	1.23
3400	6.77	11.69	12.99	23.65	1.11	0.73	36.16	20.57	1.27
3500	6.55	11.46	13.04	23.09	1.11	0.73	36.15	20.59	1.31
3600	6.35	11.25	13.14	22.56	1.11	0.73	36.07	20.58	1.35
3700	6.15	11.04	13.23	21.91	1.11	0.73	36.09	20.81	1.37
3800	5.95	10.84	13.38	21.41	1.11	0.73	36.05	20.88	1.41
4000	5.59	10.46	13.61	20.52	1.11	0.72	36.00	20.96	1.43



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 91mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.97	30.63	6.87	14.12	0.89	0.75	35.84	19.28	0.40
100	26.13	29.91	8.74	19.00	0.98	0.70	36.13	19.53	0.51
200	24.97	29.00	9.99	22.27	1.03	0.69	36.86	20.45	0.53
400	22.41	26.96	11.69	21.82	1.08	0.71	38.04	21.16	0.71
500	21.21	25.90	12.35	21.15	1.09	0.71	38.45	21.22	0.71
600	20.11	24.94	12.89	20.36	1.10	0.72	39.04	21.48	0.72
700	19.10	24.02	13.37	19.74	1.11	0.72	39.74	21.54	0.70
800	18.18	23.17	13.76	19.28	1.11	0.72	39.96	21.57	0.63
900	17.33	22.37	14.11	18.87	1.12	0.72	40.06	21.74	0.60
1000	16.55	21.64	14.42	18.51	1.12	0.73	40.73	21.65	0.63
1100	15.82	20.96	14.70	18.25	1.12	0.73	41.23	21.73	0.64
1200	15.16	20.33	14.94	17.98	1.13	0.73	41.10	21.79	0.66
1300	14.54	19.75	15.15	17.79	1.13	0.73	41.49	21.84	0.68
1400	13.96	19.20	15.31	17.65	1.13	0.73	41.84	21.95	0.70
1500	13.41	18.64	15.42	17.55	1.13	0.73	41.33	22.03	0.72
1600	12.91	18.16	15.49	17.51	1.13	0.73	41.67	22.04	0.75
1700	12.42	17.68	15.51	17.54	1.13	0.73	42.67	22.09	0.77
1800	11.97	17.23	15.47	17.68	1.13	0.73	42.46	22.25	0.78
1900	11.55	16.82	15.39	17.85	1.13	0.73	42.08	22.30	0.79
2000	11.14	16.41	15.28	18.02	1.13	0.74	41.59	22.33	0.81
2100	10.76	16.02	15.15	18.29	1.13	0.74	42.68	22.41	0.82
2200	10.39	15.66	15.00	18.61	1.13	0.74	43.43	22.45	0.84
2300	10.05	15.30	14.81	18.93	1.13	0.74	43.07	22.51	0.89
2400	9.72	14.96	14.63	19.28	1.13	0.74	42.91	22.55	0.94
2500	9.40	14.63	14.43	19.66	1.13	0.75	42.86	22.67	1.01
2600	9.10	14.33	14.27	20.05	1.13	0.75	42.61	22.74	1.09
2700	8.81	14.02	14.07	20.41	1.12	0.75	42.82	22.84	1.17
2800	8.52	13.72	13.96	20.79	1.12	0.75	43.13	22.80	1.24
2900	8.25	13.45	13.83	21.05	1.12	0.75	43.63	22.53	1.28
3000	7.99	13.18	13.78	21.21	1.12	0.75	44.18	22.27	1.30
3200	7.50	12.67	13.68	21.18	1.12	0.75	43.58	22.54	1.29
3300	7.27	12.43	13.65	21.06	1.12	0.75	43.58	22.81	1.30
3400	7.05	12.19	13.69	20.85	1.12	0.75	43.46	22.93	1.33
3500	6.83	11.95	13.73	20.58	1.11	0.75	44.65	22.98	1.36
3600	6.62	11.74	13.85	20.34	1.12	0.74	44.62	22.99	1.40
3700	6.42	11.52	13.93	19.94	1.11	0.74	44.62	23.04	1.45
3800	6.23	11.31	14.09	19.60	1.11	0.74	43.96	23.01	1.49
4000	5.86	10.92	14.34	18.96	1.11	0.73	44.30	22.84	1.57

MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 86mA @Temperature = +25°C

FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.94	30.81	6.84	14.07	0.90	0.77	36.67	18.77	0.39
100	26.10	29.83	8.71	19.04	0.98	0.70	36.84	19.06	0.50
200	24.94	28.95	9.96	22.49	1.03	0.69	37.21	20.09	0.52
400	22.38	26.89	11.66	22.21	1.08	0.71	37.70	20.88	0.71
500	21.18	25.84	12.31	21.53	1.09	0.71	38.31	20.98	0.70
600	20.08	24.89	12.85	20.71	1.10	0.72	38.92	21.15	0.73
700	19.08	23.97	13.32	20.11	1.11	0.72	39.36	21.26	0.70
800	18.16	23.13	13.71	19.64	1.11	0.72	39.79	21.33	0.63
900	17.31	22.35	14.07	19.18	1.12	0.73	40.27	21.38	0.60
1000	16.53	21.62	14.37	18.84	1.12	0.73	40.57	21.38	0.64
1100	15.80	20.94	14.65	18.58	1.12	0.73	40.86	21.43	0.64
1200	15.14	20.28	14.89	18.29	1.12	0.73	40.95	21.48	0.66
1300	14.51	19.69	15.10	18.10	1.13	0.73	41.21	21.52	0.68
1400	13.94	19.13	15.27	17.96	1.13	0.73	41.48	21.67	0.71
1500	13.39	18.60	15.36	17.85	1.13	0.73	41.51	21.73	0.72
1600	12.89	18.11	15.43	17.81	1.13	0.73	41.80	21.75	0.75
1700	12.40	17.64	15.45	17.83	1.13	0.73	42.03	21.79	0.77
1800	11.95	17.19	15.41	17.98	1.13	0.73	42.17	21.88	0.78
1900	11.53	16.77	15.34	18.14	1.13	0.73	42.26	22.02	0.79
2000	11.13	16.37	15.22	18.35	1.13	0.74	42.41	22.07	0.81
2100	10.74	15.98	15.09	18.60	1.13	0.74	42.61	22.14	0.83
2200	10.38	15.63	14.94	18.92	1.13	0.74	42.90	22.18	0.85
2300	10.03	15.26	14.75	19.25	1.13	0.74	43.05	22.26	0.88
2400	9.70	14.91	14.58	19.62	1.13	0.74	43.27	22.32	0.94
2500	9.38	14.58	14.38	20.03	1.12	0.74	43.24	22.40	1.01
2600	9.08	14.28	14.22	20.44	1.12	0.75	43.24	22.47	1.09
2700	8.79	13.97	14.04	20.77	1.12	0.75	43.26	22.50	1.17
2800	8.50	13.68	13.91	21.20	1.12	0.75	42.95	22.45	1.23
2900	8.23	13.41	13.78	21.44	1.12	0.75	43.24	22.28	1.26
3000	7.97	13.14	13.73	21.58	1.12	0.75	43.63	22.00	1.28
3200	7.48	12.64	13.64	21.53	1.12	0.75	44.14	22.27	1.28
3300	7.25	12.39	13.61	21.38	1.12	0.75	44.14	22.54	1.28
3400	7.03	12.15	13.63	21.17	1.12	0.75	44.37	22.67	1.32
3500	6.81	11.92	13.69	20.86	1.11	0.75	44.13	22.66	1.36
3600	6.60	11.70	13.80	20.60	1.11	0.74	44.19	22.70	1.40
3700	6.40	11.48	13.88	20.17	1.11	0.74	44.09	22.77	1.43
3800	6.21	11.28	14.04	19.81	1.11	0.74	44.02	22.82	1.47
4000	5.84	10.89	14.27	19.17	1.11	0.73	44.05	22.68	1.54



MMIC Amplifier Die

PGA-103-D+

Typical Performance Data

Without Full 2-Port Extension

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 93mA @Temperature = +25°C


FREQ.	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
50	26.99	30.20	6.87	13.89	0.89	0.69	35.70	19.56	0.41
100	26.15	29.92	8.77	19.04	0.98	0.70	35.98	19.76	0.51
200	24.99	29.05	10.03	22.24	1.03	0.70	36.74	20.62	0.53
400	22.42	26.97	11.74	21.72	1.08	0.71	37.99	21.20	0.71
500	21.22	25.91	12.39	20.97	1.09	0.71	38.64	21.32	0.71
600	20.12	24.94	12.93	20.19	1.10	0.72	39.23	21.48	0.73
700	19.12	24.05	13.41	19.60	1.11	0.72	39.68	21.58	0.69
800	18.19	23.18	13.79	19.13	1.11	0.72	40.07	21.60	0.63
900	17.34	22.41	14.15	18.70	1.12	0.72	40.45	21.76	0.62
1000	16.56	21.67	14.45	18.37	1.12	0.73	40.79	21.68	0.65
1100	15.83	21.01	14.74	18.13	1.13	0.73	40.92	21.72	0.66
1200	15.17	20.37	14.98	17.84	1.13	0.73	41.24	21.80	0.68
1300	14.55	19.77	15.20	17.66	1.13	0.73	41.36	21.85	0.70
1400	13.97	19.20	15.35	17.52	1.13	0.73	41.34	21.96	0.73
1500	13.42	18.67	15.45	17.42	1.13	0.73	41.48	22.02	0.74
1600	12.92	18.18	15.53	17.38	1.13	0.73	41.88	22.00	0.76
1700	12.43	17.71	15.54	17.41	1.13	0.73	42.16	22.02	0.78
1800	11.98	17.26	15.49	17.54	1.13	0.73	42.34	22.16	0.79
1900	11.56	16.84	15.44	17.70	1.13	0.73	42.46	22.30	0.80
2000	11.15	16.43	15.33	17.89	1.13	0.74	42.79	22.35	0.82
2100	10.77	16.04	15.19	18.13	1.13	0.74	42.98	22.45	0.84
2200	10.40	15.68	15.02	18.45	1.13	0.74	43.25	22.45	0.85
2300	10.06	15.32	14.84	18.77	1.13	0.74	43.12	22.51	0.90
2400	9.73	14.99	14.66	19.12	1.13	0.74	44.15	22.58	0.96
2500	9.41	14.66	14.48	19.48	1.13	0.75	43.97	22.70	1.03
2600	9.11	14.34	14.29	19.89	1.13	0.75	43.98	22.78	1.11
2700	8.82	14.04	14.11	20.22	1.12	0.75	44.17	22.81	1.19
2800	8.53	13.75	13.99	20.60	1.12	0.75	44.10	22.73	1.26
2900	8.26	13.47	13.86	20.87	1.12	0.75	44.49	22.48	1.29
3000	8.00	13.21	13.79	21.02	1.12	0.75	43.66	22.18	1.31
3200	7.51	12.70	13.71	21.01	1.12	0.75	43.95	22.48	1.31
3300	7.28	12.45	13.67	20.92	1.12	0.75	43.95	22.83	1.31
3400	7.06	12.21	13.71	20.74	1.12	0.75	44.41	23.02	1.34
3500	6.84	11.98	13.75	20.45	1.12	0.75	44.68	23.00	1.38
3600	6.63	11.75	13.86	20.19	1.11	0.74	44.91	23.07	1.42
3700	6.44	11.54	13.94	19.81	1.11	0.74	45.26	23.06	1.46
3800	6.24	11.33	14.11	19.49	1.11	0.74	45.24	23.03	1.50
4000	5.87	10.94	14.36	18.86	1.11	0.73	44.59	22.90	1.59




Typical Performance Curves

Full 2-Port Extension


GAIN vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




ISOLATION vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




INPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




OUTPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE
OUTPUT POWER = 5 dBm/tone, Temperature = +25°C



P1dB vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C










NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C



Typical Performance Curves


Full 2-Port Extension




Typical Performance Curves

Without Full 2-Port Extension


GAIN vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




ISOLATION vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




INPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




OUTPUT RETURN LOSS vs. FREQUENCY & DEVICE VOLTAGE
INPUT POWER = -25dBm, Temperature = +25°C




OUTPUT IP3 vs. FREQUENCY & DEVICE VOLTAGE
OUTPUT POWER = 5 dBm/1tone, Temperature = +25°C



P1dB vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C










NOISE FIGURE vs. FREQUENCY & DEVICE VOLTAGE
Temperature = +25°C



Typical Performance Curves

Without Full 2-Port Extension



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	