




ULTRA LOW NOISE, HIGH IP3

Monolithic Amplifier PMA2-162LN+

50Ω 0.7 to 1.6 GHz

THE BIG DEAL

- Ultra Low Noise Figure, 0.5 dB at 1 GHz
- High IP3, 30 dBm typ. at 1 GHz
- Class 1B HBM ESD (500V)
- Adjustable gain, 19.7-23.5 dB at 1 GHz
- High Pout, P1dB 20 dBm typ. at 1 GHz
- May be used as a replacement for MGA-631P8 ^{a,b}



Generic photo used for illustration purposes only

CASE STYLE: MC1631

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Base station infrastructure
- Portable Wireless
- LTE
- GPS
- GSM
- Airborne radar

PRODUCT OVERVIEW

Mini-Circuits PMA2-162LN+ is a E-PHEMT* based Ultra-Low Noise MMIC Amplifier with a unique combinations of low noise and high IP3 making this amplifier ideal for sensitive high dynamic range receiver applications. This design operates on a single 4V supply.

KEY FEATURES

Feature	Advantages
Ultra Low Noise, 0.5 dB at 1.0 GHz	Outstanding world class noise figure performance.
High IP3, +30 dBm at 1.0 GHz	Combining Low Noise and High IP3 makes this MMIC amplifier ideal for use in Low Noise Receiver Front End (RFE) as it gives the user advantages at both ends of the dynamic range: sensitivity & two-tone IM performance.
Adjustable Gain	By changing feedback resistor R1, gain can be changed from 19.7 to 23.5 dB at 1GHz
2mm x 2mm 8 lead MCLP Package	Low Inductance, repeatable transitions, excellent thermal contact to PCB
Max Input Power, +25 dBm	Ruggedized design operates up to high input powers often seen at Receiver inputs eliminating the need for an external resistor.
High Reliability	Low, small signal operating current of 55 mA nominal maintains junction temperatures typically below 100°C at 85°C ground lead temperature.
Class 1B ESD (500V HBM)	The PMA2-162LN+ is a super low noise PHEMT based design. Mini-Circuits incorporates ESD protection on die to achieve industry leading ESD performance for a low noise amplifier.

A. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

B. The Avago MGA-631P8 part number is used for identification and comparison purposes only.

*Enhancement mode Pseudomorphic High Electron Mobility Transistor





ULTRA LOW NOISE, HIGH IP3

Monolithic Amplifier PMA2-162LN+

ELECTRICAL SPECIFICATIONS^{1,2} AT 25°C AND 4V, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	R1=267Ω1			R1=93Ω2			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
Frequency Range		0.7		1.6	0.7		1.6	GHz
Noise Figure	0.7		0.55			0.57		dB
	0.8		0.51			0.54		
	1.0		0.47			0.48		
	1.3		0.64			0.65		
	1.6		0.80			0.81		
Gain	0.7	–	24.4	–	–	22.7	23.1	dB
	0.8	–	24.1	–	–	22.2		
	1.0	20.9	22.7	24.5	18.6	20.8		
	1.3	–	20.7	–	–	19.1		
	1.6	–	18.8	–	–	17.7		
Input Return Loss	0.7		9.5			11.5	dB	
	0.8		15.5			18.8		
	1.0		17.9			20.0		
	1.3		12.4			14.5		
	1.6		10.8			12.4		
Output Return Loss	0.7		13.6			21.6	dB	
	0.8		16.1			17.8		
	1.0		18.9			16.0		
	1.3		15.6			15.1		
	1.6		10.7			11.6		
Output Power @1 dB compression ³	0.7		19.5			18.3	dBm	
	0.8		19.8			18.9		
	1.0		19.9			19.7		
	1.3		19.7			19.8		
	1.6		18.8			19.0		
Output IP3	0.7		29.1			28.3	dBm	
	0.8		30.3			29.5		
	1.0		30.0			29.0		
	1.3		30.1			29.2		
	1.6		29.4			28.5		
Device Operating Voltage		3.8	4.0	4.2	3.8	4.0	4.2	V
Device Operating Current at 4V			55	60		55	60	mA
Device Current Variation vs. Temperature at 4V ⁴			2			2		μA/°C
Device Current Variation vs Voltage at 25°C			0.016			0.016		mA/mV
Thermal Resistance, junction-to-ground lead			53			53		°C/W

1. Measured on Mini-Circuits Characterization test board TB-615+. See Characterization Test Circuit (Fig. 1) R1=267Ω

2. Measured on Mini-Circuits Characterization test board TB-615+. See Characterization Test Circuit (Fig. 1) R1=93Ω

3. Current increases at P1dB


4. (Current at 85°C - Current at -45°C)/130

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Junction Temperature	150°C
Total Power Dissipation	0.55 W
Input Power (CW), Vd=4V	25 dBm
DC Voltage	5.5V

Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

DC CURRENT HISTOGRAM







ULTRA LOW NOISE, HIGH IP3

Monolithic Amplifier PMA2-162LN+

SIMPLIFIED SCHEMATIC & PAD CONNECTIONS



Function	Pad Number	Description
RF IN	2	Connects to RF input via C1 and Pad 3 via L1
RF-OUT & DC-IN	7	Connects to RF out via C2, Pad 5 via R1, and C3
RF-Ground	3	Connects to ground via C4 and Pad 2 via L1
Bias	4	Connects to Supply voltage (Vs) via Rbias
Feedback	5	Connected to pads 7, 4 via R1 and C3
No Connection	1,6	Not used internally. Pin 1 Connected to ground on test board
Ground	8 & paddle	Connects to ground

RECOMMENDED APPLICATION AND CHARACTERIZATION TEST CIRCUIT




Fig 1. Application and Characterization circuit

Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-615+)


Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin = -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Components	Size	Value	Manufacturer	P/N
C1, C6	0402	9.1pF	AVX CORP	04025U9R1CAT2A
C2, C4	0402	100pF	Murata	GRM1555C1H101JA01D
C3	0402	5.6pF	Murata	GJM1555C1H5R6BB01D
C5, C7	0402	0.1uF	Murata	GRM155R71C104KA88D
R1	0402	267 Ohm	KOA Speer Electronics	RK73H1ETTP2670F
Rbias	0402	750 Ohm	KOA Speer Electronics	RK73H1ETTP7500F
L1	0402	6.8nH	Coilcraft, Inc.	0402CS-6N8XGLW
L2	0402	15nH	Coilcraft, Inc.	0402CS-15NXGLW

PRODUCT MARKING



Marking may contain other features or characters for internal lot control






ULTRA LOW NOISE, HIGH IP3


Monolithic Amplifier PMA2-162LN+

ADJUSTABLE GAIN PERFORMANCE (VS. R1)


S21 (AMPLITUDE,dB) Vs. Frequency and R1 Values




NOISE FIGURE (dB) Vs. Frequency and R1 Values



S22 (AMPLITUDE,dB) Vs. Frequency and R1 Values



S11 (AMPLITUDE,dB) Vs. Frequency and R1 Values





ULTRA LOW NOISE, HIGH IP3

Monolithic Amplifier PMA2-162LN+

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	MC1631 Plastic package, exposed paddle, lead finish: matte tin
Tape & Reel	F108
Standard quantities available on reel	7" reels with 20, 50, 100, 200, 500,1K, 2K or 3K devices
Suggested Layout for PCB Design	PL-344
Evaluation Board	TB-615+
Environmental Ratings	ENV08T1

ESD RATING


Human Body Model (HBM): Class 1B (500 to <1000V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (pass 25V) in accordance with ANSI/ESD STM5.2-1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

- Input Return Loss = -S11 (dB)
- Gain(Power Gain) = S21 (dB)
- Reverse Isolation = -S12 (dB)
- Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4V, Id = 54.09mA, R1=267 Ohms @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	21.78	42.23	2.02	6.93	1.92	1.23	27.48	16.87	500.0	1.18
525.0	22.53	41.02	2.59	7.73	1.89	1.21	27.95	17.34	600.0	1.01
550.0	23.13	40.30	3.28	8.57	1.92	1.19	27.79	17.75	700.0	0.51
575.0	23.59	39.70	4.08	9.45	1.97	1.16	27.79	18.12	800.0	0.47
600.0	23.94	38.83	4.97	10.31	1.94	1.12	28.24	18.25	900.0	0.37
625.0	24.18	38.76	5.96	11.21	2.04	1.09	28.29	18.88	1000.0	0.39
650.0	24.32	38.36	7.04	12.10	2.06	1.06	28.58	19.09	1100.0	0.43
675.0	24.40	37.86	8.21	12.90	2.06	1.02	28.79	19.35	1200.0	0.51
700.0	24.43	38.04	9.45	13.64	2.18	1.01	29.24	19.57	1300.0	0.41
725.0	24.40	37.80	10.77	14.36	2.20	0.99	29.44	19.58	1400.0	0.55
750.0	24.33	37.95	12.21	15.02	2.31	0.97	29.69	19.91	1500.0	0.61
775.0	24.25	37.63	13.78	15.57	2.30	0.96	30.06	19.94	1600.0	0.60
800.0	24.14	37.66	15.47	16.12	2.37	0.95	30.42	19.85	1700.0	0.58
825.0	24.02	37.52	17.41	16.70	2.39	0.95	30.54	20.22	1800.0	0.74
850.0	23.88	37.50	19.50	17.20	2.44	0.94	30.40	20.22	1900.0	0.68
875.0	23.73	37.50	21.84	17.71	2.49	0.94	30.84	19.99	2000.0	0.78
900.0	23.58	37.31	24.22	18.16	2.49	0.94	30.53	20.53	2100.0	0.76
925.0	23.42	37.40	26.19	18.51	2.56	0.95	30.94	20.18	2200.0	0.81
950.0	23.26	37.59	27.29	18.85	2.66	0.95	30.95	20.07	2300.0	0.92
975.0	23.10	37.56	26.41	19.15	2.70	0.95	30.49	20.28	2400.0	0.95
1000.0	22.93	37.52	24.92	19.33	2.74	0.96	30.25	20.02	2500.0	1.09
1050.0	22.60	37.72	22.00	19.47	2.89	0.96	30.84	20.02	2600.0	1.04
1100.0	22.27	37.43	19.69	19.29	2.88	0.97	30.74	20.00	2700.0	1.19
1150.0	21.94	37.53	17.93	18.72	3.00	0.98	30.71	20.02	2800.0	1.21
1200.0	21.62	37.66	16.93	18.08	3.12	0.98	30.64	20.06	2900.0	1.25
1250.0	21.30	37.84	15.96	17.18	3.27	0.99	30.37	20.10	3000.0	1.16
1300.0	20.99	37.78	15.35	16.24	3.32	0.99	30.44	19.81	3100.0	1.46
1350.0	20.68	37.72	14.83	15.27	3.38	0.99	30.39	19.58	3200.0	1.46
1400.0	20.38	37.76	14.26	14.36	3.46	0.99	30.21	19.36	3300.0	1.51
1500.0	19.78	37.99	13.41	12.69	3.69	0.99	30.35	19.58	3400.0	1.59
1550.0	19.47	38.16	13.13	11.92	3.83	0.98	29.89	18.84	3500.0	1.49
1600.0	19.18	38.04	12.91	11.19	3.84	0.97	30.04	18.92	3600.0	1.75
1700.0	18.59	38.11	12.40	9.85	3.98	0.95	29.43	18.19	3700.0	1.78
1800.0	17.99	38.52	11.88	8.73	4.26	0.93	29.60	18.25	3800.0	1.77
1900.0	17.37	38.65	11.50	7.76	4.42	0.90	29.74	18.07	3900.0	1.84
2000.0	16.73	38.95	11.33	7.25	4.78	0.88	29.02	17.45	4000.0	1.78
2100.0	16.25	39.04	11.02	6.38	4.79	0.84	29.18	17.40		
2200.0	15.69	39.02	10.74	5.66	4.78	0.81	29.04	17.34		
2300.0	15.12	39.54	10.55	5.10	5.11	0.77	28.59	16.44		
2400.0	14.53	39.69	10.27	4.60	5.20	0.73	27.88	15.96		
2500.0	13.95	39.71	10.05	4.19	5.25	0.70	28.02	15.58		
2600.0	13.38	40.18	9.92	3.83	5.58	0.66	27.18	15.10		
2700.0	12.81	39.59	9.71	3.51	5.21	0.63	27.03	14.84		
2800.0	12.24	39.75	9.48	3.25	5.34	0.60	26.66	14.26		
2900.0	11.70	39.38	9.36	3.02	5.15	0.58	26.49	13.97		
3000.0	11.17	39.44	9.21	2.83	5.23	0.55	25.59	13.54		
3100.0	10.65	39.19	9.00	2.62	5.06	0.53	25.64	13.10		
3200.0	10.14	38.88	8.93	2.46	4.91	0.51	24.56	12.46		
3300.0	9.67	38.08	8.81	2.29	4.43	0.48	24.57	12.11		
3400.0	9.20	38.03	8.68	2.14	4.38	0.46	24.03	11.83		
3500.0	8.74	37.19	8.56	2.02	3.97	0.44	23.31	11.43		
3600.0	8.26	36.71	8.50	1.92	3.79	0.43	23.01	10.94		
3700.0	7.85	36.22	8.32	1.86	3.62	0.42	22.59	10.60		
3800.0	7.41	35.38	8.17	1.75	3.23	0.40	22.07	10.37		
3900.0	6.98	34.60	8.24	1.72	3.06	0.40	21.48	9.86		
4000.0	6.60	33.52	8.12	1.68	2.72	0.40	21.64	9.63		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.8V, Id = 50.72mA, R1=267 Ohms @ Temperature = +25degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	FREQ (MHz)	Noise Figure (dB)
					K	Measure				
500.0	21.62	41.85	2.00	6.93	1.87	1.23	26.95	16.34	500.0	1.16
525.0	22.38	40.96	2.59	7.74	1.90	1.21	27.32	16.79	600.0	1.01
550.0	22.99	39.98	3.27	8.59	1.89	1.19	27.42	17.22	700.0	0.52
575.0	23.46	39.30	4.08	9.49	1.92	1.15	27.48	17.62	800.0	0.49
600.0	23.82	38.92	4.99	10.38	1.98	1.12	27.72	17.73	900.0	0.45
625.0	24.06	38.22	5.98	11.31	1.96	1.08	27.83	18.37	1000.0	0.36
650.0	24.21	38.13	7.08	12.21	2.05	1.05	28.15	18.54	1100.0	0.45
675.0	24.29	37.79	8.28	13.02	2.07	1.02	28.33	18.84	1200.0	0.50
700.0	24.32	37.47	9.56	13.83	2.09	1.00	28.75	19.06	1300.0	0.43
725.0	24.29	37.43	10.93	14.56	2.15	0.98	29.16	19.08	1400.0	0.57
750.0	24.22	37.55	12.41	15.21	2.25	0.97	29.32	19.40	1500.0	0.60
775.0	24.14	37.23	14.06	15.84	2.24	0.95	29.99	19.43	1600.0	0.61
800.0	24.02	37.31	15.81	16.42	2.32	0.95	30.16	19.36	1700.0	0.58
825.0	23.90	37.13	17.82	16.99	2.33	0.94	30.16	19.70	1800.0	0.77
850.0	23.76	37.19	20.00	17.52	2.40	0.94	30.29	19.73	1900.0	0.68
875.0	23.61	37.10	22.28	18.03	2.43	0.94	30.85	19.51	2000.0	0.80
900.0	23.45	37.13	24.55	18.51	2.48	0.94	30.42	20.04	2100.0	0.79
925.0	23.29	37.10	25.87	18.85	2.52	0.95	30.71	19.68	2200.0	0.80
950.0	23.13	37.16	25.95	19.19	2.58	0.95	30.60	19.61	2300.0	0.88
975.0	22.97	37.21	24.77	19.47	2.64	0.95	30.55	19.82	2400.0	0.93
1000.0	22.80	37.20	23.26	19.64	2.68	0.96	30.05	19.57	2500.0	1.08
1050.0	22.47	37.33	20.74	19.78	2.80	0.97	30.35	19.57	2600.0	1.07
1100.0	22.14	37.26	18.70	19.50	2.86	0.97	30.48	19.55	2700.0	1.25
1150.0	21.80	37.51	17.14	18.89	3.03	0.98	30.57	19.60	2800.0	1.19
1200.0	21.48	37.34	16.20	18.14	3.05	0.99	30.68	19.62	2900.0	1.28
1250.0	21.16	37.39	15.32	17.25	3.15	0.99	30.38	19.68	3000.0	1.32
1300.0	20.85	37.39	14.73	16.23	3.22	0.99	29.97	19.37	3100.0	1.38
1350.0	20.53	37.51	14.25	15.26	3.34	0.99	30.28	19.15	3200.0	1.55
1400.0	20.23	37.50	13.74	14.33	3.40	1.00	29.67	18.96	3300.0	1.56
1500.0	19.62	37.72	12.94	12.65	3.62	0.99	29.88	19.17	3400.0	1.61
1550.0	19.32	37.80	12.70	11.86	3.72	0.98	29.83	18.43	3500.0	1.58
1600.0	19.02	37.90	12.48	11.15	3.82	0.98	29.87	18.53	3600.0	1.78
1700.0	18.43	38.18	12.03	9.82	4.05	0.96	29.32	17.80	3700.0	1.73
1800.0	17.83	38.38	11.53	8.70	4.24	0.93	29.56	17.83	3800.0	1.79
1900.0	17.21	38.79	11.16	7.73	4.54	0.91	29.09	17.65	3900.0	1.91
2000.0	16.56	38.50	11.04	7.21	4.59	0.89	28.62	17.07	4000.0	1.77
2100.0	16.09	38.88	10.71	6.35	4.75	0.85	28.62	17.01		
2200.0	15.53	38.83	10.48	5.64	4.72	0.81	28.80	16.92		
2300.0	14.95	39.28	10.28	5.07	5.00	0.77	27.75	15.92		
2400.0	14.37	39.60	10.04	4.56	5.20	0.73	27.36	15.46		
2500.0	13.78	39.85	9.85	4.17	5.39	0.70	27.16	15.15		
2600.0	13.21	40.21	9.71	3.81	5.65	0.66	26.22	14.50		
2700.0	12.64	39.97	9.51	3.49	5.50	0.63	26.05	14.30		
2800.0	12.07	39.55	9.27	3.23	5.26	0.60	25.77	13.89		
2900.0	11.54	39.52	9.18	3.01	5.29	0.58	25.41	13.45		
3000.0	11.00	39.44	9.04	2.81	5.27	0.55	24.53	12.99		
3100.0	10.48	39.27	8.84	2.61	5.16	0.53	24.69	12.52		
3200.0	9.97	39.01	8.76	2.44	5.03	0.51	23.56	11.90		
3300.0	9.50	38.38	8.65	2.27	4.63	0.48	23.54	11.57		
3400.0	9.03	37.87	8.52	2.13	4.33	0.46	23.01	11.30		
3500.0	8.57	37.16	8.42	2.01	3.99	0.44	22.24	10.79		
3600.0	8.08	36.84	8.37	1.90	3.87	0.43	22.01	10.32		
3700.0	7.68	36.31	8.18	1.85	3.68	0.42	21.58	10.04		
3800.0	7.24	35.22	8.04	1.74	3.20	0.41	21.17	9.81		
3900.0	6.81	35.13	8.08	1.73	3.33	0.40	20.56	9.30		
4000.0	6.44	33.75	7.98	1.68	2.84	0.40	20.73	9.03		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd =4.2V, Id = 57.17mA, R1=267 Ohms @ Temperature = +25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	21.93	42.37	2.03	6.92	1.92	1.23	28.05	17.28	500.0	1.15
525.0	22.67	41.37	2.61	7.72	1.93	1.21	28.24	17.78	600.0	0.92
550.0	23.25	40.64	3.29	8.54	1.96	1.19	28.26	18.21	700.0	0.50
575.0	23.71	40.04	4.08	9.40	2.00	1.16	28.32	18.58	800.0	0.48
600.0	24.06	39.41	4.96	10.26	2.02	1.12	28.52	18.72	900.0	0.41
625.0	24.29	38.99	5.93	11.14	2.05	1.09	28.51	19.31	1000.0	0.34
650.0	24.43	38.62	6.98	11.99	2.09	1.06	28.91	19.56	1100.0	0.42
675.0	24.51	38.47	8.13	12.73	2.15	1.03	29.18	19.81	1200.0	0.47
700.0	24.53	38.33	9.34	13.46	2.20	1.01	29.78	20.02	1300.0	0.41
725.0	24.50	38.02	10.63	14.14	2.22	0.99	30.12	20.02	1400.0	0.55
750.0	24.43	37.90	12.02	14.74	2.26	0.97	29.91	20.36	1500.0	0.61
775.0	24.35	37.94	13.53	15.30	2.34	0.96	30.48	20.36	1600.0	0.59
800.0	24.25	37.78	15.16	15.84	2.36	0.95	30.54	20.28	1700.0	0.59
825.0	24.12	37.92	16.99	16.39	2.46	0.95	30.63	20.64	1800.0	0.74
850.0	23.98	37.81	18.99	16.88	2.49	0.95	30.80	20.63	1900.0	0.67
875.0	23.84	37.80	21.19	17.36	2.54	0.95	30.97	20.40	2000.0	0.80
900.0	23.69	37.86	23.69	17.79	2.61	0.95	30.83	20.93	2100.0	0.77
925.0	23.53	37.94	26.21	18.10	2.68	0.95	31.22	20.59	2200.0	0.77
950.0	23.38	37.79	28.14	18.48	2.69	0.95	31.36	20.49	2300.0	0.91
975.0	23.22	37.99	28.05	18.75	2.80	0.95	30.97	20.70	2400.0	0.93
1000.0	23.05	37.85	26.63	18.98	2.80	0.96	30.92	20.42	2500.0	1.05
1050.0	22.73	38.18	23.46	19.21	3.00	0.96	30.90	20.42	2600.0	1.06
1100.0	22.40	38.02	20.79	19.04	3.04	0.97	31.15	20.38	2700.0	1.24
1150.0	22.07	38.02	18.82	18.61	3.13	0.98	30.78	20.40	2800.0	1.22
1200.0	21.76	37.96	17.71	18.00	3.19	0.98	30.89	20.45	2900.0	1.29
1250.0	21.44	38.05	16.67	17.20	3.31	0.98	30.69	20.47	3000.0	1.18
1300.0	21.13	38.12	15.97	16.25	3.42	0.99	30.68	20.15	3100.0	1.38
1350.0	20.82	38.13	15.41	15.34	3.50	0.99	30.40	19.95	3200.0	1.48
1400.0	20.52	38.27	14.81	14.44	3.63	0.99	30.17	19.74	3300.0	1.56
1500.0	19.92	38.29	13.87	12.78	3.78	0.98	30.25	19.92	3400.0	1.59
1550.0	19.62	38.45	13.59	12.00	3.92	0.98	30.03	19.20	3500.0	1.52
1600.0	19.33	38.38	13.34	11.28	3.96	0.97	30.08	19.30	3600.0	1.72
1700.0	18.74	38.51	12.81	9.94	4.13	0.95	29.68	18.55	3700.0	1.80
1800.0	18.15	38.80	12.25	8.81	4.36	0.93	29.75	18.62	3800.0	1.89
1900.0	17.53	39.09	11.81	7.83	4.61	0.90	29.80	18.40	3900.0	1.86
2000.0	16.88	38.95	11.68	7.31	4.74	0.88	29.36	17.83	4000.0	1.83
2100.0	16.42	39.53	11.29	6.45	5.03	0.84	29.38	17.77		
2200.0	15.86	39.45	11.00	5.72	4.99	0.80	29.30	17.73		
2300.0	15.29	40.02	10.78	5.15	5.36	0.77	28.73	16.76		
2400.0	14.70	39.57	10.51	4.64	5.10	0.73	28.42	16.33		
2500.0	14.12	39.78	10.26	4.22	5.25	0.70	28.40	16.06		
2600.0	13.55	40.16	10.13	3.87	5.53	0.66	27.92	15.48		
2700.0	12.98	40.06	9.90	3.55	5.47	0.63	27.51	15.14		
2800.0	12.41	39.86	9.66	3.28	5.36	0.60	27.38	14.80		
2900.0	11.88	39.60	9.54	3.05	5.24	0.58	27.24	14.40		
3000.0	11.34	39.38	9.38	2.85	5.15	0.55	26.31	13.96		
3100.0	10.82	39.18	9.16	2.65	5.02	0.53	26.46	13.56		
3200.0	10.31	38.93	9.09	2.48	4.91	0.51	25.45	12.89		
3300.0	9.84	38.04	8.96	2.31	4.39	0.48	25.44	12.56		
3400.0	9.37	37.80	8.81	2.16	4.23	0.46	24.83	12.37		
3500.0	8.91	37.05	8.72	2.04	3.87	0.45	24.28	11.91		
3600.0	8.44	36.93	8.63	1.93	3.85	0.43	24.00	11.44		
3700.0	8.03	36.13	8.46	1.87	3.54	0.42	23.47	11.15		
3800.0	7.59	35.16	8.31	1.76	3.12	0.41	22.90	10.89		
3900.0	7.16	34.53	8.38	1.74	3.02	0.40	22.34	10.41		
4000.0	6.78	33.61	8.27	1.69	2.74	0.40	22.39	10.16		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4V, Id = 53.52mA, R1=267 Ohms @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	22.14	42.36	1.83	6.64	1.76	1.22	27.38	16.47	500.0	0.73
525.0	22.88	41.83	2.37	7.39	1.86	1.22	27.85	16.94	600.0	0.71
550.0	23.47	41.10	2.99	8.15	1.89	1.20	27.90	17.37	700.0	0.26
575.0	23.94	40.30	3.71	8.97	1.91	1.17	27.84	17.72	800.0	0.23
600.0	24.30	39.63	4.52	9.78	1.92	1.13	28.14	17.85	900.0	0.20
625.0	24.54	39.31	5.40	10.62	1.98	1.10	28.67	18.46	1000.0	0.10
650.0	24.70	39.00	6.35	11.46	2.03	1.07	28.62	18.69	1100.0	0.18
675.0	24.79	38.72	7.39	12.24	2.08	1.05	29.06	19.03	1200.0	0.21
700.0	24.84	38.61	8.48	12.95	2.14	1.02	29.69	19.33	1300.0	0.17
725.0	24.82	38.15	9.63	13.66	2.12	1.00	29.85	19.40	1400.0	0.26
750.0	24.77	38.06	10.87	14.28	2.18	0.98	30.01	19.72	1500.0	0.31
775.0	24.70	37.97	12.16	14.81	2.22	0.97	30.44	19.78	1600.0	0.30
800.0	24.60	37.99	13.49	15.32	2.29	0.96	30.91	19.73	1700.0	0.26
825.0	24.49	37.92	14.96	15.83	2.33	0.95	30.91	20.08	1800.0	0.37
850.0	24.36	38.08	16.49	16.30	2.43	0.95	30.64	20.09	1900.0	0.31
875.0	24.22	37.99	18.06	16.75	2.47	0.95	31.03	19.89	2000.0	0.40
900.0	24.08	37.85	19.86	17.19	2.48	0.95	30.95	20.43	2100.0	0.40
925.0	23.93	37.91	21.76	17.55	2.55	0.95	31.10	20.07	2200.0	0.37
950.0	23.79	37.78	23.93	17.90	2.56	0.95	31.27	20.00	2300.0	0.47
975.0	23.63	37.83	25.88	18.27	2.62	0.95	31.17	20.19	2400.0	0.49
1000.0	23.48	37.77	27.10	18.50	2.65	0.95	30.40	19.96	2500.0	0.60
1050.0	23.16	38.02	26.53	18.89	2.82	0.96	30.80	19.97	2600.0	0.59
1100.0	22.84	38.14	23.74	18.75	2.95	0.96	30.79	19.93	2700.0	0.73
1150.0	22.53	37.99	21.32	18.34	2.98	0.97	30.61	19.97	2800.0	0.66
1200.0	22.22	37.81	20.00	17.88	3.01	0.97	30.64	20.00	2900.0	0.71
1250.0	21.91	37.90	18.66	17.19	3.12	0.97	30.49	20.05	3000.0	0.69
1300.0	21.61	37.90	17.77	16.32	3.19	0.97	30.26	19.74	3100.0	0.83
1350.0	21.31	37.88	17.04	15.35	3.26	0.97	30.37	19.52	3200.0	0.87
1400.0	21.01	37.99	16.29	14.43	3.37	0.97	30.27	19.35	3300.0	0.87
1500.0	20.43	38.03	15.24	12.75	3.52	0.97	29.96	19.55	3400.0	0.94
1550.0	20.13	38.32	14.85	12.02	3.70	0.96	29.76	18.82	3500.0	0.88
1600.0	19.84	38.10	14.50	11.32	3.67	0.96	29.80	18.90	3600.0	0.97
1700.0	19.27	38.33	13.80	9.94	3.86	0.94	29.37	18.15	3700.0	0.98
1800.0	18.68	38.66	13.22	8.76	4.09	0.91	29.63	18.21	3800.0	0.99
1900.0	18.06	39.14	12.66	7.75	4.41	0.89	29.20	17.92	3900.0	1.16
2000.0	17.39	38.79	12.36	7.26	4.43	0.87	28.83	17.37	4000.0	0.96
2100.0	16.96	39.42	11.96	6.37	4.71	0.83	28.97	17.28		
2200.0	16.41	38.98	11.61	5.60	4.44	0.79	28.71	17.20		
2300.0	15.84	39.66	11.26	5.02	4.80	0.75	28.17	16.26		
2400.0	15.26	39.78	10.91	4.50	4.86	0.71	27.73	15.89		
2500.0	14.67	40.05	10.74	4.06	5.01	0.67	27.55	15.53		
2600.0	14.10	40.20	10.48	3.68	5.09	0.64	26.80	15.06		
2700.0	13.54	40.12	10.12	3.37	5.01	0.61	26.55	14.83		
2800.0	12.97	40.45	9.92	3.11	5.23	0.58	26.21	14.42		
2900.0	12.43	39.83	9.77	2.88	4.87	0.55	25.97	14.08		
3000.0	11.89	39.81	9.49	2.72	4.91	0.54	25.12	13.69		
3100.0	11.38	39.46	9.32	2.52	4.69	0.51	25.19	13.15		
3200.0	10.87	39.58	9.25	2.35	4.77	0.49	24.23	12.66		
3300.0	10.41	38.87	9.00	2.18	4.31	0.46	24.13	12.36		
3400.0	9.99	38.43	8.90	2.04	4.05	0.44	23.76	12.12		
3500.0	9.54	37.71	8.84	1.86	3.61	0.41	23.03	11.66		
3600.0	9.07	37.31	8.59	1.75	3.42	0.40	22.79	11.24		
3700.0	8.69	36.58	8.48	1.70	3.17	0.39	22.32	10.88		
3800.0	8.27	35.72	8.47	1.58	2.79	0.37	21.97	10.74		
3900.0	7.86	35.43	8.39	1.56	2.79	0.37	21.31	10.29		
4000.0	7.52	34.20	8.24	1.51	2.40	0.36	21.57	10.01		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.8V, Id = 50.44mA, R1=267 Ohms @ Temperature = -45degC

FREQ (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	FREQ (MHz)	Noise Figure (dB)
					K	Measure				
500.0	21.94	41.79	1.81	6.65	1.70	1.22	26.76	15.84	500.0	0.77
525.0	22.69	41.40	2.34	7.41	1.81	1.22	27.31	16.31	600.0	0.67
550.0	23.30	40.44	2.97	8.18	1.82	1.19	27.26	16.68	700.0	0.28
575.0	23.77	40.14	3.69	9.01	1.91	1.17	27.29	17.06	800.0	0.26
600.0	24.14	39.30	4.51	9.85	1.90	1.13	27.73	17.12	900.0	0.18
625.0	24.39	38.84	5.39	10.71	1.92	1.10	27.81	17.80	1000.0	0.17
650.0	24.56	38.70	6.37	11.59	2.01	1.07	28.29	18.00	1100.0	0.22
675.0	24.66	38.26	7.44	12.39	2.02	1.04	28.42	18.37	1200.0	0.27
700.0	24.71	38.15	8.55	13.16	2.08	1.02	29.06	18.61	1300.0	0.22
725.0	24.69	38.01	9.75	13.88	2.13	1.00	29.48	18.74	1400.0	0.31
750.0	24.64	37.73	11.02	14.53	2.15	0.98	29.31	19.07	1500.0	0.32
775.0	24.57	37.63	12.37	15.08	2.19	0.97	29.94	19.16	1600.0	0.33
800.0	24.46	37.64	13.76	15.65	2.25	0.96	30.24	19.13	1700.0	0.29
825.0	24.36	37.69	15.29	16.19	2.32	0.95	30.32	19.50	1800.0	0.41
850.0	24.22	37.56	16.87	16.64	2.35	0.95	30.33	19.53	1900.0	0.33
875.0	24.08	37.60	18.53	17.13	2.41	0.94	30.54	19.32	2000.0	0.43
900.0	23.94	37.47	20.34	17.57	2.43	0.94	30.28	19.84	2100.0	0.42
925.0	23.79	37.58	22.26	17.89	2.50	0.94	30.73	19.52	2200.0	0.40
950.0	23.64	37.52	24.30	18.28	2.53	0.94	30.68	19.46	2300.0	0.52
975.0	23.49	37.50	25.65	18.65	2.58	0.95	30.44	19.63	2400.0	0.55
1000.0	23.33	37.59	26.05	18.90	2.64	0.95	29.85	19.44	2500.0	0.63
1050.0	23.01	37.52	24.50	19.19	2.71	0.96	30.35	19.43	2600.0	0.64
1100.0	22.69	37.48	22.00	19.02	2.78	0.96	30.31	19.44	2700.0	0.77
1150.0	22.37	37.65	19.92	18.50	2.91	0.97	30.09	19.47	2800.0	0.72
1200.0	22.06	37.61	18.79	17.94	2.98	0.97	30.22	19.49	2900.0	0.72
1250.0	21.75	37.61	17.61	17.21	3.06	0.98	30.18	19.55	3000.0	0.71
1300.0	21.44	37.58	16.84	16.27	3.13	0.98	29.87	19.27	3100.0	0.74
1350.0	21.14	37.68	16.19	15.28	3.23	0.98	30.07	19.03	3200.0	0.91
1400.0	20.84	37.76	15.52	14.35	3.33	0.98	29.41	18.84	3300.0	0.91
1500.0	20.25	37.79	14.55	12.68	3.46	0.97	29.82	19.09	3400.0	1.02
1550.0	19.95	37.88	14.20	11.93	3.56	0.97	29.38	18.38	3500.0	0.91
1600.0	19.66	38.10	13.87	11.23	3.71	0.96	29.46	18.45	3600.0	1.11
1700.0	19.08	38.33	13.27	9.85	3.91	0.94	29.12	17.69	3700.0	1.07
1800.0	18.49	38.41	12.73	8.68	4.02	0.92	29.34	17.73	3800.0	1.03
1900.0	17.87	38.52	12.22	7.69	4.15	0.89	28.88	17.52	3900.0	1.18
2000.0	17.20	38.41	11.91	7.19	4.29	0.87	28.44	16.89	4000.0	0.97
2100.0	16.76	38.88	11.57	6.32	4.47	0.83	28.41	16.77		
2200.0	16.21	38.77	11.25	5.54	4.38	0.79	28.45	16.62		
2300.0	15.63	39.50	10.93	4.97	4.77	0.75	27.59	15.64		
2400.0	15.05	39.60	10.62	4.45	4.80	0.71	27.09	15.33		
2500.0	14.47	39.73	10.46	4.02	4.88	0.67	26.96	14.99		
2600.0	13.90	39.95	10.23	3.65	4.99	0.64	26.05	14.49		
2700.0	13.33	39.93	9.88	3.34	4.95	0.61	25.90	14.15		
2800.0	12.76	39.81	9.69	3.07	4.89	0.58	25.59	13.86		
2900.0	12.22	40.00	9.56	2.85	5.03	0.55	25.27	13.47		
3000.0	11.68	40.03	9.29	2.68	5.09	0.53	24.32	13.07		
3100.0	11.17	39.88	9.13	2.50	4.99	0.51	24.54	12.59		
3200.0	10.66	39.55	9.06	2.33	4.80	0.48	23.37	12.01		
3300.0	10.21	39.02	8.83	2.15	4.42	0.46	23.39	11.71		
3400.0	9.78	38.58	8.73	1.99	4.12	0.44	22.95	11.46		
3500.0	9.33	37.61	8.67	1.84	3.60	0.41	22.17	10.99		
3600.0	8.86	37.82	8.42	1.74	3.67	0.40	21.89	10.55		
3700.0	8.47	36.90	8.32	1.68	3.32	0.39	21.46	10.20		
3800.0	8.06	35.70	8.30	1.56	2.82	0.37	21.13	10.02		
3900.0	7.64	35.76	8.22	1.55	2.95	0.37	20.44	9.62		
4000.0	7.30	34.39	8.07	1.50	2.49	0.36	20.81	9.24		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.2V, Id = 53.41mA, R1=267 Ohms @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	22.17	42.83	1.83	6.61	1.81	1.23	27.53	16.93	500.0	0.76
525.0	22.91	42.14	2.36	7.36	1.90	1.22	28.13	17.36	600.0	0.73
550.0	23.50	41.28	2.98	8.10	1.91	1.20	27.94	17.74	700.0	0.29
575.0	23.96	40.40	3.69	8.89	1.92	1.16	27.95	18.10	800.0	0.26
600.0	24.32	40.20	4.49	9.66	2.01	1.14	28.24	18.28	900.0	0.21
625.0	24.56	39.66	5.35	10.51	2.03	1.11	28.46	18.89	1000.0	0.15
650.0	24.72	39.20	6.29	11.30	2.05	1.08	28.90	19.18	1100.0	0.23
675.0	24.82	39.09	7.31	12.05	2.13	1.05	29.22	19.49	1200.0	0.28
700.0	24.86	38.42	8.39	12.74	2.08	1.02	29.81	19.80	1300.0	0.18
725.0	24.85	38.55	9.52	13.40	2.19	1.00	30.33	19.88	1400.0	0.32
750.0	24.80	38.52	10.73	14.02	2.27	0.99	30.16	20.20	1500.0	0.34
775.0	24.73	38.29	12.00	14.52	2.28	0.97	30.75	20.27	1600.0	0.34
800.0	24.63	38.28	13.30	15.02	2.34	0.96	31.20	20.22	1700.0	0.28
825.0	24.53	38.24	14.73	15.50	2.40	0.96	31.00	20.56	1800.0	0.43
850.0	24.39	38.25	16.21	15.94	2.46	0.95	30.98	20.58	1900.0	0.36
875.0	24.26	38.22	17.75	16.39	2.51	0.95	31.28	20.39	2000.0	0.45
900.0	24.11	38.20	19.50	16.77	2.56	0.95	31.04	20.92	2100.0	0.41
925.0	23.97	38.32	21.33	17.13	2.64	0.95	31.39	20.55	2200.0	0.42
950.0	23.82	38.11	23.43	17.49	2.64	0.95	31.29	20.49	2300.0	0.49
975.0	23.67	38.37	25.32	17.83	2.76	0.95	31.46	20.70	2400.0	0.52
1000.0	23.52	38.31	26.76	18.11	2.79	0.95	30.77	20.47	2500.0	0.62
1050.0	23.20	38.26	26.85	18.46	2.87	0.96	31.06	20.43	2600.0	0.59
1100.0	22.89	38.38	24.25	18.39	3.01	0.96	30.82	20.43	2700.0	0.75
1150.0	22.57	38.38	21.76	18.06	3.09	0.97	30.91	20.46	2800.0	0.67
1200.0	22.27	38.25	20.35	17.65	3.14	0.97	30.99	20.48	2900.0	0.77
1250.0	21.96	38.23	18.98	17.06	3.22	0.97	30.89	20.53	3000.0	0.71
1300.0	21.66	38.34	18.06	16.22	3.34	0.97	30.44	20.23	3100.0	0.80
1350.0	21.35	38.45	17.28	15.30	3.46	0.97	30.49	19.99	3200.0	0.89
1400.0	21.06	38.68	16.54	14.40	3.63	0.97	30.06	19.80	3300.0	0.91
1500.0	20.48	38.41	15.46	12.78	3.66	0.97	30.24	20.01	3400.0	0.97
1550.0	20.18	38.35	15.04	12.04	3.70	0.96	29.71	19.27	3500.0	0.90
1600.0	19.89	38.61	14.66	11.33	3.87	0.96	29.82	19.35	3600.0	1.09
1700.0	19.32	38.76	13.96	9.96	4.04	0.94	29.40	18.57	3700.0	1.10
1800.0	18.74	39.00	13.37	8.79	4.24	0.91	29.77	18.62	3800.0	1.13
1900.0	18.12	39.41	12.78	7.79	4.54	0.89	29.27	18.39	3900.0	1.15
2000.0	17.44	39.25	12.48	7.31	4.67	0.87	28.69	17.77	4000.0	0.98
2100.0	17.01	40.02	12.08	6.41	5.04	0.83	28.78	17.70		
2200.0	16.47	39.91	11.71	5.63	4.94	0.79	28.81	17.54		
2300.0	15.90	40.18	11.35	5.04	5.09	0.75	28.08	16.73		
2400.0	15.32	39.84	11.01	4.53	4.88	0.71	27.67	16.33		
2500.0	14.74	39.86	10.84	4.08	4.89	0.68	27.43	15.92		
2600.0	14.17	40.31	10.59	3.70	5.14	0.64	26.95	15.45		
2700.0	13.61	40.01	10.22	3.39	4.95	0.61	26.60	15.27		
2800.0	13.03	40.42	10.02	3.12	5.20	0.58	26.33	14.90		
2900.0	12.49	39.96	9.90	2.89	4.95	0.55	26.01	14.51		
3000.0	11.96	39.66	9.62	2.73	4.82	0.54	25.27	14.15		
3100.0	11.45	39.34	9.45	2.54	4.63	0.51	25.30	13.72		
3200.0	10.94	39.47	9.39	2.36	4.71	0.48	24.37	13.04		
3300.0	10.49	38.96	9.13	2.19	4.36	0.46	24.29	12.74		
3400.0	10.06	38.32	9.03	2.04	3.98	0.44	23.97	12.60		
3500.0	9.62	37.39	8.99	1.87	3.49	0.42	23.28	12.16		
3600.0	9.15	37.33	8.71	1.77	3.43	0.40	23.01	11.74		
3700.0	8.77	36.74	8.62	1.71	3.24	0.39	22.63	11.42		
3800.0	8.35	35.54	8.61	1.59	2.75	0.37	22.23	11.29		
3900.0	7.94	35.20	8.54	1.57	2.73	0.37	21.66	10.77		
4000.0	7.60	33.95	8.41	1.51	2.33	0.36	21.87	10.52		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4V, Id = 53.86mA, R1=267 Ohms @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	21.27	42.46	2.05	6.95	2.08	1.23	27.07	16.50	500.0	1.51
525.0	22.04	40.86	2.63	7.74	1.96	1.21	27.32	16.95	600.0	1.19
550.0	22.67	40.42	3.32	8.57	2.05	1.19	27.46	17.33	700.0	0.68
575.0	23.15	39.72	4.15	9.43	2.07	1.16	27.25	17.80	800.0	0.63
600.0	23.53	38.96	5.09	10.29	2.06	1.12	27.57	17.83	900.0	0.62
625.0	23.77	38.84	6.11	11.15	2.16	1.09	27.73	18.51	1000.0	0.55
650.0	23.93	38.28	7.24	11.98	2.14	1.05	27.80	18.71	1100.0	0.61
675.0	24.01	38.08	8.49	12.71	2.20	1.02	28.20	18.99	1200.0	0.71
700.0	24.04	38.16	9.80	13.37	2.31	1.00	28.57	19.24	1300.0	0.63
725.0	24.01	37.89	11.19	14.00	2.33	0.98	28.65	19.27	1400.0	0.76
750.0	23.94	37.92	12.74	14.57	2.41	0.97	28.95	19.60	1500.0	0.82
775.0	23.86	37.99	14.45	15.05	2.49	0.96	29.37	19.64	1600.0	0.84
800.0	23.74	37.91	16.30	15.56	2.54	0.95	29.50	19.60	1700.0	0.81
825.0	23.62	37.89	18.41	16.05	2.59	0.95	29.73	19.96	1800.0	0.99
850.0	23.47	37.59	20.66	16.54	2.57	0.94	29.71	19.96	1900.0	0.93
875.0	23.32	37.76	22.89	17.00	2.67	0.95	29.90	19.74	2000.0	1.08
900.0	23.17	37.78	24.51	17.43	2.73	0.95	30.04	20.25	2100.0	1.12
925.0	23.00	37.83	24.51	17.76	2.80	0.95	29.90	19.94	2200.0	1.12
950.0	22.84	37.99	23.59	18.06	2.90	0.96	30.16	19.85	2300.0	1.25
975.0	22.68	37.89	22.32	18.30	2.91	0.96	29.76	20.09	2400.0	1.29
1000.0	22.51	38.07	20.96	18.46	3.02	0.96	29.41	19.80	2500.0	1.45
1050.0	22.17	37.92	18.95	18.50	3.07	0.97	29.65	19.85	2600.0	1.48
1100.0	21.83	38.14	17.27	18.32	3.23	0.98	29.93	19.82	2700.0	1.65
1150.0	21.50	38.49	15.95	18.00	3.46	0.99	30.07	19.87	2800.0	1.65
1200.0	21.18	38.29	15.03	17.52	3.47	1.00	30.09	19.93	2900.0	1.72
1250.0	20.85	38.36	14.21	16.93	3.59	1.00	29.86	19.93	3000.0	1.78
1300.0	20.53	38.50	13.73	16.07	3.74	1.01	29.63	19.65	3100.0	1.87
1350.0	20.22	38.51	13.31	15.18	3.82	1.01	29.42	19.44	3200.0	1.96
1400.0	19.92	38.57	12.90	14.32	3.93	1.01	29.36	19.26	3300.0	2.00
1500.0	19.31	38.68	12.15	12.75	4.14	1.00	29.52	19.47	3400.0	2.13
1550.0	19.01	38.77	11.90	12.03	4.26	1.00	29.22	18.73	3500.0	2.13
1600.0	18.72	39.16	11.72	11.36	4.53	0.99	29.29	18.84	3600.0	2.35
1700.0	18.14	39.33	11.38	10.05	4.76	0.97	28.88	18.09	3700.0	2.33
1800.0	17.53	39.65	10.93	8.94	5.06	0.95	28.86	18.17	3800.0	2.45
1900.0	16.92	39.68	10.55	7.99	5.19	0.93	29.13	17.99	3900.0	2.55
2000.0	16.31	39.47	10.52	7.47	5.29	0.91	28.97	17.37	4000.0	2.47
2100.0	15.82	40.14	10.30	6.63	5.72	0.87	29.00	17.33		
2200.0	15.26	39.98	10.02	5.89	5.63	0.83	29.17	17.26		
2300.0	14.69	40.44	9.92	5.32	6.00	0.79	28.65	16.32		
2400.0	14.12	39.92	9.78	4.83	5.69	0.76	28.24	15.91		
2500.0	13.53	40.24	9.59	4.41	5.97	0.72	28.22	15.60		
2600.0	12.97	40.29	9.49	4.05	6.06	0.69	27.93	15.09		
2700.0	12.41	40.04	9.40	3.72	5.93	0.66	27.65	14.83		
2800.0	11.84	39.67	9.17	3.44	5.71	0.63	27.49	14.40		
2900.0	11.30	39.52	9.09	3.20	5.67	0.60	27.24	13.94		
3000.0	10.77	39.39	9.03	3.00	5.67	0.58	26.58	13.47		
3100.0	10.24	38.65	8.85	2.79	5.20	0.55	26.43	13.05		
3200.0	9.72	38.37	8.80	2.62	5.09	0.53	25.47	12.42		
3300.0	9.22	37.82	8.75	2.45	4.79	0.51	25.54	12.03		
3400.0	8.76	37.17	8.66	2.31	4.45	0.49	24.73	11.81		
3500.0	8.29	36.59	8.54	2.21	4.21	0.47	24.08	11.38		
3600.0	7.81	35.97	8.52	2.10	3.96	0.46	23.83	10.94		
3700.0	7.38	35.64	8.37	2.03	3.87	0.45	23.22	10.55		
3800.0	6.91	34.67	8.21	1.93	3.44	0.43	22.59	10.34		
3900.0	6.45	34.25	8.32	1.93	3.49	0.43	22.01	9.78		
4000.0	6.08	33.02	8.26	1.85	3.01	0.42	21.96	9.57		



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 3.8V, Id = 50.72mA, R1=267 Ohms @ Temperature = +85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	21.12	41.84	2.03	6.96	1.98	1.23	26.63	16.06	500.0	1.51
525.0	21.89	40.90	2.61	7.77	2.00	1.22	26.95	16.51	600.0	1.20
550.0	22.53	40.20	3.31	8.61	2.03	1.19	27.02	16.88	700.0	0.72
575.0	23.03	39.10	4.14	9.49	1.98	1.15	26.98	17.30	800.0	0.65
600.0	23.41	38.87	5.09	10.39	2.07	1.12	27.10	17.39	900.0	0.59
625.0	23.66	38.41	6.13	11.28	2.10	1.08	27.32	18.03	1000.0	0.56
650.0	23.82	38.13	7.29	12.16	2.15	1.05	27.63	18.25	1100.0	0.64
675.0	23.91	37.90	8.55	12.92	2.20	1.02	27.69	18.53	1200.0	0.69
700.0	23.94	37.57	9.88	13.62	2.21	0.99	28.25	18.80	1300.0	0.61
725.0	23.90	37.64	11.33	14.28	2.30	0.98	28.29	18.82	1400.0	0.75
750.0	23.83	37.50	12.92	14.89	2.34	0.96	28.52	19.14	1500.0	0.84
775.0	23.75	37.29	14.65	15.40	2.35	0.95	28.89	19.20	1600.0	0.83
800.0	23.63	37.42	16.57	15.95	2.45	0.95	29.17	19.15	1700.0	0.84
825.0	23.51	37.47	18.73	16.50	2.52	0.95	29.45	19.52	1800.0	1.00
850.0	23.36	37.33	20.91	16.98	2.54	0.94	29.52	19.53	1900.0	0.95
875.0	23.21	37.42	22.83	17.47	2.61	0.95	29.52	19.33	2000.0	1.11
900.0	23.05	37.39	23.85	17.90	2.66	0.95	29.66	19.83	2100.0	1.09
925.0	22.88	37.17	23.39	18.24	2.64	0.95	29.68	19.52	2200.0	1.14
950.0	22.72	37.46	22.26	18.54	2.77	0.96	29.80	19.44	2300.0	1.22
975.0	22.55	37.56	21.09	18.77	2.85	0.96	29.68	19.66	2400.0	1.30
1000.0	22.38	37.45	19.86	18.86	2.86	0.96	29.08	19.40	2500.0	1.46
1050.0	22.03	37.83	18.04	18.89	3.08	0.98	29.66	19.45	2600.0	1.45
1100.0	21.69	37.63	16.53	18.58	3.10	0.98	29.73	19.44	2700.0	1.65
1150.0	21.35	37.81	15.28	18.14	3.24	0.99	29.60	19.48	2800.0	1.62
1200.0	21.03	37.71	14.45	17.58	3.29	1.00	29.79	19.52	2900.0	1.70
1250.0	20.69	38.00	13.69	16.89	3.48	1.01	29.58	19.58	3000.0	1.70
1300.0	20.38	38.13	13.24	15.98	3.62	1.01	29.34	19.27	3100.0	1.84
1350.0	20.07	38.11	12.86	15.06	3.70	1.01	29.21	19.06	3200.0	1.96
1400.0	19.76	38.20	12.46	14.18	3.81	1.01	29.00	18.88	3300.0	1.96
1500.0	19.15	38.44	11.77	12.59	4.06	1.01	29.06	19.12	3400.0	2.09
1550.0	18.84	38.54	11.54	11.88	4.19	1.00	29.02	18.36	3500.0	2.09
1600.0	18.55	38.62	11.36	11.21	4.30	1.00	28.92	18.47	3600.0	2.31
1700.0	17.96	38.78	11.05	9.90	4.50	0.98	28.81	17.71	3700.0	2.36
1800.0	17.35	38.96	10.63	8.80	4.71	0.95	28.77	17.79	3800.0	2.39
1900.0	16.73	39.20	10.28	7.86	4.95	0.93	28.87	17.58	3900.0	2.61
2000.0	16.12	38.96	10.27	7.34	5.03	0.91	28.53	16.98	4000.0	2.50
2100.0	15.62	39.73	10.06	6.51	5.50	0.87	28.58	16.93		
2200.0	15.06	39.37	9.79	5.79	5.27	0.83	28.46	16.92		
2300.0	14.49	40.17	9.70	5.23	5.86	0.79	27.92	15.89		
2400.0	13.91	40.13	9.56	4.73	5.87	0.75	27.60	15.43		
2500.0	13.32	40.22	9.38	4.34	5.99	0.72	27.34	15.26		
2600.0	12.76	40.48	9.31	3.98	6.24	0.69	26.97	14.57		
2700.0	12.20	39.89	9.21	3.66	5.87	0.65	26.66	14.31		
2800.0	11.62	39.69	9.00	3.38	5.76	0.63	26.29	13.86		
2900.0	11.08	39.65	8.92	3.15	5.80	0.60	26.11	13.42		
3000.0	10.55	39.00	8.86	2.95	5.45	0.58	25.22	12.95		
3100.0	10.02	38.63	8.68	2.75	5.22	0.55	25.21	12.49		
3200.0	9.49	38.56	8.64	2.58	5.25	0.53	24.17	11.89		
3300.0	9.00	37.80	8.59	2.42	4.82	0.50	24.20	11.46		
3400.0	8.53	37.41	8.49	2.28	4.62	0.48	23.52	11.25		
3500.0	8.06	36.70	8.37	2.17	4.28	0.47	22.90	10.82		
3600.0	7.58	36.20	8.35	2.06	4.09	0.45	22.57	10.34		
3700.0	7.15	35.88	8.20	2.00	4.01	0.44	22.01	9.99		
3800.0	6.68	34.74	8.06	1.91	3.52	0.43	21.46	9.81		
3900.0	6.22	34.36	8.16	1.90	3.57	0.43	20.90	9.20		
4000.0	5.85	33.16	8.09	1.83	3.09	0.42	20.94	8.98		



Typical Performance Data

Definitions:









Input Return Loss = -S11 (dB)
 Gain(Power Gain) = S21 (dB)
 Reverse Isolation = -S12 (dB)
 Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd =4.2V, Id = 57.08mA, R1=267 Ohms @ Temperature = +85degC








FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	FREQ	Noise Figure
					K	Measure				
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(MHz)	(dB)
500.0	21.42	42.37	2.07	6.94	2.03	1.23	27.46	16.88	500.0	1.47
525.0	22.18	41.77	2.65	7.72	2.11	1.22	27.75	17.37	600.0	1.18
550.0	22.80	40.60	3.34	8.54	2.06	1.19	27.82	17.75	700.0	0.70
575.0	23.28	39.81	4.16	9.39	2.07	1.15	27.71	18.14	800.0	0.64
600.0	23.64	39.43	5.09	10.22	2.13	1.12	27.94	18.27	900.0	0.57
625.0	23.88	39.15	6.10	11.07	2.19	1.09	28.20	18.88	1000.0	0.56
650.0	24.04	38.88	7.22	11.86	2.25	1.05	28.38	19.06	1100.0	0.61
675.0	24.12	38.50	8.45	12.58	2.27	1.02	28.62	19.38	1200.0	0.69
700.0	24.14	38.50	9.74	13.20	2.36	1.00	28.97	19.62	1300.0	0.61
725.0	24.11	38.46	11.11	13.82	2.43	0.98	29.00	19.64	1400.0	0.74
750.0	24.04	38.27	12.61	14.34	2.46	0.97	29.22	19.99	1500.0	0.83
775.0	23.96	38.27	14.27	14.83	2.53	0.96	29.67	20.01	1600.0	0.85
800.0	23.85	38.15	16.09	15.31	2.57	0.95	29.80	19.96	1700.0	0.82
825.0	23.73	38.19	18.15	15.79	2.64	0.95	29.96	20.32	1800.0	0.99
850.0	23.58	38.36	20.45	16.23	2.75	0.95	30.27	20.32	1900.0	0.95
875.0	23.43	38.06	22.82	16.70	2.73	0.95	30.24	20.10	2000.0	1.09
900.0	23.28	38.19	24.86	17.12	2.82	0.95	30.41	20.61	2100.0	1.06
925.0	23.11	38.21	25.57	17.47	2.88	0.95	30.39	20.29	2200.0	1.11
950.0	22.96	38.17	24.86	17.74	2.92	0.95	30.43	20.22	2300.0	1.20
975.0	22.79	38.13	23.53	17.99	2.96	0.96	30.20	20.45	2400.0	1.27
1000.0	22.62	38.22	22.01	18.11	3.03	0.96	29.97	20.15	2500.0	1.44
1050.0	22.29	38.43	19.81	18.25	3.20	0.97	30.30	20.21	2600.0	1.43
1100.0	21.95	38.42	18.00	18.12	3.30	0.98	30.41	20.17	2700.0	1.59
1150.0	21.62	38.69	16.52	17.83	3.49	0.99	30.70	20.23	2800.0	1.58
1200.0	21.30	38.72	15.58	17.39	3.60	0.99	30.64	20.26	2900.0	1.70
1250.0	20.97	38.77	14.71	16.87	3.72	1.00	30.65	20.30	3000.0	1.66
1300.0	20.66	38.73	14.18	16.01	3.79	1.00	30.20	19.99	3100.0	1.81
1350.0	20.35	38.89	13.74	15.16	3.96	1.00	29.76	19.78	3200.0	1.99
1400.0	20.05	38.95	13.31	14.33	4.07	1.00	29.70	19.60	3300.0	1.99
1500.0	19.45	39.22	12.51	12.77	4.36	1.00	29.93	19.82	3400.0	2.09
1550.0	19.14	39.30	12.26	12.07	4.48	0.99	29.30	19.08	3500.0	2.04
1600.0	18.85	39.31	12.05	11.40	4.57	0.99	29.36	19.20	3600.0	2.24
1700.0	18.27	39.50	11.70	10.09	4.81	0.97	29.18	18.44	3700.0	2.33
1800.0	17.67	39.82	11.21	8.98	5.11	0.95	29.37	18.53	3800.0	2.42
1900.0	17.06	40.28	10.81	8.02	5.52	0.92	29.67	18.36	3900.0	2.49
2000.0	16.45	39.79	10.79	7.52	5.46	0.90	29.39	17.74	4000.0	2.34
2100.0	15.96	40.48	10.56	6.66	5.91	0.87	29.61	17.70		
2200.0	15.40	40.09	10.25	5.92	5.66	0.83	29.40	17.65		
2300.0	14.83	40.18	10.15	5.35	5.79	0.79	29.02	16.76		
2400.0	14.26	40.38	9.99	4.85	5.97	0.76	28.76	16.35		
2500.0	13.68	40.72	9.78	4.44	6.27	0.72	28.93	16.08		
2600.0	13.12	40.64	9.70	4.07	6.28	0.69	28.85	15.53		
2700.0	12.56	40.41	9.59	3.75	6.16	0.66	28.59	15.32		
2800.0	11.98	39.72	9.36	3.45	5.71	0.63	28.26	14.84		
2900.0	11.44	39.57	9.27	3.22	5.68	0.60	28.26	14.42		
3000.0	10.91	39.11	9.20	3.02	5.45	0.58	27.59	13.94		
3100.0	10.39	38.62	9.02	2.81	5.15	0.55	27.46	13.52		
3200.0	9.86	38.35	8.96	2.64	5.05	0.53	26.63	12.90		
3300.0	9.37	37.61	8.92	2.47	4.64	0.51	26.72	12.56		
3400.0	8.91	37.09	8.81	2.33	4.38	0.49	25.83	12.40		
3500.0	8.44	36.63	8.69	2.22	4.19	0.47	25.27	11.91		
3600.0	7.96	36.20	8.68	2.11	4.05	0.46	24.97	11.43		
3700.0	7.53	35.27	8.52	2.04	3.68	0.45	24.28	11.14		
3800.0	7.06	34.56	8.36	1.93	3.38	0.43	23.61	10.84		
3900.0	6.60	34.13	8.48	1.93	3.40	0.43	23.05	10.36		
4000.0	6.23	33.09	8.43	1.85	3.02	0.42	22.86	10.11		



Typical Performance Curves





Typical Performance Curves



Outline Dimensions

PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
MC1631	.079 (2.00)	.079 (2.00)	.022 (.55)	.047 (1.20)	.024 (.60)	.009 (.23)	.014 (.35)	.020 (.50)	.008 (.20)	.002 (.05)	.106 (2.70)	.049 (1.25)	.026 (.65)	.031 (.80)

CASE #.	Q	R	WT, GRAM
MC1631	.010 (.25)	.012 (.30)	.006

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination finish:
For RoHS Case Styles: Matte-Tin plate. All models, (+) suffix.
3. Lead #1 identifier shall be located in the cross-hatched area shown.
Identifier may be either a molded or marked feature.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F108



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	4	7	Small quantity standards	20
				50
				100
				200
				500
				1000
		7	Standard	2000
				3000

Note: Please Consult individual data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M131518	NEW RELEASE	05/12/11	PW	CW
A	M135045	UPDATED NOTE 2 & REMOVED TABLE	12/30/11	AV	DJ

SUGGESTED MOUNTING CONFIGURATION FOR MC1631 CASE STYLE, "08AM07" PIN CODE



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010'' \pm .001''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. 0402 SIZE CHIP FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUE REFER TO TB-615+.
 3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

PW

04/19/11

TOLERANCES ON:

CHECKED

AV

05/12/11

2 PL DECIMALS \pm

APPROVED


CW

05/12/11

3 PL DECIMALS \pm .005

ANGLES \pm

FRACTIONS \pm



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 08AM07, MC1631, TB-615+

SIZE
A

CODE IDENT
15542

DRAWING NO:

98-PL-344

REV:

A

FILE: 98PL344



SCALE:

8:1

SHEET:

1 OF 1

Evaluation Board and Circuit



Schematic Diagram

ITEM	DESCRIPTION
C1, C6	CAP, 9.1pF
C2, C4	CAP, 100pF
C3	CAP, 5.6pF
C5, C7	CAP, 0.1uF
R1	RES, 267 Ohm
Rbias	RES, 750 Ohm
L1	IND, 6.8nH
L2	IND, 15nH
DUT	PMA2-162LN+

NOTES:

1. SMA Female connectors.
2. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.010 inch.

Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C or -45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
	monoethanolamine at 63°C to 70°C	