



LOW NOISE, HIGH GAIN & IP3


# Monolithic Amplifier PMA4-33GLN+

Mini-Circuits

50Ω 0.7 to 3.0 GHz

## THE BIG DEAL

- Low noise figure, 0.47 dB typ. at 900 MHz
- High gain, 39 dB typ. at 900 MHz
- High OIP3, +40 dBm typ. at 900 MHz
- High Pout, P1dB 22.6 dBm typ. at 900 MHz



Generic photo used for illustration purposes only

CASE STYLE: DG1886

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## APPLICATIONS

- Base station infrastructure
- Portable Wireless
- LTE
- GPS
- GSM
- Airborne radar

## PRODUCT OVERVIEW

Mini-Circuits PMA4-33GLN+ is an E-PHEMT\* based, low noise, dual chip, MMIC amplifier with a unique combination of low noise, high gain and high IP3, making this amplifier ideal for sensitive, high-dynamic-range receiver applications. This design operates on a single 5V supply, is well matched for 50Ω systems, and comes in a 4mm x 4mm, low-profile package accommodating dense circuit board layouts.

## KEY FEATURES

Feature	Advantages
Low noise, 0.47 dB at 0.9 GHz	Enables lower system noise figure performance
High Gain <ul style="list-style-type: none"> <li>• 38.9 dB at 900 MHz</li> <li>• 26.9 dB at 2000 MHz</li> </ul>	High gain with low noise minimizes the effect of noise figure reduction resulting from cascading of multiple stages and simplifies circuit design.
High IP3 <ul style="list-style-type: none"> <li>• +40.4 dBm at 0.9 GHz</li> <li>• +40.2 dBm at 2 GHz</li> </ul>	Combination of low noise and high IP3 makes this MMIC amplifier ideal for use in low noise receiver front end (RFE) as it gives the user advantages of sensitivity & two-tone IM performance at both ends of the dynamic range.
High max input power <ul style="list-style-type: none"> <li>• +24 dBm</li> </ul>	Ruggedized design provides high power handling for input powers common at receiver inputs, eliminating the need for an external limiter in most cases.
4 x 4mm 16-lead MCLP package	Provides low inductance, repeatable transitions, and excellent thermal contact to PCB
High reliability	Low signal operating current of 154 mA nominal maintains junction temperatures typically below 103°C at 85°C ground lead temperature.

\*Enhancement mode Pseudomorphic High Electron Mobility Transistor

REV. B  
ECO-010881  
PMA4-33GLN+  
TH/RS/CP  
211130





LOW NOISE, HIGH GAIN & IP3

# Monolithic Amplifier **PMA4-33GLN+**

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C AND 5V, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		0.7		3.0	GHz
Noise Figure	0.7		0.53	—	dB
	0.9		0.47	0.85	
	1.5		0.66	—	
	2.0		0.91	—	
	3.0		1.79	—	
Gain	0.7	35.0	41.3	—	dB
	0.9		38.9		
	1.5		31.8		
	2.0		26.9		
	3.0		18.0		
Input Return Loss	0.7		9.1		dB
	0.9		12.3		
	1.5		13.0		
	2.0		11.6		
	3.0		9.4		
Output Return Loss	0.7		5.5		dB
	0.9		10.0		
	1.5		12.8		
	2.0		6.7		
	3.0		7.0		
Output Power @1 dB compression <sup>2</sup>	0.7		22.5		dBm
	0.9		22.6		
	1.5		22.6		
	2.0		22.9		
	3.0		20.6		
Output IP3	0.7		35.8		dBm
	0.9		40.4		
	1.5		41.0		
	2.0		40.2		
	3.0		35.7		
Device Operating Voltage			5.0		V
Device Operating Current	Q1 <sup>2</sup>		55		mA
	Q2 <sup>2</sup>		97		
	Total <sup>2</sup>		152	186	
Device Current Variation vs. Temperature at 5V <sup>3</sup>			-135		µA/°C
Device Current Variation vs. Voltage at 25°C			0.027		mA/mV
Thermal Resistance, junction-to-ground lead			53 (Q1), 36 (Q2)		°C/W

1. Measured on Mini-Circuits Characterization test board TB-754+. See Characterization Test Circuit (Fig. 1)  
 2. Current increases at P1dB  
 3. (Current at 85°C - Current at -45°C)/130





# Monolithic Amplifier PMA4-33GLN+

## MAXIMUM RATINGS<sup>4</sup>


Parameter	Ratings (Q1)	Ratings (Q2)
Operating Temperature (ground lead)	-40°C to 85°C	-40°C to 85°C
Storage Temperature	-65°C to 150°C	-65°C to 150°C
Total Power Dissipation	0.55W	1W
Input Power (CW)	+24dBm (5 minutes max) <sup>(Note 5)</sup>	+21 dBm (50-2000 MHz) +26 dBm (2000-3000 MHz) <sup>(Note 6)</sup>
Q1 & Q2 cascade on TB-754+	+24 dBm	
DC Voltage	5.5 V	6V

4. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.


5. Measured on Mini-Circuits test board, TB-615+

6. Measured on Mini-Circuits test board, TB-313

## SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



## TOP VIEW




Function	Pad Number	Description (See Figure 1)
RF IN Q1	2	Connects to RF input via C1 and Pad 3 via L1
RF-OUT Q1 & DC IN	5	Connects to RF IN Q2 via C2 and $V_s$ via L2
V Bias Q1	4	Connects to Supply voltage $V_s$ via R1
RF-GND Q1	3	Connects to ground via C4/C5
RF-IN Q2	8	Connects to RF OUT Q1 via C2
RF-OUT Q2 & DC IN	11	Connects to RF OUT via C3 and $V_s$ via L3
Ground	Paddle	Connects to ground
No Connection	1,6,7,9,10,12 to 16	Not used internally. Connected to ground on test board



LOW NOISE, HIGH GAIN & IP3

# Monolithic Amplifier PMA4-33GLN+

## RECOMMENDED APPLICATION AND CHARACTERIZATION TEST CIRCUIT



### BOM OF TEST BOARD TB-754+

SEQ	Size	Description
DUT	4x4 mm	PMA4-33GLN+ Amplifier
L1	0402	Inductor 15nH
L2	0402	Inductor 5.6nH
L3	0402	Inductor 82nH
C1	0402	Capacitor 56pF
C2	0402	Capacitor 82pF
C3	0402	Capacitor 68pF
C4	0402	Capacitor 1000pF
C5 to C8	0402	Capacitor 0.1μF
R1	0402	Resistor, 1kΩ

Fig 1. Application and Characterization circuit


Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-754+)

Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -40 dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 5 dBm/tone at output.

## PRODUCT MARKING



Marking may contain other features or characters for internal lot control



LOW NOISE, HIGH GAIN & IP3

# Monolithic Amplifier PMA4-33GLN+

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DG1886 Plastic package, exposed paddle, lead finish: tin-silver over nickel
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 or 1K devices
Suggested Layout for PCB Design	PL-407
Evaluation Board	TB-754+
Environmental Ratings	ENV08T1

### ESD RATING


Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (pass 25V) in accordance with ANSI/ESD STM5.2-1999

### MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

### MSL TEST FLOW CHART



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

**NOTE: Use PDF Bookmarks to view DATA at required conditions**

**Definitions:**

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 152.54mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	25.82	79.98	1.25	5.04	44.31	1.20	32.55	18.80	3.66
200.0	30.26	99.36	0.62	4.78	126.67	1.25	33.49	19.82	1.61
250.0	34.02	78.20	1.06	4.37	11.60	1.13	34.68	20.48	1.16
300.0	37.22	83.22	1.21	3.99	14.93	1.05	34.67	21.15	0.91
350.0	39.27	76.82	1.71	3.70	7.56	0.95	36.11	21.38	0.72
400.0	40.86	78.24	2.52	3.55	9.56	0.86	36.18	21.59	0.55
450.0	41.86	74.55	3.48	3.54	7.06	0.79	35.53	21.90	0.52
500.0	42.44	71.11	4.47	3.70	5.39	0.75	36.48	22.04	0.64
600.0	42.54	65.82	6.87	4.61	4.07	0.75	38.00	22.66	0.45
700.0	41.87	62.36	9.35	6.24	3.76	0.81	38.94	22.68	0.55
800.0	40.66	60.28	11.56	8.41	3.94	0.89	40.13	22.76	0.44
900.0	39.30	58.38	13.01	11.11	4.04	0.95	41.80	22.59	0.53
1000.0	37.96	57.16	14.04	14.38	4.29	0.99	43.85	22.73	0.42
1100.0	36.65	56.03	14.64	17.62	4.47	1.01	43.79	22.81	0.49
1200.0	35.39	54.97	14.75	19.18	4.58	1.01	42.94	22.83	0.54
1300.0	34.25	54.13	14.81	17.73	4.72	1.01	42.18	22.82	0.63
1400.0	33.12	53.20	14.61	15.37	4.76	1.00	41.94	22.91	0.65
1500.0	32.10	52.30	14.08	13.54	4.72	0.99	42.38	22.94	0.69
1600.0	31.14	51.50	13.94	11.99	4.71	0.97	42.13	22.71	0.73
1700.0	30.18	50.75	13.59	10.85	4.71	0.95	41.22	23.15	0.81
1800.0	29.30	49.97	12.97	9.92	4.64	0.94	41.52	23.13	0.87
1900.0	28.41	49.07	12.64	9.15	4.52	0.92	41.51	23.04	0.85
2000.0	27.52	48.45	12.28	8.54	4.56	0.90	41.12	22.84	0.95
2200.0	25.70	47.02	11.73	7.68	4.59	0.87	41.01	22.99	1.04
2400.0	23.87	45.74	11.25	7.19	4.76	0.85	40.18	23.68	1.16
2600.0	22.08	44.60	10.91	7.03	5.06	0.85	39.33	23.37	1.26
2800.0	20.25	43.49	10.59	7.05	5.47	0.85	37.34	22.39	1.35
3000.0	18.57	42.31	10.27	7.20	5.80	0.86	36.05	21.41	1.55
3200.0	16.92	41.25	9.84	7.48	6.23	0.89	34.72	20.16	1.64
3400.0	15.43	40.15	9.65	7.63	6.50	0.90	32.71	18.96	1.84
3600.0	14.04	38.99	9.38	7.76	6.65	0.91	31.28	17.67	1.96
3800.0	12.69	37.96	9.08	7.79	6.81	0.92	30.67	16.63	2.23
4000.0	11.51	36.78	9.00	7.66	6.72	0.92	29.06	15.73	2.50
4200.0	10.39	35.58	8.73	7.65	6.56	0.93	27.21	14.70	2.75
4400.0	9.21	34.48	8.61	7.43	6.48	0.93	25.28	13.55	3.14
4600.0	8.50	32.89	8.57	7.30	5.76	0.93	24.06	12.71	3.30
4800.0	8.04	31.06	8.08	7.05	4.72	0.94	22.46	11.63	3.62
5000.0	7.55	29.30	7.88	6.75	3.93	0.93	20.70	9.76	3.87

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 145.71mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	25.48	80.37	1.12	5.06	43.72	1.22	32.06	18.35	3.78
200.0	29.95	88.55	0.59	4.79	36.07	1.25	33.08	19.42	1.67
250.0	33.73	77.83	1.11	4.38	11.97	1.12	34.18	20.14	1.15
300.0	36.96	87.73	1.23	3.98	25.40	1.05	34.38	20.87	0.94
350.0	39.05	83.33	1.68	3.69	15.44	0.96	35.83	21.13	0.76
400.0	40.67	78.64	2.41	3.52	9.85	0.86	35.46	21.36	0.53
450.0	41.69	71.68	3.37	3.51	5.14	0.78	36.56	21.66	0.55
500.0	42.31	70.84	4.40	3.64	5.23	0.74	36.54	21.79	0.60
600.0	42.43	65.33	6.85	4.56	3.88	0.74	37.54	22.39	0.43
700.0	41.76	61.96	9.35	6.18	3.62	0.81	39.19	22.35	0.57
800.0	40.55	60.03	11.40	8.34	3.86	0.89	40.18	22.44	0.49
900.0	39.19	58.45	12.94	11.03	4.11	0.95	42.11	22.29	0.54
1000.0	37.82	56.84	13.85	14.35	4.20	0.99	43.58	22.45	0.44
1100.0	36.51	55.81	14.32	17.65	4.41	1.01	42.82	22.52	0.52
1200.0	35.24	54.77	14.45	19.34	4.55	1.02	42.63	22.49	0.55
1300.0	34.09	53.76	14.54	17.93	4.60	1.01	41.58	22.50	0.63
1400.0	32.96	53.01	14.39	15.51	4.73	1.00	42.52	22.60	0.66
1500.0	31.94	52.12	13.90	13.67	4.70	0.99	41.85	22.63	0.69
1600.0	30.97	51.33	13.69	12.07	4.70	0.97	41.26	22.41	0.77
1700.0	30.02	50.50	13.28	10.89	4.65	0.96	41.01	22.90	0.83
1800.0	29.14	49.80	12.79	9.97	4.63	0.94	41.07	22.84	0.85
1900.0	28.26	48.95	12.55	9.19	4.54	0.92	40.81	22.72	0.88
2000.0	27.36	48.22	12.21	8.55	4.52	0.90	40.76	22.52	0.95
2200.0	25.55	46.92	11.61	7.70	4.62	0.87	40.65	22.69	1.06
2400.0	23.71	45.69	11.21	7.19	4.81	0.85	40.12	23.40	1.18
2600.0	21.91	44.52	10.78	7.01	5.10	0.85	39.35	23.01	1.27
2800.0	20.08	43.49	10.53	7.05	5.57	0.85	37.70	21.99	1.39
3000.0	18.38	42.41	10.18	7.19	5.98	0.87	36.30	21.01	1.62
3200.0	16.74	41.36	9.79	7.46	6.41	0.89	34.69	19.74	1.65
3400.0	15.25	40.14	9.53	7.61	6.60	0.90	32.39	18.55	1.82
3600.0	13.85	39.09	9.30	7.73	6.84	0.91	30.85	17.25	1.99
3800.0	12.50	37.97	9.06	7.75	6.94	0.92	30.09	16.17	2.20
4000.0	11.33	36.82	8.90	7.65	6.86	0.93	28.40	15.24	2.45
4200.0	10.20	35.60	8.67	7.62	6.70	0.93	26.48	14.23	2.72
4400.0	9.03	34.52	8.51	7.42	6.61	0.93	24.55	13.07	3.17
4600.0	8.33	32.93	8.45	7.30	5.88	0.94	23.38	12.23	3.36
4800.0	7.86	31.07	7.96	7.05	4.80	0.94	21.92	11.20	3.50
5000.0	7.38	29.38	7.76	6.77	4.03	0.94	20.34	9.40	3.63

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 160.98mA @ Temperature = +25°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	26.08	76.07	1.23	5.03	26.70	1.20	32.88	19.20	3.66
200.0	30.50	90.28	0.61	4.76	42.76	1.24	34.02	20.23	1.53
250.0	34.24	76.16	1.16	4.36	9.79	1.11	34.81	20.89	1.15
300.0	37.41	91.13	1.25	3.98	36.10	1.05	35.17	21.47	0.83
350.0	39.43	87.18	1.72	3.70	23.30	0.96	35.91	21.70	0.71
400.0	40.99	75.02	2.56	3.55	6.76	0.85	36.41	21.90	0.54
450.0	41.96	73.77	3.51	3.56	6.50	0.78	36.92	22.19	0.53
500.0	42.54	71.23	4.54	3.69	5.45	0.74	36.64	22.34	0.61
600.0	42.61	66.46	6.94	4.61	4.35	0.75	37.49	22.98	0.47
700.0	41.94	63.07	9.52	6.21	4.04	0.81	39.68	23.04	0.55
800.0	40.74	60.46	11.60	8.34	3.98	0.88	41.83	23.12	0.49
900.0	39.40	59.02	13.12	10.96	4.28	0.94	41.25	22.92	0.50
1000.0	38.06	57.55	14.13	14.24	4.43	0.98	43.34	23.05	0.45
1100.0	36.76	56.43	14.84	17.43	4.62	1.00	43.18	23.15	0.52
1200.0	35.51	55.34	14.98	18.98	4.73	1.01	44.95	23.17	0.52
1300.0	34.36	54.40	15.15	17.63	4.81	1.01	43.78	23.15	0.60
1400.0	33.24	53.55	14.80	15.30	4.88	1.00	42.52	23.22	0.64
1500.0	32.23	52.62	14.33	13.51	4.83	0.99	43.88	23.27	0.67
1600.0	31.26	51.88	14.16	11.97	4.86	0.97	42.65	23.04	0.69
1700.0	30.31	50.99	13.72	10.81	4.77	0.95	42.73	23.44	0.82
1800.0	29.44	50.13	13.22	9.90	4.66	0.93	42.38	23.44	0.83
1900.0	28.56	49.37	12.84	9.14	4.60	0.92	41.16	23.36	0.87
2000.0	27.66	48.70	12.56	8.53	4.63	0.90	41.44	23.16	0.93
2200.0	25.87	47.12	11.93	7.68	4.56	0.87	40.80	23.31	1.04
2400.0	24.04	45.86	11.45	7.19	4.74	0.85	40.56	24.00	1.15
2600.0	22.27	44.58	11.02	7.02	4.96	0.84	38.96	23.76	1.25
2800.0	20.45	43.53	10.78	7.08	5.41	0.85	37.35	22.83	1.33
3000.0	18.77	42.36	10.39	7.23	5.73	0.86	36.40	21.86	1.58
3200.0	17.13	41.23	9.93	7.51	6.09	0.89	34.99	20.63	1.64
3400.0	15.64	40.10	9.72	7.69	6.35	0.90	33.19	19.48	1.86
3600.0	14.25	39.06	9.53	7.82	6.59	0.91	31.84	18.21	2.09
3800.0	12.91	37.95	9.29	7.84	6.70	0.92	31.26	17.17	2.20
4000.0	11.73	36.78	9.13	7.74	6.60	0.92	29.78	16.24	2.55
4200.0	10.59	35.59	8.93	7.70	6.48	0.93	27.94	15.29	2.89
4400.0	9.44	34.54	8.75	7.50	6.41	0.93	26.03	14.17	3.16
4600.0	8.73	32.92	8.74	7.36	5.69	0.93	24.70	13.36	3.42
4800.0	8.28	31.13	8.23	7.10	4.68	0.94	22.98	12.28	3.56
5000.0	7.79	29.41	8.09	6.80	3.92	0.93	21.02	10.46	3.82



## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 163.26mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	26.80	83.34	1.08	5.07	51.53	1.22	33.69	19.15	3.03
200.0	31.02	102.13	0.58	4.87	151.83	1.26	34.86	20.44	1.24
250.0	34.71	80.84	1.13	4.53	15.51	1.14	37.36	21.31	0.85
300.0	37.81	77.91	1.24	4.24	8.28	1.08	36.30	22.21	0.69
350.0	39.76	76.94	1.66	4.04	7.48	1.00	37.25	22.48	0.54
400.0	41.23	77.12	2.37	3.96	8.32	0.93	37.52	22.73	0.39
450.0	42.13	74.90	3.27	4.00	7.37	0.87	39.32	22.97	0.41
500.0	42.63	71.41	4.28	4.21	5.73	0.82	38.86	23.01	0.45
600.0	42.72	66.66	6.52	5.15	4.53	0.81	38.80	23.48	0.36
700.0	42.11	63.19	8.88	6.63	4.06	0.85	40.13	23.27	0.40
800.0	41.02	60.71	10.86	8.56	3.95	0.90	40.86	23.34	0.32
900.0	39.79	59.08	12.38	10.99	4.10	0.95	40.72	23.18	0.37
1000.0	38.54	57.79	13.72	13.48	4.27	0.98	42.32	23.45	0.30
1100.0	37.30	56.42	14.48	15.69	4.29	1.00	43.58	23.55	0.34
1200.0	36.10	55.34	14.94	16.58	4.38	1.00	45.27	23.49	0.39
1300.0	34.98	54.39	15.28	15.80	4.44	1.00	45.60	23.54	0.46
1400.0	33.88	53.53	15.08	14.45	4.51	0.99	48.65	23.67	0.46
1500.0	32.88	52.73	14.64	13.13	4.53	0.98	47.02	23.67	0.49
1600.0	31.93	51.85	14.49	11.92	4.48	0.97	46.76	23.46	0.55
1700.0	30.97	51.11	14.09	11.02	4.51	0.95	44.18	24.09	0.62
1800.0	30.10	50.32	13.49	10.19	4.45	0.94	43.88	23.90	0.59
1900.0	29.23	49.61	13.22	9.52	4.44	0.93	43.28	23.66	0.60
2000.0	28.34	48.94	12.81	8.94	4.47	0.91	43.34	23.45	0.66
2200.0	26.56	47.56	12.04	8.07	4.51	0.89	40.61	23.74	0.74
2400.0	24.74	46.35	11.49	7.42	4.67	0.86	39.81	24.50	0.82
2600.0	23.00	45.13	11.02	7.13	4.88	0.85	38.34	23.97	0.87
2800.0	21.24	44.08	10.63	7.06	5.24	0.85	36.68	23.21	0.93
3000.0	19.58	42.89	10.15	7.01	5.46	0.86	35.46	22.53	1.14
3200.0	17.99	41.86	9.76	7.21	5.83	0.87	33.89	21.47	1.14
3400.0	16.57	40.58	9.37	7.34	5.89	0.89	31.89	20.47	1.35
3600.0	15.19	39.52	9.03	7.34	6.03	0.90	30.38	19.05	1.50
3800.0	13.87	38.38	8.86	7.30	6.08	0.90	29.89	17.94	1.64
4000.0	12.70	37.17	8.57	7.22	5.93	0.91	28.39	16.96	1.89
4200.0	11.58	36.06	8.44	7.09	5.84	0.91	26.74	15.93	2.02
4400.0	10.43	34.95	8.35	6.89	5.73	0.91	25.09	14.77	2.36
4600.0	9.69	33.43	8.27	6.83	5.15	0.92	24.22	14.02	2.48
4800.0	9.25	31.63	7.83	6.48	4.18	0.92	23.18	13.38	2.70
5000.0	8.84	29.76	7.60	6.21	3.38	0.91	21.22	11.88	2.96

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 150.87mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	26.23	78.30	1.04	5.09	29.66	1.23	33.26	18.89	2.86
200.0	30.50	83.70	0.58	4.88	19.65	1.26	34.07	20.15	1.22
250.0	34.22	80.87	1.06	4.54	14.66	1.16	35.82	20.97	0.79
300.0	37.37	91.04	1.19	4.24	36.27	1.10	36.36	21.90	0.66
350.0	39.36	76.34	1.66	4.04	7.32	1.00	36.64	22.14	0.55
400.0	40.88	76.39	2.35	3.95	7.92	0.93	37.25	22.36	0.37
450.0	41.82	75.31	3.20	3.99	7.85	0.87	36.94	22.60	0.41
500.0	42.36	69.76	4.20	4.20	4.89	0.82	37.54	22.63	0.46
600.0	42.47	66.02	6.50	5.13	4.33	0.81	37.24	23.10	0.33
700.0	41.88	62.88	8.86	6.62	4.02	0.85	38.58	22.88	0.41
800.0	40.78	60.60	10.88	8.57	4.01	0.90	39.76	22.96	0.33
900.0	39.54	58.63	12.46	11.01	4.01	0.95	40.41	22.81	0.35
1000.0	38.28	57.36	13.67	13.51	4.18	0.98	41.58	23.09	0.28
1100.0	37.04	56.20	14.49	15.76	4.31	1.00	41.68	23.18	0.32
1200.0	35.83	55.04	14.69	16.68	4.35	1.00	44.11	23.11	0.37
1300.0	34.71	54.04	15.03	15.91	4.40	1.00	45.51	23.17	0.43
1400.0	33.60	53.25	14.87	14.55	4.50	0.99	46.00	23.30	0.45
1500.0	32.60	52.53	14.45	13.21	4.57	0.98	46.85	23.31	0.46
1600.0	31.65	51.63	14.32	12.00	4.51	0.97	46.89	23.11	0.48
1700.0	30.69	50.98	13.79	11.08	4.58	0.96	44.28	23.74	0.58
1800.0	29.82	50.18	13.40	10.25	4.52	0.94	43.33	23.55	0.56
1900.0	28.95	49.48	13.09	9.57	4.52	0.93	44.07	23.30	0.59
2000.0	28.05	48.74	12.77	8.98	4.52	0.91	43.24	23.09	0.65
2200.0	26.28	47.44	11.94	8.10	4.59	0.89	40.66	23.38	0.70
2400.0	24.46	46.20	11.41	7.44	4.75	0.86	39.61	24.14	0.84
2600.0	22.71	45.05	11.10	7.15	5.01	0.85	38.05	23.54	0.86
2800.0	20.96	44.02	10.65	7.08	5.38	0.85	36.34	22.77	0.93
3000.0	19.30	42.85	10.17	7.02	5.62	0.86	35.06	22.10	1.15
3200.0	17.71	41.85	9.86	7.22	6.02	0.87	33.31	21.02	1.15
3400.0	16.29	40.61	9.44	7.35	6.12	0.89	31.31	19.97	1.28
3600.0	14.91	39.57	9.14	7.36	6.28	0.90	29.57	18.48	1.47
3800.0	13.59	38.47	9.02	7.31	6.37	0.90	28.90	17.35	1.62
4000.0	12.43	37.28	8.68	7.23	6.21	0.91	27.35	16.38	1.82
4200.0	11.30	36.15	8.50	7.10	6.09	0.91	25.68	15.33	2.09
4400.0	10.15	35.07	8.49	6.91	6.03	0.91	23.97	14.19	2.35
4600.0	9.42	33.56	8.33	6.85	5.41	0.92	23.25	13.46	2.33
4800.0	8.99	31.78	7.91	6.50	4.40	0.91	22.39	12.89	2.61
5000.0	8.58	29.93	7.53	6.24	3.54	0.92	20.64	11.61	2.87

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 169.63mA @ Temperature = -45°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	26.92	77.24	1.13	5.06	26.26	1.22	34.20	19.57	3.02
200.0	31.15	81.50	0.58	4.86	14.02	1.26	35.19	20.88	1.28
250.0	34.82	83.53	1.02	4.53	18.82	1.16	37.23	21.74	0.83
300.0	37.91	81.12	1.18	4.24	11.26	1.09	37.33	22.59	0.71
350.0	39.83	80.05	1.66	4.04	10.31	1.01	37.84	22.86	0.58
400.0	41.28	77.23	2.47	3.97	8.63	0.92	38.19	23.08	0.40
450.0	42.16	74.78	3.39	4.01	7.40	0.86	37.75	23.34	0.40
500.0	42.65	71.93	4.30	4.23	6.07	0.83	39.16	23.38	0.49
600.0	42.70	66.88	6.59	5.15	4.67	0.81	39.08	23.85	0.36
700.0	42.10	63.74	8.97	6.62	4.32	0.85	40.58	23.64	0.43
800.0	41.00	61.28	10.97	8.53	4.22	0.90	40.45	23.70	0.32
900.0	39.78	59.30	12.50	10.92	4.21	0.95	41.76	23.50	0.38
1000.0	38.53	58.01	13.79	13.36	4.38	0.98	42.46	23.78	0.29
1100.0	37.31	56.71	14.58	15.52	4.43	0.99	46.72	23.91	0.38
1200.0	36.10	55.66	15.07	16.40	4.54	1.00	45.02	23.88	0.40
1300.0	34.99	54.68	15.40	15.66	4.58	1.00	47.10	23.92	0.46
1400.0	33.89	53.92	15.25	14.36	4.70	0.99	52.21	24.05	0.47
1500.0	32.90	53.03	14.87	13.05	4.68	0.98	48.50	24.05	0.50
1600.0	31.94	52.15	14.70	11.87	4.64	0.96	46.39	23.84	0.54
1700.0	30.99	51.42	14.28	10.98	4.66	0.95	45.28	24.44	0.58
1800.0	30.12	50.61	13.71	10.16	4.59	0.94	45.64	24.26	0.59
1900.0	29.26	49.80	13.40	9.50	4.53	0.92	45.31	24.02	0.62
2000.0	28.37	49.09	13.04	8.92	4.54	0.91	43.69	23.80	0.67
2200.0	26.60	47.67	12.27	8.07	4.56	0.88	42.00	24.06	0.75
2400.0	24.79	46.36	11.70	7.43	4.67	0.86	40.92	24.80	0.82
2600.0	23.06	45.12	11.23	7.15	4.86	0.85	39.27	24.24	0.84
2800.0	21.31	44.04	10.83	7.08	5.20	0.85	37.48	23.45	0.94
3000.0	19.66	42.79	10.35	7.03	5.39	0.85	36.37	22.67	1.12
3200.0	18.07	41.73	9.95	7.23	5.73	0.87	34.83	21.48	1.14
3400.0	16.65	40.51	9.59	7.39	5.84	0.89	33.01	20.35	1.31
3600.0	15.28	39.45	9.29	7.40	5.99	0.90	31.53	18.97	1.48
3800.0	13.96	38.34	9.18	7.35	6.06	0.90	31.00	17.90	1.65
4000.0	12.80	37.13	8.85	7.26	5.91	0.91	29.64	16.94	1.80
4200.0	11.67	36.03	8.69	7.13	5.82	0.91	27.99	15.94	2.03
4400.0	10.53	34.95	8.66	6.93	5.75	0.90	26.30	14.87	2.37
4600.0	9.79	33.46	8.53	6.87	5.17	0.91	25.35	14.16	2.36
4800.0	9.36	31.69	8.11	6.52	4.22	0.91	24.08	13.58	2.59
5000.0	8.95	29.84	7.80	6.25	3.41	0.91	21.80	12.12	2.83

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 145.08mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	24.58	78.82	1.29	4.93	45.13	1.18	30.78	18.11	4.41
200.0	29.28	89.92	0.67	4.63	50.64	1.22	31.81	18.87	1.98
250.0	33.13	78.86	1.25	4.17	15.00	1.08	32.67	19.31	1.33
300.0	36.43	88.23	1.37	3.72	30.44	0.99	33.11	19.74	1.11
350.0	38.59	84.37	1.82	3.35	18.17	0.89	33.79	19.96	0.89
400.0	40.29	75.81	2.56	3.11	7.31	0.78	33.96	20.15	0.69
450.0	41.40	72.46	3.50	3.03	5.38	0.70	34.39	20.44	0.70
500.0	42.10	70.45	4.65	3.11	4.81	0.65	35.27	20.61	0.72
600.0	42.29	65.45	7.13	3.92	3.73	0.67	36.14	21.35	0.59
700.0	41.60	62.19	9.59	5.53	3.63	0.76	37.57	21.81	0.66
800.0	40.34	60.35	11.81	7.80	4.03	0.86	39.32	22.03	0.60
900.0	38.90	58.47	13.10	10.52	4.22	0.94	40.25	21.80	0.65
1000.0	37.47	57.13	14.00	14.22	4.51	0.99	39.99	21.78	0.58
1100.0	36.12	56.19	14.43	18.35	4.83	1.01	39.65	21.75	0.64
1200.0	34.83	55.20	14.41	21.25	5.02	1.02	39.34	21.75	0.69
1300.0	33.65	54.45	14.39	19.46	5.25	1.02	38.63	21.58	0.77
1400.0	32.52	53.51	14.22	16.02	5.28	1.01	38.70	21.60	0.81
1500.0	31.51	52.58	13.72	13.99	5.22	1.00	38.73	21.70	0.88
1600.0	30.55	51.79	13.30	12.11	5.18	0.98	38.70	21.51	0.92
1700.0	29.61	50.94	13.06	10.74	5.10	0.96	38.59	21.76	1.05
1800.0	28.75	50.11	12.64	9.84	5.00	0.94	38.77	21.96	1.09
1900.0	27.87	49.22	12.39	8.96	4.86	0.91	38.85	22.06	1.12
2000.0	27.00	48.40	12.16	8.28	4.77	0.89	38.97	21.99	1.19
2200.0	25.20	46.93	11.49	7.50	4.76	0.86	38.71	22.13	1.33
2400.0	23.39	45.51	11.26	7.08	4.88	0.84	38.58	22.75	1.49
2600.0	21.57	44.28	10.90	7.01	5.17	0.84	38.01	22.65	1.61
2800.0	19.72	43.08	10.70	7.15	5.59	0.85	36.60	21.67	1.72
3000.0	17.99	42.00	10.60	7.39	6.08	0.87	35.69	20.69	2.02
3200.0	16.30	41.05	10.06	7.69	6.62	0.89	34.46	19.62	2.15
3400.0	14.76	39.88	10.09	7.87	6.94	0.90	32.33	18.48	2.44
3600.0	13.36	38.92	9.86	8.16	7.33	0.92	31.09	17.35	2.65
3800.0	11.99	37.79	9.58	8.18	7.45	0.93	30.31	16.29	2.91
4000.0	10.82	36.59	9.76	8.11	7.41	0.93	28.64	15.45	3.18
4200.0	9.67	35.36	9.24	8.23	7.24	0.95	26.72	14.46	3.56
4400.0	8.47	34.29	9.03	7.94	7.17	0.94	24.77	13.34	3.92
4600.0	7.79	32.62	9.28	7.86	6.39	0.94	23.47	12.38	4.10
4800.0	7.29	30.81	8.61	7.77	5.32	0.96	21.95	11.04	4.46
5000.0	6.76	29.13	8.74	7.44	4.58	0.94	20.81	9.91	4.91

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 137.78mA @ Temperature = +85°C

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	24.24	81.22	1.24	4.95	59.58	1.19	30.52	17.71	4.50
200.0	28.98	89.70	0.67	4.65	50.84	1.22	31.56	18.46	2.05
250.0	32.84	77.50	1.05	4.18	11.89	1.10	32.59	18.94	1.37
300.0	36.17	79.00	1.26	3.73	10.59	1.00	32.59	19.44	1.13
350.0	38.36	76.39	1.76	3.35	7.70	0.88	33.34	19.63	0.89
400.0	40.09	77.32	2.50	3.10	8.60	0.78	33.74	19.84	0.70
450.0	41.23	71.91	3.53	3.00	5.20	0.69	34.53	20.14	0.63
500.0	41.96	70.96	4.51	3.07	5.03	0.66	34.03	20.32	0.74
600.0	42.17	65.42	7.06	3.87	3.73	0.67	36.06	21.06	0.56
700.0	41.49	62.11	9.53	5.48	3.62	0.76	38.12	21.48	0.66
800.0	40.23	59.96	11.68	7.75	3.89	0.86	39.12	21.68	0.59
900.0	38.78	58.16	12.94	10.45	4.11	0.94	39.61	21.46	0.65
1000.0	37.35	57.05	13.65	14.13	4.51	0.99	39.21	21.47	0.59
1100.0	35.99	56.02	14.21	18.23	4.80	1.01	39.19	21.45	0.63
1200.0	34.69	55.03	14.08	21.24	4.99	1.02	39.36	21.44	0.70
1300.0	33.52	54.12	14.06	19.62	5.12	1.02	38.42	21.30	0.79
1400.0	32.38	53.31	14.00	16.16	5.24	1.01	38.49	21.32	0.84
1500.0	31.37	52.53	13.34	14.12	5.26	1.00	38.42	21.40	0.89
1600.0	30.41	51.65	12.97	12.21	5.17	0.98	38.09	21.23	0.93
1700.0	29.47	50.88	12.77	10.83	5.14	0.96	38.27	21.49	1.07
1800.0	28.61	50.02	12.49	9.92	5.03	0.94	38.37	21.67	1.09
1900.0	27.74	49.16	12.15	9.02	4.89	0.92	38.33	21.75	1.12
2000.0	26.87	48.36	11.95	8.34	4.81	0.90	38.73	21.67	1.22
2200.0	25.07	46.88	11.30	7.53	4.80	0.87	38.25	21.81	1.34
2400.0	23.26	45.47	11.14	7.10	4.93	0.85	38.32	22.47	1.53
2600.0	21.44	44.27	10.73	7.01	5.23	0.85	37.83	22.34	1.62
2800.0	19.58	43.14	10.68	7.14	5.71	0.86	36.76	21.36	1.76
3000.0	17.85	42.03	10.50	7.37	6.18	0.87	35.84	20.34	2.00
3200.0	16.16	41.04	10.01	7.66	6.70	0.89	34.47	19.20	2.12
3400.0	14.62	39.94	9.94	7.83	7.06	0.91	32.20	18.05	2.31
3600.0	13.21	38.94	9.71	8.12	7.42	0.92	30.73	16.85	2.68
3800.0	11.84	37.81	9.42	8.14	7.54	0.93	29.76	15.80	2.87
4000.0	10.68	36.64	9.72	8.06	7.55	0.93	28.08	14.90	3.23
4200.0	9.53	35.40	9.16	8.20	7.36	0.95	26.07	13.93	3.51
4400.0	8.34	34.34	8.95	7.91	7.29	0.95	24.13	12.83	4.04
4600.0	7.66	32.67	9.10	7.84	6.48	0.94	22.89	11.88	4.10
4800.0	7.16	30.85	8.47	7.77	5.40	0.96	21.47	10.58	4.52
5000.0	6.62	29.15	8.55	7.44	4.63	0.95	20.47	9.40	4.73

## Typical Performance Data

### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)









Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 150.50mA @ Temperature = +85°C








FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
					K	Measure			
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
150.0	24.76	77.45	1.32	4.89	38.54	1.17	30.88	18.36	4.46
200.0	29.46	87.88	0.65	4.59	38.03	1.21	32.00	19.02	1.98
250.0	33.28	82.83	1.09	4.13	20.85	1.09	32.96	19.45	1.30
300.0	36.57	85.92	1.34	3.69	22.25	0.99	32.99	19.83	1.10
350.0	38.71	84.34	1.92	3.33	18.73	0.87	34.09	20.02	0.92
400.0	40.39	76.62	2.62	3.09	7.99	0.77	34.29	20.21	0.68
450.0	41.48	73.93	3.61	3.01	6.34	0.70	34.83	20.49	0.68
500.0	42.17	70.34	4.69	3.10	4.70	0.65	35.18	20.67	0.73
600.0	42.34	66.36	7.25	3.90	4.11	0.67	36.10	21.40	0.56
700.0	41.65	62.68	9.76	5.51	3.81	0.76	38.33	21.95	0.67
800.0	40.40	60.74	12.01	7.78	4.19	0.86	39.04	22.23	0.59
900.0	38.97	58.83	13.41	10.50	4.37	0.93	39.86	21.99	0.63
1000.0	37.55	57.78	14.19	14.25	4.82	0.99	39.58	21.93	0.59
1100.0	36.19	56.56	14.70	18.46	5.02	1.01	39.18	21.87	0.64
1200.0	34.90	55.77	14.64	21.41	5.33	1.02	39.64	21.85	0.71
1300.0	33.73	54.74	14.62	19.46	5.38	1.02	38.67	21.66	0.79
1400.0	32.60	53.90	14.52	15.94	5.48	1.01	38.78	21.63	0.83
1500.0	31.60	52.99	13.95	13.90	5.42	0.99	38.82	21.76	0.88
1600.0	30.63	52.07	13.47	12.02	5.31	0.98	38.70	21.58	0.94
1700.0	29.69	51.27	13.37	10.65	5.26	0.95	38.75	21.77	1.04
1800.0	28.84	50.38	12.93	9.76	5.11	0.93	38.88	22.02	1.09
1900.0	27.96	49.48	12.57	8.88	4.95	0.91	39.36	22.16	1.13
2000.0	27.10	48.59	12.35	8.21	4.82	0.89	39.14	22.14	1.21
2200.0	25.31	47.04	11.67	7.45	4.77	0.86	38.93	22.25	1.35
2400.0	23.51	45.59	11.44	7.05	4.86	0.84	38.33	22.85	1.47
2600.0	21.70	44.23	10.97	7.00	5.07	0.84	37.76	22.81	1.59
2800.0	19.86	43.05	10.98	7.17	5.52	0.85	36.49	21.93	1.74
3000.0	18.13	41.95	10.79	7.45	5.99	0.87	35.61	20.96	2.01
3200.0	16.44	40.95	10.24	7.77	6.50	0.89	34.64	19.99	2.11
3400.0	14.91	39.84	10.37	7.98	6.87	0.90	32.67	18.92	2.35
3600.0	13.50	38.88	10.01	8.31	7.25	0.92	31.41	17.79	2.61
3800.0	12.13	37.72	9.73	8.33	7.35	0.93	30.69	16.81	2.85
4000.0	10.96	36.55	10.02	8.25	7.35	0.93	29.18	15.90	3.25
4200.0	9.80	35.31	9.49	8.37	7.18	0.95	27.31	14.97	3.46
4400.0	8.62	34.26	9.29	8.06	7.13	0.94	25.37	13.86	3.94
4600.0	7.94	32.62	9.59	7.97	6.38	0.94	24.00	12.87	4.19
4800.0	7.42	30.84	8.92	7.88	5.34	0.95	22.39	11.43	4.40
5000.0	6.89	29.17	9.10	7.52	4.61	0.94	21.16	10.67	4.73



## Typical Performance Curves




## Typical Performance Curves






## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm 0.002$

CASE #	A	B	C	D	E	F	G	H	J	K
DG1886	.157 (4.00)	.157 (4.00)	.035 (0.90)	.009 (0.24)	.098 (2.50)	.098 (2.50)	.012 (0.30)	-- --	.018 (0.45)	.026 (0.65)


CASE #	L	M	N	P	Q	R	WT. GRAM
DG1886	.185 (4.70)	.185 (4.70)	.085 (2.16)	.014 (0.36)	.035 (0.89)	.85 (2.16)	.04

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.


THIRD ANGLE PROJECTION



REVISIONS

REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M144560	NEW RELEASE	01/22/14	AV	RS


**SUGGESTED MOUNTING CONFIGURATION FOR  
DG1886 CASE STYLE, "16AM03" PIN CODE**



COMPONENT	SIZE
C1-8, L1-3, R1	0402

**NOTES:**

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. CHIP COMPONENT FOOT PRINTS SHOWN FOR REFERENCE. FOR COMPONENT VALUES REFER TO TB-754+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).  
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN AV	01/13/14
TOLERANCES ON:	CHECKED IL	01/22/14
2 PL DECIMALS ±	APPROVED RS	01/22/14
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



**Mini-Circuits®**



13 Neptune Avenue  
Brooklyn NY 11235

**PL, 16AM03, DG1886, TB-754+**

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-407	REV: OR
FILE: 98PL407	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit




Schematic Diagram

COMPONENT	VALUE	SIZE
DUT	EA3	0402
C1	56 pF	
C2	82 pF	
C3	68 pF	
C4	1000 pF	
C5,C6,C7,C8	1.0 uF	
R1	1.0 kOhm	
L1	15 nH	
L2	5.6 nH	
L3	82 nH	

**Notes:**

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C or -45° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	MIL-STD-202, Method 215



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
	monoethanolamine at 63°C to 70°C	